


Direct Burial, Audio & Communication



CATALOG NUMBER	NO. OF PAIRS	AWG SIZE	COND. STRAND.	NOM. INSULATION THICKNESS		NOM. JACKET THICKNESS		NOMINAL O.D.		NOM CAP.* pF/ft	
				INCHES	mm	INCHES	mm	INCHES	mm	A	B
C6061	3	20	10/30	0.013	0.33	0.047	1.19	0.340	8.64	22.0	39.0
C6062	6	20	10/30	0.013	0.33	0.047	1.19	0.442	11.23	22.0	39.0

*A - Capacitance between conductors

*B - Capacitance between one conductor and other conductors connected to shield

Color Code Chart

NO. OF PAIRS	COLORS
1	Black paired with Red
2	Black paired with White
3	Black paired with Green
4	Black paired with Blue
5	Black paired with Yellow
6	Black paired with Brown

Product Construction:

Conductor:

- 20 AWG fully annealed stranded tinned copper per ASTM B-33
- Twisted pairs

Insulation:

- Premium-grade, color-coded polypropylene
- Color Code: See chart below

Shield:

- 100% Flexfoil® aluminum/polyester with 25% overlap, minimum, foil facing in
- Stranded tinned copper drain wire each pair
- Individually shielded pairs

Jacket:

- Permaline® high-density polyethylene, black
- Temperature Range: -20°C to +80°C

Applications:

- Suitable for direct burial
- Outdoor uses
- Applications where total isolation of signal is required
- Suggested voltage rating: 350 volts

Features:

- Permaline® jackets resist deterioration
- Sunlight-resistant

Packaging:

- Please contact Customer Service for packaging and color options