


REV.	DATE	DESCRIPTION
A	04/06/04	MODIFY PART DESCRIPTION - REMOVE "REVERSE POLARITY"
B	05/26/06	REVISE PART DESCRIPTION TO "AMC" JACK



NOTES:
 1. MAX. PANEL THICKNESS = 5mm

Amphenol Connex

AMC JACK TO TNC JACK
 BULKHEAD ADAPTER

242192

REV.	DATE	DESCRIPTION	MATERIAL	FINISH	QTY
8					
7					
6		HEX NUT	BRASS	NICKEL	1
5		LOCK WASHER	BRASS	NICKEL	1
4		BODY	BRASS	NICKEL	1
3		INSULATOR	TEFLON	NATURAL	1
2		CONTACT PIN	BRASS	GOLD	1
1		BODY	BRASS	NICKEL	1
DESCRIPTION		MATERIAL FINISH QTY			

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE INCHES AND FOR CUSTOMER REFERENCE ONLY.	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE MILLIMETERS ONLY.
TOLERANCES FOR MILLIMETERS ARE:	
0.5 - 8mm ± 0.20mm	
8 - 30mm ± 0.40mm	
30 - 120mm ± 0.50mm	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE INCHES AND FOR CUSTOMER REFERENCE ONLY.	
.020 - .315 = ± 0.007"	
.315 - 1.180 = ± 0.015"	
1.180 - 4.724 = ± 0.020"	

APPROVALS	DATE
DRAWN G.R.S.	05/26/06
CHECKED	
ISSUED	
SHEET 1 OF 1	

CAD FILE	DWG. NO.	REV.	SIZE	SCALE
C:/242/242192.DWG	242192.DWG	B	A	NA