


SERIES**4470R
4470****Molded Unshielded RF Coils**

Actual Size

**Physical Parameters**

	Inches	Millimeters
Length	0.880 to 0.910	22.35 to 23.11
Diameter	0.270 to 0.310	6.86 to 7.87
Lead Size		
AWG #21 TCW	0.0260 to .0305	0.66 to 0.77
Lead Length	1.30 Min.	33.02 Min.

Operating Temperature -55°C to +125°C**Current Rating at 90°C Ambient** 35°C Rise**Maximum Power Dissipation at 90°C** 0.540 W**Test Methods** MIL-PRF-15305 test methods, only.
MS21380-01 to MS21380-49, reference.**Marking** DELEVAN; inductance with units and tolerance;
date code (YYWWL). Note: An R before the date code
indicates a RoHS component.

Example: 4470-49J

<i>Front:</i>	<i>Reverse:</i>
DELEVAN	0915B
10mH±5%	

Packaging Tape & reel: 12" reel, 800 pieces max.; 14"
reel, 1300 pieces max.**Made in the U.S.A.**

DASH NUMBER*	MIL DASH # (Ref.)	INDUCTANCE (μH)	TOLERANCE	Q TEST FREQUENCY (MHz)	INDUCTANCE TEST FREQUENCY (MHz)	SRF MINIMUM (MHz)	Q MINIMUM	DC RESISTANCE MAXIMUM (OHMS)	CURRENT RATING MAXIMUM (mA)
MS21380 (Reference) – SERIES 4470 IRON CORE									
-01K	1	1.0	± 10%	25.0	15.0	130	136.0	0.03	4000
-02K	2	1.2	± 10%	7.9	15.0	130	124.0	0.03	4000
-03K	3	1.5	± 10%	7.9	10.0	130	112.0	0.03	4000
-04K	4	1.8	± 10%	7.9	10.0	130	100.0	0.03	4000
-05K	5	2.2	± 10%	7.9	10.0	130	92.0	0.04	3500
-06K	6	2.7	± 10%	7.9	10.0	100	81.6	0.04	3500
-07K	7	3.3	± 10%	7.9	7.9	100	72.0	0.04	3500
-08K	8	3.9	± 10%	7.9	7.9	80	68.0	0.05	3100
-09K	9	4.7	± 10%	7.9	7.9	75	64.0	0.05	3100
-10K	10	5.6	± 10%	7.9	7.9	65	57.6	0.06	3000
-11K	11	6.8	± 10%	7.9	7.9	65	52.0	0.06	3000
-12K	12	8.2	± 10%	7.9	7.9	65	45.6	0.09	2400
-13K	13	10.0	± 10%	7.9	5.0	75	40.0	0.15	1800
-14K	14	12.0	± 10%	2.5	5.0	75	36.0	0.20	1600
-15J	15	15.0	± 5%	2.5	5.0	75	32.0	0.30	1300
-16J	16	18.0	± 5%	2.5	5.0	75	28.8	0.40	1150
-17J	17	22.0	± 5%	2.5	2.5	75	25.6	0.50	1000
-18J	18	27.0	± 5%	2.5	2.5	70	24.0	0.60	900
-19J	19	33.0	± 5%	2.5	2.5	70	22.4	0.70	850
-20J	20	39.0	± 5%	2.5	2.5	70	20.8	1.00	720
-21J	21	47.0	± 5%	2.5	2.5	75	20.0	1.30	620
-22J	22	56.0	± 5%	2.5	2.5	80	17.6	1.80	540
-23J	23	68.0	± 5%	2.5	2.5	100	16.0	2.40	450
-24J	24	82.0	± 5%	2.5	2.5	100	14.4	2.80	425
-25J	25	100.0	± 5%	2.5	1.5	100	13.6	3.20	400
-26J	26	120.0	± 5%	0.79	1.5	100	12.0	4.10	360
-27J	27	150.0	± 5%	0.79	1.0	100	11.2	6.40	280
-28J	28	180.0	± 5%	0.79	1.0	95	9.60	9.50	240
-29J	29	220.0	± 5%	0.79	1.0	95	8.80	12.0	200
-30J	30	270.0	± 5%	0.79	1.0	70	7.20	13.0	195
-31J	31	330.0	± 5%	0.79	0.79	65	6.00	14.0	190
-32J	32	390.0	± 5%	0.79	0.79	65	5.20	15.5	180
-33J	33	470.0	± 5%	0.79	0.79	60	4.40	17.0	170
-34J	34	560.0	± 5%	0.79	0.50	75	3.20	18.5	165
-35J	35	680.0	± 5%	0.79	0.50	75	2.56	20.0	155
-36J	36	820.0	± 5%	0.79	0.50	75	2.24	22.0	150
-37J	37	1000.0	± 5%	0.79	0.50	75	1.92	24.0	145
-38J	38	1200.0	± 5%	0.79	0.50	75	1.68	27.0	137
-39J	39	1500.0	± 5%	0.79	0.40	75	1.52	29.0	130
-40J	40	1800.0	± 5%	0.79	0.40	65	1.36	32.0	125
-41J	41	2200.0	± 5%	0.25	0.25	65	1.20	35.0	120
-42J	42	2700.0	± 5%	0.25	0.25	65	1.04	40.0	112
-43J	43	3300.0	± 5%	0.25	0.25	65	0.96	45.0	105
-44J	44	3900.0	± 5%	0.25	0.25	65	0.80	49.0	100
-45J	45	4700.0	± 5%	0.25	0.25	65	0.76	53.0	95
-46J	46	5600.0	± 5%	0.25	0.25	65	0.68	60.0	90
-47J	47	6800.0	± 5%	0.25	0.25	65	0.60	67.0	85
-48J	48	8200.0	± 5%	0.25	0.25	65	0.52	75.0	82
-49J	49	10000.0	± 5%	0.25	0.15	65	0.47	80.0	80

Optional Tolerances: J = 5% H = 3% G = 2% F = 1%

*Complete part # must include series # PLUS the dash #

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

API Delevan:

[4470-01K](#) [4470-01J](#) [4470-01H](#) [4470-01G](#) [4470-01F](#) [4470-02K](#) [4470-02J](#) [4470-02H](#) [4470-02G](#) [4470-02F](#) [4470-03K](#) [4470-03J](#) [4470-03H](#) [4470-03G](#) [4470-03F](#) [4470-04K](#) [4470-04J](#) [4470-04H](#) [4470-04G](#) [4470-04F](#) [4470-05K](#) [4470-05J](#) [4470-05H](#) [4470-05G](#) [4470-05F](#) [4470-06K](#) [4470-06J](#) [4470-06H](#) [4470-06G](#) [4470-06F](#) [4470-07K](#) [4470-07J](#) [4470-07H](#) [4470-07G](#) [4470-07F](#) [4470-08K](#) [4470-08J](#) [4470-08H](#) [4470-08G](#) [4470-08F](#) [4470-09K](#) [4470-09J](#) [4470-09H](#) [4470-09G](#) [4470-09F](#) [4470-10K](#) [4470-10J](#) [4470-10H](#) [4470-10G](#) [4470-10F](#) [4470-11K](#) [4470-11J](#) [4470-11H](#) [4470-11G](#) [4470-11F](#) [4470-12K](#) [4470-12J](#) [4470-12H](#) [4470-12G](#) [4470-12F](#) [4470-13K](#) [4470-13J](#) [4470-13H](#) [4470-13G](#) [4470-13F](#) [4470-14K](#) [4470-14J](#) [4470-14H](#) [4470-14G](#) [4470-14F](#) [4470-15J](#) [4470-15H](#) [4470-15G](#) [4470-15F](#) [4470-16J](#) [4470-16H](#) [4470-16G](#) [4470-16F](#) [4470-17J](#) [4470-17H](#) [4470-17G](#) [4470-17F](#) [4470-18J](#) [4470-18H](#) [4470-18G](#) [4470-18F](#) [4470-19J](#) [4470-19H](#) [4470-19G](#) [4470-19F](#) [4470-20J](#) [4470-20H](#) [4470-20G](#) [4470-20F](#) [4470-21J](#) [4470-21H](#) [4470-21G](#) [4470-21F](#) [4470-22J](#) [4470-22H](#)