



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	OWN
HM	00		AC	REV; ECO-14-004910	26FEB2014	GG
					JG	



1. DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
2. MATERIAL: HOUSING-POLYCARBONATE, CLEAR. TERMINAL - .36 [.014] THICK PHOSPHOR BRONZE PLATED WITH .178 μ m[.000007] THICK GOLD IN LOCALIZED PLATE AREA, OVER .762 μ m[.000030] THICK PALLADIUM NICKEL IN LOCALIZED PLATE AREA OVER 2.54 μ m[.000100] THICK NICKEL ON ENTIRE CONTACT.
3. PLUG WILL ACCEPT 26 OR 28 AWG STRANDED WIRE, 0.99[.039] MAX INSULATION DIAMETER, WITH A 2.29 X 4.83 [.090 X .190] OVAL JACKET.
4. TERMINATED DIMENSION 6.15[.242] MAXIMUM.
6. 10,000 ASSEMBLES PER PACKAGE.
7. 1000 ASSEMBLIES PER PACKAGE.
8. 100 ASSEMBLIES PER PACKAGE.

SUPERSEDED BY 5-641334-2

8	5-641334-3
7	5-641334-2
6	5-641334-1
REELED 10	641334-1
PACKAGED	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN YTP/UTA 8-31-93	 TE Connectivity			
		CHK C.WHITT 9-15-93				
DIMENSIONS: mm[INCHES]	TOLERANCES, UNLESS OTHERWISE SPECIFIED:	APVD —	NAME MODULAR PLUG ASSEMBLY, 4 POSITION, HANDSET			
	0 PLC ± —  1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	PRODUCT SPEC 108-1163 APPLICATION SPEC 114-6016				
MATERIAL — 	FINISH — 	WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C-641334	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 of 1	REV AC	