


Features

- ◆ Ultracompact DIL-16 Plastic Package
- ◆ Wide 2:1 Input Range
- ◆ Regulated Output
- ◆ I/O-Isolation 1500V
- ◆ Input Filter meets EN55022A without ext. Components
- ◆ Low Ripple and Noise
- ◆ Indefinite Shortcircuit Protection
- ◆ Operating Temperature Range -25°C to +75°C
- ◆ Lead free Design, RoHS compliant
- ◆ 3 Year Product Warranty



The TEL-2 series, comprising 28 models, is a range of isolated 2 Watt converters in a low profile DIL-16 package. Requiring only 3.25 cm² of space on the PCB they provide a complete DC/DC converter without need of any external components. Wide input range and tightly regulated output voltage qualifies these converters for many cost critical applications in industrial and consumer electronics.

Models

Ordercode	Input voltage range	Output voltage	Output current max.	Efficiency typ.
TEL 2-0510	4.5 – 9 VDC	3.3 VDC	500 mA	70 %
TEL 2-0511		5 VDC	400 mA	73 %
TEL 2-0512		12 VDC	165 mA	75 %
TEL 2-0513		15 VDC	135 mA	73 %
TEL 2-0521		± 5 VDC	± 200 mA	64 %
TEL 2-0522		± 12 VDC	± 85 mA	69 %
TEL 2-0523		± 15 VDC	± 65 mA	71 %
TEL 2-1210	9 – 18 VDC	3.3 VDC	500 mA	73 %
TEL 2-1211		5 VDC	400 mA	77 %
TEL 2-1212		12 VDC	165 mA	80 %
TEL 2-1213		15 VDC	135 mA	80 %
TEL 2-1221		± 5 VDC	± 200 mA	73 %
TEL 2-1222		± 12 VDC	± 85 mA	78 %
TEL 2-1223		± 15 VDC	± 65 mA	78 %
TEL 2-2410	18 – 36 VDC	3.3 VDC	500 mA	72 %
TEL 2-2411		5 VDC	400 mA	77 %
TEL 2-2412		12 VDC	165 mA	80 %
TEL 2-2413		15 VDC	135 mA	81 %
TEL 2-2421		± 5 VDC	± 200 mA	74 %
TEL 2-2422		± 12 VDC	± 85 mA	78 %
TEL 2-2423		± 15 VDC	± 65 mA	80 %
TEL 2-4810	36 – 75 VDC	3.3 VDC	500 mA	71 %
TEL 2-4811		5 VDC	400 mA	73 %
TEL 2-4812		12 VDC	165 mA	79 %
TEL 2-4813		15 VDC	135 mA	79 %
TEL 2-4821		± 5 VDC	± 200 mA	71 %
TEL 2-4822		± 12 VDC	± 85 mA	77 %
TEL 2-4823		± 15 VDC	± 65 mA	77 %

Input Specifications

Input current at full load / full load (nominal input)	5 Vin models: 600 mA/ 40 mA typ. 12 Vin models: 220 mA/ 20 mA typ. 24 Vin models: 110 mA/ 10 mA typ. 48 Vin models: 55 mA/ 8 mA typ.
Start-up voltage / under voltage shut down	5 Vin models: 4 VDC / 3.5 VDC typ. 12 Vin models: 7 VDC / 6.5 VDC typ. 24 Vin models: 12 VDC / 11 VDC typ. 48 Vin models: 24 VDC / 22 VDC typ.
under voltage shut down	
Surge voltage (100 msec. max.)	5 Vin models: 11 V max. 12 Vin models: 25 V max. 24 Vin models: 50 V max. 48 Vin models: 100 V max.
Reverse voltage protection	1.0 A max.
Conducted noise (input)	EN 55022 level A, FCC part 15, level A

Output Specifications

Voltage set accuracy		± 2 % max.
Regulation	– Input variation V_{in} min. to V_{in} max. – Load variation 25 – 100 % single output models: dual output models:	± 0.5 % max. ± 0.75 % max. ± 2.0% (balanced load)
Ripple and noise (20 MHz Bandwidth)		50 mVpk-pk max
Temperature coefficient		± 0.02 %/K
Short circuit protection		indefinite, automatic recovery
Minimum load		25% of rated max current (operation at lower load condition is safe but a higher output ripple will be experienced)
Capacitive load	3.3 VDC output models: 5 VDC output models: 12 VDC output models: 15 VDC output models: ± 5 VDC output models: ± 12 VDC output models: ± 15 VDC output models:	2'200 µF max. 1'000 µF max. 170 µF max. 110 µF max. 470 µF max. 100 µF max. 47 µF max.

General Specifications


Temperature ranges	– Operating – Storage	– 25 °C ... + 75 °C (no derating) – 55 °C ... + 125 °C
Humidity (non condensing)		95 % rel. H max.
Reliability, calculated MTBF (MIL-HDBK-217 F)		> 1.2 Mio h @ 25°C
Isolation voltage	Input/Output	1'500 VDC
Isolation capacity	Input/Output	250 pF max.
Isolation resistance	Input/Output (500 VDC)	> 1'000 M Ohm
Switching frequency		300 kHz (PFM)
Safety standards		UL/cUL 60950 , IEC 60950, EN 60950
Safety approval		CSA 60950-1-03 (File no. 226037)

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

Physical Specifications

Case material	non conductive FR4
Potting material	epoxy, UL94V-0 - rated
Weight	5.1 g (0.17oz)
Soldering temperature	max. 265°C / 10 sec.

Outline Dimensions mm (inches)



Pin-Out		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
7	No con.	No con.
8	No con.	Common
9	+Vout	+Vout
10	-Vout	-Vout
16	+Vin	+Vin

Pin diameter $\varnothing 0.5 \pm 0.05$ (0.02) ± 0.002
Tolerances ± 0.25 (0.01)

Specifications can be changed without notice