

Planar Power Transistors 2 AMP PNP

Device Type	V _{CEO} (V)	^h FE Min/Max	@ I _C (A)	V _{CE (sat)} Max (V)	@ I _C (A)	f _T MIN (MHz)		P _T MAX (W)	Case Type	Chip Type
2N3740	60	30/100	0.25	0.60	1.0	4.0		25.0	TO-66	269
2N3741	80	30/100	0.25	0.60	1.0	4.0		25.0	TO-66	269
2N4387	40	25/100	0.50	3.00	1.0	25.0		20.0	TO-66	269
2N4388	60	25/100	0.50	3.00	1.0	25.0		20.0	TO-66	269
2N4999	80	30/90	1.00	0.46	1.0	30.0	**	35.0	TO-59	271
2N5001	80	70/200	1.00	0.46	1.0	35.0	**	35.0	TO-59	271
2N5147	80	30/90	1.00	0.85	2.0	30.0	**	7.0	TO-39	271
2N5149	80	70/200	1.00	0.85	2.0	35.0	**	7.0	TO-39	271
2N5333	80	30/120	1.00	1.00	2.0	30.0		15.0	* TO-5	271
2N5597	60	70/200	1.00	0.85	2.0	35.0	**	20.0	TO-66	271
SDT3501	40	30	0.50	0.40	0.5	50.0		7.0	TO-5	269
SDT3502	60	30	0.50	0.40	0.5	50.0		7.0	TO-5	269
SDT3503	80	30	0.40	0.40	0.5	50.0		7.0	TO-5	269
SDT3504	100	30	0.50	0.40	0.5	50.0		7.0	TO-5	269
SDT3505	40	50/150	0.50	0.40	0.5	50.0		7.0	TO-5	269
SDT3506	60	50/150	0.50	0.40	0.5	50.0		7.0	TO-5	269
SDT3507	80	50/150	0.50	0.40	0.5	50.0		7.0	TO-5	269
SDT3508	100	50/150	0.50	0.40	0.5	50.0		7.0	TO-5	269
SDT3509	40	30	0.50	0.40	0.5	50.0		29.0	TO-66	269
SDT3510	60	30	0.50	0.40	0.5	50.0		29.0	TO-66	269
SDT3511	80	30	0.50	0.40	0.5	50.0		29.0	TO-66	269
SDT3512	100	30	0.50	0.40	0.5	50.0		29.0	TO-66	269
SDT3513	40	50/150	0.50	0.40	0.5	50.0		29.0	TO-66	269
SDT3514	60	50/150	0.50	0.40	0.5	50.0		29.0	TO-66	269
SDT3515	80	50/150	0.50	0.40	0.5	50.0		29.0	TO-66	269
SDT3516	100	50/150	0.50	0.40	0.5	50.0		29.0	TO-66	269
SDT3550	60	30/100	0.25	0.60	1.0	10.0		7.0	TO-5	269
SDT3551	80	30/100	0.25	0.60	1.0	10.0		7.0	TO-5	269
SDT3552	40	20/100	0.50	0.60	1.0	10.0		7.0	TO-5	269
SDT3553	60	20/100	0.50	0.60	1.0	10.0		7.0	TO-5	269
SDT3554	80	20/100	0.50	0.60	1.0	10.0		7.0	TO-5	269
SDF3575	40	30/150	0.25	0.60	1.0	10.0		17.0	TO-66	269
SDF3576	60	30/150	0.25	0.60	1.0	10.0		17.0	TO-66	269
SDT3577	80	30/150	0.25	0.60	1.0	10.0		17.0	TO-66	269
SDT3578	30	25/100	0.50	0.50	0.5	40.0		17.0	TO-66	269
SDT3579	50	25/100	0.50	0.50	0.5	40.0		17.0	TO-66	269
SDT69501	40	30	0.50	0.35	0.5	25.0		7.0	TO-39	269
SDT69502	60	30	0.50	0.35	0.5	25.0		7.0	TO-39	269
SDT69503	80	30	0.50	0.35	0.5	25.0		7.0	TO-39	269
SDT69504	100	30	0.50	0.35	0.5	25.0		7.0	TO-39	269
SDT69505	120	30	0.50	0.35	0.5	25.0		7.0	TO-39	269
SDT69509	40	50/150	0.50	0.35	0.5	25.0		7.0	TO-39	269
SDT69510	60	50/150	0.50	0.35	0.5	25.0		7.0	TO-39	269
SDT69511	80	50/150	0.50	0.35	0.5	25.0		7.0	TO-39	269
SDT69512	100	50/150	0.50	0.35	0.5	25.0		7.0	TO-39	269
SDT69513	120	50/150	0.50	0.35	0.5	25.0		7.0	TO-39	269
SDT69601	40	30	0.50	0.35	0.5	25.0		35.0	TO-66	269
SDT69602	60	30	0.50	0.35	0.5	25.0		35.0	TO-66	269
SDT69603	80	30	0.50	0.35	0.5	25.0		35.0	TO-66	269
SDT69604	100	30	0.50	0.35	0.5	25.0		35.0	TO-66	269
SDT69605	120	30	0.50	0.35	0.5	25.0		35.0	TO-66	269
SDT69609	40	50/150	0.50	0.35	0.5	25.0		35.0	TO-66	269
SDT69610	60	50/150	0.50	0.35	0.5	25.0		35.0	TO-66	269
SDT69611	80	50/150	0.50	0.35	0.5	25.0		35.0	TO-66	269
SDT69612	100	50/150	0.50	0.35	0.5	25.0		35.0	TO-66	269
SDT69613	120	50/150	0.50	0.35	0.5	25.0		35.0	TO-66	269

*TC = 100° C. **Exception to JEDEC