







LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
AD	39				H	REV PER 0010-1061-94	12-28-96	JH
					J	REV PER 0010-1175-95	12-28-96	JH



SECTION A-A

SECTION B-B

- 1 PHOSPHOR BRONZE $0.25 [.010]$ COMPL.
- 2 SHEAR LINES DEFINE LOOSE PIECE PART.
- 3 PRE-TINNED $0.00076 [.000030]$ MIN THICK.
- 4 GOLD FLASH OVER $0.00127 [.000050]$ NICKEL ENTIRE CONTACT, $0.00076 [.000030]$ GOLD ON CONTACT AREA.
- 5 $0.00038 [.000015]$ GOLD ON CONTACT AREA, $0.00254-0.00508 [.000100-.000200]$ BRIGHT TIN-LEAD ON TERMINATION AREA, ALL OVER $0.00127 [.000050]$ NICKEL.
- 6 $0.00076 [.000030]$ GOLD ON CONTACT AREA, $0.00254-0.00508 [.000100-.000200]$ BRIGHT TIN-LEAD ON TERMINATION AREA, ALL OVER $0.00127 [.000050]$ NICKEL.
- 7 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 8 "H" RECEPTACLE CENTERS MAY VARY DEPENDING ON REQUIREMENTS. MINIMUM NOMINAL CENTERLINE SPACING BETWEEN ADJACENT RECEPTACLES IS $3.18 [.125]$.



TYPICAL APPLICATION

RECOMMENDED P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

OBSOLETE	86443-6	6	1	86442-6
OBSOLETE	86443-3	5	1	86442-4
OBSOLETE	86443-2	4	1	86442-2
	86443-1	3	1	86442-1
LOOSE PIECE PART NO.		FINISH	MATERIAL	PART NUMBER

PART NO		
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC $\pm$ - 3 PLC DEC $\pm 0.13 [.005]$ ANGLES $\pm$ -		
MATERIAL		
SEE TABLE		
FINISH		
SEE TABLE		
DR 28-DEC-96 E. BRANDBERG CHK 28-DEC-96 J. HERRINGTON APPD 28-DEC-96 J. HERRINGTON APPD 28-DEC-96 D. TROUT PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		
AMP AMP Incorporated Harrisburg, PA 17105-3608		
NAME		
FEMALE CONTACT - VERTICAL TYPE "A", MOD 1, HIGH PRESSURE		
SIZE	CAGE CODE	DRAWING NO
C	00779	C=86442
SCALE	10:1	SHEET
		1 OF 1