




REV.	DATE	DESCRIPTION
A	01/30/04	UPDATE DRAWING FORMAT
B	05/12/07	ADD CABLE DESCRIPTION



RECOMMENDED CABLE
STRIPPING DIM'S



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex				
7						DRAWN	G.R.S.					05/12/07
6						CHECKED						
5						ISSUED			PART DESCRIPTION UHF CRIMP PLUG (FOR RG-8/U, 213/U CABLE)			
4	FERRULE	COPPER	NICKEL	1		SHEET	1 OF 1					
3	CONTACT PIN	BRASS	GOLD	1		PART NO. 182102						
2	INSULATOR	PHENOLIC	YELLOW	1								
1	BODY	BRASS	SILVER	1		DWG. NO. 182102.DWG						
	DESCRIPTION	MATERIAL	FINISH	QTY								
						REV. B				SIZE A	SCALE NA	