










- 1 HOUSING MATERIAL: LIQUID CRYSTAL POLYMER. COLOR: NATURAL
- 2 CONTACT MATERIAL: PHOSPHOR-BRONZE
- 3 CONTACT FINISH:(A)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT.
ON LEADS:
0.00381 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.
- 4 PART MARKING, LOCATED APPROXIMATELY AS SHOWN.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



Ø0.725±0.075
PLATED THROUGH HOLE
⊕ Ø0.15 (M)



RECOMMENDED CIRCUIT PATTERN
(COMPONENT SIDE)



VIEW W-W
SCALE 20:1

OBSOLETE	94.00	47	95.88	192	5223655-8
	82.00	41	83.88	168	5223655-7
	70.00	35	71.88	144	5223655-6
	58.00	29	59.88	120	5223655-5
	46.00	23	47.88	96	5223655-4
OBSOLETE	34.00	17	35.88	72	5223655-3
	22.00	11	23.88	48	5223655-2
	10.00	5	11.88	24	5223655-1
DIM C		B	DIM A	NUMBER OF SIGNAL POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.13

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

MATERIAL

1

2

3

DWN

B.MCMMASTER

15DEC04

CHK

R.WERTZ

15DEC04

APP'D

R.WERTZ

15DEC04

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

—

CUSTOMER DRAWING

Tyco Electronics

Tyco Electronics Corporation

Harrisburg, Pa 17105-3608

NAME

ASSEMBLY, RECEPTACLE, SIGNAL, VERTICAL, 4 ROW, Z-PACK 2mm FB, WITH SOLDER LEADS

SIZE

A1

CAGE CODE

00779

DRAWING NO

5223655

RESTRICTED TO

—

SCALE

4:1

SHEET

1

OF

1

REV

Q1