


(0,635 mm) .025"



QFS-PC, QFS-RF SERIES

HIGH SPEED COMBO RF & POWER

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?QFS

Insulator Material:

Liquid Crystal Polymer

Contact & Ground Plane Material:

Phosphor Bronze

Plating:

Au over 50µ" (1,27 µm) Ni

(Tin on Ground Plane Tail)

Current Rating:

Signal Contact:

2.6 A per pin

(1 pin powered per row)

Power Contact:

4.0 A per pin

(4 pins powered per end)

Ground Plane:

15.7 A per ground plane

(1 ground plane powered)

Voltage Rating:

300 VAC mated with QMS

Operating Temp:

-55°C to +125°C

RHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,10 mm) .004" max (026-078)

Board Stacking:

For applications requiring more than two connectors per board, contact ipg@samtec.com

Board Mates:

QMS-PC, QMS-RA-PC,


QMS-RF

QMS-PC/QFS-PC 10 mm Stack Height	Type	Rated @ 3dB Insertion Loss	
		with PCB effects*	w/o PCB effects**
Single-Ended Signaling	-D	9 GHz / 18 Gbps	8.5 GHz / 17 Gbps
Differential Pair Signaling	-D	8 GHz / 16 Gbps	8.5 GHz / 17 Gbps

*Performance data includes effects of a non-optimized PCB.

**Test board losses de-embedded from performance data.

Performance data for other stack heights and complete test data available at www.samtec.com?QFS or contact sig@samtec.com




FinalInch
CERTIFIED



- Increased insertion depth
- Integral guide post

APPLICATION



QMS LEAD STYLE	MATED HEIGHT*
-05.75	10 mm
-06.75	11 mm

*Processing conditions will affect mated height.

QFS

NO. OF PINS
PER ROWLEAD
STYLEPLATING
OPTION

D

END
OPTION

-026, -052, -078
(52 total pins per bank)

-04.25
=04.25 mm

-L
= 10µ" (0,25 µm) Gold on Signal Pins
and Ground Plane
(Tin on Signal Pin tails,
and Ground Plane tails)

-PC4
= 4 Power
Pins per End for
(1,60 mm) .062"
thick Board
(N/A with -RF1)

-RF1
= One RF
Jack per End
(N/A with -PC4)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality




FILE NO. E111594

ALSO AVAILABLE (MOQ Required)

- Other platings
- Differential Pairs
- Retention Pins
- 8 Power Pins/End for (1,60 mm) .062" thick Board
- 4 or 8 Power Pins/End for (2,36 mm) .093" thick Board
- 2 RF Connectors/End
- Hot Pluggable Contact Samtec.

Note: Some lengths, styles and options are non-standard, non-returnable.



OTHER SOLUTIONS



See SO Series for precision machined standoffs.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685