


BAV70

Description

The BAV70 consists of two diodes in a plastic surface mount package. The diodes are connected in series and the unit is designed for high-speed switching application in hybrid thick and thin-film circuits.

Package Dimensions




Absolute Maximum Ratings at Ta = 25°C

Parameter	Symbol	Ratings	Unit
Junction Temperature	Tj	+150	°C
Storage Temperature	Tstg	-65~+150	°C
Reverse Voltage		80	V
Forward Current		200	mA
Repetitive Forward Current		500	mA
Total Power Dissipation	PD	225	mW

Characteristics at Ta = 25°C

Characteristic	Symbol	Min.	Max.	Unit	Test Conditions
Reverse Breakdown Voltage	V(BR)	80	-	V	IR=100uA
Forward Voltage	VF(1)	-	715	mV	IF=1mA
	VF(2)	-	855	mV	IF=10mA
	VF(3)	-	1100	mV	IF=50mA
	VF(4)	-	1300	mV	IF=100mA
Reverse Current	IR	-	5	uA	VR=80V
Total Capacitance	CT		1.5	pF	VR=0, f=1MHz
Reverse Recovery Time	Trr	-	15	nS	IF=IR=10mA, RL=100Ω measured at IR=1Ma, VR=5V

Characteristics Curve



Important Notice:

- All rights are reserved. Reproduction in whole or in part is prohibited without the prior written approval of FMS.
- FMS reserves the right to make changes to its products without notice.
- FMS semiconductor products are not warranted to be suitable for use in life-support Applications, or systems.
- FMS assumes no liability for any consequence of customer product design, infringement of patents, or application assistance.

Head Office And Factory:

- **Taiwan:** 5F, No. 208, Sec 3, Chung Yang Rd. TuCheng, Taipei Hsien, Taiwan, R. O. C.
TEL : 886-2-2269-6661 FAX : 886-2-2269-6141
- **China:** No. Y Bldg, Zhijiang Hi-tech Park Binjiang Zone, Hangzhou, China
TEL : 86-571-8669-8326 FAX : 86-571-8669-6991