

## Ultra Low Power 3 Ld Voltage Supervisors in SC-70 and SOT-23 Packages


The ISL88001, ISL88002, ISL88003 supervisors are extremely low power 160nA voltage supervisors that help to monitor the power supply voltages in a wide variety of applications. By providing Power-On Reset and supply voltage supervision in small 3 Ld SC-70 and SOT-23 packages, the ISL88001, ISL88002, ISL88003 devices can help to lower system cost, reduce board space requirements and increase the reliability of systems.

The most popular voltage trip points are available for standard power supplies from 1.8V to 5.0V (see "Ordering Information" on page 3). These reset threshold voltages are accurate to within  $\pm 1.2\%$  and the reset signal is valid down to 1V. Active high and active low reset outputs are available in push-pull and open drain configurations (see "Functional Block Diagrams" on page 2).

The ISL88001, ISL88002, ISL88003 devices are specifically designed for low power consumption and high threshold accuracy, making them especially suitable for electronic devices and portable equipment.


## Pinouts

**ISL88001, ISL88002**  
(3 LD SC-70, 3 LD SOT-23)  
TOP VIEW



ISL88001 has a push-pull RST output  
ISL88002 has an open-drain RST output

**ISL88003**  
(3 LD SC-70, 3 LD SOT-23)  
TOP VIEW



ISL88003 has a push-pull RST output

## Features

- Single Voltage Monitoring Supervisors
- Fixed-Voltage Options Allow Precise Monitoring of +1.8V, +2.5V, +3.0V, +3.3V and +5.0V Power Supplies
- Ultra Low 160nA Supply Current
- $\pm 1.2\%$  Voltage Threshold Accuracy
- 190ms Power-On Reset Timeout
- Reset Signal Valid Down to  $V_{DD} = 1V$
- No External Components Necessary
- Immune to Power-Supply Transients
- Available in Small 3 Ld SC-70 and 3 Ld SOT-23 Pb-free Packages
- Pin Compatible with MAX803, MAX809, MAX810
- Pb-Free (RoHS Compliant)


## Applications

- Microprocessor/Microcontroller Systems
- Intelligent Instruments
- Controllers
- Computer Systems
- Portable/Battery-Powered Equipment
- PDA and Hand-Held PC Devices


## Pin Descriptions

| PIN                  |          | PIN NAME                | PIN FUNCTION                                                                                                                                                                  |
|----------------------|----------|-------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| ISL88001<br>ISL88002 | ISL88003 |                         |                                                                                                                                                                               |
| 1                    | 1        | GND                     | Ground IC reference.                                                                                                                                                          |
| 2                    |          | $\overline{\text{RST}}$ | The $\overline{\text{RST}}$ pin is an active-low reset output that is pulled to GND (LOW) when reset is asserted. The ISL88001 is push-pull while the ISL88002 is open drain. |
|                      | 2        | RST                     | The RST pin is a push-pull active-high reset output that is pulled to $V_{\text{DD}}$ (HIGH) when reset is asserted.                                                          |
| 3                    | 3        | $V_{\text{DD}}$         | Supply Voltage and Monitored Input. The $V_{\text{DD}}$ pin is the IC power supply terminal and also the monitored input.                                                     |


## Functional Block Diagrams



ISL88001



ISL88002



ISL88003

## Ordering Information

| PART NUMBER<br>(Notes 1, 2, 3, 4) | PART<br>MARKING<br>(Bottom Brand) | RESET                              | NOMINAL<br>V <sub>THVDD</sub> (V) | TEMPERATURE<br>RANGE (°C) | PACKAGE<br>Tape and Reel<br>(Pb-free) | PKG.<br>DWG. # |
|-----------------------------------|-----------------------------------|------------------------------------|-----------------------------------|---------------------------|---------------------------------------|----------------|
| ISL88001IE46Z-T                   | 146                               | Push-Pull $\overline{\text{RST}}$  | 4.62                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88001IE44Z-T                   | 144                               | Push-Pull $\overline{\text{RST}}$  | 4.38                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88001IE31Z-T                   | 131                               | Push-Pull $\overline{\text{RST}}$  | 3.07                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88001IE29Z-T                   | 129                               | Push-Pull $\overline{\text{RST}}$  | 2.92                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88001IE26Z-T                   | 126                               | Push-Pull $\overline{\text{RST}}$  | 2.63                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88001IE23Z-T                   | 123                               | Push-Pull $\overline{\text{RST}}$  | 2.32                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88001IE22Z-T                   | 122                               | Push-Pull $\overline{\text{RST}}$  | 2.19                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88001IE17Z-T                   | 117                               | Push-Pull $\overline{\text{RST}}$  | 1.67                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88001IE16Z-T                   | 116                               | Push-Pull $\overline{\text{RST}}$  | 1.58                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88001IH46Z-T                   | 1H46                              | Push-Pull $\overline{\text{RST}}$  | 4.62                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88001IH44Z-T                   | 1H44                              | Push-Pull $\overline{\text{RST}}$  | 4.38                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88001IH31Z-T                   | 1H31                              | Push-Pull $\overline{\text{RST}}$  | 3.07                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88001IH29Z-T                   | 1H29                              | Push-Pull $\overline{\text{RST}}$  | 2.92                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88001IH26Z-T                   | 1H26                              | Push-Pull $\overline{\text{RST}}$  | 2.63                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88001IH23Z-T                   | 1H23                              | Push-Pull $\overline{\text{RST}}$  | 2.32                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88001IH22Z-T                   | 1H22                              | Push-Pull $\overline{\text{RST}}$  | 2.19                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88001IH17Z-T                   | 1H17                              | Push-Pull $\overline{\text{RST}}$  | 1.67                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88001IH16Z-T                   | 1H16                              | Push-Pull $\overline{\text{RST}}$  | 1.58                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88002IE46Z-T                   | 246                               | Open Drain $\overline{\text{RST}}$ | 4.62                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88002IE44Z-T                   | 244                               | Open Drain $\overline{\text{RST}}$ | 4.38                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88002IE31Z-T                   | 231                               | Open Drain $\overline{\text{RST}}$ | 3.07                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88002IE29Z-T                   | 229                               | Open Drain $\overline{\text{RST}}$ | 2.92                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88002IE26Z-T                   | 226                               | Open Drain $\overline{\text{RST}}$ | 2.63                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88002IE23Z-T                   | 223                               | Open Drain $\overline{\text{RST}}$ | 2.32                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88002IE22Z-T                   | 222                               | Open Drain $\overline{\text{RST}}$ | 2.19                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88002IE17Z-T                   | 217                               | Open Drain $\overline{\text{RST}}$ | 1.67                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88002IE16Z-T                   | 216                               | Open Drain $\overline{\text{RST}}$ | 1.58                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88002IH46Z-T                   | 2H46                              | Open Drain $\overline{\text{RST}}$ | 4.62                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88002IH44Z-T                   | 2H44                              | Open Drain $\overline{\text{RST}}$ | 4.38                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88002IH31Z-T                   | 2H31                              | Open Drain $\overline{\text{RST}}$ | 3.07                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88002IH29Z-T                   | 2H29                              | Open Drain $\overline{\text{RST}}$ | 2.92                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88002IH26Z-T                   | 2H26                              | Open Drain $\overline{\text{RST}}$ | 2.63                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88002IH23Z-T                   | 2H23                              | Open Drain $\overline{\text{RST}}$ | 2.32                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88002IH22Z-T                   | 2H22                              | Open Drain $\overline{\text{RST}}$ | 2.19                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88002IH17Z-T                   | 2H17                              | Open Drain $\overline{\text{RST}}$ | 1.67                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88002IH16Z-T                   | 2H16                              | Open Drain $\overline{\text{RST}}$ | 1.58                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88003IE46Z-T                   | 346                               | Push-Pull RST                      | 4.62                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88003IE44Z-T                   | 344                               | Push-Pull RST                      | 4.38                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |

**Ordering Information** (Continued)

| PART NUMBER<br>(Notes 1, 2, 3, 4) | PART<br>MARKING<br>(Bottom Brand)                       | RESET         | NOMINAL<br>V <sub>THVDD</sub> (V) | TEMPERATURE<br>RANGE (°C) | PACKAGE<br>Tape and Reel<br>(Pb-free) | PKG.<br>DWG. # |
|-----------------------------------|---------------------------------------------------------|---------------|-----------------------------------|---------------------------|---------------------------------------|----------------|
| ISL88003IE31Z-T                   | 331                                                     | Push-Pull RST | 3.07                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88003IE29Z-T                   | 329                                                     | Push-Pull RST | 2.92                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88003IE26Z-T                   | 326                                                     | Push-Pull RST | 2.63                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88003IE23Z-T                   | 323                                                     | Push-Pull RST | 2.32                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88003IE22Z-T                   | 322                                                     | Push-Pull RST | 2.19                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88003IE17Z-T                   | 317                                                     | Push-Pull RST | 1.67                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88003IE16Z-T                   | 316                                                     | Push-Pull RST | 1.58                              | -40 to +85                | 3 Ld SC-70                            | P3.049         |
| ISL88003IH46Z-T                   | 3H46                                                    | Push-Pull RST | 4.62                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88003IH44Z-T                   | 3H44                                                    | Push-Pull RST | 4.38                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88003IH31Z-T                   | 3H31                                                    | Push-Pull RST | 3.07                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88003IH29Z-T                   | 3H29                                                    | Push-Pull RST | 2.92                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88003IH26Z-T                   | 3H26                                                    | Push-Pull RST | 2.63                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88003IH23Z-T                   | 3H23                                                    | Push-Pull RST | 2.32                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88003IH22Z-T                   | 3H22                                                    | Push-Pull RST | 2.19                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88003IH17Z-T                   | 3H17                                                    | Push-Pull RST | 1.67                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88003IH16Z-T                   | 3H16                                                    | Push-Pull RST | 1.58                              | -40 to +85                | 3 Ld SOT-23                           | P3.064         |
| ISL88001/2/3EVAL1Z                | Evaluation Platform for ISL88001, ISL88002 and ISL88003 |               |                                   |                           |                                       |                |

NOTES:

1. For non-standard voltage trip point versions between 1.5V and 5V in 100mV increments, please contact factory for availability.
2. Add "-TK" suffix for 1000 piece Tape and Reel. Please refer to [TB347](#) for details on reel specifications.
3. These Intersil Pb-free plastic packaged products employ special Pb-free material sets, molding compounds/die attach materials, and 100% matte tin plate plus anneal (e3 termination finish, which is RoHS compliant and compatible with both SnPb and Pb-free soldering operations). Intersil Pb-free products are MSL classified at Pb-free peak reflow temperatures that meet or exceed the Pb-free requirements of IPC/JEDEC J STD-020.
4. For Moisture Sensitivity Level (MSL), please see device information page for [ISL88001](#), [ISL88002](#), [ISL88003](#). For more information on MSL please see techbrief [TB363](#).

### Absolute Maximum Ratings

Voltage on Any Pin with respect to GND . . . . . -0.3V to +6.5V  
 DC Output Current . . . . . 10mA

### Recommended Operating Conditions

Temperature Range (Industrial) . . . . . -40°C to +85°C

### Thermal Information

Thermal Resistance (Typical, Note 5)  $\theta_{JA}$  (°C/W)  
 3 Lead SC-70 . . . . . 640  
 3 Lead SOT-23 . . . . . 590  
 Temperature Under Bias . . . . . -40°C to +125°C  
 Storage Temperature . . . . . -65°C to +150°C  
 Pb-Free Reflow Profile . . . . . see link below  
<http://www.intersil.com/pbfree/Pb-FreeReflow.asp>

**CAUTION:** Do not operate at or near the maximum ratings listed for extended periods of time. Exposure to such conditions may adversely impact product reliability and result in failures not covered by warranty.

NOTE:

5.  $\theta_{JA}$  is measured with the component mounted on a high effective thermal conductivity test board in free air. See Tech Brief [TB379](#) for details.

**Electrical Specifications** Over the recommended operating conditions unless otherwise specified. **Boldface limits apply over the operating temperature range, -40°C to +85°C.**

| SYMBOL                 | PARAMETER                                              | TEST CONDITIONS                                                  | MIN<br>(Note 6) | TYP   | MAX<br>(Note 6) | UNITS |
|------------------------|--------------------------------------------------------|------------------------------------------------------------------|-----------------|-------|-----------------|-------|
| BIAS                   |                                                        |                                                                  |                 |       |                 |       |
| V <sub>DD</sub>        | Supply Voltage Range                                   | V <sub>THVDD</sub> = 4.64V, 4.38V, 3.09V, 2.92V, 2.63V           | 1.8             |       | 5.5             | V     |
|                        |                                                        | V <sub>THVDD</sub> = 2.32V, 2.19V, 1.67V, 1.58V                  | 1.8             |       | 2.75            | V     |
| I <sub>DD</sub>        | Supply Current (RESET, $\overline{\text{RESET}}$ open) | V <sub>DD</sub> = 5.0V, V <sub>THVDD</sub> = 4.64V, 4.38V        |                 | 215   | 400             | nA    |
|                        |                                                        | V <sub>DD</sub> = 3.3V, V <sub>THVDD</sub> = 3.09V, 2.92V, 2.63V |                 | 200   | 350             | nA    |
|                        |                                                        | V <sub>DD</sub> = 2.5V, V <sub>THVDD</sub> = 2.32V, 2.19V        |                 | 175   | 325             | nA    |
|                        |                                                        | V <sub>DD</sub> = 1.8V, V <sub>THVDD</sub> = 1.67V, 1.58V        |                 | 160   | 300             | nA    |
| VOLTAGE THRESHOLD      |                                                        |                                                                  |                 |       |                 |       |
| V <sub>THVDD</sub>     | Falling Fixed V <sub>DD</sub> Voltage Trip Point       | ISL88001, 88002, 88003I <b>x46</b> , T <sub>A</sub> = +25°C      | 4.570           | 4.625 | 4.681           | V     |
|                        |                                                        | ISL88001, 88002, 88003I <b>x46</b>                               | 4.500           |       | 4.750           | V     |
|                        |                                                        | ISL88001, 88002, 88003I <b>x44</b> , T <sub>A</sub> = +25°C      | 4.327           | 4.380 | 4.433           | V     |
|                        |                                                        | ISL88001, 88002, 88003I <b>x44</b>                               | 4.262           |       | 4.498           | V     |
|                        |                                                        | ISL88001, 88002, 88003I <b>x31</b> , T <sub>A</sub> = +25°C      | 3.038           | 3.075 | 3.112           | V     |
|                        |                                                        | ISL88001, 88002, 88003I <b>x31</b>                               | 3.000           |       | 3.150           | V     |
|                        |                                                        | ISL88001, 88002, 88003I <b>x29</b> , T <sub>A</sub> = +25°C      | 2.890           | 2.925 | 2.960           | V     |
|                        |                                                        | ISL88001, 88002, 88003I <b>x29</b>                               | 2.850           |       | 3.000           | V     |
|                        |                                                        | ISL88001, 88002, 88003I <b>x26</b> , T <sub>A</sub> = +25°C      | 2.598           | 2.630 | 2.662           | V     |
|                        |                                                        | ISL88001, 88002, 88003I <b>x26</b>                               | 2.559           |       | 2.701           | V     |
|                        |                                                        | ISL88001, 88002, 88003I <b>x23</b> , T <sub>A</sub> = +25°C      | 2.292           | 2.320 | 2.348           | V     |
|                        |                                                        | ISL88001, 88002, 88003I <b>x23</b>                               | 2.257           |       | 2.383           | V     |
|                        |                                                        | ISL88001, 88002, 88003I <b>x22</b> , T <sub>A</sub> = +25°C      | 2.164           | 2.190 | 2.216           | V     |
|                        |                                                        | ISL88001, 88002, 88003I <b>x22</b>                               | 2.131           |       | 2.249           | V     |
|                        |                                                        | ISL88001, 88002, 88003I <b>x17</b> , T <sub>A</sub> = +25°C      | 1.650           | 1.670 | 1.690           | V     |
|                        |                                                        | ISL88001, 88002, 88003I <b>x17</b>                               | 1.625           |       | 1.715           | V     |
|                        |                                                        | ISL88001, 88002, 88003I <b>x16</b> , T <sub>A</sub> = +25°C      | 1.561           | 1.580 | 1.599           | V     |
|                        |                                                        | ISL88001, 88002, 88003I <b>x16</b>                               | 1.537           |       | 1.623           | V     |
| V <sub>THVDDHYST</sub> | Hysteresis at V <sub>DD</sub> Input                    |                                                                  |                 | 1     |                 | %     |
| T <sub>VTHVDD</sub>    | V <sub>THVDD</sub> Temperature Coefficient             |                                                                  |                 | 0.48  |                 | mV/°C |

**Electrical Specifications** Over the recommended operating conditions unless otherwise specified. (Continued) **Boldface limits apply over the operating temperature range, -40°C to +85°C.**

| SYMBOL               | PARAMETER                               | TEST CONDITIONS                                                   | MIN<br>(Note 6)             | TYP                   | MAX<br>(Note 6) | UNITS |
|----------------------|-----------------------------------------|-------------------------------------------------------------------|-----------------------------|-----------------------|-----------------|-------|
| <b>RESET / RESET</b> |                                         |                                                                   |                             |                       |                 |       |
| V <sub>OL</sub>      | Reset Output Voltage Low                | V <sub>DD</sub> < V <sub>THVDD</sub> , for ISL88001               |                             | 0.2                   | <b>0.40</b>     | V     |
|                      |                                         | V <sub>DD</sub> < V <sub>THVDD</sub> , Sinking 0.5mA for ISL88002 |                             | 0.2                   | <b>0.40</b>     | V     |
|                      |                                         | V <sub>DD</sub> > V <sub>THVDD</sub> , for ISL88003               |                             | 0.2                   | <b>0.40</b>     | V     |
| V <sub>OH</sub>      | Reset Output Voltage High               | V <sub>DD</sub> > V <sub>THVDD</sub> , for ISL88001               | <b>V<sub>DD</sub> - 0.4</b> | V <sub>DD</sub> - 0.2 |                 | V     |
|                      |                                         | V <sub>DD</sub> > V <sub>THVDD</sub> , Sourcing 0.5mA, ISL88002   |                             | V <sub>DD</sub> - 0.2 |                 | V     |
|                      |                                         | V <sub>DD</sub> < V <sub>THVDD</sub> , for ISL88003               | <b>V<sub>DD</sub> - 0.4</b> | V <sub>DD</sub> - 0.2 |                 | V     |
| t <sub>RPD</sub>     | V <sub>TH</sub> to Reset Asserted Delay |                                                                   |                             | 15                    |                 | μs    |
| t <sub>POR</sub>     | POR Timeout Delay                       |                                                                   | <b>140</b>                  | 200                   | <b>260</b>      | ms    |
| C <sub>LOAD</sub>    | Load Capacitance on Reset Pin           |                                                                   |                             | 5                     |                 | pF    |

NOTE:

6. Parameters with MIN and/or MAX limits are 100% tested at +25°C, unless otherwise specified. Temperature limits established by characterization and are not production tested.

## Pin Descriptions

### RST

The ISL88003 push-pull RST output is set to V<sub>DD</sub> (HIGH) whenever the device is first powered up or V<sub>DD</sub> falls below its respective minimum voltage sense level.

### $\overline{\text{RST}}$

The  $\overline{\text{RST}}$  output functions identically to the complementary RST output. On the ISL88001, this is a push-pull output. On the ISL88002, it is an open drain output that is pulled to GND (LOW) when reset is asserted. Suggested pull-up  $\overline{\text{RST}}$  resistor values are in the range of 5kΩ to 100kΩ.

### VDD

The V<sub>DD</sub> pin is the power supply terminal. The voltage at this pin is compared against an internal factory-programmed voltage trip point, V<sub>THVDD</sub>. A reset is first asserted when the device is initially powered up to ensure that the power supply has stabilized. Thereafter, reset is again asserted whenever V<sub>DD</sub> falls below V<sub>THVDD</sub>. The device is designed with hysteresis to help prevent chattering due to noise.


## Principles of Operation

The ISL88001, ISL88002, ISL88003 devices provide a low power, high accuracy solution for those voltage monitoring applications needing supply voltage supervision with power reset control. By integrating these features into small 3 Ld SC-70 and 3 Ld SOT-23 packages and consuming as little as 160nA of supply current, these devices can lower system cost and reduce board space requirements.

### Low Voltage Monitoring

During normal operation, the ISL88001, ISL88002, ISL88003 devices monitor the voltage level of V<sub>DD</sub>. The

device asserts a reset signal ( $\overline{\text{RST}}$  = LOW or RST = HIGH) to a μP/μC if this voltage is less than the preset voltage trip point. The reset signal prevents system operation during a power failure or brownout condition. This reset signal remains asserted until V<sub>DD</sub> exceeds the voltage threshold setting for the reset time delay period t<sub>POR</sub>. See Figure 2.



\*Necessary for ISL88002

FIGURE 1. TYPICAL APPLICATION DIAGRAM




FIGURE 2. VOLTAGE MONITORING TIMING DIAGRAM

### Power-On Reset (POR)

Applying power to the ISL88001, ISL88002, ISL88003 activates a POR circuit, which asserts reset once  $V_{DD} = 1\text{ V}$ . (i.e.  $\overline{\text{RST}}$  goes LOW). This provides several benefits:

- It prevents the system microprocessor from starting to operate with insufficient voltage.
- It prevents the processor from operating prior to stabilization of the oscillator.
- It ensures that the monitored device is held out of operation until internal registers are properly loaded.
- It allows time for an FPGA to download its configuration prior to initialization of the circuit.

The reset signal remains asserted until  $V_{DD}$  rises above the minimum voltage sense level for time period  $t_{POR}$ . This ensures that the  $V_{DD}$  voltage has stabilized.

Optional  $V_{DD}$  de-coupling capacitance can be added to filter transients if needed.

See Figures 13 and 14 illustrating the available evaluation platform, ISL88001/2/3EVAL1Z. This evaluation board is shipped with the many released variants loosely packed and the 4.6V threshold variants mounted for immediate evaluation.

### Parametric Performance




FIGURE 3. ISL88001  $\overline{\text{RST}}$   $t_{POR}$  ~144ms




FIGURE 4. ISL88002  $\overline{\text{RST}}$   $t_{POR}$  ~155ms,  $R_{PU} = 5\text{ k}\Omega$

## Parametric Performance (Continued)




FIGURE 5. ISL88003 RST  $t_{POR}$  ~145ms




FIGURE 6. ISL88003  $t_{PRD}$  ~26μs




FIGURE 7. ISL8800x 4.6V  $V_{THVDD}$  vs TEMPERATURE




FIGURE 8. ISL8800x 2.9V  $V_{THVDD}$  vs TEMPERATURE




FIGURE 9. ISL8800x 2.2V  $V_{THVDD}$  vs TEMPERATURE




FIGURE 10. ISL8800x 1.58V  $V_{THVDD}$  vs TEMPERATURE

## Parametric Performance (Continued)




FIGURE 11. ISL8800x NORMALIZED +25°C  $t_{POR}$  vs TEMPERATURE




FIGURE 12. ISL8800x NORMALIZED +25°C  $I_D$  vs TEMPERATURE

## ISL88001/2/3EVAL1Z Evaluation Platform




FIGURE 13. ISL88001/2/3EVAL1Z SCHEMATIC





FIGURE 14. ISL88001/2/3EVAL1Z PHOTOGRAPH

## Small Outline Transistor Plastic Packages (SC70-3)



## P3.049

## 3 LEAD SMALL OUTLINE TRANSISTOR PLASTIC PACKAGE

| SYMBOL   | INCHES     |       | MILLIMETERS |      | NOTES |
|----------|------------|-------|-------------|------|-------|
|          | MIN        | MAX   | MIN         | MAX  |       |
| A        | 0.031      | 0.043 | 0.80        | 1.10 | -     |
| A1       | 0.000      | 0.004 | 0.00        | 0.10 | -     |
| A2       | 0.031      | 0.039 | 0.80        | 1.00 | -     |
| b        | 0.009      | 0.016 | 0.25        | 0.40 | -     |
| b1       | 0.009      | 0.014 | 0.25        | 0.35 | -     |
| c        | 0.004      | 0.007 | 0.10        | 0.18 | 6     |
| c1       | 0.004      | 0.007 | 0.10        | 0.16 | 6     |
| D        | 0.071      | 0.087 | 1.80        | 2.20 | 3     |
| E        | 0.071      | 0.094 | 1.80        | 2.40 | -     |
| E1       | 0.045      | 0.053 | 1.15        | 1.35 | 3     |
| e        | 0.0256 Ref |       | 0.65 Ref    |      | -     |
| e1       | 0.0512 Ref |       | 1.30 Ref    |      | -     |
| L        | 0.010      | 0.018 | 0.26        | 0.46 | 4     |
| L1       | 0.017 Ref. |       | 0.420 Ref.  |      | -     |
| L2       | 0.006 BSC  |       | 0.15 BSC    |      | -     |
| $\alpha$ | 0°         | 8°    | 0°          | 8°   | -     |
| N        | 3          |       | 3           |      | 5     |
| R        | 0.004      | -     | 0.10        | -    | -     |
| R1       | 0.004      | 0.010 | 0.15        | 0.25 | -     |

Rev. 0 11/06

## NOTES:

1. Dimensioning and tolerances per ASME Y14.5M-1994.
2. Package conforms to EIAJ SC70 and JEDEC MO-203AA.
3. Dimensions D and E1 are exclusive of mold flash, protrusions, or gate burrs.
4. Footlength L measured at reference to gauge plane.
5. "N" is the number of terminal positions.
6. These Dimensions apply to the flat section of the lead between 0.08mm and 0.15mm from the lead tip.
7. Controlling dimension: MILLIMETER. Converted inch dimensions are for reference only.

All Intersil U.S. products are manufactured, assembled and tested utilizing ISO9000 quality systems.  
Intersil Corporation's quality certifications can be viewed at [www.intersil.com/design/quality](http://www.intersil.com/design/quality)

Intersil products are sold by description only. Intersil Corporation reserves the right to make changes in circuit design, software and/or specifications at any time without notice. Accordingly, the reader is cautioned to verify that data sheets are current before placing orders. Information furnished by Intersil is believed to be accurate and reliable. However, no responsibility is assumed by Intersil or its subsidiaries for its use; nor for any infringements of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Intersil or its subsidiaries.






For information regarding Intersil Corporation and its products, see [www.intersil.com](http://www.intersil.com)

# Package Outline Drawing

## P3.064

3 LEAD SMALL OUTLINE TRANSISTOR PLASTIC PACKAGE (SOT23-3)

Rev 3, 3/12



### NOTES:

1. Dimensions are in millimeters.  
Dimensions in ( ) for Reference Only.
2. Dimensioning and tolerancing conform to AMSEY14.5m-1994.
3. Reference JEDEC TO-236.
4. Dimension does not include interlead flash or protrusions.  
Interlead flash or protrusions shall not exceed 0.25mm per side.
5. Footlength is measured at reference to gauge plane.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Intersil:

[ISL88001/2/3EVAL1Z](#) [ISL88001IE16Z-T](#) [ISL88001IE16Z-T7A](#) [ISL88001IE16Z-TK](#) [ISL88001IE17Z-T](#)  
[ISL88001IE17Z-T7A](#) [ISL88001IE17Z-TK](#) [ISL88001IE22Z-T](#) [ISL88001IE22Z-T7A](#) [ISL88001IE22Z-TK](#) [ISL88001IE23Z-](#)  
[T](#) [ISL88001IE23Z-T7A](#) [ISL88001IE23Z-TK](#) [ISL88001IE26Z-T](#) [ISL88001IE26Z-T7A](#) [ISL88001IE26Z-TK](#)  
[ISL88001IE29Z-T](#) [ISL88001IE29Z-T7A](#) [ISL88001IE29Z-TK](#) [ISL88001IE31Z-T](#) [ISL88001IE31Z-T7A](#) [ISL88001IE31Z-](#)  
[TK](#) [ISL88001IE44Z-T](#) [ISL88001IE44Z-T7A](#) [ISL88001IE44Z-TK](#) [ISL88001IE46Z-T](#) [ISL88001IE46Z-T7A](#)  
[ISL88001IE46Z-TK](#) [ISL88001IH16Z-T](#) [ISL88001IH16Z-T7A](#) [ISL88001IH16Z-TK](#) [ISL88001IH17Z-T](#) [ISL88001IH17Z-](#)  
[T7A](#) [ISL88001IH17Z-TK](#) [ISL88001IH22Z-T](#) [ISL88001IH22Z-T7A](#) [ISL88001IH22Z-TK](#) [ISL88001IH23Z-T](#)  
[ISL88001IH23Z-T7A](#) [ISL88001IH23Z-TK](#) [ISL88001IH26Z-T](#) [ISL88001IH26Z-T7A](#) [ISL88001IH26Z-TK](#)  
[ISL88001IH29Z-T](#) [ISL88001IH29Z-T7A](#) [ISL88001IH29Z-TK](#) [ISL88001IH31Z-T](#) [ISL88001IH31Z-T7A](#) [ISL88001IH31Z-](#)  
[TK](#) [ISL88001IH44Z-T](#) [ISL88001IH44Z-T7A](#) [ISL88001IH44Z-TK](#) [ISL88001IH46Z-T](#) [ISL88001IH46Z-T7A](#)  
[ISL88001IH46Z-TK](#) [ISL88002IE16Z-T](#) [ISL88002IE16Z-T7A](#) [ISL88002IE16Z-TK](#) [ISL88002IE17Z-T](#) [ISL88002IE17Z-](#)  
[T7A](#) [ISL88002IE17Z-TK](#) [ISL88002IE22Z-T](#) [ISL88002IE22Z-T7A](#) [ISL88002IE22Z-TK](#) [ISL88002IE23Z-T](#)  
[ISL88002IE23Z-T7A](#) [ISL88002IE23Z-TK](#) [ISL88002IE26Z-T](#) [ISL88002IE26Z-T7A](#) [ISL88002IE26Z-TK](#) [ISL88002IE29Z-](#)  
[T](#) [ISL88002IE29Z-T7A](#) [ISL88002IE29Z-TK](#) [ISL88002IE31Z-T](#) [ISL88002IE31Z-T7A](#) [ISL88002IE31Z-TK](#)  
[ISL88002IE44Z-T](#) [ISL88002IE44Z-T7A](#) [ISL88002IE44Z-TK](#) [ISL88002IE46Z-T](#) [ISL88002IE46Z-T7A](#) [ISL88002IE46Z-](#)  
[TK](#) [ISL88002IH16Z-T](#) [ISL88002IH16Z-T7A](#) [ISL88002IH16Z-TK](#) [ISL88002IH17Z-T](#) [ISL88002IH17Z-T7A](#)  
[ISL88002IH17Z-TK](#) [ISL88002IH22Z-T](#) [ISL88002IH22Z-T7A](#) [ISL88002IH22Z-TK](#) [ISL88002IH23Z-T](#) [ISL88002IH23Z-](#)  
[T7A](#) [ISL88002IH23Z-TK](#) [ISL88002IH26Z-T](#) [ISL88002IH26Z-T7A](#) [ISL88002IH26Z-TK](#) [ISL88002IH29Z-T](#)  
[ISL88002IH29Z-T7A](#) [ISL88002IH29Z-TK](#)