



Screw Connectors for Printed Circuit Boards

TYPE 971-LH (-DS)


5 mm spacing - 2 to 12 poles



Distributor Stock Check



RoHS WEEE Pb free compliant



Dimensions: mm (in.)

Length of Connector (L)

L = No. of Poles x Center to Center Spacing

When locating connector, allow 0.5 mm clearance around it for process-induced variations.

Description

Types 971-LH terminal blocks have been specially designed to allow effective potting of PC boards. The molding design prevents seepage of the potting material into the wire clamping area.

- Wire entrance perpendicular to PC Board
- Straight PCB pin

Technical Data

Center to Center Spacing: 5 mm (0.197 in.)

Nominal Cross Section:

2.5 mm² (3874 mils²)

Wire Stripping Length: 5 mm (0.197 in.)

Recommended Hole Diameter in PC Board:

1.3 mm (0.051 in.)

Approval Information

UL File No.E69841

CSA File No.LR24322

Rating	Current(A)	Voltage(V)	Application group	AWG
UL	20	300	B,C,D	26-12
CSA	15	300	B,D,E	22-10

* Version DS is CSA certified for 26-10 AWG.
UL: 26-24 AWG is for factory wiring only

Screw Tightening Torque:


UL: 4.5 lbf·in

CSA: 0.51 Nm

Rated Impulse Withstand Voltage: 2500 V

Illustration

Material



Material

Molding: Polyamide, self extinguishing UL 94, V-0, color grey

Temperature limits:

Short Time: 140°C (284°F)

Continuous: RTI 105°C (221°F)

Low Limit: -40°C (-40°F)

Comparative Tracking Index: CTI > 600

Oxygen Index Rating: 33%

Terminal Body: Tin plated copper alloy

Wire Protector: Tin plated copper alloy

Screw: M3, Slotted head, zinc plated blue passivated, steel substrate

Solder Pin: Ø 1.0 mm (0.04 in.), Tin plated copper alloy

Item

971-LH (-DS)

Options

- ☐ CN: Consecutive Numbering (hot stamped numbers)
- ☐ SM: Special Marking (please provide sketch)
- ☐ PS: Clear Chromate Passivated, zinc plated, Steel Screws
- ☐ WG: Wire Guide
- ☐ G05: Gold Plating (5 micro inches)
- ☐ G30: Gold Plating (30 micro inches)
- ☐ S30: Silver Plating (30 micro inches)
- ☐ XXMM: Longer solder Pins up to 25 mm (0.98 in.)

Protruding length of pins, in millimeters:

Note: Plated component: terminal body

Ordering Note: Version with 10 mm spacing (973-LH (-DS)).

Accessories

971-LH

WIRE PROTECTOR:
with: - DS

/

POLES:
02 to 12