


# Multilayer Chip Band Pass Filters For 5GHz W-LAN


Conformity to RoHS Directive

DEA Series DEA165375BT-2122A1

## SHAPES AND DIMENSIONS



## RECOMMENDED PC BOARD PATTERNS



## ELECTRICAL CHARACTERISTICS

| Item              |                |                     | Minimum value | Typical value | Maximum value |
|-------------------|----------------|---------------------|---------------|---------------|---------------|
| Center frequency  |                | [5375MHz]           | (MHz)         | —             | —             |
| Insertion loss    | [+25°C]        | [4900 to 5149MHz]   | (dB)          | —             | 1.7           |
|                   |                | [5150 to 5850MHz]   | (dB)          | —             | 1.5           |
|                   | [−40 to +85°C] | [4900 to 5149MHz]   | (dB)          | —             | 2.0           |
|                   |                | [5150 to 5850MHz]   | (dB)          | —             | 1.8           |
| Return loss       |                | [4900 to 5850MHz]   | (dB)          | 10            | 14            |
| Ripple(Pass band) |                | [4900 to 5850MHz]   | (dB)          | —             | 0.2           |
| Attenuation       |                | [824 to 960MHz]     | (dB)          | 42.5          | 49            |
|                   |                | [1570 to 1580MHz]   | (dB)          | 19.5          | 48            |
|                   |                | [1710 to 1910MHz]   | (dB)          | 43.5          | 48            |
|                   |                | [1920 to 1990MHz]   | (dB)          | 30.5          | 50            |
|                   |                | [2110 to 2170MHz]   | (dB)          | 21.5          | 54            |
|                   |                | [9800 to 11700MHz]  | (dB)          | 25            | 38            |
|                   |                | [14700 to 17550MHz] | (dB)          | 10            | 36            |
| Temperature range | Operating      | (°C)                | −40           | —             | +85           |
|                   | Storage        | (°C)                | −40           | —             | +85           |


• Ta: +25°C

• Conformity to RoHS Directive: This means that, in conformity with EU Directive 2002/95/EC, lead, cadmium, mercury, hexavalent chromium, and specific bromine-based flame retardants, PBB and PBDE, have not been used, except for exempted applications.


• All specifications are subject to change without notice.

## FREQUENCY CHARACTERISTICS


### INSERTION LOSS



### RETURN LOSS



### ATTENUATION



### VSWR

