

LED

Light Emitting Diodes

SANKEN ELECTRIC CO.,LTD.



CAUTION/WARNING

- The information in this publication has been carefully checked and is believed to be accurate; however, no responsibility is assumed for inaccuracies.
- Sanken reserves the right to make changes without further notice to any products herein in the interest of improvements in the performance, reliability, or manufacturability of its products. Before placing an order, Sanken advises its customers to obtain the latest version of the relevant information to verify that the information being relied upon is current.
- Application and operation examples described in this catalog are quoted for the sole purpose of reference for the use of the products herein and Sanken can assume no responsibility for any infringement of industrial property rights, intellectual property rights or any other rights of Sanken or any third party which may result from its use.
- When using the products herein, the applicability and suitability of such products for the intended purpose or object shall be reviewed at the users' responsibility.
- Although Sanken undertakes to enhance the quality and reliability of its products, the occurrence of failure and defect of semiconductor products at a certain rate is inevitable. Users of Sanken products are requested to take, at their own risk, preventative measures including safety design of the equipment or systems against any possible injury, death, fires or damages to the society due to device failure or malfunction.
- Sanken products listed in this catalog are designed and intended for the use as components in general purpose electronic equipment or apparatus (home appliances, office equipment, telecommunication equipment, measuring equipment, etc.). Before placing an order, the user's written consent to the specifications is requested.

When considering the use of Sanken products in the applications where higher reliability is required (transportation equipment and its control systems, traffic signal control systems or equipment, fire/ crime alarm systems, various safety devices, etc.), please contact your nearest Sanken sales representative to discuss and obtain written confirmation of your specifications.

The use of Sanken products without the written consent of Sanken in the applications where extremely high reliability is required (aerospace equipment, nuclear power control systems, life support systems, etc.) is strictly prohibited.
- Anti radioactive ray design is not considered for the products listed herein.
- This publication shall not be reproduced in whole or in part without prior written approval from Sanken.
- Gallium arsenide is used in some of the products listed in this publication. These products are dangerous if they are burned or smashed in the process of disposal. It is also dangerous to drink the liquid or inhale the gas generated by such products when chemically disposed.

How to Order

Specify a multiple of the standard minimum package quantity when placing an order (100 diodes/package).

For the ordering quantity of taped products, see pages 61 to 63.


When ordering taped products, add a taping number (TP[]) to the end of the product number. (See pages 61 to 63.)

Contents


■Product Designation	2	■2×4 Rectangular LED	34
■Selection Guide	4	<i>SEL4025 Series</i>	
■Product Index by Part Number	6	■2×4 Rectangular LED (Direct Mount)	35
■Application Notes	8	<i>SEL4026 Series</i>	
■5φ Round Standard LED (With Stopper)	10	■4φ Bow-shaped LED	36
<i>SEL1010 Series</i>		<i>SEL4027 Series</i>	
■5φ Round Standard LED	11	■3.1φ Bow-shaped LED	37
<i>SEL1010M Series</i>		<i>SEL4028 Series</i>	
■5φ Round Wide-directivity LED	12	■3.1φ Bow-shaped LED (Direct Mount)	38
<i>SEL1010XM Series</i>		<i>SEL4029 Series</i>	
■5φ Round Narrow-directivity LED (Direct Mount)	13	■4φ Bow-shaped LED (Direct Mount)	39
<i>SEL1050M Series</i>		<i>SEL6027 Series</i>	
■5φ Round Narrow-directivity LED	14	■5-mm Pitch Lead Rectangular LED (Direct Mount)	40
<i>SEL1015 Series</i>		<i>SEL5020 Series</i>	
■5φ Cylindrical LED	15	■5-mm Pitch Lead 3φ Lens-type LED (Direct Mount)	41
<i>SEL1011 Series</i>		<i>SEL5021 Series</i>	
■4.6×5.6φ Egg-shaped LED	16	■5-mm Pitch Lead Bow-shaped LED (Direct Mount)	42
<i>SEL1053M Series</i>		<i>SEL5023 Series</i>	
■4φ Round Standard LED	17	■5-mm Pitch Lead Egg-shaped LED (Direct Mount)	43
<i>SEL4010 Series</i>		<i>SEL5055 Series</i>	
■4φ Round Wide-directivity LED (Direct Mount)	18	■5φ Round Standard Bicolor LED	44
<i>SEL4014 Series</i>		<i>SML1016/10016 Series</i>	
■3φ Round LED (Direct Mount)	19	■5φ Round Bicolor LED	45
<i>SEL6010 Series</i>		<i>SML10051 Series</i>	
■3φ Round Wide-directivity LED (Direct Mount)	20	■2.5×5 Rectangular Bicolor LED	46
<i>SEL6014 Series</i>		<i>SML10060 Series</i>	
■3φ Round Narrow-directivity LED (Direct Mount)	21	■3.3×6 Rectangular Bicolor LED (Direct Mount)	47
<i>SEL6015 Series</i>		<i>SML70020 Series</i>	
■3φ Round Standard LED	22	■3.3×6 Bow-shaped Bicolor LED (Direct Mount)	48
<i>SEL2010 Series</i>		<i>SML70023 Series</i>	
■3φ Round Narrow-directivity LED	23	■Egg-shaped Bicolor LED (Direct Mount)	49
<i>SEL2015 Series</i>		<i>SML70055 Series</i>	
■3φ Cylindrical LED	24	■3×1.5 Surface Mount LED (Flat Lens)	50
<i>SEL2011 Series</i>		<i>SEC1001 Series</i>	
■2φ Round Special-shaped LED	25	■3×1.5 Surface Mount LED (Inner Lens)	51
<i>SEL4017 Series</i>		<i>SEC1003 Series</i>	
■5φ Inverted-cone LED for surface illumination	26	■3×2.5 Bicolor Surface Mount LED (Flat Lens)	52
<i>SEL1013 Series</i>		<i>SEC2002 Series</i>	
■3φ Inverted-cone LED for surface illumination (Direct Mount)	27	■3×2.5 Bicolor Surface Mount LED (Inner Lens)	53
<i>SEL6013 Series</i>		<i>SEC2004 Series</i>	
■3φ Inverted-cone LED for surface illumination	28	■5φ Round Infrared LED -	54
<i>SEL2013 Series</i>		<i>SID1010M Series</i>	
■Lamp Casings Inverted-cone LED for surface illumination ..	29	■5φ Round Infrared LED (Direct Mount)	55
■3×5 Rectangular LED	30	<i>SID1050M Series</i>	
<i>SEL1021 Series</i>		■5φ Round Infrared LED	56
■2.5×5 Rectangular LED	31	<i>SID300/1003 Series</i>	
<i>SEL1022 Series</i>		■3φ Round Infrared LED	57
■2×5 Rectangular LED	32	<i>SID2010 Series</i>	
<i>SEL1020 Series</i>		■Characteristic Curves	58
■1×5 Rectangular LED	33	■Taping Specifications	61
<i>SEL1024 Series</i>		■List of Discontinued Products	64

Product Designation


Single-color LED



Bicolor LED




Surface Mount LEDs




Product Designation

Infrared LED (1)



Infrared LED (2)



Color code		Standard type			Ultra-high-intensity type		
		Emitting color	Chip material	Peak wavelength (nm)	Emitting color	Chip material	Peak wavelength (nm)
1	:	Deep red	GaP	700			
2	:	Red	GaAsP	630	Ultra-high-intensity red	AlGaInP	635
4	:	Green	GaP	560/558			
5	:	Pure green	GaP	555			
6	:	High-intensity red	GaAlAs	660			
7	:	Yellow	GaP	570	Ultra-high-intensity yellow	AlGaInP	572
8	:	Amber	GaAsP	610	Ultra-high-intensity amber	AlGaInP	615
9	:	Orange	GaAsP	587	Ultra-high-intensity orange	AlGaInP	590
B	:				Ultra-high-intensity light amber	AlGaInP	600
D	:				Ultra-high-intensity pure green	InGaIn	525
E	:	Blue	GaN	430	Ultra-high-intensity blue	InGaIn	470

Lens color			
R	Diffused red	K	Transparent yellow
W	Diffused white	G	Diffused green
S	Transparent red	E	Transparent green
C	Clear	B	Transparent blue
D	Diffused orange	BR	Transparent dark blue
A	Transparent orange	BP	Transparent Violet
Y	Diffused yellow	BQ	Transparent light dark blue

Selection Guide

Single-color LEDs/Single-color surface mount LEDs

Shape	Lens diameter	Feature	Direct mount	Series	Emitting color and peak wavelength																		Page	
					Blue	Ultra-high-intensity blue	Ultra-high-intensity pure green	Pure green	Deep green	Green	Yellow	Ultra-high-intensity yellow	Orange	Ultra-high-intensity orange	Ultra-high-intensity light amber	Amber	Ultra-high-intensity amber	Red	Ultra-high-intensity red	High-intensity red	Deep red			
					E	E	D	5	4	4	7	7	9	9	B	8	8	2	2	6	1			
					Color code⇒ Peak wavelength[nm]⇒					430	470	525	555	558	560	570	572	587	590	600	610	615		630
Round	5φ	Standard	N	SEL1010				○		○	○		○			○		○		○		○	10	
			N	SEL1010M				○		○	○		○			○		○					11	
		Wide directivity	N	SEL1010XM			○	○										○		○				12
			Narrow directivity	Y	SEL1050M			○*	○*	○		○			○				○		○			
		N		SEL1015																		○		
		N	SEL1011								○	○		○				○		○			○	
	5.6×4.6φ	Egg-shaped	N	SEL1053M							○							○		○				16
	4φ	Standard	N	SEL4010				○			○	○		○			○		○			○		17
		Wide directivity	Y	SEL4014				○			○	○		○			○		○			○		18
	3φ	Standard	Y	SEL6010				○			○	○		○			○		○			○		19
		Wide directivity	Y	SEL6014				○	○		○	○		○		○	○		○					20
		Narrow directivity	Y	SEL6015				○			○	○		○					○					21
		Standard	N	SEL2010		○	○	○	○		○	○	○	○			○		○		○	○		22
		Narrow directivity	N	SEL2015				○			○	○		○			○		○					23
		N	SEL2011							○			○										○	24
2φ		N	SEL4017							○	○		○			○					○	25		
Inverted cone	5φ	For surface illumination	N	SEL1013				○		○	○		○			○		○					26	
	3φ		Y	SEL6013				○		○												27		
	3φ		N	SEL2013				○		○	○		○			○		○		○			28	
Rectangular	3×5		N	SEL1021						○	○		○			○						○	30	
	2.5×5		N	SEL1022						○	○		○			○		○					31	
	2×5		N	SEL1020						○	○		○			○		○				○	32	
	1×5		N	SEL1024				○		○	○		○			○						○	33	
	2×4		N	SEL4025				○		○	○		○			○		○					34	
	2×4		Y	SEL4026						○	○		○			○		○					35	
Bow shaped	4φ		N	SEL4027						○								○					36	
	3.1φ		N	SEL4028				○	○	○	○		○			○		○		○			37	
	3.1φ		Y	SEL4029						○	○		○			○		○					38	
	4φ		Y	SEL6027						○			○					○					39	
5 mm pitch lead	Rectangular		Y	SEL5020			○		○				○			○		○			○		40	
	3φ	Narrow directivity	Y	SEL5021				○		○	○		○			○		○					41	
	Bow-shaped	Wide directivity	Y	SEL5023		○	○		○		○	○	○	○	○	○	○	○	○				42	
	5.6×4.6φ		Y	SEL5055							○		○					○					43	
Surface mount	Flat lens	SMD		SEC1001		○	○	○	○	○	○	○	○	○		○		○		○	○		50	
	Inner lens	SMD		SEC1003				○	○	○	○	○	○	○		○	○	○	○	○	○		51	

Y...Supported
N...Not supported
★...Not supported

Selection Guide

Bicolor LEDs/Bicolor surface mount LEDs

Shape	Lens diameter	Feature	Direct mount	Series	Emitting color and peak wavelength																Page
					Deep red	Red	Amber	Orange	High-intensity red	Red	Ultra-high-intensity orange	Ultra-high-intensity red	Red	Ultra-high-intensity amber	Orange	Red	High-intensity red	Orange	green	Pure green	
				Color code→	1	2	8	9	6	2	9	2	2	8	9	2	6	9	4	5	
				Peak wavelength[nm]→	700	630	610	587	660	630	590	635	630	615	587	630	660	587	560	555	
				Series	Pure green	green	green	green	Yellow	Orange	Yellow	Ultra-high-intensity yellow	Yellow	Ultra-high-intensity yellow	Red	Yellow	green	Pure green	green	Pure green	
				Color code→	5	4	4	4	7	9	7	7	7	7	2	7	4	5	4	5	
				Peak wavelength[nm]→	555	560	560	560	570	587	570	572	570	572	630	570	560	555	560	555	570
Round	5φ	Standard	N	SML1016/10016	○	○	○	○													44
			N	SML10016N					○												44
			N	SML10051		○															45
			N	SML10051N					○												45
	5.6×4.6φ	Egg-shaped	Y	SML70055				○				○	○	○	○						49
			Y	SML70055N												○					49
Rectangular	2.5×5		N	SML10060		○		○													46
			N	SML10060N					○												46
	3.3×6		Y	SML70020		○	○	○													47
			Y	SML70023		○	○	○		○	○										48
Surface mount	Flat lens	SMD		SEC2002		○		○	○								○	○	○	○	52
	Inner lens	SMD		SEC2004			○	○	○											○	53

Y...Supported
N...Not supported

Infrared LED lamps

Profile	Lens diameter	Direct mount	Series	High-output infrared	High-output infrared	Infrared	Page
				Chip type→	G	K	
				Peak wavelength[nm]→	850	940	
Round	5φ	N	SID1010		○	○	54
		Y	SID1050		○		55
		N	SID300/1003	○		○	56
	3φ	N	SID2010		○	○	57

Y...Supported
N...Not supported

Product Index by Part Number

Part Number	Page
SEC1101C	50
SEC1201C	50
SEC1203C	51
SEC1401C	50
SEC1401E-TG	50
SEC1403C	51
SEC1403E-TG	51
SEC1501C	50
SEC1503C	51
SEC1601C	50
SEC1603C	51
SEC1701C-YG	50
SEC1703C	51
SEC1801C	50
SEC1803C	51
SEC1901C	50
SEC1903C	51
SEC1E01C	50
SEC2422C	52
SEC2442C	52
SEC2462C	52
SEC2484C	53
SEC2492C	52
SEC2494C	53
SEC2552C	52
SEC2554C	54
SEC2592C	52
SEC2762C-YG	52
SEC2764C	53
SEC2774C	54
SECS1203C	51
SECS1803C	51
SECS1903C	51
SECU1D01C	50
SECU1E01C	50
SEL1110R	10
SEL1110S	10
SEL1110W	10
SEL1111R	15
SEL1120R	32
SEL1121R	30
SEL1124R	33
SEL1210R	10
SEL1210RM	11
SEL1210S	10
SEL1210SM	11
SEL1211R	15
SEL1213C	26
SEL1220R	32
SEL1222R	31
SEL1250RM	13
SEL1250SM	13
SEL1410E	10
SEL1410EM	11
SEL1410G	10
SEL1410GM	11

Part Number	Page
SEL1411G	15
SEL1413E	26
SEL1420G	32
SEL1421G	30
SEL1422G	31
SEL1424G	33
SEL1450EKM	13
SEL1450GM-YG	13
SEL1453CEMKT	16
SEL1510C	10
SEL1510CM	11
SEL1513E	26
SEL1550CM	13
SEL1610C	10
SEL1610W	10
SEL1615C	14
SEL1710K	10
SEL1710KM	11
SEL1710Y	10
SEL1711Y	15
SEL1713K	26
SEL1720Y	32
SEL1721Y	30
SEL1722K	31
SEL1722Y	31
SEL1724Y	33
SEL1810A	10
SEL1810AM	11
SEL1810D	10
SEL1810DM	11
SEL1811D	15
SEL1813A	26
SEL1820D	32
SEL1821D	30
SEL1822D	31
SEL1824D	33
SEL1850AM	13
SEL1850DM	13
SEL1910A	10
SEL1910AM	11
SEL1910D	10
SEL1910DM	11
SEL1911D	15
SEL1913K	26
SEL1920D	32
SEL1921D	30
SEL1922D	31
SEL1924D	33
SEL1950KM	13
SEL2110R	22
SEL2110S	22
SEL2110W	22
SEL2111R	24
SEL2210R	22
SEL2210S	22
SEL2210W	22

Part Number	Page
SEL2213C	28
SEL2215R	23
SEL2215S	23
SEL2410E	22
SEL2410G	22
SEL2411G	24
SEL2413E	28
SEL2413G	28
SEL2415E	23
SEL2415G	23
SEL2510C	22
SEL2510G	22
SEL2513E	28
SEL2515C	23
SEL2610C	22
SEL2613CS-S	28
SEL2710K	22
SEL2710Y	22
SEL2713K	28
SEL2715K	23
SEL2715Y	23
SEL2810A	22
SEL2810D	22
SEL2813A	28
SEL2815A	23
SEL2815D	23
SEL2910A	22
SEL2910D	22
SEL2911D	24
SEL2913K	28
SEL2915A	23
SEL2915D	23
SEL2E10C	22
SEL4110R	17
SEL4110S	17
SEL4114R	18
SEL4114S	18
SEL4117R	25
SEL4210R	17
SEL4210S	17
SEL4214R	18
SEL4214S	18
SEL4225C	34
SEL4225R	34
SEL4226C	35
SEL4226R	35
SEL4227C	36
SEL4228C	37
SEL4229R	38
SEL4410E	17
SEL4410G	17
SEL4414E	18
SEL4414G	18
SEL4417G	25
SEL4425E	34
SEL4425G	34

Product Index by Part Number

Part Number	Page
SEL4426E	35
SEL4426G	35
SEL4427EP	36
SEL4428B-TG	37
SEL4428E	37
SEL4429E	38
SEL4510C	17
SEL4514C	18
SEL4525C	34
SEL4528C	37
SEL4628C-S	37
SEL4710K	17
SEL4710Y	17
SEL4714K	18
SEL4714Y	18
SEL4717Y	25
SEL4725K	34
SEL4725Y	34
SEL4726K	35
SEL4726Y	35
SEL4728K	37
SEL4729KH	38
SEL4810A	17
SEL4810D	17
SEL4814A	18
SEL4814D	18
SEL4817D	25
SEL4825A	34
SEL4825D	34
SEL4826A	35
SEL4826D	35
SEL4828A	37
SEL4829A	38
SEL4910A	17
SEL4910D	17
SEL4914A	18
SEL4914D	18
SEL4917D	25
SEL4925A	34
SEL4925D	34
SEL4926A	35
SEL4926D	35
SEL4928A	37
SEL4929A	38
SEL5220S	40
SEL5221S	41
SEL5223S	42
SEL5255S	43
SEL5420E	40
SEL5421E	41
SEL5423E	42
SEL5520C	40
SEL5521C	41
SEL5523C	42
SEL5620C	40
SEL5721C	41

Part Number	Page
SEL5723C	42
SEL5755C	43
SEL5820A	40
SEL5821A	41
SEL5823A	42
SEL5920A	40
SEL5921A	41
SEL5923A	42
SEL5955A	43
SEL5E23C	42
SEL6110R	19
SEL6110S	19
SEL6210R	19
SEL6210S	19
SEL6214S	20
SEL6215S	21
SEL6227S	39
SEL6410E	19
SEL6410G	19
SEL6413E	27
SEL6414E	20
SEL6414E-TG	20
SEL6415E	21
SEL6427EP	39
SEL6510C	19
SEL6510G	19
SEL6513C	27
SEL6514C	20
SEL6515C	21
SEL6710K	19
SEL6710Y	19
SEL6714K	20
SEL6714W	20
SEL6715C	21
SEL6810A	19
SEL6810D	19
SEL6814A	20
SEL6910A	19
SEL6910D	19
SEL6914A	20
SEL6914W	20
SEL6915A	21
SEL6927A	39
SELS5223C	42
SELS5823C	42
SELS5923C	42
SELS5B23C	42
SELS6B14C	20
SELU1210CXM	12
SELU1250CM	13
SELU1253CMKT	16
SELU1810CXM	12
SELU1853CMKT	16
SELU1D10CXM	12
SELU1D50CM	13
SELU1E10CXM	12

Part Number	Page
SELU1E50CM	13
SELU2710C	22
SELU2D10C	22
SELU2E10C	22
SELU5723C	42
SELU5823C	42
SELU5E20C	40
SELU5E23C	42
SID1003BQ	56
SID1010CM	54
SID1010CXM	54
SID1050CM	55
SID1G307C	56
SID1K10CM	54
SID1K10CXM	54
SID2010C	57
SID2K10C	57
SID303C	56
SID307BR	56
SID313BP	56
SML11516C	44
SML1216C	44
SML1216W	44
SML12451W	45
SML12460C	46
SML1516W	44
SML16716CN	44
SML16716W	44
SML16716WN	44
SML16751WN	45
SML16760CN	46
SML1816W	44
SML19416W	44
SML19460C	46
SML72420C	47
SML72423C	48
SML72755C	49
SML72923C	48
SML76755WN	49
SML78420C	47
SML78423C	48
SML79255C	49
SML79420C	47
SML79423C	48
SML79455C	49
SMLS79723C	48
SMLU72755C	49
SMLU78755C	49

Application Notes

Sanken Electric's light emitting diodes (LEDs) are all molded in resin molds.

When using Sanken's LEDs, observe the following cautions:


■Heat resistance of mold resin

Since an LED must emit internally generated light with high efficiency, a highly transparent resin is used for molding. To ensure high transparency, the molding material must be free from the additives(silica, glass fiber, and others) that are used to improve the heat and moisture resistance of other semiconductor components(such as transistors).

Since the resin used for LEDs generally has a low heat resistance, the following cautions must be fully considered.

Never apply an external force, stress, or excess vibration to the terminals (leads) at high temperature. The glass transition point of the epoxy resin used in LEDs is about 120 to 130°C. Beyond this temperature range, the coefficient of linear thermal expansion becomes more than double that at room temperature, and the

Figure 1 Disconnection temperature - Terminal load




resin softens as well.

Under this condition, an external force or stress may budge the terminals, and may result in disconnection of the internal wire. Figure 1 shows reference data for the disconnection temperature and terminal load for the SEL1010 Series.

- Do not apply heat beyond the absolute maximum rating of the storage temperature (100°C for ordinary LEDs, 90°C for chip LEDs). (For soldering, see the soldering conditions.)

Fracture strength




■Mechanical strength

If an excessive mechanical force is applied between the lens resin and the terminals, the lens resin or internal connections may be damaged. The previous figure shows the fracture strength of the SEL1000 Series according to the direction of the force applied to the terminals. When aligning or forming the terminals after soldering, do not bend or twist them with a force beyond the limits shown in the diagram below.

■Forming

1. Be sure to form terminals before soldering.
2. When forming the terminals, hold tightly them at a point closer to the lens resin than the forming position to prevent stress from being applied between the lens resin and the terminals.
3. Form the terminals only below the tie-bar cuts(protruding part of the terminals).
4. Make the forming pitch equal to the board hole pitch.



■Chemical resistance

For washing after soldering, the following chemicals are recommended:

- Isopropyl alcohol
- Ethyl alcohol

In addition, keep the dip time within five minutes and work at room temperature.

- Freon-substitute cleaning liquid

Depending on the constituents, the chemicals may discolor the resin. Make sure that there will be no problems before use.

■Mounting method

Do not mount the LED in such a way that there is a residual stress between the terminal and lens resin.

■Soldering

1. Mounting holes





The recommended PCB hole diameters are as follows:

Lead diameter	PCB hole diameter
0.4×0.45mm	φ0.9 to 1.0
□0.5mm	φ1.0 to 1.1
□0.6mm	φ1.0 to 1.2

Application Notes


2. Soldering conditions

●Lamp Type

		Standard	Manual contact mount insertion	Automatic contact mount insertion	
Soldering iron	Temperature	Iron bit: 320 to 340°C	Iron bit: 320 to 340°C		
	Time	3 sec. or less	3 sec. or less		
	Position				
Dip	Temperature	Soldering Bath: 250±5°C	Soldering Bath: 250±5°C	Preheat: 90°C (back of the PCB)	Soldering Bath: 250°C
	Time	3 sec. or less	3 sec. or less	2 min. or less	3 sec. or less
	Position				

- The heat resistance of the mold-resin of the direct mount type is almost equal to that of the standard type. Be careful not to apply a load when the LED is heated.
- When thermally curing the adhesive of chip components on the same board after LED mounting, keep the temperature of the curing oven below 120°C and the curing time to less than 60 seconds. (For soldering a Surface Mount LED, see the soldering conditions.)
- When an LED is mounted by means of automatic contact mount insertion, note that soldering defects may occur depending on the conditions of insertion even under the above conditions.

●Surface Mount Type



■Overcurrent

Since an overcurrent may burn the LED, connect a protective resistor in series to prevent a current in excess of 100 mA in the case of a spontaneous pulse (excluding infrared LED).

■Contact mount LEDs

●Printed circuit board(PCB)

Single-faced PCBs are recommended. (Do not use through hole types when using double-faced PCBs.) If chip components coexist on the same board, insert the LEDs after curing the chip adhesive.

●Conditions of insertion

Keep the insertion pressure as low as possible. The T pattern of Pana-sert is recommended for cut & clinch. When using the N pattern, maximize the clinch angle on the anode side of the LED.

■Moisture-proof packaging of Surface Mount LEDs

1. Influence of moisture absorption on resin of chip LEDs

- If the resin is unusually damp, solder dipping may cause interfacial defoliation. This phenomenon, generally called "popcorn

phenomenon", occurs when a drastic temperature change causes moisture in the resin to evaporate and to swell.

- Due to this defoliation, the efficiency of light emission might worsen and the luminosity could lower.

2. Moisture-proof packaging

- Surface Mount LEDs are protected by a moisture-proof packaging (baked on by Sanken) to minimize moisture absorption by the resin before use.
- Aluminum laminates with high moisture resistance are used for packaging.
- Silica gel packs are enclosed in each package to further improve moisture-proof efficiency.


3. Storage after opening

- Once the package has been opened, solder dipping should be carried out within seven days.

4. Handling of Remaining LED Chips

- If some Surface Mount LEDs have not been used, put them back into the moisture-proof packaging, seal the package completely and store it in a dry place.

■Reference mounting pattern for Surface Mount LED (Unit: mm)




5 ϕ Round Standard LED (With Stopper)


SEL1010 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, tw≤100μs
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage		Condition I _F (mA)	Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F (V)	I _R (μA)		Condition V _R (V)	I _V (mcd)	Condition I _F (mA)	λ _P (nm)	Condition I _F (mA)	Δλ (nm)	Condition I _F (mA)		
			typ		max		typ		(mA)		typ		(mA)	
Deep red	SEL1110R	Diffused red	2.0	2.5	10	50	3	2.8	5	700	10	100	10	GaP
	SEL1110W	Diffused white						2.8						
	SEL1110S	Transparent red						4.5						
High-intensity red	SEL1610W	Diffused white	1.75	2.2	10	100	3	1000	20	660	10	30	10	GaAlAs
	SEL1610C	Clear						1200						
Red	SEL1210R	Diffused red	1.9	2.5	10	50	3	26	20	630	10	35	10	GaAsP
	SEL1210S	Transparent red						75						
Amber	SEL1810D	Diffused orange	1.9	2.5	10	50	3	18	10	610	10	35	10	
	SEL1810A	Transparent orange						37						
Orange	SEL1910D	Diffused orange	1.9	2.5	10	50	3	14	10	587	10	33	10	
	SEL1910A	Transparent orange						25						
Yellow	SEL1710Y	Diffused yellow	2.0	2.5	10	50	3	22	10	570	10	30	10	GaP
	SEL1710K	Transparent yellow						65						
Green	SEL1410G	Diffused green	2.0	2.5	10	50	3	32	20	560	10	20	10	
	SEL1410E	Transparent green						84						
Pure green	SEL1510C	Clear	2.0	2.5	10	50	3	50	20	555	10	20	10	

5 ϕ Round Standard LED


SEL1010M Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, $t_w \leq 100\mu s$
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material	
			V _F		Condition	I _R	Condition	I _V	Condition	λP	Condition	Δλ	Condition		
			typ	max	I _F (mA)	max	V _R (V)	typ	I _F (mA)	typ	I _F (mA)	typ	I _F (mA)		
Red	SEL1210RM	Diffused red	1.9	2.5	10	50	3	36	20	630	10	35	10	GaAsP	
	SEL1210SM	Transparent red						75							
Amber	SEL1810DM	Diffused orange	1.9	2.5	10	50	3	18	10	610	10	35	10		
	SEL1810AM	Transparent orange						37							
Orange	SEL1910DM	Diffused orange	1.9	2.5	10	50	3	19	10	587	10	33	10		
	SEL1910AM	Transparent orange						34							
Yellow	SEL1710KM	Transparent yellow	2.0	2.5	10	50	3	65	10	570	10	30	10		GaP
Green	SEL1410GM	Diffused green	2.0	2.5	10	50	3	30	20	560	10	20	10		
	SEL1410EM	Transparent green						84							
Pure green	SEL1510CM	Clear	2.0	2.5	10	50	3	50	20	555	10	20	10		

5 ϕ Round Wide-directivity LED


SEL1010XM Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating		Condition
		AlGaInP	InGaN	
I_F	mA	30		
ΔI_F	mA/°C	-0.45		Above 25°C
I_{FP}	mA	100		f=1kHz, $t_w \leq 100\mu s$
V_R	V	4	5	
Top	°C	-30 to +85	-25 to +85	
Tstg	°C	-30 to +100		

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition	I _R	Condition	I _V	Condition	λP	Condition	Δλ	Condition	
			(V)			(μA)		V _R		(mcd)		I _F		
			typ	max	(mA)	max	(V)	typ	(mA)	typ	(mA)	typ	(mA)	
Ultra-high-intensity red	SELU1210CXM	Clear	2.0	2.5	10	100	4	280	20	635	10	15	10	AlGaInP
Ultra-high-intensity amber	SELU1810CXM	Clear						570	20	615	10	15	10	
Ultra-high-intensity pure green	SELU1D10CXM	Clear	3.3	4.0	20	10	5	2000	20	525	10	35	10	InGaN
Ultra-high-intensity blue	SELU1E10CXM	Clear						600	20	470	10	35	10	

5 ϕ Round Narrow-directivity LED (Direct Mount)


SEL1050M Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating			Condition
		GaP/GaAsP	AlGaInP	InGaN	
I_F	mA	30			
ΔI_F	mA/°C	-0.45			Above 25°C
I_{FP}	mA	100			$f=1\text{kHz}$, $t_w \leq 100\mu\text{s}$
V_R	V	3	4	5	
Top	°C	-30 to +85		-25 to +85	
Tstg	°C	-30 to +100			

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition I _F (mA)	I _R (μA)	Condition V _R (V)	I _V (mcd)	Condition I _F (mA)	λP (nm)	Condition I _F (mA)	Δλ (nm)	Condition I _F (mA)	
			typ	max										
Ultra-high-intensity red	SELU1250CM	Clear	2.0	2.5	10	100	4	900	20	635	10	15	10	AlGaInP
Red	SEL1250SM	Transparent red	1.9	2.5	10	50	3	75	20	630	10	35	10	GaAsP
	SEL1250RM	Diffused red						48						
Amber	SEL1850AM	Transparent orange	1.9	2.5	10	50	3	90	20	610	10	35	10	GaAsP
	SEL1850DM	Diffused orange						60						
Orange	SEL1950KM	Transparent orange	1.9	2.5	10	50	3	96	20	587	10	33	10	
Green	SEL1450EK	Transparent green	2.0	2.5	10	50	3	190	20	560	10	20	10	GaP
	SEL1450GM-YG	Diffused green						120						
Pure green	SEL1550CM	Clear	2.0	2.5	10	50	3	72	20	555	10	20	10	
Ultra-high-intensity pure green	SELU1D50CM	Clear	3.3	4.0	20	10	5	6000	20	525	10	35	10	InGaN
Ultra-high-intensity blue	SELU1E50CM	Clear	3.3	4.0	20	10	5	1850	20	470	10	35	10	

5 ϕ Round Narrow-directivity LED


SEL1015 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, $t_w \leq 100\mu s$
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	


Electrical Optical characteristics (Ta=25°C)

Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition I _F	I _R	Condition V _R	I _V	Condition I _F	λ _P	Condition I _F	Δλ	Condition I _F	
			(V)			(μA)		(mcd)		(nm)		(nm)		
			typ	max	(mA)	max	(V)	typ	(mA)	typ	(mA)	typ	(mA)	
High-intensity red	SEL1615C	Clear	1.75	2.2	10	100	3	700	20	660	10	30	10	GaAlAs

5 ϕ Cylindrical LED

SEL1011 Series

External Dimensions (Unit: mm)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, tw≤100μs
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition I _F	I _R	Condition V _R	I _V	Condition I _F	λP	Condition I _F	Δλ	Condition I _F	
			(V)			(μA)		(mcd)		(nm)		(nm)		
			typ	max	max	(V)	typ	(mA)	typ	(mA)	typ	(mA)		
Deep red	SEL1111R	Diffused red	2.0	2.5	10	50	3	1.4	10	700	10	100	10	GaP
Red	SEL1211R	Diffused red	1.9	2.5	10	50	3	12	20	630	10	35	10	GaAsP
Amber	SEL1811D	Diffused orange	1.9	2.5	10	50	3	8.0	10	610	10	35	10	
Orange	SEL1911D	Diffused orange	1.9	2.5	10	50	3	8.0	10	587	10	33	10	
Yellow	SEL1711Y	Diffused yellow	2.0	2.5	10	50	3	13	10	570	10	30	10	GaP
Green	SEL1411G	Diffused green	2.0	2.5	10	50	3	30	20	560	10	20	10	

4.6×5.6 ϕ Egg-shaped LED


SEL1053M Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating		Condition
		GaP	AlGaInP	
I_F	mA	30		
ΔI_F	mA/°C	-0.45		Above 25°C
I_{FP}	mA	100		f=1kHz, $t_w \leq 100\mu s$
V_R	V	3	4	
Top	°C	-30 to +85		
Tstg	°C	-30 to +100		

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage		Condition	Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F (V)	I _F (mA)		I _R (μA)	Condition	I _V (mcd)	I _F (mA)	λ _P (nm)	I _F (mA)	Δλ (nm)	Condition	
					typ									
Ultra-high-intensity red	SELU1253CMKT	Clear	2.0	2.5	10	100	4	200	20	635	10	15	10	AlGaInP
Ultra-high-intensity amber	SELU1853CMKT	Clear	2.0	2.5	10	100	4	450	20	615	10	15	10	
Green	SEL1453CEMKT	Transparent green	2.0	2.5	10	50	3	140	20	560	10	20	10	GaP

4 ϕ Round Standard LED


SEL4010 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, tw≤100μs
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition I _F (mA)	I _R (μA) max	Condition V _R (V)	I _V (mcd) typ	Condition I _F (mA)	λ _P (nm) typ	Condition I _F (mA)	Δλ (nm) typ	Condition I _F (mA)	
			typ	max										
Deep red	SEL4110S	Transparent red	2.0	2.5	10	50	3	2.4	5	700	10	100	10	GaP
	SEL4110R	Diffused red						1.7						
Red	SEL4210S	Transparent red	1.9	2.5	10	50	3	30	20	630	10	35	10	GaAsP
	SEL4210R	Diffused red						17						
Amber	SEL4810A	Transparent orange	1.9	2.5	10	50	3	20	10	610	10	35	10	
	SEL4810D	Diffused orange						15						
Orange	SEL4910A	Transparent orange	1.9	2.5	10	50	3	26	10	587	10	33	10	
	SEL4910D	Diffused orange						16						
Yellow	SEL4710K	Transparent yellow	2.0	2.5	10	50	3	36	10	570	10	30	10	
	SEL4710Y	Diffused yellow						14	10					
Green	SEL4410E	Transparent green	2.0	2.5	10	50	3	87	20	560	10	20	10	
	SEL4410G	Diffused green						34	20					
Pure green	SEL4510C	Clear	2.0	2.5	10	50	3	45	20	555	10	20	10	

4 ϕ Round Wide-directivity LED (Direct Mount)


SEL4014 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	$f=1\text{kHz}$, $t_w \leq 100\mu\text{s}$
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to 100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F (V)	Condition I _F (mA)	I _R (μA)	Condition V _R (V)	I _V (mcd)	Condition I _F (mA)	λ _P (nm)	Condition I _F (mA)	Δλ (nm)	Condition I _F (mA)		
													typ	
Deep red	SEL4114S	Transparent red	2.0	2.5	10	50	3	3.8	10	700	10	100	10	GaP
	SEL4114R	Diffused red						2.8						
Red	SEL4214S	Transparent red	1.9	2.5	10	50	3	40	20	630	10	35	10	GaAsP
	SEL4214R	Diffused red						24						
Amber	SEL4814A	Transparent orange	1.9	2.5	10	50	3	20	10	610	10	35	10	
	SEL4814D	Diffused orange						15						
Orange	SEL4914A	Transparent orange	1.9	2.5	10	50	3	26	10	587	10	33	10	
	SEL4914D	Diffused orange						11						
Yellow	SEL4714K	Transparent yellow	2.0	2.5	10	50	3	38	10	570	10	30	10	
	SEL4714Y	Diffused yellow						27						
Green	SEL4414E	Transparent green	2.0	2.5	10	50	3	69	20	560	10	20	10	GaP
	SEL4414G	Diffused green						48						
Pure green	SEL4514C	Clear	2.0	2.5	10	50	3	26	20	555	10	20	10	

3 ϕ Round LED (Direct Mount)


SEL6010 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I _F	mA	30	
ΔI _F	mA/°C	-0.45	Above 25°C
I _{FP}	mA	100	f=1kHz, tw≤100μs
V _R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage		Condition	Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip materia
			V _F			I _R	Condition	I _V	Condition	λP	Condition	Δλ	Condition	
			(V)	I _F	(μA)	V _R		(mcd)		I _F		(nm)		
			typ	max	(mA)	max	(V)	typ	(mA)	typ	(mA)	typ	(mA)	
Deep red	SEL6110S	Transparent red	2.0	2.5	10	50	3	3.9	10	700	10	100	10	GaP
	SEL6110R	Diffused red						2.6						
Red	SEL6210S	Transparent red	1.9	2.5	10	50	3	41	20	630	10	35	10	
	SEL6210R	Diffused red						18						
Amber	SEL6810A	Transparent orange	1.9	2.5	10	50	3	22	10	610	10	35	10	GaAsP
	SEL6810D	Diffused orange						9.6						
Orange	SEL6910A	Transparent orange	1.9	2.5	10	50	3	22	10	587	10	33	10	
	SEL6910D	Diffused orange						11						
Yellow	SEL6710K	Transparent yellow	2.0	2.5	10	50	3	37	10	570	10	30	10	
	SEL6710Y	Diffused yellow						11						
Green	SEL6410E	Transparent green	2.0	2.5	10	50	3	90	20	560	10	20	10	GaP
	SEL6410G	Diffused green						30						
Pure green	SEL6510C	Clear	2.0	2.5	10	50	3	42	20	555	10	20	10	
	SEL6510G	Diffused green						9.6						

3 ϕ Round Wide-directivity LED (Direct Mount)


SEL6014 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating		Condition
		GaAsP/GaP	AlGaInP	
I_F	mA	30		
ΔI_F	mA/°C	-0.45		Above 25°C
I_{FP}	mA	100		f=1kHz, $t_w \leq 100\mu s$
V_R	V	3	4	
Top	°C	-30 to +85		
Tstg	°C	-30 to +100		

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage		Condition	Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		I _F	I _R	Condition	I _V	Condition	λ _P	Condition	Δλ	Condition	
			typ	max	(mA)	(μA)	V _R	(mcd)	I _F	(nm)	I _F	(nm)	I _F	
Red	SEL6214S	Transparent red	1.9	2.5	10	50	3	18	20	630	10	35	10	GaAsP
Amber	SEL6814A	Transparent orange	1.9	2.5	10	50	3	9.0	10	610	10	35	10	
Ultra-high-intensity light amber	SELS6B14C	Clear	2.0	2.5	10	100	4	120	20	600	10	15	10	AlGaInP
	SEL6914A	Transparent orange	1.9	2.5	10	50	3	8.0	10	587	10	33	10	GaAsP
Orange	SEL6914W	Diffused white						5.0						
Yellow	SEL6714K	Transparent yellow	2.0	2.5	10	50	3	66	20	570	10	30	10	GaP
	SEL6714W	Diffused white						30						
Green	SEL6414E	Transparent green	2.0	2.5	10	50	3	42	20	560	10	20	10	
Deep green	SEL6414E-TG	Transparent green						18		558				
Pure green	SEL6514C	Clear	2.0	2.5	10	50	3	12	20	555	10	20	10	

3 ϕ Round Narrow-directivity LED (Direct Mount)


SEL6015 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, tw≤100μs
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition I _F (mA)	I _R (μA)	Condition V _R (V)	I _V (mcd)	Condition I _F (mA)	λP (nm)	Condition I _F (mA)	Δλ (nm)	Condition I _F (mA)	
			(V)											
			typ	max										
Red	SEL6215S	Transparent red	1.9	2.5	10	50	3	45	20	630	10	35	10	GaAsP
Orange	SEL6915A	Transparent orange	1.9	2.5	10	50	3	60	20	587	10	33	10	
Yellow	SEL6715C	Clear	2.0	2.5	10	50	3	90	20	570	10	30	10	
Green	SEL6415E	Transparent green	2.0	2.5	10	50	3	81	20	560	10	20	10	
Pure green	SEL6515C	Clear	2.0	2.5	10	50	3	44	20	555	10	20	10	

3 ϕ Round Standard LED


SEL2010 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating						Condition
		GaP	GaAsP	GaAlAs	AlGaInP	InGaN	GaN	
I _F	mA	30						
ΔI _F	mA/°C	−0.45						Above 25°C
I _{FP}	mA	100					70	f=1kHz, tw≤100μs
V _R	V	3			4	5		
Top	°C	−30 to +85				−25 to +85		
Tstg	°C	−30 to +100						

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F (V)	Condition	I _R	Condition	I _V	Condition	λ _P	Condition	Δλ	Condition		
				I _F (mA)	max	V _R (V)	(mcd)	I _F (mA)	typ	(nm)	I _F (mA)	(nm)	I _F (mA)	
			typ	max						typ		typ		
Deep red	SEL2110S	Transparent red	2.0	2.5	10	50	3	4.0	10	700	10	100	10	GaP
	SEL2110R	Diffused red						1.8						
	SEL2110W	Diffused white						1.8						
High-intensity red	SEL2610C	Clear	1.75	2.2	10	100	3	350	20	660	10	30	10	GaAlAs
Red	SEL2210S	Transparent red	1.9	2.5	10	50	3	40	20	630	10	35	10	GaAsP
	SEL2210R	Diffused red						15						
	SEL2210W	Diffused white						15						
Amber	SEL2810A	Transparent orange	1.9	2.5	10	50	3	22	10	610	10	35	10	GaAsP
	SEL2810D	Diffused orange						9.0						
Orange	SEL2910A	Transparent orange	1.9	2.5	10	50	3	16	10	587	10	33	10	
	SEL2910D	Diffused orange						8.0						
Ultra-high-intensity yellow	SELU2710C	Clear	2.0	2.5	10	100	4	270	20	572	10	15	10	AlGaInP
Yellow	SEL2710K	Transparent yellow	2.0	2.5	10	50	3	40	10	570	10	30	10	GaP
	SEL2710Y	Diffused yellow						14						
Green	SEL2410E	Transparent green	2.0	2.5	10	50	3	77	20	560	20	20	10	
	SEL2410G	Diffused green						20						
Pure green	SEL2510C	Clear	2.0	2.5	10	50	3	43	20	555	10	20	10	
	SEL2510G	Diffused green						8.2						
Ultra-high-intensity pure green	SELU2D10C	Clear	3.3	4.0	20	10	5	1200	20	525	10	35	10	InGaN
Ultra-high-intensity blue	SELU2E10C	Clear						400						
Blue	SEL2E10C	Clear	3.8	4.8	20	10	5	60	20	430	10	65	10	GaN

3 ϕ Round Narrow-directivity LED


SEL2015 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, $t_w \leq 100\mu s$
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material		
			V _F		Condition	I _R	Condition	I _V	Condition	λP	Condition	Δλ	Condition			
			(V)		I _F	(μA)	V _R	(mcd)	I _F	(nm)	I _F	(nm)	I _F			
			typ	max	(mA)	max	(V)	typ	(mA)	typ	(mA)	typ	(mA)			
Red	SEL2215S	Transparent red	1.9	2.5	10	50	3	45	20	630	10	35	10	GaAsP		
	SEL2215R	Diffused red						38								
Amber	SEL2815A	Transparent orange	1.9	2.5	10	50	3	80	10	610	10	35	10		GaAsP	
	SEL2815D	Diffused orange						60								
Orange	SEL2915A	Transparent orange	1.9	2.5	10	50	3	81	10	587	10	33	10			GaP
	SEL2915D	Diffused orange						53								
Yellow	SEL2715K	Transparent yellow	2.0	2.5	10	50	3	130	10	570	10	30	10	GaP		
	SEL2715Y	Diffused yellow						110								
Green	SEL2415E	Transparent green	2.0	2.5	10	50	3	110	20	560	10	20	10		GaP	
	SEL2415G	Diffused green						72								
Pure green	SEL2515C	Clear	2.0	2.5	10	50	3	52	20	555	10	20	10			

3 ϕ Cylindrical LED

SEL2011 Series

External Dimensions

(Unit: mm)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, tw≤100μs
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition I _F (mA)	I _R	Condition V _R (V)	I _V	Condition I _F (mA)	λ _P	Condition I _F (mA)	Δλ	Condition I _F (mA)	
			(V)			(μA)		(mcd)		(nm)		(nm)		
			typ	max	max	typ	typ	typ	typ					
Deep red	SEL2111R	Diffused red	2.0	2.5	10	50	3	0.7	10	700	10	100	10	GaP
Orange	SEL2911D	Diffused orange	1.9	2.5	10	50	3	3.3	10	587	10	33	10	GaAsP
Green	SEL2411G	Diffused green	2.0	2.5	10	50	3	18	20	560	10	20	10	GaP

2 ϕ Round Special-shaped LED

SEL4017 Series

External Dimensions

(Unit: mm)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, tw≤100μs
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition I _F	I _R (μA)	Condition V _R	I _V (mcd)	Condition I _F	λP (nm)	Condition I _F	Δλ (nm)	Condition I _F	
			(V)											
			typ	max	typ	max	typ	max	typ	max	typ	max	typ	
Deep red	SEL4117R	Diffused red	2.0	2.5	10	50	3	1.1	10	700	10	100	10	GaP
Amber	SEL4817D	Diffused orange	1.9	2.5	10	50	3	7.5	10	610	10	35	10	GaAsP
Orange	SEL4917D	Diffused orange	1.9	2.5	10	50	3	7.5	10	587	10	33	10	
Yellow	SEL4717Y	Diffused yellow	2.0	2.5	10	50	3	14	20	570	10	30	10	GaP
Green	SEL4417G	Diffused green	2.0	2.5	10	50	3	16	20	560	10	20	10	

5 ϕ Inverted-cone LED for surface illumination


SEL1013 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, $t_w \leq 100\mu s$
V_R	V	3	
Top	°C	-30 to 85	
Tstg	°C	-30 to 100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F (V)	Condition I _F (mA)	I _R (μA)	Condition V _R (V)	I _V (mcd)	Condition I _F (mA)	λ _P (nm)	Condition I _F (mA)	Δλ (nm)	Condition I _F (mA)		
Red	SEL1213C	Clear	1.9	2.5	10	50	3	7.0	20	630	10	35	10	GaAsP
Amber	SEL1813A	Transparent orange	1.9	2.5	10	50	3	8.0	20	610	10	35	10	
Orange	SEL1913K	Transparent light orange	1.9	2.5	10	50	3	8.0	20	587	10	33	10	
Yellow	SEL1713K	Transparent yellow	2.0	2.5	10	50	3	15	20	570	10	30	10	GaP
Green	SEL1413E	Transparent green	2.0	2.5	10	50	3	12	20	560	10	20	10	
Pure green	SEL1513E	Transparent light green	2.0	2.5	10	50	3	5.0	20	555	10	20	10	

3 ϕ Inverted-cone LED for surface illumination (Direct Mount)


SEL6013 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, $t_w \leq 100\mu s$
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage		Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material	
			V _F (V)	Condition	I _R	Condition	I _V	Condition	λ _P	Condition	Δλ	Condition		
				I _F	(μA)	V _R	(mcd)	I _F	I _F	(nm)	I _F	(nm)		I _F
			typ	max	(mA)	max	(V)	typ	(mA)	typ	(mA)	typ		(mA)
Green	SEL6413E	Transparent green	2.0	2.5	10	50	3	14	20	560	10	20	10	GaP
Pure green	SEL6513C	Clear	2.0	2.5	10	50	3	5.0	20	555	10	20	10	

3 ϕ Inverted-cone LED for surface illumination


SEL2013 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, $t_w \leq 100\mu s$
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)

Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition	I _R	Condition	I _V	Condition	λ _P	Condition	Δλ	Condition	
			(V)		I _F	(μA)	V _R	(mcd)	I _F	(nm)	I _F	(nm)	I _F	
			typ	max	(mA)	max	(V)	typ	(mA)	typ	(mA)	typ	(mA)	
High-intensity red	SEL2613CS-S	Transparent light red	1.7	2.5	10	100	3	80	20	660	10	30	10	GaAlAs
Red	SEL2213C	Clear	1.9	2.5	10	50	3	7.0	20	630	10	35	10	GaAsP
Amber	SEL2813A	Transparent orange	1.9	2.5	10	50	3	8.0	20	610	10	35	10	
Orange	SEL2913K	Transparent light yellow	1.9	2.5	10	50	3	8.0	20	587	10	33	10	
Yellow	SEL2713K	Transparent yellow	2.0	2.5	10	50	3	17	20	570	10	30	10	
Green	SEL2413E	Transparent green	2.0	2.5	10	50	3	14	20	560	10	20	10	GaP
	SEL2413G	Diffused green						12						
Pure green	SEL2513E	Transparent green	2.0	2.5	10	50	3	5.0	20	555	10	20	10	

Lamp Casings Inverted-cone LED for surface illumination

The following three types of standard lamp casings are provided for the area-illuminating LED (SEL1013 Series):


SEL9100 Casing (Illuminating area: 6.5×16.0)

SEL9101 Casing (Illuminating area: 10.0×14.0)


SEL9104 Casing (Illuminating area: 7.0×18.0)

These casings have tabs to assist positioning during printed wiring board mounting.

SEL9100 Lamp Casing




SEL9101 Lamp Casing



●The standard housing is designed to accept an area-illuminating LED press-fit from the rear.●


SEL9104 Lamp Casing




Design examples of reflective surface

(The figures below show design examples of the reflective surface of the housing.)

Example of 7×10 mm




Example of 8×16 mm



3×5 Rectangular LED

SEL1021 Series

External Dimensions (Unit: mm)



Absolute maximum ratings (Ta=25°C)


Symbol	Unit	Rating	Condition
I _F	mA	30	
ΔI _F	mA/°C	−0.45	Above 25°C
I _{FP}	mA	100	f=1kHz, tw≤100μs
V _R	V	3	
Top	°C	−30 to +85	
Tstg	°C	−30 to +100	

Electrical Optical characteristics (Ta=25°C)

Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F (V)	Condition I _F (mA)	I _R (μA)	Condition V _R (V)	I _V (mcd)	Condition I _F (mA)	λ _P (nm)	Condition I _F (mA)	Δλ (nm)	Condition I _F (mA)		
													typ	
Deep red	SEL1121R	Diffused red	2.0	2.5	10	50	3	0.9	10	700	10	100	10	GaP
Amber	SEL1821D	Diffused orange	1.9	2.5	10	50	3	3.0	10	610	10	35	10	GaAsP
Orange	SEL1921D	Diffused orange	1.9	2.5	10	50	3	3.8	10	587	10	33	10	
Yellow	SEL1721Y	Diffused yellow	2.0	2.5	10	50	3	7.0	10	570	10	30	10	GaP
Green	SEL1421G	Diffused green	2.0	2.5	10	50	3	12	20	560	10	20	10	

SEL1022 Series

(Unit: mm)




Symbol	Unit	Rating	Condition
I _F	mA	30	
ΔI _F	mA/°C	−0.45	Above 25°C
I _{FP}	mA	100	f=1kHz, tw≤100μs
V _R	V	3	
Top	°C	−30 to +85	
Tstg	°C	−30 to +100	

Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition	I _R	Condition	I _V	Condition	λ _P	Condition	Δλ	Condition	
			(V)		I _F	(μA)	V _R	(mcd)	I _F	(nm)	I _F	(nm)	I _F	
			typ	max	(mA)	max	(V)	typ	(mA)	typ	(mA)	typ	(mA)	
Red	SEL1222R	Diffused red	1.9	2.5	10	50	3	9.0	20	630	10	35	10	GaAsP
Amber	SEL1822D	Diffused orange	1.9	2.5	10	50	3	4.8	10	610	10	35	10	
Orange	SEL1922D	Diffused orange	1.9	2.5	10	50	3	4.5	10	587	10	33	10	
Yellow	SEL1722Y	Diffused yellow	2.0	2.5	10	50	3	7.8	10	570	10	30	10	GaP
	SEL1722K	Transparent yellow						12						
Green	SEL1422G	Diffused green	2.0	2.5	10	50	3	7.2	20	560	10	20	10	

2×5 Rectangular LED

SEL1020 Series

External Dimensions (Unit: mm)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I _F	mA	30	
ΔI _F	mA/°C	-0.45	Above 25°C
I _{FP}	mA	100	f=1kHz, tw≤100μs
V _R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	


Electrical Optical characteristics (Ta=25°C)

Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F (V)	Condition I _F (mA)	I _R (μA)	Condition V _R (V)	I _V (mcd)	Condition I _F (mA)	λ _P (nm)	Condition I _F (mA)	Δλ (nm)	Condition I _F (mA)		
Deep red	SEL1120R	Diffused red	2.0	2.5	10	50	3	0.9	10	700	10	100	10	GaP
Red	SEL1220R	Diffused red	1.9	2.5	10	50	3	4.8	20	630	10	35	10	GaAsP
Amber	SEL1820D	Diffused orange	1.9	2.5	10	50	3	3.0	10	610	10	35	10	
Orange	SEL1920D	Diffused orange	1.9	2.5	10	50	3	3.8	10	587	10	33	10	
Yellow	SEL1720Y	Diffused yellow	2.0	2.5	10	50	3	7.0	10	570	10	30	10	GaP
Green	SEL1420G	Diffused green	2.0	2.5	10	50	3	11	20	560	10	20	10	

1×5 Rectangular LED

SEL1024 Series

External Dimensions (Unit: mm)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I _F	mA	30	
ΔI _F	mA/°C	-0.45	Above 25°C
I _{FP}	mA	100	f=1kHz, tw≤100μs
V _R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	


Electrical Optical characteristics (Ta=25°C)

Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition I _F	I _R (μA)	Condition V _R	I _V (mcd)	Condition I _F	λ _P (nm)	Condition I _F	Δλ (nm)	Condition I _F	
			(V)											
			typ	max	(mA)		(V)		typ	(mA)	typ	(mA)	typ	
Deep red	SEL1124R	Diffused red	2.0	2.5	10	50	3	0.5	10	700	10	100	10	GaP
Amber	SEL1824D	Diffused orange	1.9	2.5	10	50	3	4.0	10	610	10	35	10	GaAsP
Orange	SEL1924D	Diffused orange	1.9	2.5	10	50	3	3.0	10	587	10	33	10	
Yellow	SEL1724Y	Diffused yellow	2.0	2.5	10	50	3	6.0	10	570	10	30	10	GaP
Green	SEL1424G	Diffused green	2.0	2.5	10	50	3	15	20	560	10	20	10	

2×4 Rectangular LED

SEL4025 Series

External Dimensions (Unit: mm)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, $t_w \leq 100 \mu s$
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	


Electrical Optical characteristics (Ta=25°C)

Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material	
			V _F		Condition	I _R	Condition	I _V	Condition	λ _P	Condition	Δλ	Condition		
			typ	max	I _F (mA)	(μA)	V _R (V)	(mcd)	I _F (mA)	(nm)	I _F (mA)	(nm)	I _F (mA)		
Red	SEL4225C	Clear	1.9	2.5	10	50	3	12	20	630	10	35	10	GaAsP	
	SEL4225R	Diffused red						5.4							
Amber	SEL4825A	Transparent orange	1.9	2.5	10	50	3	5.4	10	610	10	35	10		
	SEL4825D	Diffused orange						4.0							
Orange	SEL4925A	Transparent orange	1.9	2.5	10	50	3	4.5	10	587	10	33	10		
	SEL4925D	Diffused orange						4.0							
Yellow	SEL4725K	Transparent yellow	2.0	2.5	10	50	3	13	10	570	10	30	10		GaP
	SEL4725Y	Diffused yellow						5.0							
Green	SEL4425E	Transparent green	2.0	2.5	10	50	3	20	20	560	10	20	10		
	SEL4425G	Diffused green						10							
Pure green	SEL4525C	Clear	2.0	2.5	10	50	3	6.6	20	555	10	20	10		

2×4 Rectangular LED (Direct Mount)

SEL4026 Series

External Dimensions (Unit: mm)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I _F	mA	30	
ΔI _F	mA/°C	−0.45	Above 25°C
I _{FP}	mA	100	f=1kHz, t _w ≤100μs
V _R	V	3	
Top	°C	−30 to +85	
Tstg	°C	−30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material	
			V _F (V)	Condition I _F (mA)	I _R (μA)	Condition V _R (V)	I _V (mcd)	Condition I _F (mA)	λ _P (nm)	Condition I _F (mA)	Δλ (nm)	Condition I _F (mA)			
													typ		max
Red	SEL4226C	Clear	1.9	2.5	10	50	3	12	20	630	10	35	10	GaAsP	
	SEL4226R	Diffused red						10							
Amber	SEL4826A	Transparent orange	1.9	2.5	10	50	3	5.4	10	610	10	35	10		
	SEL4826D	Diffused orange						4.5							
Orange	SEL4926A	Transparent orange	1.9	2.5	10	50	3	6.0	10	587	10	33	10		
	SEL4926D	Diffused orange						4.5							
Yellow	SEL4726K	Transparent yellow	2.0	2.5	10	50	3	14.0	10	570	10	30	10		GaP
	SEL4726Y	Diffused yellow						8.6							
Green	SEL4426E	Transparent green	2.0	2.5	10	50	3	20	20	560	10	20	10		
	SEL4426G	Diffused green						14							

4 ϕ Bow-shaped LED


SEL4027 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	$f=1\text{kHz}$, $t_w \leq 100\mu\text{s}$
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage		Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material	
			V _F (V)	Condition	I _R	Condition	I _v	Condition	λ _P	Condition	Δλ	Condition		
				I _F	(μA)	V _R	(mcd)	I _F	(nm)	I _F	(nm)	I _F		
			typ	max	(mA)	max	(V)	typ	(mA)	typ	(mA)	typ		(mA)
Red	SEL4227C	Clear	1.9	2.5	10	50	3	15	20	630	10	35	10	GaAsP
Green	SEL4427EP	Transparent green	2.0	2.5	10	50	3	19	20	560	10	20	10	GaP

3.1 ϕ Bow-shaped LED


SEL4028 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, $t_w \leq 100\mu s$
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F (V)	Condition	I _R (μA)	Condition	I _v (mcd)	Condition	λ _P (nm)	Condition	Δλ (nm)	Condition		
				I _F (mA)		V _R (V)		I _F (mA)		I _F (mA)		I _F (mA)		
			typ	max	(mA)	max	(V)	typ	(mA)	typ	(mA)	typ	(mA)	
High-intensity red	SEL4628C-S	Clear	1.7	2.2	10	100	3	200	20	660	10	30	10	GaAlAs
Red	SEL4228C	Clear	1.9	2.5	10	50	3	27	20	630	10	35	10	GaAsP
Amber	SEL4828A	Transparent orange	1.9	2.5	10	50	3	14	10	610	10	35	10	
Orange	SEL4928A	Transparent orange	1.9	2.5	10	50	3	14	10	587	10	33	10	
Yellow	SEL4728K	Transparent yellow	2.0	2.5	10	50	3	30	10	570	10	30	10	GaP
Green	SEL4428E	Transparent green	2.0	2.5	10	50	3	63	20	560	10	20	10	
Deep green	SEL4428B-TG	Transparent dark blue	2.0	2.5	10	50	3	18	20	558	10	20	10	
Pure green	SEL4528C	Clear	2.0	2.5	10	50	3	30	20	555	10	20	10	

3.1 ϕ Bow-shaped LED (Direct Mount)


SEL4029 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	$f=1\text{kHz}$, $t_w \leq 100\mu\text{s}$
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F (V)	Condition I _F (mA)	I _R (μA)	Condition V _R (V)	I _V (mcd)	Condition I _F (mA)	λ _P (nm)	Condition I _F (mA)	Δλ (nm)	Condition I _F (mA)		
													typ	
Red	SEL4229R	Diffused red	1.9	2.5	10	50	3	21	20	630	10	35	10	GaAsP
Amber	SEL4829A	Transparent orange	1.9	2.5	10	50	3	18	10	610	10	35	10	
Orange	SEL4929A	Transparent orange	1.9	2.5	10	50	3	18	10	587	10	33	10	
Yellow	SEL4729KH	Transparent yellow	2.0	2.5	10	50	3	60	10	570	10	30	10	GaP
Green	SEL4429E	Transparent green	2.0	2.5	10	50	3	60	20	560	10	20	10	

4 ϕ Bow-shaped LED (Direct Mount)


SEL6027 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, tw≤100μs
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)

Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition I _F (mA)	I _R (μA) max	Condition V _R (V)	I _V (mcd) typ	Condition I _F (mA)	λ _P (nm) typ	Condition I _F (mA)	Δλ (nm) typ	Condition I _F (mA)	
			typ	max										
Red	SEL6227S	Transparent red	1.9	2.5	10	50	3	14	20	630	10	35	10	GaAsP
Orange	SEL6927A	Transparent orange	1.9	2.5	10	50	3	10	10	587	10	33	10	
Green	SEL6427EP	Transparent green	2.0	2.5	10	50	3	26	20	560	10	20	10	GaP


5-mm Pitch Lead Rectangular LED (Direct Mount)

SEL5020 Series


External Dimensions

(Unit: mm)


(Other than GaAlAs chip)

Tolerance: ± 0.3 

(GaAlAs)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating		Condition
		GaP/GaAsP/GaAlAs	InGaN	
I_F	mA	30		
ΔI_F	mA/°C	-0.45		Above 25°C
I_{FP}	mA	100		$f=1\text{kHz}$, $t_w \leq 100\mu\text{s}$
V_R	V	3	5	
Top	°C	-30 to +85	-25 to +80	
Tstg	°C	-30 to +100		

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F (V)	Condition	I _R	Condition	I _V	Condition	λ _P	Condition	Δλ	Condition		
				I _F	(μA)	V _R	(mcd)	I _F	(nm)	I _F	(nm)	I _F		
			typ	max	(mA)	max	(V)	typ	(mA)	typ	(mA)	typ	(mA)	
High-intensity red	SEL5620C	Clear	1.7	2.2	10	50	3	100	20	660	10	30	10	GaAlAs
Red	SEL5220S	Transparent red	1.9	2.5	10	50	3	20	20	630	10	35	10	GaAsP
Amber	SEL5820A	Transparent orange	1.9	2.5	10	50	3	12	20	610	10	35	10	
Orange	SEL5920A	Transparent orange	1.9	2.5	10	50	3	12	20	587	10	33	10	
Green	SEL5420E	Transparent green	2.0	2.5	10	50	3	20	20	560	10	20	10	GaP
Pure green	SEL5520C	Clear	2.0	2.5	10	50	3	6.0	20	555	10	20	10	
Ultra-high-intensity blue	SELU5E20C	Clear	3.3	4.0	10	10	5	60	10	470	10	35	10	InGaN

5-mm Pitch Lead 3 ϕ Lens-type LED (Direct Mount)


SEL5021 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, tw≤100μs
V_R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition	I _R	Condition	I _V	Condition	λ _P	Condition	Δλ	Condition	
			(V)											
			typ	max	(mA)	max	(V)	typ	(mA)	typ	(mA)	typ	(mA)	
Red	SEL5221S	Transparent red	1.9	2.5	10	50	3	35	20	630	10	35	10	GaAsP
Amber	SEL5821A	Transparent orange	1.9	2.5	10	50	3	60	20	610	10	35	10	
Orange	SEL5921A	Transparent orange	1.9	2.5	10	50	3	60	20	587	10	33	10	
Yellow	SEL5721C	Clear	2.0	2.5	10	50	3	90	20	570	10	30	10	GaP
Green	SEL5421E	Transparent green	2.0	2.5	10	50	3	95	20	560	10	20	10	
Pure green	SEL5521C	Clear	2.0	2.5	10	50	3	35	20	555	10	20	10	

5-mm Pitch Lead Bow-shaped LED (Direct Mount)


SEL5023 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating				Condition
		GaP/GaAsP	AlGaInP	InGaN	GaN	
I _F	mA	30				Above 25°C
ΔI _F	mA/°C	-0.45				
I _{FP}	mA	100			70	f=1kHz, tw≤100μs
V _R	V	3	4	5		
Top	°C	-30 to +85		-25 to +80		
Tstg	°C	-30 to +100				

Electrical Optical characteristics (Ta=25°C)

Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F (V)	Condition I _F (mA)	I _R (μA)	Condition V _R (V)	I _V (mcd)	Condition I _F (mA)	λ _P (nm)	Condition I _F (mA)	Δλ (nm)	Condition I _F (mA)		
Red	SEL5223S	Transparent red	1.9	2.5	10	50	3	25	20	630	10	35	10	GaAsP
Amber	SEL5823A	Transparent orange	1.9	2.5	10	50	3	35	20	610	10	35	10	
Orange	SEL5923A	Transparent orange	1.9	2.5	10	50	3	35	20	587	10	33	10	
Yellow	SEL5723C	Clear	2.0	2.5	10	50	3	60	20	570	10	30	10	GaP
Green	SEL5423E	Transparent green	2.0	2.5	10	50	3	40	20	560	10	20	10	
Pure green	SEL5523C	Clear	2.0	2.5	10	50	3	13	20	555	10	20	10	
Blue	SEL5E23C	Clear	4.0	4.8	10	10	5	20	20	430	10	65	10	GaN

●Ultra-high-intensity series


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F (V)	Condition I _F (mA)	I _R (μA)	Condition V _R (V)	I _V (mcd)	Condition I _F (mA)	λ _P (nm)	Condition I _F (mA)	Δλ (nm)	Condition I _F (mA)		
													typ	
Red	SELS5223C	Clear	2.0	2.5	10	100	4	100	20	635	10	15	10	AlGaInP
Amber	SELS5823C	Clear	2.0	2.5	10	100	4	130	20	615	10	15	10	
Amber	SELU5823C	Clear	2.0	2.5	10	100	4	185	20	615	10	15	10	
Light amber	SELS5B23C	Clear	2.0	2.5	10	100	4	135	20	600	10	15	10	
Orange	SELS5923C	Clear	2.0	2.5	10	100	4	145	20	590	10	15	10	
Yellow	SELU5723C	Clear	2.0	2.5	10	100	4	155	20	572	10	15	10	
Blue	SELU5E23C	Clear	3.6	4.0	10	10	5	110	10	470	10	35	10	InGaIn

5-mm Pitch Lead Egg-shaped LED (Direct Mount)


SEL5055 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)


Symbol	Unit	Rating	Condition
I _F	mA	30	
ΔI _F	mA/°C	-0.45	Above 25°C
I _{FP}	mA	100	f=1kHz, tw≤100μs
V _R	V	3	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)

Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition I _F (mA)	I _R (μA) max	Condition V _R (V)	I _V (mcd) typ	Condition I _F (mA)	λ _P (nm) typ	Condition I _F (mA)	Δλ (nm) typ	Condition I _F (mA)	
			V _F (V)											
			typ	max										
Red	SEL5255S	Transparent red	1.9	2.5	10	50	3	35	20	630	10	35	10	GaAsP
Orange	SEL5955A	Transparent orange	1.9	2.5	10	50	3	25	20	587	10	33	10	
Yellow	SEL5755C	Clear	2.0	2.5	10	50	3	140	20	570	10	30	10	GaP

SML1016/10016 Series

(Unit: mm)



Symbol	Unit	Rating	Condition
I _F	mA	30	
ΔI _F	mA/°C	−0.45	Above 25°C
I _{FP}	mA	100	f=1kHz, t _w ≤100μs
V _R	V	4	
Top	°C	−30 to +85	
Tstg	°C	−30 to +100	

●Common cathode (Internal wiring diagram 1)

Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition	I _R	Condition	I _V	Condition	λ _P	Condition	Δλ	Condition	
			(V)		I _F	(μA)	V _R	(mcd)	I _F	(nm)	I _F	(nm)	I _F	
			typ	max	(mA)	max	(V)	typ	(mA)	typ	(mA)	typ	(mA)	
A Deep red	SML11516C	Clear	2.0	2.5	10	10	4	15	20	700	10	100	10	GaP
B Pure green			2.0	2.5	10	10	4	50	20	555	10	20	10	GaP
A Deep red	SML1516W	Diffused white	2.0	2.5	10	10	4	6.0	20	700	10	100	10	GaP
B Pure green			2.0	2.5	10	10	4	20	20	555	10	20	10	GaP
A Red	SML1216C	Clear	1.9	2.5	10	10	4	65	20	630	10	35	10	GaAsP
B Green			2.0	2.5	10	10	4	90	20	560	10	20	10	GaP
A Red	SML1216W	Diffused white	1.9	2.5	10	10	4	60	20	630	10	35	10	GaAsP
B Green			2.0	2.5	10	10	4	60	20	560	10	20	10	GaP
A Amber	SML1816W	Diffused white	1.9	2.5	10	10	4	50	20	610	10	35	10	GaAsP
B Green			2.0	2.5	10	10	4	60	20	560	10	20	10	GaP
A Orange	SML19416W	Diffused white	1.9	2.5	10	10	4	45	20	587	10	33	10	GaAsP
B Green			2.0	2.5	10	10	4	60	20	560	10	20	10	GaP


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition	I _R	Condition	I _V	Condition	λ _P	Condition	Δλ	Condition	
			(V)		I _F	(μA)	V _R	(mcd)	I _F	(nm)	I _F	(nm)	I _F	
			typ	max	(mA)	max	(V)	typ	(mA)	typ	(mA)	typ	(mA)	
A High-intensity red	SML16716CN	Clear	1.7	2.2	10	10	4	100	20	660	10	30	10	GaAlAs
B Yellow			2.4	3.0	10	10	4	140	20	570	10	30	10	GaP
A High-intensity red	SML16716WN	Diffused white	1.7	2.2	10	10	4	50	20	660	10	30	10	GaAlAs
B Yellow			2.4	3.0	10	10	4	70	20	570	10	30	10	GaP

5 ϕ Round Bicolor LED


SML10051 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, $t_w \leq 100\mu s$
V_R	V	4	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)

●Common cathode (Internal wiring diagram 1)

Emitting color	Part Number	Lens color	Forward voltage		Condition	Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F			I _R	Condition	I _V	Condition	λ _P	Condition	Δλ	Condition	
			(V)	I _F	(μA)	V _R		(mcd)		I _F		(nm)		
			typ	max	(mA)	max	(V)	typ	(mA)	typ	(mA)	typ	(mA)	
A Red	SML12451W	Diffused white	1.9	2.5	10	10	4	40	20	630	10	35	10	GaAsP
B Green			2.0	2.5	10	10	4	60	20	560	10	20	10	GaP

●Common anode (Internal wiring diagram 2)


Emitting color	Part Number	Lens color	Forward voltage		Condition	Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		I _F	I _R	Condition	I _V	Condition	λ _P	Condition	Δλ	Condition	
			(V)	(mA)		(μA)		V _R		(mcd)		I _F		
			typ	max		max	(V)	typ	(mA)	typ	(mA)	typ	(mA)	
A High-intensity red	SML16751WN	Diffused white	1.7	2.2	10	10	4	50	20	660	10	30	10	GaAlAs
B Yellow			2.4	3.0	10	10	4	60	20	570	10	30	10	GaP

2.5×5 Rectangular Bicolor LED


SML10060 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, $t_w \leq 100\mu s$
V_R	V	4	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)

●Common cathode (Internal wiring diagram 1)

Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition I _F (mA)	I _R (μA)	Condition V _R (V)	I _V (mcd)	Condition I _F (mA)	λP (nm)	Condition I _F (mA)	Δλ (nm)	Condition I _F (mA)	
			typ	max		max		typ		typ		typ		
A Red	SML12460C	Clear	1.9	2.5	10	10	4	10	20	630	10	35	10	GaAsP
B Green			2.0	2.5	10	10	4	25	20	560	10	20	10	GaP
A Orange	SML19460C	Clear	1.9	2.5	10	10	4	15	20	587	10	35	10	GaAsP
B Green			2.0	2.5	10	10	4	25	20	560	10	20	10	GaP

●Common anode (Internal wiring diagram 2)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition	I _R	Condition	I _V	Condition	λ _P	Condition	Δλ	Condition	
			(V)											
			typ	max	(mA)	max	(V)	typ	(mA)	typ	(mA)	typ	(mA)	
A High-intensity red	SML16760CN	Clear	1.7	2.2	10	10	4	30	20	660	10	30	10	GaAlAs
B Yellow			2.4	3.0	10	10	4	40	20	570	10	30	10	GaP

3.3×6 Rectangular Bicolor LED (Direct Mount)


SML70020 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, $t_w \leq 100\mu s$
V_R	V	4	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)

●Common cathode


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition I _F (mA)	I _R	Condition V _R (V)	I _V	Condition I _F (mA)	λ _P	Condition I _F (mA)	Δλ	Condition I _F (mA)	
			(V)			(μA)		(mcd)		(nm)		(nm)		
			typ	max	max	typ	typ	typ	typ					
A Red	SML72420C	Clear	1.9	2.5	10	10	4	15	20	630	10	35	10	GaAsP
B Green			2.0	2.5	10	10	4	20	20	560	10	20	10	GaP
A Amber	SML78420C	Clear	1.9	2.5	10	10	4	10	20	610	10	35	10	GaAsP
B Green			2.0	2.5	10	10	4	20	20	560	10	20	10	GaP
A Orange	SML79420C	Clear	1.9	2.5	10	10	4	10	20	587	10	33	10	GaAsP
B Green			2.0	2.5	10	10	4	20	20	560	10	20	10	GaP

3.3×6 Bow-shaped Bicolor LED (Direct Mount)


SML70023 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, tw≤100μs
V_R	V	4	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)

●Common cathode


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition	I _R	Condition	I _V	Condition	λ _P	Condition	Δλ	Condition	
			typ	max	I _F (mA)	(μA) max	V _R (V)	(mcd) typ	I _F (mA)	(nm) typ	I _F (mA)	(nm) typ	I _F (mA)	
A Red	SML72423C	Clear	1.9	2.5	10	10	4	25	20	630	10	35	10	GaAsP
B Green			2.0	2.5	10	10	4	35	20	560	10	20	10	GaP
A Red	SML72923C	Clear	1.9	2.5	10	10	4	25	20	630	10	35	10	GaAsP
B Orange			1.9	2.5	10	10	4	25	20	587	10	33	10	GaAsP
A Amber	SML78423C	Clear	1.9	2.5	10	10	4	25	20	610	10	35	10	GaAsP
B Green			2.0	2.5	10	10	4	35	20	560	10	20	10	GaP
A Ultra-high-intensity orange	SMLS79723C	Clear	2.0	2.5	10	100	4	150	20	590	10	15	10	AlGaInP
B Yellow			2.0	2.5	10	10	4	40	20	570	10	30	10	GaP
A Orange	SML79423C	Clear	1.9	2.5	10	10	4	25	20	587	10	33	10	GaAsP
B Green			2.0	2.5	10	10	4	35	20	560	10	20	10	GaP

Egg-shaped Bicolor LED (Direct Mount)


SML70055 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	100	f=1kHz, $t_w \leq 100\mu s$
V_R	V	4	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)

●Common cathode (Internal wiring diagram 1)

Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition	I _R	Condition	I _V	Condition	λ _P	Condition	Δλ	Condition	
			typ	max	I _F (mA)	(μA)	V _R (V)	(mcd)	I _F (mA)	typ	(nm)	I _F (mA)	(nm)	
A Ultra-high-intensity red	SMLU72755C	Clear	2.0	2.5	10	10	4	160	20	635	10	15	10	AlGaInP
B Ultra-high-intensity yellow			2.0	2.5	10	10	4	170	20	572	10	15	10	AlGaInP
A Red	SML72755C	Clear	1.9	2.5	10	10	4	45	20	630	10	35	10	GaAsP
B Yellow			2.0	2.5	10	10	4	75	20	570	10	30	10	GaP
A Ultra-high-intensity amber	SMLU78755C	Clear	2.0	2.5	10	10	4	280	20	615	10	15	10	AlGaInP
B Ultra-high-intensity yellow			2.0	2.5	10	10	4	170	20	572	10	15	10	AlGaInP
A Orange	SML79255C	Clear	1.9	2.5	10	10	4	40	20	587	10	33	10	GaAsP
B Red			2.0	2.5	10	10	4	45	20	630	10	35	10	GaAsP
A Orange	SML79455C	Clear	1.9	2.5	10	10	4	45	20	587	10	33	10	GaAsP
B Green			2.0	2.5	10	10	4	75	20	560	10	20	10	GaP

●Common anode (Internal wiring diagram 2)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition I _F (mA)	I _R (μA)	Condition V _R (V)	I _v (mcd)	Condition I _F (mA)	λ _P (nm)	Condition I _F (mA)	Δλ (nm)	Condition I _F (mA)	
			typ	max										
A High-intensity red	SML76755WN	Diffused white	1.7	2.2	10	10	4	50	20	660	10	30	10	GaAlAs
B Yellow			2.4	3.0	10	10	4	50	20	570	10	30	10	GaP

3×1.5 Surface Mount LED (Flat Lens)


SEC1001 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating		Condition
		GaP/GaAsP/GaAlAs	GaN/InGaN	
I _F	mA	30		
ΔI _F	mA/°C	-0.45		Above 25°C
I _{FP}	mA	70		f=1kHz, tw≤100μs
V _R	V	4	5	
Top	°C	-30 to +85	-25 to +80	
Tstg	°C	-30 to +100		

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition I _F (mA)	I _R	Condition V _R (V)	I _V	Condition I _F (mA)	λ _P	Condition I _F	Δλ	Condition I _F	
			typ	max		(μA)		(mcd)		(nm)		(nm)		
Deep red	SEC1101C	Clear	2.0	2.5	10	100	4	1.5	20	700	10	100	10	GaP
High-intensity red	SEC1601C	Clear	1.7	2.2	10	100	4	100	20	660	10	30	10	GaAlAs
Red	SEC1201C	Clear	1.9	2.5	10	100	4	10	20	630	10	35	10	GaAsP
Amber	SEC1801C	Clear	1.9	2.5	10	100	4	16	20	610	10	35	10	
Orange	SEC1901C	Clear	1.9	2.5	10	100	4	13	20	587	10	33	10	
Yellow	SEC1701C-YG	Clear	2.0	2.5	10	100	4	25	20	570	10	30	10	GaP
Green	SEC1401C	Clear	2.0	2.5	10	100	4	22	20	560	10	20	10	
Deep green	SEC1401E-TG	Transparent green	2.0	2.5	10	100	4	11	20	558	10	20	10	
Pure green	SEC1501C	Clear	2.0	2.5	10	100	4	8.0	20	555	10	20	10	InGaN
Ultra-high-intensity pure green	SECU1D01C	Clear	3.3	4.0	20	10	5	150	20	525	20	35	20	
Ultra-high-intensity blue	SECU1E01C	Clear	3.3	4.0	20	10	5	50	20	470	20	35	20	
Blue	SEC1E01C	Clear	3.9	4.8	20	10	5	6.0	20	430	20	65	20	GaN

3×1.5 Surface Mount LED (Inner Lens)


SEC1003 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	70	$f=1\text{kHz}$, $t_w \leq 100\mu\text{s}$
V_R	V	4	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition I _F (mA)	I _R (μA)	Condition V _R (V)	I _V (mcd)	Condition I _F (mA)	λ _P (nm)	Condition I _F (mA)	Δλ (nm)	Condition I _F (mA)	
			typ	max										
High-intensity red	SEC1603C	Clear	1.7	2.2	10	100	4	150	20	660	10	30	10	GaAlAs
Ultra-high-intensity red	SECS1203C	Clear	1.9	2.5	20	100	4	100	20	635	20	35	20	AlGaInP
Red	SEC1203C	Clear	1.9	2.5	10	100	4	15	20	630	10	35	10	GaAsP
Ultra-high-intensity amber	SECS1803C	Clear	1.9	2.5	3	10	4	10	3	615	3	35	3	AlGaInP
Amber	SEC1803C	Clear	1.9	2.5	10	100	4	20	20	610	10	35	10	GaAsP
Ultra-high-intensity orange	SECS1903C	Clear	1.9	2.5	3	10	4	10	3	590	3	35	3	AlGaInP
Orange	SEC1903C	Clear	1.9	2.5	10	100	4	15	20	587	10	33	10	GaAsP
Yellow	SEC1703C	Clear	2.0	2.5	10	100	4	35	20	570	10	30	10	GaP
Green	SEC1403C	Clear	2.0	2.5	10	100	4	33	20	560	10	20	10	
Deep green	SEC1403E-TG	Transparent green	2.0	2.5	10	100	4	15	20	558	10	20	10	
Pure green	SEC1503C	Clear	2.0	2.5	10	100	4	10	20	555	10	20	10	

3×2.5 Bicolor Surface Mount LED (Flat Lens)


SEC2002 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	70	f=1kHz, $t_w \leq 100\mu s$
V_R	V	4	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F (V)	Condition I _F (mA)	I _R (μA) max	Condition V _R (V)	I _V (mcd) typ	Condition I _F (mA)	λ _P (nm) typ	Condition I _F (mA)	Δλ (nm) typ	Condition I _F (mA)		
													typ	
A Yellow	SEC2762C-YG	Clear	2.0	2.5	10	100	4	20	20	570	10	30	10	GaP
B High-intensity red			1.7	2.2	10	100	4	20	20	660	10	30	10	GaAlAs
A Green	SEC2462C	Clear	2.0	2.5	10	100	4	20	20	560	10	20	10	GaP
B High-intensity red			1.7	2.2	10	100	4	20	20	660	10	30	10	GaAlAs
A Green	SEC2422C	Clear	2.0	2.5	10	100	4	20	20	560	10	20	10	GaP
B Red			1.9	2.5	10	100	4	10	20	630	10	35	10	GaAsP
A Green	SEC2492C	Clear	2.0	2.5	10	100	4	20	20	560	10	20	10	GaP
B Orange			1.9	2.5	10	100	4	10	20	587	10	33	10	GaAsP
A Pure green	SEC2592C	Clear	2.0	2.5	10	100	4	5.0	20	555	10	20	10	GaP
B Orange			1.9	2.5	10	100	4	10	20	587	10	33	10	GaAsP
A Green	SEC2442C	Clear	2.0	2.5	10	100	4	20	20	560	10	20	10	GaP
B Green			2.0	2.5	10	100	4	20	20	560	10	20	10	GaP
A Pure green	SEC2552C	Clear	2.0	2.5	10	100	4	5.0	20	555	10	20	10	GaP
B Pure green			2.0	2.5	10	100	4	5.0	20	555	10	20	10	GaP

3×2.5 Bicolor Surface Mount LED (Inner Lens)


SEC2004 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I_F	mA	30	
ΔI_F	mA/°C	-0.45	Above 25°C
I_{FP}	mA	70	f=1kHz, $t_w \leq 100\mu s$
V_R	V	4	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Emitting color	Part Number	Lens color	Forward voltage			Reverse current		Intensity		Peak wavelength		Spectrum half width		Chip material
			V _F		Condition I _F (mA)	I _R (μA)	Condition V _R (V)	I _V (mcd)	Condition I _F (mA)	λ _P (nm)	Condition I _F (mA)	Δλ (nm)	Condition I _F (mA)	
			typ	max										
A Yellow	SEC2764C	Clear	2.0	2.5	10	100	4	50	20	570	10	30	10	GaP
B High-intensity red			1.7	2.2	10	100	4	50	20	660	10	30	10	GaAlAs
A Green	SEC2484C	Clear	2.0	2.5	10	100	4	30	20	560	10	20	10	GaP
B Amber			1.9	2.5	10	100	4	20	20	610	10	35	10	GaAsP
A Green	SEC2494C	Clear	2.0	2.5	10	100	4	30	20	560	10	20	10	GaP
B Orange			1.9	2.5	10	100	4	20	20	587	10	33	10	GaAsP
A Yellow	SEC2774C	Clear	2.0	2.5	10	100	4	50	20	570	10	30	10	GaP
B Yellow			2.0	2.5	10	100	4	50	20	570	10	30	10	GaP
A Pure green	SEC2554C	Clear	2.0	2.5	10	100	4	10	20	555	10	20	10	GaP
B Pure green			2.0	2.5	10	100	4	10	20	555	10	20	10	GaP

5 ϕ Round Infrared LED


SID1010M Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I _F	mA	150	
ΔI _F	mA/°C	-1.33	Above 25°C
I _{FP}	mA	1000	f=1kHz, tw≤10μs
V _R	V	5	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)


Part Number	Lens color	Forward voltage		Reverse current		Optical Power		Peak wavelength		Spectrum half width		Chip material	Dimension A (mm)	
		V _F		Condition I _F (mA)	I _R (μA)	Condition V _R (V)	I _e (mW/sr)	Condition λ _P (nm)	Condition I _F (mA)	Δλ (nm)	Condition I _F (mA)			
		typ	max		max		typ							typ
SID1010CM	Clear	1.3	1.5	50	10	5	130	(Constant voltage) V _{CC} =3V R=2.2Ω	940	50	50	50	GaAs	7.6 ±0.2
SID1K10CM	Clear	1.3	1.5	50	10	5	200		940	50	50	50		
SID1010CXM	Clear	1.3	1.5	50	10	5	60		940	50	50	50		6.9 ±0.2
SID1K10CXM	Clear	1.3	1.5	50	10	5	110		940	50	50	50		

5 ϕ Round Infrared LED (Direct Mount)


SID1050M Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)


Symbol	Unit	Rating	Condition
I_F	mA	150	
ΔI_F	mA/°C	-1.33	Above 25°C
I_{FP}	mA	1000	$f=1\text{kHz}$, $t_w \leq 10\mu\text{s}$
V_R	V	5	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	

Electrical Optical characteristics (Ta=25°C)

Part Number	Lens color	Forward voltage		Reverse current		Optical Power		Peak wavelength		Spectrum half width		Chip material	
		V _F (V)	Condition I _F (mA)	I _R (μA)	Condition V _R (V)	I _e (mW/sr)	Condition	λ _P (nm)	Condition I _F (mA)	Δλ (nm)	Condition I _F (mA)		
													typ
SID1050CM	Clear	1.3	1.5	50	10	5	250	(Constant voltage) V _{CC} =3V, R=2.2Ω	940	50	50	50	GaAs

SID300/1003 Series

(Unit: mm)



The figure displays three polar plots, each representing the radiation pattern of a different antenna model. Each plot is a semi-circle with a radial scale from 0 to 100% and an angular scale from 0° to 90° on both sides. The plots show a main lobe centered at 0° and side lobes at 30° and 60°.

- SID303C:** The main lobe reaches 100% at 0°. The side lobes at 30° and 60° are significantly lower, with the 60° lobe being the lowest.
- SID313BP / SID1003BQ:** The main lobe reaches 100% at 0°. The side lobes at 30° and 60° are higher than in the SID303C plot, with the 60° lobe being the lowest.
- SID307BR / SID1G307C:** The main lobe reaches 100% at 0°. The side lobes at 30° and 60° are the highest among the three, with the 60° lobe being the lowest.

Symbol	Unit	Rating	Condition
I _F	mA	150	
ΔI _F	mA/°C	−1.33	Above 25°C
I _{FP}	mA	1000	f=1kHz, tw≤10μs
V _R	V	5	
Top	°C	−30 to +85	
Tstg	°C	−30 to +100	


Part Number	Lens color	Forward voltage			Reverse current		Optical Power		Peak wavelength		Spectrum half width		Chip material	Dimension A (mm)
		V _F		Condition I _F (mA)	I _R	Condition V _R (V)	I _e	Condition (mW/sr)	λP	Condition I _F (mA)	Δλ	Condition I _F (mA)		
		(V)			(μA)		(nm)		(nm)					
		typ	max		max		typ		typ		typ			
SID303C	Clear	1.3	1.5	50	10	5	80	(Constant voltage) V _{CC} =3V R=2.2Ω I _F =50mA	940	50	50	50	GaAs	3.0 ^{±0.5}
SID313BP	Transparent light purple	1.3	1.5	50	10	5	130		940	50	50	50		3.6 ^{±0.5}
SID1003BQ	Transparent light navy blue	1.3	1.5	50	10	5	180		940	50	50	50		4.2 ^{±0.5}
SID307BR	Transparent dark navy blue	1.3	1.5	50	10	5	200		940	50	50	50		
SID1G307C	Clear	1.5	1.8	50	10	5	50		850	50	40	50		

3 ϕ Round Infrared LED


SID2010 Series

External Dimensions

(Unit: mm)



Directivity (Typical)



Absolute maximum ratings (Ta=25°C)

Symbol	Unit	Rating	Condition
I _F	mA	150	
ΔI _F	mA/°C	-1.33	Above 25°C
I _{FP}	mA	1000	f=1kHz, tw≤10μs
V _R	V	5	
Top	°C	-30 to +85	
Tstg	°C	-30 to +100	


Electrical Optical characteristics (Ta=25°C)

Part Number	Lens color	Forward voltage		Reverse current		Optical Power		Peak wavelength		Spectrum half width		Chip material	
		V _F		Condition I _F	I _R	Condition V _R	I _e	Condition	λP	Condition I _F	Δλ		Condition I _F
		(V)	(mA)		(μA)		(V)		(mW/sr)		(nm)		
		typ	max		max		typ		typ	(mA)	typ	(mA)	
SID2010C	Clear	1.3	1.5	50	10	5	7.0	I _F =50mA	940	50	50	50	GaAs
SID2K10C	Clear	1.3	1.5	50	10	5	14	I _F =50mA	940	50	50	50	

Characteristic Curves


Spectral distribution

●Standard type



	Light color	Chip material	Peak Wavelength(nm)
①	Blue	GaN	430
②	Pure green	GaP	555
③	Green/deep green	GaP	560/558
④	Yellow	GaP	570
⑤	Orange	GaAsP	587
⑥	Amber	GaAsP	610
⑦	Red	GaAsP	630
⑧	High-intensity red	GaAlAs	660
⑨	Deep red	GaP	700







●Ultra-high-intensity type









	Light color	Chip material	Peak Wavelength(nm)
①	Ultra-high-intensity blue	InGaN	470
②	Ultra-high-intensity pure green	InGaN	525
③	Ultra-high-intensity yellow	AlGaInP	572
④	Ultra-high-intensity orange	AlGaInP	590
⑤	Ultra-high-intensity light amber	AlGaInP	600
⑥	Ultra-high-intensity amber	AlGaInP	615
⑦	Ultra-high-intensity red	AlGaInP	635

Characteristic Curves

■ IF - VF characteristic










■ Relative intensity - IF characteristic



Characteristic Curves

■ Infrared LED




Taping Specifications

Lamp Types

1. Straight type

2. Forming (5 mm pitch) type



Taping shape (unit: mm)




Taping compatibility table

Series name Taping No.⇒ H1 or H0 dimension⇒	Forming (5 mm pitch) type							Straight type						With holder*			Package contents	Page
	TP1	TP2	TP3	TP6	TP7	TP8	TP19	TP4	TP5	TP15	TP16	TP17	TP18	TH8F	TH10D	TH12E		
	4.5	7.5	6.0	3.5	5.0	9.0	7.4	17.0	20.5	20.5	19.0	23.5	25.0					
SEL1010		○	○		○	○											2500	10
SEL1010M	○	○	○	○	○	○											2500	11
SEL1010XM	○	○	○	○	○	○											2500	12
SEL1050M	○	○	○	○	○	○			○								2500	13
SEL1015		○	○		○	○											2500	14
SEL1011		○	○		○	○											2500	15
SEL1053M																	2500	16
SEL4010		○	○		○	○											3000	17
SEL4014	○	○	○	○	○	○			○								3000	18
SEL6010	Use SEL2010								○						○	○	4000	19
SEL6014		○	○		○	○			○								4000	20
SEL6015	Use SEL2015								○								4000	21
SEL2010	○	○	○	○	○	○											4000	22
SEL2015	○	○	○	○	○	○											4000	23
SEL2011	○	○	○	○	○	○											4000	24
SEL4017	○	○	○	○	○	○											4000	25
SEL1013		○	○		○	○											2500	26
SEL6013	Use SEL2013								○								4000	27
SEL2013	○	○	○	○	○	○											4000	28
SEL1021		○	○		○	○											2500	30
SEL1022		○	○		○	○											2500	31
SEL1020		○	○		○	○											3000	32
SEL1024		○	○		○	○											3000	33
SEL4025	○	○	○	○	○	○											6000	34
SEL4026	○	○	○	○	○	○		○									6000	35
SEL4027	○	○	○	○	○	○											6000	36
SEL4028	○	○	○	○	○	○											6000	37
SEL4029	○	○	○	○	○	○											6000	38
SEL6027	Use SEL4027								○								6000	39
SEL5020										○				○			4000	40
SEL5021										○							4000	41
SEL5023										○							4000	42
SEL5055										○							4000	43
SML1016/10016								○									2500	44
SML10051								○									2500	45
SML10060								○									6000	46
SML70020										○							4000	47
SML70023										○							4000	48
SML70055										○							3000	49
SID1010	○	○	○	○	○	○											2500	54
SID1050	○	○	○	○	○	○			○								2500	55
SID300/1003											○	○	○				2000	56
SID2010																	3000	57

* The package contents for taping with holder are 1200.

Taping with holder

- This taping format saves the customer the trouble of attaching a holder.
- Any available inserter can be used with the 5 mm lead pitch radial taping.




Unit: mm


Taping Specifications

Chip type


Single-color SEC1001/1003 Series



Bicolor SEC2002/2004 Series



Reel specifications



General tolerance: ± 0.2

Package contents: 3000

List of Discontinued Products

Part Number	Substitute
SEL1112R	SEL4117R
SEL1120RKT	SEL1120R
SEL1123R	SEL1124R
SEL1131R	–
SEL1132R	–
SEL1134R	–
SEL1142R	–
SEL1213CM	SEL1213C
SEL1215R	–
SEL1310E	SEL1410E
SEL1310G	SEL1410G
SEL1311G	SEL1411G
SEL1312G	SEL4417G
SEL1320G	SEL1420G
SEL1321G	SEL1421G
SEL1323G	SEL1424G
SEL1324G	SEL1424G
SEL1331G	–
SEL1332G	–
SEL1334G	–
SEL1342G	–
SEL1420GW	–
SEL152R	–
SEL1650CM	–
SEL1723Y	SEL1724Y
SEL1731Y	–
SEL1742Y	–
SEL1820W	–
SEL1823D	SEL1824D
SEL1842D	–
SEL1915C	–
SEL1923D	SEL1924D
SEL1942D	–
SEL1E10CM	SELU1E10CXM/SELU1E50CM
SEL2111W	–
SEL2111W	–
SEL2215RM	SEL2215R
SEL2310E	SEL2410E
SEL2310G	SEL2410G
SEL2311G	SEL2411G
SEL2710E	–
SEL2915DM	SEL2915D
SEL3110R	SEL2110R/SEL6210R
SEL3110S	SEL2110S/SEL6210S
SEL3210R	SEL2210R/SEL6210R
SEL3210S	SEL2210S/SEL6210S
SEL3213C	SEL2213C
SEL3410E	SEL2410E/SEL6410E
SEL3410G	SEL2410G
SEL3413E	SEL2413E

Part Number	Substitute
SEL3510C	SEL2510C/SEL6510C
SEL3510G	SEL2510G/SEL6510G
SEL352G	–
SEL3710K	SEL2710K/SEL6710K
SEL3710Y	SEL2710Y/SEL6710Y
SEL3713K	SEL2713K
SEL3810A	SEL2910A/SEL6810A
SEL3810D	SEL2910D/SEL6810D
SEL3813A	SEL2813A
SEL3910A	SEL2910A/SEL6910A
SEL3910D	SEL2910D/SEL6910D
SEL3913K	SEL2913K
SEL3E10C	SELU2E10C
SEL4110RT	SEL4110R
SEL4210RT	SEL4210R
SEL4225RM	SEL4225R
SEL4310E	SEL4410E
SEL4310G	SEL4410G
SEL4425GM	SEL4425G
SEL4427E	SEL4427EP
SEL4725CM	–
SEL4814W	–
SEL550ST	–
SEL650ST	–
SEL8301A	–
SEL8302A	–
SEL8701Y	–
SEL8701YB	–
SID1010BXM	–
SID1010CM2	–
SID1H10CXM	–
SID1K10CM2	–
SID1K10CM2	–
SLH30	–
SLH50	–
SLS34	–
SLS36	–
SLS54	–



Sanken Electric Co.,Ltd.

1-11-1 Nishi -Ikebukuro,Toshima-ku, Tokyo

PHONE: 03-3986-6164

FAX: 03-3986-8637

TELEX: 0272-2323(SANKEN J)

Overseas Sales Offices

●Asia

Sanken Electric Singapore Pte.Ltd.

150 Beach Road,#14-03 The Gateway West,
Singapore 0718

PHONE: 291-4755

FAX: 297-1744

Sanken Electric Hong Kong Co.,Ltd.

1018 Ocean Centre, Canton Road,
Kowloon, Hong Kong

PHONE: 2735-5262

FAX: 2735-5494

TELEX: 45498 (SANKEN HX)

Sanken Electric Korea Co.,Ltd.

SK Life B/D 6F,

168 Kongduk-dong, Mapo-ku, Seoul, 121-705, Korea

PHONE: 82-2-714-3700

FAX: 82-2-3272-2145

●North America

Allegro MicroSystems,Inc.

115 Northeast Cutoff, Box 15036

Worcester, Massachusetts 01615, U.S.A.

PHONE: (508)853-5000

FAX: (508)853-7861

●Europe

Allegro MicroSystems Europe Limited.

Balfour House, Churchfield Road,

Walton-on-Thames, Surrey KT12 2TD, U.K.

PHONE: 01932-253355

FAX: 01932-246622