

FEATURES

- Low dropout performance,
1.2V max. for EZ1086A,
1.3V max. for EZ1086
- Full current rating over line and temperature
- Fast transient response
- $\pm 2\%$ Total output regulation over line, load
and temperature
- Adjust pin current max $90\mu\text{A}$ over temperature
- Fixed/adjustable output voltage
- Line regulation typically 0.015%
- Load regulation typically 0.05%
- TO-220 or TO-263 packages

DESCRIPTION

The EZ1086 Series are high performance positive voltage regulators designed for use in applications requiring low dropout performance at full rated current. Additionally, the EZ1086 Series provides excellent regulation over variations due to changes in line, load and temperature. Outstanding features include low dropout performance at rated current, fast transient response, internal current limiting and thermal shutdown protection of the output device. The EZ1086 Series are three terminal regulators with fixed and adjustable voltage options available in popular packages.

DEVICE SELECTION GUIDE


DEVICE	V _{OUT} VOLTS	PACKAGE
EZ1086ACM	1.30 to 4.0	TO-263
EZ1086CM	1.30 to 4.0	
EZ1086CM-3.3	3.3	
EZ1086CM-3.45	3.45	
EZ1086ACT	1.30 to 4.0	TO-220
EZ1086CT	1.30 to 4.0	
EZ1086CT-3.3	3.3	
EZ1086CT-3.45	3.45	

NOTE: Contact factory for additional voltage options.

ABSOLUTE MAXIMUM RATINGS

Parameter	Symbol	Maximum	Units
Input Voltage	V _{IN}	7	V
Power Dissipation	P _D	Internally Limited	W
Thermal Resistance Junction to Case TO-220 TO-263	θ_{JC}	3 3	°C/W
Thermal Resistance Junction to Ambient TO-220 TO-263	θ_{JA}	50 60	
Operating Junction Temperature Range	T _J	0 to 125	
Storage Temperature Range	T _{STG}	-65 to 150	°C
Lead Temperature (Soldering) 10 Sec.	T _{LEAD}	260	

BLOCK DIAGRAM



ELECTRICAL CHARACTERISTICS

Unless otherwise specified, Adj $V_{IN} = 2.75V$ to $7.0V$ and Adj $I_O = 10mA$ to $1.5A$;
Fixed $V_{IN} = 4.75V$ to $7.0V$ and Fixed $I_O = 0mA$ to $1.5A$

		Test Conditions			Test Limits				
PARAMETER	SYMBOL	V _{IN}	I _O	T _J (⁴)	MIN	TYP	MAX	UNITS	
Output Voltage(¹) Fixed Voltage	V _O	5V	0mA	25	0.99 V _O	V _O	1.01 V _O	V	
				Over Temp.	0.98 V _O		1.02 V _O		
Reference Voltage(¹) Adj Voltage	V _{REF}	5V	10mA	25	1.238	1.250	1.262		
				Over Temp.	1.225		1.275		
Line Regulation(¹)	REG _(LINE)		10mA	25		0.015	0.2	%	
				Over Temp.		0.035			
Load Regulation(¹)	REG _(LOAD)	5V		25		0.05	0.3		
				Over Temp.		0.2	0.4		
Dropout Voltage ΔV _{OUT} , ΔV _{REF} = 1% EZ1086A EZ1086	V _D			25		1		V	
				Over Temp.		1.0 1.1	1.2 1.3		
Current Limit	I _{CL}					1.5	2		A
Quiescent Current Fixed Model	I _Q	5V					12	14	mA
Temperature Coefficient	T _C						0.005		%/°C
Adjust Pin Current	I _{ADJ}			25		55		μA	
Adjust Pin Current Change	ΔI _{ADJ}			Over Temp.			90		
							0.2	5	
Temperature Stability	T _S	5V	500mA				0.5		%
Minimum Load Current Adj Model	I _O	5V					5	10	mA
RMS Output Noise(²)	V _N			25			0.003		%V _O
Ripple Rejection Ratio(³)	R _A	5V	1.5A	Over Temp.	60	72		dB	

(1) Low duty cycle pulse testing with Kelvin connections required.

(2) Bandwidth of 10Hz to 10kHz.

(3) 120Hz input ripple (C_{ADJ} for ADJ) = 25μF.

(4) Over Temp. = over specified operating junction temperature range.