

SERIES 19X MAXI® CIRCUIT BREAKERS



Series 19X MAXI® Circuit Breakers

Auto, Manual & Modified Reset

SPECIFICATIONS

Single Pole Thermal Type Breakers

Rating: 8-50A; 14VDC; 28VDC (Series 193, 194, & 195).

Interrupt Rating: 150A @ 14VDC (8-10A versions); 225A @ 14VDC (15A version); 300A @ 14VDC (20A version); 450A @ 14VDC (25-30A versions); 600A @ 4VDC (35-40A versions); 750A @ 14VDC (50A version).

Operating Temperature Rating: -40°F (-40°C) to 185°F (85°C).

Storage Temperature Rating: -40°F (-40°C) to 260°F (125°C).


Materials: Grey UL-Rated 94V-0 thermoplastic.

Termination: Compatible with fuse blocks accepting MAXI® or ATC® blade fuses.

Compliances: SAE J553.


10 AMPS & BELOW
TYPICAL CURVE

15 AMPS & ABOVE
TYPICAL CURVE




10 AMPS & BELOW
TYPICAL CURVE

15 AMPS & ABOVE
TYPICAL CURVE



DIMENSIONS (Dims. shown are for reference only. Consult factory for latest prints) TERMINAL OPTIONS



PART NUMBERING SYSTEM

Series	Rating	Terminal	Cover	Button (193 Series Only)	Marking
191 – Type I, 14 VDC 192 – Type II, 14 VDC 193 – Type III, 12V/28 VDC 194 – Type I, 28 VDC 195 – Type II, 28 VDC	08 – 8 amps 10 – 10 amps 15 – 15 amps 20 – 20 amps 25 – 25 amps 30 – 30 amps 35 – 35 amps 40 – 40 amps 50 – 50 amps (191, 193, 194 only)	01 – MAXI® 02 – Wide ATC® 03 – Long ATC® (w/dimple) 04 – Long ATC® (no dimple)	M – Metal* P – Plastic (193 only)	1 – Black 2 – White	(Consult factory for special markings.)

* All breakers have metal cover except 193 series.