

4

3

2

1

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC	DIST	REVISIONS							
C COPYRIGHT		ALL RIGHTS RESERVED.				P	LTR	DESCRIPTION			DATE	DWN	APVD
						A1		ECR-15-001337			27JAN2015	GK	HMR

REPLACED BY OCEAN STYLE APPLICATOR PART



NUMBER 2266586-1

FOR REPLACEMENT PARTS FOR APPLICATOR 1238095
 REFER TO ADDITIONAL PAGE(S). SPARE PARTS KIT (IF LISTED)
 WILL REMAIN AVAILABLE.

THE REPLACEMENT OCEAN STYLE APPLICATOR HAS THE
 SAME TERMINATOR/PRESS INTERFACE AS APPLICATOR
 1238095

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN GOPALAKRISHNA HV		CHK RAGHAVENDRA		APVD RAGHAVENDRA		NAME		TE Connectivity	
				0 PLC	±										
				1 PLC	±										
				2 PLC	±										
				3 PLC	±										
				4 PLC	±										
				ANGLES	±										
MATERIAL		FINISH		WEIGHT		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
						A 3				C- 1238095					

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20
(C) COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION, ALL RIGHTS RESERVED.				
PART NUMBER	REV	TERMINATOR	FEED TYPE	DESCRIPTION
1238095-1	A	LEADMAKER	MECH POST FEED	CUTS CARRIER
1238095-2	A	BENCH	MECH PRE FEED	CUTS CARRIER
1238095-6	A	LEADMAKER	MECH POST FEED	CONTINUOUS CARRIER
7-1238095-1	A	LEADMAKER	MECH POST FEED	-1 AND SPARE PARTS
7-1238095-2	A	BENCH	MECH PRE FEED	-2 AND SPARE PARTS
7-1238095-6	A	LEADMAKER	MECH POST FEED	-6 AND SPARE PARTS
7-1238095-7	A	-	-	SPARE PARTS KIT



-	I	I	I	I	I	I	21028-2	PIN, SLOTTED SPRING .062 X .250	85
-	I	I	I	I	I	I	854769-4	HOLDER, INS	84
-	I	I	I	I	I	I	22278-7	SPRING, COMPRESSION	83
-	I	I	I	I	I	I	1338705-1	DOCUMENTATION PACKAGE	71
-	I	I	I	I	I	I	461264-1	PLATE, IDENTIFICATION	67
-	2	2	2	2	2	2	21017-2	SCREW, DRIVE	66
-	I	I	I	I	I	I	986950-1	WASHER, FLAT PRECISION	64
-	I	I	I	I	I	I	3-18031-0	SCR, SET, CUP POINT M6 X 6.0	63
-	I	I	I	I	I	I	18023-9	SCR, SKT HD CAP M4 X 6.0	62
-	2	2	2	2	2	2	2-18032-5	SCR, SET, FLT POINT M5 X 20.0	61
-	I	I	I	I	I	I	18024-7	SCR, BTN SKT HD CAP (M4 X 10.0)	60
-	I	I	I	I	I	I	5-18022-2	SCR, HEX HD CAP M4 X 8.0	59
-	I	I	I	I	I	I	1338685-1	PAWL, FEED	56
-	2	2	2	2	2	2	18024-8	SCR, BTN SKT HD CAP (M4 X 12.0)	54
-	2	2	2	2	2	2	1-18023-2	SCR, SKT HD CAP M4 X 12.0	53
-	I	I	I	I	I	I	18030-1	NUT, HEX, REG M3	52
-	I	I	I	I	I	I	811242-5	BUMPER, HOLD DOWN	51
-	I	I	I	I	I	I	690753-2	SPACER, TONKER	50
-	I	I	I	I	I	I	18024-3	SCR, BTN SKT HD CAP (M3 X 10.0)	49
-	-	I	-	-	I	-	1338675-1	CAM, UNIVERSAL PRE FEED	48
-	I	-	I	I	-	I	1338676-1	CAM, UNIVERSAL POST-FEED	47
-	I	I	I	I	I	I	1320999-3	APPLICATOR SUBASSEMBLY, HDI	46
-	I	I	I	I	I	I	690191-1	PLUG, NYLON	45
-	I	I	I	I	I	I	1633724-1	RAM, (SIDE FEED)	44
-	I	I	I	I	I	I	690125-1	SHIM SUB-ASSY	43
-	I	I	I	I	I	I	690124-1	WASHER, RAM (.115)	42
-	I	I	I	I	I	I	2-18024-6	SCR, BTN SKT HD CAP (M8 X 25.0)	41
-	I	I	I	I	I	I	23241-1	BALL, STEEL	40
-	I	I	I	I	I	I	2-22278-7	SPRING, COMPRESSION	39
-	I	I	I	I	I	I	1320922-1	DISC, ADJUST, INSULATION CRIMP	38
-	I	I	I	I	I	I	354777-1	WIRE DISC, ASSEMBLY	37
-	I	I	I	I	I	I	22480-5	SPRING, COMPRESSION	36
-	I	I	I	I	I	I	690212-1	POST, RAM	35
-	2	2	2	2	2	2	1-18024-0	SCR, BTN SKT HD CAP (M4 X 20.0)	33
-	I	I	I	I	I	I	18027-2	WASHER, FLAT, REG M4	32
-	I	I	I	I	I	I	1-18023-2	SCR, SKT HD CAP M4 X 12.0	31
-	I	I	I	I	I	I	1320908-4	SPACER, STRIP GUIDE	30
-	I	I	I	I	I	I	1633073-1	STRIP GUIDE ASSEMBLY	29
-	I	I	I	I	I	I	455888-3	SPACER, CRIMPER	28
-	2	2	2	2	2	2	1-22284-0	SPRING, COMPRESSION	27
-	I	I	I	I	I	I	356835-1	LEVER, DRAG RELEASE	26
-	I	I	I	I	I	I	240792-1	DRAG, TERMINAL	25
-	I	I	I	I	I	I	1320928-1	PLATE, STRIP GUIDE	24
-	I	I	I	I	I	I	980371-4	SCR, SKT HD SHLDR 5.0 DIA X 6.0	23
-	I	-	I	I	-	I	690472-2	STRIPPER	22
-	I	I	I	I	I	I	1-18023-1	SCR, SKT HD CAP M4 X 10.0	21
-	4	4	4	4	4	4	18025-2	WASHER, SPRG LOCK, REG M4	20
-	-	I	-	I	-	I	690472-1	STRIPPER	19
-	I	-	I	-	I	-	1338684-2	SHEAR HOLDER, FRONT	13
-	I	I	I	I	I	I	3-22280-3	SPRING, COMPRESSION	12
-	I	I	I	I	I	I	356885-5	STOP, SHEAR	11
-	-	I	I	-	I	I	1-1320921-0	SHEAR HOLDER, FRONT, CUT	10
-	I	I	I	I	I	I	462006-6	FLOATING SHEAR, FRONT	9
-	I	2	2	2	I	I	5-1633129-0	ANVIL, COMBINATION .062	8
-	-	-	-	-	-	-	-	-	7
-	-	-	-	-	-	-	-	-	6
-	I	I	I	I	I	I	854772-6	DEPRESSOR, SHEAR	5
-	I	I	I	I	I	I	2-238011-2	BLOCK, CRIMPER SPACER	4
I	2	2	2	I	I	I	2-679440-1	CRIMPER, INSULATION F	3
-	I	I	I	I	I	I	455888-3	SPACER, CRIMPER	2
I	2	2	2	I	I	I	3-456403-2	CRIMPER, WIRE PREMIUM	1

<small>This drawing is a CONTROLLING DOCUMENT FOR THIS ELECTRO-ASSY. CORRECTION SHEET SHOULD BE REFERENCED FOR THE LATEST REVISION.</small>		OWN: K STAKEM 29/JULY/2009	Tyco Electronics	
		APV: G BAILEY 29/JULY/2009	Harrisburg, PA 17105-3608	
DIMENSIONS: mm [IN]		NAME: SIDE FEED HDI APPLICATOR		RESTRICTED
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		-
0 PLC ± ^{0.005}		-		-
1 PLC ± ^{0.005}		-		-
2 PLC ± ^{0.005}		-		-
3 PLC ± ^{0.005}		APPLICATION SPEC		-
4 PLC ± ^{0.005}		See Table		-
ANGLES		SIZE: A CAGE CODE: 00779 DRAWING NO: C-1238095		-
MATERIAL: -		WEIGHT: -		-
FINISH: -		CUSTOMER DRAWING		SCALE: 3:5 SHEET: 1 OF 1 REV: A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1238095-1](#)