




LOC	DIST	REVISIONS				
AJ	16	P	LTR	DESCRIPTION	DATE	DWN
			J	REVISED PER EC 0514-0457-04	04NOV05	TS
			J1	REVISED PER ECO-09-021826	12SEP09	KK
						AEG



- 1 ZINC PER QQ-Z-363.
- 2 POLYMETHYLPENTENE, GENERAL PURPOSE.
- 3 PHOSPHOR BRONZE PER QQ-B-750.
- 4 NICKEL PLATE PER QQ-N-290, 3.81 μm [.000150] MINIMUM THICK.
- 5 GOLD PLATE PER MIL-G-45204, 0.76 μm [.000030] MINIMUM THICK.
- 6 ZAMAK 8
- 7 TIN PLATE PER ASTM-B-545, 3.81 μm [.000150] MINIMUM THICK.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



FOR 414373-3 AND 414373-4 ONLY



SUGGESTED PCB CONFIGURATION

OBSOLETE	7	1	414373-4
OBSOLETE	4	1	414373-3
OBSOLETE	4	6	414373-2
	4	1	414373-1
SHELL FINISH		SHELL MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. LIPPERT 05AUG92	Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK A. GABANY 10AUG92	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. GABANY 10AUG92	PRODUCT SPEC 108-12078	
MATERIAL SEE NOTES 1-3, 6		APPLICATION SPEC		RESTRICTED TO
FINISH SEE NOTES 4 - 5		WEIGHT -		REV J1
		CUSTOMER DRAWING		SCALE 8:1 SHEET 1 OF 1