



*AMPPOWER is a trademark

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
GP	00	F		REV PER ECO-12-000102	9JAN2012	RG DY


1. CABLE LENGTH TOLERANCE ON 0-150 INCH LONG CABLES = +0.2% -0% OF TOTAL CABLE LENGTH WITH A MINIMUM TOLERANCE OF +6.4 [.25] 0 [0].
CABLE LENGTH TOLERANCE ON CABLES OVER 150 INCHES LONG = + 1% -0% OF TOTAL CABLE LENGTH.
2. LABEL APPROXIMATELY WHERE SHOWN.
3. BECAUSE OF SHIPPING CONSTRAINTS, REFOLDING/SHAPING OF CABLE ASSEMBLIES MAY BE REQUIRED BY CUSTOMER BEFORE INSTALLATION.
4. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.
5. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



2 - 0.50[.020] THK SINGLE CONDUCTOR CABLES



	1778.0 [70.0]	SOLID	0.50 [.020]	1-766109-0
	2108.2 [83.0]	SOLID	0.50 [.020]	766109-9
	1136.65 [44.75]	SOLID	0.50 [.020]	766109-8
OBSOLETE	1384.30 [54.50]	SOLID	0.50 [.020]	766109-7
	1714.50 [67.50]	SOLID	0.50 [.020]	766109-6
	2051.05 [80.75]	SOLID	0.50 [.020]	766109-5
5 OBSOLETE	755.7 [29.75]	SOLID	0.50 [.020]	766109-4
	1574.8 [62.00]	SOLID	0.50 [.020]	766109-3
5 OBSOLETE	1765.3 [69.50]	SOLID	0.50 [.020]	766109-2
5 OBSOLETE	2032 [80.00]	SOLID	0.50 [.020]	766109-1
CABLE ASSY REF LENGTH A		STYLE	CONDUCTOR THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09-22-95 D.A. BABOW		 TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK 09-22-95 D.E. PETRIE					
		APVD 09-22-95 J.E. LUCIUS		NAME CABLE ASSEMBLY, WAVE CRIMP — —			
		PRODUCT SPEC —					
		APPLICATION SPEC 114-49005					
		WEIGHT —					
MATERIAL —	FINISH —	CUSTOMER DRAWING		SIZE A2	CAGE CODE 00779	DRAWING NO C=766109	RESTRICTED TO —
		SCALE FULL				SHEET 1 of 1	REV F