



## 25W AC-DC Triple Output Desktop

## P25B-T series



### ■ Features :

- 2 pole AC inlet IEC320-C8
- Class II power (without earth pin)
- Protections: Short circuit/ Over load/ Over voltage/ Over temp.
- Fix switching frequency and regulation
- LED indicator for power on
- Fully enclosed plastic case
- Topology: Top switch circuit
- Approvals: UL/ CUL/ TUV/ CB/ CE
- 1 year warranty




### SPECIFICATION

| ORDER NO.                 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | P25B13A-R1B                                                                                                                   |            |            | P25B13D-R1B |          |           | P25B14E-R1B |            |            |
|---------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|------------|------------|-------------|----------|-----------|-------------|------------|------------|
| OUTPUT                    | SAFETY MODEL NO.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          | PSU25B-13A                                                                                                                    |            |            | PSU25B-13D  |          |           | PSU25B-14E  |            |            |
|                           | DC VOLTAGE <span>Note.2</span>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            | 5V                                                                                                                            | 12V        | -5V        | 5V          | 12V      | -12V      | 5V          | 15V        | -15V       |
|                           | RATED CURRENT                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | 2.5A                                                                                                                          | 0.8A       | 0.3A       | 2.5A        | 0.8A     | 0.3A      | 2.5A        | 0.5A       | 0.3A       |
|                           | CURRENT RANGE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | 0.5 ~ 2.5A                                                                                                                    | 0.1 ~ 0.8A | 0.1 ~ 0.3A | 0.5 ~ 2.5A  | 0.1~0.8A | 0.1 ~0.3A | 0.5 ~ 2.5A  | 0.1 ~ 0.5A | 0.1 ~ 0.3A |
|                           | RATED POWER                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               | 25W                                                                                                                           |            |            | 25W         |          |           | 25W         |            |            |
|                           | RIPPLE & NOISE (max.) <span>Note.3</span>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 | 50mVp-p                                                                                                                       | 100mVp-p   | 100mVp-p   | 50mVp-p     | 100mVp-p | 100mVp-p  | 50mVp-p     | 100mVp-p   | 100mVp-p   |
|                           | VOLTAGE ADJ. RANGE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        | Fixed                                                                                                                         |            |            |             |          |           |             |            |            |
|                           | VOLTAGE TOLERANCE <span>Note.4</span>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     | ±5.0%                                                                                                                         | ±5.0%      | ±3.0%      | ±5.0%       | ±5.0%    | ±3.0%     | ±5.0%       | ±5.0%      | ±3.0%      |
|                           | LINE REGULATION <span>Note.5</span>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | ±1.0%                                                                                                                         | ±1.0%      | ±1.0%      | ±1.0%       | ±1.0%    | ±1.0%     | ±1.0%       | ±1.0%      | ±1.0%      |
|                           | LOAD REGULATION <span>Note.6</span>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | ±4.0%                                                                                                                         | ±4.0%      | ±2.0%      | ±4.0%       | ±4.0%    | ±2.0%     | ±4.0%       | ±4.0%      | ±2.0%      |
| SETUP, RISE, HOLD TIME    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | 200ms, 50ms, 16ms at full load                                                                                                |            |            |             |          |           |             |            |            |
| INPUT                     | VOLTAGE RANGE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | 90 ~ 264VAC 135~370VDC                                                                                                        |            |            |             |          |           |             |            |            |
|                           | FREQUENCY RANGE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | 47~63Hz                                                                                                                       |            |            |             |          |           |             |            |            |
|                           | EFFICIENCY (Typ.)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         | 70%                                                                                                                           |            |            | 72%         |          |           | 74%         |            |            |
|                           | AC CURRENT                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                | 0.8A / 100VAC                                                                                                                 |            |            |             |          |           |             |            |            |
|                           | INRUSH CURRENT (max.)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     | 60A / 230VAC                                                                                                                  |            |            |             |          |           |             |            |            |
|                           | LEAKAGE CURRENT (max.)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    | 0.25mA / 240VAC                                                                                                               |            |            |             |          |           |             |            |            |
| PROTECTION                | OVER LOAD                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 | 115~160% rated output power<br>Protection type : Hiccup mode, recovers automatically after fault condition is removed         |            |            |             |          |           |             |            |            |
|                           | OVER VOLTAGE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | +5V: 110~140% rated output voltage<br>Protection type : Shut down o/p voltage, re-power on to recover                         |            |            |             |          |           |             |            |            |
|                           | OVER TEMPERATURE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          | IC1Tj135℃<br>Protection type : Shut down o/p voltage, recovers automatically after temperature goes down                      |            |            |             |          |           |             |            |            |
|                           |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |                                                                                                                               |            |            |             |          |           |             |            |            |
| ENVIRONMENT               | WORKING TEMP.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | 0~+40℃ (Refer to output load derating curve)                                                                                  |            |            |             |          |           |             |            |            |
|                           | WORKING HUMIDITY                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          | 20%~90% RH non-condensing                                                                                                     |            |            |             |          |           |             |            |            |
|                           | STORAGE TEMP., HUMIDITY                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   | -20~+85℃ 10~95% RH                                                                                                            |            |            |             |          |           |             |            |            |
|                           | TEMP. COEFFICIENT                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         | ±0.03% / °C (0~50℃)                                                                                                           |            |            |             |          |           |             |            |            |
|                           | VIBRATION                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 | 10~500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes                                                         |            |            |             |          |           |             |            |            |
| SAFETY & EMC<br>(Note. 7) | SAFETY STANDARDS                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          | UL1950, CSA22.2, EN60950 Approved                                                                                             |            |            |             |          |           |             |            |            |
|                           | WITHSTAND VOLTAGE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         | I/P-O/P:3KVAC                                                                                                                 |            |            |             |          |           |             |            |            |
|                           | ISOLATION RESISTANCE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | I/P-O/P:100M Ohms / 500VDC                                                                                                    |            |            |             |          |           |             |            |            |
|                           | EMI CONDUCTION & RADIATION                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                | Compliance to EN55022(CISPR22) Class B                                                                                        |            |            |             |          |           |             |            |            |
|                           | HARMONIC CURRENT                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          | Compliance to EN61000-3-2,3                                                                                                   |            |            |             |          |           |             |            |            |
| OTHERS                    | EMS IMMUNITY                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | Compliance to EN61000-4-2,3,4,5,6,11, Light industry level, criteria A                                                        |            |            |             |          |           |             |            |            |
|                           | MTBF                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | 520K hrs min. MIL-HDBK-217F(25℃)                                                                                              |            |            |             |          |           |             |            |            |
|                           | DIMENSION                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 | 108*67*36mm (L*W*H)                                                                                                           |            |            |             |          |           |             |            |            |
| CONNECTOR                 | PACKING                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   | 0.3kg ; 54pcs / 20kg / CARTON                                                                                                 |            |            |             |          |           |             |            |            |
|                           | PLUG                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | Standard type R1B: DIN 5PIN for stock ; Other type available by customer requested                                            |            |            |             |          |           |             |            |            |
|                           | CABLE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     | Standard type UL2464 18AWG*2C, 20AWG*2C shield wire*1C with 5fts length for stock; Other type available by customer requested |            |            |             |          |           |             |            |            |
| NOTE                      | 1.All parameters are specified at 230VAC input, rated load, 25℃ 70% RH. Ambient.<br>2.DC voltage: The output voltage set at point measure by plug terminal & 50% load.<br>3.Ripple & noise are measured at 20MHz by using a 12" twisted pair terminated with a 0.1uf & 47uf capacitor.<br>4.Tolerance: includes set up tolerance, line regulation, load regulation.<br>5.Line regulation is measured from low line to high line at rated load.<br>6.Load regulation is measured from 20% to 100% rated load.<br>7.The power supply is considered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets EMC directives. |                                                                                                                               |            |            |             |          |           |             |            |            |


## Mechanical Specification

Unit:mm




## Plug Assignment

Standard plug: R1B (option)



| PIN NO | OUTPUT |
|--------|--------|
| 1      | COM    |
| 2      | COM    |
| 3      | +5VDC  |
| 4      | -Vout  |
| 5      | +Vout  |

## Derating Curve



## Static Characteristics

