



# Chip Monolithic Ceramic Capacitors



Murata  
Manufacturing Co., Ltd.

*Innovator  
in Electronics*



## Explanation of Symbols in This Catalog

### Ultra-compact

Lx W dimension: products of 0.6 x 0.3 mm or less

### HiQ

Low dissipation for high frequency  
By devising ceramic materials and electrode materials, low dissipation is achieved in frequency bands of VHF, UHF and microwave or beyond.

### Low ESL

Low inductance  
This capacitor is designed so that the parasitic inductance component (ESL) that the capacitor has on the high frequency side becomes lower.

### Anti-noise

Product suitable for acoustic noise reduction and low distortion  
This product suppresses acoustic noise, which occurs when a ceramic capacitor is used, by devising the materials and configuration.

### Deflecting crack

Product resistant to deflection cracking  
This capacitor is designed to prevent failures as much as possible by short mode caused by cracking when there is board deflection.


### Soldering crack

Product with solder cracking suppression  
This capacitor is configured with metal terminals and leads connected to the chip.  
The metal terminals and leads relieve the stress from expansion and contraction of the solder, to suppress solder cracking.

### Derating


Voltage and temperature derating recommended product  
This product is suitable when a voltage continuously applied to a capacitor in an operating circuit, is used below (derated) the rated voltage of the capacitor.  
This model guarantees the test conditions in the endurance test, at a rated voltage x 100% at the maximum operating temperature. A reliability assurance level equivalent to a common product can be secured, by using this product within the voltage and temperature derated conditions recommended in the figure below.

Recommended Conditions of the Derating Operating Voltage and Temperature




### EU RoHS Compliant


- All the products in this catalog comply with EU RoHS.
- EU RoHS is "the European Directive 2011/65/EU on the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment."
- For more details, please refer to our website 'Murata's Approach for EU RoHS' (<http://www.murata.com/info/rohs.html>).



## For General Purpose GRM Series Capacitance Table



# Contents



Product specifications are as of August 2013.

|                         |    |
|-------------------------|----|
| Part Numbering .....    | p2 |
| Selection Guide .....   | p5 |
| Capacitance Table ..... | p6 |

## Chip Monolithic Ceramic Capacitors

Cap. Table

|                                      |     |                 |
|--------------------------------------|-----|-----------------|
| For General Purpose GRM Series ..... | p16 | separate volume |
|--------------------------------------|-----|-----------------|

|                                                                                    |     |    |
|------------------------------------------------------------------------------------|-----|----|
| High Frequency High Q Type<br>1005(in mm)/0402(in inch) Size Max. GJM Series ..... | p83 | p7 |
|------------------------------------------------------------------------------------|-----|----|

|                                                             |      |    |
|-------------------------------------------------------------|------|----|
| Top & Bottom Electrode Type for Bonding<br>GMA Series ..... | p105 | p8 |
|-------------------------------------------------------------|------|----|

|                                                            |      |    |
|------------------------------------------------------------|------|----|
| Compatible to Bonding / AuSn Soldering<br>GMD Series ..... | p107 | p9 |
|------------------------------------------------------------|------|----|

|                                                                                    |      |     |
|------------------------------------------------------------------------------------|------|-----|
| High Frequency High Q Type<br>1608(in mm)/0603(in inch) Size Min. GQM Series ..... | p110 | p10 |
|------------------------------------------------------------------------------------|------|-----|

|                                                |      |     |
|------------------------------------------------|------|-----|
| Resin External Electrode Type GRJ Series ..... | p119 | p11 |
|------------------------------------------------|------|-----|

|                                                                                |      |     |
|--------------------------------------------------------------------------------|------|-----|
| High Effective Capacitance &<br>High Allowable Ripple Current GR3 Series ..... | p121 | p11 |
|--------------------------------------------------------------------------------|------|-----|

|                                                             |      |     |
|-------------------------------------------------------------|------|-----|
| Metal Terminal Type For General Purpose<br>KRM Series ..... | p123 | p12 |
|-------------------------------------------------------------|------|-----|

|                                                                                                    |      |     |
|----------------------------------------------------------------------------------------------------|------|-----|
| Metal Terminal Type High Effective Capacitance &<br>High Allowable Ripple Current KR3 Series ..... | p126 | p13 |
|----------------------------------------------------------------------------------------------------|------|-----|

|                                          |      |     |
|------------------------------------------|------|-----|
| 8-Terminal Low ESL Type LLA Series ..... | p129 | p13 |
|------------------------------------------|------|-----|

|                                           |      |     |
|-------------------------------------------|------|-----|
| LW Reversed Low ESL Type LLL Series ..... | p131 | p14 |
|-------------------------------------------|------|-----|

|                                           |      |     |
|-------------------------------------------|------|-----|
| 10-Terminal Low ESL Type LLM Series ..... | p133 | p14 |
|-------------------------------------------|------|-----|

|                                              |      |     |
|----------------------------------------------|------|-----|
| ESR Controlled Low ESL Type LLR Series ..... | p135 | p14 |
|----------------------------------------------|------|-----|

|                                          |      |
|------------------------------------------|------|
| ⚠Caution/Notice .....                    | p137 |
| Qualified Standards .....                | p158 |
| Introduction of Website SimSurfing ..... | p160 |
| EMICON-FUN! .....                        | p161 |
| Product Information .....                | p162 |

Please check the MURATA home page (<http://www.murata.com/>) if you cannot find the part number in the catalog.

## ● Part Numbering

### Chip Monolithic Ceramic Capacitors for General

(Part Number) 

|    |   |    |   |    |    |     |   |     |   |
|----|---|----|---|----|----|-----|---|-----|---|
| GR | M | 18 | 8 | B1 | 1H | 102 | K | A01 | D |
|----|---|----|---|----|----|-----|---|-----|---|

|   |   |   |   |   |   |   |   |   |   |
|---|---|---|---|---|---|---|---|---|---|
| ① | ② | ③ | ④ | ⑤ | ⑥ | ⑦ | ⑧ | ⑨ | ⑩ |
|---|---|---|---|---|---|---|---|---|---|

#### ①Product ID ②Series

| Product ID | Code | Series                                                                            |
|------------|------|-----------------------------------------------------------------------------------|
| GJ         | M    | High frequency HiQ type<br>1005(in mm)/0402(in inch) size max.                    |
|            | A    | Top & bottom electrode type for bonding                                           |
| GM         | D    | Product for bonding/AuSn soldering                                                |
|            | M    | High frequency HiQ type<br>1608(in mm)/0603(in inch) size min.                    |
| GR         | 3    | High effective capacitance &<br>High allowable ripple current                     |
|            | J    | Resin external electrode type                                                     |
|            | M    | General purpose products                                                          |
| KR         | 3    | Metal terminal type/High effective capacitance &<br>High allowable ripple current |
|            | M    | Metal terminal type                                                               |
| LL         | A    | 8-terminal low ESL type                                                           |
|            | L    | LW reversed low ESL type                                                          |
|            | M    | 10-terminal low ESL type                                                          |
|            | R    | Controlled ESR low ESL type                                                       |

#### ③Chip Dimensions (L×W)

| Code | Dimensions (L×W) | Size Code (in inch) |
|------|------------------|---------------------|
| 02   | 0.4×0.2mm        | 01005               |
| 03   | 0.6×0.3mm        | 0201                |
| 05   | 0.5×0.5mm        | 0202                |
| 08   | 0.8×0.8mm        | 0303                |
| 0D   | 0.38×0.38mm      | 015015              |
| 15   | 1.0×0.5mm        | 0402                |
| 18   | 1.6×0.8mm        | 0603                |
| 1U   | 0.6×1.0mm        | 02404               |
| 21   | 2.0×1.25mm       | 0805                |
| 22   | 2.8×2.8mm        | 1111                |
| 31   | 3.2×1.6mm        | 1206                |
| 32   | 3.2×2.5mm        | 1210                |
| 42   | 4.5×2.0mm        | 1808                |
| 43   | 4.5×3.2mm        | 1812                |
| 55   | 5.7×5.0mm        | 2220                |

#### ④Height Dimension (T) (Except KR□)

| Code | Dimension (T)                    |
|------|----------------------------------|
| 2    | 0.2mm                            |
| 3    | 0.3mm                            |
| 4    | 0.4mm                            |
| 5    | 0.5mm                            |
| 6    | 0.6mm                            |
| 7    | 0.7mm                            |
| 8    | 0.8mm                            |
| 9    | 0.85mm                           |
| A    | 1.0mm                            |
| B    | 1.25mm                           |
| C    | 1.6mm                            |
| D    | 2.0mm                            |
| E    | 2.5mm                            |
| M    | 1.15mm                           |
| Q    | 1.5mm                            |
| R    | 1.8mm                            |
| S    | 2.8mm                            |
| X    | Depends on individual standards. |

#### ④Height Dimension (T) (KR□ Only)

| Code | Dimension (T) |
|------|---------------|
| E    | 1.8mm         |
| F    | 1.9mm         |
| K    | 2.7mm         |
| L    | 2.8mm         |
| Q    | 3.7mm         |
| T    | 4.8mm         |
| W    | 6.4mm         |

Continued on the following page. 

(Part Number)

| GR | M | 18 | 8 | B1 | 1H | 102 | K | A01 | D  |
|----|---|----|---|----|----|-----|---|-----|----|
| 1  | 2 | 3  | 4 | 5  | 6  | 7   | 8 | 9   | 10 |

Continued from the preceding page.

## ⑤ Temperature Characteristics

| Temperature Characteristic Codes |                 | Temperature Characteristics |                   |                                               |                     | Operating Temperature Range | Capacitance Change Each Temperature (%) |       |       |       |      |       |
|----------------------------------|-----------------|-----------------------------|-------------------|-----------------------------------------------|---------------------|-----------------------------|-----------------------------------------|-------|-------|-------|------|-------|
| Code                             | Public STD Code | Reference Temperature       | Temperature Range | Capacitance Change or Temperature Coefficient | -55°C               |                             | *3                                      |       | -10°C |       |      |       |
|                                  |                 |                             |                   |                                               | Max.                |                             | Min.                                    | Max.  | Min.  | Max.  | Min. |       |
| 1X                               | SL              | JIS                         | 20°C              | 20 to 85°C                                    | +350 to -1000ppm/°C | -55 to 125°C                | -                                       | -     | -     | -     | -    | -     |
| 2C                               | CH              | JIS                         | 20°C              | 20 to 125°C                                   | 0±60ppm/°C          | -55 to 125°C                | 0.82                                    | -0.45 | 0.49  | -0.27 | 0.33 | -0.18 |
| 3C                               | CJ              | JIS                         | 20°C              | 20 to 125°C                                   | 0±120ppm/°C         | -55 to 125°C                | 1.37                                    | -0.9  | 0.82  | -0.54 | 0.55 | -0.36 |
| 3U                               | UJ              | JIS                         | 20°C              | 20 to 85°C                                    | -750±120ppm/°C      | -25 to 85°C                 | -                                       | -     | 4.94  | 2.84  | 3.29 | 1.89  |
| 4C                               | CK              | JIS                         | 20°C              | 20 to 125°C                                   | 0±250ppm/°C         | -55 to 125°C                | 2.56                                    | -1.88 | 1.54  | -1.13 | 1.02 | -0.75 |
| 5C                               | C0G             | EIA                         | 25°C              | 25 to 125°C                                   | 0±30ppm/°C          | -55 to 125°C                | 0.58                                    | -0.24 | 0.4   | -0.17 | 0.25 | -0.11 |
| 7U                               | U2J             | EIA                         | 25°C              | 25 to 125°C *2                                | -750±120ppm/°C      | -55 to 125°C                | 8.78                                    | 5.04  | 6.04  | 3.47  | 3.84 | 2.21  |
| B1                               | B *1            | JIS                         | 20°C              | -25 to 85°C                                   | ±10%                | -25 to 85°C                 | -                                       | -     | -     | -     | -    | -     |
| B3                               | B               | JIS                         | 20°C              | -25 to 85°C                                   | ±10%                | -25 to 85°C                 | -                                       | -     | -     | -     | -    | -     |
| C6                               | X5S             | EIA                         | 25°C              | -55 to 85°C                                   | ±22%                | -55 to 85°C                 | -                                       | -     | -     | -     | -    | -     |
| C7                               | X7S             | EIA                         | 25°C              | -55 to 125°C                                  | ±22%                | -55 to 125°C                | -                                       | -     | -     | -     | -    | -     |
| C8                               | X6S             | EIA                         | 25°C              | -55 to 105°C                                  | ±22%                | -55 to 105°C                | -                                       | -     | -     | -     | -    | -     |
| D7                               | X7T             | EIA                         | 25°C              | -55 to 125°C                                  | +22%, -33%          | -55 to 125°C                | -                                       | -     | -     | -     | -    | -     |
| D8                               | X6T             | EIA                         | 25°C              | -55 to 105°C                                  | +22%, -33%          | -55 to 105°C                | -                                       | -     | -     | -     | -    | -     |
| E7                               | X7U             | EIA                         | 25°C              | -55 to 125°C                                  | +22%, -56%          | -55 to 125°C                | -                                       | -     | -     | -     | -    | -     |
| R1                               | R *1            | JIS                         | 20°C              | -55 to 125°C                                  | ±15%                | -55 to 125°C                | -                                       | -     | -     | -     | -    | -     |
| R6                               | X5R             | EIA                         | 25°C              | -55 to 85°C                                   | ±15%                | -55 to 85°C                 | -                                       | -     | -     | -     | -    | -     |
| R7                               | X7R             | EIA                         | 25°C              | -55 to 125°C                                  | ±15%                | -55 to 125°C                | -                                       | -     | -     | -     | -    | -     |

\*1 Capacitance change is specified with 50% rated voltage applied.

\*2 Rated Voltage 100Vdc max: 25 to 85°C

\*3 -25°C (Reference Temperature 20°C) / -30°C (Reference Temperature 25°C)

## ⑥ Rated Voltage

| Code | Rated Voltage |
|------|---------------|
| 0E   | DC2.5V        |
| 0G   | DC4V          |
| 0J   | DC6.3V        |
| 1A   | DC10V         |
| 1C   | DC16V         |
| 1E   | DC25V         |
| 1H   | DC50V         |
| 1J   | DC63V         |
| 1K   | DC80V         |
| 2A   | DC100V        |
| 2D   | DC200V        |
| 2E   | DC250V        |
| 2W   | DC450V        |
| 2H   | DC500V        |
| 2J   | DC630V        |
| 3A   | DC1kV         |
| 3D   | DC2kV         |
| 3F   | DC3.15kV      |
| YA   | DC35V         |

## ⑦ Capacitance

Expressed by three-digit alphanumerics. The unit is picofarad (pF). The first and second figures are significant digits, and the third figure expresses the number of zeros which follow the two numbers. If there is a decimal point, it is expressed by the capital letter "R." In this case, all figures are significant digits. If any alphabet, other than "R", is included, this indicates the specific part number is a non-standard part.

| Ex.) | Code | Capacitance |
|------|------|-------------|
|      | R50  | 0.50pF      |
|      | 1R0  | 1.0pF       |
|      | 100  | 10pF        |
|      | 103  | 10000pF     |

## ⑧ Capacitance Tolerance

| Code | Capacitance Tolerance   |
|------|-------------------------|
| B    | ±0.1pF                  |
| C    | ±0.25pF                 |
| D    | ±0.5pF (10pF and below) |
|      | ±0.5% (10pF and over)   |
| F    | ±1%                     |
| G    | ±2%                     |
| J    | ±5%                     |
| K    | ±10%                    |
| M    | ±20%                    |
| W    | ±0.05pF                 |

Continued on the following page. ➤

Please check the MURATA home page (<http://www.murata.com/>) if you cannot find the part number in the catalog.

(Part Number)

| GR | M | 18 | 8 | B1 | 1H | 102 | K | A01 | D  |
|----|---|----|---|----|----|-----|---|-----|----|
| 1  | 2 | 3  | 4 | 5  | 6  | 7   | 8 | 9   | 10 |

 Continued from the preceding page.

⑨ Individual Specification Code (Except LLR)

Expressed by three figures.

⑨ ESR (LLR Only)

| Code | ESR    |
|------|--------|
| E01  | 100mΩ  |
| E03  | 220mΩ  |
| E05  | 470mΩ  |
| E07  | 1000mΩ |

⑩ Packaging

| Code  | Packaging              |
|-------|------------------------|
| L     | ø180mm Embossed Taping |
| D/E/W | ø180mm Paper Taping    |
| K     | ø330mm Embossed Taping |
| J/F   | ø330mm Paper Taping    |
| B     | Bulk                   |
| C     | Bulk Case              |
| T     | Bulk Tray              |

Please contact us if you find any part number not provided in this table.

## Selection Guide for Chip Monolithic Ceramic Capacitors

|                               | Series                      | Ultra-small<br>(smaller than 0201) | Low dissipation/HiQ | Low ESL | Fail safe | Anti-deflecting crack | Anti-soldering crack | Anti-noise, low distortion | For bonding | Specific applications | Safety standard<br>certified type |
|-------------------------------|-----------------------------|------------------------------------|---------------------|---------|-----------|-----------------------|----------------------|----------------------------|-------------|-----------------------|-----------------------------------|
| For General Purpose           | GRM <small>page p16</small> |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | GA2                         |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | GA3                         |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | GJM <small>p83</small>      |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | GJ4                         |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | GJ8                         |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | GMA <small>p105</small>     |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | GMD <small>p107</small>     |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | GQM <small>p110</small>     |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | GRJ <small>p119</small>     |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | GR3 <small>p121</small>     |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | GR4                         |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | GR7                         |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | KRM <small>p123</small>     |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | KR3 <small>p126</small>     |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | LLA <small>p129</small>     |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | LLL <small>p131</small>     |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | LLM <small>p133</small>     |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | LLR <small>p135</small>     |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | ZRA                         |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
| For Automotive (Cat. No. C03) | GCM                         |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | GCD                         |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | GCE                         |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | GCG                         |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | GCJ                         |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | GC3                         |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | KCM                         |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |
|                               | KC3                         |                                    |                     |         |           |                       |                      |                            |             |                       |                                   |

## Capacitance Table

### How to read the Capacitance Table

| LxW (mm)            | 0.4×0.2 |     | 0.6×0.3 |     | 1.0 |
|---------------------|---------|-----|---------|-----|-----|
| T max. (mm)         | 0.22    |     | 0.33    |     | 0.4 |
| Rated Voltage (Vdc) | 25      |     | 25      |     | 50  |
| Cap. / TC Code      | C0G     | CΔ  | C0G     | CΔ  | C0G |
| 0.10pF              |         |     |         |     | p97 |
| 0.20pF              | p84     | p87 | p90     | p93 | p97 |
| 1.0pF               | p84     | p87 | p90     | p94 | p97 |
| 2.0pF               | p84     | p87 | p91     | p94 | p97 |
| 3.0pF               | p84     | p87 | p91     | p94 | p98 |

→ The values can be narrowed down in the order of size, rated voltage, and temperature characteristics.

→ Refers to the page of the part number list.  
Check the part number list for the applicable product number.

### Temperature Characteristics Table

The Table is colored by temperature characteristic codes.  
Refer to the following Table for the meaning of each code.


|      |     |     |     |     |     |     |     |     |     |     |
|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| EIA: | C0G | U2J | X7R | X7S | X7T | X7U | X6S | X6T | X5R | X5S |
| JIS: | CK  | CJ  | CH  | SL  | UJ  | R   | B   |     |     |     |

| Temperature<br>Characteristic Codes |     | Temperature Characteristics |                      |                                                     | Operating<br>Temperature<br>Range | Capacitance Change Each Temperature (%) |       |      |       |       |       |
|-------------------------------------|-----|-----------------------------|----------------------|-----------------------------------------------------|-----------------------------------|-----------------------------------------|-------|------|-------|-------|-------|
|                                     |     |                             |                      |                                                     |                                   | -55°C                                   |       | *2   |       | -10°C |       |
| Public<br>STD Code                  |     | Reference<br>Temperature    | Temperature<br>Range | Capacitance Change<br>or Temperature<br>Coefficient |                                   | Max.                                    | Min.  | Max. | Min.  | Max.  | Min.  |
| C0G                                 | EIA | 25°C                        | 25 to 125°C          | 0±30ppm/°C                                          | -55 to 125°C                      | 0.58                                    | -0.24 | 0.4  | -0.17 | 0.25  | -0.11 |
| CK                                  | JIS | 20°C                        | 20 to 125°C          | 0±250ppm/°C                                         | -55 to 125°C                      | 2.56                                    | -1.88 | 1.54 | -1.13 | 1.02  | -0.75 |
| CJ                                  | JIS | 20°C                        | 20 to 125°C          | 0±120ppm/°C                                         | -55 to 125°C                      | 1.37                                    | -0.9  | 0.82 | -0.54 | 0.55  | -0.36 |
| CH                                  | JIS | 20°C                        | 20 to 125°C          | 0±60ppm/°C                                          | -55 to 125°C                      | 0.82                                    | -0.45 | 0.49 | -0.27 | 0.33  | -0.18 |
| SL                                  | JIS | 20°C                        | 20 to 85°C           | +350 to -1000ppm/°C                                 | -55 to 125°C                      | -                                       | -     | -    | -     | -     | -     |
| U2J                                 | EIA | 25°C                        | 25 to 125°C *1       | -750±120ppm/°C                                      | -55 to 125°C                      | 8.78                                    | 5.04  | 6.04 | 3.47  | 3.84  | 2.21  |
| UJ                                  | JIS | 20°C                        | 20 to 85°C           | -750±120ppm/°C                                      | -25 to 85°C                       | -                                       | -     | 4.94 | 2.84  | 3.29  | 1.89  |
| X7R                                 | EIA | 25°C                        | -55 to 125°C         | ±15%                                                | -55 to 125°C                      | -                                       | -     | -    | -     | -     | -     |
| X7S                                 | EIA | 25°C                        | -55 to 125°C         | ±22%                                                | -55 to 125°C                      | -                                       | -     | -    | -     | -     | -     |
| X7T                                 | EIA | 25°C                        | -55 to 125°C         | +22%, -33%                                          | -55 to 125°C                      | -                                       | -     | -    | -     | -     | -     |
| X7U                                 | EIA | 25°C                        | -55 to 125°C         | +22%, -56%                                          | -55 to 125°C                      | -                                       | -     | -    | -     | -     | -     |
| R                                   | JIS | 20°C                        | -55 to 125°C         | ±15%                                                | -55 to 125°C                      | -                                       | -     | -    | -     | -     | -     |
| X6S                                 | EIA | 25°C                        | -55 to 105°C         | ±22%                                                | -55 to 105°C                      | -                                       | -     | -    | -     | -     | -     |
| X6T                                 | EIA | 25°C                        | -55 to 105°C         | +22%, -33%                                          | -55 to 105°C                      | -                                       | -     | -    | -     | -     | -     |
| X5R                                 | EIA | 25°C                        | -55 to 85°C          | ±15%                                                | -55 to 85°C                       | -                                       | -     | -    | -     | -     | -     |
| X5S                                 | EIA | 25°C                        | -55 to 85°C          | ±22%                                                | -55 to 85°C                       | -                                       | -     | -    | -     | -     | -     |
| B                                   | JIS | 20°C                        | -25 to 85°C          | ±10%                                                | -25 to 85°C                       | -                                       | -     | -    | -     | -     | -     |

\*1 Rated Voltage 100Vdc max: 25 to 85°C

\*2 -25°C (Reference Temperature 20°C) / -30°C (Reference Temperature 25°C)

### GRM Series



For the Capacitance Table of General Purpose GRM Series, please review the inserted Capacitance Table of "Chip Monolithic Ceramic Capacitors For General Purpose GRM Series".



## Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

### ■ GRM Series Temperature Compensating Type

p00

← Part Number List

JIS:

CK

CJ

CH

SL

UJ

EIA:

C0G

U2J

| LxW (mm)            | 0.4x0.2 |     |     |     | 0.6x0.3 |     |     |     | 1.0x0.5 |     |     |     |                                                                                                                  |     | 1.6x0.8 |     |     |     |     |     |     |     |     |  |
|---------------------|---------|-----|-----|-----|---------|-----|-----|-----|---------|-----|-----|-----|------------------------------------------------------------------------------------------------------------------|-----|---------|-----|-----|-----|-----|-----|-----|-----|-----|--|
| T max. (mm)         | 0.22    |     |     |     | 0.33    |     |     |     | 0.55    |     |     |     |                                                                                                                  |     | 0.5     |     |     |     |     |     | 0.9 |     |     |  |
| Rated Voltage (Vdc) | 16      |     | 10  |     | 100     |     | 50  |     | 100     |     | 50  |     | 10                                                                                                               |     | 50      |     |     | 10  |     |     | 100 |     |     |  |
| Cap. / TC Code      | C0G     | CΔ  | C0G | CH  | C0G     | CΔ  | C0G | CΔ  | C0G     | CΔ  | C0G | CΔ  | SL                                                                                                               | U2J | UJ      | SL  | U2J | UJ  | SL  | U2J | UJ  | C0G | CΔ  |  |
| 0.10pF              |         |     |     |     | p23     | p26 | p30 | p33 | p36     | p40 | p43 | p47 |                                                                                                                  |     |         |     |     |     |     |     |     |     |     |  |
| 0.20pF              | p17     | p20 |     |     | p23     | p26 | p30 | p33 | p36     | p40 | p43 | p47 | The indication for every 0.1 pF has been omitted for less than 10 pF. Refer to the Part Number List for details. |     |         |     |     |     |     |     |     |     |     |  |
| 0.50pF              | p17     | p20 |     |     | p23     | p26 | p30 | p33 | p36     | p40 | p43 | p47 |                                                                                                                  |     |         |     |     |     |     |     |     |     |     |  |
| 1.0pF               | p17     | p20 |     |     | p23     | p27 | p30 | p33 | p37     | p40 | p43 | p47 |                                                                                                                  |     |         |     |     |     |     |     |     |     |     |  |
| 2.0pF               | p17     | p20 |     |     | p24     | p27 | p30 | p33 | p37     | p40 | p44 | p47 |                                                                                                                  |     |         |     |     |     |     |     |     |     |     |  |
| 3.0pF               | p17     | p20 |     |     | p24     | p27 | p30 | p34 | p37     | p40 | p44 | p47 |                                                                                                                  |     |         |     |     |     |     |     |     |     |     |  |
| 4.0pF               | p18     | p21 |     |     | p24     | p27 | p31 | p34 | p37     | p41 | p44 | p48 |                                                                                                                  |     |         |     |     |     |     |     |     | p52 | p55 |  |
| 5.0pF               | p18     | p21 |     |     | p25     | p28 | p31 | p34 | p38     | p41 | p44 | p48 |                                                                                                                  |     |         |     |     |     |     |     |     | p52 | p55 |  |
| 6.0pF               | p18     | p21 |     |     | p25     | p28 | p31 | p35 | p38     | p41 | p45 | p48 |                                                                                                                  |     |         |     |     |     |     |     |     | p52 | p56 |  |
| 7.0pF               | p19     | p22 |     |     | p25     | p28 | p32 | p35 | p38     | p42 | p45 | p49 |                                                                                                                  |     |         |     |     |     |     |     |     | p53 | p56 |  |
| 8.0pF               | p19     | p22 |     |     | p26     | p29 | p32 | p35 | p39     | p42 | p45 | p49 |                                                                                                                  |     |         |     |     |     |     |     |     | p53 | p56 |  |
| 9.0pF               | p19     | p23 |     |     | p26     | p29 | p32 | p36 | p39     | p42 | p46 | p49 |                                                                                                                  |     |         |     |     |     |     |     |     | p53 | p57 |  |
| 10pF                | p20     | p23 |     |     | p26     | p30 | p33 | p36 | p39     | p43 | p46 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 12pF                | p20     | p23 |     |     | p26     | p30 | p33 | p36 | p40     | p43 | p46 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 15pF                | p20     | p23 |     |     | p26     | p30 | p33 | p36 | p40     | p43 | p46 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 18pF                | p20     | p23 |     |     |         |     | p33 | p36 | p40     | p43 | p46 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 22pF                | p20     | p23 |     |     |         |     | p33 | p36 | p40     | p43 | p46 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 27pF                | p20     | p23 |     |     |         |     | p33 | p36 | p40     | p43 | p46 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 33pF                | p20     | p23 |     |     |         |     | p33 | p36 | p40     | p43 | p46 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 39pF                | p20     | p23 |     |     |         |     | p33 | p36 | p40     | p43 | p46 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 47pF                | p20     | p23 |     |     |         |     | p33 | p36 | p40     | p43 | p46 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 56pF                |         |     | p23 | p23 |         |     | p33 | p36 | p40     | p43 | p46 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 68pF                |         |     | p23 | p23 |         |     | p33 | p36 | p40     | p43 | p46 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 82pF                |         |     | p23 | p23 |         |     | p33 | p36 | p40     | p43 | p46 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 100pF               |         |     | p23 | p23 |         |     | p33 | p36 | p40     | p43 | p46 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 120pF               |         |     |     |     |         |     | p33 | p36 |         |     | p46 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 150pF               |         |     |     |     |         |     |     |     |         |     | p46 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 180pF               |         |     |     |     |         |     |     |     |         |     | p46 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 220pF               |         |     |     |     |         |     |     |     |         |     | p46 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 270pF               |         |     |     |     |         |     |     |     |         |     | p47 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 330pF               |         |     |     |     |         |     |     |     |         |     | p47 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 390pF               |         |     |     |     |         |     |     |     |         |     | p47 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 470pF               |         |     |     |     |         |     |     |     |         |     | p47 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 560pF               |         |     |     |     |         |     |     |     |         |     | p47 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 680pF               |         |     |     |     |         |     |     |     |         |     | p47 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 820pF               |         |     |     |     |         |     |     |     |         |     | p47 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 1000pF              |         |     |     |     |         |     |     |     |         |     | p47 | p50 |                                                                                                                  |     |         |     |     |     |     |     |     | p54 | p57 |  |
| 1200pF              |         |     |     |     |         |     |     |     |         |     |     |     | p50                                                                                                              | p50 | p50     |     |     |     |     |     |     | p54 | p57 |  |
| 1500pF              |         |     |     |     |         |     |     |     |         |     |     |     | p50                                                                                                              | p50 | p50     |     |     |     |     |     |     | p54 | p57 |  |
| 1800pF              |         |     |     |     |         |     |     |     |         |     |     |     | p50                                                                                                              | p50 | p50     |     |     |     |     |     |     |     |     |  |
| 2200pF              |         |     |     |     |         |     |     |     |         |     |     |     | p50                                                                                                              | p50 | p50     | p50 | p51 | p51 |     |     |     |     |     |  |
| 2700pF              |         |     |     |     |         |     |     |     |         |     |     |     | p50                                                                                                              | p50 | p50     | p51 | p51 | p51 |     |     |     |     |     |  |
| 3300pF              |         |     |     |     |         |     |     |     |         |     |     |     | p50                                                                                                              | p50 | p50     | p51 | p51 | p51 |     |     |     |     |     |  |
| 3900pF              |         |     |     |     |         |     |     |     |         |     |     |     | p50                                                                                                              | p50 | p50     | p51 | p51 | p51 |     |     |     |     |     |  |
| 4700pF              |         |     |     |     |         |     |     |     |         |     |     |     | p50                                                                                                              | p50 | p50     | p51 | p51 | p51 |     |     |     |     |     |  |
| 5600pF              |         |     |     |     |         |     |     |     |         |     |     |     |                                                                                                                  |     |         |     |     |     | p51 | p51 | p51 |     |     |  |
| 6800pF              |         |     |     |     |         |     |     |     |         |     |     |     |                                                                                                                  |     |         |     |     |     | p51 | p51 | p51 |     |     |  |
| 8200pF              |         |     |     |     |         |     |     |     |         |     |     |     |                                                                                                                  |     |         |     |     |     | p51 | p51 | p51 |     |     |  |
| 10000pF             |         |     |     |     |         |     |     |     |         |     |     |     |                                                                                                                  |     |         |     |     |     | p51 | p51 | p51 |     |     |  |

The indication for every 0.1 pF has been omitted for less than 10 pF. Refer to the Part Number List for details.



# Capacitance Table

p00 Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series Temperature Compensating Type)

p00 ← Part Number List JIS: CK CJ CH SL UJ EIA: C0G U2J

| LxW (mm)            | 1.6x0.8 |     |     |     |     |     |     |     |     | 2.0x1.25 |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
|---------------------|---------|-----|-----|-----|-----|-----|-----|-----|-----|----------|-----|-----|----|-----|-----|-----|-----|-----|------|-----|-----|-----|-----|--|--|
| T max. (mm)         | 0.9     |     |     |     |     |     |     |     |     | 0.7      |     |     |    |     |     |     |     |     | 0.95 |     |     |     |     |  |  |
| Rated Voltage (Vdc) | 50      |     |     |     |     | 10  |     |     |     | 100      |     | 50  |    |     |     |     |     | 50  |      |     |     |     | 10  |  |  |
| Cap. / TC Code      | C0G     | CΔ  | SL  | U2J | UJ  | SL  | UJ  | U2J | C0G | CH       | C0G | CH  | SL | U2J | UJ  | C0G | CH  | SL  | U2J  | UJ  | SL  | U2J | UJ  |  |  |
| 0.50pF              | p57     | p61 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 1.0pF               | p57     | p61 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 2.0pF               | p58     | p61 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 3.0pF               | p58     | p61 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 4.0pF               | p58     | p62 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 5.0pF               | p59     | p62 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 6.0pF               | p59     | p62 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 7.0pF               | p59     | p63 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 8.0pF               | p60     | p63 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 9.0pF               | p60     | p63 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 10pF                | p60     | p64 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 12pF                | p60     | p64 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 15pF                | p60     | p64 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 18pF                | p60     | p64 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 22pF                | p60     | p64 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 27pF                | p60     | p64 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 33pF                | p60     | p64 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 39pF                | p60     | p64 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 47pF                | p60     | p64 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 56pF                | p60     | p64 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 68pF                | p60     | p64 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 82pF                | p60     | p64 |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 100pF               | p60     | p64 |     |     |     |     |     |     | p65 | p65      |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 120pF               | p61     | p64 |     |     |     |     |     |     | p65 | p65      |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 150pF               | p61     | p64 |     |     |     |     |     |     | p65 | p65      |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 180pF               | p61     | p64 |     |     |     |     |     |     | p65 | p65      |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 220pF               | p61     | p64 |     |     |     |     |     |     | p65 | p65      |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 270pF               | p61     | p64 |     |     |     |     |     |     | p65 | p65      |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 330pF               | p61     | p64 |     |     |     |     |     |     | p65 | p65      |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 390pF               | p61     | p64 |     |     |     |     |     |     | p65 | p65      |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 470pF               | p61     | p64 |     |     |     |     |     |     | p65 | p65      |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 560pF               | p61     | p64 |     |     |     |     |     |     | p65 | p65      |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 680pF               | p61     | p64 |     |     |     |     |     |     | p65 | p65      |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 820pF               | p61     | p64 |     |     |     |     |     |     | p65 | p65      |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 1000pF              | p61     | p64 |     |     | p64 |     |     |     | p65 | p65      |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 1200pF              | p61     | p64 | p64 | p64 | p64 |     |     |     | p65 | p65      | p65 | p65 |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 1500pF              | p61     | p64 | p64 | p64 | p64 |     |     |     | p65 | p65      | p65 | p65 |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 1800pF              | p61     | p64 | p64 | p64 | p64 |     |     |     | p65 | p65      | p65 | p65 |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 2200pF              | p61     | p64 | p64 | p64 | p64 |     |     |     | p65 | p65      | p65 | p65 |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 2700pF              | p61     | p64 | p64 | p64 | p64 |     |     |     | p65 | p65      | p65 | p65 |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 3300pF              | p61     | p64 | p64 | p64 | p64 |     |     |     | p65 | p65      | p65 | p65 |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 3900pF              | p61     | p64 | p64 | p64 | p64 |     |     |     |     |          | p65 | p65 |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 4700pF              | p61     | p64 | p64 | p64 | p64 |     |     |     |     |          | p65 | p65 |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 5600pF              | p61     | p64 | p64 | p64 | p64 |     |     |     |     |          |     |     |    |     |     |     |     | p65 | p65  |     |     |     |     |  |  |
| 6800pF              | p61     | p64 | p64 | p64 | p64 |     |     |     |     |          |     |     |    |     |     |     |     | p65 | p65  |     |     |     |     |  |  |
| 8200pF              | p61     | p64 | p64 | p64 | p64 |     |     |     |     |          |     |     |    |     |     |     |     | p65 | p65  |     |     |     |     |  |  |
| 10000pF             | p61     | p64 | p64 | p64 | p64 |     |     |     |     |          |     |     |    |     |     |     |     | p65 | p65  | p65 |     |     |     |  |  |
| 12000pF             |         |     |     |     |     | p64 | p64 | p65 |     |          |     |     |    | p65 | p65 | p65 | p65 | p65 |      |     |     |     |     |  |  |
| 15000pF             |         |     |     |     |     | p64 | p65 | p65 |     |          |     |     |    | p65 | p65 | p65 | p65 | p65 |      |     |     |     |     |  |  |
| 18000pF             |         |     |     |     |     | p64 | p65 | p65 |     |          |     |     |    | p65 | p65 | p65 |     |     |      |     |     |     |     |  |  |
| 22000pF             |         |     |     |     |     | p64 | p65 | p65 |     |          |     |     |    |     |     |     |     |     | p65  | p65 | p65 |     |     |  |  |
| 27000pF             |         |     |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     | p65  | p65 | p65 |     |     |  |  |
| 33000pF             |         |     |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 39000pF             |         |     |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 47000pF             |         |     |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     |     |     |     |  |  |
| 56000pF             |         |     |     |     |     |     |     |     |     |          |     |     |    |     |     |     |     |     |      |     | p65 | p65 | p65 |  |  |

The indication for every 0.1 pF has been omitted for less than 10 pF. Refer to the Part Number List for details.

# Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series Temperature Compensating Type)

p00

← Part Number List

JIS:

CK

CJ

CH

SL

UJ

EIA:

C0G

U2J

| LxW (mm)            | 2.0x1.25 |     |     |     |     |     |     |      |     |     |     |     |     |     |      |     | 3.2x1.6 |     |     |     |     |     |     |
|---------------------|----------|-----|-----|-----|-----|-----|-----|------|-----|-----|-----|-----|-----|-----|------|-----|---------|-----|-----|-----|-----|-----|-----|
| T max. (mm)         | 1.0      |     |     |     |     |     |     | 1.35 |     |     |     |     |     |     | 1.45 |     | 0.95    |     |     |     |     |     |     |
| Rated Voltage (Vdc) | 250      |     | 200 |     | 50  |     |     | 50   |     |     |     |     | 10  |     |      | 250 | 200     | 100 |     | 50  |     |     |     |
| Cap. / TC Code      | C0G      | U2J | C0G | U2J | SL  | U2J | UJ  | CH   | C0G | SL  | U2J | UJ  | SL  | U2J | UJ   | U2J | U2J     | C0G | CH  | C0G | CH  | SL  | U2J |
| 10pF                | p65      |     | p66 |     |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 12pF                | p65      |     | p66 |     |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 15pF                | p65      |     | p66 |     |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 18pF                | p65      |     | p66 |     |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 22pF                | p65      |     | p66 |     |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 27pF                | p65      |     | p66 |     |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 33pF                | p65      |     | p66 |     |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 39pF                | p65      |     | p66 |     |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 47pF                | p65      |     | p66 |     |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 56pF                | p65      |     | p66 |     |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 68pF                | p65      |     | p66 |     |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 82pF                | p66      |     | p66 |     |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 100pF               | p66      | p66 | p66 | p66 |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 120pF               | p66      | p66 | p66 | p66 |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 150pF               | p66      | p66 | p66 | p66 |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 180pF               | p66      | p66 | p66 | p66 |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 220pF               | p66      | p66 | p66 | p66 |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 270pF               | p66      | p66 | p66 | p66 |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 330pF               | p66      | p66 | p66 | p66 |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 390pF               |          | p66 |     | p66 |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 470pF               |          | p66 |     | p66 |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 560pF               |          | p66 |     | p66 |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 680pF               |          | p66 |     | p66 |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 820pF               |          | p66 |     | p66 |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 1000pF              |          | p66 |     | p66 |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 1200pF              |          | p66 |     | p66 |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 1500pF              |          | p66 |     | p66 |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     |     |     |
| 1800pF              |          | p66 |     | p66 |     |     |     |      |     |     |     |     |     |     |      |     |         | p66 | p67 |     |     |     |     |
| 2200pF              |          | p66 |     | p66 |     |     |     |      |     |     |     |     |     |     |      |     |         | p66 | p67 |     |     |     |     |
| 2700pF              |          |     |     |     |     |     |     |      |     |     |     |     |     |     |      | p66 | p66     | p66 | p67 |     |     |     |     |
| 3300pF              |          |     |     |     |     |     |     |      |     |     |     |     |     |     |      | p66 | p66     | p66 | p67 |     |     |     |     |
| 3900pF              |          |     |     |     |     |     |     |      |     |     |     |     |     |     |      | p66 | p66     | p66 | p67 |     |     |     |     |
| 4700pF              |          |     |     |     |     |     |     |      |     |     |     |     |     |     |      | p66 | p66     | p66 | p67 |     |     |     |     |
| 5600pF              |          |     |     |     |     |     |     |      |     |     |     |     |     |     |      | p66 | p66     | p66 | p67 |     |     |     |     |
| 6800pF              |          |     |     |     |     |     |     |      |     |     |     |     |     |     |      |     |         | p66 | p67 |     |     |     |     |
| 8200pF              |          |     |     |     |     |     |     |      |     |     |     |     |     |     |      |     |         | p66 | p67 |     |     |     |     |
| 10000pF             |          |     |     |     |     |     |     |      |     |     |     |     |     |     |      |     |         | p66 | p67 |     |     |     |     |
| 12000pF             |          |     |     |     |     |     |     |      |     |     |     |     |     |     |      |     |         | p67 | p67 | p67 | p67 |     |     |
| 15000pF             |          |     |     |     |     |     |     |      |     |     |     |     |     |     |      |     |         | p67 | p67 | p67 | p67 |     |     |
| 18000pF             |          |     |     |     |     |     |     | p66  | p66 |     |     |     |     |     |      |     |         | p67 | p67 | p67 | p67 |     |     |
| 22000pF             |          |     |     |     |     |     |     | p66  | p66 |     |     |     |     |     |      |     |         | p67 | p67 | p67 | p67 |     |     |
| 27000pF             |          |     |     |     |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     | p67 | p67 |     |     |
| 33000pF             |          |     |     |     | p66 | p66 | p66 |      |     |     |     |     |     |     |      |     |         |     |     | p67 | p67 |     |     |
| 39000pF             |          |     |     |     |     |     |     |      |     | p66 | p66 | p66 |     |     |      |     |         |     |     | p67 | p67 |     |     |
| 47000pF             |          |     |     |     |     |     |     |      |     | p66 | p66 | p66 |     |     |      |     |         |     |     | p67 | p67 |     |     |
| 56000pF             |          |     |     |     |     |     |     |      |     |     |     |     |     |     |      |     |         |     |     |     |     | p67 | p67 |
| 68000pF             |          |     |     |     |     |     |     |      |     |     | p66 | p66 | p66 |     |      |     |         |     |     |     |     |     |     |
| 82000pF             |          |     |     |     |     |     |     |      |     |     | p66 | p66 | p66 |     |      |     |         |     |     |     |     |     |     |
| 0.10μF              |          |     |     |     |     |     |     |      |     |     | p66 | p66 | p66 |     |      |     |         |     |     |     |     |     |     |



# Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series Temperature Compensating Type)

p00

← Part Number List

JIS:

CK

CJ

CH

SL

UJ

EIA:

C0G

U2J

| LxW (mm)            | 3.2x1.6 |      |      |     |     |     |     |      |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
|---------------------|---------|------|------|-----|-----|-----|-----|------|-----|------|-----|-----|------|-----|-----|-----|-----|------|-----|-----|-----|-----|
| T max. (mm)         | 0.95    | 1.0  |      |     |     |     |     |      |     | 1.25 |     |     |      |     |     |     |     |      |     |     |     | 1.8 |
| Rated Voltage (Vdc) | 50      | 2000 | 1000 | 630 | 500 | 250 | 200 | 1000 | 630 | 500  | 250 | 200 | 1000 | 630 | 500 | 250 | 200 | 1000 | 630 | 500 | 250 | 200 |
| Cap. / TC Code      | UJ      | U2J  | C0G  | U2J | C0G | U2J | C0G | U2J  | U2J | U2J  | U2J | C0G | U2J  | C0G | U2J | U2J | U2J | C0G  | CH  | SL  | U2J | UJ  |
| 10pF                |         | p67  | p67  | p67 | p67 | p67 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 12pF                |         | p67  | p67  | p67 | p67 | p67 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 15pF                |         | p67  | p67  | p67 | p67 | p67 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 18pF                |         | p67  | p67  | p67 | p67 | p67 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 22pF                |         | p67  | p67  | p67 | p67 | p68 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 27pF                |         | p67  | p67  | p67 | p67 | p68 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 33pF                |         | p67  | p67  | p67 | p67 | p68 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 39pF                |         | p67  | p67  | p67 | p67 | p68 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 47pF                |         | p67  | p67  | p67 | p67 | p68 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 56pF                |         | p67  | p67  | p67 | p67 | p68 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 68pF                |         | p67  | p67  | p67 | p67 | p68 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 82pF                |         |      | p67  | p67 | p67 | p68 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 100pF               |         |      | p67  | p67 | p67 | p68 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 120pF               |         |      | p67  | p67 | p67 | p68 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 150pF               |         |      | p67  | p67 | p67 | p68 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 180pF               |         |      | p67  | p67 | p67 | p68 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 220pF               |         |      | p67  | p67 | p67 | p68 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 270pF               |         |      |      | p67 | p67 | p68 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 330pF               |         |      |      | p67 | p67 | p68 | p68 | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 390pF               |         |      |      |     | p67 | p68 | p68 | p68  |     | p68  |     |     |      |     |     |     |     |      |     |     |     |     |
| 470pF               |         |      |      |     | p67 | p68 | p68 | p68  |     | p68  |     |     |      |     |     |     |     |      |     |     |     |     |
| 560pF               |         |      |      |     | p67 | p68 | p68 | p68  |     | p68  |     |     |      |     |     |     |     |      |     |     |     |     |
| 680pF               |         |      |      |     |     | p68 |     | p68  |     | p68  | p68 |     | p68  |     |     |     |     |      |     |     |     |     |
| 820pF               |         |      |      |     |     | p68 |     | p68  |     |      | p68 |     | p68  |     |     |     |     |      |     |     |     | p69 |
| 1000pF              |         |      |      |     |     | p68 |     | p68  |     |      | p68 |     | p68  |     |     |     |     |      |     |     |     | p69 |
| 1200pF              |         |      |      |     |     | p68 |     | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 1500pF              |         |      |      |     |     | p68 |     | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 1800pF              |         |      |      |     |     | p68 |     | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 2200pF              |         |      |      |     |     | p68 |     | p68  |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 2700pF              |         |      |      |     |     |     |     |      | p68 | p68  |     |     | p68  |     | p68 |     |     |      |     |     |     |     |
| 3300pF              |         |      |      |     |     |     |     |      | p68 | p68  |     |     | p68  |     | p68 |     |     |      |     |     |     |     |
| 3900pF              |         |      |      |     |     |     |     |      | p68 | p68  |     |     |      |     |     |     |     |      |     |     |     |     |
| 4700pF              |         |      |      |     |     |     |     |      | p68 | p68  |     |     |      |     |     |     |     |      |     |     |     |     |
| 5600pF              |         |      |      |     |     |     |     |      | p68 | p68  |     |     |      |     |     |     |     |      |     |     |     |     |
| 6800pF              |         |      |      |     |     |     |     |      |     |      |     |     |      |     |     | p68 | p68 |      |     |     |     |     |
| 8200pF              |         |      |      |     |     |     |     |      |     |      |     |     |      |     |     | p68 | p68 |      |     |     |     |     |
| 10000pF             |         |      |      |     |     |     |     |      |     |      |     |     |      |     |     | p68 | p68 |      |     |     |     |     |
| 12000pF             |         |      |      |     |     |     |     |      |     |      |     |     |      |     |     | p68 |     |      |     |     |     |     |
| 15000pF             |         |      |      |     |     |     |     |      |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 18000pF             |         |      |      |     |     |     |     |      |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 22000pF             |         |      |      |     |     |     |     |      |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 27000pF             |         |      |      |     |     |     |     |      |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 33000pF             |         |      |      |     |     |     |     |      |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 39000pF             |         |      |      |     |     |     |     |      |     |      |     |     |      |     |     |     |     |      |     |     |     |     |
| 47000pF             |         |      |      |     |     |     |     |      |     |      |     |     |      |     |     |     |     | p68  | p69 |     |     |     |
| 56000pF             | p67     |      |      |     |     |     |     |      |     |      |     |     |      |     |     |     |     | p69  | p69 |     |     |     |
| 68000pF             |         |      |      |     |     |     |     |      |     |      |     |     |      |     |     |     |     |      |     | p69 | p69 | p69 |
| 82000pF             |         |      |      |     |     |     |     |      |     |      |     |     |      |     |     |     |     |      |     | p69 | p69 | p69 |
| 0.10μF              |         |      |      |     |     |     |     |      |     |      |     |     |      |     |     |     |     |      |     | p69 | p69 | p69 |



# Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series Temperature Compensating Type)

p00

← Part Number List

JIS:

CK

CJ

CH

SL

UJ

EIA:

C0G

U2J

| LxW (mm)            | 3.2x1.6 |     |     |     |     | 3.2x2.5 |     |     |      |      |     |     |      |     |     |     |      |     |     |     | 4.5x2.0 | 4.5x3.2 |     |
|---------------------|---------|-----|-----|-----|-----|---------|-----|-----|------|------|-----|-----|------|-----|-----|-----|------|-----|-----|-----|---------|---------|-----|
| T max. (mm)         | 1.8     |     |     |     |     | 1.0     |     |     | 1.25 |      |     |     | 1.5  |     |     |     | 2.0  |     |     |     | 1.0     | 1.5     |     |
| Rated Voltage (Vdc) | 630     | 500 | 250 | 50  |     | 2000    | 630 | 500 | 2000 | 1000 | 630 | 500 | 1000 | 630 | 500 | 250 | 1000 | 630 | 500 | 250 | 3150    | 1000    | 630 |
| Cap. / TC Code      | U2J     | U2J | U2J | C0G | CH  | U2J     | U2J | U2J | U2J  | U2J  | U2J | U2J | U2J  | U2J | U2J | U2J | U2J  | U2J | U2J | U2J | U2J     | U2J     | U2J |
| 27pF                |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     | p69     |         |     |
| 33pF                |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     | p69     |         |     |
| 39pF                |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     | p69     |         |     |
| 47pF                |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     | p69     |         |     |
| 56pF                |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     | p69     |         |     |
| 68pF                |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     | p69     |         |     |
| 82pF                |         |     |     |     |     | p69     |     |     |      |      |     |     |      |     |     |     |      |     |     |     | p69     |         |     |
| 100pF               |         |     |     |     |     | p69     |     |     |      |      |     |     |      |     |     |     |      |     |     |     | p69     |         |     |
| 120pF               |         |     |     |     |     | p69     |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 150pF               |         |     |     |     |     | p69     |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 180pF               |         |     |     |     |     |         |     |     | p69  |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 220pF               |         |     |     |     |     |         |     |     | p69  |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 270pF               |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 330pF               |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 390pF               |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 470pF               |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 560pF               |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 680pF               |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 820pF               |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 1000pF              |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 1200pF              |         |     |     |     |     | p69     | p69 |     | p69  |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 1500pF              |         |     |     |     |     | p69     | p69 |     |      |      | p69 |     |      |     |     |     |      |     |     |     |         |         |     |
| 1800pF              |         |     |     |     |     | p69     | p69 |     |      |      |     |     |      |     |     |     | p69  |     |     |     |         |         |     |
| 2200pF              |         |     |     |     |     | p69     | p69 |     |      |      |     |     |      |     |     |     | p69  |     |     |     |         |         |     |
| 2700pF              |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         | p69     |     |
| 3300pF              |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         | p69     |     |
| 3900pF              | p69     | p69 |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 4700pF              | p69     | p69 |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 5600pF              |         |     |     |     |     |         |     |     |      | p69  | p69 |     |      |     |     |     |      |     |     |     |         |         |     |
| 6800pF              |         |     |     |     |     |         |     |     |      |      |     |     | p69  | p69 |     |     |      |     |     |     |         |         |     |
| 8200pF              |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     | p69  | p69 |     |     |         |         |     |
| 10000pF             |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     | p69  | p69 |     |     |         |         |     |
| 12000pF             |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         | p69 |
| 15000pF             |         |     | p69 |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 18000pF             |         |     | p69 |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 22000pF             |         |     | p69 |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 27000pF             |         |     |     |     |     |         |     |     |      |      |     |     |      |     | p69 |     |      |     |     |     |         |         |     |
| 33000pF             |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     | p69 |         |         |     |
| 39000pF             |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     | p69 |         |         |     |
| 47000pF             |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     | p69 |         |         |     |
| 56000pF             |         |     |     |     |     |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 68000pF             |         |     |     | p69 | p69 |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 82000pF             |         |     |     | p69 | p69 |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |
| 0.10μF              |         |     |     | p69 | p69 |         |     |     |      |      |     |     |      |     |     |     |      |     |     |     |         |         |     |



## Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

### (→ ■ GRM Series Temperature Compensating Type)

p00 ← Part Number List JIS: CK CJ CH SL UJ EIA: C0G U2J

| LxW (mm)            | 4.5x3.2 |      |     |     | 5.7x5.0 |     |     |      |     |     |
|---------------------|---------|------|-----|-----|---------|-----|-----|------|-----|-----|
| T max. (mm)         | 1.5     | 2.0  |     |     | 1.5     |     |     | 2.0  |     |     |
| Rated Voltage (Vdc) | 500     | 1000 | 630 | 500 | 1000    | 630 | 500 | 1000 | 630 | 500 |
| Cap. / TC Code      | U2J     | U2J  | U2J | U2J | U2J     | U2J | U2J | U2J  | U2J | U2J |
| 3900pF              |         | p69  |     |     |         |     |     |      |     |     |
| 4700pF              |         | p69  |     |     |         |     |     |      |     |     |
| 5600pF              |         |      |     |     | p69     |     |     |      |     |     |
| 6800pF              |         |      |     |     | p69     |     |     |      |     |     |
| 8200pF              |         |      |     |     |         |     |     | p69  |     |     |
| 10000pF             |         |      |     |     |         |     |     | p69  |     |     |
| 12000pF             | p69     |      |     |     |         |     |     |      |     |     |
| 15000pF             |         |      | p69 | p69 |         |     |     |      |     |     |
| 18000pF             |         |      | p69 | p69 |         |     |     |      |     |     |
| 22000pF             |         |      | p69 | p69 |         |     |     |      |     |     |
| 27000pF             |         |      |     |     |         | p69 | p69 |      |     |     |
| 33000pF             |         |      |     |     |         |     |     |      | p69 | p69 |
| 39000pF             |         |      |     |     |         |     |     |      | p69 | p69 |
| 47000pF             |         |      |     |     |         |     |     |      | p69 | p70 |

# Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

## GRM Series High Dielectric Constant Type

p00 ← Part Number List JIS: R B EIA: X7R X7S X7T X7U X6S X6T X5R X5S

| LxW (mm)            | 0.4x0.2 |        |        |     | 0.6x0.3 |     |        |        |        |        |        |        |        |     |        | 1.0x0.5 |        |     |     |     |     |  |
|---------------------|---------|--------|--------|-----|---------|-----|--------|--------|--------|--------|--------|--------|--------|-----|--------|---------|--------|-----|-----|-----|-----|--|
| T max. (mm)         | 0.22    |        |        |     | 0.33    |     |        |        |        |        |        |        |        |     |        | 0.22    |        |     |     |     |     |  |
| Rated Voltage (Vdc) | 10      | 6.3    | 4      |     | 50      | 25  | 16     | 10     | 6.3    | 4      | 10     | 6.3    | 4      | 10  | 6.3    | 4       | 2.5    |     |     |     |     |  |
| Cap. / TC Code      | X7R     | X5R, B | X5R, B | X5R | X7R     | B   | X7R, R | X5R, B | X7R, R | X5R, B | X7R, R | X5R, B | X7R, R | X6S | X5R, B | X6S     | X5R, B | X7T | X6Δ | X5R | X7T |  |
| 100pF               | p71     | p71    | p71    |     | p71     | p72 | p72    |        |        |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 150pF               | p71     | p71    | p71    |     | p72     | p72 | p72    |        |        |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 220pF               | p71     | p71    | p71    |     | p72     | p72 | p72    |        |        |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 330pF               | p71     | p71    | p71    |     | p72     | p72 | p72    |        |        |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 470pF               | p71     | p71    | p71    |     | p72     | p72 | p72    |        |        |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 680pF               | p71     | p71    | p71    |     | p72     | p72 | p72    |        |        |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 820pF               | p71     |        |        |     |         |     |        |        |        |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 1000pF              | p71     | p71    | p71    | p71 | p72     | p72 | p72    | p72    | p72    |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 1500pF              |         | p71    | p71    | p71 | p72     | p72 | p72    | p72    | p72    |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 2200pF              |         | p71    | p71    | p71 |         |     | p72    | p72    | p72    | p72    | p72    |        |        |     |        |         |        |     |     |     |     |  |
| 3300pF              |         | p71    | p71    | p71 |         |     | p72    | p72    | p72    | p72    | p72    |        |        |     |        |         |        |     |     |     |     |  |
| 4700pF              |         | p71    | p71    | p71 |         |     |        | p72    |        |        | p72    | p73    | p73    | p73 | p73    | p73     |        |     |     |     |     |  |
| 6800pF              |         | p71    | p71    | p71 |         |     |        | p72    |        |        | p72    | p73    | p73    | p73 | p73    | p73     |        |     |     |     |     |  |
| 10000pF             |         | p71    | p71    | p71 |         |     | p72    | p72    | p72    | p72    |        | p73    | p73    |     |        |         |        |     |     |     |     |  |
| 15000pF             |         |        | p71    | p71 |         |     |        |        | p72    | p72    |        | p73    | p73    |     | p73    | p73     |        |     |     |     |     |  |
| 22000pF             |         |        | p71    | p71 |         |     |        |        | p72    | p72    |        | p73    | p73    |     | p73    | p73     |        |     |     |     |     |  |
| 33000pF             |         |        | p71    | p71 |         |     |        |        | p72    | p72    |        | p73    | p73    |     | p73    | p73     |        |     |     |     |     |  |
| 47000pF             |         |        | p71    | p71 |         |     |        |        | p72    | p72    |        | p73    | p73    |     | p73    |         |        |     |     |     |     |  |
| 68000pF             |         |        | p71    | p71 |         |     |        |        | p72    | p72    |        | p73    | p73    |     | p73    |         |        |     |     |     |     |  |
| 0.10μF              |         |        | p71    | p71 |         |     |        |        | p72    | p72    |        | p73    | p73    |     | p73    |         | p73    | p73 | p73 | p73 | p73 |  |
| 0.15μF              |         |        |        |     |         |     |        |        |        |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 0.22μF              |         |        |        |     |         |     |        |        |        |        | p73    |        |        | p73 | p73    | p73     | p73    | p73 | p73 | p73 | p73 |  |
| 0.33μF              |         |        |        |     |         |     |        |        |        |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 0.47μF              |         |        |        |     |         |     |        |        |        |        |        |        |        |     |        |         |        | p73 | p73 |     | p73 |  |
| 0.68μF              |         |        |        |     |         |     |        |        |        |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 1.0μF               |         |        |        |     |         |     |        |        |        |        |        |        |        |     |        |         |        | p73 |     | p73 | p73 |  |
| 2.2μF               |         |        |        |     |         |     |        |        |        |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 4.7μF               |         |        |        |     |         |     |        |        |        |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 10μF                |         |        |        |     |         |     |        |        |        |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 22μF                |         |        |        |     |         |     |        |        |        |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 47μF                |         |        |        |     |         |     |        |        |        |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 100μF               |         |        |        |     |         |     |        |        |        |        |        |        |        |     |        |         |        |     |     |     |     |  |
| 150μF               |         |        |        |     |         |     |        |        |        |        |        |        |        |     |        |         |        |     |     |     |     |  |



# Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00

← Part Number List

JIS:

R

B

EIA:

X7R

X7S

X7T

X7U

X6S

X6T

X5R

X5S

| LxW (mm)            | 1.0x0.5 |     |     |     |     |      |     |        |     |        |      |     |         |        |        |        |        |        |     |        |
|---------------------|---------|-----|-----|-----|-----|------|-----|--------|-----|--------|------|-----|---------|--------|--------|--------|--------|--------|-----|--------|
| T max. (mm)         | 0.3     |     |     |     |     | 0.33 |     |        |     |        | 0.55 |     |         |        |        |        |        |        |     |        |
| Rated Voltage (Vdc) | 50      | 25  | 16  | 10  | 10  | 6.3  | 4   | 100    | 50  | 25     | 16   | 10  | 6.3     | 100    | 50     | 25     | 16     | 10     | 6.3 | 100    |
| Cap. / TC Code      | X7R, R  | B   | X7R | B   | X7R | B    | X5R | X5R, B | X6T | X5R, B | X6T  | X7R | X7R, R  | X5R, B | X7R, R | X5R, B | X7R, R | X5R, B | X6S | X5R, B |
| 100pF               |         |     |     |     |     |      |     |        |     |        |      |     |         |        |        |        |        |        |     |        |
| 150pF               |         |     |     |     |     |      |     |        |     |        |      |     |         |        |        |        |        |        |     |        |
| 220pF               | p74 p73 | p74 |     |     |     |      |     |        |     |        |      | p74 | p74 p74 | p74    |        |        |        |        |     |        |
| 330pF               | p74 p73 | p74 |     |     |     |      |     |        |     |        |      | p74 | p74 p74 | p74    |        |        |        |        |     |        |
| 470pF               | p74 p73 | p74 |     |     |     |      |     |        |     |        |      | p74 | p74 p74 | p74    |        |        |        |        |     |        |
| 680pF               | p74 p74 | p74 |     |     |     |      |     |        |     |        |      | p74 | p74 p74 | p74    |        |        |        |        |     |        |
| 820pF               |         |     |     |     |     |      |     |        |     |        |      |     |         |        |        |        |        |        |     |        |
| 1000pF              | p74 p74 | p74 |     |     |     |      |     |        |     |        |      | p74 | p74 p74 | p75    |        |        |        |        |     |        |
| 1500pF              | p74 p74 | p74 |     |     |     |      |     |        |     |        |      | p74 | p74 p74 | p75    |        |        |        |        |     |        |
| 2200pF              |         |     | p74 | p74 |     |      |     |        |     |        |      | p74 | p74 p74 | p75    |        |        |        |        |     |        |
| 3300pF              |         |     |     |     | p74 | p74  |     |        |     |        |      | p74 | p74 p74 | p75    |        |        |        |        |     |        |
| 4700pF              |         |     |     |     | p74 | p74  |     |        |     |        |      | p74 | p74 p74 | p75    |        |        |        |        |     |        |
| 6800pF              |         |     |     |     | p74 | p74  |     |        |     |        |      |     | p74     | p75    | p75    |        |        |        |     |        |
| 10000pF             |         |     |     |     | p74 | p74  |     |        |     |        |      |     | p74     | p75    | p75    | p75    |        |        |     |        |
| 15000pF             |         |     |     |     |     |      | p74 |        |     |        |      |     | p74     | p75    | p75    | p75    | p75    |        |     |        |
| 22000pF             |         |     |     |     |     |      | p74 |        |     |        |      |     | p74     | p75    | p75    | p75    | p75    |        |     |        |
| 33000pF             |         |     |     |     |     |      | p74 |        |     |        |      |     | p74     | p75    | p75    | p75    | p75    |        |     |        |
| 47000pF             |         |     |     |     |     |      |     |        |     |        |      |     | p74     | p75    | p75    | p75    | p75    |        |     |        |
| 68000pF             |         |     |     |     |     |      |     |        |     |        |      |     | p74     | p75    | p75    | p75    | p75    | p75    |     |        |
| 0.10μF              |         |     |     |     |     |      |     |        |     |        |      |     | p74     | p75    | p75    | p75    | p75    |        |     |        |
| 0.15μF              |         |     |     |     |     |      |     |        |     |        |      |     |         |        |        |        | p75    |        | p75 | p76    |
| 0.22μF              |         |     |     |     |     |      |     |        |     |        |      |     |         |        |        |        | p75    | p75    |     | p75    |
| 0.33μF              |         |     |     |     |     |      |     |        |     |        |      |     |         |        |        |        |        | p75    |     | p75    |
| 0.47μF              |         |     |     |     |     |      |     |        |     |        |      |     |         |        |        |        | p75    |        |     | p75    |
| 0.68μF              |         |     |     |     |     |      |     |        |     |        |      |     |         |        |        |        |        | p75    |     | p75    |
| 1.0μF               |         |     |     |     |     |      |     | p74    | p74 | p74    | p74  | p74 |         |        | p75    | p75    |        | p75    |     |        |
| 2.2μF               |         |     |     |     |     |      |     |        |     |        |      |     |         |        |        |        |        | p75    |     | p75    |
| 4.7μF               |         |     |     |     |     |      |     |        |     |        |      |     |         |        |        |        |        |        | p75 | p76    |
| 10μF                |         |     |     |     |     |      |     |        |     |        |      |     |         |        |        |        |        |        |     |        |
| 22μF                |         |     |     |     |     |      |     |        |     |        |      |     |         |        |        |        |        |        |     |        |
| 47μF                |         |     |     |     |     |      |     |        |     |        |      |     |         |        |        |        |        |        |     |        |
| 100μF               |         |     |     |     |     |      |     |        |     |        |      |     |         |        |        |        |        |        |     |        |
| 150μF               |         |     |     |     |     |      |     |        |     |        |      |     |         |        |        |        |        |        |     |        |





# Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00

← Part Number List

JIS:

R

B

EIA:

X7R

X7S

X7T

X7U

X6S

X6T

X5R

X5S

| LxW (mm)            | 1.0x0.5 |     |     |     |        |        |     |     |     |     |     |     |     |     | 1.6x0.8 |        |     |     |     |        |        |        |
|---------------------|---------|-----|-----|-----|--------|--------|-----|-----|-----|-----|-----|-----|-----|-----|---------|--------|-----|-----|-----|--------|--------|--------|
| T max. (mm)         | 0.55    | 0.6 |     |     |        |        |     | 0.7 |     |     |     |     |     |     | 0.5     |        | 0.9 |     |     |        |        |        |
| Rated Voltage (Vdc) | 4       | 35  | 25  | 16  | 6.3    | 4      | 2.5 | 25  | 16  | 10  | 6.3 | 4   | 2.5 | 25  | 16      | 250    | 200 | 100 | 50  | 25     |        |        |
| Cap. / TC Code      | X7R     | X5R | X6S | X6S | X5R, B | X5R, B | X6T | X5R | X6S | X5R | X7S | X6S | X7S | X5R | X5R, B  | X5R, B | X7R | X7R | X7R | X7R, R | X5R, B | X7R, R |
| 100pF               |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     |     |        |        |        |
| 150pF               |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     |     |        |        |        |
| 220pF               |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        | p76 | p76 | p76 | p76    | p77    |        |
| 330pF               |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        | p76 | p76 | p76 | p76    | p77    |        |
| 470pF               |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        | p76 | p76 | p76 | p76    | p77    |        |
| 680pF               |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        | p76 | p76 | p76 | p76    | p77    |        |
| 820pF               |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     |     |        |        |        |
| 1000pF              |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        | p76 | p76 | p76 | p76    | p77    |        |
| 1500pF              |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        | p76 | p76 | p76 | p76    | p77    |        |
| 2200pF              |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        | p76 | p76 | p76 | p76    | p77    |        |
| 3300pF              |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     | p76 | p76    | p77    |        |
| 4700pF              |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     | p76 | p76    | p77    |        |
| 6800pF              |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     | p76 | p76    | p77    |        |
| 10000pF             |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     | p76 | p76    | p77    |        |
| 15000pF             |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     | p76 | p76    | p77    |        |
| 22000pF             |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     | p76 | p76    | p77    |        |
| 33000pF             |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     |     | p76    | p77    |        |
| 47000pF             |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     |     | p76    | p77    |        |
| 68000pF             |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     |     | p76    | p77    |        |
| 0.10μF              |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     |     | p76    | p77    |        |
| 0.15μF              |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     |     |        |        | p77    |
| 0.22μF              |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     |     |        |        | p77    |
| 0.33μF              |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     |     |        |        |        |
| 0.47μF              |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     |     |        |        | p77    |
| 0.68μF              |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     |     |        |        |        |
| 1.0μF               | p76     | p76 | p76 | p76 |        |        |     |     | p76 | p76 | p76 | p76 | p76 |     |         | p76    | p76 | p76 |     |        | p77    | p77    |
| 2.2μF               |         |     |     |     |        |        |     |     | p76 | p76 | p76 | p76 | p76 |     |         |        |     |     |     |        |        |        |
| 4.7μF               |         |     |     |     | p76    | p76    | p76 | p76 |     |     |     |     |     |     |         |        |     |     |     |        |        |        |
| 10μF                |         |     |     |     |        |        |     |     |     |     |     |     |     | p76 | p76     |        |     |     |     |        |        |        |
| 22μF                |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     |     |        |        |        |
| 47μF                |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     |     |        |        |        |
| 100μF               |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     |     |        |        |        |
| 150μF               |         |     |     |     |        |        |     |     |     |     |     |     |     |     |         |        |     |     |     |        |        |        |



# Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00

← Part Number List

JIS:

R

B

EIA:

X7R

X7S

X7T

X7U

X6S

X6T

X5R

X5S

| LxW (mm)            | 1.6x0.8 |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
|---------------------|---------|--------|-----|--------|-----|--------|-----|------|-----|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--------|
| T max. (mm)         | 0.9     |        |     |        |     |        |     | 0.95 |     |        |     |     | 1.0 |     |     |     |     |     |     |     |     |        |
| Rated Voltage (Vdc) | 25      | 16     |     |        | 10  |        | 6.3 | 25   | 16  |        | 10  |     | 50  | 35  | 25  |     |     | 16  |     | 10  | 6.3 |        |
| Cap. / TC Code      | X5R, B  | X7R, R | X6S | X5R, B | X7Δ | X5R, B | B   | X5R  | X6S | X5R, B | X7S | B   | X5R | X6S | X5R | X7S | X6S | X5R | X7S | X6S | X7T | X5R, B |
| 100pF               |         |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 150pF               |         |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 220pF               |         |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 330pF               |         |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 470pF               |         |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 680pF               |         |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 820pF               |         |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 1000pF              |         |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 1500pF              |         |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 2200pF              |         |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 3300pF              |         |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 4700pF              |         |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 6800pF              |         |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 10000pF             | p77     |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 15000pF             | p77     |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 22000pF             | p77     |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 33000pF             | p77     |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 47000pF             | p77     |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 68000pF             | p77     |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 0.10μF              | p77     |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 0.15μF              | p77     | p77    |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 0.22μF              | p77     | p77    | p77 |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 0.33μF              |         | p77    | p77 |        | p77 | p78    | p78 |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 0.47μF              | p77     | p77    | p77 | p77    |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 0.68μF              | p77     | p77    |     |        | p77 | p78    | p78 |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 1.0μF               | p77     | p77    | p77 |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 2.2μF               | p77     | p77    |     | p77    | p77 | p78    | p78 |      |     |        |     |     | p78 | p78 |     | p78 | p78 |     | p78 |     |     |        |
| 4.7μF               |         |        |     |        |     |        |     | p78  | p78 | p78    | p78 | p78 |     |     | p78 |     | p78 |     |     |     |     |        |
| 10μF                |         |        |     |        |     |        | p78 |      |     | p78    |     | p78 |     |     |     |     | p78 |     | p78 | p78 | p78 |        |
| 22μF                |         |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     | p78    |
| 47μF                |         |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     | p78    |
| 100μF               |         |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |
| 150μF               |         |        |     |        |     |        |     |      |     |        |     |     |     |     |     |     |     |     |     |     |     |        |



# Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00 ← Part Number List JIS: R B EIA: X7R X7S X7T X7U X6S X6T X5R X5S

| LxW (mm)            | 1.6x0.8 |        | 2.0x1.25 |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
|---------------------|---------|--------|----------|------|--------|--------|-----|-----|--------|-----|--------|--------|-----|--------|-----|--------|-----|--------|-----|-----|-----|-----|-----|--|-----|
| T max. (mm)         | 1.0     |        | 0.7      | 0.95 |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  | 1.0 |
| Rated Voltage (Vdc) | 4       |        | 16       | 100  | 50     | 35     | 25  | 16  | 10     | 6.3 | 4      | 2.5    | 250 | 200    |     |        |     |        |     |     |     |     |     |  |     |
| Cap. / TC Code      | X6S     | X5R, B | X6S      | X7R  | X7R, R | X5R, B | X6S | X5R | X7R, R | X6S | X5R, B | X7R, R | X6S | X5R, B | X7Δ | X5R, B | X6S | X5R, B | X6S | X5R | X6T | X7R | X7R |  |     |
| 100pF               |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 150pF               |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 220pF               |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 330pF               |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 470pF               |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 680pF               |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 820pF               |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 1000pF              |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 1500pF              |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 2200pF              |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 3300pF              |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 4700pF              |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 6800pF              |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 10000pF             |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 15000pF             |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 22000pF             |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 33000pF             |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 47000pF             |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 68000pF             |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 0.10μF              |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 0.15μF              |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 0.22μF              |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 0.33μF              |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 0.47μF              |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 0.68μF              |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 1.0μF               |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 2.2μF               |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 4.7μF               |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 10μF                |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 22μF                |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 47μF                |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 100μF               |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |
| 150μF               |         |        |          |      |        |        |     |     |        |     |        |        |     |        |     |        |     |        |     |     |     |     |     |  |     |



# Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00

← Part Number List

JIS:

R

B

EIA:

X7R

X7S

X7T

X7U

X6S

X6T

X5R

X5S

| LxW (mm)            | 2.0x1.25 |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
|---------------------|----------|-----|------|--------|-----|-----|-----|--------|-----|--------|--------|--------|--------|-----|-----|-----|---|-----|-----|-----|------|-----|-----|
| T max. (mm)         | 1.0      |     | 1.35 |        |     |     |     |        |     |        | 1.4    |        |        |     |     |     |   |     |     |     | 1.45 |     |     |
| Rated Voltage (Vdc) | 50       | 16  | 100  | 50     |     | 25  |     |        | 16  |        | 50     | 25     |        | 16  |     | 10  |   | 6.3 |     | 4   |      | 250 | 200 |
| Cap. / TC Code      | X7R      | X5R | X7R  | X7R, R | B   | R   | X6S | X5R, B | X7R | X5R, B | X5R, B | X7R, R | X5R, B | X7R | X6S | X7R | B | X7R | X6S | X7U | X6S  | X7R | X7R |
| 100pF               |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 150pF               |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 220pF               |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 330pF               |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 470pF               |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 680pF               |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 820pF               |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 1000pF              |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 1500pF              |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 2200pF              |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 3300pF              |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 4700pF              |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 6800pF              |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 10000pF             |          |     | p79  |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      | p79 | p79 |
| 15000pF             |          |     | p79  |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      | p79 | p79 |
| 22000pF             | p79      |     | p79  |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      | p79 | p79 |
| 33000pF             |          |     | p79  |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 47000pF             |          |     | p79  | p79    |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 68000pF             |          |     | p79  | p79    |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 0.10μF              |          |     | p79  | p79    | p79 |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 0.15μF              |          |     |      | p79    | p79 | p79 |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 0.22μF              |          |     |      | p79    | p79 |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 0.33μF              |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 0.47μF              |          |     |      | p79    | p79 |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 0.68μF              |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 1.0μF               |          |     |      |        |     |     |     |        |     |        |        |        | p79    | p79 |     |     |   |     |     |     |      |     |     |
| 2.2μF               |          |     |      |        |     |     |     | p79    | p79 |        |        | p79    | p79    |     |     |     |   |     |     |     |      |     |     |
| 4.7μF               |          |     |      |        |     |     | p79 | p79    | p79 |        |        | p79    | p79    | p79 |     | p79 |   | p79 |     |     |      |     |     |
| 10μF                |          |     |      |        |     |     |     |        |     | p79    | p79    |        |        |     | p79 | p79 |   |     | p79 |     |      |     |     |
| 22μF                |          | p79 |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   | p79 |     | p79 | p79  | p79 |     |
| 47μF                |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 100μF               |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |
| 150μF               |          |     |      |        |     |     |     |        |     |        |        |        |        |     |     |     |   |     |     |     |      |     |     |



## Capacitance Table

*p00*

Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

*p00*

← Part Number List

JIS:

R

B

EIA:

X7R

X7

S X

K7T

X7U

X6S

X6

ST X

5R

[illegible]

# Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00

← Part Number List

JIS:

R

B

EIA:

X7R

X7S

X7T

X7U

X6S

X6T

X5R

X5S

| LxW (mm)            | 3.2x1.6 |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
|---------------------|---------|-----|-----|-----|-----|------|-----|-----|-----|-----|-----|--------|-----|--------|-----|-----|--------|-----|--------|-----|-----|--------|-----|
| T max. (mm)         | 1.25    |     |     |     |     | 1.8  |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| Rated Voltage (Vdc) | 250     | 200 | 50  |     | 25  | 1000 | 630 | 500 | 250 | 200 | 50  | 25     |     | 16     |     |     | 10     |     |        | 6.3 |     |        | 4   |
| Cap. / TC Code      | X7R     | X7R | X7R | B   | X5R | X7R  | X7R | X7R | X7R | X7R | X7R | X5R, B | X7R | X5R, B | X7R | X6S | X5R, B | X7R | X5R, B | X7Δ | X6S | X5R, B | X7U |
| 100pF               |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 150pF               |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 220pF               |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 330pF               |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 470pF               |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 680pF               |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 820pF               |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 1000pF              |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 1500pF              |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 2200pF              |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 3300pF              |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 4700pF              |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 6800pF              |         |     |     |     |     | p80  |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 10000pF             |         |     |     |     |     | p80  |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 15000pF             | p80     | p80 |     |     |     |      | p80 | p80 |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 22000pF             | p80     | p80 |     |     |     |      | p80 | p80 |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 33000pF             |         |     |     |     |     |      |     |     | p80 | p80 |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 47000pF             |         |     |     |     |     |      |     |     | p80 | p80 |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 68000pF             | p80     | p80 |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 0.10μF              |         |     |     |     |     |      |     |     | p80 | p80 |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 0.15μF              |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 0.22μF              |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 0.33μF              |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 0.47μF              |         |     | p80 |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 0.68μF              |         |     | p80 |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 1.0μF               |         |     | p80 | p80 |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 2.2μF               |         |     |     |     |     |      |     |     |     |     | p80 | p80    |     |        |     |     |        |     |        |     |     |        |     |
| 4.7μF               |         |     |     |     |     |      |     |     |     |     | p80 | p80    | p80 |        | p80 |     |        |     |        |     |     |        |     |
| 10μF                |         |     |     |     | p80 |      |     |     |     |     |     | p80    | p80 | p80    | p80 |     |        |     |        |     |     |        |     |
| 22μF                |         |     |     |     |     |      |     |     |     |     |     | p80    | p80 |        | p80 | p80 | p80    | p81 |        | p81 |     |        |     |
| 47μF                |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     | p81    | p81 | p81 | p81    | p81 |
| 100μF               |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |
| 150μF               |         |     |     |     |     |      |     |     |     |     |     |        |     |        |     |     |        |     |        |     |     |        |     |



# Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00

← Part Number List

JIS:

R

B

EIA:

X7R

X7S

X7T

X7U

X6S

X6T

X5R

X5S

| LxW (mm)            | 3.2x1.6 |     |     |     |     |     | 3.2x2.5 |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
|---------------------|---------|-----|-----|-----|-----|-----|---------|-----|-----|-----|-----|-----|-----|-----|------|-----|-----|-----|-----|-----|-----|
| T max. (mm)         | 1.8     | 1.9 |     |     |     |     | 1.5     |     |     |     |     | 1.8 |     |     | 2.0  |     |     |     |     | 2.2 | 2.7 |
| Rated Voltage (Vdc) | 4       | 100 | 6.3 | 4   |     |     | 1000    | 630 | 500 | 250 | 200 | 6.3 | 4   | 2.5 | 1000 | 630 | 500 | 250 | 200 | 25  | 80  |
| Cap. / TC Code      | X6S     | X7R | X6T | X5R | X7U | X6T | X5R     | X7R | X7R | X7R | X7R | X5S | X6T | X5S | X6T  | X7R | X7R | X7R | X7R | X7R | X7R |
| 100pF               |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 150pF               |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 220pF               |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 330pF               |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 470pF               |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 680pF               |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 820pF               |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 1000pF              |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 1500pF              |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 2200pF              |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 3300pF              |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 4700pF              |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 6800pF              |         |     |     |     |     |     |         | p81 |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 10000pF             |         |     |     |     |     |     |         | p81 |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 15000pF             |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      | p81 |     |     |     |     |     |
| 22000pF             |         |     |     |     |     |     |         |     | p81 | p81 |     |     |     |     |      | p81 |     |     |     |     |     |
| 33000pF             |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     | p81 | p81 |     |     |     |
| 47000pF             |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     | p81 | p81 |     |     |     |
| 68000pF             |         |     |     |     |     |     |         |     |     | p81 | p81 |     |     |     |      |     |     |     |     |     |     |
| 0.10μF              |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     | p81 | p81 |     |     |
| 0.15μF              |         |     |     |     |     |     |         |     |     | p81 | p81 |     |     |     |      |     |     |     |     |     |     |
| 0.22μF              |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     | p81 | p81 |     |     |
| 0.33μF              |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 0.47μF              |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 0.68μF              |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 1.0μF               |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 2.2μF               |         | p81 |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 4.7μF               |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     | p81 |
| 10μF                |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     | p81 |     |
| 22μF                |         |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 47μF                | p81     |     |     |     |     |     |         |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 100μF               |         |     | p81 | p81 | p81 | p81 | p81     |     |     |     |     |     |     |     |      |     |     |     |     |     |     |
| 150μF               |         |     |     |     |     |     |         |     |     |     |     | p81 | p81 | p81 | p81  |     |     |     |     |     |     |



# Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00

← Part Number List

JIS:

R

B

EIA:

X7R

X7S

X7T

X7U

X6S

X6T

X5R

X5S

| LxW (mm)            | 3.2x2.5 |     |        |     |        |     |        |     |     |        |     |        | 4.5x3.2 |        |     |     |     |     |     |     |
|---------------------|---------|-----|--------|-----|--------|-----|--------|-----|-----|--------|-----|--------|---------|--------|-----|-----|-----|-----|-----|-----|
| T max. (mm)         | 2.7     |     |        |     |        |     |        |     |     |        |     |        | 1.5     |        |     |     | 2.0 |     |     |     |
| Rated Voltage (Vdc) | 63      | 50  | 35     | 25  | 16     | 10  | 6.3    | 4   | 630 | 500    | 250 | 200    | 1000    | 630    | 500 | 250 | 630 | 500 | 250 | 250 |
| Cap. / TC Code      | X7R     | X7R | X5R, B | X7R | X5R, B | X7R | X5R, B | X7R | X6S | X5R, B | X7R | X5R, B | X7Δ     | X5R, B | X7U | X7R | X7R | X7R | X7R | X7R |
| 100pF               |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 150pF               |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 220pF               |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 330pF               |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 470pF               |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 680pF               |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 820pF               |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 1000pF              |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 1500pF              |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 2200pF              |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 3300pF              |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 4700pF              |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 6800pF              |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 10000pF             |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 15000pF             |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 22000pF             |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 33000pF             |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 47000pF             |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 68000pF             |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 0.10μF              |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 0.15μF              |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 0.22μF              |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 0.33μF              |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 0.47μF              |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 0.68μF              |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 1.0μF               |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 2.2μF               |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 4.7μF               |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 10μF                |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 22μF                |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 47μF                |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 100μF               |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |
| 150μF               |         |     |        |     |        |     |        |     |     |        |     |        |         |        |     |     |     |     |     |     |





## Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

(→ ■ GRM Series High Dielectric Constant Type)

p00

← Part Number List

JIS:

R

B

EIA:

X7R

X7S

X7T

X7U

X6S

X6T

X5R

X5S

| LxW (mm)            | 4.5x3.2 | 5.7x5.0 |     |     |     |     |
|---------------------|---------|---------|-----|-----|-----|-----|
| T max. (mm)         | 2.0     | 2.0     |     |     |     |     |
| Rated Voltage (Vdc) | 200     | 1000    | 630 | 500 | 250 | 200 |
| Cap. / TC Code      | X7R     | X7R     | X7R | X7R | X7R | X7R |
| 100pF               |         |         |     |     |     |     |
| 150pF               |         |         |     |     |     |     |
| 220pF               |         |         |     |     |     |     |
| 330pF               |         |         |     |     |     |     |
| 470pF               |         |         |     |     |     |     |
| 680pF               |         |         |     |     |     |     |
| 820pF               |         |         |     |     |     |     |
| 1000pF              |         |         |     |     |     |     |
| 1500pF              |         |         |     |     |     |     |
| 2200pF              |         |         |     |     |     |     |
| 3300pF              |         |         |     |     |     |     |
| 4700pF              |         |         |     |     |     |     |
| 6800pF              |         |         |     |     |     |     |
| 10000pF             |         |         |     |     |     |     |
| 15000pF             |         |         |     |     |     |     |
| 22000pF             |         |         |     |     |     |     |
| 33000pF             |         |         |     |     |     |     |
| 47000pF             |         |         |     |     |     |     |
| 68000pF             |         | p81     |     |     |     |     |
| 0.10μF              |         | p81     |     |     |     |     |
| 0.15μF              |         |         | p81 | p81 |     |     |
| 0.22μF              | p81     |         | p81 | p81 |     |     |
| 0.33μF              | p81     |         |     |     | p82 | p82 |
| 0.47μF              | p81     |         |     |     | p82 | p82 |
| 0.68μF              |         |         |     |     | p82 | p82 |
| 1.0μF               |         |         |     |     | p82 | p82 |
| 2.2μF               |         |         |     |     |     |     |
| 4.7μF               |         |         |     |     |     |     |
| 10μF                |         |         |     |     |     |     |
| 22μF                |         |         |     |     |     |     |
| 47μF                |         |         |     |     |     |     |
| 100μF               |         |         |     |     |     |     |
| 150μF               |         |         |     |     |     |     |

## Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

### ■ GJM Series Temperature Compensating Type

p00

← Part Number List

JIS:

CK

CJ

CH

EIA:

C0G

| L×W (mm)            | 0.4×0.2 |     | 0.6×0.3 |     | 1.0×0.5 |      |
|---------------------|---------|-----|---------|-----|---------|------|
| T max. (mm)         | 0.22    |     | 0.33    |     | 0.55    |      |
| Rated Voltage (Vdc) | 25      |     | 25      |     | 50      |      |
| Cap. / TC Code      | C0G     | CΔ  | C0G     | CΔ  | C0G     | CΔ   |
| 0.10pF              |         |     |         |     | p97     | p100 |
| 0.20pF              | p84     | p87 | p90     | p93 | p97     | p100 |
| 1.0pF               | p84     | p87 | p90     | p94 | p97     | p101 |
| 2.0pF               | p84     | p87 | p91     | p94 | p97     | p101 |
| 3.0pF               | p84     | p87 | p91     | p94 | p98     | p101 |
| 4.0pF               | p85     | p88 | p91     | p94 | p98     | p101 |
| 5.0pF               | p85     | p88 | p91     | p95 | p98     | p102 |
| 6.0pF               | p85     | p88 | p92     | p95 | p98     | p102 |
| 7.0pF               | p86     | p89 | p92     | p95 | p99     | p102 |
| 8.0pF               | p86     | p89 | p92     | p96 | p99     | p103 |
| 9.0pF               | p86     | p90 | p93     | p96 | p100    | p103 |
| 10pF                | p87     | p90 | p93     | p97 | p100    | p103 |
| 11pF                | p87     | p90 | p93     | p97 | p100    | p103 |
| 12pF                | p87     | p90 | p93     | p97 | p100    | p104 |
| 13pF                | p87     | p90 | p93     | p97 | p100    | p104 |
| 15pF                | p87     | p90 | p93     | p97 | p100    | p104 |
| 16pF                | p87     | p90 | p93     | p97 | p100    | p104 |
| 18pF                | p87     | p90 | p93     | p97 | p100    | p104 |
| 20pF                | p87     | p90 | p93     | p97 | p100    | p104 |
| 22pF                | p87     | p90 | p93     | p97 | p100    | p104 |
| 24pF                |         |     | p93     | p97 | p100    | p104 |
| 27pF                |         |     | p93     | p97 | p100    | p104 |
| 30pF                |         |     | p93     | p97 | p100    | p104 |
| 33pF                |         |     | p93     | p97 | p100    | p104 |
| 36pF                |         |     |         |     | p100    | p104 |
| 39pF                |         |     |         |     | p100    | p104 |
| 43pF                |         |     |         |     | p100    | p104 |
| 47pF                |         |     |         |     | p100    | p104 |

The indication for every 0.1 pF has been omitted for less than 10 pF. Refer to the Part Number List for details.

# Capacitance Table

Each number in the Part Number List refers to the page number printed at the bottom of the page.

## GMA Series High Dielectric Constant Type

p00 ← Part Number List JIS: R B EIA: X7R X5R

| LxW (mm)            | 0.38x0.38 |      | 0.5x0.5 |      |      |      |      |      |      |      | 0.8x0.8 |      |      |      |      |      |      |      |
|---------------------|-----------|------|---------|------|------|------|------|------|------|------|---------|------|------|------|------|------|------|------|
| T max. (mm)         | 0.35      |      | 0.4     |      |      |      |      |      |      |      | 0.6     |      |      |      |      |      |      |      |
| Rated Voltage (Vdc) | 10        |      | 100     | 25   |      | 10   |      |      | 6.3  |      | 100     | 25   |      | 10   |      |      | 6.3  |      |
| Cap. / TC Code      | X7R       | R    | X7R     | X7R  | B    | X7R  | R    | B    | X5R  | B    | X7R     | X7R  | B    | X7R  | R    | B    | X5R  | B    |
| 100pF               |           |      | p106    |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |
| 150pF               |           |      | p106    |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |
| 220pF               |           |      | p106    |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |
| 330pF               |           |      | p106    |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |
| 470pF               |           |      | p106    |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |
| 680pF               |           |      | p106    |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |
| 1000pF              |           |      | p106    |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |
| 1500pF              |           |      |         | p106 | p106 |      |      |      |      |      | p106    |      |      |      |      |      |      |      |
| 2200pF              |           |      |         | p106 | p106 |      |      |      |      |      | p106    |      |      |      |      |      |      |      |
| 3300pF              |           |      |         | p106 | p106 |      |      |      |      |      | p106    |      |      |      |      |      |      |      |
| 4700pF              |           |      |         | p106 | p106 |      |      |      |      |      | p106    |      |      |      |      |      |      |      |
| 6800pF              |           |      |         |      |      | p106 | p106 | p106 |      |      | p106    |      |      |      |      |      |      |      |
| 10000pF             | p106      | p106 |         |      |      | p106 | p106 | p106 |      |      |         | p106 | p106 |      |      |      |      |      |
| 15000pF             |           |      |         |      |      | p106 | p106 | p106 |      |      |         | p106 | p106 |      |      |      |      |      |
| 22000pF             |           |      |         |      |      | p106 | p106 | p106 |      |      |         | p106 | p106 |      |      |      |      |      |
| 33000pF             |           |      |         |      |      |      |      |      |      |      |         |      |      | p106 | p106 | p106 |      |      |
| 47000pF             |           |      |         |      |      |      |      |      |      |      |         |      |      | p106 | p106 | p106 |      |      |
| 68000pF             |           |      |         |      |      |      |      |      |      |      |         |      |      | p106 | p106 | p106 |      |      |
| 0.10μF              |           |      |         |      |      |      |      |      | p106 | p106 |         |      |      | p106 | p106 | p106 |      |      |
| 0.47μF              |           |      |         |      |      |      |      |      |      |      |         |      |      |      |      |      | p106 | p106 |

## Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

### ■ GMD Series High Dielectric Constant Type

p00

← Part Number List

JIS:

R

B

EIA:

X7R

X5R

| LxW (mm)            | 0.6x0.3 |      |      |      |      |      |      |      |      |      | 1.0x0.5 |      |      |      |      |      |      |      |      |      |      |      |
|---------------------|---------|------|------|------|------|------|------|------|------|------|---------|------|------|------|------|------|------|------|------|------|------|------|
| T max. (mm)         | 0.33    |      |      |      |      |      |      |      |      |      | 0.55    |      |      |      |      |      |      |      |      |      |      |      |
| Rated Voltage (Vdc) | 25      |      |      | 16   |      |      | 10   |      |      | 6.3  |         | 50   |      |      | 25   |      |      | 16   |      |      | 10   |      |
| Cap. / TC Code      | X7R     | R    | B    | X7R  | R    | B    | X7R  | R    | B    | X5R  | B       | X7R  | R    | B    | X7R  | R    | B    | X7R  | R    | B    | X5R  | B    |
| 100pF               | p108    | p108 | p108 |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |      |      |      |      |
| 120pF               | p108    | p108 | p108 |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |      |      |      |      |
| 150pF               | p108    | p108 | p108 |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |      |      |      |      |
| 180pF               | p108    | p108 | p108 |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |      |      |      |      |
| 220pF               | p108    | p108 | p108 |      |      |      |      |      |      |      |         | p108 | p108 | p109 |      |      |      |      |      |      |      |      |
| 270pF               | p108    | p108 | p108 |      |      |      |      |      |      |      |         | p108 | p109 | p109 |      |      |      |      |      |      |      |      |
| 330pF               | p108    | p108 | p108 |      |      |      |      |      |      |      |         | p108 | p109 | p109 |      |      |      |      |      |      |      |      |
| 390pF               | p108    | p108 | p108 |      |      |      |      |      |      |      |         | p108 | p109 | p109 |      |      |      |      |      |      |      |      |
| 470pF               | p108    | p108 | p108 |      |      |      |      |      |      |      |         | p108 | p109 | p109 |      |      |      |      |      |      |      |      |
| 560pF               | p108    | p108 | p108 |      |      |      |      |      |      |      |         | p108 | p109 | p109 |      |      |      |      |      |      |      |      |
| 680pF               | p108    | p108 | p108 |      |      |      |      |      |      |      |         | p108 | p109 | p109 |      |      |      |      |      |      |      |      |
| 820pF               | p108    | p108 | p108 |      |      |      |      |      |      |      |         | p108 | p109 | p109 |      |      |      |      |      |      |      |      |
| 1000pF              | p108    | p108 | p108 |      |      |      |      |      |      |      |         | p108 | p109 | p109 |      |      |      |      |      |      |      |      |
| 1200pF              | p108    | p108 | p108 |      |      |      |      |      |      |      |         | p108 | p109 | p109 |      |      |      |      |      |      |      |      |
| 1500pF              | p108    | p108 | p108 |      |      |      |      |      |      |      |         | p108 | p109 | p109 |      |      |      |      |      |      |      |      |
| 1800pF              |         |      |      | p108 | p108 | p108 |      |      |      |      |         | p108 | p109 | p109 |      |      |      |      |      |      |      |      |
| 2200pF              |         |      |      | p108 | p108 | p108 |      |      |      |      |         | p108 | p109 | p109 |      |      |      |      |      |      |      |      |
| 2700pF              |         |      |      | p108 | p108 | p108 |      |      |      |      |         | p108 | p109 | p109 |      |      |      |      |      |      |      |      |
| 3300pF              |         |      |      | p108 | p108 | p108 |      |      |      |      |         | p108 | p109 | p109 |      |      |      |      |      |      |      |      |
| 3900pF              |         |      |      |      |      |      | p108 | p108 | p108 |      |         | p108 | p109 | p109 |      |      |      |      |      |      |      |      |
| 4700pF              |         |      |      |      |      |      | p108 | p108 | p108 |      |         | p108 | p109 | p109 |      |      |      |      |      |      |      |      |
| 5600pF              |         |      |      |      |      |      | p108 | p108 | p108 |      |         |      |      |      | p109 | p109 | p109 |      |      |      |      |      |
| 6800pF              |         |      |      |      |      |      | p108 | p108 | p108 |      |         |      |      |      | p109 | p109 | p109 |      |      |      |      |      |
| 8200pF              |         |      |      |      |      |      | p108 | p108 | p108 |      |         |      |      |      | p109 | p109 | p109 |      |      |      |      |      |
| 10000pF             |         |      |      |      |      |      | p108 | p108 | p108 |      |         |      |      |      | p109 | p109 | p109 |      |      |      |      |      |
| 12000pF             |         |      |      |      |      |      |      |      |      |      |         |      |      |      | p109 | p109 | p109 |      |      |      |      |      |
| 15000pF             |         |      |      |      |      |      |      |      |      |      |         |      |      |      | p109 | p109 | p109 |      |      |      |      |      |
| 18000pF             |         |      |      |      |      |      |      |      |      |      |         |      |      |      | p109 | p109 | p109 |      |      |      |      |      |
| 22000pF             |         |      |      |      |      |      |      |      |      |      |         |      |      |      | p109 | p109 | p109 |      |      |      |      |      |
| 27000pF             |         |      |      |      |      |      |      |      |      |      |         |      |      |      | p109 | p109 | p109 |      |      |      |      |      |
| 33000pF             |         |      |      |      |      |      |      |      |      |      |         |      |      |      | p109 | p109 | p109 |      |      |      |      |      |
| 39000pF             |         |      |      |      |      |      |      |      |      |      |         |      |      |      | p109 | p109 | p109 |      |      |      |      |      |
| 47000pF             |         |      |      |      |      |      |      |      |      |      |         |      |      |      | p109 | p109 | p109 |      |      |      |      |      |
| 56000pF             |         |      |      |      |      |      |      |      |      | p108 | p108    |      |      |      |      |      |      | p109 | p109 | p109 |      |      |
| 68000pF             |         |      |      |      |      |      |      |      |      | p108 | p108    |      |      |      |      |      |      | p109 | p109 | p109 |      |      |
| 82000pF             |         |      |      |      |      |      |      |      |      | p108 | p108    |      |      |      |      |      |      | p109 | p109 | p109 |      |      |
| 0.10μF              |         |      |      |      |      |      |      |      |      | p108 | p108    |      |      |      |      |      |      | p109 | p109 | p109 |      |      |
| 0.12μF              |         |      |      |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |      |      | p109 | p109 |
| 0.15μF              |         |      |      |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |      |      | p109 | p109 |
| 0.18μF              |         |      |      |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |      |      | p109 | p109 |
| 0.22μF              |         |      |      |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |      |      | p109 | p109 |
| 0.27μF              |         |      |      |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |      |      | p109 | p109 |
| 0.33μF              |         |      |      |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |      |      | p109 | p109 |
| 0.39μF              |         |      |      |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |      |      | p109 | p109 |
| 0.47μF              |         |      |      |      |      |      |      |      |      |      |         |      |      |      |      |      |      |      |      |      | p109 | p109 |

## Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

### ■ GQM Series Temperature Compensating Type

p00

← Part Number List

JIS:

CK

CJ

CH

EIA:

C0G

| LxW (mm)            | 1.6x0.8 |      |      |      |      | 2.0x1.25 |      |      |      |      | 2.8x2.8 |
|---------------------|---------|------|------|------|------|----------|------|------|------|------|---------|
| T max. (mm)         | 0.8     | 0.9  |      |      |      | 0.95     |      |      |      | 1.0  | 1.35    |
| Rated Voltage (Vdc) | 250     | 100  |      | 50   |      | 100      |      | 50   |      | 250  | 500     |
| Cap. / TC Code      | C0G     | C0G  | CΔ   | C0G  | CH   | C0G      | CΔ   | C0G  | CH   | C0G  | C0G     |
| 1.0pF               | p111    | p111 | p112 |      |      | p113     | p114 |      |      | p116 | p117    |
| 2.0pF               | p111    | p112 | p112 |      |      | p114     | p114 |      |      | p116 | p117    |
| 3.0pF               | p111    | p112 | p112 |      |      | p114     | p114 |      |      | p116 | p117    |
| 4.0pF               | p111    | p112 | p112 |      |      | p114     | p114 |      |      | p116 | p117    |
| 5.0pF               | p111    | p112 | p112 |      |      | p114     | p114 |      |      | p116 | p117    |
| 6.0pF               | p111    | p112 | p112 |      |      | p114     | p115 |      |      | p116 | p117    |
| 7.0pF               | p111    |      |      | p112 | p113 | p114     | p115 |      |      | p116 | p117    |
| 8.0pF               | p111    |      |      | p112 | p113 | p114     | p115 |      |      | p116 | p117    |
| 9.0pF               | p111    |      |      | p112 | p113 | p114     | p115 |      |      | p116 | p117    |
| 10pF                | p111    |      |      | p112 | p113 | p114     | p115 |      |      | p116 | p117    |
| 11pF                | p111    |      |      | p112 | p113 | p114     | p115 |      |      | p116 | p117    |
| 12pF                | p111    |      |      | p112 | p113 | p114     | p115 |      |      | p116 | p117    |
| 13pF                | p111    |      |      | p112 | p113 | p114     | p115 |      |      | p116 | p117    |
| 15pF                | p111    |      |      | p112 | p113 | p114     | p115 |      |      | p116 | p117    |
| 16pF                | p111    |      |      | p112 | p113 | p114     | p115 |      |      | p116 | p117    |
| 18pF                | p111    |      |      | p113 | p113 | p114     | p115 |      |      | p116 | p117    |
| 20pF                | p111    |      |      | p113 | p113 |          |      | p115 | p115 | p116 | p117    |
| 22pF                | p111    |      |      | p113 | p113 |          |      | p115 | p115 | p116 | p117    |
| 24pF                | p111    |      |      | p113 | p113 |          |      | p115 | p115 | p116 | p117    |
| 27pF                | p111    |      |      | p113 | p113 |          |      | p115 | p115 | p116 | p117    |
| 30pF                | p111    |      |      | p113 | p113 |          |      | p115 | p115 | p116 | p117    |
| 33pF                | p111    |      |      | p113 | p113 |          |      | p115 | p115 | p116 | p117    |
| 36pF                | p111    |      |      | p113 | p113 |          |      | p115 | p115 | p116 | p117    |
| 39pF                | p111    |      |      | p113 | p113 |          |      | p115 | p115 | p116 | p117    |
| 43pF                | p111    |      |      | p113 | p113 |          |      | p115 | p115 | p116 | p117    |
| 47pF                | p111    |      |      | p113 | p113 |          |      | p115 | p115 | p116 | p117    |
| 51pF                |         |      |      | p113 | p113 |          |      | p115 | p115 | p116 | p117    |
| 56pF                |         |      |      | p113 | p113 |          |      | p115 | p115 | p116 | p117    |
| 62pF                |         |      |      | p113 | p113 |          |      | p115 | p115 | p116 | p117    |
| 68pF                |         |      |      | p113 | p113 |          |      | p115 | p115 | p116 | p118    |
| 75pF                |         |      |      | p113 | p113 |          |      | p115 | p115 | p116 | p118    |
| 82pF                |         |      |      | p113 | p113 |          |      | p115 | p115 | p116 | p118    |
| 91pF                |         |      |      | p113 | p113 |          |      | p115 | p115 | p116 | p118    |
| 100pF               |         |      |      | p113 | p113 |          |      | p115 | p115 | p117 | p118    |

The indication for every 0.1 pF has been omitted for less than 10 pF. Refer to the Part Number List for details.

## Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

### GRJ Series High Dielectric Constant Type

p00

← Part Number List

EIA:

X7R

| LxW (mm)            | 2.0x1.25 |      | 3.2x1.6 |      |      |      |      |      | 3.2x2.5 |      |     |      |      |      | 4.5x3.2 |      |      |      |      |      | 5.7x5.0 |      |  |  |
|---------------------|----------|------|---------|------|------|------|------|------|---------|------|-----|------|------|------|---------|------|------|------|------|------|---------|------|--|--|
| T max. (mm)         | 1.0      | 1.45 | 1.25    |      |      | 1.8  |      |      | 1.5     |      |     | 2.0  |      |      | 1.5     |      | 2.0  |      | 2.0  |      |         |      |  |  |
| Rated Voltage (Vdc) | 250      | 250  | 1000    | 630  | 250  | 1000 | 630  | 250  | 1000    | 630  | 250 | 1000 | 630  | 250  | 630     | 250  | 1000 | 630  | 250  | 1000 | 630     | 250  |  |  |
| Cap. / TC Code      | X7R      | X7R  | X7R     | X7R  | X7R  | X7R  | X7R  | X7R  | X7R     | X7R  | X7R | X7R  | X7R  | X7R  | X7R     | X7R  | X7R  | X7R  | X7R  | X7R  | X7R     | X7R  |  |  |
| 470pF               |          |      | p120    |      |      |      |      |      |         |      |     |      |      |      |         |      |      |      |      |      |         |      |  |  |
| 680pF               |          |      | p120    |      |      |      |      |      |         |      |     |      |      |      |         |      |      |      |      |      |         |      |  |  |
| 1000pF              | p120     |      | p120    | p120 |      |      |      |      |         |      |     |      |      |      |         |      |      |      |      |      |         |      |  |  |
| 1500pF              | p120     |      | p120    | p120 |      |      |      |      |         |      |     |      |      |      |         |      |      |      |      |      |         |      |  |  |
| 2200pF              | p120     |      | p120    | p120 |      |      |      |      |         |      |     |      |      |      |         |      |      |      |      |      |         |      |  |  |
| 3300pF              | p120     |      | p120    | p120 |      |      |      |      |         |      |     |      |      |      |         |      |      |      |      |      |         |      |  |  |
| 4700pF              | p120     |      | p120    | p120 |      |      |      |      |         |      |     |      |      |      |         |      |      |      |      |      |         |      |  |  |
| 6800pF              | p120     |      |         | p120 |      | p120 |      |      | p120    |      |     |      |      |      |         |      |      |      |      |      |         |      |  |  |
| 10000pF             |          | p120 |         | p120 |      | p120 |      |      | p120    |      |     |      |      |      |         |      |      |      |      |      |         |      |  |  |
| 15000pF             |          | p120 |         |      | p120 |      | p120 |      |         |      |     | p120 |      |      |         |      |      |      |      |      |         |      |  |  |
| 22000pF             |          | p120 |         |      | p120 |      | p120 |      |         | p120 |     | p120 |      |      |         |      |      |      |      |      |         |      |  |  |
| 33000pF             |          |      |         |      |      |      |      | p120 |         |      |     |      | p120 |      |         |      | p120 |      |      |      |         |      |  |  |
| 47000pF             |          |      |         |      |      |      |      | p120 |         |      |     |      | p120 |      |         |      | p120 |      |      |      |         |      |  |  |
| 68000pF             |          |      |         | p120 |      |      |      |      |         | p120 |     |      |      | p120 |         |      |      |      | p120 |      |         |      |  |  |
| 0.10μF              |          |      |         |      |      |      |      | p120 |         |      |     |      |      | p120 |         |      | p120 |      |      | p120 |         |      |  |  |
| 0.15μF              |          |      |         |      |      |      |      |      |         | p120 |     |      |      |      |         | p120 |      |      |      |      | p120    |      |  |  |
| 0.22μF              |          |      |         |      |      |      |      |      |         |      |     |      | p120 |      |         |      |      |      | p120 |      | p120    |      |  |  |
| 0.33μF              |          |      |         |      |      |      |      |      |         |      |     |      |      |      |         |      |      | p120 |      |      |         | p120 |  |  |
| 0.47μF              |          |      |         |      |      |      |      |      |         |      |     |      |      |      |         |      |      | p120 |      |      |         | p120 |  |  |
| 0.68μF              |          |      |         |      |      |      |      |      |         |      |     |      |      |      |         |      |      |      |      |      |         | p120 |  |  |
| 1.0μF               |          |      |         |      |      |      |      |      |         |      |     |      |      |      |         |      |      |      |      |      |         | p120 |  |  |

### GR3 Series High Dielectric Constant Type

p00

← Part Number List

EIA:

X7T

| LxW (mm)            | 2.0x1.25 |      | 3.2x1.6 |      |      |      |      |      |      |      | 3.2x2.5 |     |      |      |      |      | 4.5x3.2 |      |     |      |      |      | 5.7x5.0 |      |      |  |  |  |
|---------------------|----------|------|---------|------|------|------|------|------|------|------|---------|-----|------|------|------|------|---------|------|-----|------|------|------|---------|------|------|--|--|--|
| T max. (mm)         | 1.0      | 1.45 | 1.0     |      | 1.25 |      |      | 1.8  |      |      | 1.5     |     | 2.0  |      | 1.5  | 2.0  |         |      | 2.0 |      |      | 2.7  |         |      |      |  |  |  |
| Rated Voltage (Vdc) | 250      | 250  | 450     | 250  | 630  | 450  | 250  | 630  | 450  | 250  | 630     | 250 | 630  | 450  | 250  | 250  | 630     | 450  | 250 | 630  | 450  | 250  | 630     | 450  | 250  |  |  |  |
| Cap. / TC Code      | X7T      | X7T  | X7T     | X7T  | X7T  | X7T  | X7T  | X7T  | X7T  | X7T  | X7T     | X7T | X7T  | X7T  | X7T  | X7T  | X7T     | X7T  | X7T | X7T  | X7T  | X7T  | X7T     | X7T  | X7T  |  |  |  |
| 10000pF             | p122     |      | p122    |      | p122 |      |      |      |      |      |         |     |      |      |      |      |         |      |     |      |      |      |         |      |      |  |  |  |
| 15000pF             | p122     |      | p122    |      |      |      |      | p122 |      |      |         |     |      |      |      |      |         |      |     |      |      |      |         |      |      |  |  |  |
| 22000pF             |          | p122 |         |      |      | p122 |      |      |      |      | p122    |     |      |      |      |      |         |      |     |      |      |      |         |      |      |  |  |  |
| 33000pF             |          |      |         | p122 |      | p122 |      |      |      |      |         |     | p122 |      |      |      |         |      |     |      |      |      |         |      |      |  |  |  |
| 47000pF             |          |      |         |      |      |      | p122 |      | p122 |      |         |     | p122 |      |      |      |         |      |     |      |      |      |         |      |      |  |  |  |
| 68000pF             |          |      |         |      |      |      |      |      |      | p122 |         |     |      | p122 |      |      | p122    |      |     |      |      |      |         |      |      |  |  |  |
| 0.10μF              |          |      |         |      |      |      |      |      |      |      | p122    |     |      | p122 |      |      |         |      |     | p122 |      |      |         |      |      |  |  |  |
| 0.15μF              |          |      |         |      |      |      |      |      |      |      |         |     |      |      | p122 |      |         | p122 |     | p122 |      |      |         |      |      |  |  |  |
| 0.22μF              |          |      |         |      |      |      |      |      |      |      |         |     |      |      |      | p122 |         |      |     |      | p122 |      | p122    |      |      |  |  |  |
| 0.27μF              |          |      |         |      |      |      |      |      |      |      |         |     |      |      |      |      |         |      |     |      |      |      | p122    |      |      |  |  |  |
| 0.33μF              |          |      |         |      |      |      |      |      |      |      |         |     |      |      |      |      |         | p122 |     |      | p122 |      |         |      |      |  |  |  |
| 0.47μF              |          |      |         |      |      |      |      |      |      |      |         |     |      |      |      |      |         |      |     | p122 | p122 |      |         |      |      |  |  |  |
| 0.56μF              |          |      |         |      |      |      |      |      |      |      |         |     |      |      |      |      |         |      |     |      |      |      |         | p122 |      |  |  |  |
| 0.68μF              |          |      |         |      |      |      |      |      |      |      |         |     |      |      |      |      |         |      |     |      |      | p122 |         |      |      |  |  |  |
| 1.0μF               |          |      |         |      |      |      |      |      |      |      |         |     |      |      |      |      |         |      |     |      |      |      |         |      | p122 |  |  |  |

## Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

### ■ KRM Series High Dielectric Constant Type

p00

← Part Number List

EIA:

X7R

X6S

X5R

| LxW (mm)            | 2.2x1.25 |      | 3.5x1.7 |      |      |      | 3.6x1.7 | 3.7x1.85 | 6.1x5.3 |      |      |     |     |      |      |      |      |      |      |      |      |      |
|---------------------|----------|------|---------|------|------|------|---------|----------|---------|------|------|-----|-----|------|------|------|------|------|------|------|------|------|
| T max. (mm)         | 1.9      |      | 2.0     | 2.9  |      |      |         | 2.9      | 2.9     | 3.0  |      |     |     |      |      |      |      | 3.9  |      |      |      |      |
| Rated Voltage (Vdc) | 25       | 16   | 25      | 100  | 50   | 35   | 25      | 50       | 100     | 1000 | 630  | 250 | 100 | 63   | 50   | 35   | 25   | 100  | 63   | 50   | 35   | 25   |
| Cap. / TC Code      | X5R      | X5R  | X5R     | X7R  | X7R  | X6S  | X6S     | X7R      | X7R     | X7R  | X7R  | X7R | X7R | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  |
| 68000pF             |          |      |         |      |      |      |         |          |         | p125 |      |     |     |      |      |      |      |      |      |      |      |      |
| 0.10μF              |          |      |         |      |      |      |         |          |         | p125 |      |     |     |      |      |      |      |      |      |      |      |      |
| 0.15μF              |          |      |         |      |      |      |         |          |         |      | p125 |     |     |      |      |      |      |      |      |      |      |      |
| 0.22μF              |          |      |         |      |      |      |         |          |         |      | p125 |     |     |      |      |      |      |      |      |      |      |      |
| 0.33μF              |          |      |         |      |      |      |         |          |         |      |      |     |     |      |      |      |      |      |      |      |      |      |
| 0.47μF              |          |      |         |      |      |      |         |          |         |      |      |     |     |      |      |      |      |      |      |      |      |      |
| 0.68μF              |          |      |         |      |      |      |         |          |         |      |      |     |     | p125 |      |      |      |      |      |      |      |      |
| 1.0μF               |          |      |         | p125 |      |      |         |          |         |      |      |     |     | p125 |      |      |      |      |      |      |      |      |
| 1.5μF               |          |      |         |      |      |      |         |          |         |      |      |     |     |      |      |      |      |      |      |      |      |      |
| 2.2μF               |          |      |         |      |      |      |         | p125     | p125    |      |      |     |     |      |      |      |      |      |      |      |      |      |
| 4.7μF               |          |      |         |      | p125 |      |         |          |         |      |      |     |     | p125 | p125 | p125 |      |      |      |      |      |      |
| 6.8μF               |          |      |         |      |      |      |         |          |         |      |      |     |     |      |      |      |      | p125 |      |      |      |      |
| 10μF                | p125     | p125 | p125    |      |      | p125 | p125    |          |         |      |      |     |     |      |      |      | p125 |      | p125 | p125 |      |      |
| 15μF                |          |      |         |      |      |      |         |          |         |      |      |     |     |      |      |      | p125 |      |      |      |      |      |
| 17μF                |          |      |         |      |      |      |         |          |         |      |      |     |     |      |      |      |      |      |      |      | p125 |      |
| 22μF                |          |      |         |      |      |      |         |          |         |      |      |     |     |      |      |      |      |      |      |      |      | p125 |
| 33μF                |          |      |         |      |      |      |         |          |         |      |      |     |     |      |      |      |      |      |      |      |      |      |
| 47μF                |          |      |         |      |      |      |         |          |         |      |      |     |     |      |      |      |      |      |      |      |      |      |



| LxW (mm)            | 6.1x5.3 |      |      |      |      |      |      |      |      |      |      |
|---------------------|---------|------|------|------|------|------|------|------|------|------|------|
| T max. (mm)         | 5.0     |      |      |      |      |      | 6.7  |      |      |      |      |
| Rated Voltage (Vdc) | 1000    | 630  | 250  | 100  | 35   | 25   | 100  | 63   | 50   | 35   | 25   |
| Cap. / TC Code      | X7R     | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  |
| 68000pF             |         |      |      |      |      |      |      |      |      |      |      |
| 0.10μF              |         |      |      |      |      |      |      |      |      |      |      |
| 0.15μF              | p125    |      |      |      |      |      |      |      |      |      |      |
| 0.22μF              | p125    |      |      |      |      |      |      |      |      |      |      |
| 0.33μF              |         | p125 |      |      |      |      |      |      |      |      |      |
| 0.47μF              |         | p125 |      |      |      |      |      |      |      |      |      |
| 0.68μF              |         |      |      |      |      |      |      |      |      |      |      |
| 1.0μF               |         |      |      |      |      |      |      |      |      |      |      |
| 1.5μF               |         |      | p125 |      |      |      |      |      |      |      |      |
| 2.2μF               |         |      | p125 |      |      |      |      |      |      |      |      |
| 4.7μF               |         |      |      |      |      |      |      |      |      |      |      |
| 6.8μF               |         |      |      |      |      |      |      |      |      |      |      |
| 10μF                |         |      |      | p125 |      |      |      |      |      |      |      |
| 15μF                |         |      |      |      |      |      | p125 |      |      |      |      |
| 17μF                |         |      |      |      |      |      |      |      |      |      |      |
| 22μF                |         |      |      |      | p125 |      |      | p125 | p125 |      |      |
| 33μF                |         |      |      |      |      | p125 |      |      |      | p125 |      |
| 47μF                |         |      |      |      |      |      |      |      |      |      | p125 |

## Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

### ■ KR3 Series High Dielectric Constant Type

p00

← Part Number List

EIA:

X7T

| LxW (mm)            | 6.1×5.3 |      |      |      |     |      |      |      |      |      |      |
|---------------------|---------|------|------|------|-----|------|------|------|------|------|------|
| T max. (mm)         | 3.0     |      |      | 3.9  |     |      | 5.0  |      | 6.7  |      |      |
| Rated Voltage (Vdc) | 630     | 450  | 250  | 630  | 450 | 250  | 450  | 250  | 630  | 450  | 250  |
| Cap. / TC Code      | X7T     | X7T  | X7T  | X7T  | X7T | X7T  | X7T  | X7T  | X7T  | X7T  | X7T  |
| 0.10μF              | p128    |      |      |      |     |      |      |      |      |      |      |
| 0.15μF              | p128    |      |      |      |     |      |      |      |      |      |      |
| 0.22μF              |         | p128 |      | p128 |     |      |      |      |      |      |      |
| 0.27μF              |         |      |      | p128 |     |      |      |      |      |      |      |
| 0.33μF              |         | p128 |      |      |     |      |      |      |      |      |      |
| 0.47μF              |         | p128 | p128 |      |     |      |      |      | p128 |      |      |
| 0.56μF              |         |      |      | p128 |     |      |      |      | p128 |      |      |
| 0.68μF              |         |      | p128 |      |     |      | p128 |      |      |      |      |
| 1.0μF               |         |      |      |      |     | p128 | p128 |      |      |      |      |
| 1.2μF               |         |      |      |      |     |      |      |      |      | p128 |      |
| 1.5μF               |         |      |      |      |     |      |      | p128 |      |      |      |
| 2.2μF               |         |      |      |      |     |      |      |      |      |      | p128 |

### ■ LLA Series High Dielectric Constant Type

p00

← Part Number List

EIA:

X7R

X7S

| LxW (mm)            | 1.6×0.8 | 2.0×1.25 |      |      |      |      |      |      |      |      |      | 3.2×1.6 |      |      |      |      |      |      |  |
|---------------------|---------|----------|------|------|------|------|------|------|------|------|------|---------|------|------|------|------|------|------|--|
| T max. (mm)         | 0.55    | 0.55     |      |      |      |      | 0.95 |      |      |      |      | 0.55    |      |      | 0.95 |      | 1.25 |      |  |
| Rated Voltage (Vdc) | 4       | 25       | 16   | 10   | 6.3  | 4    | 25   | 16   | 10   | 6.3  | 4    | 16      | 10   | 6.3  | 16   | 10   | 16   | 10   |  |
| Cap. / TC Code      | X7S     | X7R      | X7R  | X7R  | X7R  | X7S  | X7R  | X7R  | X7R  | X7R  | X7S  | X7R     | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  |  |
| 10000pF             |         | p130     |      |      |      |      | p130 |      |      |      |      |         |      |      |      |      |      |      |  |
| 22000pF             |         | p130     |      |      |      |      | p130 |      |      |      |      |         |      |      |      |      |      |      |  |
| 47000pF             |         |          | p130 |      |      |      | p130 |      |      |      |      |         |      |      |      |      |      |      |  |
| 0.10μF              | p130    |          | p130 |      |      |      |      | p130 |      |      |      |         |      |      |      |      |      |      |  |
| 0.22μF              | p130    |          |      | p130 |      |      |      | p130 |      |      |      | p130    |      |      |      |      |      |      |  |
| 0.47μF              | p130    |          |      |      | p130 |      |      |      | p130 |      |      |         | p130 |      | p130 |      |      |      |  |
| 1.0μF               |         |          |      |      |      | p130 |      |      |      | p130 |      |         |      | p130 |      | p130 | p130 |      |  |
| 2.2μF               | p130    |          |      |      |      |      |      |      |      |      | p130 |         |      | p130 |      |      |      | p130 |  |
| 4.7μF               |         |          |      |      |      | p130 |      |      |      |      |      |         |      |      |      |      |      |      |  |



## Capacitance Table

p00

Each number in the Part Number List refers to the page number printed at the bottom of the page.

### ■ LLL Series High Dielectric Constant Type

p00

← Part Number List

EIA:

X7R

X7S

X6S

X5R

| LxW (mm)            | 0.5x1.0 |      |      | 0.6x1.0 | 0.8x1.6 |      |      |      |      |      |      |      |      | 1.25x2.0 |      |      |      |      |      |      |      |      |     |  |
|---------------------|---------|------|------|---------|---------|------|------|------|------|------|------|------|------|----------|------|------|------|------|------|------|------|------|-----|--|
| T max. (mm)         | 0.35    |      |      | 0.45    | 0.5     |      |      |      | 0.55 | 0.6  |      |      |      |          | 0.5  |      |      |      |      |      |      |      | 0.7 |  |
| Rated Voltage (Vdc) | 6.3     | 4    |      | 4       | 25      | 16   | 10   | 4    | 4    | 50   | 25   | 16   | 10   | 4        | 50   | 25   | 16   | 10   | 6.3  | 4    | 50   | 25   |     |  |
| Cap. / TC Code      | X6S     | X7S  | X6S  | X5R     | X7R     | X7R  | X7R  | X7S  | X7S  | X7R  | X7R  | X7R  | X7R  | X7S      | X7R  | X7R  | X7R  | X7R  | X7R  | X7S  | X7R  | X7R  |     |  |
| 2200pF              |         |      |      |         |         |      |      |      |      | p132 |      |      |      |          |      |      |      |      |      |      |      |      |     |  |
| 4700pF              |         |      |      |         |         |      |      |      |      | p132 |      |      |      |          |      |      |      |      |      |      |      |      |     |  |
| 10000pF             |         |      |      |         | p132    |      |      |      |      |      | p132 |      |      |          | p132 |      |      |      |      |      | p132 |      |     |  |
| 22000pF             |         |      |      |         |         | p132 |      |      |      |      | p132 |      |      |          |      | p132 |      |      |      |      | p132 |      |     |  |
| 47000pF             |         |      |      |         |         | p132 |      |      |      |      |      | p132 |      |          |      |      | p132 |      |      |      |      | p132 |     |  |
| 0.10µF              | p132    |      |      |         |         |      | p132 |      |      |      |      |      | p132 |          |      |      |      | p132 |      |      |      | p132 |     |  |
| 0.22µF              | p132    |      |      |         |         |      |      | p132 |      |      |      |      | p132 |          |      |      |      |      | p132 |      |      | p132 |     |  |
| 0.47µF              |         | p132 |      |         |         |      |      |      |      |      |      |      |      | p132     |      |      |      |      |      | p132 |      |      |     |  |
| 1.0µF               |         |      | p132 |         |         |      |      |      |      |      |      |      |      |          |      |      |      |      |      |      | p132 |      |     |  |
| 2.2µF               |         |      |      |         |         |      |      |      | p132 |      |      |      |      |          |      |      |      |      |      |      |      |      |     |  |
| 4.3µF               |         |      |      | p132    |         |      |      |      |      |      |      |      |      |          |      |      |      |      |      |      |      |      |     |  |
| 4.7µF               |         |      |      |         |         |      |      |      |      |      |      |      |      |          |      |      |      |      |      |      |      |      |     |  |
| 10µF                |         |      |      |         |         |      |      |      |      |      |      |      |      |          |      |      |      |      |      |      |      |      |     |  |



| LxW (mm)            | 1.25x2.0 |      |      |      | 1.6x3.2 |      |      |      |      |      |      |      |      |      | 1.25 |      |      |      |      |
|---------------------|----------|------|------|------|---------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|
| T max. (mm)         | 0.7      | 0.95 |      |      | 0.5     |      |      |      | 0.8  |      |      |      | 1.25 |      |      |      |      | 0.7  |      |
| Rated Voltage (Vdc) | 10       | 16   | 10   | 4    | 50      | 25   | 16   | 10   | 50   | 25   | 16   | 10   | 6.3  | 50   | 25   | 16   | 10   | 6.3  |      |
| Cap. / TC Code      | X7R      | X7R  | X7R  | X7S  | X7R     | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  | X7R  | X5R  |
| 2200pF              |          |      |      |      |         |      |      |      |      |      |      |      |      |      |      |      |      |      |      |
| 4700pF              |          |      |      |      |         |      |      |      |      |      |      |      |      |      |      |      |      |      |      |
| 10000pF             |          |      |      |      | p132    |      |      |      | p132 |      |      |      |      |      |      |      |      |      |      |
| 22000pF             |          |      |      |      | p132    |      |      |      | p132 |      |      |      |      |      |      |      |      |      |      |
| 47000pF             |          |      |      |      |         | p132 |      |      | p132 |      |      |      |      |      |      |      |      |      |      |
| 0.10μF              |          |      |      |      |         | p132 |      |      | p132 |      |      |      |      | p132 |      |      |      |      |      |
| 0.22μF              | p132     | p132 |      |      |         |      | p132 |      |      | p132 |      |      |      |      | p132 |      |      |      |      |
| 0.47μF              |          |      | p132 |      |         |      |      | p132 |      | p132 |      |      |      |      | p132 |      |      |      |      |
| 1.0μF               |          |      | p132 |      |         |      |      |      |      |      | p132 |      |      |      |      | p132 |      |      |      |
| 2.2μF               |          |      |      | p132 |         |      |      |      |      |      |      | p132 |      |      |      |      | p132 |      |      |
| 4.3μF               |          |      |      |      |         |      |      |      |      |      |      |      |      |      |      |      |      | p132 |      |
| 4.7μF               |          |      |      |      |         |      |      |      |      |      |      |      |      |      |      |      |      |      | p132 |
| 10μF                |          |      |      |      |         |      |      |      |      |      |      |      |      |      |      |      |      |      | p132 |

### ■ LLM Series High Dielectric Constant Type

p00

← Part Number List

EIA:

X7R

X7S

| LxW (mm)            | 2.0x1.25 |      |      |      | 3.2x1.6 |      |      |
|---------------------|----------|------|------|------|---------|------|------|
| T max. (mm)         | 0.55     |      |      |      | 0.55    |      |      |
| Rated Voltage (Vdc) | 25       | 16   | 6.3  | 4    | 16      | 10   | 6.3  |
| Cap. / TC Code      | X7R      | X7R  | X7R  | X7S  | X7R     | X7R  | X7R  |
| 10000pF             | p134     |      |      |      |         |      |      |
| 22000pF             | p134     |      |      |      |         |      |      |
| 47000pF             |          | p134 |      |      |         |      |      |
| 0.10μF              |          | p134 |      |      | p134    |      |      |
| 0.22μF              |          |      | p134 |      | p134    |      |      |
| 0.47μF              |          |      | p134 |      |         | p134 |      |
| 1.0μF               |          |      |      | p134 |         |      |      |
| 2.2μF               |          |      |      |      |         |      | p134 |

### ■ LLR Series High Dielectric Constant Type

p00

← Part Number List

EIA:


X7S

|                     |         |      |      |      |
|---------------------|---------|------|------|------|
| LxW (mm)            | 0.8×1.6 |      |      |      |
| T max. (mm)         | 0.55    |      |      |      |
| Rated Voltage (Vdc) | 4       |      |      |      |
| TC Code             | X7S     |      |      |      |
| Cap. / ESR (mΩ)     | 100     | 220  | 470  | 1000 |
| 1.0μF               | p136    | p136 | p136 | p136 |

## Search Capacitors

Specifications and Test Methods, Package, Chart of Characteristic Data, please refer to the search web page.

<http://www.murata.com/products/capacitor/>



## Data Sheet

The product details page can be output in PDF.

## Status and Features Icons

The status and features of products can be checked at once. When  is clicked, a description of each icon will be displayed.

## Characteristics & Applications

This links to the introduction page of each series.

## Detailed Specifications Sheet

- Rated value
- Specifications and Test Methods
- Package
- Caution, Notice  
(Storage, Soldering and Mounting, ....etc.)

## Characteristics Data

The following characteristics data of the main products can be acquired.

- SPICE Netlist (mod type)
- S parameter (S2P type)
- Reliability Test Data \*Typical data

- Shape (Dimensions)
- Rated Values

- Specification by Packaging Code/  
Minimum Order Quantity
- Weight (1 pc/ø180mm reel)

### Chart of Characteristic Data

The main products published characteristic data.

- Frequency characteristics (ESR, Impedance)
- S parameter (Smith chart S11)
- DC bias characteristics
- AC voltage characteristics
- Capacitance - temperature characteristics
- Calorific property by ripple current

For General Purpose


# GRM Series




This is Murata primary products renowned for both small size and large capacitance value with latest advanced technology.

## Features


### 1 Achieves large-capacity and small size in a multilayer structure.




#### "Thin Layer Technology" for thinner layers



#### "Fine Particle Technology" for finer particles



#### "High Precision Lamination Technology" for more accuracy



### 2 Sn plating is applied to the external electrodes; excellent solderability.


### 3 High reliability with no polarity.

|                                                        | Ceramic Capacitor | Tantalum Capacitor | Aluminum Electrolytic Capacitor | Conductive Polymer Capacitor |
|--------------------------------------------------------|-------------------|--------------------|---------------------------------|------------------------------|
| Price                                                  | ○                 | ○                  | ◎                               | ○                            |
| Comparison between Impedance Frequency Characteristics | ◎                 | △                  | △                               | ○                            |
| Capacitance temperature characteristics                | ○                 | ◎                  | ○                               | ○                            |
| DC breakdown voltage                                   | ◎                 | △                  | △                               | △                            |
| Polarity                                               | No                | Yes                | Yes                             | Yes                          |
| Pulse response                                         | ◎                 | △                  | △                               | ○                            |
| Allowable ripple current                               | ◎                 | △                  | △                               | △                            |
| Reliability                                            | ◎                 | ○                  | ○                               | ○                            |
| DC bias characteristics                                | △                 | ◎                  | ◎                               | ◎                            |

◎: Particularly excellent ○: Excellent △: Inferior

## Specifications

|                   |                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|-------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Size              | 0.4×0.2mm to 5.7×5.0mm                                                                                                                                                                                                                                                                                                                                                                                                                |
| Rated Voltage     | DC2.5V to 3.15kV                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Capacitance       | 0.1pF to 150μF                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Main Applications | <p>1. Rated voltage 100V Max.<br/>High Dielectric Constant Type . . . For decoupling and smoothing circuits<br/>Temperature Compensating Type . . . For tuning circuits, oscillating circuits, and high frequency filter circuits</p> <p>2. Rated voltage 200V min.<br/>High Dielectric Constant Type . . . For clamp snubber circuits and smoothing circuits<br/>Temperature Compensating Type . . . Power supply damper snubber</p> |



This catalog contains only a portion of the product lineup.  
Please refer to the capacitor search tool on the Murata Web site for details.

## GRM Series Temperature Compensating Type Part Number List

■ 0.4×0.2mm Ultra-compact

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.22mm | 16Vdc         | C0G     | 0.20pF | ±0.05pF | GRM0225C1CR20WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1CR20BD05# |  |
|        |               |         | 0.30pF | ±0.05pF | GRM0225C1CR30WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1CR30BD05# |  |
|        |               |         | 0.40pF | ±0.05pF | GRM0225C1CR40WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1CR40BD05# |  |
|        |               |         | 0.50pF | ±0.05pF | GRM0225C1CR50WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1CR50BD05# |  |
|        |               |         | 0.60pF | ±0.05pF | GRM0225C1CR60WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1CR60BD05# |  |
|        |               |         | 0.70pF | ±0.05pF | GRM0225C1CR70WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1CR70BD05# |  |
|        |               |         | 0.80pF | ±0.05pF | GRM0225C1CR80WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1CR80BD05# |  |
|        |               |         | 0.90pF | ±0.05pF | GRM0225C1CR90WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1CR90BD05# |  |
|        |               |         | 1.0pF  | ±0.05pF | GRM0225C1C1R0WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1C1R0BD05# |  |
|        |               |         |        | ±0.25pF | GRM0225C1C1R0CD05# |  |
|        |               |         | 1.1pF  | ±0.05pF | GRM0225C1C1R1WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1C1R1BD05# |  |
|        |               |         |        | ±0.25pF | GRM0225C1C1R1CD05# |  |
|        |               |         | 1.2pF  | ±0.05pF | GRM0225C1C1R2WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1C1R2BD05# |  |
|        |               |         |        | ±0.25pF | GRM0225C1C1R2CD05# |  |
|        |               |         | 1.3pF  | ±0.05pF | GRM0225C1C1R3WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1C1R3BD05# |  |
|        |               |         |        | ±0.25pF | GRM0225C1C1R3CD05# |  |
|        |               |         | 1.4pF  | ±0.05pF | GRM0225C1C1R4WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1C1R4BD05# |  |
|        |               |         |        | ±0.25pF | GRM0225C1C1R4CD05# |  |
|        |               |         | 1.5pF  | ±0.05pF | GRM0225C1C1R5WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1C1R5BD05# |  |
|        |               |         |        | ±0.25pF | GRM0225C1C1R5CD05# |  |
|        |               |         | 1.6pF  | ±0.05pF | GRM0225C1C1R6WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1C1R6BD05# |  |
|        |               |         |        | ±0.25pF | GRM0225C1C1R6CD05# |  |
|        |               |         | 1.7pF  | ±0.05pF | GRM0225C1C1R7WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1C1R7BD05# |  |
|        |               |         |        | ±0.25pF | GRM0225C1C1R7CD05# |  |
|        |               |         | 1.8pF  | ±0.05pF | GRM0225C1C1R8WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1C1R8BD05# |  |
|        |               |         |        | ±0.25pF | GRM0225C1C1R8CD05# |  |
|        |               |         | 1.9pF  | ±0.05pF | GRM0225C1C1R9WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1C1R9BD05# |  |
|        |               |         |        | ±0.25pF | GRM0225C1C1R9CD05# |  |
|        |               |         | 2.0pF  | ±0.05pF | GRM0225C1C2R0WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1C2R0BD05# |  |
|        |               |         |        | ±0.25pF | GRM0225C1C2R0CD05# |  |
|        |               |         | 2.1pF  | ±0.05pF | GRM0225C1C2R1WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1C2R1BD05# |  |
|        |               |         |        | ±0.25pF | GRM0225C1C2R1CD05# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 16Vdc         | C0G     | 2.2pF | ±0.05pF | GRM0225C1C2R2WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C2R2BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C2R2CD05# |  |
|        |               |         | 2.3pF | ±0.05pF | GRM0225C1C2R3WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C2R3BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C2R3CD05# |  |
|        |               |         | 2.4pF | ±0.05pF | GRM0225C1C2R4WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C2R4BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C2R4CD05# |  |
|        |               |         | 2.5pF | ±0.05pF | GRM0225C1C2R5WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C2R5BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C2R5CD05# |  |
|        |               |         | 2.6pF | ±0.05pF | GRM0225C1C2R6WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C2R6BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C2R6CD05# |  |
|        |               |         | 2.7pF | ±0.05pF | GRM0225C1C2R7WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C2R7BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C2R7CD05# |  |
|        |               |         | 2.8pF | ±0.05pF | GRM0225C1C2R8WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C2R8BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C2R8CD05# |  |
|        |               |         | 2.9pF | ±0.05pF | GRM0225C1C2R9WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C2R9BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C2R9CD05# |  |
|        |               |         | 3.0pF | ±0.05pF | GRM0225C1C3R0WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C3R0BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C3R0CD05# |  |
|        |               |         | 3.1pF | ±0.05pF | GRM0225C1C3R1WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C3R1BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C3R1CD05# |  |
|        |               |         | 3.2pF | ±0.05pF | GRM0225C1C3R2WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C3R2BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C3R2CD05# |  |
|        |               |         | 3.3pF | ±0.05pF | GRM0225C1C3R3WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C3R3BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C3R3CD05# |  |
|        |               |         | 3.4pF | ±0.05pF | GRM0225C1C3R4WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C3R4BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C3R4CD05# |  |
|        |               |         | 3.5pF | ±0.05pF | GRM0225C1C3R5WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C3R5BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C3R5CD05# |  |
|        |               |         | 3.6pF | ±0.05pF | GRM0225C1C3R6WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C3R6BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C3R6CD05# |  |
|        |               |         | 3.7pF | ±0.05pF | GRM0225C1C3R7WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C3R7BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C3R7CD05# |  |
|        |               |         | 3.8pF | ±0.05pF | GRM0225C1C3R8WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C3R8BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C3R8CD05# |  |
|        |               |         | 3.9pF | ±0.05pF | GRM0225C1C3R9WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C3R9BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C3R9CD05# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 16Vdc         | C0G     | 4.0pF | ±0.05pF | GRM0225C1C4R0WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C4R0BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C4R0CD05# |  |
|        |               |         | 4.1pF | ±0.05pF | GRM0225C1C4R1WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C4R1BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C4R1CD05# |  |
|        |               |         | 4.2pF | ±0.05pF | GRM0225C1C4R2WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C4R2BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C4R2CD05# |  |
|        |               |         | 4.3pF | ±0.05pF | GRM0225C1C4R3WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C4R3BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C4R3CD05# |  |
|        |               |         | 4.4pF | ±0.05pF | GRM0225C1C4R4WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C4R4BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C4R4CD05# |  |
|        |               |         | 4.5pF | ±0.05pF | GRM0225C1C4R5WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C4R5BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C4R5CD05# |  |
|        |               |         | 4.6pF | ±0.05pF | GRM0225C1C4R6WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C4R6BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C4R6CD05# |  |
|        |               |         | 4.7pF | ±0.05pF | GRM0225C1C4R7WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C4R7BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C4R7CD05# |  |
|        |               |         | 4.8pF | ±0.05pF | GRM0225C1C4R8WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C4R8BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C4R8CD05# |  |
|        |               |         | 4.9pF | ±0.05pF | GRM0225C1C4R9WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C4R9BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C4R9CD05# |  |
|        |               |         | 5.0pF | ±0.05pF | GRM0225C1C5R0WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C5R0BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C5R0CD05# |  |
|        |               |         | 5.1pF | ±0.05pF | GRM0225C1C5R1WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C5R1BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C5R1CD05# |  |
|        |               |         | 5.2pF | ±0.05pF | GRM0225C1C5R2WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C5R2BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C5R2CD05# |  |
|        |               |         | 5.3pF | ±0.05pF | GRM0225C1C5R3WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C5R3BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C5R3CD05# |  |
|        |               |         | 5.4pF | ±0.05pF | GRM0225C1C5R4WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C5R4BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C5R4CD05# |  |
|        |               |         | 5.5pF | ±0.05pF | GRM0225C1C5R5WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C5R5BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C5R5CD05# |  |
|        |               |         | 5.6pF | ±0.05pF | GRM0225C1C5R5DD05# |  |
|        |               |         |       | ±0.05pF | GRM0225C1C5R6WD05# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 16Vdc         | C0G     | 5.6pF | ±0.1pF  | GRM0225C1C5R6BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C5R6CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C5R6DD05# |  |
|        |               |         | 5.7pF | ±0.05pF | GRM0225C1C5R7WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C5R7BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C5R7CD05# |  |
|        |               |         | 5.8pF | ±0.05pF | GRM0225C1C5R8WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C5R8BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C5R8CD05# |  |
|        |               |         | 5.9pF | ±0.05pF | GRM0225C1C5R9WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C5R9BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C5R9CD05# |  |
|        |               |         | 6.0pF | ±0.05pF | GRM0225C1C6R0WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C6R0BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C6R0CD05# |  |
|        |               |         | 6.1pF | ±0.05pF | GRM0225C1C6R1WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C6R1BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C6R1CD05# |  |
|        |               |         | 6.2pF | ±0.05pF | GRM0225C1C6R2WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C6R2BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C6R2CD05# |  |
|        |               |         | 6.3pF | ±0.05pF | GRM0225C1C6R3WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C6R3BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C6R3CD05# |  |
|        |               |         | 6.4pF | ±0.05pF | GRM0225C1C6R4WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C6R4BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C6R4CD05# |  |
|        |               |         | 6.5pF | ±0.05pF | GRM0225C1C6R5WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C6R5BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C6R5CD05# |  |
|        |               |         | 6.6pF | ±0.05pF | GRM0225C1C6R6WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C6R6BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C6R6CD05# |  |
|        |               |         | 6.7pF | ±0.05pF | GRM0225C1C6R7WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C6R7BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C6R7CD05# |  |
|        |               |         | 6.8pF | ±0.05pF | GRM0225C1C6R8WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C6R8BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C6R8CD05# |  |
|        |               |         | 6.9pF | ±0.05pF | GRM0225C1C6R9WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C6R9BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C6R9CD05# |  |

Part number # indicates the package specification code.



## GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 16Vdc         | C0G     | 6.9pF | ±0.5pF  | GRM0225C1C6R9DD05# |  |
|        |               |         | 7.0pF | ±0.05pF | GRM0225C1C7R0WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C7R0BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C7R0CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C7R0DD05# |  |
|        |               |         | 7.1pF | ±0.05pF | GRM0225C1C7R1WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C7R1BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C7R1CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C7R1DD05# |  |
|        |               |         | 7.2pF | ±0.05pF | GRM0225C1C7R2WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C7R2BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C7R2CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C7R2DD05# |  |
|        |               |         | 7.3pF | ±0.05pF | GRM0225C1C7R3WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C7R3BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C7R3CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C7R3DD05# |  |
|        |               |         | 7.4pF | ±0.05pF | GRM0225C1C7R4WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C7R4BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C7R4CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C7R4DD05# |  |
|        |               |         | 7.5pF | ±0.05pF | GRM0225C1C7R5WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C7R5BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C7R5CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C7R5DD05# |  |
|        |               |         | 7.6pF | ±0.05pF | GRM0225C1C7R6WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C7R6BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C7R6CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C7R6DD05# |  |
|        |               |         | 7.7pF | ±0.05pF | GRM0225C1C7R7WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C7R7BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C7R7CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C7R7DD05# |  |
|        |               |         | 7.8pF | ±0.05pF | GRM0225C1C7R8WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C7R8BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C7R8CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C7R8DD05# |  |
|        |               |         | 7.9pF | ±0.05pF | GRM0225C1C7R9WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C7R9BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C7R9CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C7R9DD05# |  |
|        |               |         | 8.0pF | ±0.05pF | GRM0225C1C8R0WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C8R0BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C8R0CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C8R0DD05# |  |
|        |               |         | 8.1pF | ±0.05pF | GRM0225C1C8R1WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C8R1BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C8R1CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C8R1DD05# |  |
|        |               |         | 8.2pF | ±0.05pF | GRM0225C1C8R2WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C8R2BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C8R2CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C8R2DD05# |  |
|        |               |         | 8.3pF | ±0.05pF | GRM0225C1C8R3WD05# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 16Vdc         | C0G     | 8.3pF | ±0.1pF  | GRM0225C1C8R3BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C8R3CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C8R3DD05# |  |
|        |               |         | 8.4pF | ±0.05pF | GRM0225C1C8R4WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C8R4BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C8R4CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C8R4DD05# |  |
|        |               |         | 8.5pF | ±0.05pF | GRM0225C1C8R5WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C8R5BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C8R5CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C8R5DD05# |  |
|        |               |         | 8.6pF | ±0.05pF | GRM0225C1C8R6WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C8R6BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C8R6CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C8R6DD05# |  |
|        |               |         | 8.7pF | ±0.05pF | GRM0225C1C8R7WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C8R7BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C8R7CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C8R7DD05# |  |
|        |               |         | 8.8pF | ±0.05pF | GRM0225C1C8R8WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C8R8BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C8R8CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C8R8DD05# |  |
|        |               |         | 8.9pF | ±0.05pF | GRM0225C1C8R9WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C8R9BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C8R9CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C8R9DD05# |  |
|        |               |         | 9.0pF | ±0.05pF | GRM0225C1C9R0WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C9R0BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C9R0CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C9R0DD05# |  |
|        |               |         | 9.1pF | ±0.05pF | GRM0225C1C9R1WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C9R1BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C9R1CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C9R1DD05# |  |
|        |               |         | 9.2pF | ±0.05pF | GRM0225C1C9R2WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C9R2BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C9R2CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C9R2DD05# |  |
|        |               |         | 9.3pF | ±0.05pF | GRM0225C1C9R3WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C9R3BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C9R3CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C9R3DD05# |  |
|        |               |         | 9.4pF | ±0.05pF | GRM0225C1C9R4WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C9R4BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C9R4CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C9R4DD05# |  |
|        |               |         | 9.5pF | ±0.05pF | GRM0225C1C9R5WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C9R5BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C9R5CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0225C1C9R5DD05# |  |
|        |               |         | 9.6pF | ±0.05pF | GRM0225C1C9R6WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0225C1C9R6BD05# |  |
|        |               |         |       | ±0.25pF | GRM0225C1C9R6CD05# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.22mm | 16Vdc         | C0G     | 9.6pF  | ±0.5pF  | GRM0225C1C9R6DD05# |  |
|        |               |         |        | ±0.05pF | GRM0225C1C9R7WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1C9R7BD05# |  |
|        |               |         |        | ±0.25pF | GRM0225C1C9R7CD05# |  |
|        |               |         |        | ±0.5pF  | GRM0225C1C9R7DD05# |  |
|        |               |         | 9.8pF  | ±0.05pF | GRM0225C1C9R8WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1C9R8BD05# |  |
|        |               |         |        | ±0.25pF | GRM0225C1C9R8CD05# |  |
|        |               |         |        | ±0.5pF  | GRM0225C1C9R8DD05# |  |
|        |               |         | 9.9pF  | ±0.05pF | GRM0225C1C9R9WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0225C1C9R9BD05# |  |
|        |               |         |        | ±0.25pF | GRM0225C1C9R9CD05# |  |
|        |               |         |        | ±0.5pF  | GRM0225C1C9R9DD05# |  |
|        |               |         | 10pF   | ±2%     | GRM0225C1C100GD05# |  |
|        |               |         |        | ±5%     | GRM0225C1C100JD05# |  |
|        |               |         |        |         |                    |  |
|        |               |         | 12pF   | ±2%     | GRM0225C1C120GD05# |  |
|        |               |         |        | ±5%     | GRM0225C1C120JD05# |  |
|        |               |         | 15pF   | ±2%     | GRM0225C1C150GD05# |  |
|        |               |         |        | ±5%     | GRM0225C1C150JD05# |  |
|        |               |         | 18pF   | ±2%     | GRM0225C1C180GD05# |  |
|        |               |         |        | ±5%     | GRM0225C1C180JD05# |  |
|        |               |         | 22pF   | ±2%     | GRM0225C1C220GD05# |  |
|        |               |         |        | ±5%     | GRM0225C1C220JD05# |  |
|        |               |         | 27pF   | ±2%     | GRM0225C1C270GD05# |  |
|        |               |         |        | ±5%     | GRM0225C1C270JD05# |  |
|        |               |         | 33pF   | ±2%     | GRM0225C1C330GD05# |  |
|        |               |         |        | ±5%     | GRM0225C1C330JD05# |  |
|        |               |         | 39pF   | ±2%     | GRM0225C1C390GD05# |  |
|        |               |         |        | ±5%     | GRM0225C1C390JD05# |  |
|        |               |         | 47pF   | ±2%     | GRM0225C1C470GD05# |  |
|        |               |         |        | ±5%     | GRM0225C1C470JD05# |  |
|        |               | CK      | 0.20pF | ±0.05pF | GRM0224C1CR20WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0224C1CR20BD05# |  |
|        |               |         | 0.30pF | ±0.05pF | GRM0224C1CR30WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0224C1CR30BD05# |  |
|        |               |         | 0.40pF | ±0.05pF | GRM0224C1CR40WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0224C1CR40BD05# |  |
|        |               |         | 0.50pF | ±0.05pF | GRM0224C1CR50WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0224C1CR50BD05# |  |
|        |               |         | 0.60pF | ±0.05pF | GRM0224C1CR60WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0224C1CR60BD05# |  |
|        |               |         | 0.70pF | ±0.05pF | GRM0224C1CR70WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0224C1CR70BD05# |  |
|        |               |         | 0.80pF | ±0.05pF | GRM0224C1CR80WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0224C1CR80BD05# |  |
|        |               |         | 0.90pF | ±0.05pF | GRM0224C1CR90WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0224C1CR90BD05# |  |
|        |               |         | 1.0pF  | ±0.05pF | GRM0224C1C1R0WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0224C1C1R0BD05# |  |
|        |               |         |        | ±0.25pF | GRM0224C1C1R0CD05# |  |
|        |               |         | 1.1pF  | ±0.05pF | GRM0224C1C1R1WD05# |  |
|        |               |         |        | ±0.1pF  | GRM0224C1C1R1BD05# |  |
|        |               |         |        | ±0.25pF | GRM0224C1C1R1CD05# |  |
|        |               |         | 1.2pF  | ±0.05pF | GRM0224C1C1R2WD05# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 16Vdc         | CK      | 1.2pF | ±0.1pF  | GRM0224C1C1R2BD05# |  |
|        |               |         |       | ±0.25pF | GRM0224C1C1R2CD05# |  |
|        |               |         | 1.3pF | ±0.05pF | GRM0224C1C1R3WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0224C1C1R3BD05# |  |
|        |               |         |       | ±0.25pF | GRM0224C1C1R3CD05# |  |
|        |               |         | 1.4pF | ±0.05pF | GRM0224C1C1R4WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0224C1C1R4BD05# |  |
|        |               |         |       | ±0.25pF | GRM0224C1C1R4CD05# |  |
|        |               |         | 1.5pF | ±0.05pF | GRM0224C1C1R5WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0224C1C1R5BD05# |  |
|        |               |         |       | ±0.25pF | GRM0224C1C1R5CD05# |  |
|        |               |         | 1.6pF | ±0.05pF | GRM0224C1C1R6WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0224C1C1R6BD05# |  |
|        |               |         |       | ±0.25pF | GRM0224C1C1R6CD05# |  |
|        |               |         | 1.7pF | ±0.05pF | GRM0224C1C1R7WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0224C1C1R7BD05# |  |
|        |               |         |       | ±0.25pF | GRM0224C1C1R7CD05# |  |
|        |               |         | 1.8pF | ±0.05pF | GRM0224C1C1R8WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0224C1C1R8BD05# |  |
|        |               |         |       | ±0.25pF | GRM0224C1C1R8CD05# |  |
|        |               |         | 1.9pF | ±0.05pF | GRM0224C1C1R9WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0224C1C1R9BD05# |  |
|        |               |         |       | ±0.25pF | GRM0224C1C1R9CD05# |  |
|        |               |         | 2.0pF | ±0.05pF | GRM0224C1C2R0WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0224C1C2R0BD05# |  |
|        |               |         |       | ±0.25pF | GRM0224C1C2R0CD05# |  |
|        |               | CJ      | 2.1pF | ±0.05pF | GRM0223C1C2R1WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C2R1BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C2R1CD05# |  |
|        |               |         | 2.2pF | ±0.05pF | GRM0223C1C2R2WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C2R2BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C2R2CD05# |  |
|        |               |         | 2.3pF | ±0.05pF | GRM0223C1C2R3WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C2R3BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C2R3CD05# |  |
|        |               |         | 2.4pF | ±0.05pF | GRM0223C1C2R4WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C2R4BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C2R4CD05# |  |
|        |               |         | 2.5pF | ±0.05pF | GRM0223C1C2R5WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C2R5BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C2R5CD05# |  |
|        |               |         | 2.6pF | ±0.05pF | GRM0223C1C2R6WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C2R6BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C2R6CD05# |  |
|        |               |         | 2.7pF | ±0.05pF | GRM0223C1C2R7WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C2R7BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C2R7CD05# |  |
|        |               |         | 2.8pF | ±0.05pF | GRM0223C1C2R8WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C2R8BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C2R8CD05# |  |
|        |               |         | 2.9pF | ±0.05pF | GRM0223C1C2R9WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C2R9BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C2R9CD05# |  |
|        |               |         | 3.0pF | ±0.05pF | GRM0223C1C3R0WD05# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 16Vdc         | CJ      | 3.0pF | ±0.1pF  | GRM0223C1C3R0BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C3R0CD05# |  |
|        |               |         | 3.1pF | ±0.05pF | GRM0223C1C3R1WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C3R1BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C3R1CD05# |  |
|        |               |         | 3.2pF | ±0.05pF | GRM0223C1C3R2WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C3R2BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C3R2CD05# |  |
|        |               |         | 3.3pF | ±0.05pF | GRM0223C1C3R3WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C3R3BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C3R3CD05# |  |
|        |               |         | 3.4pF | ±0.05pF | GRM0223C1C3R4WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C3R4BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C3R4CD05# |  |
|        |               |         | 3.5pF | ±0.05pF | GRM0223C1C3R5WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C3R5BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C3R5CD05# |  |
|        |               |         | 3.6pF | ±0.05pF | GRM0223C1C3R6WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C3R6BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C3R6CD05# |  |
|        |               |         | 3.7pF | ±0.05pF | GRM0223C1C3R7WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C3R7BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C3R7CD05# |  |
|        |               |         | 3.8pF | ±0.05pF | GRM0223C1C3R8WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C3R8BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C3R8CD05# |  |
|        |               |         | 3.9pF | ±0.05pF | GRM0223C1C3R9WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0223C1C3R9BD05# |  |
|        |               |         |       | ±0.25pF | GRM0223C1C3R9CD05# |  |
|        |               | CH      | 4.0pF | ±0.05pF | GRM0222C1C4R0WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C4R0BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C4R0CD05# |  |
|        |               |         | 4.1pF | ±0.05pF | GRM0222C1C4R1WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C4R1BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C4R1CD05# |  |
|        |               |         | 4.2pF | ±0.05pF | GRM0222C1C4R2WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C4R2BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C4R2CD05# |  |
|        |               |         | 4.3pF | ±0.05pF | GRM0222C1C4R3WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C4R3BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C4R3CD05# |  |
|        |               |         | 4.4pF | ±0.05pF | GRM0222C1C4R4WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C4R4BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C4R4CD05# |  |
|        |               |         | 4.5pF | ±0.05pF | GRM0222C1C4R5WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C4R5BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C4R5CD05# |  |
|        |               |         | 4.6pF | ±0.05pF | GRM0222C1C4R6WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C4R6BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C4R6CD05# |  |
|        |               |         | 4.7pF | ±0.05pF | GRM0222C1C4R7WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C4R7BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C4R7CD05# |  |
|        |               |         | 4.8pF | ±0.05pF | GRM0222C1C4R8WD05# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 16Vdc         | CH      | 4.8pF | ±0.1pF  | GRM0222C1C4R8BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C4R8CD05# |  |
|        |               |         | 4.9pF | ±0.05pF | GRM0222C1C4R9WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C4R9BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C4R9CD05# |  |
|        |               |         | 5.0pF | ±0.05pF | GRM0222C1C5R0WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C5R0BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C5R0CD05# |  |
|        |               |         | 5.1pF | ±0.05pF | GRM0222C1C5R1WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C5R1BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C5R1CD05# |  |
|        |               |         | 5.2pF | ±0.05pF | GRM0222C1C5R2WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C5R2BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C5R2CD05# |  |
|        |               |         | 5.3pF | ±0.05pF | GRM0222C1C5R3WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C5R3BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C5R3CD05# |  |
|        |               |         | 5.4pF | ±0.05pF | GRM0222C1C5R4WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C5R4BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C5R4CD05# |  |
|        |               |         | 5.5pF | ±0.05pF | GRM0222C1C5R5WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C5R5BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C5R5CD05# |  |
|        |               |         | 5.6pF | ±0.05pF | GRM0222C1C5R6WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C5R6BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C5R6CD05# |  |
|        |               |         | 5.7pF | ±0.05pF | GRM0222C1C5R7WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C5R7BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C5R7CD05# |  |
|        |               |         | 5.8pF | ±0.05pF | GRM0222C1C5R8WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C5R8BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C5R8CD05# |  |
|        |               |         | 5.9pF | ±0.05pF | GRM0222C1C5R9WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C5R9BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C5R9CD05# |  |
|        |               |         | 6.0pF | ±0.05pF | GRM0222C1C6R0WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C6R0BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C6R0CD05# |  |
|        |               |         | 6.1pF | ±0.05pF | GRM0222C1C6R1WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C6R1BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C6R1CD05# |  |
|        |               |         | 6.2pF | ±0.05pF | GRM0222C1C6R2WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C6R2BD05# |  |

Part number # indicates the package specification code.



# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 16Vdc         | CH      | 6.2pF | ±0.25pF | GRM0222C1C6R2CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C6R2DD05# |  |
|        |               |         | 6.3pF | ±0.05pF | GRM0222C1C6R3WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C6R3BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C6R3CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C6R3DD05# |  |
|        |               |         | 6.4pF | ±0.05pF | GRM0222C1C6R4WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C6R4BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C6R4CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C6R4DD05# |  |
|        |               |         | 6.5pF | ±0.05pF | GRM0222C1C6R5WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C6R5BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C6R5CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C6R5DD05# |  |
|        |               |         | 6.6pF | ±0.05pF | GRM0222C1C6R6WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C6R6BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C6R6CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C6R6DD05# |  |
|        |               |         | 6.7pF | ±0.05pF | GRM0222C1C6R7WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C6R7BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C6R7CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C6R7DD05# |  |
|        |               |         | 6.8pF | ±0.05pF | GRM0222C1C6R8WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C6R8BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C6R8CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C6R8DD05# |  |
|        |               |         | 6.9pF | ±0.05pF | GRM0222C1C6R9WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C6R9BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C6R9CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C6R9DD05# |  |
|        |               |         | 7.0pF | ±0.05pF | GRM0222C1C7R0WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C7R0BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C7R0CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C7R0DD05# |  |
|        |               |         | 7.1pF | ±0.05pF | GRM0222C1C7R1WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C7R1BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C7R1CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C7R1DD05# |  |
|        |               |         | 7.2pF | ±0.05pF | GRM0222C1C7R2WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C7R2BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C7R2CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C7R2DD05# |  |
|        |               |         | 7.3pF | ±0.05pF | GRM0222C1C7R3WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C7R3BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C7R3CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C7R3DD05# |  |
|        |               |         | 7.4pF | ±0.05pF | GRM0222C1C7R4WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C7R4BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C7R4CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C7R4DD05# |  |
|        |               |         | 7.5pF | ±0.05pF | GRM0222C1C7R5WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C7R5BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C7R5CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C7R5DD05# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 16Vdc         | CH      | 7.6pF | ±0.05pF | GRM0222C1C7R6WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C7R6BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C7R6CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C7R6DD05# |  |
|        |               |         | 7.7pF | ±0.05pF | GRM0222C1C7R7WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C7R7BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C7R7CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C7R7DD05# |  |
|        |               |         | 7.8pF | ±0.05pF | GRM0222C1C7R8WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C7R8BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C7R8CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C7R8DD05# |  |
|        |               |         | 7.9pF | ±0.05pF | GRM0222C1C7R9WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C7R9BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C7R9CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C7R9DD05# |  |
|        |               |         | 8.0pF | ±0.05pF | GRM0222C1C8R0WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C8R0BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C8R0CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C8R0DD05# |  |
|        |               |         | 8.1pF | ±0.05pF | GRM0222C1C8R1WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C8R1BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C8R1CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C8R1DD05# |  |
|        |               |         | 8.2pF | ±0.05pF | GRM0222C1C8R2WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C8R2BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C8R2CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C8R2DD05# |  |
|        |               |         | 8.3pF | ±0.05pF | GRM0222C1C8R3WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C8R3BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C8R3CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C8R3DD05# |  |
|        |               |         | 8.4pF | ±0.05pF | GRM0222C1C8R4WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C8R4BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C8R4CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C8R4DD05# |  |
|        |               |         | 8.5pF | ±0.05pF | GRM0222C1C8R5WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C8R5BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C8R5CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C8R5DD05# |  |
|        |               |         | 8.6pF | ±0.05pF | GRM0222C1C8R6WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C8R6BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C8R6CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C8R6DD05# |  |
|        |               |         | 8.7pF | ±0.05pF | GRM0222C1C8R7WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C8R7BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C8R7CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C8R7DD05# |  |
|        |               |         | 8.8pF | ±0.05pF | GRM0222C1C8R8WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C8R8BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C8R8CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C8R8DD05# |  |
|        |               |         | 8.9pF | ±0.05pF | GRM0222C1C8R9WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C8R9BD05# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 16Vdc         | CH      | 8.9pF | ±0.25pF | GRM0222C1C8R9CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C8R9DD05# |  |
|        |               |         | 9.0pF | ±0.05pF | GRM0222C1C9R0WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C9R0BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C9R0CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C9R0DD05# |  |
|        |               |         | 9.1pF | ±0.05pF | GRM0222C1C9R1WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C9R1BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C9R1CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C9R1DD05# |  |
|        |               |         | 9.2pF | ±0.05pF | GRM0222C1C9R2WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C9R2BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C9R2CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C9R2DD05# |  |
|        |               |         | 9.3pF | ±0.05pF | GRM0222C1C9R3WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C9R3BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C9R3CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C9R3DD05# |  |
|        |               |         | 9.4pF | ±0.05pF | GRM0222C1C9R4WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C9R4BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C9R4CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C9R4DD05# |  |
|        |               |         | 9.5pF | ±0.05pF | GRM0222C1C9R5WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C9R5BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C9R5CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C9R5DD05# |  |
|        |               |         | 9.6pF | ±0.05pF | GRM0222C1C9R6WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C9R6BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C9R6CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C9R6DD05# |  |
|        |               |         | 9.7pF | ±0.05pF | GRM0222C1C9R7WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C9R7BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C9R7CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C9R7DD05# |  |
|        |               |         | 9.8pF | ±0.05pF | GRM0222C1C9R8WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C9R8BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C9R8CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C9R8DD05# |  |
|        |               |         | 9.9pF | ±0.05pF | GRM0222C1C9R9WD05# |  |
|        |               |         |       | ±0.1pF  | GRM0222C1C9R9BD05# |  |
|        |               |         |       | ±0.25pF | GRM0222C1C9R9CD05# |  |
|        |               |         |       | ±0.5pF  | GRM0222C1C9R9DD05# |  |
|        |               |         | 10pF  | ±2%     | GRM0222C1C100GD05# |  |
|        |               |         |       | ±5%     | GRM0222C1C100JD05# |  |
|        |               |         | 12pF  | ±2%     | GRM0222C1C120GD05# |  |
|        |               |         |       | ±5%     | GRM0222C1C120JD05# |  |
|        |               |         | 15pF  | ±2%     | GRM0222C1C150GD05# |  |
|        |               |         |       | ±5%     | GRM0222C1C150JD05# |  |
|        |               |         | 18pF  | ±2%     | GRM0222C1C180GD05# |  |
|        |               |         |       | ±5%     | GRM0222C1C180JD05# |  |
|        |               |         | 22pF  | ±2%     | GRM0222C1C220GD05# |  |
|        |               |         |       | ±5%     | GRM0222C1C220JD05# |  |
|        |               |         | 27pF  | ±2%     | GRM0222C1C270GD05# |  |
|        |               |         |       | ±5%     | GRM0222C1C270JD05# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol. | Part Number        |  |
|--------|---------------|---------|-------|------|--------------------|--|
| 0.22mm | 16Vdc         | CH      | 33pF  | ±2%  | GRM0222C1C330GD05# |  |
|        |               |         |       | ±5%  | GRM0222C1C330JD05# |  |
|        |               |         | 39pF  | ±2%  | GRM0222C1C390GD05# |  |
|        |               |         |       | ±5%  | GRM0222C1C390JD05# |  |
|        |               |         | 47pF  | ±2%  | GRM0222C1C470GD05# |  |
|        |               |         |       | ±5%  | GRM0222C1C470JD05# |  |
|        | 10Vdc         | C0G     | 56pF  | ±2%  | GRM0225C1A560GD05# |  |
|        |               |         |       | ±5%  | GRM0225C1A560JD05# |  |
|        |               |         | 68pF  | ±2%  | GRM0225C1A680GD05# |  |
|        |               |         |       | ±5%  | GRM0225C1A680JD05# |  |
|        |               |         | 82pF  | ±2%  | GRM0225C1A820GD05# |  |
|        |               |         |       | ±5%  | GRM0225C1A820JD05# |  |
|        |               |         | 100pF | ±2%  | GRM0225C1A101GD05# |  |
|        |               |         |       | ±5%  | GRM0225C1A101JD05# |  |
|        |               | CH      | 56pF  | ±2%  | GRM0222C1A560GD05# |  |
|        |               |         |       | ±5%  | GRM0222C1A560JD05# |  |
|        |               |         | 68pF  | ±2%  | GRM0222C1A680GD05# |  |
|        |               |         |       | ±5%  | GRM0222C1A680JD05# |  |
|        |               |         | 82pF  | ±2%  | GRM0222C1A820GD05# |  |
|        |               |         |       | ±5%  | GRM0222C1A820JD05# |  |
|        |               |         | 100pF | ±2%  | GRM0222C1A101GD05# |  |
|        |               |         |       | ±5%  | GRM0222C1A101JD05# |  |

■ 0.6×0.3mm Ultra-compact

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.33mm | 100Vdc        | C0G     | 0.10pF | ±0.05pF | GRM0335C2AR10WA01# |  |
|        |               |         |        | ±0.05pF | GRM0335C2AR20WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2AR20BA01# |  |
|        |               |         | 0.30pF | ±0.05pF | GRM0335C2AR30WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2AR30BA01# |  |
|        |               |         | 0.40pF | ±0.05pF | GRM0335C2AR40WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2AR40BA01# |  |
|        |               |         | 0.50pF | ±0.05pF | GRM0335C2AR50WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2AR50BA01# |  |
|        |               |         | 0.60pF | ±0.05pF | GRM0335C2AR60WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2AR60BA01# |  |
|        |               |         | 0.70pF | ±0.05pF | GRM0335C2AR70WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2AR70BA01# |  |
|        |               |         | 0.80pF | ±0.05pF | GRM0335C2AR80WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2AR80BA01# |  |
|        |               |         | 0.90pF | ±0.05pF | GRM0335C2AR90WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2AR90BA01# |  |
|        |               |         | 1.0pF  | ±0.05pF | GRM0335C2A1R0WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2A1R0BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C2A1R0CA01# |  |
|        |               |         | 1.1pF  | ±0.05pF | GRM0335C2A1R1WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2A1R1BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C2A1R1CA01# |  |
|        |               |         | 1.2pF  | ±0.05pF | GRM0335C2A1R2WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2A1R2BA01# |  |
|        |               |         | 1.3pF  | ±0.05pF | GRM0335C2A1R3WA01# |  |
|        |               |         |        | ±0.05pF | GRM0335C2A1R3BA01# |  |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 100Vdc        | C0G     | 1.3pF | ±0.1pF  | GRM0335C2A1R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A1R3CA01# |  |
|        |               |         | 1.4pF | ±0.05pF | GRM0335C2A1R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A1R4BA01# |  |
|        |               |         | 1.5pF | ±0.25pF | GRM0335C2A1R4CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A1R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A1R5BA01# |  |
|        |               |         | 1.6pF | ±0.25pF | GRM0335C2A1R5CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A1R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A1R6BA01# |  |
|        |               |         | 1.7pF | ±0.25pF | GRM0335C2A1R6CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A1R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A1R7BA01# |  |
|        |               |         | 1.8pF | ±0.25pF | GRM0335C2A1R7CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A1R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A1R8BA01# |  |
|        |               |         | 1.9pF | ±0.25pF | GRM0335C2A1R8CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A1R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A1R9BA01# |  |
|        |               |         | 2.0pF | ±0.25pF | GRM0335C2A1R9CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A2R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A2R0BA01# |  |
|        |               |         | 2.1pF | ±0.25pF | GRM0335C2A2R0CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A2R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A2R1BA01# |  |
|        |               |         | 2.2pF | ±0.25pF | GRM0335C2A2R1CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A2R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A2R2BA01# |  |
|        |               |         | 2.3pF | ±0.25pF | GRM0335C2A2R2CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A2R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A2R3BA01# |  |
|        |               |         | 2.4pF | ±0.25pF | GRM0335C2A2R3CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A2R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A2R4BA01# |  |
|        |               |         | 2.5pF | ±0.25pF | GRM0335C2A2R4CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A2R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A2R5BA01# |  |
|        |               |         | 2.6pF | ±0.25pF | GRM0335C2A2R5CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A2R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A2R6BA01# |  |
|        |               |         | 2.7pF | ±0.25pF | GRM0335C2A2R6CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A2R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A2R7BA01# |  |
|        |               |         | 2.8pF | ±0.25pF | GRM0335C2A2R7CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A2R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A2R8BA01# |  |
|        |               |         | 2.9pF | ±0.25pF | GRM0335C2A2R8CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A2R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A2R9BA01# |  |
|        |               |         | 3.0pF | ±0.25pF | GRM0335C2A2R9CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A3R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A3R0BA01# |  |
|        |               |         | 3.1pF | ±0.25pF | GRM0335C2A3R0CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A3R1WA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 100Vdc        | C0G     | 3.1pF | ±0.1pF  | GRM0335C2A3R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A3R1CA01# |  |
|        |               |         | 3.2pF | ±0.05pF | GRM0335C2A3R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A3R2BA01# |  |
|        |               |         | 3.3pF | ±0.25pF | GRM0335C2A3R2CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A3R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A3R3BA01# |  |
|        |               |         | 3.4pF | ±0.25pF | GRM0335C2A3R3CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A3R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A3R4BA01# |  |
|        |               |         | 3.5pF | ±0.25pF | GRM0335C2A3R4CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A3R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A3R5BA01# |  |
|        |               |         | 3.6pF | ±0.25pF | GRM0335C2A3R5CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A3R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A3R6BA01# |  |
|        |               |         | 3.7pF | ±0.25pF | GRM0335C2A3R6CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A3R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A3R7BA01# |  |
|        |               |         | 3.8pF | ±0.25pF | GRM0335C2A3R7CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A3R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A3R8BA01# |  |
|        |               |         | 3.9pF | ±0.25pF | GRM0335C2A3R8CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A3R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A3R9BA01# |  |
|        |               |         | 4.0pF | ±0.25pF | GRM0335C2A3R9CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A4R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A4R0BA01# |  |
|        |               |         | 4.1pF | ±0.25pF | GRM0335C2A4R0CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A4R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A4R1BA01# |  |
|        |               |         | 4.2pF | ±0.25pF | GRM0335C2A4R1CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A4R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A4R2BA01# |  |
|        |               |         | 4.3pF | ±0.25pF | GRM0335C2A4R2CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A4R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A4R3BA01# |  |
|        |               |         | 4.4pF | ±0.25pF | GRM0335C2A4R3CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A4R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A4R4BA01# |  |
|        |               |         | 4.5pF | ±0.25pF | GRM0335C2A4R4CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A4R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A4R5BA01# |  |
|        |               |         | 4.6pF | ±0.25pF | GRM0335C2A4R5CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A4R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A4R6BA01# |  |
|        |               |         | 4.7pF | ±0.25pF | GRM0335C2A4R6CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A4R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A4R7BA01# |  |
|        |               |         | 4.8pF | ±0.25pF | GRM0335C2A4R7CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A4R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A4R8BA01# |  |
|        |               |         | 4.9pF | ±0.25pF | GRM0335C2A4R8CA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A4R9WA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 100Vdc        | C0G     | 4.9pF | ±0.1pF  | GRM0335C2A4R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A4R9CA01# |  |
|        |               |         | 5.0pF | ±0.05pF | GRM0335C2A5R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A5R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A5R0CA01# |  |
|        |               |         | 5.1pF | ±0.05pF | GRM0335C2A5R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A5R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A5R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C2A5R1DA01# |  |
|        |               |         | 5.2pF | ±0.05pF | GRM0335C2A5R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A5R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A5R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C2A5R2DA01# |  |
|        |               |         | 5.3pF | ±0.05pF | GRM0335C2A5R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A5R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A5R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C2A5R3DA01# |  |
|        |               |         | 5.4pF | ±0.05pF | GRM0335C2A5R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A5R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A5R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C2A5R4DA01# |  |
|        |               |         | 5.5pF | ±0.05pF | GRM0335C2A5R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A5R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A5R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C2A5R5DA01# |  |
|        |               |         | 5.6pF | ±0.05pF | GRM0335C2A5R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A5R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A5R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C2A5R6DA01# |  |
|        |               |         | 5.7pF | ±0.05pF | GRM0335C2A5R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A5R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A5R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C2A5R7DA01# |  |
|        |               |         | 5.8pF | ±0.05pF | GRM0335C2A5R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A5R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A5R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C2A5R8DA01# |  |
|        |               |         | 5.9pF | ±0.05pF | GRM0335C2A5R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A5R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A5R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C2A5R9DA01# |  |
|        |               |         | 6.0pF | ±0.05pF | GRM0335C2A6R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A6R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A6R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C2A6R0DA01# |  |
|        |               |         | 6.1pF | ±0.05pF | GRM0335C2A6R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A6R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A6R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C2A6R1DA01# |  |
|        |               |         | 6.2pF | ±0.05pF | GRM0335C2A6R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A6R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A6R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C2A6R2DA01# |  |
|        |               |         | 6.3pF | ±0.05pF | GRM0335C2A6R3WA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 100Vdc        | C0G     | 6.3pF | ±0.1pF  | GRM0335C2A6R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A6R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C2A6R3DA01# |  |
|        |               |         | 6.4pF | ±0.05pF | GRM0335C2A6R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A6R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A6R4CA01# |  |
|        |               |         | 6.5pF | ±0.05pF | GRM0335C2A6R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A6R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A6R5CA01# |  |
|        |               |         | 6.6pF | ±0.05pF | GRM0335C2A6R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A6R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A6R6CA01# |  |
|        |               |         | 6.7pF | ±0.05pF | GRM0335C2A6R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A6R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A6R7CA01# |  |
|        |               |         | 6.8pF | ±0.05pF | GRM0335C2A6R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A6R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A6R8CA01# |  |
|        |               |         | 6.9pF | ±0.05pF | GRM0335C2A6R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A6R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A6R9CA01# |  |
|        |               |         | 7.0pF | ±0.05pF | GRM0335C2A7R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A7R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A7R0CA01# |  |
|        |               |         | 7.1pF | ±0.05pF | GRM0335C2A7R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A7R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A7R1CA01# |  |
|        |               |         | 7.2pF | ±0.05pF | GRM0335C2A7R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A7R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A7R2CA01# |  |
|        |               |         | 7.3pF | ±0.05pF | GRM0335C2A7R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A7R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A7R3CA01# |  |
|        |               |         | 7.4pF | ±0.05pF | GRM0335C2A7R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A7R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A7R4CA01# |  |
|        |               |         | 7.5pF | ±0.05pF | GRM0335C2A7R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A7R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A7R5CA01# |  |
|        |               |         | 7.6pF | ±0.05pF | GRM0335C2A7R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A7R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A7R6CA01# |  |

Part number # indicates the package specification code.



# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 100Vdc        | C0G     | 7.6pF | ±0.5pF  | GRM0335C2A7R6DA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A7R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A7R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A7R7CA01# |  |
|        |               |         | 7.7pF | ±0.5pF  | GRM0335C2A7R7DA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A7R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A7R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A7R8CA01# |  |
|        |               |         | 7.8pF | ±0.5pF  | GRM0335C2A7R8DA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A7R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A7R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A7R9CA01# |  |
|        |               |         | 7.9pF | ±0.5pF  | GRM0335C2A7R9DA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A8R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A8R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A8R0CA01# |  |
|        |               |         | 8.0pF | ±0.5pF  | GRM0335C2A8R0DA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A8R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A8R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A8R1CA01# |  |
|        |               |         | 8.1pF | ±0.5pF  | GRM0335C2A8R1DA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A8R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A8R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A8R2CA01# |  |
|        |               |         | 8.2pF | ±0.5pF  | GRM0335C2A8R2DA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A8R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A8R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A8R3CA01# |  |
|        |               |         | 8.3pF | ±0.5pF  | GRM0335C2A8R3DA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A8R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A8R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A8R4CA01# |  |
|        |               |         | 8.4pF | ±0.5pF  | GRM0335C2A8R4DA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A8R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A8R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A8R5CA01# |  |
|        |               |         | 8.5pF | ±0.5pF  | GRM0335C2A8R5DA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A8R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A8R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A8R6CA01# |  |
|        |               |         | 8.6pF | ±0.5pF  | GRM0335C2A8R6DA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A8R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A8R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A8R7CA01# |  |
|        |               |         | 8.7pF | ±0.5pF  | GRM0335C2A8R7DA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A8R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A8R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A8R8CA01# |  |
|        |               |         | 8.8pF | ±0.5pF  | GRM0335C2A8R8DA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A8R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C2A8R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C2A8R9CA01# |  |
|        |               |         | 9.0pF | ±0.5pF  | GRM0335C2A8R9DA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C2A9R0WA01# |  |

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.33mm | 100Vdc        | C0G     | 9.0pF  | ±0.1pF  | GRM0335C2A9R0BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C2A9R0CA01# |  |
|        |               |         |        | ±0.5pF  | GRM0335C2A9R0DA01# |  |
|        |               |         | 9.1pF  | ±0.05pF | GRM0335C2A9R1WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2A9R1BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C2A9R1CA01# |  |
|        |               |         | 9.2pF  | ±0.5pF  | GRM0335C2A9R1DA01# |  |
|        |               |         |        | ±0.05pF | GRM0335C2A9R2WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2A9R2BA01# |  |
|        |               |         | 9.3pF  | ±0.25pF | GRM0335C2A9R2CA01# |  |
|        |               |         |        | ±0.5pF  | GRM0335C2A9R2DA01# |  |
|        |               |         | 9.4pF  | ±0.05pF | GRM0335C2A9R3WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2A9R3BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C2A9R3CA01# |  |
|        |               |         | 9.5pF  | ±0.5pF  | GRM0335C2A9R3DA01# |  |
|        |               |         |        | ±0.05pF | GRM0335C2A9R4WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2A9R4BA01# |  |
|        |               |         | 9.6pF  | ±0.25pF | GRM0335C2A9R4CA01# |  |
|        |               |         |        | ±0.5pF  | GRM0335C2A9R4DA01# |  |
|        |               |         | 9.7pF  | ±0.05pF | GRM0335C2A9R5WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2A9R5BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C2A9R5CA01# |  |
|        |               |         | 9.8pF  | ±0.5pF  | GRM0335C2A9R5DA01# |  |
|        |               |         |        | ±0.05pF | GRM0335C2A9R6WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2A9R6BA01# |  |
|        |               |         | 9.9pF  | ±0.25pF | GRM0335C2A9R6CA01# |  |
|        |               |         |        | ±0.5pF  | GRM0335C2A9R6DA01# |  |
|        |               |         | 10pF   | ±0.05pF | GRM0335C2A9R7WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2A9R7BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C2A9R7CA01# |  |
|        |               |         | 12pF   | ±0.5pF  | GRM0335C2A9R7DA01# |  |
|        |               |         |        | ±0.05pF | GRM0335C2A9R8WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2A9R8BA01# |  |
|        |               |         | 15pF   | ±0.25pF | GRM0335C2A9R8CA01# |  |
|        |               |         |        | ±0.5pF  | GRM0335C2A9R8DA01# |  |
|        |               |         | 0.10pF | ±0.05pF | GRM0335C2A9R9WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C2A9R9BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C2A9R9CA01# |  |
|        |               |         | 0.20pF | ±0.5pF  | GRM0335C2A9R9DA01# |  |
|        |               |         |        | ±2%     | GRM0335C2A100GA01# |  |
|        |               |         |        | ±5%     | GRM0335C2A100JA01# |  |
|        |               |         | 0.30pF | ±2%     | GRM0335C2A120GA01# |  |
|        |               |         |        | ±5%     | GRM0335C2A120JA01# |  |
|        |               |         |        | ±2%     | GRM0335C2A150GA01# |  |
|        |               |         |        | ±5%     | GRM0335C2A150JA01# |  |
|        |               | CK      | 0.10pF | ±0.05pF | GRM0334C2AR10WA01# |  |
|        |               |         |        | ±0.05pF | GRM0334C2AR20WA01# |  |
|        |               |         | 0.20pF | ±0.1pF  | GRM0334C2AR20BA01# |  |
|        |               |         |        | ±0.05pF | GRM0334C2AR30WA01# |  |
|        |               |         | 0.30pF | ±0.1pF  | GRM0334C2AR30BA01# |  |
|        |               |         |        | ±0.05pF | GRM0334C2AR40WA01# |  |
|        |               |         | 0.40pF | ±0.1pF  | GRM0334C2AR40BA01# |  |
|        |               |         |        | ±0.05pF | GRM0334C2AR50WA01# |  |
|        |               |         | 0.50pF | ±0.1pF  | GRM0334C2AR50BA01# |  |
|        |               |         |        | ±0.05pF | GRM0334C2AR50BA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.33mm | 100Vdc        | CK      | 0.60pF | ±0.05pF | GRM0334C2AR60WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C2AR60BA01# |  |
|        |               |         | 0.70pF | ±0.05pF | GRM0334C2AR70WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C2AR70BA01# |  |
|        |               |         | 0.80pF | ±0.05pF | GRM0334C2AR80WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C2AR80BA01# |  |
|        |               |         | 0.90pF | ±0.05pF | GRM0334C2AR90WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C2AR90BA01# |  |
|        |               |         | 1.0pF  | ±0.05pF | GRM0334C2A1R0WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C2A1R0BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C2A1R0CA01# |  |
|        |               |         | 1.1pF  | ±0.05pF | GRM0334C2A1R1WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C2A1R1BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C2A1R1CA01# |  |
|        |               |         | 1.2pF  | ±0.05pF | GRM0334C2A1R2WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C2A1R2BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C2A1R2CA01# |  |
|        |               |         | 1.3pF  | ±0.05pF | GRM0334C2A1R3WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C2A1R3BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C2A1R3CA01# |  |
|        |               |         | 1.4pF  | ±0.05pF | GRM0334C2A1R4WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C2A1R4BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C2A1R4CA01# |  |
|        |               |         | 1.5pF  | ±0.05pF | GRM0334C2A1R5WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C2A1R5BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C2A1R5CA01# |  |
|        |               |         | 1.6pF  | ±0.05pF | GRM0334C2A1R6WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C2A1R6BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C2A1R6CA01# |  |
|        |               |         | 1.7pF  | ±0.05pF | GRM0334C2A1R7WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C2A1R7BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C2A1R7CA01# |  |
|        |               |         | 1.8pF  | ±0.05pF | GRM0334C2A1R8WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C2A1R8BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C2A1R8CA01# |  |
|        |               |         | 1.9pF  | ±0.05pF | GRM0334C2A1R9WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C2A1R9BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C2A1R9CA01# |  |
|        |               |         | 2.0pF  | ±0.05pF | GRM0334C2A2R0WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C2A2R0BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C2A2R0CA01# |  |
|        |               | CJ      | 2.1pF  | ±0.05pF | GRM0333C2A2R1WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0333C2A2R1BA01# |  |
|        |               |         |        | ±0.25pF | GRM0333C2A2R1CA01# |  |
|        |               |         | 2.2pF  | ±0.05pF | GRM0333C2A2R2WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0333C2A2R2BA01# |  |
|        |               |         |        | ±0.25pF | GRM0333C2A2R2CA01# |  |
|        |               |         | 2.3pF  | ±0.05pF | GRM0333C2A2R3WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0333C2A2R3BA01# |  |
|        |               |         |        | ±0.25pF | GRM0333C2A2R3CA01# |  |
|        |               |         | 2.4pF  | ±0.05pF | GRM0333C2A2R4WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0333C2A2R4BA01# |  |
|        |               |         |        | ±0.25pF | GRM0333C2A2R4CA01# |  |
|        |               |         | 2.5pF  | ±0.05pF | GRM0333C2A2R5WA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 100Vdc        | CJ      | 2.5pF | ±0.1pF  | GRM0333C2A2R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C2A2R5CA01# |  |
|        |               |         | 2.6pF | ±0.05pF | GRM0333C2A2R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C2A2R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C2A2R6CA01# |  |
|        |               |         | 2.7pF | ±0.05pF | GRM0333C2A2R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C2A2R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C2A2R7CA01# |  |
|        |               |         | 2.8pF | ±0.05pF | GRM0333C2A2R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C2A2R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C2A2R8CA01# |  |
|        |               |         | 2.9pF | ±0.05pF | GRM0333C2A2R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C2A2R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C2A2R9CA01# |  |
|        |               |         | 3.0pF | ±0.05pF | GRM0333C2A3R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C2A3R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C2A3R0CA01# |  |
|        |               |         | 3.1pF | ±0.05pF | GRM0333C2A3R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C2A3R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C2A3R1CA01# |  |
|        |               |         | 3.2pF | ±0.05pF | GRM0333C2A3R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C2A3R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C2A3R2CA01# |  |
|        |               |         | 3.3pF | ±0.05pF | GRM0333C2A3R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C2A3R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C2A3R3CA01# |  |
|        |               |         | 3.4pF | ±0.05pF | GRM0333C2A3R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C2A3R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C2A3R4CA01# |  |
|        |               |         | 3.5pF | ±0.05pF | GRM0333C2A3R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C2A3R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C2A3R5CA01# |  |
|        |               |         | 3.6pF | ±0.05pF | GRM0333C2A3R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C2A3R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C2A3R6CA01# |  |
|        |               |         | 3.7pF | ±0.05pF | GRM0333C2A3R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C2A3R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C2A3R7CA01# |  |
|        |               |         | 3.8pF | ±0.05pF | GRM0333C2A3R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C2A3R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C2A3R8CA01# |  |
|        |               |         | 3.9pF | ±0.05pF | GRM0333C2A3R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C2A3R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C2A3R9CA01# |  |
|        |               | CH      | 4.0pF | ±0.05pF | GRM0332C2A4R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A4R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A4R0CA01# |  |
|        |               |         | 4.1pF | ±0.05pF | GRM0332C2A4R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A4R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A4R1CA01# |  |
|        |               |         | 4.2pF | ±0.05pF | GRM0332C2A4R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A4R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A4R2CA01# |  |
|        |               |         | 4.3pF | ±0.05pF | GRM0332C2A4R3WA01# |  |
|        |               |         |       |         |                    |  |
|        |               |         |       |         |                    |  |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 100Vdc        | CH      | 4.3pF | ±0.1pF  | GRM0332C2A4R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A4R3CA01# |  |
|        |               |         | 4.4pF | ±0.05pF | GRM0332C2A4R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A4R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A4R4CA01# |  |
|        |               |         | 4.5pF | ±0.05pF | GRM0332C2A4R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A4R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A4R5CA01# |  |
|        |               |         | 4.6pF | ±0.05pF | GRM0332C2A4R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A4R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A4R6CA01# |  |
|        |               |         | 4.7pF | ±0.05pF | GRM0332C2A4R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A4R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A4R7CA01# |  |
|        |               |         | 4.8pF | ±0.05pF | GRM0332C2A4R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A4R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A4R8CA01# |  |
|        |               |         | 4.9pF | ±0.05pF | GRM0332C2A4R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A4R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A4R9CA01# |  |
|        |               |         | 5.0pF | ±0.05pF | GRM0332C2A5R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A5R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A5R0CA01# |  |
|        |               |         | 5.1pF | ±0.05pF | GRM0332C2A5R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A5R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A5R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A5R1DA01# |  |
|        |               |         | 5.2pF | ±0.05pF | GRM0332C2A5R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A5R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A5R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A5R2DA01# |  |
|        |               |         | 5.3pF | ±0.05pF | GRM0332C2A5R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A5R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A5R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A5R3DA01# |  |
|        |               |         | 5.4pF | ±0.05pF | GRM0332C2A5R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A5R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A5R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A5R4DA01# |  |
|        |               |         | 5.5pF | ±0.05pF | GRM0332C2A5R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A5R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A5R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A5R5DA01# |  |
|        |               |         | 5.6pF | ±0.05pF | GRM0332C2A5R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A5R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A5R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A5R6DA01# |  |
|        |               |         | 5.7pF | ±0.05pF | GRM0332C2A5R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A5R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A5R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A5R7DA01# |  |
|        |               |         | 5.8pF | ±0.05pF | GRM0332C2A5R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A5R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A5R8CA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A5R8CA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 100Vdc        | CH      | 5.8pF | ±0.5pF  | GRM0332C2A5R8DA01# |  |
|        |               |         |       | ±0.05pF | GRM0332C2A5R9WA01# |  |
|        |               |         | 5.9pF | ±0.1pF  | GRM0332C2A5R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A5R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A5R9DA01# |  |
|        |               |         | 6.0pF | ±0.05pF | GRM0332C2A6R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A6R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A6R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A6R0DA01# |  |
|        |               |         | 6.1pF | ±0.05pF | GRM0332C2A6R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A6R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A6R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A6R1DA01# |  |
|        |               |         | 6.2pF | ±0.05pF | GRM0332C2A6R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A6R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A6R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A6R2DA01# |  |
|        |               |         | 6.3pF | ±0.05pF | GRM0332C2A6R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A6R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A6R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A6R3DA01# |  |
|        |               |         | 6.4pF | ±0.05pF | GRM0332C2A6R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A6R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A6R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A6R4DA01# |  |
|        |               |         | 6.5pF | ±0.05pF | GRM0332C2A6R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A6R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A6R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A6R5DA01# |  |
|        |               |         | 6.6pF | ±0.05pF | GRM0332C2A6R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A6R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A6R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A6R6DA01# |  |
|        |               |         | 6.7pF | ±0.05pF | GRM0332C2A6R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A6R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A6R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A6R7DA01# |  |
|        |               |         | 6.8pF | ±0.05pF | GRM0332C2A6R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A6R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A6R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A6R8DA01# |  |
|        |               |         | 6.9pF | ±0.05pF | GRM0332C2A6R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A6R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A6R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A6R9DA01# |  |
|        |               |         | 7.0pF | ±0.05pF | GRM0332C2A7R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A7R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A7R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A7R0DA01# |  |
|        |               |         | 7.1pF | ±0.05pF | GRM0332C2A7R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A7R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A7R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A7R1DA01# |  |
|        |               |         | 7.2pF | ±0.05pF | GRM0332C2A7R2WA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 100Vdc        | CH      | 7.2pF | ±0.1pF  | GRM0332C2A7R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A7R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A7R2DA01# |  |
|        |               |         | 7.3pF | ±0.05pF | GRM0332C2A7R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A7R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A7R3CA01# |  |
|        |               |         | 7.4pF | ±0.05pF | GRM0332C2A7R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A7R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A7R4CA01# |  |
|        |               |         | 7.5pF | ±0.05pF | GRM0332C2A7R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A7R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A7R5CA01# |  |
|        |               |         | 7.6pF | ±0.05pF | GRM0332C2A7R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A7R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A7R6CA01# |  |
|        |               |         | 7.7pF | ±0.05pF | GRM0332C2A7R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A7R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A7R7CA01# |  |
|        |               |         | 7.8pF | ±0.05pF | GRM0332C2A7R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A7R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A7R8CA01# |  |
|        |               |         | 7.9pF | ±0.05pF | GRM0332C2A7R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A7R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A7R9CA01# |  |
|        |               |         | 8.0pF | ±0.05pF | GRM0332C2A8R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A8R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A8R0CA01# |  |
|        |               |         | 8.1pF | ±0.05pF | GRM0332C2A8R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A8R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A8R1CA01# |  |
|        |               |         | 8.2pF | ±0.05pF | GRM0332C2A8R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A8R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A8R2CA01# |  |
|        |               |         | 8.3pF | ±0.05pF | GRM0332C2A8R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A8R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A8R3CA01# |  |
|        |               |         | 8.4pF | ±0.05pF | GRM0332C2A8R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A8R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A8R4CA01# |  |
|        |               |         | 8.5pF | ±0.05pF | GRM0332C2A8R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A8R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A8R5CA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 100Vdc        | CH      | 8.5pF | ±0.5pF  | GRM0332C2A8R5DA01# |  |
|        |               |         |       | ±0.05pF | GRM0332C2A8R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A8R6BA01# |  |
|        |               |         | 8.6pF | ±0.25pF | GRM0332C2A8R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C2A8R6DA01# |  |
|        |               |         | 8.7pF | ±0.05pF | GRM0332C2A8R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A8R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A8R7CA01# |  |
|        |               |         | 8.8pF | ±0.05pF | GRM0332C2A8R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A8R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A8R8CA01# |  |
|        |               |         | 8.9pF | ±0.05pF | GRM0332C2A8R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A8R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A8R9CA01# |  |
|        |               |         | 9.0pF | ±0.05pF | GRM0332C2A9R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A9R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A9R0CA01# |  |
|        |               |         | 9.1pF | ±0.05pF | GRM0332C2A9R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A9R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A9R1CA01# |  |
|        |               |         | 9.2pF | ±0.05pF | GRM0332C2A9R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A9R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A9R2CA01# |  |
|        |               |         | 9.3pF | ±0.05pF | GRM0332C2A9R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A9R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A9R3CA01# |  |
|        |               |         | 9.4pF | ±0.05pF | GRM0332C2A9R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A9R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A9R4CA01# |  |
|        |               |         | 9.5pF | ±0.05pF | GRM0332C2A9R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A9R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A9R5CA01# |  |
|        |               |         | 9.6pF | ±0.05pF | GRM0332C2A9R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A9R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A9R6CA01# |  |
|        |               |         | 9.7pF | ±0.05pF | GRM0332C2A9R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A9R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A9R7CA01# |  |
|        |               |         | 9.8pF | ±0.05pF | GRM0332C2A9R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A9R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A9R8CA01# |  |
|        |               |         | 9.9pF | ±0.05pF | GRM0332C2A9R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C2A9R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C2A9R9CA01# |  |

Part number # indicates the package specification code.



## GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.33mm | 100Vdc        | CH      | 9.9pF  | ±0.1pF  | GRM0332C2A9R9BA01# |  |
|        |               |         |        | ±0.25pF | GRM0332C2A9R9CA01# |  |
|        |               |         |        | ±0.5pF  | GRM0332C2A9R9DA01# |  |
|        |               |         | 10pF   | ±2%     | GRM0332C2A100GA01# |  |
|        |               |         |        | ±5%     | GRM0332C2A100JA01# |  |
|        |               |         | 12pF   | ±2%     | GRM0332C2A120GA01# |  |
|        |               |         |        | ±5%     | GRM0332C2A120JA01# |  |
|        |               |         | 15pF   | ±2%     | GRM0332C2A150GA01# |  |
|        |               |         |        | ±5%     | GRM0332C2A150JA01# |  |
|        | 50Vdc         | C0G     | 0.10pF | ±0.05pF | GRM0335C1HR10WA01# |  |
|        |               |         |        | ±0.05pF | GRM0335C1HR20WA01# |  |
|        |               |         | 0.20pF | ±0.05pF | GRM0335C1HR20BA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1HR20CA01# |  |
|        |               |         | 0.30pF | ±0.05pF | GRM0335C1HR30WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1HR30BA01# |  |
|        |               |         | 0.40pF | ±0.05pF | GRM0335C1HR40WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1HR40BA01# |  |
|        |               |         | 0.50pF | ±0.05pF | GRM0335C1HR50WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1HR50BA01# |  |
|        |               |         | 0.60pF | ±0.05pF | GRM0335C1HR60WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1HR60BA01# |  |
|        |               |         | 0.70pF | ±0.05pF | GRM0335C1HR70WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1HR70BA01# |  |
|        |               |         | 0.80pF | ±0.05pF | GRM0335C1HR80WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1HR80BA01# |  |
|        |               |         | 0.90pF | ±0.05pF | GRM0335C1HR90WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1HR90BA01# |  |
|        |               |         | 1.0pF  | ±0.05pF | GRM0335C1H1R0WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1H1R0BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C1H1R0CA01# |  |
|        |               |         | 1.1pF  | ±0.05pF | GRM0335C1H1R1WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1H1R1BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C1H1R1CA01# |  |
|        |               |         | 1.2pF  | ±0.05pF | GRM0335C1H1R2WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1H1R2BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C1H1R2CA01# |  |
|        |               |         | 1.3pF  | ±0.05pF | GRM0335C1H1R3WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1H1R3BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C1H1R3CA01# |  |
|        |               |         | 1.4pF  | ±0.05pF | GRM0335C1H1R4WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1H1R4BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C1H1R4CA01# |  |
|        |               |         | 1.5pF  | ±0.05pF | GRM0335C1H1R5WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1H1R5BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C1H1R5CA01# |  |
|        |               |         | 1.6pF  | ±0.05pF | GRM0335C1H1R6WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1H1R6BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C1H1R6CA01# |  |
|        |               |         | 1.7pF  | ±0.05pF | GRM0335C1H1R7WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1H1R7BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C1H1R7CA01# |  |
|        |               |         | 1.8pF  | ±0.05pF | GRM0335C1H1R8WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1H1R8BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C1H1R8CA01# |  |
|        |               |         | 1.9pF  | ±0.05pF | GRM0335C1H1R9WA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 50Vdc         | C0G     | 1.9pF | ±0.1pF  | GRM0335C1H1R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H1R9CA01# |  |
|        |               |         | 2.0pF | ±0.05pF | GRM0335C1H2R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H2R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H2R0CA01# |  |
|        |               |         | 2.1pF | ±0.05pF | GRM0335C1H2R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H2R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H2R1CA01# |  |
|        |               |         | 2.2pF | ±0.05pF | GRM0335C1H2R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H2R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H2R2CA01# |  |
|        |               |         | 2.3pF | ±0.05pF | GRM0335C1H2R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H2R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H2R3CA01# |  |
|        |               |         | 2.4pF | ±0.05pF | GRM0335C1H2R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H2R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H2R4CA01# |  |
|        |               |         | 2.5pF | ±0.05pF | GRM0335C1H2R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H2R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H2R5CA01# |  |
|        |               |         | 2.6pF | ±0.05pF | GRM0335C1H2R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H2R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H2R6CA01# |  |
|        |               |         | 2.7pF | ±0.05pF | GRM0335C1H2R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H2R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H2R7CA01# |  |
|        |               |         | 2.8pF | ±0.05pF | GRM0335C1H2R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H2R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H2R8CA01# |  |
|        |               |         | 2.9pF | ±0.05pF | GRM0335C1H2R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H2R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H2R9CA01# |  |
|        |               |         | 3.0pF | ±0.05pF | GRM0335C1H3R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H3R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H3R0CA01# |  |
|        |               |         | 3.1pF | ±0.05pF | GRM0335C1H3R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H3R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H3R1CA01# |  |
|        |               |         | 3.2pF | ±0.05pF | GRM0335C1H3R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H3R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H3R2CA01# |  |
|        |               |         | 3.3pF | ±0.05pF | GRM0335C1H3R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H3R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H3R3CA01# |  |
|        |               |         | 3.4pF | ±0.05pF | GRM0335C1H3R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H3R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H3R4CA01# |  |
|        |               |         | 3.5pF | ±0.05pF | GRM0335C1H3R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H3R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H3R5CA01# |  |
|        |               |         | 3.6pF | ±0.05pF | GRM0335C1H3R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H3R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H3R6CA01# |  |
|        |               |         | 3.7pF | ±0.05pF | GRM0335C1H3R7WA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 50Vdc         | C0G     | 3.7pF | ±0.1pF  | GRM0335C1H3R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H3R7CA01# |  |
|        |               |         | 3.8pF | ±0.05pF | GRM0335C1H3R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H3R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H3R8CA01# |  |
|        |               |         | 3.9pF | ±0.05pF | GRM0335C1H3R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H3R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H3R9CA01# |  |
|        |               |         | 4.0pF | ±0.05pF | GRM0335C1H4R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H4R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H4R0CA01# |  |
|        |               |         | 4.1pF | ±0.05pF | GRM0335C1H4R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H4R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H4R1CA01# |  |
|        |               |         | 4.2pF | ±0.05pF | GRM0335C1H4R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H4R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H4R2CA01# |  |
|        |               |         | 4.3pF | ±0.05pF | GRM0335C1H4R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H4R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H4R3CA01# |  |
|        |               |         | 4.4pF | ±0.05pF | GRM0335C1H4R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H4R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H4R4CA01# |  |
|        |               |         | 4.5pF | ±0.05pF | GRM0335C1H4R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H4R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H4R5CA01# |  |
|        |               |         | 4.6pF | ±0.05pF | GRM0335C1H4R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H4R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H4R6CA01# |  |
|        |               |         | 4.7pF | ±0.05pF | GRM0335C1H4R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H4R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H4R7CA01# |  |
|        |               |         | 4.8pF | ±0.05pF | GRM0335C1H4R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H4R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H4R8CA01# |  |
|        |               |         | 4.9pF | ±0.05pF | GRM0335C1H4R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H4R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H4R9CA01# |  |
|        |               |         | 5.0pF | ±0.05pF | GRM0335C1H5R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H5R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H5R0CA01# |  |
|        |               |         | 5.1pF | ±0.05pF | GRM0335C1H5R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H5R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H5R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H5R1DA01# |  |
|        |               |         | 5.2pF | ±0.05pF | GRM0335C1H5R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H5R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H5R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H5R2DA01# |  |
|        |               |         | 5.3pF | ±0.05pF | GRM0335C1H5R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H5R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H5R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H5R3DA01# |  |
|        |               |         | 5.4pF | ±0.05pF | GRM0335C1H5R4WA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 50Vdc         | C0G     | 5.4pF | ±0.1pF  | GRM0335C1H5R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H5R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H5R4DA01# |  |
|        |               |         | 5.5pF | ±0.05pF | GRM0335C1H5R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H5R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H5R5CA01# |  |
|        |               |         | 5.6pF | ±0.05pF | GRM0335C1H5R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H5R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H5R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H5R6DA01# |  |
|        |               |         | 5.7pF | ±0.05pF | GRM0335C1H5R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H5R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H5R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H5R7DA01# |  |
|        |               |         | 5.8pF | ±0.05pF | GRM0335C1H5R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H5R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H5R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H5R8DA01# |  |
|        |               |         | 5.9pF | ±0.05pF | GRM0335C1H5R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H5R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H5R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H5R9DA01# |  |
|        |               |         | 6.0pF | ±0.05pF | GRM0335C1H6R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H6R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H6R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H6R0DA01# |  |
|        |               |         | 6.1pF | ±0.05pF | GRM0335C1H6R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H6R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H6R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H6R1DA01# |  |
|        |               |         | 6.2pF | ±0.05pF | GRM0335C1H6R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H6R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H6R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H6R2DA01# |  |
|        |               |         | 6.3pF | ±0.05pF | GRM0335C1H6R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H6R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H6R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H6R3DA01# |  |
|        |               |         | 6.4pF | ±0.05pF | GRM0335C1H6R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H6R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H6R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H6R4DA01# |  |
|        |               |         | 6.5pF | ±0.05pF | GRM0335C1H6R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H6R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H6R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H6R5DA01# |  |
|        |               |         | 6.6pF | ±0.05pF | GRM0335C1H6R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H6R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H6R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H6R6DA01# |  |
|        |               |         | 6.7pF | ±0.05pF | GRM0335C1H6R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H6R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H6R7CA01# |  |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 50Vdc         | C0G     | 6.7pF | ±0.5pF  | GRM0335C1H6R7DA01# |  |
|        |               |         |       | ±0.05pF | GRM0335C1H6R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H6R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H6R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H6R8DA01# |  |
|        |               |         | 6.9pF | ±0.05pF | GRM0335C1H6R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H6R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H6R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H6R9DA01# |  |
|        |               |         | 7.0pF | ±0.05pF | GRM0335C1H7R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H7R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H7R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H7R0DA01# |  |
|        |               |         | 7.1pF | ±0.05pF | GRM0335C1H7R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H7R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H7R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H7R1DA01# |  |
|        |               |         | 7.2pF | ±0.05pF | GRM0335C1H7R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H7R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H7R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H7R2DA01# |  |
|        |               |         | 7.3pF | ±0.05pF | GRM0335C1H7R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H7R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H7R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H7R3DA01# |  |
|        |               |         | 7.4pF | ±0.05pF | GRM0335C1H7R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H7R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H7R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H7R4DA01# |  |
|        |               |         | 7.5pF | ±0.05pF | GRM0335C1H7R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H7R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H7R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H7R5DA01# |  |
|        |               |         | 7.6pF | ±0.05pF | GRM0335C1H7R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H7R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H7R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H7R6DA01# |  |
|        |               |         | 7.7pF | ±0.05pF | GRM0335C1H7R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H7R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H7R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H7R7DA01# |  |
|        |               |         | 7.8pF | ±0.05pF | GRM0335C1H7R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H7R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H7R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H7R8DA01# |  |
|        |               |         | 7.9pF | ±0.05pF | GRM0335C1H7R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H7R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H7R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H7R9DA01# |  |
|        |               |         | 8.0pF | ±0.05pF | GRM0335C1H8R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H8R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H8R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H8R0DA01# |  |
|        |               |         | 8.1pF | ±0.05pF | GRM0335C1H8R1WA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 50Vdc         | C0G     | 8.1pF | ±0.1pF  | GRM0335C1H8R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H8R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0335C1H8R1DA01# |  |
|        |               |         | 8.2pF | ±0.05pF | GRM0335C1H8R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H8R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H8R2CA01# |  |
|        |               |         | 8.3pF | ±0.05pF | GRM0335C1H8R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H8R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H8R3CA01# |  |
|        |               |         | 8.4pF | ±0.05pF | GRM0335C1H8R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H8R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H8R4CA01# |  |
|        |               |         | 8.5pF | ±0.05pF | GRM0335C1H8R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H8R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H8R5CA01# |  |
|        |               |         | 8.6pF | ±0.05pF | GRM0335C1H8R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H8R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H8R6CA01# |  |
|        |               |         | 8.7pF | ±0.05pF | GRM0335C1H8R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H8R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H8R7CA01# |  |
|        |               |         | 8.8pF | ±0.05pF | GRM0335C1H8R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H8R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H8R8CA01# |  |
|        |               |         | 8.9pF | ±0.05pF | GRM0335C1H8R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H8R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H8R9CA01# |  |
|        |               |         | 9.0pF | ±0.05pF | GRM0335C1H9R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H9R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H9R0CA01# |  |
|        |               |         | 9.1pF | ±0.05pF | GRM0335C1H9R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H9R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H9R1CA01# |  |
|        |               |         | 9.2pF | ±0.05pF | GRM0335C1H9R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H9R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H9R2CA01# |  |
|        |               |         | 9.3pF | ±0.05pF | GRM0335C1H9R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H9R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H9R3CA01# |  |
|        |               |         | 9.4pF | ±0.05pF | GRM0335C1H9R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0335C1H9R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0335C1H9R4CA01# |  |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.33mm | 50Vdc         | C0G     | 9.4pF  | ±0.5pF  | GRM0335C1H9R4DA01# |  |
|        |               |         |        | ±0.05pF | GRM0335C1H9R5WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1H9R5BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C1H9R5CA01# |  |
|        |               |         |        | ±0.5pF  | GRM0335C1H9R5DA01# |  |
|        |               |         | 9.6pF  | ±0.05pF | GRM0335C1H9R6WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1H9R6BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C1H9R6CA01# |  |
|        |               |         |        | ±0.5pF  | GRM0335C1H9R6DA01# |  |
|        |               |         | 9.7pF  | ±0.05pF | GRM0335C1H9R7WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1H9R7BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C1H9R7CA01# |  |
|        |               |         |        | ±0.5pF  | GRM0335C1H9R7DA01# |  |
|        |               |         | 9.8pF  | ±0.05pF | GRM0335C1H9R8WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1H9R8BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C1H9R8CA01# |  |
|        |               |         |        | ±0.5pF  | GRM0335C1H9R8DA01# |  |
|        |               |         | 9.9pF  | ±0.05pF | GRM0335C1H9R9WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0335C1H9R9BA01# |  |
|        |               |         |        | ±0.25pF | GRM0335C1H9R9CA01# |  |
|        |               |         |        | ±0.5pF  | GRM0335C1H9R9DA01# |  |
|        |               |         | 10pF   | ±2%     | GRM0335C1H100GA01# |  |
|        |               |         |        | ±5%     | GRM0335C1H100JA01# |  |
|        |               |         | 12pF   | ±2%     | GRM0335C1H120GA01# |  |
|        |               |         |        | ±5%     | GRM0335C1H120JA01# |  |
|        |               |         | 15pF   | ±2%     | GRM0335C1H150GA01# |  |
|        |               |         |        | ±5%     | GRM0335C1H150JA01# |  |
|        |               |         | 18pF   | ±2%     | GRM0335C1H180GA01# |  |
|        |               |         |        | ±5%     | GRM0335C1H180JA01# |  |
|        |               |         | 22pF   | ±2%     | GRM0335C1H220GA01# |  |
|        |               |         |        | ±5%     | GRM0335C1H220JA01# |  |
|        |               |         | 27pF   | ±2%     | GRM0335C1H270GA01# |  |
|        |               |         |        | ±5%     | GRM0335C1H270JA01# |  |
|        |               |         | 33pF   | ±2%     | GRM0335C1H330GA01# |  |
|        |               |         |        | ±5%     | GRM0335C1H330JA01# |  |
|        |               |         | 39pF   | ±2%     | GRM0335C1H390GA01# |  |
|        |               |         |        | ±5%     | GRM0335C1H390JA01# |  |
|        |               |         | 47pF   | ±2%     | GRM0335C1H470GA01# |  |
|        |               |         |        | ±5%     | GRM0335C1H470JA01# |  |
|        |               |         | 56pF   | ±2%     | GRM0335C1H560GA01# |  |
|        |               |         |        | ±5%     | GRM0335C1H560JA01# |  |
|        |               |         | 68pF   | ±2%     | GRM0335C1H680GA01# |  |
|        |               |         |        | ±5%     | GRM0335C1H680JA01# |  |
|        |               |         | 82pF   | ±2%     | GRM0335C1H820GA01# |  |
|        |               |         |        | ±5%     | GRM0335C1H820JA01# |  |
|        |               |         | 100pF  | ±2%     | GRM0335C1H101GA01# |  |
|        |               |         |        | ±5%     | GRM0335C1H101JA01# |  |
|        |               |         | 120pF  | ±2%     | GRM0335C1H121GA01# |  |
|        |               |         |        | ±5%     | GRM0335C1H121JA01# |  |
|        |               | CK      | 0.10pF | ±0.05pF | GRM0334C1HR10WA01# |  |
|        |               |         |        | ±0.05pF | GRM0334C1HR20WA01# |  |
|        |               |         | 0.20pF | ±0.1pF  | GRM0334C1HR20BA01# |  |
|        |               |         | 0.30pF | ±0.05pF | GRM0334C1HR30WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1HR30BA01# |  |

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.33mm | 50Vdc         | CK      | 0.40pF | ±0.05pF | GRM0334C1HR40WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1HR40BA01# |  |
|        |               |         | 0.50pF | ±0.05pF | GRM0334C1HR50WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1HR50BA01# |  |
|        |               |         | 0.60pF | ±0.05pF | GRM0334C1HR60WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1HR60BA01# |  |
|        |               |         | 0.70pF | ±0.05pF | GRM0334C1HR70WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1HR70BA01# |  |
|        |               |         | 0.80pF | ±0.05pF | GRM0334C1HR80WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1HR80BA01# |  |
|        |               |         | 0.90pF | ±0.05pF | GRM0334C1HR90WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1HR90BA01# |  |
|        |               |         | 1.0pF  | ±0.05pF | GRM0334C1H1R0WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1H1R0BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C1H1R0CA01# |  |
|        |               |         | 1.1pF  | ±0.05pF | GRM0334C1H1R1WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1H1R1BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C1H1R1CA01# |  |
|        |               |         | 1.2pF  | ±0.05pF | GRM0334C1H1R2WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1H1R2BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C1H1R2CA01# |  |
|        |               |         | 1.3pF  | ±0.05pF | GRM0334C1H1R3WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1H1R3BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C1H1R3CA01# |  |
|        |               |         | 1.4pF  | ±0.05pF | GRM0334C1H1R4WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1H1R4BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C1H1R4CA01# |  |
|        |               |         | 1.5pF  | ±0.05pF | GRM0334C1H1R5WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1H1R5BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C1H1R5CA01# |  |
|        |               |         | 1.6pF  | ±0.05pF | GRM0334C1H1R6WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1H1R6BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C1H1R6CA01# |  |
|        |               |         | 1.7pF  | ±0.05pF | GRM0334C1H1R7WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1H1R7BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C1H1R7CA01# |  |
|        |               |         | 1.8pF  | ±0.05pF | GRM0334C1H1R8WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1H1R8BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C1H1R8CA01# |  |
|        |               |         | 1.9pF  | ±0.05pF | GRM0334C1H1R9WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1H1R9BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C1H1R9CA01# |  |
|        |               |         | 2.0pF  | ±0.05pF | GRM0334C1H2R0WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0334C1H2R0BA01# |  |
|        |               |         |        | ±0.25pF | GRM0334C1H2R0CA01# |  |
|        |               | CJ      | 2.1pF  | ±0.05pF | GRM0333C1H2R1WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0333C1H2R1BA01# |  |
|        |               |         |        | ±0.25pF | GRM0333C1H2R1CA01# |  |
|        |               |         | 2.2pF  | ±0.05pF | GRM0333C1H2R2WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0333C1H2R2BA01# |  |
|        |               |         |        | ±0.25pF | GRM0333C1H2R2CA01# |  |
|        |               |         | 2.3pF  | ±0.05pF | GRM0333C1H2R3WA01# |  |
|        |               |         |        | ±0.1pF  | GRM0333C1H2R3BA01# |  |
|        |               |         |        | ±0.25pF | GRM0333C1H2R3CA01# |  |

Part number # indicates the package specification code.



# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 50Vdc         | CJ      | 2.4pF | ±0.05pF | GRM0333C1H2R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C1H2R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C1H2R4CA01# |  |
|        |               |         | 2.5pF | ±0.05pF | GRM0333C1H2R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C1H2R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C1H2R5CA01# |  |
|        |               |         | 2.6pF | ±0.05pF | GRM0333C1H2R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C1H2R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C1H2R6CA01# |  |
|        |               |         | 2.7pF | ±0.05pF | GRM0333C1H2R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C1H2R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C1H2R7CA01# |  |
|        |               |         | 2.8pF | ±0.05pF | GRM0333C1H2R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C1H2R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C1H2R8CA01# |  |
|        |               |         | 2.9pF | ±0.05pF | GRM0333C1H2R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C1H2R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C1H2R9CA01# |  |
|        |               |         | 3.0pF | ±0.05pF | GRM0333C1H3R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C1H3R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C1H3R0CA01# |  |
|        |               |         | 3.1pF | ±0.05pF | GRM0333C1H3R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C1H3R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C1H3R1CA01# |  |
|        |               |         | 3.2pF | ±0.05pF | GRM0333C1H3R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C1H3R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C1H3R2CA01# |  |
|        |               |         | 3.3pF | ±0.05pF | GRM0333C1H3R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C1H3R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C1H3R3CA01# |  |
|        |               |         | 3.4pF | ±0.05pF | GRM0333C1H3R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C1H3R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C1H3R4CA01# |  |
|        |               |         | 3.5pF | ±0.05pF | GRM0333C1H3R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C1H3R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C1H3R5CA01# |  |
|        |               |         | 3.6pF | ±0.05pF | GRM0333C1H3R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C1H3R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C1H3R6CA01# |  |
|        |               |         | 3.7pF | ±0.05pF | GRM0333C1H3R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C1H3R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C1H3R7CA01# |  |
|        |               |         | 3.8pF | ±0.05pF | GRM0333C1H3R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C1H3R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C1H3R8CA01# |  |
|        |               |         | 3.9pF | ±0.05pF | GRM0333C1H3R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0333C1H3R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0333C1H3R9CA01# |  |
|        |               | CH      | 4.0pF | ±0.05pF | GRM0332C1H4R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H4R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H4R0CA01# |  |
|        |               |         | 4.1pF | ±0.05pF | GRM0332C1H4R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H4R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H4R1CA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 50Vdc         | CH      | 4.2pF | ±0.05pF | GRM0332C1H4R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H4R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H4R2CA01# |  |
|        |               |         | 4.3pF | ±0.05pF | GRM0332C1H4R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H4R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H4R3CA01# |  |
|        |               |         | 4.4pF | ±0.05pF | GRM0332C1H4R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H4R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H4R4CA01# |  |
|        |               |         | 4.5pF | ±0.05pF | GRM0332C1H4R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H4R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H4R5CA01# |  |
|        |               |         | 4.6pF | ±0.05pF | GRM0332C1H4R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H4R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H4R6CA01# |  |
|        |               |         | 4.7pF | ±0.05pF | GRM0332C1H4R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H4R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H4R7CA01# |  |
|        |               |         | 4.8pF | ±0.05pF | GRM0332C1H4R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H4R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H4R8CA01# |  |
|        |               |         | 4.9pF | ±0.05pF | GRM0332C1H4R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H4R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H4R9CA01# |  |
|        |               |         | 5.0pF | ±0.05pF | GRM0332C1H5R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H5R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H5R0CA01# |  |
|        |               |         | 5.1pF | ±0.05pF | GRM0332C1H5R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H5R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H5R1CA01# |  |
|        |               |         | 5.2pF | ±0.05pF | GRM0332C1H5R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H5R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H5R2CA01# |  |
|        |               |         | 5.3pF | ±0.05pF | GRM0332C1H5R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H5R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H5R3CA01# |  |
|        |               |         | 5.4pF | ±0.05pF | GRM0332C1H5R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H5R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H5R4CA01# |  |
|        |               |         | 5.5pF | ±0.05pF | GRM0332C1H5R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H5R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H5R5CA01# |  |
|        |               |         | 5.6pF | ±0.05pF | GRM0332C1H5R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H5R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H5R6CA01# |  |
|        |               |         | 5.7pF | ±0.05pF | GRM0332C1H5R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H5R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H5R7CA01# |  |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 50Vdc         | CH      | 5.7pF | ±0.5pF  | GRM0332C1H5R7DA01# |  |
|        |               |         |       | ±0.05pF | GRM0332C1H5R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H5R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H5R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H5R8DA01# |  |
|        |               |         | 5.9pF | ±0.05pF | GRM0332C1H5R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H5R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H5R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H5R9DA01# |  |
|        |               |         | 6.0pF | ±0.05pF | GRM0332C1H6R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H6R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H6R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H6R0DA01# |  |
|        |               |         | 6.1pF | ±0.05pF | GRM0332C1H6R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H6R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H6R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H6R1DA01# |  |
|        |               |         | 6.2pF | ±0.05pF | GRM0332C1H6R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H6R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H6R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H6R2DA01# |  |
|        |               |         | 6.3pF | ±0.05pF | GRM0332C1H6R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H6R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H6R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H6R3DA01# |  |
|        |               |         | 6.4pF | ±0.05pF | GRM0332C1H6R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H6R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H6R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H6R4DA01# |  |
|        |               |         | 6.5pF | ±0.05pF | GRM0332C1H6R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H6R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H6R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H6R5DA01# |  |
|        |               |         | 6.6pF | ±0.05pF | GRM0332C1H6R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H6R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H6R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H6R6DA01# |  |
|        |               |         | 6.7pF | ±0.05pF | GRM0332C1H6R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H6R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H6R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H6R7DA01# |  |
|        |               |         | 6.8pF | ±0.05pF | GRM0332C1H6R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H6R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H6R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H6R8DA01# |  |
|        |               |         | 6.9pF | ±0.05pF | GRM0332C1H6R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H6R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H6R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H6R9DA01# |  |
|        |               |         | 7.0pF | ±0.05pF | GRM0332C1H7R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H7R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H7R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H7R0DA01# |  |
|        |               |         | 7.1pF | ±0.05pF | GRM0332C1H7R1WA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 50Vdc         | CH      | 7.1pF | ±0.1pF  | GRM0332C1H7R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H7R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H7R1DA01# |  |
|        |               |         | 7.2pF | ±0.05pF | GRM0332C1H7R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H7R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H7R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H7R2DA01# |  |
|        |               |         | 7.3pF | ±0.05pF | GRM0332C1H7R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H7R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H7R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H7R3DA01# |  |
|        |               |         | 7.4pF | ±0.05pF | GRM0332C1H7R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H7R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H7R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H7R4DA01# |  |
|        |               |         | 7.5pF | ±0.05pF | GRM0332C1H7R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H7R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H7R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H7R5DA01# |  |
|        |               |         | 7.6pF | ±0.05pF | GRM0332C1H7R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H7R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H7R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H7R6DA01# |  |
|        |               |         | 7.7pF | ±0.05pF | GRM0332C1H7R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H7R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H7R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H7R7DA01# |  |
|        |               |         | 7.8pF | ±0.05pF | GRM0332C1H7R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H7R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H7R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H7R8DA01# |  |
|        |               |         | 7.9pF | ±0.05pF | GRM0332C1H7R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H7R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H7R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H7R9DA01# |  |
|        |               |         | 8.0pF | ±0.05pF | GRM0332C1H8R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H8R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H8R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H8R0DA01# |  |
|        |               |         | 8.1pF | ±0.05pF | GRM0332C1H8R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H8R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H8R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H8R1DA01# |  |
|        |               |         | 8.2pF | ±0.05pF | GRM0332C1H8R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H8R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H8R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H8R2DA01# |  |
|        |               |         | 8.3pF | ±0.05pF | GRM0332C1H8R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H8R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H8R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H8R3DA01# |  |
|        |               |         | 8.4pF | ±0.05pF | GRM0332C1H8R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H8R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H8R4CA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 50Vdc         | CH      | 8.4pF | ±0.5pF  | GRM0332C1H8R4DA01# |  |
|        |               |         |       | ±0.05pF | GRM0332C1H8R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H8R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H8R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H8R5DA01# |  |
|        |               |         | 8.6pF | ±0.05pF | GRM0332C1H8R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H8R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H8R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H8R6DA01# |  |
|        |               |         | 8.7pF | ±0.05pF | GRM0332C1H8R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H8R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H8R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H8R7DA01# |  |
|        |               |         | 8.8pF | ±0.05pF | GRM0332C1H8R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H8R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H8R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H8R8DA01# |  |
|        |               |         | 8.9pF | ±0.05pF | GRM0332C1H8R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H8R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H8R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H8R9DA01# |  |
|        |               |         | 9.0pF | ±0.05pF | GRM0332C1H9R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H9R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H9R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H9R0DA01# |  |
|        |               |         | 9.1pF | ±0.05pF | GRM0332C1H9R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H9R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H9R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H9R1DA01# |  |
|        |               |         | 9.2pF | ±0.05pF | GRM0332C1H9R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H9R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H9R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H9R2DA01# |  |
|        |               |         | 9.3pF | ±0.05pF | GRM0332C1H9R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H9R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H9R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H9R3DA01# |  |
|        |               |         | 9.4pF | ±0.05pF | GRM0332C1H9R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H9R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H9R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H9R4DA01# |  |
|        |               |         | 9.5pF | ±0.05pF | GRM0332C1H9R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H9R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H9R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H9R5DA01# |  |
|        |               |         | 9.6pF | ±0.05pF | GRM0332C1H9R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H9R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H9R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H9R6DA01# |  |
|        |               |         | 9.7pF | ±0.05pF | GRM0332C1H9R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H9R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H9R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H9R7DA01# |  |
|        |               |         | 9.8pF | ±0.05pF | GRM0332C1H9R8WA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 50Vdc         | CH      | 9.8pF | ±0.1pF  | GRM0332C1H9R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H9R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H9R8DA01# |  |
|        |               |         | 9.9pF | ±0.05pF | GRM0332C1H9R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM0332C1H9R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM0332C1H9R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM0332C1H9R9DA01# |  |
|        |               |         | 10pF  | ±2%     | GRM0332C1H100GA01# |  |
|        |               |         |       | ±5%     | GRM0332C1H100JA01# |  |
|        |               |         | 12pF  | ±2%     | GRM0332C1H120GA01# |  |
|        |               |         |       | ±5%     | GRM0332C1H120JA01# |  |
|        |               |         | 15pF  | ±2%     | GRM0332C1H150GA01# |  |
|        |               |         |       | ±5%     | GRM0332C1H150JA01# |  |
|        |               |         | 18pF  | ±2%     | GRM0332C1H180GA01# |  |
|        |               |         |       | ±5%     | GRM0332C1H180JA01# |  |
|        |               |         | 22pF  | ±2%     | GRM0332C1H220GA01# |  |
|        |               |         |       | ±5%     | GRM0332C1H220JA01# |  |
|        |               |         | 27pF  | ±2%     | GRM0332C1H270GA01# |  |
|        |               |         |       | ±5%     | GRM0332C1H270JA01# |  |
|        |               |         | 33pF  | ±2%     | GRM0332C1H330GA01# |  |
|        |               |         |       | ±5%     | GRM0332C1H330JA01# |  |
|        |               |         | 39pF  | ±2%     | GRM0332C1H390GA01# |  |
|        |               |         |       | ±5%     | GRM0332C1H390JA01# |  |
|        |               |         | 47pF  | ±2%     | GRM0332C1H470GA01# |  |
|        |               |         |       | ±5%     | GRM0332C1H470JA01# |  |
|        |               |         | 56pF  | ±2%     | GRM0332C1H560GA01# |  |
|        |               |         |       | ±5%     | GRM0332C1H560JA01# |  |
|        |               |         | 68pF  | ±2%     | GRM0332C1H680GA01# |  |
|        |               |         |       | ±5%     | GRM0332C1H680JA01# |  |
|        |               |         | 82pF  | ±2%     | GRM0332C1H820GA01# |  |
|        |               |         |       | ±5%     | GRM0332C1H820JA01# |  |
|        |               |         | 100pF | ±2%     | GRM0332C1H101GA01# |  |
|        |               |         |       | ±5%     | GRM0332C1H101JA01# |  |
|        |               |         | 120pF | ±2%     | GRM0332C1H121GA01# |  |
|        |               |         |       | ±5%     | GRM0332C1H121JA01# |  |

■ 1.0×0.5mm

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.55mm | 100Vdc        | C0G     | 0.10pF | ±0.05pF | GRM1555C2AR10WA01# |  |
|        |               |         |        | ±0.05pF | GRM1555C2AR20WA01# |  |
|        |               |         | 0.20pF | ±0.05pF | GRM1555C2AR20BA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2AR20CA01# |  |
|        |               |         | 0.30pF | ±0.05pF | GRM1555C2AR30WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2AR30BA01# |  |
|        |               |         | 0.40pF | ±0.05pF | GRM1555C2AR40WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2AR40BA01# |  |
|        |               |         | 0.50pF | ±0.05pF | GRM1555C2AR50WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2AR50BA01# |  |
|        |               |         | 0.60pF | ±0.05pF | GRM1555C2AR60WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2AR60BA01# |  |
|        |               |         | 0.70pF | ±0.05pF | GRM1555C2AR70WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2AR70BA01# |  |
|        |               |         | 0.80pF | ±0.05pF | GRM1555C2AR80WA01# |  |
|        |               |         |        | ±0.05pF | GRM1555C2AR80CA01# |  |

Part number # indicates the package specification code.



## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.55mm | 100Vdc        | C0G     | 0.80pF | ±0.1pF  | GRM1555C2AR80BA01# |  |
|        |               |         |        | ±0.05pF | GRM1555C2AR90WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2AR90BA01# |  |
|        |               |         | 1.0pF  | ±0.05pF | GRM1555C2A1R0WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2A1R0BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C2A1R0CA01# |  |
|        |               |         | 1.1pF  | ±0.05pF | GRM1555C2A1R1WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2A1R1BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C2A1R1CA01# |  |
|        |               |         | 1.2pF  | ±0.05pF | GRM1555C2A1R2WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2A1R2BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C2A1R2CA01# |  |
|        |               |         | 1.3pF  | ±0.05pF | GRM1555C2A1R3WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2A1R3BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C2A1R3CA01# |  |
|        |               |         | 1.4pF  | ±0.05pF | GRM1555C2A1R4WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2A1R4BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C2A1R4CA01# |  |
|        |               |         | 1.5pF  | ±0.05pF | GRM1555C2A1R5WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2A1R5BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C2A1R5CA01# |  |
|        |               |         | 1.6pF  | ±0.05pF | GRM1555C2A1R6WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2A1R6BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C2A1R6CA01# |  |
|        |               |         | 1.7pF  | ±0.05pF | GRM1555C2A1R7WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2A1R7BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C2A1R7CA01# |  |
|        |               |         | 1.8pF  | ±0.05pF | GRM1555C2A1R8WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2A1R8BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C2A1R8CA01# |  |
|        |               |         | 1.9pF  | ±0.05pF | GRM1555C2A1R9WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2A1R9BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C2A1R9CA01# |  |
|        |               |         | 2.0pF  | ±0.05pF | GRM1555C2A2R0WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2A2R0BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C2A2R0CA01# |  |
|        |               |         | 2.1pF  | ±0.05pF | GRM1555C2A2R1WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2A2R1BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C2A2R1CA01# |  |
|        |               |         | 2.2pF  | ±0.05pF | GRM1555C2A2R2WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2A2R2BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C2A2R2CA01# |  |
|        |               |         | 2.3pF  | ±0.05pF | GRM1555C2A2R3WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2A2R3BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C2A2R3CA01# |  |
|        |               |         | 2.4pF  | ±0.05pF | GRM1555C2A2R4WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2A2R4BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C2A2R4CA01# |  |
|        |               |         | 2.5pF  | ±0.05pF | GRM1555C2A2R5WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2A2R5BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C2A2R5CA01# |  |
|        |               |         | 2.6pF  | ±0.05pF | GRM1555C2A2R6WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C2A2R6BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C2A2R6CA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 100Vdc        | C0G     | 2.7pF | ±0.05pF | GRM1555C2A2R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A2R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A2R7CA01# |  |
|        |               |         | 2.8pF | ±0.05pF | GRM1555C2A2R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A2R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A2R8CA01# |  |
|        |               |         | 2.9pF | ±0.05pF | GRM1555C2A2R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A2R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A2R9CA01# |  |
|        |               |         | 3.0pF | ±0.05pF | GRM1555C2A3R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A3R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A3R0CA01# |  |
|        |               |         | 3.1pF | ±0.05pF | GRM1555C2A3R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A3R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A3R1CA01# |  |
|        |               |         | 3.2pF | ±0.05pF | GRM1555C2A3R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A3R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A3R2CA01# |  |
|        |               |         | 3.3pF | ±0.05pF | GRM1555C2A3R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A3R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A3R3CA01# |  |
|        |               |         | 3.4pF | ±0.05pF | GRM1555C2A3R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A3R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A3R4CA01# |  |
|        |               |         | 3.5pF | ±0.05pF | GRM1555C2A3R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A3R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A3R5CA01# |  |
|        |               |         | 3.6pF | ±0.05pF | GRM1555C2A3R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A3R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A3R6CA01# |  |
|        |               |         | 3.7pF | ±0.05pF | GRM1555C2A3R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A3R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A3R7CA01# |  |
|        |               |         | 3.8pF | ±0.05pF | GRM1555C2A3R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A3R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A3R8CA01# |  |
|        |               |         | 3.9pF | ±0.05pF | GRM1555C2A3R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A3R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A3R9CA01# |  |
|        |               |         | 4.0pF | ±0.05pF | GRM1555C2A4R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A4R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A4R0CA01# |  |
|        |               |         | 4.1pF | ±0.05pF | GRM1555C2A4R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A4R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A4R1CA01# |  |
|        |               |         | 4.2pF | ±0.05pF | GRM1555C2A4R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A4R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A4R2CA01# |  |
|        |               |         | 4.3pF | ±0.05pF | GRM1555C2A4R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A4R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A4R3CA01# |  |
|        |               |         | 4.4pF | ±0.05pF | GRM1555C2A4R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A4R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A4R4CA01# |  |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 100Vdc        | C0G     | 4.5pF | ±0.05pF | GRM1555C2A4R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A4R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A4R5CA01# |  |
|        |               |         | 4.6pF | ±0.05pF | GRM1555C2A4R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A4R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A4R6CA01# |  |
|        |               |         | 4.7pF | ±0.05pF | GRM1555C2A4R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A4R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A4R7CA01# |  |
|        |               |         | 4.8pF | ±0.05pF | GRM1555C2A4R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A4R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A4R8CA01# |  |
|        |               |         | 4.9pF | ±0.05pF | GRM1555C2A4R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A4R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A4R9CA01# |  |
|        |               |         | 5.0pF | ±0.05pF | GRM1555C2A5R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A5R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A5R0CA01# |  |
|        |               |         | 5.1pF | ±0.05pF | GRM1555C2A5R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A5R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A5R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A5R1DA01# |  |
|        |               |         | 5.2pF | ±0.05pF | GRM1555C2A5R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A5R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A5R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A5R2DA01# |  |
|        |               |         | 5.3pF | ±0.05pF | GRM1555C2A5R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A5R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A5R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A5R3DA01# |  |
|        |               |         | 5.4pF | ±0.05pF | GRM1555C2A5R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A5R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A5R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A5R4DA01# |  |
|        |               |         | 5.5pF | ±0.05pF | GRM1555C2A5R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A5R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A5R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A5R5DA01# |  |
|        |               |         | 5.6pF | ±0.05pF | GRM1555C2A5R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A5R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A5R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A5R6DA01# |  |
|        |               |         | 5.7pF | ±0.05pF | GRM1555C2A5R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A5R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A5R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A5R7DA01# |  |
|        |               |         | 5.8pF | ±0.05pF | GRM1555C2A5R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A5R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A5R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A5R8DA01# |  |
|        |               |         | 5.9pF | ±0.05pF | GRM1555C2A5R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A5R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A5R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A5R9DA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 100Vdc        | C0G     | 6.0pF | ±0.05pF | GRM1555C2A6R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A6R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A6R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A6R0DA01# |  |
|        |               |         | 6.1pF | ±0.05pF | GRM1555C2A6R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A6R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A6R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A6R1DA01# |  |
|        |               |         | 6.2pF | ±0.05pF | GRM1555C2A6R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A6R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A6R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A6R2DA01# |  |
|        |               |         | 6.3pF | ±0.05pF | GRM1555C2A6R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A6R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A6R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A6R3DA01# |  |
|        |               |         | 6.4pF | ±0.05pF | GRM1555C2A6R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A6R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A6R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A6R4DA01# |  |
|        |               |         | 6.5pF | ±0.05pF | GRM1555C2A6R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A6R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A6R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A6R5DA01# |  |
|        |               |         | 6.6pF | ±0.05pF | GRM1555C2A6R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A6R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A6R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A6R6DA01# |  |
|        |               |         | 6.7pF | ±0.05pF | GRM1555C2A6R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A6R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A6R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A6R7DA01# |  |
|        |               |         | 6.8pF | ±0.05pF | GRM1555C2A6R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A6R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A6R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A6R8DA01# |  |
|        |               |         | 6.9pF | ±0.05pF | GRM1555C2A6R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A6R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A6R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A6R9DA01# |  |
|        |               |         | 7.0pF | ±0.05pF | GRM1555C2A7R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A7R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A7R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A7R0DA01# |  |
|        |               |         | 7.1pF | ±0.05pF | GRM1555C2A7R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A7R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A7R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A7R1DA01# |  |
|        |               |         | 7.2pF | ±0.05pF | GRM1555C2A7R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A7R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A7R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A7R2DA01# |  |
|        |               |         | 7.3pF | ±0.05pF | GRM1555C2A7R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A7R3BA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 100Vdc        | C0G     | 7.3pF | ±0.25pF | GRM1555C2A7R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A7R3DA01# |  |
|        |               |         | 7.4pF | ±0.05pF | GRM1555C2A7R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A7R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A7R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A7R4DA01# |  |
|        |               |         | 7.5pF | ±0.05pF | GRM1555C2A7R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A7R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A7R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A7R5DA01# |  |
|        |               |         | 7.6pF | ±0.05pF | GRM1555C2A7R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A7R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A7R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A7R6DA01# |  |
|        |               |         | 7.7pF | ±0.05pF | GRM1555C2A7R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A7R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A7R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A7R7DA01# |  |
|        |               |         | 7.8pF | ±0.05pF | GRM1555C2A7R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A7R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A7R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A7R8DA01# |  |
|        |               |         | 7.9pF | ±0.05pF | GRM1555C2A7R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A7R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A7R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A7R9DA01# |  |
|        |               |         | 8.0pF | ±0.05pF | GRM1555C2A8R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A8R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A8R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A8R0DA01# |  |
|        |               |         | 8.1pF | ±0.05pF | GRM1555C2A8R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A8R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A8R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A8R1DA01# |  |
|        |               |         | 8.2pF | ±0.05pF | GRM1555C2A8R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A8R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A8R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A8R2DA01# |  |
|        |               |         | 8.3pF | ±0.05pF | GRM1555C2A8R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A8R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A8R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A8R3DA01# |  |
|        |               |         | 8.4pF | ±0.05pF | GRM1555C2A8R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A8R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A8R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A8R4DA01# |  |
|        |               |         | 8.5pF | ±0.05pF | GRM1555C2A8R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A8R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A8R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A8R5DA01# |  |
|        |               |         | 8.6pF | ±0.05pF | GRM1555C2A8R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A8R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A8R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A8R6DA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 100Vdc        | C0G     | 8.7pF | ±0.05pF | GRM1555C2A8R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A8R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A8R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A8R7DA01# |  |
|        |               |         | 8.8pF | ±0.05pF | GRM1555C2A8R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A8R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A8R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A8R8DA01# |  |
|        |               |         | 8.9pF | ±0.05pF | GRM1555C2A8R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A8R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A8R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A8R9DA01# |  |
|        |               |         | 9.0pF | ±0.05pF | GRM1555C2A9R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A9R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A9R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A9R0DA01# |  |
|        |               |         | 9.1pF | ±0.05pF | GRM1555C2A9R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A9R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A9R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A9R1DA01# |  |
|        |               |         | 9.2pF | ±0.05pF | GRM1555C2A9R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A9R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A9R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A9R2DA01# |  |
|        |               |         | 9.3pF | ±0.05pF | GRM1555C2A9R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A9R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A9R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A9R3DA01# |  |
|        |               |         | 9.4pF | ±0.05pF | GRM1555C2A9R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A9R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A9R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A9R4DA01# |  |
|        |               |         | 9.5pF | ±0.05pF | GRM1555C2A9R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A9R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A9R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A9R5DA01# |  |
|        |               |         | 9.6pF | ±0.05pF | GRM1555C2A9R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A9R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A9R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A9R6DA01# |  |
|        |               |         | 9.7pF | ±0.05pF | GRM1555C2A9R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A9R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A9R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A9R7DA01# |  |
|        |               |         | 9.8pF | ±0.05pF | GRM1555C2A9R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A9R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A9R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A9R8DA01# |  |
|        |               |         | 9.9pF | ±0.05pF | GRM1555C2A9R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C2A9R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C2A9R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C2A9R9DA01# |  |
|        |               |         | 10pF  | ±2%     | GRM1555C2A100GA01# |  |
|        |               |         |       | ±5%     | GRM1555C2A100JA01# |  |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.55mm | 100Vdc        | C0G     | 12pF   | ±2%     | GRM1555C2A120GA01# |  |
|        |               |         |        | ±5%     | GRM1555C2A120JA01# |  |
|        |               |         | 15pF   | ±2%     | GRM1555C2A150GA01# |  |
|        |               |         |        | ±5%     | GRM1555C2A150JA01# |  |
|        |               |         | 18pF   | ±2%     | GRM1555C2A180GA01# |  |
|        |               |         |        | ±5%     | GRM1555C2A180JA01# |  |
|        |               |         | 22pF   | ±2%     | GRM1555C2A220GA01# |  |
|        |               |         |        | ±5%     | GRM1555C2A220JA01# |  |
|        |               |         | 27pF   | ±2%     | GRM1555C2A270GA01# |  |
|        |               |         |        | ±5%     | GRM1555C2A270JA01# |  |
|        |               |         | 33pF   | ±2%     | GRM1555C2A330GA01# |  |
|        |               |         |        | ±5%     | GRM1555C2A330JA01# |  |
|        |               |         | 39pF   | ±2%     | GRM1555C2A390GA01# |  |
|        |               |         |        | ±5%     | GRM1555C2A390JA01# |  |
|        |               |         | 47pF   | ±2%     | GRM1555C2A470GA01# |  |
|        |               |         |        | ±5%     | GRM1555C2A470JA01# |  |
|        |               |         | 56pF   | ±2%     | GRM1555C2A560GA01# |  |
|        |               |         |        | ±5%     | GRM1555C2A560JA01# |  |
|        |               |         | 68pF   | ±2%     | GRM1555C2A680GA01# |  |
|        |               |         |        | ±5%     | GRM1555C2A680JA01# |  |
|        |               |         | 82pF   | ±2%     | GRM1555C2A820GA01# |  |
|        |               |         |        | ±5%     | GRM1555C2A820JA01# |  |
|        |               |         | 100pF  | ±2%     | GRM1555C2A101GA01# |  |
|        |               |         |        | ±5%     | GRM1555C2A101JA01# |  |
|        |               | CK      | 0.10pF | ±0.05pF | GRM1554C2AR10WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C2AR20BA01# |  |
|        |               |         | 0.20pF | ±0.05pF | GRM1554C2AR20WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C2AR20BA01# |  |
|        |               |         | 0.30pF | ±0.05pF | GRM1554C2AR30WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C2AR30BA01# |  |
|        |               |         | 0.40pF | ±0.05pF | GRM1554C2AR40WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C2AR40BA01# |  |
|        |               |         | 0.50pF | ±0.05pF | GRM1554C2AR50WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C2AR50BA01# |  |
|        |               |         | 0.60pF | ±0.05pF | GRM1554C2AR60WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C2AR60BA01# |  |
|        |               |         | 0.70pF | ±0.05pF | GRM1554C2AR70WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C2AR70BA01# |  |
|        |               |         | 0.80pF | ±0.05pF | GRM1554C2AR80WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C2AR80BA01# |  |
|        |               |         | 0.90pF | ±0.05pF | GRM1554C2AR90WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C2AR90BA01# |  |
|        |               |         | 1.0pF  | ±0.05pF | GRM1554C2A1R0WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C2A1R0BA01# |  |
|        |               |         | 1.1pF  | ±0.05pF | GRM1554C2A1R1WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C2A1R1BA01# |  |
|        |               |         | 1.2pF  | ±0.05pF | GRM1554C2A1R2WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C2A1R2BA01# |  |
|        |               |         | 1.3pF  | ±0.05pF | GRM1554C2A1R3WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C2A1R3BA01# |  |
|        |               |         | 1.4pF  | ±0.05pF | GRM1554C2A1R4WA01# |  |
|        |               |         |        | ±0.25pF | GRM1554C2A1R4CA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 100Vdc        | CK      | 1.4pF | ±0.1pF  | GRM1554C2A1R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1554C2A1R4CA01# |  |
|        |               |         | 1.5pF | ±0.05pF | GRM1554C2A1R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1554C2A1R5BA01# |  |
|        |               |         | 1.6pF | ±0.05pF | GRM1554C2A1R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1554C2A1R6BA01# |  |
|        |               |         | 1.7pF | ±0.05pF | GRM1554C2A1R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1554C2A1R7BA01# |  |
|        |               |         | 1.8pF | ±0.05pF | GRM1554C2A1R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1554C2A1R8BA01# |  |
|        |               |         | 1.9pF | ±0.05pF | GRM1554C2A1R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1554C2A1R9BA01# |  |
|        |               |         | 2.0pF | ±0.05pF | GRM1554C2A2R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1554C2A2R0BA01# |  |
|        |               |         | 2.1pF | ±0.05pF | GRM1553C2A2R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A2R1BA01# |  |
|        |               |         | 2.2pF | ±0.05pF | GRM1553C2A2R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A2R2BA01# |  |
|        |               |         | 2.3pF | ±0.05pF | GRM1553C2A2R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A2R3BA01# |  |
|        |               |         | 2.4pF | ±0.05pF | GRM1553C2A2R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A2R4BA01# |  |
|        |               |         | 2.5pF | ±0.05pF | GRM1553C2A2R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A2R5BA01# |  |
|        |               |         | 2.6pF | ±0.05pF | GRM1553C2A2R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A2R6BA01# |  |
|        |               |         | 2.7pF | ±0.05pF | GRM1553C2A2R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A2R7BA01# |  |
|        |               |         | 2.8pF | ±0.05pF | GRM1553C2A2R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A2R8BA01# |  |
|        |               |         | 2.9pF | ±0.05pF | GRM1553C2A2R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A2R9BA01# |  |
|        |               |         | 3.0pF | ±0.05pF | GRM1553C2A3R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A3R0BA01# |  |
|        |               |         | 3.1pF | ±0.05pF | GRM1553C2A3R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A3R1BA01# |  |
|        |               |         | 3.2pF | ±0.05pF | GRM1553C2A3R2WA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C2A3R2CA01# |  |

Part number # indicates the package specification code.



## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 100Vdc        | CJ      | 3.2pF | ±0.1pF  | GRM1553C2A3R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C2A3R2CA01# |  |
|        |               |         | 3.3pF | ±0.05pF | GRM1553C2A3R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A3R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C2A3R3CA01# |  |
|        |               |         | 3.4pF | ±0.05pF | GRM1553C2A3R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A3R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C2A3R4CA01# |  |
|        |               |         | 3.5pF | ±0.05pF | GRM1553C2A3R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A3R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C2A3R5CA01# |  |
|        |               |         | 3.6pF | ±0.05pF | GRM1553C2A3R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A3R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C2A3R6CA01# |  |
|        |               |         | 3.7pF | ±0.05pF | GRM1553C2A3R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A3R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C2A3R7CA01# |  |
|        |               |         | 3.8pF | ±0.05pF | GRM1553C2A3R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A3R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C2A3R8CA01# |  |
|        |               |         | 3.9pF | ±0.05pF | GRM1553C2A3R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C2A3R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C2A3R9CA01# |  |
|        |               | CH      | 4.0pF | ±0.05pF | GRM1552C2A4R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A4R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A4R0CA01# |  |
|        |               |         | 4.1pF | ±0.05pF | GRM1552C2A4R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A4R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A4R1CA01# |  |
|        |               |         | 4.2pF | ±0.05pF | GRM1552C2A4R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A4R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A4R2CA01# |  |
|        |               |         | 4.3pF | ±0.05pF | GRM1552C2A4R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A4R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A4R3CA01# |  |
|        |               |         | 4.4pF | ±0.05pF | GRM1552C2A4R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A4R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A4R4CA01# |  |
|        |               |         | 4.5pF | ±0.05pF | GRM1552C2A4R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A4R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A4R5CA01# |  |
|        |               |         | 4.6pF | ±0.05pF | GRM1552C2A4R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A4R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A4R6CA01# |  |
|        |               |         | 4.7pF | ±0.05pF | GRM1552C2A4R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A4R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A4R7CA01# |  |
|        |               |         | 4.8pF | ±0.05pF | GRM1552C2A4R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A4R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A4R8CA01# |  |
|        |               |         | 4.9pF | ±0.05pF | GRM1552C2A4R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A4R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A4R9CA01# |  |
|        |               |         | 5.0pF | ±0.05pF | GRM1552C2A5R0WA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 100Vdc        | CH      | 5.0pF | ±0.1pF  | GRM1552C2A5R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A5R0CA01# |  |
|        |               |         | 5.1pF | ±0.05pF | GRM1552C2A5R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A5R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A5R1CA01# |  |
|        |               |         | 5.2pF | ±0.05pF | GRM1552C2A5R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A5R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A5R2CA01# |  |
|        |               |         | 5.3pF | ±0.05pF | GRM1552C2A5R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A5R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A5R3CA01# |  |
|        |               |         | 5.4pF | ±0.05pF | GRM1552C2A5R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A5R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A5R4CA01# |  |
|        |               |         | 5.5pF | ±0.05pF | GRM1552C2A5R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A5R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A5R5CA01# |  |
|        |               |         | 5.6pF | ±0.05pF | GRM1552C2A5R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A5R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A5R6CA01# |  |
|        |               |         | 5.7pF | ±0.05pF | GRM1552C2A5R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A5R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A5R7CA01# |  |
|        |               |         | 5.8pF | ±0.05pF | GRM1552C2A5R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A5R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A5R8CA01# |  |
|        |               |         | 5.9pF | ±0.05pF | GRM1552C2A5R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A5R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A5R9CA01# |  |
|        |               |         | 6.0pF | ±0.05pF | GRM1552C2A6R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A6R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A6R0CA01# |  |
|        |               |         | 6.1pF | ±0.05pF | GRM1552C2A6R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A6R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A6R1CA01# |  |
|        |               |         | 6.2pF | ±0.05pF | GRM1552C2A6R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A6R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A6R2CA01# |  |
|        |               |         | 6.3pF | ±0.05pF | GRM1552C2A6R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A6R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A6R3CA01# |  |
|        |               |         | 6.4pF | ±0.05pF | GRM1552C2A6R4WA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A6R4CA01# |  |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 100Vdc        | CH      | 6.4pF | ±0.05pF | GRM1552C2A6R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A6R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A6R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A6R4DA01# |  |
|        |               |         | 6.5pF | ±0.05pF | GRM1552C2A6R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A6R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A6R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A6R5DA01# |  |
|        |               |         | 6.6pF | ±0.05pF | GRM1552C2A6R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A6R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A6R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A6R6DA01# |  |
|        |               |         | 6.7pF | ±0.05pF | GRM1552C2A6R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A6R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A6R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A6R7DA01# |  |
|        |               |         | 6.8pF | ±0.05pF | GRM1552C2A6R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A6R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A6R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A6R8DA01# |  |
|        |               |         | 6.9pF | ±0.05pF | GRM1552C2A6R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A6R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A6R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A6R9DA01# |  |
|        |               |         | 7.0pF | ±0.05pF | GRM1552C2A7R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A7R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A7R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A7R0DA01# |  |
|        |               |         | 7.1pF | ±0.05pF | GRM1552C2A7R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A7R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A7R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A7R1DA01# |  |
|        |               |         | 7.2pF | ±0.05pF | GRM1552C2A7R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A7R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A7R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A7R2DA01# |  |
|        |               |         | 7.3pF | ±0.05pF | GRM1552C2A7R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A7R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A7R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A7R3DA01# |  |
|        |               |         | 7.4pF | ±0.05pF | GRM1552C2A7R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A7R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A7R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A7R4DA01# |  |
|        |               |         | 7.5pF | ±0.05pF | GRM1552C2A7R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A7R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A7R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A7R5DA01# |  |
|        |               |         | 7.6pF | ±0.05pF | GRM1552C2A7R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A7R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A7R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A7R6DA01# |  |
|        |               |         | 7.7pF | ±0.05pF | GRM1552C2A7R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A7R7BA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 100Vdc        | CH      | 7.7pF | ±0.25pF | GRM1552C2A7R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A7R7DA01# |  |
|        |               |         | 7.8pF | ±0.05pF | GRM1552C2A7R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A7R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A7R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A7R8DA01# |  |
|        |               |         | 7.9pF | ±0.05pF | GRM1552C2A7R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A7R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A7R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A7R9DA01# |  |
|        |               |         | 8.0pF | ±0.05pF | GRM1552C2A8R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A8R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A8R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A8R0DA01# |  |
|        |               |         | 8.1pF | ±0.05pF | GRM1552C2A8R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A8R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A8R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A8R1DA01# |  |
|        |               |         | 8.2pF | ±0.05pF | GRM1552C2A8R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A8R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A8R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A8R2DA01# |  |
|        |               |         | 8.3pF | ±0.05pF | GRM1552C2A8R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A8R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A8R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A8R3DA01# |  |
|        |               |         | 8.4pF | ±0.05pF | GRM1552C2A8R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A8R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A8R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A8R4DA01# |  |
|        |               |         | 8.5pF | ±0.05pF | GRM1552C2A8R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A8R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A8R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A8R5DA01# |  |
|        |               |         | 8.6pF | ±0.05pF | GRM1552C2A8R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A8R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A8R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A8R6DA01# |  |
|        |               |         | 8.7pF | ±0.05pF | GRM1552C2A8R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A8R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A8R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A8R7DA01# |  |
|        |               |         | 8.8pF | ±0.05pF | GRM1552C2A8R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A8R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A8R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A8R8DA01# |  |
|        |               |         | 8.9pF | ±0.05pF | GRM1552C2A8R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A8R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A8R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A8R9DA01# |  |
|        |               |         | 9.0pF | ±0.05pF | GRM1552C2A9R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A9R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A9R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A9R0DA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 100Vdc        | CH      | 9.1pF | ±0.05pF | GRM1552C2A9R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A9R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A9R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A9R1DA01# |  |
|        |               |         | 9.2pF | ±0.05pF | GRM1552C2A9R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A9R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A9R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A9R2DA01# |  |
|        |               |         | 9.3pF | ±0.05pF | GRM1552C2A9R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A9R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A9R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A9R3DA01# |  |
|        |               |         | 9.4pF | ±0.05pF | GRM1552C2A9R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A9R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A9R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A9R4DA01# |  |
|        |               |         | 9.5pF | ±0.05pF | GRM1552C2A9R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A9R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A9R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A9R5DA01# |  |
|        |               |         | 9.6pF | ±0.05pF | GRM1552C2A9R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A9R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A9R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A9R6DA01# |  |
|        |               |         | 9.7pF | ±0.05pF | GRM1552C2A9R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A9R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A9R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A9R7DA01# |  |
|        |               |         | 9.8pF | ±0.05pF | GRM1552C2A9R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A9R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A9R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A9R8DA01# |  |
|        |               |         | 9.9pF | ±0.05pF | GRM1552C2A9R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C2A9R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C2A9R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C2A9R9DA01# |  |
|        |               |         | 10pF  | ±2%     | GRM1552C2A100GA01# |  |
|        |               |         |       | ±5%     | GRM1552C2A100JA01# |  |
|        |               |         | 12pF  | ±2%     | GRM1552C2A120GA01# |  |
|        |               |         |       | ±5%     | GRM1552C2A120JA01# |  |
|        |               |         | 15pF  | ±2%     | GRM1552C2A150GA01# |  |
|        |               |         |       | ±5%     | GRM1552C2A150JA01# |  |
|        |               |         | 18pF  | ±2%     | GRM1552C2A180GA01# |  |
|        |               |         |       | ±5%     | GRM1552C2A180JA01# |  |
|        |               |         | 22pF  | ±2%     | GRM1552C2A220GA01# |  |
|        |               |         |       | ±5%     | GRM1552C2A220JA01# |  |
|        |               |         | 27pF  | ±2%     | GRM1552C2A270GA01# |  |
|        |               |         |       | ±5%     | GRM1552C2A270JA01# |  |
|        |               |         | 33pF  | ±2%     | GRM1552C2A330GA01# |  |
|        |               |         |       | ±5%     | GRM1552C2A330JA01# |  |
|        |               |         | 39pF  | ±2%     | GRM1552C2A390GA01# |  |
|        |               |         |       | ±5%     | GRM1552C2A390JA01# |  |
|        |               |         | 47pF  | ±2%     | GRM1552C2A470GA01# |  |
|        |               |         |       | ±5%     | GRM1552C2A470JA01# |  |

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.55mm | 100Vdc        | CH      | 56pF   | ±2%     | GRM1552C2A560GA01# |  |
|        |               |         |        | ±5%     | GRM1552C2A560JA01# |  |
|        |               |         | 68pF   | ±2%     | GRM1552C2A680GA01# |  |
|        |               |         |        | ±5%     | GRM1552C2A680JA01# |  |
|        |               |         | 82pF   | ±2%     | GRM1552C2A820GA01# |  |
|        |               |         |        | ±5%     | GRM1552C2A820JA01# |  |
|        |               |         | 100pF  | ±2%     | GRM1552C2A101GA01# |  |
|        |               |         |        | ±5%     | GRM1552C2A101JA01# |  |
|        | 50Vdc         | C0G     | 0.10pF | ±0.05pF | GRM1555C1HR10WA01# |  |
|        |               |         |        | ±0.05pF | GRM1555C1HR20WA01# |  |
|        |               |         | 0.20pF | ±0.05pF | GRM1555C1HR20BA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1HR20BA01# |  |
|        |               |         | 0.30pF | ±0.05pF | GRM1555C1HR30WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1HR30BA01# |  |
|        |               |         | 0.40pF | ±0.05pF | GRM1555C1HR40WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1HR40BA01# |  |
|        |               |         | 0.50pF | ±0.05pF | GRM1555C1HR50WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1HR50BA01# |  |
|        |               |         | 0.60pF | ±0.05pF | GRM1555C1HR60WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1HR60BA01# |  |
|        |               |         | 0.70pF | ±0.05pF | GRM1555C1HR70WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1HR70BA01# |  |
|        |               |         | 0.80pF | ±0.05pF | GRM1555C1HR80WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1HR80BA01# |  |
|        |               |         | 0.90pF | ±0.05pF | GRM1555C1HR90WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1HR90BA01# |  |
|        |               |         | 1.0pF  | ±0.05pF | GRM1555C1H1R0WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1H1R0BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C1H1R0CA01# |  |
|        |               |         | 1.1pF  | ±0.05pF | GRM1555C1H1R1WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1H1R1BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C1H1R1CA01# |  |
|        |               |         | 1.2pF  | ±0.05pF | GRM1555C1H1R2WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1H1R2BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C1H1R2CA01# |  |
|        |               |         | 1.3pF  | ±0.05pF | GRM1555C1H1R3WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1H1R3BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C1H1R3CA01# |  |
|        |               |         | 1.4pF  | ±0.05pF | GRM1555C1H1R4WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1H1R4BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C1H1R4CA01# |  |
|        |               |         | 1.5pF  | ±0.05pF | GRM1555C1H1R5WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1H1R5BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C1H1R5CA01# |  |
|        |               |         | 1.6pF  | ±0.05pF | GRM1555C1H1R6WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1H1R6BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C1H1R6CA01# |  |
|        |               |         | 1.7pF  | ±0.05pF | GRM1555C1H1R7WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1H1R7BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C1H1R7CA01# |  |
|        |               |         | 1.8pF  | ±0.05pF | GRM1555C1H1R8WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1H1R8BA01# |  |
|        |               |         |        | ±0.25pF | GRM1555C1H1R8CA01# |  |
|        |               |         | 1.9pF  | ±0.05pF | GRM1555C1H1R9WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1555C1H1R9BA01# |  |

Part number # indicates the package specification code.



# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | C0G     | 1.9pF | ±0.25pF | GRM1555C1H1R9CA01# |  |
|        |               |         |       | ±0.05pF | GRM1555C1H2R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H2R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H2R0CA01# |  |
|        |               |         | 2.1pF | ±0.05pF | GRM1555C1H2R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H2R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H2R1CA01# |  |
|        |               |         | 2.2pF | ±0.05pF | GRM1555C1H2R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H2R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H2R2CA01# |  |
|        |               |         | 2.3pF | ±0.05pF | GRM1555C1H2R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H2R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H2R3CA01# |  |
|        |               |         | 2.4pF | ±0.05pF | GRM1555C1H2R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H2R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H2R4CA01# |  |
|        |               |         | 2.5pF | ±0.05pF | GRM1555C1H2R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H2R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H2R5CA01# |  |
|        |               |         | 2.6pF | ±0.05pF | GRM1555C1H2R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H2R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H2R6CA01# |  |
|        |               |         | 2.7pF | ±0.05pF | GRM1555C1H2R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H2R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H2R7CA01# |  |
|        |               |         | 2.8pF | ±0.05pF | GRM1555C1H2R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H2R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H2R8CA01# |  |
|        |               |         | 2.9pF | ±0.05pF | GRM1555C1H2R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H2R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H2R9CA01# |  |
|        |               |         | 3.0pF | ±0.05pF | GRM1555C1H3R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H3R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H3R0CA01# |  |
|        |               |         | 3.1pF | ±0.05pF | GRM1555C1H3R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H3R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H3R1CA01# |  |
|        |               |         | 3.2pF | ±0.05pF | GRM1555C1H3R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H3R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H3R2CA01# |  |
|        |               |         | 3.3pF | ±0.05pF | GRM1555C1H3R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H3R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H3R3CA01# |  |
|        |               |         | 3.4pF | ±0.05pF | GRM1555C1H3R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H3R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H3R4CA01# |  |
|        |               |         | 3.5pF | ±0.05pF | GRM1555C1H3R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H3R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H3R5CA01# |  |
|        |               |         | 3.6pF | ±0.05pF | GRM1555C1H3R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H3R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H3R6CA01# |  |
|        |               |         | 3.7pF | ±0.05pF | GRM1555C1H3R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H3R7BA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | C0G     | 3.7pF | ±0.25pF | GRM1555C1H3R7CA01# |  |
|        |               |         |       | ±0.05pF | GRM1555C1H3R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H3R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H3R8CA01# |  |
|        |               |         | 3.9pF | ±0.05pF | GRM1555C1H3R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H3R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H3R9CA01# |  |
|        |               |         | 4.0pF | ±0.05pF | GRM1555C1H4R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H4R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H4R0CA01# |  |
|        |               |         | 4.1pF | ±0.05pF | GRM1555C1H4R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H4R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H4R1CA01# |  |
|        |               |         | 4.2pF | ±0.05pF | GRM1555C1H4R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H4R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H4R2CA01# |  |
|        |               |         | 4.3pF | ±0.05pF | GRM1555C1H4R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H4R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H4R3CA01# |  |
|        |               |         | 4.4pF | ±0.05pF | GRM1555C1H4R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H4R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H4R4CA01# |  |
|        |               |         | 4.5pF | ±0.05pF | GRM1555C1H4R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H4R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H4R5CA01# |  |
|        |               |         | 4.6pF | ±0.05pF | GRM1555C1H4R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H4R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H4R6CA01# |  |
|        |               |         | 4.7pF | ±0.05pF | GRM1555C1H4R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H4R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H4R7CA01# |  |
|        |               |         | 4.8pF | ±0.05pF | GRM1555C1H4R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H4R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H4R8CA01# |  |
|        |               |         | 4.9pF | ±0.05pF | GRM1555C1H4R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H4R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H4R9CA01# |  |
|        |               |         | 5.0pF | ±0.05pF | GRM1555C1H5R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H5R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H5R0CA01# |  |
|        |               |         | 5.1pF | ±0.05pF | GRM1555C1H5R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H5R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H5R1CA01# |  |
|        |               |         | 5.2pF | ±0.05pF | GRM1555C1H5R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H5R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H5R2CA01# |  |
|        |               |         | 5.3pF | ±0.05pF | GRM1555C1H5R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H5R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H5R3CA01# |  |
|        |               |         | 5.4pF | ±0.05pF | GRM1555C1H5R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H5R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H5R4CA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | C0G     | 5.4pF | ±0.25pF | GRM1555C1H5R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H5R4DA01# |  |
|        |               |         | 5.5pF | ±0.05pF | GRM1555C1H5R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H5R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H5R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H5R5DA01# |  |
|        |               |         | 5.6pF | ±0.05pF | GRM1555C1H5R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H5R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H5R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H5R6DA01# |  |
|        |               |         | 5.7pF | ±0.05pF | GRM1555C1H5R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H5R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H5R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H5R7DA01# |  |
|        |               |         | 5.8pF | ±0.05pF | GRM1555C1H5R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H5R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H5R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H5R8DA01# |  |
|        |               |         | 5.9pF | ±0.05pF | GRM1555C1H5R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H5R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H5R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H5R9DA01# |  |
|        |               |         | 6.0pF | ±0.05pF | GRM1555C1H6R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H6R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H6R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H6R0DA01# |  |
|        |               |         | 6.1pF | ±0.05pF | GRM1555C1H6R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H6R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H6R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H6R1DA01# |  |
|        |               |         | 6.2pF | ±0.05pF | GRM1555C1H6R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H6R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H6R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H6R2DA01# |  |
|        |               |         | 6.3pF | ±0.05pF | GRM1555C1H6R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H6R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H6R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H6R3DA01# |  |
|        |               |         | 6.4pF | ±0.05pF | GRM1555C1H6R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H6R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H6R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H6R4DA01# |  |
|        |               |         | 6.5pF | ±0.05pF | GRM1555C1H6R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H6R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H6R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H6R5DA01# |  |
|        |               |         | 6.6pF | ±0.05pF | GRM1555C1H6R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H6R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H6R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H6R6DA01# |  |
|        |               |         | 6.7pF | ±0.05pF | GRM1555C1H6R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H6R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H6R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H6R7DA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | C0G     | 6.8pF | ±0.05pF | GRM1555C1H6R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H6R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H6R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H6R8DA01# |  |
|        |               |         | 6.9pF | ±0.05pF | GRM1555C1H6R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H6R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H6R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H6R9DA01# |  |
|        |               |         | 7.0pF | ±0.05pF | GRM1555C1H7R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H7R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H7R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H7R0DA01# |  |
|        |               |         | 7.1pF | ±0.05pF | GRM1555C1H7R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H7R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H7R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H7R1DA01# |  |
|        |               |         | 7.2pF | ±0.05pF | GRM1555C1H7R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H7R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H7R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H7R2DA01# |  |
|        |               |         | 7.3pF | ±0.05pF | GRM1555C1H7R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H7R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H7R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H7R3DA01# |  |
|        |               |         | 7.4pF | ±0.05pF | GRM1555C1H7R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H7R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H7R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H7R4DA01# |  |
|        |               |         | 7.5pF | ±0.05pF | GRM1555C1H7R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H7R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H7R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H7R5DA01# |  |
|        |               |         | 7.6pF | ±0.05pF | GRM1555C1H7R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H7R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H7R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H7R6DA01# |  |
|        |               |         | 7.7pF | ±0.05pF | GRM1555C1H7R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H7R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H7R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H7R7DA01# |  |
|        |               |         | 7.8pF | ±0.05pF | GRM1555C1H7R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H7R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H7R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H7R8DA01# |  |
|        |               |         | 7.9pF | ±0.05pF | GRM1555C1H7R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H7R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H7R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H7R9DA01# |  |
|        |               |         | 8.0pF | ±0.05pF | GRM1555C1H8R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H8R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H8R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H8R0DA01# |  |
|        |               |         | 8.1pF | ±0.05pF | GRM1555C1H8R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H8R1BA01# |  |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | C0G     | 8.1pF | ±0.25pF | GRM1555C1H8R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H8R1DA01# |  |
|        |               |         | 8.2pF | ±0.05pF | GRM1555C1H8R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H8R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H8R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H8R2DA01# |  |
|        |               |         | 8.3pF | ±0.05pF | GRM1555C1H8R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H8R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H8R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H8R3DA01# |  |
|        |               |         | 8.4pF | ±0.05pF | GRM1555C1H8R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H8R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H8R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H8R4DA01# |  |
|        |               |         | 8.5pF | ±0.05pF | GRM1555C1H8R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H8R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H8R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H8R5DA01# |  |
|        |               |         | 8.6pF | ±0.05pF | GRM1555C1H8R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H8R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H8R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H8R6DA01# |  |
|        |               |         | 8.7pF | ±0.05pF | GRM1555C1H8R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H8R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H8R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H8R7DA01# |  |
|        |               |         | 8.8pF | ±0.05pF | GRM1555C1H8R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H8R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H8R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H8R8DA01# |  |
|        |               |         | 8.9pF | ±0.05pF | GRM1555C1H8R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H8R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H8R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H8R9DA01# |  |
|        |               |         | 9.0pF | ±0.05pF | GRM1555C1H9R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H9R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H9R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H9R0DA01# |  |
|        |               |         | 9.1pF | ±0.05pF | GRM1555C1H9R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H9R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H9R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H9R1DA01# |  |
|        |               |         | 9.2pF | ±0.05pF | GRM1555C1H9R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H9R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H9R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H9R2DA01# |  |
|        |               |         | 9.3pF | ±0.05pF | GRM1555C1H9R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H9R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H9R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H9R3DA01# |  |
|        |               |         | 9.4pF | ±0.05pF | GRM1555C1H9R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H9R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H9R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H9R4DA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | C0G     | 9.5pF | ±0.05pF | GRM1555C1H9R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H9R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H9R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H9R5DA01# |  |
|        |               |         | 9.6pF | ±0.05pF | GRM1555C1H9R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H9R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H9R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H9R6DA01# |  |
|        |               |         | 9.7pF | ±0.05pF | GRM1555C1H9R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H9R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H9R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H9R7DA01# |  |
|        |               |         | 9.8pF | ±0.05pF | GRM1555C1H9R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H9R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H9R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H9R8DA01# |  |
|        |               |         | 9.9pF | ±0.05pF | GRM1555C1H9R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1555C1H9R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1555C1H9R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1555C1H9R9DA01# |  |
|        |               |         | 10pF  | ±2%     | GRM1555C1H100GA01# |  |
|        |               |         |       | ±5%     | GRM1555C1H100JA01# |  |
|        |               |         | 12pF  | ±2%     | GRM1555C1H120GA01# |  |
|        |               |         |       | ±5%     | GRM1555C1H120JA01# |  |
|        |               |         | 15pF  | ±2%     | GRM1555C1H150GA01# |  |
|        |               |         |       | ±5%     | GRM1555C1H150JA01# |  |
|        |               |         | 18pF  | ±2%     | GRM1555C1H180GA01# |  |
|        |               |         |       | ±5%     | GRM1555C1H180JA01# |  |
|        |               |         | 22pF  | ±2%     | GRM1555C1H220GA01# |  |
|        |               |         |       | ±5%     | GRM1555C1H220JA01# |  |
|        |               |         | 27pF  | ±2%     | GRM1555C1H270GA01# |  |
|        |               |         |       | ±5%     | GRM1555C1H270JA01# |  |
|        |               |         | 33pF  | ±2%     | GRM1555C1H330GA01# |  |
|        |               |         |       | ±5%     | GRM1555C1H330JA01# |  |
|        |               |         | 39pF  | ±2%     | GRM1555C1H390GA01# |  |
|        |               |         |       | ±5%     | GRM1555C1H390JA01# |  |
|        |               |         | 47pF  | ±2%     | GRM1555C1H470GA01# |  |
|        |               |         |       | ±5%     | GRM1555C1H470JA01# |  |
|        |               |         | 56pF  | ±2%     | GRM1555C1H560GA01# |  |
|        |               |         |       | ±5%     | GRM1555C1H560JA01# |  |
|        |               |         | 68pF  | ±2%     | GRM1555C1H680GA01# |  |
|        |               |         |       | ±5%     | GRM1555C1H680JA01# |  |
|        |               |         | 82pF  | ±2%     | GRM1555C1H820GA01# |  |
|        |               |         |       | ±5%     | GRM1555C1H820JA01# |  |
|        |               |         | 100pF | ±2%     | GRM1555C1H101GA01# |  |
|        |               |         |       | ±5%     | GRM1555C1H101JA01# |  |
|        |               |         | 120pF | ±2%     | GRM1555C1H121GA01# |  |
|        |               |         |       | ±5%     | GRM1555C1H121JA01# |  |
|        |               |         | 150pF | ±2%     | GRM1555C1H151GA01# |  |
|        |               |         |       | ±5%     | GRM1555C1H151JA01# |  |
|        |               |         | 180pF | ±2%     | GRM1555C1H181GA01# |  |
|        |               |         |       | ±5%     | GRM1555C1H181JA01# |  |
|        |               |         | 220pF | ±2%     | GRM1555C1H221GA01# |  |
|        |               |         |       | ±5%     | GRM1555C1H221JA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.55mm | 50Vdc         | COG     | 270pF  | ±2%     | GRM1555C1H271GA01# |  |
|        |               |         |        | ±5%     | GRM1555C1H271JA01# |  |
|        |               |         | 330pF  | ±2%     | GRM1555C1H331GA01# |  |
|        |               |         |        | ±5%     | GRM1555C1H331JA01# |  |
|        |               |         | 390pF  | ±2%     | GRM1555C1H391GA01# |  |
|        |               |         |        | ±5%     | GRM1555C1H391JA01# |  |
|        |               |         | 470pF  | ±2%     | GRM1555C1H471GA01# |  |
|        |               |         |        | ±5%     | GRM1555C1H471JA01# |  |
|        |               |         | 560pF  | ±2%     | GRM1555C1H561GA01# |  |
|        |               |         |        | ±5%     | GRM1555C1H561JA01# |  |
|        |               |         | 680pF  | ±2%     | GRM1555C1H681GA01# |  |
|        |               |         |        | ±5%     | GRM1555C1H681JA01# |  |
|        |               |         | 820pF  | ±2%     | GRM1555C1H821GA01# |  |
|        |               |         |        | ±5%     | GRM1555C1H821JA01# |  |
|        |               |         | 1000pF | ±2%     | GRM1555C1H102GA01# |  |
|        |               |         |        | ±5%     | GRM1555C1H102JA01# |  |
|        |               | CK      | 0.10pF | ±0.05pF | GRM1554C1HR10WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C1HR20BA01# |  |
|        |               |         | 0.20pF | ±0.05pF | GRM1554C1HR20WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C1HR20BA01# |  |
|        |               |         | 0.30pF | ±0.05pF | GRM1554C1HR30WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C1HR30BA01# |  |
|        |               |         | 0.40pF | ±0.05pF | GRM1554C1HR40WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C1HR40BA01# |  |
|        |               |         | 0.50pF | ±0.05pF | GRM1554C1HR50WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C1HR50BA01# |  |
|        |               |         | 0.60pF | ±0.05pF | GRM1554C1HR60WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C1HR60BA01# |  |
|        |               |         | 0.70pF | ±0.05pF | GRM1554C1HR70WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C1HR70BA01# |  |
|        |               |         | 0.80pF | ±0.05pF | GRM1554C1HR80WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C1HR80BA01# |  |
|        |               |         | 0.90pF | ±0.05pF | GRM1554C1HR90WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C1HR90BA01# |  |
|        |               |         | 1.0pF  | ±0.05pF | GRM1554C1H1R0WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C1H1R0BA01# |  |
|        |               |         |        | ±0.25pF | GRM1554C1H1R0CA01# |  |
|        |               |         | 1.1pF  | ±0.05pF | GRM1554C1H1R1WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C1H1R1BA01# |  |
|        |               |         |        | ±0.25pF | GRM1554C1H1R1CA01# |  |
|        |               |         | 1.2pF  | ±0.05pF | GRM1554C1H1R2WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C1H1R2BA01# |  |
|        |               |         |        | ±0.25pF | GRM1554C1H1R2CA01# |  |
|        |               |         | 1.3pF  | ±0.05pF | GRM1554C1H1R3WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C1H1R3BA01# |  |
|        |               |         |        | ±0.25pF | GRM1554C1H1R3CA01# |  |
|        |               |         | 1.4pF  | ±0.05pF | GRM1554C1H1R4WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C1H1R4BA01# |  |
|        |               |         |        | ±0.25pF | GRM1554C1H1R4CA01# |  |
|        |               |         | 1.5pF  | ±0.05pF | GRM1554C1H1R5WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C1H1R5BA01# |  |
|        |               |         |        | ±0.25pF | GRM1554C1H1R5CA01# |  |
|        |               |         | 1.6pF  | ±0.05pF | GRM1554C1H1R6WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1554C1H1R6BA01# |  |
|        |               |         |        | ±0.25pF | GRM1554C1H1R6CA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | CK      | 1.7pF | ±0.05pF | GRM1554C1H1R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1554C1H1R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1554C1H1R7CA01# |  |
|        |               |         | 1.8pF | ±0.05pF | GRM1554C1H1R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1554C1H1R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1554C1H1R8CA01# |  |
|        |               |         | 1.9pF | ±0.05pF | GRM1554C1H1R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1554C1H1R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1554C1H1R9CA01# |  |
|        |               |         | 2.0pF | ±0.05pF | GRM1554C1H2R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1554C1H2R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1554C1H2R0CA01# |  |
|        |               | CJ      | 2.1pF | ±0.05pF | GRM1553C1H2R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H2R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H2R1CA01# |  |
|        |               |         | 2.2pF | ±0.05pF | GRM1553C1H2R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H2R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H2R2CA01# |  |
|        |               |         | 2.3pF | ±0.05pF | GRM1553C1H2R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H2R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H2R3CA01# |  |
|        |               |         | 2.4pF | ±0.05pF | GRM1553C1H2R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H2R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H2R4CA01# |  |
|        |               |         | 2.5pF | ±0.05pF | GRM1553C1H2R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H2R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H2R5CA01# |  |
|        |               |         | 2.6pF | ±0.05pF | GRM1553C1H2R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H2R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H2R6CA01# |  |
|        |               |         | 2.7pF | ±0.05pF | GRM1553C1H2R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H2R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H2R7CA01# |  |
|        |               |         | 2.8pF | ±0.05pF | GRM1553C1H2R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H2R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H2R8CA01# |  |
|        |               |         | 2.9pF | ±0.05pF | GRM1553C1H2R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H2R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H2R9CA01# |  |
|        |               |         | 3.0pF | ±0.05pF | GRM1553C1H3R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H3R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H3R0CA01# |  |
|        |               |         | 3.1pF | ±0.05pF | GRM1553C1H3R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H3R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H3R1CA01# |  |
|        |               |         | 3.2pF | ±0.05pF | GRM1553C1H3R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H3R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H3R2CA01# |  |
|        |               |         | 3.3pF | ±0.05pF | GRM1553C1H3R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H3R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H3R3CA01# |  |
|        |               |         | 3.4pF | ±0.05pF | GRM1553C1H3R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H3R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H3R4CA01# |  |

Part number # indicates the package specification code.



# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | CJ      | 3.5pF | ±0.05pF | GRM1553C1H3R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H3R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H3R5CA01# |  |
|        |               |         | 3.6pF | ±0.05pF | GRM1553C1H3R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H3R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H3R6CA01# |  |
|        |               |         | 3.7pF | ±0.05pF | GRM1553C1H3R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H3R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H3R7CA01# |  |
|        |               |         | 3.8pF | ±0.05pF | GRM1553C1H3R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H3R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H3R8CA01# |  |
|        |               |         | 3.9pF | ±0.05pF | GRM1553C1H3R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1553C1H3R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1553C1H3R9CA01# |  |
|        |               | CH      | 4.0pF | ±0.05pF | GRM1552C1H4R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H4R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H4R0CA01# |  |
|        |               |         | 4.1pF | ±0.05pF | GRM1552C1H4R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H4R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H4R1CA01# |  |
|        |               |         | 4.2pF | ±0.05pF | GRM1552C1H4R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H4R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H4R2CA01# |  |
|        |               |         | 4.3pF | ±0.05pF | GRM1552C1H4R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H4R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H4R3CA01# |  |
|        |               |         | 4.4pF | ±0.05pF | GRM1552C1H4R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H4R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H4R4CA01# |  |
|        |               |         | 4.5pF | ±0.05pF | GRM1552C1H4R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H4R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H4R5CA01# |  |
|        |               |         | 4.6pF | ±0.05pF | GRM1552C1H4R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H4R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H4R6CA01# |  |
|        |               |         | 4.7pF | ±0.05pF | GRM1552C1H4R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H4R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H4R7CA01# |  |
|        |               |         | 4.8pF | ±0.05pF | GRM1552C1H4R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H4R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H4R8CA01# |  |
|        |               |         | 4.9pF | ±0.05pF | GRM1552C1H4R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H4R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H4R9CA01# |  |
|        |               |         | 5.0pF | ±0.05pF | GRM1552C1H5R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H5R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H5R0CA01# |  |
|        |               |         | 5.1pF | ±0.05pF | GRM1552C1H5R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H5R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H5R1CA01# |  |
|        |               |         | 5.2pF | ±0.05pF | GRM1552C1H5R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H5R2BA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | CH      | 5.2pF | ±0.25pF | GRM1552C1H5R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H5R2DA01# |  |
|        |               |         | 5.3pF | ±0.05pF | GRM1552C1H5R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H5R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H5R3CA01# |  |
|        |               |         | 5.4pF | ±0.05pF | GRM1552C1H5R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H5R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H5R4CA01# |  |
|        |               |         | 5.5pF | ±0.05pF | GRM1552C1H5R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H5R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H5R5CA01# |  |
|        |               |         | 5.6pF | ±0.05pF | GRM1552C1H5R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H5R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H5R6CA01# |  |
|        |               |         | 5.7pF | ±0.05pF | GRM1552C1H5R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H5R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H5R7CA01# |  |
|        |               |         | 5.8pF | ±0.05pF | GRM1552C1H5R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H5R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H5R8CA01# |  |
|        |               |         | 5.9pF | ±0.05pF | GRM1552C1H5R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H5R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H5R9CA01# |  |
|        |               |         | 6.0pF | ±0.05pF | GRM1552C1H6R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H6R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H6R0CA01# |  |
|        |               |         | 6.1pF | ±0.05pF | GRM1552C1H6R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H6R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H6R1CA01# |  |
|        |               |         | 6.2pF | ±0.05pF | GRM1552C1H6R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H6R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H6R2CA01# |  |
|        |               |         | 6.3pF | ±0.05pF | GRM1552C1H6R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H6R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H6R3CA01# |  |
|        |               |         | 6.4pF | ±0.05pF | GRM1552C1H6R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H6R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H6R4CA01# |  |
|        |               |         | 6.5pF | ±0.05pF | GRM1552C1H6R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H6R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H6R5CA01# |  |
|        |               |         | 6.6pF | ±0.05pF | GRM1552C1H6R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H6R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H6R6CA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | CH      | 6.6pF | ±0.05pF | GRM1552C1H6R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H6R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H6R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H6R6DA01# |  |
|        |               |         | 6.7pF | ±0.05pF | GRM1552C1H6R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H6R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H6R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H6R7DA01# |  |
|        |               |         | 6.8pF | ±0.05pF | GRM1552C1H6R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H6R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H6R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H6R8DA01# |  |
|        |               |         | 6.9pF | ±0.05pF | GRM1552C1H6R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H6R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H6R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H6R9DA01# |  |
|        |               |         | 7.0pF | ±0.05pF | GRM1552C1H7R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H7R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H7R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H7R0DA01# |  |
|        |               |         | 7.1pF | ±0.05pF | GRM1552C1H7R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H7R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H7R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H7R1DA01# |  |
|        |               |         | 7.2pF | ±0.05pF | GRM1552C1H7R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H7R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H7R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H7R2DA01# |  |
|        |               |         | 7.3pF | ±0.05pF | GRM1552C1H7R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H7R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H7R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H7R3DA01# |  |
|        |               |         | 7.4pF | ±0.05pF | GRM1552C1H7R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H7R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H7R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H7R4DA01# |  |
|        |               |         | 7.5pF | ±0.05pF | GRM1552C1H7R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H7R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H7R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H7R5DA01# |  |
|        |               |         | 7.6pF | ±0.05pF | GRM1552C1H7R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H7R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H7R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H7R6DA01# |  |
|        |               |         | 7.7pF | ±0.05pF | GRM1552C1H7R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H7R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H7R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H7R7DA01# |  |
|        |               |         | 7.8pF | ±0.05pF | GRM1552C1H7R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H7R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H7R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H7R8DA01# |  |
|        |               |         | 7.9pF | ±0.05pF | GRM1552C1H7R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H7R9BA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | CH      | 7.9pF | ±0.25pF | GRM1552C1H7R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H7R9DA01# |  |
|        |               |         | 8.0pF | ±0.05pF | GRM1552C1H8R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H8R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H8R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H8R0DA01# |  |
|        |               |         | 8.1pF | ±0.05pF | GRM1552C1H8R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H8R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H8R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H8R1DA01# |  |
|        |               |         | 8.2pF | ±0.05pF | GRM1552C1H8R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H8R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H8R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H8R2DA01# |  |
|        |               |         | 8.3pF | ±0.05pF | GRM1552C1H8R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H8R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H8R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H8R3DA01# |  |
|        |               |         | 8.4pF | ±0.05pF | GRM1552C1H8R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H8R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H8R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H8R4DA01# |  |
|        |               |         | 8.5pF | ±0.05pF | GRM1552C1H8R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H8R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H8R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H8R5DA01# |  |
|        |               |         | 8.6pF | ±0.05pF | GRM1552C1H8R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H8R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H8R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H8R6DA01# |  |
|        |               |         | 8.7pF | ±0.05pF | GRM1552C1H8R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H8R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H8R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H8R7DA01# |  |
|        |               |         | 8.8pF | ±0.05pF | GRM1552C1H8R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H8R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H8R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H8R8DA01# |  |
|        |               |         | 8.9pF | ±0.05pF | GRM1552C1H8R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H8R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H8R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H8R9DA01# |  |
|        |               |         | 9.0pF | ±0.05pF | GRM1552C1H9R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H9R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H9R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H9R0DA01# |  |
|        |               |         | 9.1pF | ±0.05pF | GRM1552C1H9R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H9R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H9R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H9R1DA01# |  |
|        |               |         | 9.2pF | ±0.05pF | GRM1552C1H9R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H9R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H9R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H9R2DA01# |  |

Part number # indicates the package specification code.



## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | CH      | 9.3pF | ±0.05pF | GRM1552C1H9R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H9R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H9R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H9R3DA01# |  |
|        |               |         | 9.4pF | ±0.05pF | GRM1552C1H9R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H9R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H9R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H9R4DA01# |  |
|        |               |         | 9.5pF | ±0.05pF | GRM1552C1H9R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H9R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H9R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H9R5DA01# |  |
|        |               |         | 9.6pF | ±0.05pF | GRM1552C1H9R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H9R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H9R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H9R6DA01# |  |
|        |               |         | 9.7pF | ±0.05pF | GRM1552C1H9R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H9R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H9R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H9R7DA01# |  |
|        |               |         | 9.8pF | ±0.05pF | GRM1552C1H9R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H9R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H9R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H9R8DA01# |  |
|        |               |         | 9.9pF | ±0.05pF | GRM1552C1H9R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1552C1H9R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1552C1H9R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1552C1H9R9DA01# |  |
|        |               |         | 10pF  | ±2%     | GRM1552C1H100GA01# |  |
|        |               |         |       | ±5%     | GRM1552C1H100JA01# |  |
|        |               |         | 12pF  | ±2%     | GRM1552C1H120GA01# |  |
|        |               |         |       | ±5%     | GRM1552C1H120JA01# |  |
|        |               |         | 15pF  | ±2%     | GRM1552C1H150GA01# |  |
|        |               |         |       | ±5%     | GRM1552C1H150JA01# |  |
|        |               |         | 18pF  | ±2%     | GRM1552C1H180GA01# |  |
|        |               |         |       | ±5%     | GRM1552C1H180JA01# |  |
|        |               |         | 22pF  | ±2%     | GRM1552C1H220GA01# |  |
|        |               |         |       | ±5%     | GRM1552C1H220JA01# |  |
|        |               |         | 27pF  | ±2%     | GRM1552C1H270GA01# |  |
|        |               |         |       | ±5%     | GRM1552C1H270JA01# |  |
|        |               |         | 33pF  | ±2%     | GRM1552C1H330GA01# |  |
|        |               |         |       | ±5%     | GRM1552C1H330JA01# |  |
|        |               |         | 39pF  | ±2%     | GRM1552C1H390GA01# |  |
|        |               |         |       | ±5%     | GRM1552C1H390JA01# |  |
|        |               |         | 47pF  | ±2%     | GRM1552C1H470GA01# |  |
|        |               |         |       | ±5%     | GRM1552C1H470JA01# |  |
|        |               |         | 56pF  | ±2%     | GRM1552C1H560GA01# |  |
|        |               |         |       | ±5%     | GRM1552C1H560JA01# |  |
|        |               |         | 68pF  | ±2%     | GRM1552C1H680GA01# |  |
|        |               |         |       | ±5%     | GRM1552C1H680JA01# |  |
|        |               |         | 82pF  | ±2%     | GRM1552C1H820GA01# |  |
|        |               |         |       | ±5%     | GRM1552C1H820JA01# |  |
|        |               |         | 100pF | ±2%     | GRM1552C1H101GA01# |  |
|        |               |         |       | ±5%     | GRM1552C1H101JA01# |  |

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |  |
|--------|---------------|---------|--------|------|--------------------|--|
| 0.55mm | 50Vdc         | CH      | 120pF  | ±2%  | GRM1552C1H121GA01# |  |
|        |               |         |        | ±5%  | GRM1552C1H121JA01# |  |
|        |               |         | 150pF  | ±2%  | GRM1552C1H151GA01# |  |
|        |               |         |        | ±5%  | GRM1552C1H151JA01# |  |
|        |               |         | 180pF  | ±2%  | GRM1552C1H181GA01# |  |
|        |               |         |        | ±5%  | GRM1552C1H181JA01# |  |
|        |               |         | 220pF  | ±2%  | GRM1552C1H221GA01# |  |
|        |               |         |        | ±5%  | GRM1552C1H221JA01# |  |
|        |               |         | 270pF  | ±2%  | GRM1552C1H271GA01# |  |
|        |               |         |        | ±5%  | GRM1552C1H271JA01# |  |
|        |               |         | 330pF  | ±2%  | GRM1552C1H331GA01# |  |
|        |               |         |        | ±5%  | GRM1552C1H331JA01# |  |
|        |               |         | 390pF  | ±2%  | GRM1552C1H391GA01# |  |
|        |               |         |        | ±5%  | GRM1552C1H391JA01# |  |
|        |               |         | 470pF  | ±2%  | GRM1552C1H471GA01# |  |
|        |               |         |        | ±5%  | GRM1552C1H471JA01# |  |
|        |               |         | 560pF  | ±2%  | GRM1552C1H561GA01# |  |
|        |               |         |        | ±5%  | GRM1552C1H561JA01# |  |
|        |               |         | 680pF  | ±2%  | GRM1552C1H681GA01# |  |
|        |               |         |        | ±5%  | GRM1552C1H681JA01# |  |
|        |               |         | 820pF  | ±2%  | GRM1552C1H821GA01# |  |
|        |               |         |        | ±5%  | GRM1552C1H821JA01# |  |
|        |               |         | 1000pF | ±2%  | GRM1552C1H102GA01# |  |
|        |               |         |        | ±5%  | GRM1552C1H102JA01# |  |
|        | 10Vdc         | SL      | 1200pF | ±5%  | GRM1551X1A122JA01# |  |
|        |               |         | 1500pF | ±5%  | GRM1551X1A152JA01# |  |
|        |               |         | 1800pF | ±5%  | GRM1551X1A182JA01# |  |
|        |               |         | 2200pF | ±5%  | GRM1551X1A222JA01# |  |
|        |               |         | 2700pF | ±5%  | GRM1551X1A272JA01# |  |
|        |               |         | 3300pF | ±5%  | GRM1551X1A332JA01# |  |
|        |               |         | 3900pF | ±5%  | GRM1551X1A392JA01# |  |
|        |               |         | 4700pF | ±5%  | GRM1551X1A472JA01# |  |
|        |               | U2J     | 1200pF | ±5%  | GRM1557U1A122JA01# |  |
|        |               |         | 1500pF | ±5%  | GRM1557U1A152JA01# |  |
|        |               |         | 1800pF | ±5%  | GRM1557U1A182JA01# |  |
|        |               |         | 2200pF | ±5%  | GRM1557U1A222JA01# |  |
|        |               |         | 2700pF | ±5%  | GRM1557U1A272JA01# |  |
|        |               |         | 3300pF | ±5%  | GRM1557U1A332JA01# |  |
|        |               |         | 3900pF | ±5%  | GRM1557U1A392JA01# |  |
|        |               |         | 4700pF | ±5%  | GRM1557U1A472JA01# |  |
|        |               | UJ      | 1200pF | ±5%  | GRM1553U1A122JA01# |  |
|        |               |         | 1500pF | ±5%  | GRM1553U1A152JA01# |  |
|        |               |         | 1800pF | ±5%  | GRM1553U1A182JA01# |  |
|        |               |         | 2200pF | ±5%  | GRM1553U1A222JA01# |  |
|        |               |         | 2700pF | ±5%  | GRM1553U1A272JA01# |  |
|        |               |         | 3300pF | ±5%  | GRM1553U1A332JA01# |  |
|        |               |         | 3900pF | ±5%  | GRM1553U1A392JA01# |  |
|        |               |         | 4700pF | ±5%  | GRM1553U1A472JA01# |  |

■ 1.6×0.8mm

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |  |
|--------|---------------|---------|--------|------|--------------------|--|
| 0.5mm  | 50Vdc         | SL      | 2200pF | ±5%  | GRM1851X1H222JA44# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.    | Tol.    | Part Number        |  |
|--------|---------------|---------|---------|---------|--------------------|--|
| 0.5mm  | 50Vdc         | SL      | 2700pF  | ±5%     | GRM1851X1H272JA44# |  |
|        |               |         | 3300pF  | ±5%     | GRM1851X1H332JA44# |  |
|        |               |         | 3900pF  | ±5%     | GRM1851X1H392JA44# |  |
|        |               |         | 4700pF  | ±5%     | GRM1851X1H472JA44# |  |
|        |               | U2J     | 2200pF  | ±5%     | GRM1857U1H222JA44# |  |
|        |               |         | 2700pF  | ±5%     | GRM1857U1H272JA44# |  |
|        |               |         | 3300pF  | ±5%     | GRM1857U1H332JA44# |  |
|        |               |         | 3900pF  | ±5%     | GRM1857U1H392JA44# |  |
|        |               |         | 4700pF  | ±5%     | GRM1857U1H472JA44# |  |
|        |               | UJ      | 2200pF  | ±5%     | GRM1853U1H222JA44# |  |
|        |               |         | 2700pF  | ±5%     | GRM1853U1H272JA44# |  |
|        |               |         | 3300pF  | ±5%     | GRM1853U1H332JA44# |  |
|        |               |         | 3900pF  | ±5%     | GRM1853U1H392JA44# |  |
|        |               |         | 4700pF  | ±5%     | GRM1853U1H472JA44# |  |
|        | 10Vdc         | SL      | 5600pF  | ±5%     | GRM1851X1A562JA44# |  |
|        |               |         | 6800pF  | ±5%     | GRM1851X1A682JA44# |  |
|        |               |         | 8200pF  | ±5%     | GRM1851X1A822JA44# |  |
|        |               |         | 10000pF | ±5%     | GRM1851X1A103JA44# |  |
|        |               | U2J     | 5600pF  | ±5%     | GRM1857U1A562JA44# |  |
|        |               |         | 6800pF  | ±5%     | GRM1857U1A682JA44# |  |
|        |               |         | 8200pF  | ±5%     | GRM1857U1A822JA44# |  |
|        |               |         | 10000pF | ±5%     | GRM1857U1A103JA44# |  |
|        |               | UJ      | 5600pF  | ±5%     | GRM1853U1A562JA44# |  |
|        |               |         | 6800pF  | ±5%     | GRM1853U1A682JA44# |  |
|        |               |         | 8200pF  | ±5%     | GRM1853U1A822JA44# |  |
|        |               |         | 10000pF | ±5%     | GRM1853U1A103JA44# |  |
| 0.9mm  | 100Vdc        | C0G     | 0.50pF  | ±0.05pF | GRM1885C2AR50WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1885C2AR50BA01# |  |
|        |               |         | 0.60pF  | ±0.05pF | GRM1885C2AR60WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1885C2AR60BA01# |  |
|        |               |         | 0.70pF  | ±0.05pF | GRM1885C2AR70WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1885C2AR70BA01# |  |
|        |               |         | 0.80pF  | ±0.05pF | GRM1885C2AR80WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1885C2AR80BA01# |  |
|        |               |         | 0.90pF  | ±0.05pF | GRM1885C2AR90WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1885C2AR90BA01# |  |
|        |               |         | 1.0pF   | ±0.05pF | GRM1885C2A1R0WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1885C2A1R0BA01# |  |
|        |               |         |         | ±0.25pF | GRM1885C2A1R0CA01# |  |
|        |               |         | 1.1pF   | ±0.05pF | GRM1885C2A1R1WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1885C2A1R1BA01# |  |
|        |               |         |         | ±0.25pF | GRM1885C2A1R1CA01# |  |
|        |               |         | 1.2pF   | ±0.05pF | GRM1885C2A1R2WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1885C2A1R2BA01# |  |
|        |               |         |         | ±0.25pF | GRM1885C2A1R2CA01# |  |
|        |               |         | 1.3pF   | ±0.05pF | GRM1885C2A1R3WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1885C2A1R3BA01# |  |
|        |               |         |         | ±0.25pF | GRM1885C2A1R3CA01# |  |
|        |               |         | 1.4pF   | ±0.05pF | GRM1885C2A1R4WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1885C2A1R4BA01# |  |
|        |               |         |         | ±0.25pF | GRM1885C2A1R4CA01# |  |
|        |               |         | 1.5pF   | ±0.05pF | GRM1885C2A1R5WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1885C2A1R5BA01# |  |
|        |               |         |         | ±0.25pF | GRM1885C2A1R5CA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 100Vdc        | C0G     | 1.6pF | ±0.05pF | GRM1885C2A1R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A1R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A1R6CA01# |  |
|        |               |         | 1.7pF | ±0.05pF | GRM1885C2A1R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A1R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A1R7CA01# |  |
|        |               |         | 1.8pF | ±0.05pF | GRM1885C2A1R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A1R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A1R8CA01# |  |
|        |               |         | 1.9pF | ±0.05pF | GRM1885C2A1R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A1R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A1R9CA01# |  |
|        |               |         | 2.0pF | ±0.05pF | GRM1885C2A2R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A2R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A2R0CA01# |  |
|        |               |         | 2.1pF | ±0.05pF | GRM1885C2A2R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A2R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A2R1CA01# |  |
|        |               |         | 2.2pF | ±0.05pF | GRM1885C2A2R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A2R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A2R2CA01# |  |
|        |               |         | 2.3pF | ±0.05pF | GRM1885C2A2R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A2R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A2R3CA01# |  |
|        |               |         | 2.4pF | ±0.05pF | GRM1885C2A2R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A2R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A2R4CA01# |  |
|        |               |         | 2.5pF | ±0.05pF | GRM1885C2A2R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A2R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A2R5CA01# |  |
|        |               |         | 2.6pF | ±0.05pF | GRM1885C2A2R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A2R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A2R6CA01# |  |
|        |               |         | 2.7pF | ±0.05pF | GRM1885C2A2R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A2R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A2R7CA01# |  |
|        |               |         | 2.8pF | ±0.05pF | GRM1885C2A2R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A2R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A2R8CA01# |  |
|        |               |         | 2.9pF | ±0.05pF | GRM1885C2A2R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A2R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A2R9CA01# |  |
|        |               |         | 3.0pF | ±0.05pF | GRM1885C2A3R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A3R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A3R0CA01# |  |
|        |               |         | 3.1pF | ±0.05pF | GRM1885C2A3R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A3R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A3R1CA01# |  |
|        |               |         | 3.2pF | ±0.05pF | GRM1885C2A3R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A3R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A3R2CA01# |  |
|        |               |         | 3.3pF | ±0.05pF | GRM1885C2A3R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A3R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A3R3CA01# |  |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 100Vdc        | C0G     | 3.4pF | ±0.05pF | GRM1885C2A3R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A3R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A3R4CA01# |  |
|        |               |         | 3.5pF | ±0.05pF | GRM1885C2A3R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A3R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A3R5CA01# |  |
|        |               |         | 3.6pF | ±0.05pF | GRM1885C2A3R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A3R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A3R6CA01# |  |
|        |               |         | 3.7pF | ±0.05pF | GRM1885C2A3R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A3R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A3R7CA01# |  |
|        |               |         | 3.8pF | ±0.05pF | GRM1885C2A3R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A3R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A3R8CA01# |  |
|        |               |         | 3.9pF | ±0.05pF | GRM1885C2A3R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A3R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A3R9CA01# |  |
|        |               |         | 4.0pF | ±0.05pF | GRM1885C2A4R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A4R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A4R0CA01# |  |
|        |               |         | 4.1pF | ±0.05pF | GRM1885C2A4R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A4R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A4R1CA01# |  |
|        |               |         | 4.2pF | ±0.05pF | GRM1885C2A4R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A4R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A4R2CA01# |  |
|        |               |         | 4.3pF | ±0.05pF | GRM1885C2A4R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A4R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A4R3CA01# |  |
|        |               |         | 4.4pF | ±0.05pF | GRM1885C2A4R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A4R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A4R4CA01# |  |
|        |               |         | 4.5pF | ±0.05pF | GRM1885C2A4R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A4R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A4R5CA01# |  |
|        |               |         | 4.6pF | ±0.05pF | GRM1885C2A4R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A4R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A4R6CA01# |  |
|        |               |         | 4.7pF | ±0.05pF | GRM1885C2A4R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A4R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A4R7CA01# |  |
|        |               |         | 4.8pF | ±0.05pF | GRM1885C2A4R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A4R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A4R8CA01# |  |
|        |               |         | 4.9pF | ±0.05pF | GRM1885C2A4R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A4R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A4R9CA01# |  |
|        |               |         | 5.0pF | ±0.05pF | GRM1885C2A5R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A5R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A5R0CA01# |  |
|        |               |         | 5.1pF | ±0.05pF | GRM1885C2A5R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A5R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A5R1CA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 100Vdc        | C0G     | 5.1pF | ±0.5pF  | GRM1885C2A5R1DA01# |  |
|        |               |         |       | ±0.05pF | GRM1885C2A5R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A5R2BA01# |  |
|        |               |         | 5.2pF | ±0.25pF | GRM1885C2A5R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C2A5R2DA01# |  |
|        |               |         | 5.3pF | ±0.05pF | GRM1885C2A5R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A5R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A5R3CA01# |  |
|        |               |         | 5.4pF | ±0.05pF | GRM1885C2A5R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A5R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A5R4CA01# |  |
|        |               |         | 5.5pF | ±0.05pF | GRM1885C2A5R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A5R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A5R5CA01# |  |
|        |               |         | 5.6pF | ±0.05pF | GRM1885C2A5R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A5R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A5R6CA01# |  |
|        |               |         | 5.7pF | ±0.05pF | GRM1885C2A5R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A5R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A5R7CA01# |  |
|        |               |         | 5.8pF | ±0.05pF | GRM1885C2A5R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A5R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A5R8CA01# |  |
|        |               |         | 5.9pF | ±0.05pF | GRM1885C2A5R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A5R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A5R9CA01# |  |
|        |               |         | 6.0pF | ±0.05pF | GRM1885C2A6R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A6R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A6R0CA01# |  |
|        |               |         | 6.1pF | ±0.05pF | GRM1885C2A6R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A6R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A6R1CA01# |  |
|        |               |         | 6.2pF | ±0.05pF | GRM1885C2A6R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A6R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A6R2CA01# |  |
|        |               |         | 6.3pF | ±0.05pF | GRM1885C2A6R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A6R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A6R3CA01# |  |
|        |               |         | 6.4pF | ±0.05pF | GRM1885C2A6R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A6R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A6R4CA01# |  |
|        |               |         | 6.5pF | ±0.05pF | GRM1885C2A6R5WA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 100Vdc        | C0G     | 6.5pF | ±0.1pF  | GRM1885C2A6R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A6R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C2A6R5DA01# |  |
|        |               |         | 6.6pF | ±0.05pF | GRM1885C2A6R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A6R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A6R6CA01# |  |
|        |               |         | 6.7pF | ±0.05pF | GRM1885C2A6R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A6R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A6R7CA01# |  |
|        |               |         | 6.8pF | ±0.05pF | GRM1885C2A6R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A6R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A6R8CA01# |  |
|        |               |         | 6.9pF | ±0.05pF | GRM1885C2A6R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A6R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A6R9CA01# |  |
|        |               |         | 7.0pF | ±0.05pF | GRM1885C2A7R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A7R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A7R0CA01# |  |
|        |               |         | 7.1pF | ±0.05pF | GRM1885C2A7R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A7R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A7R1CA01# |  |
|        |               |         | 7.2pF | ±0.05pF | GRM1885C2A7R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A7R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A7R2CA01# |  |
|        |               |         | 7.3pF | ±0.05pF | GRM1885C2A7R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A7R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A7R3CA01# |  |
|        |               |         | 7.4pF | ±0.05pF | GRM1885C2A7R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A7R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A7R4CA01# |  |
|        |               |         | 7.5pF | ±0.05pF | GRM1885C2A7R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A7R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A7R5CA01# |  |
|        |               |         | 7.6pF | ±0.05pF | GRM1885C2A7R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A7R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A7R6CA01# |  |
|        |               |         | 7.7pF | ±0.05pF | GRM1885C2A7R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A7R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A7R7CA01# |  |
|        |               |         | 7.8pF | ±0.05pF | GRM1885C2A7R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A7R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A7R8CA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 100Vdc        | C0G     | 7.8pF | ±0.5pF  | GRM1885C2A7R8DA01# |  |
|        |               |         |       | ±0.05pF | GRM1885C2A7R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A7R9BA01# |  |
|        |               |         | 8.0pF | ±0.25pF | GRM1885C2A7R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C2A7R9DA01# |  |
|        |               |         | 8.1pF | ±0.05pF | GRM1885C2A8R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A8R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A8R0CA01# |  |
|        |               |         | 8.2pF | ±0.05pF | GRM1885C2A8R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A8R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A8R1CA01# |  |
|        |               |         | 8.3pF | ±0.05pF | GRM1885C2A8R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A8R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A8R2CA01# |  |
|        |               |         | 8.4pF | ±0.05pF | GRM1885C2A8R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A8R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A8R3CA01# |  |
|        |               |         | 8.5pF | ±0.05pF | GRM1885C2A8R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A8R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A8R4CA01# |  |
|        |               |         | 8.6pF | ±0.05pF | GRM1885C2A8R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A8R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A8R5CA01# |  |
|        |               |         | 8.7pF | ±0.05pF | GRM1885C2A8R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A8R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A8R6CA01# |  |
|        |               |         | 8.8pF | ±0.05pF | GRM1885C2A8R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A8R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A8R7CA01# |  |
|        |               |         | 8.9pF | ±0.05pF | GRM1885C2A8R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A8R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A8R8CA01# |  |
|        |               |         | 9.0pF | ±0.05pF | GRM1885C2A8R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A8R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A8R9CA01# |  |
|        |               |         | 9.1pF | ±0.05pF | GRM1885C2A9R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A9R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A9R0CA01# |  |
|        |               |         | 9.2pF | ±0.05pF | GRM1885C2A9R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A9R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A9R1CA01# |  |

Part number # indicates the package specification code.



# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 100Vdc        | C0G     | 9.2pF | ±0.1pF  | GRM1885C2A9R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A9R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C2A9R2DA01# |  |
|        |               |         | 9.3pF | ±0.05pF | GRM1885C2A9R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A9R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A9R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C2A9R3DA01# |  |
|        |               |         | 9.4pF | ±0.05pF | GRM1885C2A9R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A9R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A9R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C2A9R4DA01# |  |
|        |               |         | 9.5pF | ±0.05pF | GRM1885C2A9R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A9R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A9R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C2A9R5DA01# |  |
|        |               |         | 9.6pF | ±0.05pF | GRM1885C2A9R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A9R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A9R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C2A9R6DA01# |  |
|        |               |         | 9.7pF | ±0.05pF | GRM1885C2A9R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A9R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A9R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C2A9R7DA01# |  |
|        |               |         | 9.8pF | ±0.05pF | GRM1885C2A9R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A9R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A9R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C2A9R8DA01# |  |
|        |               |         | 9.9pF | ±0.05pF | GRM1885C2A9R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C2A9R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C2A9R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C2A9R9DA01# |  |
|        |               |         | 10pF  | ±5%     | GRM1885C2A100JA01# |  |
|        |               |         | 12pF  | ±5%     | GRM1885C2A120JA01# |  |
|        |               |         | 15pF  | ±5%     | GRM1885C2A150JA01# |  |
|        |               |         | 18pF  | ±5%     | GRM1885C2A180JA01# |  |
|        |               |         | 22pF  | ±5%     | GRM1885C2A220JA01# |  |
|        |               |         | 27pF  | ±5%     | GRM1885C2A270JA01# |  |
|        |               |         | 33pF  | ±5%     | GRM1885C2A330JA01# |  |
|        |               |         | 39pF  | ±5%     | GRM1885C2A390JA01# |  |
|        |               |         | 47pF  | ±5%     | GRM1885C2A470JA01# |  |
|        |               |         | 56pF  | ±5%     | GRM1885C2A560JA01# |  |
|        |               |         | 68pF  | ±5%     | GRM1885C2A680JA01# |  |
|        |               |         | 82pF  | ±5%     | GRM1885C2A820JA01# |  |
|        |               |         | 100pF | ±5%     | GRM1885C2A101JA01# |  |
|        |               |         | 120pF | ±5%     | GRM1885C2A121JA01# |  |
|        |               |         | 150pF | ±5%     | GRM1885C2A151JA01# |  |
|        |               |         | 180pF | ±5%     | GRM1885C2A181JA01# |  |
|        |               |         | 220pF | ±5%     | GRM1885C2A221JA01# |  |
|        |               |         | 270pF | ±5%     | GRM1885C2A271JA01# |  |
|        |               |         | 330pF | ±5%     | GRM1885C2A331JA01# |  |
|        |               |         | 390pF | ±5%     | GRM1885C2A391JA01# |  |
|        |               |         | 470pF | ±5%     | GRM1885C2A471JA01# |  |
|        |               |         | 560pF | ±5%     | GRM1885C2A561JA01# |  |
|        |               |         | 680pF | ±5%     | GRM1885C2A681JA01# |  |

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.9mm  | 100Vdc        | C0G     | 820pF  | ±5%     | GRM1885C2A821JA01# |  |
|        |               |         | 1000pF | ±5%     | GRM1885C2A102JA01# |  |
|        |               |         | 1200pF | ±5%     | GRM1885C2A122JA01# |  |
|        |               |         | 1500pF | ±5%     | GRM1885C2A152JA01# |  |
|        |               | CK      | 0.50pF | ±0.05pF | GRM1884C2AR50WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1884C2AR50BA01# |  |
|        |               |         | 0.60pF | ±0.05pF | GRM1884C2AR60WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1884C2AR60BA01# |  |
|        |               |         | 0.70pF | ±0.05pF | GRM1884C2AR70WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1884C2AR70BA01# |  |
|        |               |         | 0.80pF | ±0.05pF | GRM1884C2AR80WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1884C2AR80BA01# |  |
|        |               |         | 0.90pF | ±0.05pF | GRM1884C2AR90WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1884C2AR90BA01# |  |
|        |               |         | 1.0pF  | ±0.05pF | GRM1884C2A1R0WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1884C2A1R0BA01# |  |
|        |               |         |        | ±0.25pF | GRM1884C2A1R0CA01# |  |
|        |               |         | 1.1pF  | ±0.05pF | GRM1884C2A1R1WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1884C2A1R1BA01# |  |
|        |               |         |        | ±0.25pF | GRM1884C2A1R1CA01# |  |
|        |               |         | 1.2pF  | ±0.05pF | GRM1884C2A1R2WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1884C2A1R2BA01# |  |
|        |               |         |        | ±0.25pF | GRM1884C2A1R2CA01# |  |
|        |               |         | 1.3pF  | ±0.05pF | GRM1884C2A1R3WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1884C2A1R3BA01# |  |
|        |               |         |        | ±0.25pF | GRM1884C2A1R3CA01# |  |
|        |               |         | 1.4pF  | ±0.05pF | GRM1884C2A1R4WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1884C2A1R4BA01# |  |
|        |               |         |        | ±0.25pF | GRM1884C2A1R4CA01# |  |
|        |               |         | 1.5pF  | ±0.05pF | GRM1884C2A1R5WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1884C2A1R5BA01# |  |
|        |               |         |        | ±0.25pF | GRM1884C2A1R5CA01# |  |
|        |               |         | 1.6pF  | ±0.05pF | GRM1884C2A1R6WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1884C2A1R6BA01# |  |
|        |               |         |        | ±0.25pF | GRM1884C2A1R6CA01# |  |
|        |               |         | 1.7pF  | ±0.05pF | GRM1884C2A1R7WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1884C2A1R7BA01# |  |
|        |               |         |        | ±0.25pF | GRM1884C2A1R7CA01# |  |
|        |               |         | 1.8pF  | ±0.05pF | GRM1884C2A1R8WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1884C2A1R8BA01# |  |
|        |               |         |        | ±0.25pF | GRM1884C2A1R8CA01# |  |
|        |               |         | 1.9pF  | ±0.05pF | GRM1884C2A1R9WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1884C2A1R9BA01# |  |
|        |               |         |        | ±0.25pF | GRM1884C2A1R9CA01# |  |
|        |               | CJ      | 2.0pF  | ±0.05pF | GRM1884C2A2R0WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1884C2A2R0BA01# |  |
|        |               |         |        | ±0.25pF | GRM1884C2A2R0CA01# |  |
|        |               |         | 2.1pF  | ±0.05pF | GRM1883C2A2R1WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1883C2A2R1BA01# |  |
|        |               |         |        | ±0.25pF | GRM1883C2A2R1CA01# |  |
|        |               |         | 2.2pF  | ±0.05pF | GRM1883C2A2R2WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1883C2A2R2BA01# |  |
|        |               |         |        | ±0.25pF | GRM1883C2A2R2CA01# |  |
|        |               |         | 2.3pF  | ±0.05pF | GRM1883C2A2R3WA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 100Vdc        | CJ      | 2.3pF | ±0.1pF  | GRM1883C2A2R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C2A2R3CA01# |  |
|        |               |         | 2.4pF | ±0.05pF | GRM1883C2A2R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C2A2R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C2A2R4CA01# |  |
|        |               |         | 2.5pF | ±0.05pF | GRM1883C2A2R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C2A2R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C2A2R5CA01# |  |
|        |               |         | 2.6pF | ±0.05pF | GRM1883C2A2R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C2A2R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C2A2R6CA01# |  |
|        |               |         | 2.7pF | ±0.05pF | GRM1883C2A2R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C2A2R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C2A2R7CA01# |  |
|        |               |         | 2.8pF | ±0.05pF | GRM1883C2A2R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C2A2R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C2A2R8CA01# |  |
|        |               |         | 2.9pF | ±0.05pF | GRM1883C2A2R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C2A2R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C2A2R9CA01# |  |
|        |               |         | 3.0pF | ±0.05pF | GRM1883C2A3R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C2A3R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C2A3R0CA01# |  |
|        |               |         | 3.1pF | ±0.05pF | GRM1883C2A3R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C2A3R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C2A3R1CA01# |  |
|        |               |         | 3.2pF | ±0.05pF | GRM1883C2A3R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C2A3R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C2A3R2CA01# |  |
|        |               |         | 3.3pF | ±0.05pF | GRM1883C2A3R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C2A3R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C2A3R3CA01# |  |
|        |               |         | 3.4pF | ±0.05pF | GRM1883C2A3R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C2A3R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C2A3R4CA01# |  |
|        |               |         | 3.5pF | ±0.05pF | GRM1883C2A3R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C2A3R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C2A3R5CA01# |  |
|        |               |         | 3.6pF | ±0.05pF | GRM1883C2A3R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C2A3R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C2A3R6CA01# |  |
|        |               |         | 3.7pF | ±0.05pF | GRM1883C2A3R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C2A3R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C2A3R7CA01# |  |
|        |               |         | 3.8pF | ±0.05pF | GRM1883C2A3R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C2A3R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C2A3R8CA01# |  |
|        |               |         | 3.9pF | ±0.05pF | GRM1883C2A3R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C2A3R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C2A3R9CA01# |  |
|        |               | CH      | 4.0pF | ±0.05pF | GRM1882C2A4R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A4R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A4R0CA01# |  |
|        |               |         | 4.1pF | ±0.05pF | GRM1882C2A4R1WA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 100Vdc        | CH      | 4.1pF | ±0.1pF  | GRM1882C2A4R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A4R1CA01# |  |
|        |               |         | 4.2pF | ±0.05pF | GRM1882C2A4R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A4R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A4R2CA01# |  |
|        |               |         | 4.3pF | ±0.05pF | GRM1882C2A4R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A4R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A4R3CA01# |  |
|        |               |         | 4.4pF | ±0.05pF | GRM1882C2A4R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A4R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A4R4CA01# |  |
|        |               |         | 4.5pF | ±0.05pF | GRM1882C2A4R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A4R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A4R5CA01# |  |
|        |               |         | 4.6pF | ±0.05pF | GRM1882C2A4R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A4R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A4R6CA01# |  |
|        |               |         | 4.7pF | ±0.05pF | GRM1882C2A4R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A4R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A4R7CA01# |  |
|        |               |         | 4.8pF | ±0.05pF | GRM1882C2A4R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A4R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A4R8CA01# |  |
|        |               |         | 4.9pF | ±0.05pF | GRM1882C2A4R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A4R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A4R9CA01# |  |
|        |               |         | 5.0pF | ±0.05pF | GRM1882C2A5R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A5R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A5R0CA01# |  |
|        |               |         | 5.1pF | ±0.05pF | GRM1882C2A5R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A5R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A5R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C2A5R1DA01# |  |
|        |               |         | 5.2pF | ±0.05pF | GRM1882C2A5R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A5R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A5R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C2A5R2DA01# |  |
|        |               |         | 5.3pF | ±0.05pF | GRM1882C2A5R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A5R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A5R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C2A5R3DA01# |  |
|        |               |         | 5.4pF | ±0.05pF | GRM1882C2A5R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A5R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A5R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C2A5R4DA01# |  |
|        |               |         | 5.5pF | ±0.05pF | GRM1882C2A5R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A5R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A5R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C2A5R5DA01# |  |
|        |               |         | 5.6pF | ±0.05pF | GRM1882C2A5R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A5R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A5R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C2A5R6DA01# |  |
|        |               |         | 5.7pF | ±0.05pF | GRM1882C2A5R7WA01# |  |

Part number # indicates the package specification code.



## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 100Vdc        | CH      | 5.7pF | ±0.1pF  | GRM1882C2A5R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A5R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C2A5R7DA01# |  |
|        |               |         | 5.8pF | ±0.05pF | GRM1882C2A5R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A5R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A5R8CA01# |  |
|        |               |         | 5.9pF | ±0.05pF | GRM1882C2A5R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A5R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A5R9CA01# |  |
|        |               |         | 6.0pF | ±0.05pF | GRM1882C2A6R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A6R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A6R0CA01# |  |
|        |               |         | 6.1pF | ±0.05pF | GRM1882C2A6R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A6R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A6R1CA01# |  |
|        |               |         | 6.2pF | ±0.05pF | GRM1882C2A6R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A6R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A6R2CA01# |  |
|        |               |         | 6.3pF | ±0.05pF | GRM1882C2A6R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A6R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A6R3CA01# |  |
|        |               |         | 6.4pF | ±0.05pF | GRM1882C2A6R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A6R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A6R4CA01# |  |
|        |               |         | 6.5pF | ±0.05pF | GRM1882C2A6R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A6R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A6R5CA01# |  |
|        |               |         | 6.6pF | ±0.05pF | GRM1882C2A6R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A6R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A6R6CA01# |  |
|        |               |         | 6.7pF | ±0.05pF | GRM1882C2A6R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A6R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A6R7CA01# |  |
|        |               |         | 6.8pF | ±0.05pF | GRM1882C2A6R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A6R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A6R8CA01# |  |
|        |               |         | 6.9pF | ±0.05pF | GRM1882C2A6R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A6R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A6R9CA01# |  |
|        |               |         | 7.0pF | ±0.05pF | GRM1882C2A7R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A7R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A7R0CA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 100Vdc        | CH      | 7.0pF | ±0.5pF  | GRM1882C2A7R0DA01# |  |
|        |               |         |       | ±0.05pF | GRM1882C2A7R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A7R1BA01# |  |
|        |               |         | 7.1pF | ±0.05pF | GRM1882C2A7R1CA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A7R1DA01# |  |
|        |               |         | 7.2pF | ±0.05pF | GRM1882C2A7R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A7R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A7R2CA01# |  |
|        |               |         | 7.3pF | ±0.05pF | GRM1882C2A7R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A7R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A7R3CA01# |  |
|        |               |         | 7.4pF | ±0.05pF | GRM1882C2A7R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A7R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A7R4CA01# |  |
|        |               |         | 7.5pF | ±0.05pF | GRM1882C2A7R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A7R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A7R5CA01# |  |
|        |               |         | 7.6pF | ±0.05pF | GRM1882C2A7R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A7R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A7R6CA01# |  |
|        |               |         | 7.7pF | ±0.05pF | GRM1882C2A7R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A7R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A7R7CA01# |  |
|        |               |         | 7.8pF | ±0.05pF | GRM1882C2A7R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A7R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A7R8CA01# |  |
|        |               |         | 7.9pF | ±0.05pF | GRM1882C2A7R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A7R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A7R9CA01# |  |
|        |               |         | 8.0pF | ±0.05pF | GRM1882C2A8R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A8R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A8R0CA01# |  |
|        |               |         | 8.1pF | ±0.05pF | GRM1882C2A8R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A8R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A8R1CA01# |  |
|        |               |         | 8.2pF | ±0.05pF | GRM1882C2A8R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A8R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A8R2CA01# |  |
|        |               |         | 8.3pF | ±0.05pF | GRM1882C2A8R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A8R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A8R3CA01# |  |
|        |               |         | 8.4pF | ±0.05pF | GRM1882C2A8R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A8R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A8R4CA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 100Vdc        | CH      | 8.4pF | ±0.1pF  | GRM1882C2A8R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A8R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C2A8R4DA01# |  |
|        |               |         | 8.5pF | ±0.05pF | GRM1882C2A8R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A8R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A8R5CA01# |  |
|        |               |         | 8.6pF | ±0.05pF | GRM1882C2A8R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A8R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A8R6CA01# |  |
|        |               |         | 8.7pF | ±0.05pF | GRM1882C2A8R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A8R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A8R7CA01# |  |
|        |               |         | 8.8pF | ±0.05pF | GRM1882C2A8R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A8R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A8R8CA01# |  |
|        |               |         | 8.9pF | ±0.05pF | GRM1882C2A8R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A8R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A8R9CA01# |  |
|        |               |         | 9.0pF | ±0.05pF | GRM1882C2A9R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A9R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A9R0CA01# |  |
|        |               |         | 9.1pF | ±0.05pF | GRM1882C2A9R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A9R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A9R1CA01# |  |
|        |               |         | 9.2pF | ±0.05pF | GRM1882C2A9R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A9R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A9R2CA01# |  |
|        |               |         | 9.3pF | ±0.05pF | GRM1882C2A9R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A9R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A9R3CA01# |  |
|        |               |         | 9.4pF | ±0.05pF | GRM1882C2A9R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A9R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A9R4CA01# |  |
|        |               |         | 9.5pF | ±0.05pF | GRM1882C2A9R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A9R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A9R5CA01# |  |
|        |               |         | 9.6pF | ±0.05pF | GRM1882C2A9R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A9R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A9R6CA01# |  |
|        |               |         | 9.7pF | ±0.05pF | GRM1882C2A9R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C2A9R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C2A9R7CA01# |  |

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.9mm  | 100Vdc        | CH      | 9.7pF  | ±0.5pF  | GRM1882C2A9R7DA01# |  |
|        |               |         |        | ±0.05pF | GRM1882C2A9R8WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1882C2A9R8BA01# |  |
|        |               |         | 9.8pF  | ±0.25pF | GRM1882C2A9R8CA01# |  |
|        |               |         |        | ±0.5pF  | GRM1882C2A9R8DA01# |  |
|        |               |         | 9.9pF  | ±0.05pF | GRM1882C2A9R9WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1882C2A9R9BA01# |  |
|        |               |         |        | ±0.25pF | GRM1882C2A9R9CA01# |  |
|        |               |         | 10pF   | ±5%     | GRM1882C2A100JA01# |  |
|        |               |         |        | ±5%     | GRM1882C2A120JA01# |  |
|        |               |         | 12pF   | ±5%     | GRM1882C2A150JA01# |  |
|        |               |         |        | ±5%     | GRM1882C2A180JA01# |  |
|        |               |         | 22pF   | ±5%     | GRM1882C2A220JA01# |  |
|        |               |         |        | ±5%     | GRM1882C2A270JA01# |  |
|        |               |         | 33pF   | ±5%     | GRM1882C2A330JA01# |  |
|        |               |         |        | ±5%     | GRM1882C2A390JA01# |  |
|        |               |         | 47pF   | ±5%     | GRM1882C2A470JA01# |  |
|        |               |         |        | ±5%     | GRM1882C2A560JA01# |  |
|        |               |         | 68pF   | ±5%     | GRM1882C2A680JA01# |  |
|        |               |         |        | ±5%     | GRM1882C2A820JA01# |  |
|        |               |         | 100pF  | ±5%     | GRM1882C2A101JA01# |  |
|        |               |         |        | ±5%     | GRM1882C2A121JA01# |  |
|        |               |         | 150pF  | ±5%     | GRM1882C2A151JA01# |  |
|        |               |         |        | ±5%     | GRM1882C2A181JA01# |  |
|        |               |         | 220pF  | ±5%     | GRM1882C2A221JA01# |  |
|        |               |         |        | ±5%     | GRM1882C2A271JA01# |  |
|        |               |         | 330pF  | ±5%     | GRM1882C2A331JA01# |  |
|        |               |         |        | ±5%     | GRM1882C2A391JA01# |  |
|        |               |         | 470pF  | ±5%     | GRM1882C2A471JA01# |  |
|        |               |         |        | ±5%     | GRM1882C2A561JA01# |  |
|        |               |         | 680pF  | ±5%     | GRM1882C2A681JA01# |  |
|        |               |         |        | ±5%     | GRM1882C2A821JA01# |  |
|        |               |         | 1000pF | ±5%     | GRM1882C2A102JA01# |  |
|        |               |         |        | ±5%     | GRM1882C2A122JA01# |  |
|        |               |         | 1500pF | ±5%     | GRM1882C2A152JA01# |  |
|        | 50Vdc         | C0G     | 0.50pF | ±0.05pF | GRM1885C1HR50WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1885C1HR50BA01# |  |
|        |               |         | 0.60pF | ±0.05pF | GRM1885C1HR60WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1885C1HR60BA01# |  |
|        |               |         | 0.70pF | ±0.05pF | GRM1885C1HR70WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1885C1HR70BA01# |  |
|        |               |         | 0.80pF | ±0.05pF | GRM1885C1HR80WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1885C1HR80BA01# |  |
|        |               |         | 0.90pF | ±0.05pF | GRM1885C1HR90WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1885C1HR90BA01# |  |
|        |               |         | 1.0pF  | ±0.05pF | GRM1885C1H1R0WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1885C1H1R0BA01# |  |
|        |               |         |        | ±0.25pF | GRM1885C1H1R0CA01# |  |
|        |               |         | 1.1pF  | ±0.05pF | GRM1885C1H1R1WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1885C1H1R1BA01# |  |
|        |               |         |        | ±0.25pF | GRM1885C1H1R1CA01# |  |
|        |               |         | 1.2pF  | ±0.05pF | GRM1885C1H1R2WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1885C1H1R2BA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 50Vdc         | C0G     | 1.2pF | ±0.25pF | GRM1885C1H1R2CA01# |  |
|        |               |         |       | ±0.05pF | GRM1885C1H1R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H1R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H1R3CA01# |  |
|        |               |         | 1.4pF | ±0.05pF | GRM1885C1H1R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H1R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H1R4CA01# |  |
|        |               |         | 1.5pF | ±0.05pF | GRM1885C1H1R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H1R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H1R5CA01# |  |
|        |               |         | 1.6pF | ±0.05pF | GRM1885C1H1R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H1R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H1R6CA01# |  |
|        |               |         | 1.7pF | ±0.05pF | GRM1885C1H1R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H1R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H1R7CA01# |  |
|        |               |         | 1.8pF | ±0.05pF | GRM1885C1H1R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H1R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H1R8CA01# |  |
|        |               |         | 1.9pF | ±0.05pF | GRM1885C1H1R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H1R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H1R9CA01# |  |
|        |               |         | 2.0pF | ±0.05pF | GRM1885C1H2R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H2R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H2R0CA01# |  |
|        |               |         | 2.1pF | ±0.05pF | GRM1885C1H2R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H2R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H2R1CA01# |  |
|        |               |         | 2.2pF | ±0.05pF | GRM1885C1H2R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H2R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H2R2CA01# |  |
|        |               |         | 2.3pF | ±0.05pF | GRM1885C1H2R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H2R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H2R3CA01# |  |
|        |               |         | 2.4pF | ±0.05pF | GRM1885C1H2R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H2R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H2R4CA01# |  |
|        |               |         | 2.5pF | ±0.05pF | GRM1885C1H2R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H2R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H2R5CA01# |  |
|        |               |         | 2.6pF | ±0.05pF | GRM1885C1H2R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H2R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H2R6CA01# |  |
|        |               |         | 2.7pF | ±0.05pF | GRM1885C1H2R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H2R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H2R7CA01# |  |
|        |               |         | 2.8pF | ±0.05pF | GRM1885C1H2R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H2R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H2R8CA01# |  |
|        |               |         | 2.9pF | ±0.05pF | GRM1885C1H2R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H2R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H2R9CA01# |  |
|        |               |         | 3.0pF | ±0.05pF | GRM1885C1H3R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H3R0BA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 50Vdc         | C0G     | 3.0pF | ±0.25pF | GRM1885C1H3R0CA01# |  |
|        |               |         |       | ±0.05pF | GRM1885C1H3R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H3R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H3R1CA01# |  |
|        |               |         | 3.2pF | ±0.05pF | GRM1885C1H3R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H3R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H3R2CA01# |  |
|        |               |         | 3.3pF | ±0.05pF | GRM1885C1H3R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H3R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H3R3CA01# |  |
|        |               |         | 3.4pF | ±0.05pF | GRM1885C1H3R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H3R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H3R4CA01# |  |
|        |               |         | 3.5pF | ±0.05pF | GRM1885C1H3R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H3R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H3R5CA01# |  |
|        |               |         | 3.6pF | ±0.05pF | GRM1885C1H3R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H3R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H3R6CA01# |  |
|        |               |         | 3.7pF | ±0.05pF | GRM1885C1H3R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H3R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H3R7CA01# |  |
|        |               |         | 3.8pF | ±0.05pF | GRM1885C1H3R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H3R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H3R8CA01# |  |
|        |               |         | 3.9pF | ±0.05pF | GRM1885C1H3R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H3R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H3R9CA01# |  |
|        |               |         | 4.0pF | ±0.05pF | GRM1885C1H4R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H4R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H4R0CA01# |  |
|        |               |         | 4.1pF | ±0.05pF | GRM1885C1H4R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H4R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H4R1CA01# |  |
|        |               |         | 4.2pF | ±0.05pF | GRM1885C1H4R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H4R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H4R2CA01# |  |
|        |               |         | 4.3pF | ±0.05pF | GRM1885C1H4R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H4R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H4R3CA01# |  |
|        |               |         | 4.4pF | ±0.05pF | GRM1885C1H4R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H4R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H4R4CA01# |  |
|        |               |         | 4.5pF | ±0.05pF | GRM1885C1H4R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H4R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H4R5CA01# |  |
|        |               |         | 4.6pF | ±0.05pF | GRM1885C1H4R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H4R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H4R6CA01# |  |
|        |               |         | 4.7pF | ±0.05pF | GRM1885C1H4R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H4R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H4R7CA01# |  |
|        |               |         | 4.8pF | ±0.05pF | GRM1885C1H4R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H4R8BA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 50Vdc         | C0G     | 4.8pF | ±0.25pF | GRM1885C1H4R8CA01# |  |
|        |               |         |       | ±0.05pF | GRM1885C1H4R9WA01# |  |
|        |               |         | 4.9pF | ±0.1pF  | GRM1885C1H4R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H4R9CA01# |  |
|        |               |         | 5.0pF | ±0.05pF | GRM1885C1H5R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H5R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H5R0CA01# |  |
|        |               |         | 5.1pF | ±0.05pF | GRM1885C1H5R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H5R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H5R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H5R1DA01# |  |
|        |               |         | 5.2pF | ±0.05pF | GRM1885C1H5R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H5R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H5R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H5R2DA01# |  |
|        |               |         | 5.3pF | ±0.05pF | GRM1885C1H5R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H5R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H5R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H5R3DA01# |  |
|        |               |         | 5.4pF | ±0.05pF | GRM1885C1H5R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H5R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H5R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H5R4DA01# |  |
|        |               |         | 5.5pF | ±0.05pF | GRM1885C1H5R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H5R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H5R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H5R5DA01# |  |
|        |               |         | 5.6pF | ±0.05pF | GRM1885C1H5R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H5R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H5R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H5R6DA01# |  |
|        |               |         | 5.7pF | ±0.05pF | GRM1885C1H5R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H5R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H5R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H5R7DA01# |  |
|        |               |         | 5.8pF | ±0.05pF | GRM1885C1H5R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H5R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H5R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H5R8DA01# |  |
|        |               |         | 5.9pF | ±0.05pF | GRM1885C1H5R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H5R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H5R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H5R9DA01# |  |
|        |               |         | 6.0pF | ±0.05pF | GRM1885C1H6R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H6R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H6R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H6R0DA01# |  |
|        |               |         | 6.1pF | ±0.05pF | GRM1885C1H6R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H6R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H6R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H6R1DA01# |  |
|        |               |         | 6.2pF | ±0.05pF | GRM1885C1H6R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H6R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H6R2CA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 50Vdc         | C0G     | 6.2pF | ±0.5pF  | GRM1885C1H6R2DA01# |  |
|        |               |         |       | ±0.05pF | GRM1885C1H6R3WA01# |  |
|        |               |         | 6.3pF | ±0.1pF  | GRM1885C1H6R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H6R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H6R3DA01# |  |
|        |               |         | 6.4pF | ±0.05pF | GRM1885C1H6R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H6R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H6R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H6R4DA01# |  |
|        |               |         | 6.5pF | ±0.05pF | GRM1885C1H6R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H6R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H6R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H6R5DA01# |  |
|        |               |         | 6.6pF | ±0.05pF | GRM1885C1H6R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H6R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H6R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H6R6DA01# |  |
|        |               |         | 6.7pF | ±0.05pF | GRM1885C1H6R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H6R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H6R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H6R7DA01# |  |
|        |               |         | 6.8pF | ±0.05pF | GRM1885C1H6R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H6R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H6R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H6R8DA01# |  |
|        |               |         | 6.9pF | ±0.05pF | GRM1885C1H6R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H6R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H6R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H6R9DA01# |  |
|        |               |         | 7.0pF | ±0.05pF | GRM1885C1H7R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H7R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H7R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H7R0DA01# |  |
|        |               |         | 7.1pF | ±0.05pF | GRM1885C1H7R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H7R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H7R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H7R1DA01# |  |
|        |               |         | 7.2pF | ±0.05pF | GRM1885C1H7R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H7R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H7R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H7R2DA01# |  |
|        |               |         | 7.3pF | ±0.05pF | GRM1885C1H7R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H7R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H7R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H7R3DA01# |  |
|        |               |         | 7.4pF | ±0.05pF | GRM1885C1H7R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H7R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H7R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H7R4DA01# |  |
|        |               |         | 7.5pF | ±0.05pF | GRM1885C1H7R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H7R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H7R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H7R5DA01# |  |
|        |               |         | 7.6pF | ±0.05pF | GRM1885C1H7R6WA01# |  |

Part number # indicates the package specification code.



# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 50Vdc         | C0G     | 7.6pF | ±0.1pF  | GRM1885C1H7R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H7R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H7R6DA01# |  |
|        |               |         | 7.7pF | ±0.05pF | GRM1885C1H7R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H7R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H7R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H7R7DA01# |  |
|        |               |         | 7.8pF | ±0.05pF | GRM1885C1H7R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H7R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H7R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H7R8DA01# |  |
|        |               |         | 7.9pF | ±0.05pF | GRM1885C1H7R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H7R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H7R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H7R9DA01# |  |
|        |               |         | 8.0pF | ±0.05pF | GRM1885C1H8R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H8R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H8R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H8R0DA01# |  |
|        |               |         | 8.1pF | ±0.05pF | GRM1885C1H8R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H8R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H8R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H8R1DA01# |  |
|        |               |         | 8.2pF | ±0.05pF | GRM1885C1H8R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H8R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H8R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H8R2DA01# |  |
|        |               |         | 8.3pF | ±0.05pF | GRM1885C1H8R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H8R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H8R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H8R3DA01# |  |
|        |               |         | 8.4pF | ±0.05pF | GRM1885C1H8R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H8R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H8R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H8R4DA01# |  |
|        |               |         | 8.5pF | ±0.05pF | GRM1885C1H8R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H8R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H8R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H8R5DA01# |  |
|        |               |         | 8.6pF | ±0.05pF | GRM1885C1H8R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H8R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H8R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H8R6DA01# |  |
|        |               |         | 8.7pF | ±0.05pF | GRM1885C1H8R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H8R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H8R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H8R7DA01# |  |
|        |               |         | 8.8pF | ±0.05pF | GRM1885C1H8R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H8R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H8R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H8R8DA01# |  |
|        |               |         | 8.9pF | ±0.05pF | GRM1885C1H8R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H8R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H8R9CA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 50Vdc         | C0G     | 8.9pF | ±0.5pF  | GRM1885C1H8R9DA01# |  |
|        |               |         |       | ±0.05pF | GRM1885C1H9R0WA01# |  |
|        |               |         | 9.0pF | ±0.1pF  | GRM1885C1H9R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H9R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1885C1H9R0DA01# |  |
|        |               |         | 9.1pF | ±0.05pF | GRM1885C1H9R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H9R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H9R1CA01# |  |
|        |               |         | 9.2pF | ±0.05pF | GRM1885C1H9R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H9R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H9R2CA01# |  |
|        |               |         | 9.3pF | ±0.05pF | GRM1885C1H9R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H9R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H9R3CA01# |  |
|        |               |         | 9.4pF | ±0.05pF | GRM1885C1H9R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H9R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H9R4CA01# |  |
|        |               |         | 9.5pF | ±0.05pF | GRM1885C1H9R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H9R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H9R5CA01# |  |
|        |               |         | 9.6pF | ±0.05pF | GRM1885C1H9R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H9R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H9R6CA01# |  |
|        |               |         | 9.7pF | ±0.05pF | GRM1885C1H9R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H9R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H9R7CA01# |  |
|        |               |         | 9.8pF | ±0.05pF | GRM1885C1H9R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H9R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H9R8CA01# |  |
|        |               |         | 9.9pF | ±0.05pF | GRM1885C1H9R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1885C1H9R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1885C1H9R9CA01# |  |
|        |               |         | 10pF  | ±5%     | GRM1885C1H100JA01# |  |
|        |               |         | 12pF  | ±5%     | GRM1885C1H120JA01# |  |
|        |               |         | 15pF  | ±5%     | GRM1885C1H150JA01# |  |
|        |               |         | 18pF  | ±5%     | GRM1885C1H180JA01# |  |
|        |               |         | 22pF  | ±5%     | GRM1885C1H220JA01# |  |
|        |               |         | 27pF  | ±5%     | GRM1885C1H270JA01# |  |
|        |               |         | 33pF  | ±5%     | GRM1885C1H330JA01# |  |
|        |               |         | 39pF  | ±5%     | GRM1885C1H390JA01# |  |
|        |               |         | 47pF  | ±5%     | GRM1885C1H470JA01# |  |
|        |               |         | 56pF  | ±5%     | GRM1885C1H560JA01# |  |
|        |               |         | 68pF  | ±5%     | GRM1885C1H680JA01# |  |
|        |               |         | 82pF  | ±5%     | GRM1885C1H820JA01# |  |
|        |               |         | 100pF | ±5%     | GRM1885C1H101JA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.    | Tol.    | Part Number        |  |
|--------|---------------|---------|---------|---------|--------------------|--|
| 0.9mm  | 50Vdc         | C0G     | 120pF   | ±5%     | GRM1885C1H121JA01# |  |
|        |               |         | 150pF   | ±5%     | GRM1885C1H151JA01# |  |
|        |               |         | 180pF   | ±5%     | GRM1885C1H181JA01# |  |
|        |               |         | 220pF   | ±5%     | GRM1885C1H221JA01# |  |
|        |               |         | 270pF   | ±5%     | GRM1885C1H271JA01# |  |
|        |               |         | 330pF   | ±5%     | GRM1885C1H331JA01# |  |
|        |               |         | 390pF   | ±5%     | GRM1885C1H391JA01# |  |
|        |               |         | 470pF   | ±5%     | GRM1885C1H471JA01# |  |
|        |               |         | 560pF   | ±5%     | GRM1885C1H561JA01# |  |
|        |               |         | 680pF   | ±5%     | GRM1885C1H681JA01# |  |
|        |               |         | 820pF   | ±5%     | GRM1885C1H821JA01# |  |
|        |               |         | 1000pF  | ±5%     | GRM1885C1H102JA01# |  |
|        |               |         | 1200pF  | ±5%     | GRM1885C1H122JA01# |  |
|        |               |         | 1500pF  | ±5%     | GRM1885C1H152JA01# |  |
|        |               |         | 1800pF  | ±5%     | GRM1885C1H182JA01# |  |
|        |               |         | 2200pF  | ±5%     | GRM1885C1H222JA01# |  |
|        |               |         | 2700pF  | ±5%     | GRM1885C1H272JA01# |  |
|        |               |         | 3300pF  | ±5%     | GRM1885C1H332JA01# |  |
|        |               |         | 3900pF  | ±5%     | GRM1885C1H392JA01# |  |
|        |               |         | 4700pF  | ±5%     | GRM1885C1H472JA01# |  |
|        |               |         | 5600pF  | ±5%     | GRM1885C1H562JA01# |  |
|        |               |         | 6800pF  | ±5%     | GRM1885C1H682JA01# |  |
|        |               |         | 8200pF  | ±5%     | GRM1885C1H822JA01# |  |
|        |               |         | 10000pF | ±5%     | GRM1885C1H103JA01# |  |
|        |               | CK      | 0.50pF  | ±0.05pF | GRM1884C1HR50WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1884C1HR50BA01# |  |
|        |               |         | 0.60pF  | ±0.05pF | GRM1884C1HR60WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1884C1HR60BA01# |  |
|        |               |         | 0.70pF  | ±0.05pF | GRM1884C1HR70WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1884C1HR70BA01# |  |
|        |               |         | 0.80pF  | ±0.05pF | GRM1884C1HR80WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1884C1HR80BA01# |  |
|        |               |         | 0.90pF  | ±0.05pF | GRM1884C1HR90WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1884C1HR90BA01# |  |
|        |               |         | 1.0pF   | ±0.05pF | GRM1884C1H1R0WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1884C1H1R0BA01# |  |
|        |               |         |         | ±0.25pF | GRM1884C1H1R0CA01# |  |
|        |               |         | 1.1pF   | ±0.05pF | GRM1884C1H1R1WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1884C1H1R1BA01# |  |
|        |               |         |         | ±0.25pF | GRM1884C1H1R1CA01# |  |
|        |               |         | 1.2pF   | ±0.05pF | GRM1884C1H1R2WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1884C1H1R2BA01# |  |
|        |               |         |         | ±0.25pF | GRM1884C1H1R2CA01# |  |
|        |               |         | 1.3pF   | ±0.05pF | GRM1884C1H1R3WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1884C1H1R3BA01# |  |
|        |               |         |         | ±0.25pF | GRM1884C1H1R3CA01# |  |
|        |               |         | 1.4pF   | ±0.05pF | GRM1884C1H1R4WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1884C1H1R4BA01# |  |
|        |               |         |         | ±0.25pF | GRM1884C1H1R4CA01# |  |
|        |               |         | 1.5pF   | ±0.05pF | GRM1884C1H1R5WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1884C1H1R5BA01# |  |
|        |               |         |         | ±0.25pF | GRM1884C1H1R5CA01# |  |
|        |               |         | 1.6pF   | ±0.05pF | GRM1884C1H1R6WA01# |  |
|        |               |         |         | ±0.1pF  | GRM1884C1H1R6BA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 50Vdc         | CK      | 1.6pF | ±0.25pF | GRM1884C1H1R6CA01# |  |
|        |               |         |       | ±0.05pF | GRM1884C1H1R7WA01# |  |
|        |               |         | 1.7pF | ±0.1pF  | GRM1884C1H1R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1884C1H1R7CA01# |  |
|        |               |         | 1.8pF | ±0.05pF | GRM1884C1H1R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1884C1H1R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1884C1H1R8CA01# |  |
|        |               |         | 1.9pF | ±0.05pF | GRM1884C1H1R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1884C1H1R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1884C1H1R9CA01# |  |
|        |               |         | 2.0pF | ±0.05pF | GRM1884C1H2R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1884C1H2R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1884C1H2R0CA01# |  |
|        |               | CJ      | 2.1pF | ±0.05pF | GRM1883C1H2R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H2R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H2R1CA01# |  |
|        |               |         | 2.2pF | ±0.05pF | GRM1883C1H2R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H2R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H2R2CA01# |  |
|        |               |         | 2.3pF | ±0.05pF | GRM1883C1H2R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H2R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H2R3CA01# |  |
|        |               |         | 2.4pF | ±0.05pF | GRM1883C1H2R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H2R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H2R4CA01# |  |
|        |               |         | 2.5pF | ±0.05pF | GRM1883C1H2R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H2R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H2R5CA01# |  |
|        |               |         | 2.6pF | ±0.05pF | GRM1883C1H2R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H2R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H2R6CA01# |  |
|        |               |         | 2.7pF | ±0.05pF | GRM1883C1H2R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H2R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H2R7CA01# |  |
|        |               |         | 2.8pF | ±0.05pF | GRM1883C1H2R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H2R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H2R8CA01# |  |
|        |               |         | 2.9pF | ±0.05pF | GRM1883C1H2R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H2R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H2R9CA01# |  |
|        |               |         | 3.0pF | ±0.05pF | GRM1883C1H3R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H3R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H3R0CA01# |  |
|        |               |         | 3.1pF | ±0.05pF | GRM1883C1H3R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H3R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H3R1CA01# |  |
|        |               |         | 3.2pF | ±0.05pF | GRM1883C1H3R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H3R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H3R2CA01# |  |
|        |               |         | 3.3pF | ±0.05pF | GRM1883C1H3R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H3R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H3R3CA01# |  |
|        |               |         | 3.4pF | ±0.05pF | GRM1883C1H3R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H3R4BA01# |  |

Part number # indicates the package specification code.



# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 50Vdc         | CJ      | 3.4pF | ±0.25pF | GRM1883C1H3R4CA01# |  |
|        |               |         |       | ±0.05pF | GRM1883C1H3R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H3R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H3R5CA01# |  |
|        |               |         | 3.6pF | ±0.05pF | GRM1883C1H3R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H3R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H3R6CA01# |  |
|        |               |         |       |         |                    |  |
|        |               |         | 3.7pF | ±0.05pF | GRM1883C1H3R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H3R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H3R7CA01# |  |
|        |               |         |       |         |                    |  |
|        |               |         | 3.8pF | ±0.05pF | GRM1883C1H3R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H3R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H3R8CA01# |  |
|        |               |         |       |         |                    |  |
|        |               |         | 3.9pF | ±0.05pF | GRM1883C1H3R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1883C1H3R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1883C1H3R9CA01# |  |
|        |               |         |       |         |                    |  |
|        |               | CH      | 4.0pF | ±0.05pF | GRM1882C1H4R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H4R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H4R0CA01# |  |
|        |               |         |       |         |                    |  |
|        |               |         | 4.1pF | ±0.05pF | GRM1882C1H4R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H4R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H4R1CA01# |  |
|        |               |         |       |         |                    |  |
|        |               |         | 4.2pF | ±0.05pF | GRM1882C1H4R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H4R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H4R2CA01# |  |
|        |               |         |       |         |                    |  |
|        |               |         | 4.3pF | ±0.05pF | GRM1882C1H4R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H4R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H4R3CA01# |  |
|        |               |         |       |         |                    |  |
|        |               |         | 4.4pF | ±0.05pF | GRM1882C1H4R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H4R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H4R4CA01# |  |
|        |               |         |       |         |                    |  |
|        |               |         | 4.5pF | ±0.05pF | GRM1882C1H4R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H4R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H4R5CA01# |  |
|        |               |         |       |         |                    |  |
|        |               |         | 4.6pF | ±0.05pF | GRM1882C1H4R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H4R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H4R6CA01# |  |
|        |               |         |       |         |                    |  |
|        |               |         | 4.7pF | ±0.05pF | GRM1882C1H4R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H4R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H4R7CA01# |  |
|        |               |         |       |         |                    |  |
|        |               |         | 4.8pF | ±0.05pF | GRM1882C1H4R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H4R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H4R8CA01# |  |
|        |               |         |       |         |                    |  |
|        |               |         | 4.9pF | ±0.05pF | GRM1882C1H4R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H4R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H4R9CA01# |  |
|        |               |         |       |         |                    |  |
|        |               |         | 5.0pF | ±0.05pF | GRM1882C1H5R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H5R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H5R0CA01# |  |
|        |               |         |       |         |                    |  |
|        |               |         | 5.1pF | ±0.05pF | GRM1882C1H5R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H5R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H5R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H5R1DA01# |  |
|        |               |         | 5.2pF | ±0.05pF | GRM1882C1H5R2WA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 50Vdc         | CH      | 5.2pF | ±0.1pF  | GRM1882C1H5R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H5R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H5R2DA01# |  |
|        |               |         |       |         |                    |  |
|        |               |         | 5.3pF | ±0.05pF | GRM1882C1H5R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H5R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H5R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H5R3DA01# |  |
|        |               |         | 5.4pF | ±0.05pF | GRM1882C1H5R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H5R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H5R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H5R4DA01# |  |
|        |               |         | 5.5pF | ±0.05pF | GRM1882C1H5R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H5R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H5R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H5R5DA01# |  |
|        |               |         | 5.6pF | ±0.05pF | GRM1882C1H5R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H5R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H5R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H5R6DA01# |  |
|        |               |         | 5.7pF | ±0.05pF | GRM1882C1H5R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H5R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H5R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H5R7DA01# |  |
|        |               |         | 5.8pF | ±0.05pF | GRM1882C1H5R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H5R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H5R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H5R8DA01# |  |
|        |               |         | 5.9pF | ±0.05pF | GRM1882C1H5R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H5R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H5R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H5R9DA01# |  |
|        |               |         | 6.0pF | ±0.05pF | GRM1882C1H6R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H6R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H6R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H6R0DA01# |  |
|        |               |         | 6.1pF | ±0.05pF | GRM1882C1H6R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H6R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H6R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H6R1DA01# |  |
|        |               |         | 6.2pF | ±0.05pF | GRM1882C1H6R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H6R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H6R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H6R2DA01# |  |
|        |               |         | 6.3pF | ±0.05pF | GRM1882C1H6R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H6R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H6R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H6R3DA01# |  |
|        |               |         | 6.4pF | ±0.05pF | GRM1882C1H6R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H6R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H6R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H6R4DA01# |  |
|        |               |         | 6.5pF | ±0.05pF | GRM1882C1H6R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H6R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H6R5CA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 50Vdc         | CH      | 6.5pF | ±0.5pF  | GRM1882C1H6R5DA01# |  |
|        |               |         |       | ±0.05pF | GRM1882C1H6R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H6R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H6R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H6R6DA01# |  |
|        |               |         | 6.6pF | ±0.05pF | GRM1882C1H6R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H6R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H6R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H6R7DA01# |  |
|        |               |         | 6.7pF | ±0.05pF | GRM1882C1H6R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H6R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H6R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H6R8DA01# |  |
|        |               |         | 6.8pF | ±0.05pF | GRM1882C1H6R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H6R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H6R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H6R9DA01# |  |
|        |               |         | 6.9pF | ±0.05pF | GRM1882C1H7R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H7R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H7R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H7R0DA01# |  |
|        |               |         | 7.0pF | ±0.05pF | GRM1882C1H7R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H7R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H7R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H7R1DA01# |  |
|        |               |         | 7.1pF | ±0.05pF | GRM1882C1H7R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H7R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H7R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H7R2DA01# |  |
|        |               |         | 7.2pF | ±0.05pF | GRM1882C1H7R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H7R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H7R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H7R3DA01# |  |
|        |               |         | 7.3pF | ±0.05pF | GRM1882C1H7R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H7R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H7R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H7R4DA01# |  |
|        |               |         | 7.4pF | ±0.05pF | GRM1882C1H7R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H7R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H7R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H7R5DA01# |  |
|        |               |         | 7.5pF | ±0.05pF | GRM1882C1H7R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H7R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H7R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H7R6DA01# |  |
|        |               |         | 7.6pF | ±0.05pF | GRM1882C1H7R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H7R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H7R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H7R7DA01# |  |
|        |               |         | 7.7pF | ±0.05pF | GRM1882C1H7R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H7R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H7R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H7R8DA01# |  |
|        |               |         | 7.8pF | ±0.05pF | GRM1882C1H7R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H7R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H7R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H7R9DA01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 50Vdc         | CH      | 7.9pF | ±0.1pF  | GRM1882C1H7R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H7R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H7R9DA01# |  |
|        |               |         | 8.0pF | ±0.05pF | GRM1882C1H8R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H8R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H8R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H8R0DA01# |  |
|        |               |         | 8.1pF | ±0.05pF | GRM1882C1H8R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H8R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H8R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H8R1DA01# |  |
|        |               |         | 8.2pF | ±0.05pF | GRM1882C1H8R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H8R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H8R2CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H8R2DA01# |  |
|        |               |         | 8.3pF | ±0.05pF | GRM1882C1H8R3WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H8R3BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H8R3CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H8R3DA01# |  |
|        |               |         | 8.4pF | ±0.05pF | GRM1882C1H8R4WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H8R4BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H8R4CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H8R4DA01# |  |
|        |               |         | 8.5pF | ±0.05pF | GRM1882C1H8R5WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H8R5BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H8R5CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H8R5DA01# |  |
|        |               |         | 8.6pF | ±0.05pF | GRM1882C1H8R6WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H8R6BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H8R6CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H8R6DA01# |  |
|        |               |         | 8.7pF | ±0.05pF | GRM1882C1H8R7WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H8R7BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H8R7CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H8R7DA01# |  |
|        |               |         | 8.8pF | ±0.05pF | GRM1882C1H8R8WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H8R8BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H8R8CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H8R8DA01# |  |
|        |               |         | 8.9pF | ±0.05pF | GRM1882C1H8R9WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H8R9BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H8R9CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H8R9DA01# |  |
|        |               |         | 9.0pF | ±0.05pF | GRM1882C1H9R0WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H9R0BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H9R0CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H9R0DA01# |  |
|        |               |         | 9.1pF | ±0.05pF | GRM1882C1H9R1WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H9R1BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H9R1CA01# |  |
|        |               |         |       | ±0.5pF  | GRM1882C1H9R1DA01# |  |
|        |               |         | 9.2pF | ±0.05pF | GRM1882C1H9R2WA01# |  |
|        |               |         |       | ±0.1pF  | GRM1882C1H9R2BA01# |  |
|        |               |         |       | ±0.25pF | GRM1882C1H9R2CA01# |  |

Part number # indicates the package specification code.

# GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.9mm  | 50Vdc         | CH      | 9.2pF  | ±0.5pF  | GRM1882C1H9R2DA01# |  |
|        |               |         |        | ±0.05pF | GRM1882C1H9R3WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1882C1H9R3BA01# |  |
|        |               |         |        | ±0.25pF | GRM1882C1H9R3CA01# |  |
|        |               |         |        | ±0.5pF  | GRM1882C1H9R3DA01# |  |
|        |               |         | 9.4pF  | ±0.05pF | GRM1882C1H9R4WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1882C1H9R4BA01# |  |
|        |               |         |        | ±0.25pF | GRM1882C1H9R4CA01# |  |
|        |               |         |        | ±0.5pF  | GRM1882C1H9R4DA01# |  |
|        |               |         | 9.5pF  | ±0.05pF | GRM1882C1H9R5WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1882C1H9R5BA01# |  |
|        |               |         |        | ±0.25pF | GRM1882C1H9R5CA01# |  |
|        |               |         |        | ±0.5pF  | GRM1882C1H9R5DA01# |  |
|        |               |         | 9.6pF  | ±0.05pF | GRM1882C1H9R6WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1882C1H9R6BA01# |  |
|        |               |         |        | ±0.25pF | GRM1882C1H9R6CA01# |  |
|        |               |         |        | ±0.5pF  | GRM1882C1H9R6DA01# |  |
|        |               |         | 9.7pF  | ±0.05pF | GRM1882C1H9R7WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1882C1H9R7BA01# |  |
|        |               |         |        | ±0.25pF | GRM1882C1H9R7CA01# |  |
|        |               |         |        | ±0.5pF  | GRM1882C1H9R7DA01# |  |
|        |               |         | 9.8pF  | ±0.05pF | GRM1882C1H9R8WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1882C1H9R8BA01# |  |
|        |               |         |        | ±0.25pF | GRM1882C1H9R8CA01# |  |
|        |               |         |        | ±0.5pF  | GRM1882C1H9R8DA01# |  |
|        |               |         | 9.9pF  | ±0.05pF | GRM1882C1H9R9WA01# |  |
|        |               |         |        | ±0.1pF  | GRM1882C1H9R9BA01# |  |
|        |               |         |        | ±0.25pF | GRM1882C1H9R9CA01# |  |
|        |               |         |        | ±0.5pF  | GRM1882C1H9R9DA01# |  |
|        |               |         | 10pF   | ±5%     | GRM1882C1H100JA01# |  |
|        |               |         |        | ±5%     | GRM1882C1H120JA01# |  |
|        |               |         | 15pF   | ±5%     | GRM1882C1H150JA01# |  |
|        |               |         | 18pF   | ±5%     | GRM1882C1H180JA01# |  |
|        |               |         | 22pF   | ±5%     | GRM1882C1H220JA01# |  |
|        |               |         | 27pF   | ±5%     | GRM1882C1H270JA01# |  |
|        |               |         | 33pF   | ±5%     | GRM1882C1H330JA01# |  |
|        |               |         | 39pF   | ±5%     | GRM1882C1H390JA01# |  |
|        |               |         | 47pF   | ±5%     | GRM1882C1H470JA01# |  |
|        |               |         | 56pF   | ±5%     | GRM1882C1H560JA01# |  |
|        |               |         | 68pF   | ±5%     | GRM1882C1H680JA01# |  |
|        |               |         | 82pF   | ±5%     | GRM1882C1H820JA01# |  |
|        |               |         | 100pF  | ±5%     | GRM1882C1H101JA01# |  |
|        |               |         | 120pF  | ±5%     | GRM1882C1H121JA01# |  |
|        |               |         | 150pF  | ±5%     | GRM1882C1H151JA01# |  |
|        |               |         | 180pF  | ±5%     | GRM1882C1H181JA01# |  |
|        |               |         | 220pF  | ±5%     | GRM1882C1H221JA01# |  |
|        |               |         | 270pF  | ±5%     | GRM1882C1H271JA01# |  |
|        |               |         | 330pF  | ±5%     | GRM1882C1H331JA01# |  |
|        |               |         | 390pF  | ±5%     | GRM1882C1H391JA01# |  |
|        |               |         | 470pF  | ±5%     | GRM1882C1H471JA01# |  |
|        |               |         | 560pF  | ±5%     | GRM1882C1H561JA01# |  |
|        |               |         | 680pF  | ±5%     | GRM1882C1H681JA01# |  |
|        |               |         | 820pF  | ±5%     | GRM1882C1H821JA01# |  |
|        |               |         | 1000pF | ±5%     | GRM1882C1H102JA01# |  |

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.9mm  | 50Vdc         | CH      | 1200pF  | ±5%  | GRM1882C1H122JA01# |  |
|        |               |         |         | ±5%  | GRM1882C1H152JA01# |  |
|        |               |         |         | ±5%  | GRM1882C1H182JA01# |  |
|        |               |         |         | ±5%  | GRM1882C1H222JA01# |  |
|        |               |         |         | ±5%  | GRM1882C1H272JA01# |  |
|        |               |         | 3300pF  | ±5%  | GRM1882C1H332JA01# |  |
|        |               |         | 3900pF  | ±5%  | GRM1882C1H392JA01# |  |
|        |               |         | 4700pF  | ±5%  | GRM1882C1H472JA01# |  |
|        |               |         | 5600pF  | ±5%  | GRM1882C1H562JA01# |  |
|        |               |         | 6800pF  | ±5%  | GRM1882C1H682JA01# |  |
|        |               |         | 8200pF  | ±5%  | GRM1882C1H822JA01# |  |
|        |               |         | 10000pF | ±5%  | GRM1882C1H103JA01# |  |
|        |               | SL      | 1200pF  | ±5%  | GRM1881X1H122JA01# |  |
|        |               |         |         | ±5%  | GRM1881X1H152JA01# |  |
|        |               |         |         | ±5%  | GRM1881X1H182JA01# |  |
|        |               |         |         | ±5%  | GRM1881X1H222JA01# |  |
|        |               |         |         | ±5%  | GRM1881X1H272JA01# |  |
|        |               |         | 3300pF  | ±5%  | GRM1881X1H332JA01# |  |
|        |               |         | 3900pF  | ±5%  | GRM1881X1H392JA01# |  |
|        |               |         | 4700pF  | ±5%  | GRM1881X1H472JA01# |  |
|        |               |         | 5600pF  | ±5%  | GRM1881X1H562JA01# |  |
|        |               |         | 6800pF  | ±5%  | GRM1881X1H682JA01# |  |
|        |               |         | 8200pF  | ±5%  | GRM1881X1H822JA01# |  |
|        |               |         | 10000pF | ±5%  | GRM1881X1H103JA01# |  |
|        |               | U2J     | 1200pF  | ±5%  | GRM1887U1H122JA01# |  |
|        |               |         |         | ±5%  | GRM1887U1H152JA01# |  |
|        |               |         |         | ±5%  | GRM1887U1H182JA01# |  |
|        |               |         |         | ±5%  | GRM1887U1H222JA01# |  |
|        |               |         |         | ±5%  | GRM1887U1H272JA01# |  |
|        |               |         | 3300pF  | ±5%  | GRM1887U1H332JA01# |  |
|        |               |         | 3900pF  | ±5%  | GRM1887U1H392JA01# |  |
|        |               |         | 4700pF  | ±5%  | GRM1887U1H472JA01# |  |
|        |               |         | 5600pF  | ±5%  | GRM1887U1H562JA01# |  |
|        |               |         | 6800pF  | ±5%  | GRM1887U1H682JA01# |  |
|        |               |         | 8200pF  | ±5%  | GRM1887U1H822JA01# |  |
|        |               |         | 10000pF | ±5%  | GRM1887U1H103JA01# |  |
|        |               | UJ      | 1000pF  | ±5%  | GRM1883U1H102JA01# |  |
|        |               |         |         | ±5%  | GRM1883U1H122JA01# |  |
|        |               |         |         | ±5%  | GRM1883U1H152JA01# |  |
|        |               |         |         | ±5%  | GRM1883U1H182JA01# |  |
|        |               |         |         | ±5%  | GRM1883U1H222JA01# |  |
|        |               |         | 2700pF  | ±5%  | GRM1883U1H272JA01# |  |
|        |               |         | 3300pF  | ±5%  | GRM1883U1H332JA01# |  |
|        |               |         | 3900pF  | ±5%  | GRM1883U1H392JA01# |  |
|        |               |         | 4700pF  | ±5%  | GRM1883U1H472JA01# |  |
|        |               |         | 5600pF  | ±5%  | GRM1883U1H562JA01# |  |
|        |               |         | 6800pF  | ±5%  | GRM1883U1H682JA01# |  |
|        |               |         | 8200pF  | ±5%  | GRM1883U1H822JA01# |  |
|        |               |         | 10000pF | ±5%  | GRM1883U1H103JA01# |  |
|        | 10Vdc         | SL      | 12000pF | ±5%  | GRM1881X1A123JA01# |  |
|        |               |         |         | ±5%  | GRM1881X1A153JA01# |  |
|        |               |         |         | ±5%  | GRM1881X1A183JA01# |  |
|        |               |         |         | ±5%  | GRM1881X1A223JA01# |  |
|        |               |         |         | ±5%  | GRM1881X1A273JA01# |  |
|        |               | U2J     | 12000pF | ±5%  | GRM1887U1A123JA01# |  |
|        |               |         |         | ±5%  | GRM1887U1A153JA01# |  |
|        |               |         |         | ±5%  | GRM1887U1A183JA01# |  |
|        |               |         |         | ±5%  | GRM1887U1A223JA01# |  |
|        |               |         |         | ±5%  | GRM1887U1A273JA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.9mm  | 10Vdc         | U2J     | 15000pF | ±5%  | GRM1887U1A153JA01# |  |
|        |               |         | 18000pF | ±5%  | GRM1887U1A183JA01# |  |
|        |               |         | 22000pF | ±5%  | GRM1887U1A223JA01# |  |
|        |               | UJ      | 12000pF | ±5%  | GRM1883U1A123JA01# |  |
|        |               |         | 15000pF | ±5%  | GRM1883U1A153JA01# |  |
|        |               |         | 18000pF | ±5%  | GRM1883U1A183JA01# |  |
|        |               |         | 22000pF | ±5%  | GRM1883U1A223JA01# |  |
|        |               |         |         |      |                    |  |
|        |               |         |         |      |                    |  |

■ 2.0×1.25mm

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |  |
|--------|---------------|---------|--------|------|--------------------|--|
| 0.7mm  | 100Vdc        | C0G     | 100pF  | ±5%  | GRM2165C2A101JA01# |  |
|        |               |         | 120pF  | ±5%  | GRM2165C2A121JA01# |  |
|        |               |         | 150pF  | ±5%  | GRM2165C2A151JA01# |  |
|        |               |         | 180pF  | ±5%  | GRM2165C2A181JA01# |  |
|        |               |         | 220pF  | ±5%  | GRM2165C2A221JA01# |  |
|        |               |         | 270pF  | ±5%  | GRM2165C2A271JA01# |  |
|        |               |         | 330pF  | ±5%  | GRM2165C2A331JA01# |  |
|        |               |         | 390pF  | ±5%  | GRM2165C2A391JA01# |  |
|        |               |         | 470pF  | ±5%  | GRM2165C2A471JA01# |  |
|        |               |         | 560pF  | ±5%  | GRM2165C2A561JA01# |  |
|        |               |         | 680pF  | ±5%  | GRM2165C2A681JA01# |  |
|        |               |         | 820pF  | ±5%  | GRM2165C2A821JA01# |  |
|        |               |         | 1000pF | ±5%  | GRM2165C2A102JA01# |  |
|        |               |         | 1200pF | ±5%  | GRM2165C2A122JA01# |  |
|        |               |         | 1500pF | ±5%  | GRM2165C2A152JA01# |  |
|        |               |         | 1800pF | ±5%  | GRM2165C2A182JA01# |  |
|        |               |         | 2200pF | ±5%  | GRM2165C2A222JA01# |  |
|        |               |         | 2700pF | ±5%  | GRM2165C2A272JA01# |  |
|        |               |         | 3300pF | ±5%  | GRM2165C2A332JA01# |  |
|        |               | CH      | 100pF  | ±5%  | GRM2162C2A101JA01# |  |
|        |               |         | 120pF  | ±5%  | GRM2162C2A121JA01# |  |
|        |               |         | 150pF  | ±5%  | GRM2162C2A151JA01# |  |
|        |               |         | 180pF  | ±5%  | GRM2162C2A181JA01# |  |
|        |               |         | 220pF  | ±5%  | GRM2162C2A221JA01# |  |
|        |               |         | 270pF  | ±5%  | GRM2162C2A271JA01# |  |
|        |               |         | 330pF  | ±5%  | GRM2162C2A331JA01# |  |
|        |               |         | 390pF  | ±5%  | GRM2162C2A391JA01# |  |
|        |               |         | 470pF  | ±5%  | GRM2162C2A471JA01# |  |
|        |               |         | 560pF  | ±5%  | GRM2162C2A561JA01# |  |
|        |               |         | 680pF  | ±5%  | GRM2162C2A681JA01# |  |
|        |               |         | 820pF  | ±5%  | GRM2162C2A821JA01# |  |
|        |               |         | 1000pF | ±5%  | GRM2162C2A102JA01# |  |
|        |               |         | 1200pF | ±5%  | GRM2162C2A122JA01# |  |
|        |               |         | 1500pF | ±5%  | GRM2162C2A152JA01# |  |
|        |               |         | 1800pF | ±5%  | GRM2162C2A182JA01# |  |
|        |               |         | 2200pF | ±5%  | GRM2162C2A222JA01# |  |
|        |               |         | 2700pF | ±5%  | GRM2162C2A272JA01# |  |
|        |               |         | 3300pF | ±5%  | GRM2162C2A332JA01# |  |
|        | 50Vdc         | C0G     | 1200pF | ±5%  | GRM2165C1H122JA01# |  |
|        |               |         | 1500pF | ±5%  | GRM2165C1H152JA01# |  |
|        |               |         | 1800pF | ±5%  | GRM2165C1H182JA01# |  |
|        |               |         | 2200pF | ±5%  | GRM2165C1H222JA01# |  |
|        |               |         |        |      |                    |  |
|        |               |         |        |      |                    |  |
|        |               |         |        |      |                    |  |
|        |               |         |        |      |                    |  |
|        |               |         |        |      |                    |  |
|        |               |         |        |      |                    |  |
|        |               |         |        |      |                    |  |
|        |               |         |        |      |                    |  |

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.7mm  | 50Vdc         | C0G     | 2700pF  | ±5%  | GRM2165C1H272JA01# |  |
|        |               |         | 3300pF  | ±5%  | GRM2165C1H332JA01# |  |
|        |               |         | 3900pF  | ±5%  | GRM2165C1H392JA01# |  |
|        |               |         | 4700pF  | ±5%  | GRM2165C1H472JA01# |  |
|        |               | CH      | 1200pF  | ±5%  | GRM2162C1H122JA01# |  |
|        |               |         | 1500pF  | ±5%  | GRM2162C1H152JA01# |  |
|        |               |         | 1800pF  | ±5%  | GRM2162C1H182JA01# |  |
|        |               |         | 2200pF  | ±5%  | GRM2162C1H222JA01# |  |
|        |               |         | 2700pF  | ±5%  | GRM2162C1H272JA01# |  |
|        |               |         | 3300pF  | ±5%  | GRM2162C1H332JA01# |  |
|        |               |         | 3900pF  | ±5%  | GRM2162C1H392JA01# |  |
|        |               |         | 4700pF  | ±5%  | GRM2162C1H472JA01# |  |
|        |               | SL      | 12000pF | ±5%  | GRM2161X1H123JA01# |  |
|        |               |         | 15000pF | ±5%  | GRM2161X1H153JA01# |  |
|        |               |         | 18000pF | ±5%  | GRM2161X1H183JA01# |  |
|        |               |         |         |      |                    |  |
|        |               | U2J     | 12000pF | ±5%  | GRM2167U1H123JA01# |  |
|        |               |         | 15000pF | ±5%  | GRM2167U1H153JA01# |  |
|        |               |         | 18000pF | ±5%  | GRM2167U1H183JA01# |  |
|        |               | UJ      | 10000pF | ±5%  | GRM2163U1H103JA01# |  |
|        |               |         | 12000pF | ±5%  | GRM2163U1H123JA01# |  |
|        |               |         | 15000pF | ±5%  | GRM2163U1H153JA01# |  |
|        |               |         | 18000pF | ±5%  | GRM2163U1H183JA01# |  |
| 0.95mm | 50Vdc         | C0G     | 5600pF  | ±5%  | GRM2195C1H562JA01# |  |
|        |               |         | 6800pF  | ±5%  | GRM2195C1H682JA01# |  |
|        |               |         | 8200pF  | ±5%  | GRM2195C1H822JA01# |  |
|        |               |         | 10000pF | ±5%  | GRM2195C1H103JA01# |  |
|        |               |         | 12000pF | ±5%  | GRM2195C1H123JA01# |  |
|        |               |         | 15000pF | ±5%  | GRM2195C1H153JA01# |  |
|        |               | CH      | 5600pF  | ±5%  | GRM2192C1H562JA01# |  |
|        |               |         | 6800pF  | ±5%  | GRM2192C1H682JA01# |  |
|        |               |         | 8200pF  | ±5%  | GRM2192C1H822JA01# |  |
|        |               |         | 10000pF | ±5%  | GRM2192C1H103JA01# |  |
|        |               |         | 12000pF | ±5%  | GRM2192C1H123JA01# |  |
|        |               |         | 15000pF | ±5%  | GRM2192C1H153JA01# |  |
|        |               | SL      | 22000pF | ±5%  | GRM2191X1H223JA01# |  |
|        |               |         | 27000pF | ±5%  | GRM2191X1H273JA01# |  |
|        |               | U2J     | 22000pF | ±5%  | GRM2197U1H223JA01# |  |
|        |               |         | 27000pF | ±5%  | GRM2197U1H273JA01# |  |
|        |               | UJ      | 22000pF | ±5%  | GRM2193U1H223JA01# |  |
|        |               |         | 27000pF | ±5%  | GRM2193U1H273JA01# |  |
|        | 10Vdc         | SL      | 56000pF | ±5%  | GRM2191X1A563JA01# |  |
|        |               |         |         |      |                    |  |
|        |               |         |         |      |                    |  |
|        |               |         |         |      |                    |  |
|        |               |         |         |      |                    |  |
|        |               |         |         |      |                    |  |
|        |               |         |         |      |                    |  |
|        |               |         |         |      |                    |  |
|        |               |         |         |      |                    |  |
|        |               |         |         |      |                    |  |
|        |               |         |         |      |                    |  |
| 1.0mm  | 250Vdc        | C0G     | 10pF    | ±5%  | GRM21A5C2E100JW01# |  |
|        |               |         | 12pF    | ±5%  | GRM21A5C2E120JW01# |  |
|        |               |         | 15pF    | ±5%  | GRM21A5C2E150JW01# |  |
|        |               |         | 18pF    | ±5%  | GRM21A5C2E180JW01# |  |
|        |               |         | 22pF    | ±5%  | GRM21A5C2E220JW01# |  |
|        |               |         | 27pF    | ±5%  | GRM21A5C2E270JW01# |  |
|        |               |         | 33pF    | ±5%  | GRM21A5C2E330JW01# |  |
|        |               |         | 39pF    | ±5%  | GRM21A5C2E390JW01# |  |
|        |               |         | 47pF    | ±5%  | GRM21A5C2E470JW01# |  |
|        |               |         | 56pF    | ±5%  | GRM21A5C2E560JW01# |  |
|        |               |         | 68pF    | ±5%  | GRM21A5C2E680JW01# |  |
|        |               |         |         |      |                    |  |
|        |               |         |         |      |                    |  |
|        |               |         |         |      |                    |  |
|        |               |         |         |      |                    |  |

Part number # indicates the package specification code.



## GRM Series Temperature Compensating Type Part Number List

(→ ■ 2.0×1.25mm)

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |  |
|--------|---------------|---------|--------|------|--------------------|--|
| 1.0mm  | 250Vdc        | C0G     | 82pF   | ±5%  | GRM21A5C2E820JW01# |  |
|        |               |         | 100pF  | ±5%  | GRM21A5C2E101JW01# |  |
|        |               |         | 120pF  | ±5%  | GRM21A5C2E121JW01# |  |
|        |               |         | 150pF  | ±5%  | GRM21A5C2E151JW01# |  |
|        |               |         | 180pF  | ±5%  | GRM21A5C2E181JW01# |  |
|        |               |         | 220pF  | ±5%  | GRM21A5C2E221JW01# |  |
|        |               |         | 270pF  | ±5%  | GRM21A5C2E271JW01# |  |
|        |               |         | 330pF  | ±5%  | GRM21A5C2E331JW01# |  |
|        |               | U2J     | 100pF  | ±5%  | GRM21A7U2E101JW31# |  |
|        |               |         | 120pF  | ±5%  | GRM21A7U2E121JW31# |  |
|        |               |         | 150pF  | ±5%  | GRM21A7U2E151JW31# |  |
|        |               |         | 180pF  | ±5%  | GRM21A7U2E181JW31# |  |
|        |               |         | 220pF  | ±5%  | GRM21A7U2E221JW31# |  |
|        |               |         | 270pF  | ±5%  | GRM21A7U2E271JW31# |  |
|        |               |         | 330pF  | ±5%  | GRM21A7U2E331JW31# |  |
|        |               |         | 390pF  | ±5%  | GRM21A7U2E391JW31# |  |
|        |               |         | 470pF  | ±5%  | GRM21A7U2E471JW31# |  |
|        |               |         | 560pF  | ±5%  | GRM21A7U2E561JW31# |  |
|        |               |         | 680pF  | ±5%  | GRM21A7U2E681JW31# |  |
|        |               |         | 820pF  | ±5%  | GRM21A7U2E821JW31# |  |
|        |               |         | 1000pF | ±5%  | GRM21A7U2E102JW31# |  |
|        |               |         | 1200pF | ±5%  | GRM21A7U2E122JW31# |  |
|        |               |         | 1500pF | ±5%  | GRM21A7U2E152JW31# |  |
|        |               |         | 1800pF | ±5%  | GRM21A7U2E182JW31# |  |
|        |               |         | 2200pF | ±5%  | GRM21A7U2E222JW31# |  |
|        | 200Vdc        | C0G     | 10pF   | ±5%  | GRM21A5C2D100JW01# |  |
|        |               |         | 12pF   | ±5%  | GRM21A5C2D120JW01# |  |
|        |               |         | 15pF   | ±5%  | GRM21A5C2D150JW01# |  |
|        |               |         | 18pF   | ±5%  | GRM21A5C2D180JW01# |  |
|        |               |         | 22pF   | ±5%  | GRM21A5C2D220JW01# |  |
|        |               |         | 27pF   | ±5%  | GRM21A5C2D270JW01# |  |
|        |               |         | 33pF   | ±5%  | GRM21A5C2D330JW01# |  |
|        |               |         | 39pF   | ±5%  | GRM21A5C2D390JW01# |  |
|        |               |         | 47pF   | ±5%  | GRM21A5C2D470JW01# |  |
|        |               |         | 56pF   | ±5%  | GRM21A5C2D560JW01# |  |
|        |               |         | 68pF   | ±5%  | GRM21A5C2D680JW01# |  |
|        |               |         | 82pF   | ±5%  | GRM21A5C2D820JW01# |  |
|        |               |         | 100pF  | ±5%  | GRM21A5C2D101JW01# |  |
|        |               |         | 120pF  | ±5%  | GRM21A5C2D121JW01# |  |
|        |               |         | 150pF  | ±5%  | GRM21A5C2D151JW01# |  |
|        |               |         | 180pF  | ±5%  | GRM21A5C2D181JW01# |  |
|        |               |         | 220pF  | ±5%  | GRM21A5C2D221JW01# |  |
|        |               |         | 270pF  | ±5%  | GRM21A5C2D271JW01# |  |
|        |               |         | 330pF  | ±5%  | GRM21A5C2D331JW01# |  |
|        |               | U2J     | 100pF  | ±5%  | GRM21A7U2D101JW31# |  |
|        |               |         | 120pF  | ±5%  | GRM21A7U2D121JW31# |  |
|        |               |         | 150pF  | ±5%  | GRM21A7U2D151JW31# |  |
|        |               |         | 180pF  | ±5%  | GRM21A7U2D181JW31# |  |
|        |               |         | 220pF  | ±5%  | GRM21A7U2D221JW31# |  |
|        |               |         | 270pF  | ±5%  | GRM21A7U2D271JW31# |  |
|        |               |         | 330pF  | ±5%  | GRM21A7U2D331JW31# |  |
|        |               |         | 390pF  | ±5%  | GRM21A7U2D391JW31# |  |
|        |               |         | 470pF  | ±5%  | GRM21A7U2D471JW31# |  |
|        |               |         | 560pF  | ±5%  | GRM21A7U2D561JW31# |  |

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 1.0mm  | 200Vdc        | U2J     | 680pF   | ±5%  | GRM21A7U2D681JW31# |  |
|        |               |         | 820pF   | ±5%  | GRM21A7U2D821JW31# |  |
|        |               |         | 1000pF  | ±5%  | GRM21A7U2D102JW31# |  |
|        |               |         | 1200pF  | ±5%  | GRM21A7U2D122JW31# |  |
|        |               |         | 1500pF  | ±5%  | GRM21A7U2D152JW31# |  |
|        |               |         | 1800pF  | ±5%  | GRM21A7U2D182JW31# |  |
|        |               |         | 2200pF  | ±5%  | GRM21A7U2D222JW31# |  |
|        | 50Vdc         | SL      | 33000pF | ±5%  | GRM21A1X1H333JA39# |  |
|        |               | U2J     | 33000pF | ±5%  | GRM21A7U1H333JA39# |  |
|        |               | UJ      | 33000pF | ±5%  | GRM21A3U1H333JA39# |  |
| 1.35mm | 50Vdc         | C0G     | 18000pF | ±5%  | GRM21B5C1H183JA01# |  |
|        |               |         | 22000pF | ±5%  | GRM21B5C1H223JA01# |  |
|        |               | CH      | 18000pF | ±5%  | GRM21B2C1H183JA01# |  |
|        |               |         | 22000pF | ±5%  | GRM21B2C1H223JA01# |  |
|        |               | SL      | 39000pF | ±5%  | GRM21B1X1H393JA01# |  |
|        |               |         | 47000pF | ±5%  | GRM21B1X1H473JA01# |  |
|        |               | U2J     | 39000pF | ±5%  | GRM21B7U1H393JA01# |  |
|        |               |         | 47000pF | ±5%  | GRM21B7U1H473JA01# |  |
|        |               | UJ      | 39000pF | ±5%  | GRM21B3U1H393JA01# |  |
|        |               |         | 47000pF | ±5%  | GRM21B3U1H473JA01# |  |
|        | 10Vdc         | SL      | 68000pF | ±5%  | GRM21B1X1A683JA01# |  |
|        |               |         | 82000pF | ±5%  | GRM21B1X1A823JA01# |  |
|        |               |         | 0.10μF  | ±5%  | GRM21B1X1A104JA01# |  |
|        |               | U2J     | 68000pF | ±5%  | GRM21B7U1A683JA01# |  |
|        |               |         | 82000pF | ±5%  | GRM21B7U1A823JA01# |  |
|        |               |         | 0.10μF  | ±5%  | GRM21B7U1A104JA01# |  |
|        |               | UJ      | 68000pF | ±5%  | GRM21B3U1A683JA01# |  |
|        |               |         | 82000pF | ±5%  | GRM21B3U1A823JA01# |  |
|        |               |         | 0.10μF  | ±5%  | GRM21B3U1A104JA01# |  |
| 1.45mm | 250Vdc        | U2J     | 2700pF  | ±5%  | GRM21B7U2E272JW32# |  |
|        |               |         | 3300pF  | ±5%  | GRM21B7U2E332JW32# |  |
|        |               |         | 3900pF  | ±5%  | GRM21B7U2E392JW32# |  |
|        |               |         | 4700pF  | ±5%  | GRM21B7U2E472JW32# |  |
|        |               |         | 5600pF  | ±5%  | GRM21B7U2E562JW32# |  |
|        | 200Vdc        | U2J     | 2700pF  | ±5%  | GRM21B7U2D272JW32# |  |
|        |               |         | 3300pF  | ±5%  | GRM21B7U2D332JW32# |  |
|        |               |         | 3900pF  | ±5%  | GRM21B7U2D392JW32# |  |
|        |               |         | 4700pF  | ±5%  | GRM21B7U2D472JW32# |  |
|        |               |         | 5600pF  | ±5%  | GRM21B7U2D562JW32# |  |
|        |               | UJ      | 2700pF  | ±5%  | GRM21B3U2D272JW32# |  |
|        |               |         | 3300pF  | ±5%  | GRM21B3U2D332JW32# |  |
|        |               |         | 3900pF  | ±5%  | GRM21B3U2D392JW32# |  |
|        |               |         | 4700pF  | ±5%  | GRM21B3U2D472JW32# |  |
|        |               |         | 5600pF  | ±5%  | GRM21B3U2D562JW32# |  |

■ 3.2×1.6mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.95mm | 100Vdc        | C0G     | 1800pF  | ±5%  | GRM3195C2A182JA01# |  |
|        |               |         | 2200pF  | ±5%  | GRM3195C2A222JA01# |  |
|        |               |         | 2700pF  | ±5%  | GRM3195C2A272JA01# |  |
|        |               |         | 3300pF  | ±5%  | GRM3195C2A332JA01# |  |
|        |               |         | 3900pF  | ±5%  | GRM3195C2A392JA01# |  |
|        |               |         | 4700pF  | ±5%  | GRM3195C2A472JA01# |  |
|        |               |         | 5600pF  | ±5%  | GRM3195C2A562JA01# |  |
|        |               |         | 6800pF  | ±5%  | GRM3195C2A682JA01# |  |
|        |               |         | 8200pF  | ±5%  | GRM3195C2A822JA01# |  |
|        |               |         | 10000pF | ±5%  | GRM3195C2A103JA01# |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 3.2×1.6mm)

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.95mm | 100Vdc        | C0G     | 12000pF | ±5%  | GRM3195C2A123JA01# |  |
|        |               |         | 15000pF | ±5%  | GRM3195C2A153JA01# |  |
|        |               |         | 18000pF | ±5%  | GRM3195C2A183JA01# |  |
|        |               |         | 22000pF | ±5%  | GRM3195C2A223JA01# |  |
|        |               | CH      | 1800pF  | ±5%  | GRM3192C2A182JA01# |  |
|        |               |         | 2200pF  | ±5%  | GRM3192C2A222JA01# |  |
|        |               |         | 2700pF  | ±5%  | GRM3192C2A272JA01# |  |
|        |               |         | 3300pF  | ±5%  | GRM3192C2A332JA01# |  |
|        |               |         | 3900pF  | ±5%  | GRM3192C2A392JA01# |  |
|        |               |         | 4700pF  | ±5%  | GRM3192C2A472JA01# |  |
|        |               |         | 5600pF  | ±5%  | GRM3192C2A562JA01# |  |
|        |               |         | 6800pF  | ±5%  | GRM3192C2A682JA01# |  |
|        |               |         | 8200pF  | ±5%  | GRM3192C2A822JA01# |  |
|        |               |         | 10000pF | ±5%  | GRM3192C2A103JA01# |  |
|        |               |         | 12000pF | ±5%  | GRM3192C2A123JA01# |  |
|        |               |         | 15000pF | ±5%  | GRM3192C2A153JA01# |  |
|        |               |         | 18000pF | ±5%  | GRM3192C2A183JA01# |  |
|        |               |         | 22000pF | ±5%  | GRM3192C2A223JA01# |  |
|        | 50Vdc         | C0G     | 12000pF | ±5%  | GRM3195C1H123JA01# |  |
|        |               |         | 15000pF | ±5%  | GRM3195C1H153JA01# |  |
|        |               |         | 18000pF | ±5%  | GRM3195C1H183JA01# |  |
|        |               |         | 22000pF | ±5%  | GRM3195C1H223JA01# |  |
|        |               |         | 27000pF | ±5%  | GRM3195C1H273JA01# |  |
|        |               |         | 33000pF | ±5%  | GRM3195C1H333JA01# |  |
|        |               |         | 39000pF | ±5%  | GRM3195C1H393JA01# |  |
|        |               | CH      | 12000pF | ±5%  | GRM3192C1H123JA01# |  |
|        |               |         | 15000pF | ±5%  | GRM3192C1H153JA01# |  |
|        |               |         | 18000pF | ±5%  | GRM3192C1H183JA01# |  |
|        |               |         | 22000pF | ±5%  | GRM3192C1H223JA01# |  |
|        |               |         | 27000pF | ±5%  | GRM3192C1H273JA01# |  |
|        |               |         | 33000pF | ±5%  | GRM3192C1H333JA01# |  |
|        |               |         | 39000pF | ±5%  | GRM3192C1H393JA01# |  |
|        |               | SL      | 56000pF | ±5%  | GRM3191X1H563JA01# |  |
|        |               | U2J     | 56000pF | ±5%  | GRM3197U1H563JA01# |  |
|        |               | UJ      | 56000pF | ±5%  | GRM3193U1H563JA01# |  |
| 1.0mm  | 2000Vdc       | U2J     | 10pF    | ±5%  | GRM31A7U3D100JW31# |  |
|        |               |         | 12pF    | ±5%  | GRM31A7U3D120JW31# |  |
|        |               |         | 15pF    | ±5%  | GRM31A7U3D150JW31# |  |
|        |               |         | 18pF    | ±5%  | GRM31A7U3D180JW31# |  |
|        |               |         | 22pF    | ±5%  | GRM31A7U3D220JW31# |  |
|        |               |         | 27pF    | ±5%  | GRM31A7U3D270JW31# |  |
|        |               |         | 33pF    | ±5%  | GRM31A7U3D330JW31# |  |
|        |               |         | 39pF    | ±5%  | GRM31A7U3D390JW31# |  |
|        |               |         | 47pF    | ±5%  | GRM31A7U3D470JW31# |  |
|        |               |         | 56pF    | ±5%  | GRM31A7U3D560JW31# |  |
|        |               |         | 68pF    | ±5%  | GRM31A7U3D680JW31# |  |
|        | 1000Vdc       | C0G     | 10pF    | ±5%  | GRM31A5C3A100JW01# |  |
|        |               |         | 12pF    | ±5%  | GRM31A5C3A120JW01# |  |
|        |               |         | 15pF    | ±5%  | GRM31A5C3A150JW01# |  |
|        |               |         | 18pF    | ±5%  | GRM31A5C3A180JW01# |  |
|        |               |         | 22pF    | ±5%  | GRM31A5C3A220JW01# |  |
|        |               |         | 27pF    | ±5%  | GRM31A5C3A270JW01# |  |
|        |               |         | 33pF    | ±5%  | GRM31A5C3A330JW01# |  |
|        |               |         | 39pF    | ±5%  | GRM31A5C3A390JW01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol. | Part Number        |  |
|--------|---------------|---------|-------|------|--------------------|--|
| 1.0mm  | 1000Vdc       | C0G     | 47pF  | ±5%  | GRM31A5C3A470JW01# |  |
|        |               |         | 56pF  | ±5%  | GRM31A5C3A560JW01# |  |
|        |               |         | 68pF  | ±5%  | GRM31A5C3A680JW01# |  |
|        |               |         | 82pF  | ±5%  | GRM31A5C3A820JW01# |  |
|        |               |         | 100pF | ±5%  | GRM31A5C3A101JW01# |  |
|        |               |         | 120pF | ±5%  | GRM31A5C3A121JW01# |  |
|        |               |         | 150pF | ±5%  | GRM31A5C3A151JW01# |  |
|        |               |         | 180pF | ±5%  | GRM31A5C3A181JW01# |  |
|        |               |         | 220pF | ±5%  | GRM31A5C3A221JW01# |  |
|        |               | U2J     | 10pF  | ±5%  | GRM31A7U3A100JW31# |  |
|        |               |         | 12pF  | ±5%  | GRM31A7U3A120JW31# |  |
|        |               |         | 15pF  | ±5%  | GRM31A7U3A150JW31# |  |
|        |               |         | 18pF  | ±5%  | GRM31A7U3A180JW31# |  |
|        |               |         | 22pF  | ±5%  | GRM31A7U3A220JW31# |  |
|        |               |         | 27pF  | ±5%  | GRM31A7U3A270JW31# |  |
|        |               |         | 33pF  | ±5%  | GRM31A7U3A330JW31# |  |
|        |               |         | 39pF  | ±5%  | GRM31A7U3A390JW31# |  |
|        |               |         | 47pF  | ±5%  | GRM31A7U3A470JW31# |  |
|        |               |         | 56pF  | ±5%  | GRM31A7U3A560JW31# |  |
|        | 630Vdc        | C0G     | 68pF  | ±5%  | GRM31A7U3A680JW31# |  |
|        |               |         | 82pF  | ±5%  | GRM31A7U3A820JW31# |  |
|        |               |         | 100pF | ±5%  | GRM31A7U3A101JW31# |  |
|        |               |         | 120pF | ±5%  | GRM31A7U3A121JW31# |  |
|        |               |         | 150pF | ±5%  | GRM31A7U3A151JW31# |  |
|        |               |         | 180pF | ±5%  | GRM31A7U3A181JW31# |  |
|        |               |         | 220pF | ±5%  | GRM31A7U3A221JW31# |  |
|        |               |         | 270pF | ±5%  | GRM31A7U3A271JW31# |  |
|        |               |         | 330pF | ±5%  | GRM31A7U3A331JW31# |  |
|        |               | U2J     | 10pF  | ±5%  | GRM31A5C2J100JW01# |  |
|        |               |         | 12pF  | ±5%  | GRM31A5C2J120JW01# |  |
|        |               |         | 15pF  | ±5%  | GRM31A5C2J150JW01# |  |
|        |               |         | 18pF  | ±5%  | GRM31A5C2J180JW01# |  |
|        |               |         | 22pF  | ±5%  | GRM31A5C2J220JW01# |  |
|        |               |         | 27pF  | ±5%  | GRM31A5C2J270JW01# |  |
|        |               |         | 33pF  | ±5%  | GRM31A5C2J330JW01# |  |
|        |               |         | 39pF  | ±5%  | GRM31A5C2J390JW01# |  |
|        |               |         | 47pF  | ±5%  | GRM31A5C2J470JW01# |  |
|        |               |         | 56pF  | ±5%  | GRM31A5C2J560JW01# |  |
|        |               |         | 68pF  | ±5%  | GRM31A5C2J680JW01# |  |
|        |               |         | 82pF  | ±5%  | GRM31A5C2J820JW01# |  |
|        |               |         | 100pF | ±5%  | GRM31A5C2J101JW01# |  |
|        |               |         | 120pF | ±5%  | GRM31A5C2J121JW01# |  |
|        |               |         | 150pF | ±5%  | GRM31A5C2J151JW01# |  |
|        |               |         | 180pF | ±5%  | GRM31A5C2J181JW01# |  |
|        |               |         | 220pF | ±5%  | GRM31A5C2J221JW01# |  |
|        |               |         | 270pF | ±5%  | GRM31A5C2J271JW01# |  |
|        |               |         | 330pF | ±5%  | GRM31A5C2J331JW01# |  |
|        |               |         | 390pF | ±5%  | GRM31A5C2J391JW01# |  |
|        |               |         | 470pF | ±5%  | GRM31A5C2J471JW01# |  |
|        |               |         | 560pF | ±5%  | GRM31A5C2J561JW01# |  |
|        |               | U2J     | 10pF  | ±5%  | GRM31A7U2J100JW31# |  |
|        |               |         | 12pF  | ±5%  | GRM31A7U2J120JW31# |  |
|        |               |         | 15pF  | ±5%  | GRM31A7U2J150JW31# |  |
|        |               |         | 18pF  | ±5%  | GRM31A7U2J180JW31# |  |

Part number # indicates the package specification code.



# GRM Series Temperature Compensating Type Part Number List

(→ ■ 3.2×1.6mm)

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |                    |                    |  |
|--------|---------------|---------|--------|------|--------------------|--------------------|--------------------|--|
| 1.0mm  | 630Vdc        | U2J     | 22pF   | ±5%  | GRM31A7U2J220JW31# |                    |                    |  |
|        |               |         | 27pF   | ±5%  | GRM31A7U2J270JW31# |                    |                    |  |
|        |               |         | 33pF   | ±5%  | GRM31A7U2J330JW31# |                    |                    |  |
|        |               |         | 39pF   | ±5%  | GRM31A7U2J390JW31# |                    |                    |  |
|        |               |         | 47pF   | ±5%  | GRM31A7U2J470JW31# |                    |                    |  |
|        |               |         | 56pF   | ±5%  | GRM31A7U2J560JW31# |                    |                    |  |
|        |               |         | 68pF   | ±5%  | GRM31A7U2J680JW31# |                    |                    |  |
|        |               |         | 82pF   | ±5%  | GRM31A7U2J820JW31# |                    |                    |  |
|        |               |         | 100pF  | ±5%  | GRM31A7U2J101JW31# |                    |                    |  |
|        |               |         | 120pF  | ±5%  | GRM31A7U2J121JW31# |                    |                    |  |
|        |               |         | 150pF  | ±5%  | GRM31A7U2J151JW31# |                    |                    |  |
|        |               |         | 180pF  | ±5%  | GRM31A7U2J181JW31# |                    |                    |  |
|        |               |         | 220pF  | ±5%  | GRM31A7U2J221JW31# |                    |                    |  |
|        |               |         | 270pF  | ±5%  | GRM31A7U2J271JW31# |                    |                    |  |
|        |               |         | 330pF  | ±5%  | GRM31A7U2J331JW31# |                    |                    |  |
|        |               |         | 390pF  | ±5%  | GRM31A7U2J391JW31# |                    |                    |  |
|        |               |         | 470pF  | ±5%  | GRM31A7U2J471JW31# |                    |                    |  |
|        |               |         | 560pF  | ±5%  | GRM31A7U2J561JW31# |                    |                    |  |
|        |               |         | 680pF  | ±5%  | GRM31A7U2J681JW31# |                    |                    |  |
|        |               |         | 820pF  | ±5%  | GRM31A7U2J821JW31# |                    |                    |  |
|        |               |         | 1000pF | ±5%  | GRM31A7U2J102JW31# |                    |                    |  |
|        |               |         | 1200pF | ±5%  | GRM31A7U2J122JW31# |                    |                    |  |
|        |               |         | 1500pF | ±5%  | GRM31A7U2J152JW31# |                    |                    |  |
|        |               |         | 1800pF | ±5%  | GRM31A7U2J182JW31# |                    |                    |  |
|        |               |         | 2200pF | ±5%  | GRM31A7U2J222JW31# |                    |                    |  |
|        | 500Vdc        | C0G     | 10pF   | ±5%  | GRM31A5C2H100JW01# |                    |                    |  |
|        |               |         | 12pF   | ±5%  | GRM31A5C2H120JW01# |                    |                    |  |
|        |               |         | 15pF   | ±5%  | GRM31A5C2H150JW01# |                    |                    |  |
|        |               |         | 18pF   | ±5%  | GRM31A5C2H180JW01# |                    |                    |  |
|        |               |         | 22pF   | ±5%  | GRM31A5C2H220JW01# |                    |                    |  |
|        |               |         | 27pF   | ±5%  | GRM31A5C2H270JW01# |                    |                    |  |
|        |               |         | 33pF   | ±5%  | GRM31A5C2H330JW01# |                    |                    |  |
|        |               |         | 39pF   | ±5%  | GRM31A5C2H390JW01# |                    |                    |  |
|        |               |         | 47pF   | ±5%  | GRM31A5C2H470JW01# |                    |                    |  |
|        |               |         | 56pF   | ±5%  | GRM31A5C2H560JW01# |                    |                    |  |
|        |               |         | 68pF   | ±5%  | GRM31A5C2H680JW01# |                    |                    |  |
|        |               |         | 82pF   | ±5%  | GRM31A5C2H820JW01# |                    |                    |  |
|        |               |         | 100pF  | ±5%  | GRM31A5C2H101JW01# |                    |                    |  |
|        |               |         | 120pF  | ±5%  | GRM31A5C2H121JW01# |                    |                    |  |
|        |               |         | 150pF  | ±5%  | GRM31A5C2H151JW01# |                    |                    |  |
|        |               |         | 180pF  | ±5%  | GRM31A5C2H181JW01# |                    |                    |  |
|        |               |         | 220pF  | ±5%  | GRM31A5C2H221JW01# |                    |                    |  |
|        |               |         | 270pF  | ±5%  | GRM31A5C2H271JW01# |                    |                    |  |
|        |               |         | 330pF  | ±5%  | GRM31A5C2H331JW01# |                    |                    |  |
|        |               |         | 390pF  | ±5%  | GRM31A5C2H391JW01# |                    |                    |  |
|        |               |         | 470pF  | ±5%  | GRM31A5C2H471JW01# |                    |                    |  |
|        |               |         | 560pF  | ±5%  | GRM31A5C2H561JW01# |                    |                    |  |
|        |               |         | U2J    |      | 10pF               | ±5%                | GRM31A7U2H100JW31# |  |
|        |               |         |        |      | 12pF               | ±5%                | GRM31A7U2H120JW31# |  |
|        |               |         |        |      | 15pF               | ±5%                | GRM31A7U2H150JW31# |  |
|        |               | 18pF    |        |      | ±5%                | GRM31A7U2H180JW31# |                    |  |
|        |               | 22pF    |        |      | ±5%                | GRM31A7U2H220JW31# |                    |  |
|        |               |         |        | 27pF | ±5%                | GRM31A7U2H270JW31# |                    |  |
|        |               |         |        | 33pF | ±5%                | GRM31A7U2H330JW31# |                    |  |
|        |               |         |        |      |                    |                    |                    |  |

| T max. | Rated Voltage | TC Code | Cap.    | Tol.   | Part Number        |                    |  |
|--------|---------------|---------|---------|--------|--------------------|--------------------|--|
| 1.0mm  | 500Vdc        | U2J     | 39pF    | ±5%    | GRM31A7U2H390JW31# |                    |  |
|        |               |         | 47pF    | ±5%    | GRM31A7U2H470JW31# |                    |  |
|        |               |         | 56pF    | ±5%    | GRM31A7U2H560JW31# |                    |  |
|        |               |         | 68pF    | ±5%    | GRM31A7U2H680JW31# |                    |  |
|        |               |         | 82pF    | ±5%    | GRM31A7U2H820JW31# |                    |  |
|        |               |         | 100pF   | ±5%    | GRM31A7U2H101JW31# |                    |  |
|        |               |         | 120pF   | ±5%    | GRM31A7U2H121JW31# |                    |  |
|        |               |         | 150pF   | ±5%    | GRM31A7U2H151JW31# |                    |  |
|        |               |         | 180pF   | ±5%    | GRM31A7U2H181JW31# |                    |  |
|        |               |         | 220pF   | ±5%    | GRM31A7U2H221JW31# |                    |  |
|        |               |         | 270pF   | ±5%    | GRM31A7U2H271JW31# |                    |  |
|        |               |         | 330pF   | ±5%    | GRM31A7U2H331JW31# |                    |  |
|        |               |         | 390pF   | ±5%    | GRM31A7U2H391JW31# |                    |  |
|        |               |         | 470pF   | ±5%    | GRM31A7U2H471JW31# |                    |  |
|        |               |         | 560pF   | ±5%    | GRM31A7U2H561JW31# |                    |  |
|        |               |         | 680pF   | ±5%    | GRM31A7U2H681JW31# |                    |  |
|        |               |         | 820pF   | ±5%    | GRM31A7U2H821JW31# |                    |  |
|        |               |         | 1000pF  | ±5%    | GRM31A7U2H102JW31# |                    |  |
|        |               |         | 1200pF  | ±5%    | GRM31A7U2H122JW31# |                    |  |
|        |               |         | 1500pF  | ±5%    | GRM31A7U2H152JW31# |                    |  |
|        |               |         | 1800pF  | ±5%    | GRM31A7U2H182JW31# |                    |  |
|        |               |         | 2200pF  | ±5%    | GRM31A7U2H222JW31# |                    |  |
|        | 250Vdc        | U2J     | 2700pF  | ±5%    | GRM31A7U2E272JW31# |                    |  |
|        |               |         | 3300pF  | ±5%    | GRM31A7U2E332JW31# |                    |  |
|        |               |         | 3900pF  | ±5%    | GRM31A7U2E392JW31# |                    |  |
|        |               |         | 4700pF  | ±5%    | GRM31A7U2E472JW31# |                    |  |
|        |               |         | 5600pF  | ±5%    | GRM31A7U2E562JW31# |                    |  |
|        | 200Vdc        | U2J     | 2700pF  | ±5%    | GRM31A7U2D272JW31# |                    |  |
|        |               |         | 3300pF  | ±5%    | GRM31A7U2D332JW31# |                    |  |
|        |               |         | 3900pF  | ±5%    | GRM31A7U2D392JW31# |                    |  |
|        |               |         | 4700pF  | ±5%    | GRM31A7U2D472JW31# |                    |  |
|        |               |         | 5600pF  | ±5%    | GRM31A7U2D562JW31# |                    |  |
|        | 1.25mm        | 1000Vdc | U2J     | 390pF  | ±5%                | GRM31B7U3A391JW31# |  |
|        |               |         |         | 470pF  | ±5%                | GRM31B7U3A471JW31# |  |
|        |               |         |         | 560pF  | ±5%                | GRM31B7U3A561JW31# |  |
|        |               |         |         | 680pF  | ±5%                | GRM31B7U3A681JW31# |  |
|        |               | 630Vdc  | C0G     | 680pF  | ±5%                | GRM31B5C2J681JW01# |  |
|        |               |         |         | 820pF  | ±5%                | GRM31B5C2J821JW01# |  |
|        |               |         |         | 1000pF | ±5%                | GRM31B5C2J102JW01# |  |
|        |               |         | U2J     | 2700pF | ±5%                | GRM31B7U2J272JW31# |  |
| 3300pF |               |         |         | ±5%    | GRM31B7U2J332JW31# |                    |  |
| 500Vdc |               |         | C0G     | 680pF  | ±5%                | GRM31B5C2H681JW01# |  |
|        |               | 820pF   |         | ±5%    | GRM31B5C2H821JW01# |                    |  |
|        |               | 1000pF  |         | ±5%    | GRM31B5C2H102JW01# |                    |  |
|        |               | U2J     | 2700pF  | ±5%    | GRM31B7U2H272JW31# |                    |  |
|        |               |         | 3300pF  | ±5%    | GRM31B7U2H332JW31# |                    |  |
| 250Vdc |               | U2J     | 6800pF  | ±5%    | GRM31B7U2E682JW31# |                    |  |
|        |               |         | 8200pF  | ±5%    | GRM31B7U2E822JW31# |                    |  |
|        |               |         | 10000pF | ±5%    | GRM31B7U2E103JW31# |                    |  |
|        |               |         | 12000pF | ±5%    | GRM31B7U2E123JW31# |                    |  |
| 200Vdc |               | U2J     | 6800pF  | ±5%    | GRM31B7U2D682JW31# |                    |  |
|        |               |         | 8200pF  | ±5%    | GRM31B7U2D822JW31# |                    |  |
|        |               |         | 10000pF | ±5%    | GRM31B7U2D103JW31# |                    |  |
| 50Vdc  |               | C0G     | 47000pF | ±5%    | GRM31M5C1H473JA01# |                    |  |

Part number # indicates the package specification code.

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 3.2×1.6mm)

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 1.25mm | 50Vdc         | C0G     | 56000pF | ±5%  | GRM31M5C1H563JA01# |  |
|        |               |         | 47000pF | ±5%  | GRM31M2C1H473JA01# |  |
|        |               |         | 56000pF | ±5%  | GRM31M2C1H563JA01# |  |
|        |               | SL      | 68000pF | ±5%  | GRM31M1X1H683JA01# |  |
|        |               |         | 82000pF | ±5%  | GRM31M1X1H823JA01# |  |
|        |               |         | 0.10μF  | ±5%  | GRM31M1X1H104JA01# |  |
|        |               | U2J     | 68000pF | ±5%  | GRM31M7U1H683JA01# |  |
|        |               |         | 82000pF | ±5%  | GRM31M7U1H823JA01# |  |
|        |               |         | 0.10μF  | ±5%  | GRM31M7U1H104JA01# |  |
|        |               | UJ      | 68000pF | ±5%  | GRM31M3U1H683JA01# |  |
|        |               |         | 82000pF | ±5%  | GRM31M3U1H823JA01# |  |
|        |               |         | 0.10μF  | ±5%  | GRM31M3U1H104JA01# |  |
| 1.8mm  | 1000Vdc       | U2J     | 820pF   | ±5%  | GRM31C7U3A821JW32# |  |
|        |               |         | 1000pF  | ±5%  | GRM31C7U3A102JW32# |  |
|        | 630Vdc        | U2J     | 3900pF  | ±5%  | GRM31C7U2J392JW32# |  |
|        |               |         | 4700pF  | ±5%  | GRM31C7U2J472JW32# |  |
|        | 500Vdc        | U2J     | 3900pF  | ±5%  | GRM31C7U2H392JW32# |  |
|        |               |         | 4700pF  | ±5%  | GRM31C7U2H472JW32# |  |
|        | 250Vdc        | U2J     | 15000pF | ±5%  | GRM31C7U2E153JW32# |  |
|        |               |         | 18000pF | ±5%  | GRM31C7U2E183JW32# |  |
|        |               |         | 22000pF | ±5%  | GRM31C7U2E223JW32# |  |
|        | 50Vdc         | C0G     | 68000pF | ±5%  | GRM31C5C1H683JA01# |  |
|        |               |         | 82000pF | ±5%  | GRM31C5C1H823JA01# |  |
|        |               |         | 0.10μF  | ±5%  | GRM31C5C1H104JA01# |  |
|        |               | CH      | 68000pF | ±5%  | GRM31C2C1H683JA01# |  |
|        |               |         | 82000pF | ±5%  | GRM31C2C1H823JA01# |  |
|        |               |         | 0.10μF  | ±5%  | GRM31C2C1H104JA01# |  |

■ 3.2×2.5mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 1.0mm  | 2000Vdc       | U2J     | 82pF    | ±5%  | GRM32A7U3D820JW31# |  |
|        |               |         | 100pF   | ±5%  | GRM32A7U3D101JW31# |  |
|        |               |         | 120pF   | ±5%  | GRM32A7U3D121JW31# |  |
|        |               |         | 150pF   | ±5%  | GRM32A7U3D151JW31# |  |
|        | 630Vdc        | U2J     | 1200pF  | ±5%  | GRM32A7U2J122JW31# |  |
|        |               |         | 1500pF  | ±5%  | GRM32A7U2J152JW31# |  |
|        |               |         | 1800pF  | ±5%  | GRM32A7U2J182JW31# |  |
|        |               |         | 2200pF  | ±5%  | GRM32A7U2J222JW31# |  |
|        | 500Vdc        | U2J     | 1200pF  | ±5%  | GRM32A7U2H122JW31# |  |
|        |               |         | 1500pF  | ±5%  | GRM32A7U2H152JW31# |  |
|        |               |         | 1800pF  | ±5%  | GRM32A7U2H182JW31# |  |
|        |               |         | 2200pF  | ±5%  | GRM32A7U2H222JW31# |  |
| 1.25mm | 2000Vdc       | U2J     | 180pF   | ±5%  | GRM32B7U3D181JW31# |  |
|        |               |         | 220pF   | ±5%  | GRM32B7U3D221JW31# |  |
|        | 1000Vdc       | U2J     | 1200pF  | ±5%  | GRM32B7U3A122JW31# |  |
|        | 630Vdc        | U2J     | 5600pF  | ±5%  | GRM32B7U2J562JW31# |  |
| 1.5mm  | 500Vdc        | U2J     | 5600pF  | ±5%  | GRM32B7U2H562JW31# |  |
|        | 1000Vdc       | U2J     | 1500pF  | ±5%  | GRM32Q7U3A152JW31# |  |
|        | 630Vdc        | U2J     | 6800pF  | ±5%  | GRM32Q7U2J682JW31# |  |
|        | 500Vdc        | U2J     | 6800pF  | ±5%  | GRM32Q7U2H682JW31# |  |
| 2.0mm  | 250Vdc        | U2J     | 27000pF | ±5%  | GRM32Q7U2E273JW31# |  |
|        | 1000Vdc       | U2J     | 1800pF  | ±5%  | GRM32D7U3A182JW31# |  |

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 2.0mm  | 1000Vdc       | U2J     | 2200pF  | ±5%  | GRM32D7U3A222JW31# |  |
|        |               |         | 8200pF  | ±5%  | GRM32D7U2J822JW31# |  |
|        | 630Vdc        | U2J     | 10000pF | ±5%  | GRM32D7U2J103JW31# |  |
|        |               |         | 8200pF  | ±5%  | GRM32D7U2H822JW31# |  |
|        | 500Vdc        | U2J     | 10000pF | ±5%  | GRM32D7U2H103JW31# |  |
|        |               |         | 33000pF | ±5%  | GRM32D7U2E333JW31# |  |
|        | 250Vdc        | U2J     | 39000pF | ±5%  | GRM32D7U2E393JW31# |  |
|        |               |         | 47000pF | ±5%  | GRM32D7U2E473JW31# |  |

■ 4.5×2.0mm

| T max. | Rated Voltage | TC Code | Cap.  | Tol. | Part Number        |  |
|--------|---------------|---------|-------|------|--------------------|--|
| 1.0mm  | 3150Vdc       | U2J     | 27pF  | ±5%  | GRM42A7U3F270JW31# |  |
|        |               |         | 33pF  | ±5%  | GRM42A7U3F330JW31# |  |
|        |               |         | 39pF  | ±5%  | GRM42A7U3F390JW31# |  |
|        |               |         | 47pF  | ±5%  | GRM42A7U3F470JW31# |  |
|        |               |         | 56pF  | ±5%  | GRM42A7U3F560JW31# |  |
|        |               |         | 68pF  | ±5%  | GRM42A7U3F680JW31# |  |
|        |               |         | 82pF  | ±5%  | GRM42A7U3F820JW31# |  |
|        |               |         | 100pF | ±5%  | GRM42A7U3F101JW31# |  |

■ 4.5×3.2mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 1.5mm  | 1000Vdc       | U2J     | 2700pF  | ±5%  | GRM43Q7U3A272JW31# |  |
|        |               |         | 3300pF  | ±5%  | GRM43Q7U3A332JW31# |  |
|        | 630Vdc        | U2J     | 12000pF | ±5%  | GRM43Q7U2J123JW31# |  |
|        | 500Vdc        | U2J     | 12000pF | ±5%  | GRM43Q7U2H123JW31# |  |
| 2.0mm  | 1000Vdc       | U2J     | 3900pF  | ±5%  | GRM43D7U3A392JW31# |  |
|        |               |         | 4700pF  | ±5%  | GRM43D7U3A472JW31# |  |
|        |               |         | 18000pF | ±5%  | GRM43D7U2J183JW31# |  |
|        |               |         | 22000pF | ±5%  | GRM43D7U2J223JW31# |  |
|        | 630Vdc        | U2J     | 15000pF | ±5%  | GRM43D7U2J153JW31# |  |
|        |               |         | 18000pF | ±5%  | GRM43D7U2J183JW31# |  |
|        |               |         | 22000pF | ±5%  | GRM43D7U2J223JW31# |  |
|        |               |         | 22000pF | ±5%  | GRM43D7U2H223JW31# |  |

■ 5.7×5.0mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 1.5mm  | 1000Vdc       | U2J     | 5600pF  | ±5%  | GRM55Q7U3A562JW31# |  |
|        |               |         | 6800pF  | ±5%  | GRM55Q7U3A682JW31# |  |
|        | 630Vdc        | U2J     | 27000pF | ±5%  | GRM55Q7U2J273JW31# |  |
| 2.0mm  | 500Vdc        | U2J     | 27000pF | ±5%  | GRM55Q7U2H273JW31# |  |
|        | 1000Vdc       | U2J     | 8200pF  | ±5%  | GRM55D7U3A822JW31# |  |
|        |               |         | 10000pF | ±5%  | GRM55D7U3A103JW31# |  |
|        |               |         | 33000pF | ±5%  | GRM55D7U2J333JW31# |  |
|        | 630Vdc        | U2J     | 39000pF | ±5%  | GRM55D7U2J393JW31# |  |
|        |               |         | 47000pF | ±5%  | GRM55D7U2J473JW31# |  |
|        |               |         | 33000pF | ±5%  | GRM55D7U2H333JW31# |  |
|        | 500Vdc        | U2J     | 39000pF | ±5%  | GRM55D7U2H393JW31# |  |

Part number # indicates the package specification code.

GRM Series

GJM Series

GMA Series

GMD Series

GQM Series

GRJ Series

GR3 Series

KRM Series

KR3 Series

LLA Series

LLL Series

LLM Series

LLR Series

⚠Caution/  
 Notice

## GRM Series Temperature Compensating Type Part Number List

(→ ■ 5.7×5.0mm)

| T<br>max. | Rated<br>Voltage | TC<br>Code | Cap.    | Tol. | Part Number        |  |
|-----------|------------------|------------|---------|------|--------------------|--|
| 2.0mm     | 500Vdc           | U2J        | 47000pF | ±5%  | GRM55D7U2H473JW31# |  |

Part number # indicates the package specification code.

## GRM Series High Dielectric Constant Type Part Number List

### ■ 0.4×0.2mm Ultra-compact

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.22mm | 10Vdc         | X7R     | 100pF   | ±10% | GRM022R71A101KA01# |  |
|        |               |         |         | ±20% | GRM022R71A101MA01# |  |
|        |               |         | 150pF   | ±10% | GRM022R71A151KA01# |  |
|        |               |         |         | ±20% | GRM022R71A151MA01# |  |
|        |               |         | 220pF   | ±10% | GRM022R71A221KA01# |  |
|        |               |         |         | ±20% | GRM022R71A221MA01# |  |
|        |               |         | 330pF   | ±10% | GRM022R71A331KA01# |  |
|        |               |         |         | ±20% | GRM022R71A331MA01# |  |
|        |               |         | 470pF   | ±10% | GRM022R71A471KA01# |  |
|        |               |         |         | ±20% | GRM022R71A471MA01# |  |
|        |               |         | 680pF   | ±10% | GRM022R71A681KA12# |  |
|        |               |         |         | ±20% | GRM022R71A681MA12# |  |
|        |               |         | 820pF   | ±10% | GRM022R71A821KA12# |  |
|        |               |         |         | ±20% | GRM022R71A821MA12# |  |
|        |               |         | 1000pF  | ±10% | GRM022R71A102KA12# |  |
|        |               |         |         | ±20% | GRM022R71A102MA12# |  |
|        |               | X5R     | 100pF   | ±10% | GRM022R61A101KA01# |  |
|        |               |         |         | ±20% | GRM022R61A101MA01# |  |
|        |               |         | 150pF   | ±10% | GRM022R61A151KA01# |  |
|        |               |         |         | ±20% | GRM022R61A151MA01# |  |
|        |               |         | 220pF   | ±10% | GRM022R61A221KA01# |  |
|        |               |         |         | ±20% | GRM022R61A221MA01# |  |
|        |               |         | 330pF   | ±10% | GRM022R61A331KA01# |  |
|        |               |         |         | ±20% | GRM022R61A331MA01# |  |
|        |               |         | 470pF   | ±10% | GRM022R61A471KA01# |  |
|        |               |         |         | ±20% | GRM022R61A471MA01# |  |
|        |               |         | 680pF   | ±10% | GRM022R61A681KE19# |  |
|        |               |         |         | ±20% | GRM022R61A681ME19# |  |
|        |               |         | 1000pF  | ±10% | GRM022R61A102KE19# |  |
|        |               |         |         | ±20% | GRM022R61A102ME19# |  |
|        |               |         | 1500pF  | ±10% | GRM022R61A152KE19# |  |
|        |               |         |         | ±20% | GRM022R61A152ME19# |  |
|        |               |         | 2200pF  | ±10% | GRM022R61A222KE19# |  |
|        |               |         |         | ±20% | GRM022R61A222ME19# |  |
|        |               |         | 3300pF  | ±10% | GRM022R61A332KE19# |  |
|        |               |         |         | ±20% | GRM022R61A332ME19# |  |
|        |               |         | 4700pF  | ±10% | GRM022R61A472KE19# |  |
|        |               |         |         | ±20% | GRM022R61A472ME19# |  |
|        |               |         | 6800pF  | ±10% | GRM022R61A682KE19# |  |
|        |               |         |         | ±20% | GRM022R61A682ME19# |  |
|        |               |         | 10000pF | ±10% | GRM022R61A103KE19# |  |
|        |               |         |         | ±20% | GRM022R61A103ME19# |  |
|        |               | B       | 100pF   | ±10% | GRM022B11A101KA01# |  |
|        |               |         |         | ±20% | GRM022B11A101MA01# |  |
|        |               |         | 150pF   | ±10% | GRM022B11A151KA01# |  |
|        |               |         |         | ±20% | GRM022B11A151MA01# |  |
|        |               |         | 220pF   | ±10% | GRM022B11A221KA01# |  |
|        |               |         |         | ±20% | GRM022B11A221MA01# |  |
|        |               |         | 330pF   | ±10% | GRM022B11A331KA01# |  |
|        |               |         |         | ±20% | GRM022B11A331MA01# |  |
|        |               |         | 470pF   | ±10% | GRM022B11A471KA01# |  |
|        |               |         |         | ±20% | GRM022B11A471MA01# |  |
|        |               |         |         | ±10% |                    |  |
|        |               |         |         | ±20% |                    |  |

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |           |
|--------|---------------|---------|---------|------|--------------------|-----------|
| 0.22mm | 10Vdc         | B       | 680pF   | ±10% | GRM022B31A681KE19# |           |
|        |               |         |         | ±20% | GRM022B31A681ME19# |           |
|        |               |         | 1000pF  | ±10% | GRM022B31A102KE19# |           |
|        |               |         |         | ±20% | GRM022B31A102ME19# |           |
|        |               |         | 1500pF  | ±10% | GRM022B31A152KE19# |           |
|        |               |         |         | ±20% | GRM022B31A152ME19# |           |
|        |               |         | 2200pF  | ±10% | GRM022B31A222KE19# |           |
|        |               |         |         | ±20% | GRM022B31A222ME19# |           |
|        |               |         | 3300pF  | ±10% | GRM022B31A332KE19# |           |
|        |               |         |         | ±20% | GRM022B31A332ME19# |           |
|        |               |         | 4700pF  | ±10% | GRM022B31A472KE19# |           |
|        |               |         |         | ±20% | GRM022B31A472ME19# |           |
|        |               |         | 6800pF  | ±10% | GRM022B31A682KE19# |           |
|        |               |         |         | ±20% | GRM022B31A682ME19# |           |
|        |               |         | 10000pF | ±10% | GRM022B31A103KE19# |           |
|        |               |         |         | ±20% | GRM022B31A103ME19# |           |
|        | 6.3Vdc        | X5R     | 1000pF  | ±20% | GRM022R60J102ME19# |           |
|        |               |         |         | ±20% | GRM022R60J152ME19# |           |
|        |               |         | 2200pF  | ±20% | GRM022R60J222ME19# |           |
|        |               |         |         | ±20% | GRM022R60J332ME19# |           |
|        |               |         | 4700pF  | ±20% | GRM022R60J472ME19# |           |
|        |               |         |         | ±20% | GRM022R60J682ME19# |           |
|        |               |         | 10000pF | ±20% | GRM022R60J103ME19# |           |
|        |               |         |         | ±20% | GRM022R60J153ME15# | Degrating |
|        |               |         | 22000pF | ±10% | GRM022R60J223KE15# | Degrating |
|        |               |         |         | ±20% | GRM022R60J223ME15# | Degrating |
|        |               |         | 33000pF | ±20% | GRM022R60J333ME15# | Degrating |
|        |               |         |         | ±20% | GRM022R60J473ME15# | Degrating |
|        |               |         | 47000pF | ±20% | GRM022R60J473ME15# | Degrating |
|        |               |         |         | ±20% | GRM022R60J683ME15# | Degrating |
|        |               |         | 68000pF | ±20% | GRM022R60J683ME15# | Degrating |
|        |               |         |         | ±20% | GRM022R60J104ME15# | Degrating |
|        |               |         | 0.10μF  | ±20% | GRM022B30J102ME19# |           |
|        |               |         |         | ±20% | GRM022B30J152ME19# |           |
|        |               |         | 2200pF  | ±20% | GRM022B30J222ME19# |           |
|        |               |         |         | ±20% | GRM022B30J332ME19# |           |
|        |               |         | 4700pF  | ±20% | GRM022B30J472ME19# |           |
|        |               |         |         | ±20% | GRM022B30J682ME19# |           |
|        |               |         | 10000pF | ±20% | GRM022B30J103ME19# |           |
|        |               |         |         | ±20% | GRM022R60G153KE15# |           |
|        | 4Vdc          | X5R     | 15000pF | ±10% | GRM022R60G153KE15# |           |
|        |               |         |         | ±20% | GRM022R60G153ME15# |           |
|        |               |         | 22000pF | ±10% | GRM022R60G223KE15# |           |
|        |               |         |         | ±20% | GRM022R60G223ME15# |           |
|        |               |         | 33000pF | ±10% | GRM022R60G333KE15# |           |
|        |               |         |         | ±20% | GRM022R60G333ME15# |           |
|        |               |         | 47000pF | ±10% | GRM022R60G473KE15# |           |
|        |               |         |         | ±20% | GRM022R60G473ME15# |           |
|        |               |         | 68000pF | ±20% | GRM022R60G683ME15# |           |
|        |               |         |         | ±20% | GRM022R60G104ME15# |           |
|        |               |         | 0.10μF  | ±20% | GRM022R60G104ME15# |           |
|        |               |         |         | ±20% |                    |           |

### ■ 0.6×0.3mm Ultra-compact

| T max. | Rated Voltage | TC Code | Cap.  | Tol. | Part Number        |  |
|--------|---------------|---------|-------|------|--------------------|--|
| 0.33mm | 50Vdc         | X7R     | 100pF | ±10% | GRM033R71H101KA12# |  |
|        |               |         |       | ±20% | GRM033R71H101MA12# |  |

Part number # indicates the package specification code.

## GRM Series High Dielectric Constant Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |           |
|--------|---------------|---------|---------|------|--------------------|-----------|
| 0.33mm | 50Vdc         | X7R     | 150pF   | ±10% | GRM033R71H151KA12# |           |
|        |               |         |         | ±20% | GRM033R71H151MA12# |           |
|        |               |         | 220pF   | ±10% | GRM033R71H221KA12# |           |
|        |               |         |         | ±20% | GRM033R71H221MA12# |           |
|        |               |         | 330pF   | ±10% | GRM033R71H331KA12# |           |
|        |               |         |         | ±20% | GRM033R71H331MA12# |           |
|        |               |         | 470pF   | ±10% | GRM033R71H471KA12# |           |
|        |               |         |         | ±20% | GRM033R71H471MA12# |           |
|        |               |         | 680pF   | ±10% | GRM033R71H681KA12# |           |
|        |               |         |         | ±20% | GRM033R71H681MA12# |           |
|        |               |         | 1000pF  | ±10% | GRM033R71H102KA12# |           |
|        |               |         |         | ±20% | GRM033R71H102MA12# |           |
|        |               |         | 1500pF  | ±10% | GRM033R71H152KA12# |           |
|        |               |         |         | ±20% | GRM033R71H152MA12# |           |
|        |               | B       | 100pF   | ±10% | GRM033B31H101KA12# |           |
|        |               |         |         | ±20% | GRM033B31H101MA12# |           |
|        |               |         | 150pF   | ±10% | GRM033B31H151KA12# |           |
|        |               |         |         | ±20% | GRM033B31H151MA12# |           |
|        |               |         | 220pF   | ±10% | GRM033B31H221KA12# |           |
|        |               |         |         | ±20% | GRM033B31H221MA12# |           |
|        |               |         | 330pF   | ±10% | GRM033B31H331KA12# |           |
|        |               |         |         | ±20% | GRM033B31H331MA12# |           |
|        |               |         | 470pF   | ±10% | GRM033B31H471KA12# |           |
|        |               |         |         | ±20% | GRM033B31H471MA12# |           |
|        |               |         | 680pF   | ±10% | GRM033B31H681KA12# |           |
|        |               |         |         | ±20% | GRM033B31H681MA12# |           |
|        |               |         | 1000pF  | ±10% | GRM033B31H102KA12# |           |
|        |               |         |         | ±20% | GRM033B31H102MA12# |           |
|        |               |         | 1500pF  | ±10% | GRM033B31H152KA12# |           |
|        |               |         |         | ±20% | GRM033B31H152MA12# |           |
|        | 25Vdc         | X7R     | 1000pF  | ±10% | GRM033R71E102KA01# |           |
|        |               |         |         | ±20% | GRM033R71E102MA01# |           |
|        |               |         | 1500pF  | ±10% | GRM033R71E152KA01# |           |
|        |               |         |         | ±20% | GRM033R71E152MA01# |           |
|        |               |         | 2200pF  | ±10% | GRM033R71E222KA12# |           |
|        |               |         |         | ±20% | GRM033R71E222MA12# |           |
|        |               | R       | 100pF   | ±10% | GRM033R11E101KA01# |           |
|        |               |         |         | ±20% | GRM033R11E101MA01# |           |
|        |               |         | 150pF   | ±10% | GRM033R11E151KA01# |           |
|        |               |         |         | ±20% | GRM033R11E151MA01# |           |
|        |               |         | 220pF   | ±10% | GRM033R11E221KA01# |           |
|        |               |         |         | ±20% | GRM033R11E221MA01# |           |
|        |               | X5R     | 4700pF  | ±10% | GRM033R61E472KA12# | Degrating |
|        |               |         |         | ±20% | GRM033R61E472MA12# | Degrating |
|        |               |         | 6800pF  | ±10% | GRM033R61E682KA12# | Degrating |
|        |               |         |         | ±20% | GRM033R61E682MA12# | Degrating |
|        |               |         | 10000pF | ±10% | GRM033R61E103KA12# | Degrating |
|        |               |         |         | ±20% | GRM033R61E103MA12# | Degrating |
|        |               | B       | 1000pF  | ±10% | GRM033B11E102KA01# |           |
|        |               |         |         | ±20% | GRM033B11E102MA01# |           |
|        |               |         | 1500pF  | ±10% | GRM033B11E152KA01# |           |
|        |               |         |         | ±20% | GRM033B11E152MA01# |           |

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |           |
|--------|---------------|---------|---------|------|--------------------|-----------|
| 0.33mm | 25Vdc         | B       | 2200pF  | ±10% | GRM033B31E222KA12# |           |
|        |               |         |         | ±20% | GRM033B31E222MA12# |           |
|        |               |         | 3300pF  | ±10% | GRM033B31E332KA12# |           |
|        |               |         |         | ±20% | GRM033B31E332MA12# |           |
|        |               |         | 10000pF | ±10% | GRM033B31E103KA12# | Degrating |
|        |               |         |         | ±20% | GRM033B31E103MA12# | Degrating |
|        | 16Vdc         | X7R     | 2200pF  | ±10% | GRM033R71C222KA88# |           |
|        |               |         |         | ±20% | GRM033R71C222MA88# |           |
|        |               |         | 3300pF  | ±10% | GRM033R11C222KA88# |           |
|        |               |         |         | ±20% | GRM033R11C222MA88# |           |
|        |               | R       | 2200pF  | ±10% | GRM033R11C222KA88# |           |
|        |               |         |         | ±20% | GRM033R11C222MA88# |           |
|        |               |         | 3300pF  | ±10% | GRM033R11C332KA88# |           |
|        |               |         |         | ±20% | GRM033R11C332MA88# |           |
|        |               | X5R     | 10000pF | ±10% | GRM033R61C103KA12# |           |
|        |               |         |         | ±20% | GRM033R61C103MA12# |           |
|        |               |         | 15000pF | ±10% | GRM033R61C153KE84# | Degrating |
|        |               |         |         | ±20% | GRM033R61C153ME84# | Degrating |
|        |               |         | 22000pF | ±10% | GRM033R61C223KE84# | Degrating |
|        |               |         |         | ±20% | GRM033R61C223ME84# | Degrating |
|        |               |         | 33000pF | ±10% | GRM033R61C333KE84# | Degrating |
|        |               |         |         | ±20% | GRM033R61C333ME84# | Degrating |
|        |               | B       | 47000pF | ±10% | GRM033R61C473KE84# | Degrating |
|        |               |         |         | ±20% | GRM033R61C473ME84# | Degrating |
|        |               |         | 68000pF | ±10% | GRM033R61C683KE84# | Degrating |
|        |               |         |         | ±20% | GRM033R61C683ME84# | Degrating |
|        |               |         | 0.10μF  | ±10% | GRM033R61C104KE84# | Degrating |
|        |               |         |         | ±20% | GRM033R61C104ME84# | Degrating |
|        |               |         | 2200pF  | ±10% | GRM033B31C222KA87# |           |
|        |               |         |         | ±20% | GRM033B31C222MA87# |           |
|        |               |         | 3300pF  | ±10% | GRM033B31C332KA87# |           |
|        |               |         |         | ±20% | GRM033B31C332MA87# |           |
|        |               |         | 10000pF | ±10% | GRM033B31C103KA12# |           |
|        |               |         |         | ±20% | GRM033B31C103MA12# |           |
|        |               |         | 15000pF | ±10% | GRM033B31C153KE84# | Degrating |
|        |               |         |         | ±20% | GRM033B31C153ME84# | Degrating |
|        |               |         | 22000pF | ±10% | GRM033B31C223KE84# | Degrating |
|        |               |         |         | ±20% | GRM033B31C223ME84# | Degrating |
|        |               |         | 33000pF | ±10% | GRM033B31C333KE84# | Degrating |
|        |               |         |         | ±20% | GRM033B31C333ME84# | Degrating |
|        |               |         | 47000pF | ±10% | GRM033B31C473KE84# | Degrating |
|        |               |         |         | ±20% | GRM033B31C473ME84# | Degrating |
|        |               |         | 68000pF | ±10% | GRM033B31C683KE84# | Degrating |
|        |               |         |         | ±20% | GRM033B31C683ME84# | Degrating |
|        |               |         | 0.10μF  | ±10% | GRM033B31C104KE84# | Degrating |
|        |               |         |         | ±20% | GRM033B31C104ME84# | Degrating |
|        | 10Vdc         | X7R     | 4700pF  | ±10% | GRM033R71A472KA01# |           |
|        |               |         |         | ±20% | GRM033R71A472MA01# |           |
|        |               |         | 6800pF  | ±10% | GRM033R71A682KA01# |           |
|        |               |         |         | ±20% | GRM033R71A682MA01# |           |
|        |               |         | 10000pF | ±10% | GRM033R71A103KA01# |           |
|        |               |         |         | ±20% | GRM033R71A103MA01# |           |
|        |               | R       | 4700pF  | ±10% | GRM033R11A472KA01# |           |
|        |               |         |         | ±20% | GRM033R11A472MA01# |           |
|        |               |         | 6800pF  | ±10% | GRM033R11A682KA01# |           |
|        |               |         |         | ±20% | GRM033R11A682MA01# |           |
|        |               |         | 10000pF | ±10% | GRM033R11A103KA01# |           |
|        |               |         |         | ±20% | GRM033R11A103MA01# |           |

Part number # indicates the package specification code.



## GRM Series High Dielectric Constant Type Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |           |
|--------|---------------|---------|---------|------|--------------------|-----------|
| 0.33mm | 10Vdc         | X5R     | 4700pF  | ±10% | GRM033R61A472KA01# |           |
|        |               |         |         | ±20% | GRM033R61A472MA01# |           |
|        |               |         | 6800pF  | ±10% | GRM033R61A682KA01# |           |
|        |               |         |         | ±20% | GRM033R61A682MA01# |           |
|        |               |         | 15000pF | ±10% | GRM033R61A153KE84# |           |
|        |               |         |         | ±20% | GRM033R61A153ME84# |           |
|        |               |         | 22000pF | ±10% | GRM033R61A223KE84# |           |
|        |               |         |         | ±20% | GRM033R61A223ME84# |           |
|        |               |         | 33000pF | ±10% | GRM033R61A333KE84# |           |
|        |               |         |         | ±20% | GRM033R61A333ME84# |           |
|        |               |         | 47000pF | ±10% | GRM033R61A473KE84# |           |
|        |               |         |         | ±20% | GRM033R61A473ME84# |           |
|        |               |         | 68000pF | ±10% | GRM033R61A683KE84# |           |
|        |               |         |         | ±20% | GRM033R61A683ME84# |           |
|        |               |         | 0.10μF  | ±10% | GRM033R61A104KE84# |           |
|        |               |         |         | ±20% | GRM033R61A104ME84# |           |
|        |               |         | 0.22μF  | ±20% | GRM033R61A224ME90# | Degrating |
|        |               | B       | 4700pF  | ±10% | GRM033B11A472KA01# |           |
|        |               |         |         | ±20% | GRM033B11A472MA01# |           |
|        |               |         | 6800pF  | ±10% | GRM033B11A682KA01# |           |
|        |               |         |         | ±20% | GRM033B11A682MA01# |           |
|        |               |         | 15000pF | ±10% | GRM033B31A153KE84# |           |
|        |               |         |         | ±20% | GRM033B31A153ME84# |           |
|        |               |         | 22000pF | ±10% | GRM033B31A223KE84# |           |
|        |               |         |         | ±20% | GRM033B31A223ME84# |           |
|        |               |         | 33000pF | ±10% | GRM033B31A333KE84# |           |
|        |               |         |         | ±20% | GRM033B31A333ME84# |           |
|        |               |         | 47000pF | ±10% | GRM033B31A473KE84# |           |
|        |               |         |         | ±20% | GRM033B31A473ME84# |           |
|        |               |         | 68000pF | ±10% | GRM033B31A683KE84# |           |
|        |               |         |         | ±20% | GRM033B31A683ME84# |           |
|        |               |         | 0.10μF  | ±10% | GRM033B31A104KE84# |           |
|        |               |         |         | ±20% | GRM033B31A104ME84# |           |
|        | 6.3Vdc        | X7R     | 4700pF  | ±10% | GRM033R70J472KA01# |           |
|        |               |         | 6800pF  | ±10% | GRM033R70J682KA01# |           |
|        |               |         | 10000pF | ±10% | GRM033R70J103KA01# |           |
|        |               | R       | 4700pF  | ±10% | GRM033R10J472KA01# |           |
|        |               |         | 6800pF  | ±10% | GRM033R10J682KA01# |           |
|        |               |         | 10000pF | ±10% | GRM033R10J103KA01# |           |
|        |               | X6S     | 15000pF | ±10% | GRM033C80J153KE01# |           |
|        |               |         |         | ±20% | GRM033C80J153ME01# |           |
|        |               |         | 22000pF | ±10% | GRM033C80J223KE01# |           |
|        |               |         |         | ±20% | GRM033C80J223ME01# |           |
|        |               |         | 33000pF | ±10% | GRM033C80J333KE01# |           |
|        |               |         |         | ±20% | GRM033C80J333ME01# |           |
|        |               |         | 47000pF | ±10% | GRM033C80J473KE19# |           |
|        |               |         |         | ±20% | GRM033C80J473ME19# |           |
|        |               |         | 68000pF | ±10% | GRM033C80J683KE84# | Degrating |
|        |               |         |         | ±20% | GRM033C80J683ME84# | Degrating |
|        |               |         | 0.10μF  | ±10% | GRM033C80J104KE84# | Degrating |
|        |               |         |         | ±20% | GRM033C80J104ME84# | Degrating |
|        |               |         | 0.22μF  | ±20% | GRM033C80J224ME90# | Degrating |
|        |               |         |         | ±20% | GRM033C80J224ME90# | Degrating |
|        |               | X5R     | 0.22μF  | ±20% | GRM033R60J224ME90# |           |
|        |               | B       | 4700pF  | ±10% | GRM033B10J472KA01# |           |

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.33mm | 6.3Vdc        | B       | 6800pF  | ±10% | GRM033B10J682KA01# |  |
|        |               |         |         | ±10% | GRM033B10J153KE01# |  |
|        |               |         | 15000pF | ±10% | GRM033B10J153ME01# |  |
|        |               |         |         | ±20% | GRM033B10J153ME01# |  |
|        |               |         | 22000pF | ±10% | GRM033B10J223KE01# |  |
|        |               |         |         | ±20% | GRM033B10J223ME01# |  |
|        |               |         | 33000pF | ±10% | GRM033B10J333KE01# |  |
|        |               |         |         | ±20% | GRM033B10J333ME01# |  |
|        |               |         | 4Vdc    | ±20% | GRM033C80G224ME90# |  |
|        |               |         |         | ±20% | GRM033C80G224ME90# |  |

■ 1.0×0.5mm

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |           |
|--------|---------------|---------|--------|------|--------------------|-----------|
| 0.22mm | 10Vdc         | X5R     | 0.10μF | ±10% | GRM152R61A104KE19# | Degrating |
|        |               |         |        | ±20% | GRM152R61A104ME19# | Degrating |
|        |               |         | 0.22μF | ±10% | GRM152R61A224KE19# | Degrating |
|        |               |         |        | ±20% | GRM152R61A224ME19# | Degrating |
|        |               | B       | 0.10μF | ±10% | GRM152B31A104KE19# | Degrating |
|        |               |         |        | ±20% | GRM152B31A104ME19# | Degrating |
|        |               |         | 0.22μF | ±10% | GRM152B31A224KE19# | Degrating |
|        |               |         |        | ±20% | GRM152B31A224ME19# | Degrating |
|        |               | 6.3Vdc  | 0.10μF | ±10% | GRM152C80J104KE19# | Degrating |
|        |               |         |        | ±20% | GRM152C80J104ME19# | Degrating |
|        |               |         | 0.22μF | ±10% | GRM152C80J224KE19# | Degrating |
|        |               |         |        | ±20% | GRM152C80J224ME19# | Degrating |
|        |               | X5R     | 0.10μF | ±10% | GRM152R60J104KE19# |           |
|        |               |         |        | ±20% | GRM152R60J104ME19# |           |
|        |               |         | 0.22μF | ±10% | GRM152R60J224KE19# |           |
|        |               |         |        | ±20% | GRM152R60J224ME19# |           |
|        |               |         | 0.47μF | ±20% | GRM152R60J474ME15# | Degrating |
|        |               |         |        | ±20% | GRM152R60J105ME15# | Degrating |
|        |               | B       | 0.10μF | ±10% | GRM152B30J104KE19# |           |
|        |               |         |        | ±20% | GRM152B30J104ME19# |           |
|        |               |         | 0.22μF | ±10% | GRM152B30J224KE19# |           |
|        |               |         |        | ±20% | GRM152B30J224ME19# |           |
|        |               |         | 0.47μF | ±20% | GRM152B30J474ME15# | Degrating |
|        |               |         |        | ±20% | GRM152B30J105ME15# | Degrating |
|        | 4Vdc          | X7T     | 0.10μF | ±10% | GRM152D70G104KE15# | Degrating |
|        |               |         |        | ±20% | GRM152D70G104ME15# | Degrating |
|        |               |         | 0.22μF | ±10% | GRM152D70G224KE15# | Degrating |
|        |               |         |        | ±20% | GRM152D70G224ME15# | Degrating |
|        |               | X6S     | 0.10μF | ±10% | GRM152C80G104KE19# |           |
|        |               |         |        | ±20% | GRM152C80G104ME19# |           |
|        |               | X6T     | 0.47μF | ±20% | GRM152D80G474ME15# |           |
|        |               |         |        | ±20% | GRM152D80G105ME15# | Degrating |
|        |               | X5R     | 1.0μF  | ±20% | GRM152R60G105ME15# |           |
|        |               |         |        | ±20% | GRM152R60G105ME15# |           |
|        | 2.5Vdc        | X7T     | 0.10μF | ±10% | GRM152D70E104KE19# |           |
|        |               |         |        | ±20% | GRM152D70E104ME19# |           |
|        |               |         | 0.22μF | ±10% | GRM152D70E224KE19# |           |
|        |               |         |        | ±20% | GRM152D70E224ME19# |           |
|        |               |         | 470pF  | ±10% | GRM15XR71H221KA86# |           |
|        |               |         |        | ±10% | GRM15XR71H331KA86# |           |

Part number # indicates the package specification code.

# GRM Series High Dielectric Constant Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.    | Tol.               | Part Number        |                    |           |
|--------|---------------|---------|---------|--------------------|--------------------|--------------------|-----------|
| 0.3mm  | 50Vdc         | X7R     | 680pF   | ±10%               | GRM15XR71H681KA86# |                    |           |
|        |               |         | 1000pF  | ±10%               | GRM15XR71H102KA86# |                    |           |
|        |               |         | 1500pF  | ±10%               | GRM15XR71H152KA86# |                    |           |
|        |               | R       | 220pF   | ±10%               | GRM15XR11H221KA86# |                    |           |
|        |               |         | 330pF   | ±10%               | GRM15XR11H331KA86# |                    |           |
|        |               |         | 470pF   | ±10%               | GRM15XR11H471KA86# |                    |           |
|        |               |         | 680pF   | ±10%               | GRM15XR11H681KA86# |                    |           |
|        |               |         | 1000pF  | ±10%               | GRM15XR11H102KA86# |                    |           |
|        |               |         | 1500pF  | ±10%               | GRM15XR11H152KA86# |                    |           |
|        |               |         | B       | 220pF              | ±10%               | GRM15XB11H221KA86# |           |
|        |               | ±20%    |         |                    | GRM15XB11H221MA86# |                    |           |
|        |               | 330pF   |         | ±10%               | GRM15XB11H331KA86# |                    |           |
|        |               |         |         | ±20%               | GRM15XB11H331MA86# |                    |           |
|        |               | 470pF   |         | ±10%               | GRM15XB11H471KA86# |                    |           |
|        |               |         |         | ±20%               | GRM15XB11H471MA86# |                    |           |
|        |               | 680pF   |         | ±10%               | GRM15XB11H681KA86# |                    |           |
|        |               |         |         | ±20%               | GRM15XB11H681MA86# |                    |           |
|        |               | 1000pF  |         | ±10%               | GRM15XB11H102KA86# |                    |           |
|        |               |         |         | ±20%               | GRM15XB11H102MA86# |                    |           |
|        |               | 1500pF  |         | ±10%               | GRM15XB11H152KA86# |                    |           |
|        |               |         |         | ±20%               | GRM15XB11H152MA86# |                    |           |
|        | 25Vdc         | X7R     | 2200pF  | ±10%               | GRM15XR71E222KA86# |                    |           |
|        |               |         |         | ±20%               | GRM15XR71E222MA86# |                    |           |
|        |               | B       | 2200pF  | ±10%               | GRM15XB11E222KA86# |                    |           |
|        |               |         |         | ±20%               | GRM15XB11E222MA86# |                    |           |
|        |               | 16Vdc   | X7R     | 3300pF             | ±10%               | GRM15XR71C332KA86# |           |
|        |               |         |         |                    | ±20%               | GRM15XR71C332MA86# |           |
|        |               |         |         | 4700pF             | ±10%               | GRM15XR71C472KA86# |           |
|        |               |         |         |                    | ±20%               | GRM15XR71C472MA86# |           |
|        | 6800pF        |         |         | ±10%               | GRM15XR71C682KA86# |                    |           |
|        |               |         |         | ±20%               | GRM15XR71C682MA86# |                    |           |
|        | 10000pF       |         | ±10%    | GRM15XR71C103KA86# |                    |                    |           |
|        |               |         |         | GRM15XR71C103MA86# |                    |                    |           |
|        |               |         | B       | 3300pF             | ±10%               | GRM15XB11C332KA86# |           |
|        |               |         |         |                    | ±20%               | GRM15XB11C332MA86# |           |
|        | 4700pF        |         |         | ±10%               | GRM15XB11C472KA86# |                    |           |
|        |               |         |         | ±20%               | GRM15XB11C472MA86# |                    |           |
|        | 6800pF        | ±10%    |         | GRM15XB11C682KA86# |                    |                    |           |
|        |               | ±20%    |         | GRM15XB11C682MA86# |                    |                    |           |
|        | 10000pF       | ±10%    |         | GRM15XB11C103KA86# |                    |                    |           |
|        |               | ±20%    |         | GRM15XB11C103MA86# |                    |                    |           |
|        | 10Vdc         | X5R     | 15000pF | ±10%               | GRM15XR61A153KA86# |                    |           |
|        |               |         |         | ±20%               | GRM15XR61A153MA86# |                    |           |
|        |               |         | 22000pF | ±10%               | GRM15XR61A223KA86# |                    |           |
|        |               |         |         | ±20%               | GRM15XR61A223MA86# |                    |           |
|        |               |         | 33000pF | ±10%               | GRM15XR61A333KA86# |                    |           |
|        |               |         |         | ±20%               | GRM15XR61A333MA86# |                    |           |
|        | 0.33mm        | 10Vdc   | X5R     | 1.0μF              | ±20%               | GRM153R61A105ME95# | Degrating |
|        |               |         | B       | 1.0μF              | ±20%               | GRM153B31A105ME95# | Degrating |
|        |               | 6.3Vdc  | X6T     | 1.0μF              | ±20%               | GRM153D80J105ME95# | Degrating |
| X5R    |               |         | 1.0μF   | ±20%               | GRM153R60J105ME95# |                    |           |
| B      |               |         | 1.0μF   | ±20%               | GRM153B30J105ME95# |                    |           |
| 4Vdc   |               | X6T     | 1.0μF   | ±20%               | GRM153D80G105ME95# |                    |           |
| 0.55mm |               | 100Vdc  | X7R     | 220pF              | ±10%               | GRM155R72A221KA01# |           |

| T max. | Rated Voltage | TC Code | Cap.    | Tol.  | Part Number        |                    |
|--------|---------------|---------|---------|-------|--------------------|--------------------|
| 0.55mm | 100Vdc        | X7R     | 330pF   | ±10%  | GRM155R72A331KA01# |                    |
|        |               |         | 470pF   | ±10%  | GRM155R72A471KA01# |                    |
|        |               |         | 680pF   | ±10%  | GRM155R72A681KA01# |                    |
|        |               |         | 1000pF  | ±10%  | GRM155R72A102KA01# |                    |
|        |               |         | 1500pF  | ±10%  | GRM155R72A152KA01# |                    |
|        |               |         | 2200pF  | ±10%  | GRM155R72A222KA01# |                    |
|        |               |         | 3300pF  | ±10%  | GRM155R72A332KA01# |                    |
|        |               |         | 4700pF  | ±10%  | GRM155R72A472KA01# |                    |
|        |               | 50Vdc   | X7R     | 220pF | ±10%               | GRM155R71H221KA01# |
|        |               |         |         |       |                    |                    |
|        |               |         | 330pF   | ±10%  | GRM155R71H331KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 470pF   | ±10%  | GRM155R71H471KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 680pF   | ±10%  | GRM155R71H681KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 1000pF  | ±10%  | GRM155R71H102KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 1500pF  | ±10%  | GRM155R71H152KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 2200pF  | ±10%  | GRM155R71H222KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 3300pF  | ±10%  | GRM155R71H332KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 4700pF  | ±10%  | GRM155R71H472KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 6800pF  | ±10%  | GRM155R71H682KA88# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 10000pF | ±10%  | GRM155R71H103KA88# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 15000pF | ±10%  | GRM155R71H153KA12# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 22000pF | ±10%  | GRM155R71H223KA12# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 33000pF | ±10%  | GRM155R71H333KE14# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 47000pF | ±10%  | GRM155R71H473KE14# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 68000pF | ±10%  | GRM155R71H683KE14# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 0.10μF  | ±10%  | GRM155R71H104KE14# |                    |
|        |               |         |         |       |                    |                    |
|        |               | R       | 220pF   | ±10%  | GRM155R11H221KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 330pF   | ±10%  | GRM155R11H331KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 470pF   | ±10%  | GRM155R11H471KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 680pF   | ±10%  | GRM155R11H681KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 1000pF  | ±10%  | GRM155R11H102KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 1500pF  | ±10%  | GRM155R11H152KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 2200pF  | ±10%  | GRM155R11H222KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 3300pF  | ±10%  | GRM155R11H332KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 4700pF  | ±10%  | GRM155R11H472KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 6800pF  | ±10%  | GRM155R11H682KA88# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 10000pF | ±10%  | GRM155R11H103KA88# |                    |
|        |               |         |         |       |                    |                    |
|        |               | X5R     | 33000pF | ±10%  | GRM155R61H333KE19# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 47000pF | ±10%  | GRM155R61H473KE19# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 68000pF | ±10%  | GRM155R61H683KE19# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 0.10μF  | ±10%  | GRM155R61H104KE14# |                    |
|        |               |         |         |       |                    |                    |
|        |               | B       | 220pF   | ±10%  | GRM155B11H221KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 330pF   | ±10%  | GRM155B11H331KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | 470pF   | ±10%  | GRM155B11H471KA01# |                    |
|        |               |         |         |       |                    |                    |
|        |               |         | ±20%    |       | GRM155B11H471MA01# |                    |
|        |               |         |         |       |                    |                    |

Part number # indicates the package specification code.

## GRM Series High Dielectric Constant Type Part Number List

(→ ■ 1.0×0.5mm)

| T max.  | Rated Voltage | TC Code | Cap.               | Tol.               | Part Number        |                    |  |
|---------|---------------|---------|--------------------|--------------------|--------------------|--------------------|--|
| 0.55mm  | 50Vdc         | B       | 680pF              | ±10%               | GRM155B11H681KA01# |                    |  |
|         |               |         |                    | ±20%               | GRM155B11H681MA01# |                    |  |
|         |               |         | 1000pF             | ±10%               | GRM155B11H102KA01# |                    |  |
|         |               |         |                    | ±20%               | GRM155B11H102MA01# |                    |  |
|         |               |         | 1500pF             | ±10%               | GRM155B11H152KA01# |                    |  |
|         |               |         |                    | ±20%               | GRM155B11H152MA01# |                    |  |
|         |               |         | 2200pF             | ±10%               | GRM155B11H222KA01# |                    |  |
|         |               |         |                    | ±20%               | GRM155B11H222MA01# |                    |  |
|         |               |         | 3300pF             | ±10%               | GRM155B11H332KA01# |                    |  |
|         |               |         |                    | ±20%               | GRM155B11H332MA01# |                    |  |
|         |               |         | 4700pF             | ±10%               | GRM155B11H472KA01# |                    |  |
|         |               |         |                    | ±20%               | GRM155B11H472MA01# |                    |  |
|         |               |         | 6800pF             | ±10%               | GRM155B31H682KA88# |                    |  |
|         |               |         |                    | ±20%               | GRM155B31H682MA88# |                    |  |
|         |               |         | 10000pF            | ±10%               | GRM155B31H103KA88# |                    |  |
|         |               |         |                    | ±20%               | GRM155B31H103MA88# |                    |  |
|         |               |         | 15000pF            | ±10%               | GRM155B31H153KA12# |                    |  |
|         |               |         |                    | ±20%               | GRM155B31H153MA12# |                    |  |
|         |               |         | 22000pF            | ±10%               | GRM155B31H223KA12# |                    |  |
|         |               |         |                    | ±20%               | GRM155B31H223MA12# |                    |  |
|         |               |         | 0.10μF             | ±10%               | GRM155B31H104KE14# |                    |  |
|         |               |         |                    | ±20%               | GRM155B31H104ME14# |                    |  |
|         | 25Vdc         | X7R     | 10000pF            | ±10%               | GRM155R71E103KA01# |                    |  |
|         |               |         | 15000pF            | ±10%               | GRM155R71E153KA61# |                    |  |
|         |               |         | 22000pF            | ±10%               | GRM155R71E223KA61# |                    |  |
|         |               |         | 33000pF            | ±10%               | GRM155R71E333KA88# |                    |  |
|         |               |         | 47000pF            | ±10%               | GRM155R71E473KA88# |                    |  |
|         |               |         | 68000pF            | ±10%               | GRM155R71E683KE14# |                    |  |
|         |               |         |                    | ±20%               | GRM155R71E683ME14# |                    |  |
|         |               |         | 0.10μF             | ±10%               | GRM155R71E104KE14# |                    |  |
|         |               |         |                    | ±20%               | GRM155R71E104ME14# |                    |  |
|         |               |         | R                  | 6800pF             | ±10%               | GRM155R11E682KA01# |  |
|         |               |         |                    | 10000pF            | ±10%               | GRM155R11E103KA01# |  |
|         |               |         |                    | 15000pF            | ±10%               | GRM155R11E153KA61# |  |
|         |               |         |                    | 22000pF            | ±10%               | GRM155R11E223KA61# |  |
|         |               |         |                    | 33000pF            | ±10%               | GRM155R11E333KA88# |  |
|         |               | 47000pF |                    | ±10%               | GRM155R11E473KA88# |                    |  |
|         |               | X5R     | 68000pF            | ±10%               | GRM155R61E683KA87# |                    |  |
|         |               |         |                    | ±20%               | GRM155R61E683MA87# |                    |  |
|         |               |         | 0.10μF             | ±10%               | GRM155R61E104KA87# |                    |  |
| ±20%    |               |         |                    | GRM155R61E104MA87# |                    |                    |  |
| 0.47μF  |               |         | ±10%               | GRM155R61E474KA12# | Derating           |                    |  |
|         |               |         | ±20%               | GRM155R61E474MA12# | Derating           |                    |  |
| 1.0μF   |               |         | ±10%               | GRM155R61E105KA12# | Derating           |                    |  |
|         |               |         | ±20%               | GRM155R61E105MA12# | Derating           |                    |  |
| B       |               | 10000pF | ±10%               | GRM155B11E103KA01# |                    |                    |  |
|         |               |         | ±20%               | GRM155B11E103MA01# |                    |                    |  |
|         |               | 15000pF | ±10%               | GRM155B11E153KA61# |                    |                    |  |
|         |               |         | ±20%               | GRM155B11E153MA61# |                    |                    |  |
|         |               | 22000pF | ±10%               | GRM155B11E223KA61# |                    |                    |  |
|         |               |         | ±20%               | GRM155B11E223MA61# |                    |                    |  |
|         |               | 33000pF | ±10%               | GRM155B31E333KA87# |                    |                    |  |
|         |               |         | ±20%               | GRM155B31E333MA87# |                    |                    |  |
| 47000pF |               | ±10%    | GRM155B31E473KA87# |                    |                    |                    |  |

| T max. | Rated Voltage | TC Code | Cap.    | Tol.   | Part Number        |          |
|--------|---------------|---------|---------|--------|--------------------|----------|
| 0.55mm | 25Vdc         | B       | 47000pF | ±20%   | GRM155B31E473MA87# |          |
|        |               |         |         | ±10%   | GRM155B31E683KA87# |          |
|        |               |         | 68000pF | ±10%   | GRM155B31E683MA87# |          |
|        |               |         |         | ±20%   | GRM155B31E104KA87# |          |
|        |               |         | 0.10μF  | ±10%   | GRM155B31E104MA87# |          |
|        |               |         |         | ±20%   | GRM155B31E105KA12# | Derating |
|        |               |         | 1.0μF   | ±10%   | GRM155B31E105MA12# | Derating |
|        |               |         |         | ±20%   | GRM155R71C683KA88# |          |
|        |               | 16Vdc   | X7R     | 0.15μF | GRM155R71C154KA12# |          |
|        |               |         |         | ±10%   | GRM155R71C224KA12# |          |
|        |               |         |         | ±20%   | GRM155R11C683KA88# |          |
|        |               |         | R       | 0.22μF | GRM155R61C224KA12# |          |
|        |               |         |         | ±10%   | GRM155R61C224MA12# |          |
|        |               |         |         | ±20%   | GRM155R61C105KA12# |          |
|        |               | X5R     | 0.22μF  | ±10%   | GRM155R61C105MA12# |          |
|        |               |         |         | ±20%   | GRM155B31C105KA12# |          |
|        |               |         |         | ±20%   | GRM155B31C105MA12# |          |
|        |               |         | 1.0μF   | ±10%   | GRM155C81A105KA12# |          |
|        |               |         |         | ±20%   | GRM155C81A105MA12# |          |
|        |               |         |         | ±20%   | GRM155R61A154KE19# |          |
|        | 16Vdc         | X6S     | 0.15μF  | ±10%   | GRM155R61A154ME19# |          |
|        |               |         |         | ±20%   | GRM155R61A224KE19# |          |
|        |               |         |         | ±20%   | GRM155R61A224ME19# |          |
|        |               |         | 0.33μF  | ±10%   | GRM155R61A334KE15# |          |
|        |               |         |         | ±20%   | GRM155R61A334ME15# |          |
|        |               |         |         | ±20%   | GRM155R61A474KE15# |          |
|        |               |         | 0.47μF  | ±10%   | GRM155R61A474ME15# |          |
|        |               |         |         | ±20%   | GRM155R61A684KE15# |          |
|        |               |         |         | ±20%   | GRM155R61A684ME15# |          |
|        |               | X5R     | 0.15μF  | ±10%   | GRM155B31A154KE18# |          |
|        |               |         |         | ±20%   | GRM155B31A154ME18# |          |
|        |               |         |         | ±20%   | GRM155B31A224KE18# |          |
|        |               |         | 0.22μF  | ±10%   | GRM155B31A224ME18# |          |
|        |               |         |         | ±20%   | GRM155B31A334KE14# |          |
|        |               |         |         | ±20%   | GRM155B31A334ME14# |          |
|        |               |         | 0.33μF  | ±10%   | GRM155B31A474KE14# |          |
|        |               |         |         | ±20%   | GRM155B31A474ME14# |          |
|        |               |         |         | ±20%   | GRM155B31A684KE15# |          |
|        |               |         | 0.68μF  | ±10%   | GRM155B31A684ME15# |          |
|        |               |         |         | ±20%   | GRM155B31A225KE95# | Derating |
|        |               |         |         | ±20%   | GRM155B31A225ME95# | Derating |
|        | 6.3Vdc        | X7R     | 1.0μF   | ±10%   | GRM155R70J105KA12# | Derating |
|        |               |         |         | ±20%   | GRM155R70J105MA12# | Derating |
|        |               |         |         | ±20%   | GRM155C80J225KE95# | Derating |
|        |               |         | 2.2μF   | ±10%   | GRM155C80J225ME95# | Derating |
|        |               |         |         | ±20%   | GRM155R60J154KE01# |          |
|        |               |         |         | ±20%   | GRM155R60J154ME01# |          |
|        |               | X6S     | 0.15μF  | ±10%   | GRM155R60J224KE01# |          |
|        |               |         |         | ±20%   | GRM155R60J224ME01# |          |
|        |               |         |         | ±20%   | GRM155R60J334KE01# |          |
|        |               |         | 0.22μF  | ±10%   | GRM155R60J334ME01# |          |
|        |               |         |         | ±20%   | GRM155R60J474KE19# |          |
|        |               |         |         | ±20%   | GRM155R60J474ME19# |          |
|        |               | X5R     | 0.33μF  | ±10%   | GRM155R60J684KE19# |          |
|        |               |         |         | ±20%   | GRM155R60J684ME19# |          |
|        |               |         |         | ±20%   | GRM155R60J684KE19# |          |
|        |               |         | 0.47μF  | ±10%   | GRM155R60J684ME19# |          |
|        |               |         |         | ±20%   | GRM155R60J684KE19# |          |
|        |               |         |         | ±20%   | GRM155R60J684KE19# |          |

Part number # indicates the package specification code.

## GRM Series High Dielectric Constant Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |                                                                                     |
|--------|---------------|---------|--------|------|--------------------|-------------------------------------------------------------------------------------|
| 0.55mm | 6.3Vdc        | X5R     | 0.68μF | ±20% | GRM155R60J684ME19# |                                                                                     |
|        |               |         | 0.15μF | ±10% | GRM155B10J154KE01# |                                                                                     |
|        |               |         |        | ±20% | GRM155B10J154ME01# |                                                                                     |
|        |               |         |        |      |                    |                                                                                     |
|        |               |         | 0.22μF | ±10% | GRM155B10J224KE01# |                                                                                     |
|        |               |         |        | ±20% | GRM155B10J224ME01# |                                                                                     |
|        |               |         | 0.33μF | ±10% | GRM155B10J334KE01# |                                                                                     |
|        |               |         |        | ±20% | GRM155B10J334ME01# |                                                                                     |
|        |               | X7R     | 0.47μF | ±10% | GRM155B30J474KE18# |                                                                                     |
|        |               |         |        | ±20% | GRM155B30J474ME18# |                                                                                     |
|        |               |         | 0.68μF | ±10% | GRM155B30J684KE18# |                                                                                     |
|        |               |         |        | ±20% | GRM155B30J684ME18# |                                                                                     |
|        |               | X7R     | 2.2μF  | ±10% | GRM155B30J225KE95# |                                                                                     |
|        |               |         |        | ±20% | GRM155B30J225ME95# |                                                                                     |
|        |               |         | 1.0μF  | ±10% | GRM155R70G105KA12# |                                                                                     |
|        |               |         |        | ±20% | GRM155R70G105MA12# |                                                                                     |
| 0.6mm  | 35Vdc         | X5R     | 1.0μF  | ±10% | GRM155R6YA105KE11# |    |
|        |               |         |        | ±20% | GRM155R6YA105ME11# |    |
|        |               |         |        |      |                    |                                                                                     |
|        | 25Vdc         | X6S     | 1.0μF  | ±10% | GRM155C81E105KE11# |    |
|        |               |         |        | ±20% | GRM155C81E105ME11# |    |
|        | 16Vdc         | X6S     | 1.0μF  | ±10% | GRM155C81C105KE11# |                                                                                     |
|        |               |         |        | ±20% | GRM155C81C105ME11# |                                                                                     |
|        | 6.3Vdc        | X5R     | 4.7μF  | ±20% | GRM155R60J475ME47# |  |
|        |               | B       | 4.7μF  | ±20% | GRM155B30J475ME47# |  |
|        | 4Vdc          | X5R     | 4.7μF  | ±20% | GRM155R60G475ME47# |                                                                                     |
|        |               | B       | 4.7μF  | ±20% | GRM155B30G475ME47# |                                                                                     |
| 0.7mm  | 2.5Vdc        | X6T     | 4.7μF  | ±20% | GRM155D80E475ME47# |  |
|        | 25Vdc         | X5R     | 2.2μF  | ±10% | GRM155R61E225KE11# |                                                                                     |
|        |               |         |        | ±20% | GRM155R61E225ME11# |                                                                                     |
|        | 16Vdc         | X6S     | 2.2μF  | ±10% | GRM155C81C225KE11# |                                                                                     |
|        |               |         |        | ±20% | GRM155C81C225ME11# |                                                                                     |
|        |               | X5R     | 2.2μF  | ±10% | GRM155R61C225KE11# |                                                                                     |
|        |               |         |        | ±20% | GRM155R61C225ME11# |                                                                                     |
|        | 10Vdc         | X7S     | 2.2μF  | ±10% | GRM155C71A225KE11# |                                                                                     |
|        |               |         |        | ±20% | GRM155C71A225ME11# |                                                                                     |
|        |               | X6S     | 2.2μF  | ±10% | GRM155C81A225KE11# |                                                                                     |
|        |               |         |        | ±20% | GRM155C81A225ME11# |                                                                                     |
|        | 6.3Vdc        | X7S     | 2.2μF  | ±10% | GRM155C70J225KE11# |                                                                                     |
|        |               |         |        | ±20% | GRM155C70J225ME11# |                                                                                     |
|        | 4Vdc          | X5R     | 10μF   | ±20% | GRM155R60G106ME44# |                                                                                     |
|        | 2.5Vdc        | X5R     | 10μF   | ±20% | GRM155R60E106ME16# |                                                                                     |

■ 1.6×0.8mm

| T max. | Rated Voltage | TC Code | Cap.  | Tol. | Part Number        |                                                                                     |
|--------|---------------|---------|-------|------|--------------------|-------------------------------------------------------------------------------------|
| 0.5mm  | 25Vdc         | X5R     | 1.0μF | ±10% | GRM185R61E105KA12# |  |
|        |               |         |       | ±20% | GRM185R61E105MA12# |  |
|        |               | B       | 1.0μF | ±10% | GRM185B31E105KA12# |  |
|        |               |         |       | ±20% | GRM185B31E105MA12# |  |
|        | 16Vdc         | X5R     | 1.0μF | ±10% | GRM185R61C105KE44# |                                                                                     |
|        |               |         |       | ±20% | GRM185R61C105ME44# |                                                                                     |
|        |               | B       | 1.0μF | ±10% | GRM185B31C105KE43# |                                                                                     |
|        |               |         |       | ±20% | GRM185B31C105ME43# |                                                                                     |
| 0.9mm  | 250Vdc        | X7R     | 220pF | ±10% | GRM188R72E221KW07# |                                                                                     |

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.9mm  | 250Vdc        | X7R     | 330pF   | ±10% | GRM188R72E331KW07# |  |
|        |               |         | 470pF   | ±10% | GRM188R72E471KW07# |  |
|        |               |         | 680pF   | ±10% | GRM188R72E681KW07# |  |
|        |               |         | 1000pF  | ±10% | GRM188R72E102KW07# |  |
|        |               |         | 1500pF  | ±10% | GRM188R72E152KW07# |  |
|        |               |         | 2200pF  | ±10% | GRM188R72E222KW07# |  |
|        |               | X7R     | 220pF   | ±10% | GRM188R72D221KW07# |  |
|        |               |         | 330pF   | ±10% | GRM188R72D331KW07# |  |
|        |               |         | 470pF   | ±10% | GRM188R72D471KW07# |  |
|        |               |         | 680pF   | ±10% | GRM188R72D681KW07# |  |
|        |               |         | 1000pF  | ±10% | GRM188R72D102KW07# |  |
|        |               |         | 1500pF  | ±10% | GRM188R72D152KW07# |  |
|        |               |         | 2200pF  | ±10% | GRM188R72D222KW07# |  |
|        | 100Vdc        | X7R     | 220pF   | ±10% | GRM188R72A221KA01# |  |
|        |               |         | 330pF   | ±10% | GRM188R72A331KA01# |  |
|        |               |         | 470pF   | ±10% | GRM188R72A471KA01# |  |
|        |               |         | 680pF   | ±10% | GRM188R72A681KA01# |  |
|        |               |         | 1000pF  | ±10% | GRM188R72A102KA01# |  |
|        |               |         | 1500pF  | ±10% | GRM188R72A152KA01# |  |
|        |               |         | 2200pF  | ±10% | GRM188R72A222KA01# |  |
|        |               |         | 3300pF  | ±10% | GRM188R72A332KA01# |  |
|        |               |         | 4700pF  | ±10% | GRM188R72A472KA01# |  |
|        |               |         | 6800pF  | ±10% | GRM188R72A682KA01# |  |
|        |               |         | 10000pF | ±10% | GRM188R72A103KA01# |  |
|        |               |         | 15000pF | ±10% | GRM188R72A153KAC4# |  |
|        |               |         |         | ±20% | GRM188R72A153MAC4# |  |
|        |               |         | 22000pF | ±10% | GRM188R72A223KAC4# |  |
|        |               |         |         | ±20% | GRM188R72A223MAC4# |  |
|        | 50Vdc         | X7R     | 220pF   | ±10% | GRM188R71H221KA01# |  |
|        |               |         | 330pF   | ±10% | GRM188R71H331KA01# |  |
|        |               |         | 470pF   | ±10% | GRM188R71H471KA01# |  |
|        |               |         | 680pF   | ±10% | GRM188R71H681KA01# |  |
|        |               |         | 1000pF  | ±10% | GRM188R71H102KA01# |  |
|        |               |         | 1500pF  | ±10% | GRM188R71H152KA01# |  |
|        |               |         | 2200pF  | ±10% | GRM188R71H222KA01# |  |
|        |               |         | 3300pF  | ±10% | GRM188R71H332KA01# |  |
|        |               |         | 4700pF  | ±10% | GRM188R71H472KA01# |  |
|        |               |         | 6800pF  | ±10% | GRM188R71H682KA01# |  |
|        |               |         | 10000pF | ±10% | GRM188R71H103KA01# |  |
|        |               |         | 15000pF | ±10% | GRM188R71H153KA01# |  |
|        |               |         | 22000pF | ±10% | GRM188R71H223KA01# |  |
|        |               |         | 33000pF | ±10% | GRM188R71H333KA61# |  |
|        |               |         | 47000pF | ±10% | GRM188R71H473KA61# |  |
|        |               |         | 68000pF | ±10% | GRM188R71H683KA93# |  |
|        |               |         | 0.10μF  | ±10% | GRM188R71H104KA93# |  |
|        |               | R       | 220pF   | ±10% | GRM188R11H221KA01# |  |
|        |               |         | 330pF   | ±10% | GRM188R11H331KA01# |  |
|        |               |         | 470pF   | ±10% | GRM188R11H471KA01# |  |
|        |               |         | 680pF   | ±10% | GRM188R11H681KA01# |  |
|        |               |         | 1000pF  | ±10% | GRM188R11H102KA01# |  |
|        |               |         | 1500pF  | ±10% | GRM188R11H152KA01# |  |
|        |               |         | 2200pF  | ±10% | GRM188R11H222KA01# |  |
|        |               |         | 3300pF  | ±10% | GRM188R11H332KA01# |  |
|        |               |         | 4700pF  | ±10% | GRM188R11H472KA01# |  |

Part number # indicates the package specification code.



## GRM Series High Dielectric Constant Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.9mm  | 50Vdc         | R       | 6800pF  | ±10% | GRM188R11H682KA01# |  |
|        |               |         | 10000pF | ±10% | GRM188R11H103KA01# |  |
|        |               |         | 15000pF | ±10% | GRM188R11H153KA01# |  |
|        |               |         | 22000pF | ±10% | GRM188R11H223KA01# |  |
|        |               |         | 33000pF | ±10% | GRM188R11H333KA61# |  |
|        |               |         | 47000pF | ±10% | GRM188R11H473KA61# |  |
|        |               |         | 68000pF | ±10% | GRM188R11H683KA93# |  |
|        |               |         | 0.10μF  | ±10% | GRM188R11H104KA93# |  |
|        |               | X5R     | 0.47μF  | ±10% | GRM188R61H474KA12# |  |
|        |               |         |         | ±20% | GRM188R61H474MA12# |  |
|        |               |         | 1.0μF   | ±10% | GRM188R61H105KAAL# |  |
|        |               |         |         | ±20% | GRM188R61H105MAAL# |  |
|        |               | B       | 220pF   | ±10% | GRM188B11H221KA01# |  |
|        |               |         |         | ±20% | GRM188B11H221MA01# |  |
|        |               |         | 330pF   | ±10% | GRM188B11H331KA01# |  |
|        |               |         |         | ±20% | GRM188B11H331MA01# |  |
|        |               |         | 470pF   | ±10% | GRM188B11H471KA01# |  |
|        |               |         |         | ±20% | GRM188B11H471MA01# |  |
|        |               |         | 680pF   | ±10% | GRM188B11H681KA01# |  |
|        |               |         |         | ±20% | GRM188B11H681MA01# |  |
|        |               |         | 1000pF  | ±10% | GRM188B11H102KA01# |  |
|        |               |         |         | ±20% | GRM188B11H102MA01# |  |
|        |               |         | 1500pF  | ±10% | GRM188B11H152KA01# |  |
|        |               |         |         | ±20% | GRM188B11H152MA01# |  |
|        |               |         | 2200pF  | ±10% | GRM188B11H222KA01# |  |
|        |               |         |         | ±20% | GRM188B11H222MA01# |  |
|        |               |         | 3300pF  | ±10% | GRM188B11H332KA01# |  |
|        |               |         |         | ±20% | GRM188B11H332MA01# |  |
|        |               |         | 4700pF  | ±10% | GRM188B11H472KA01# |  |
|        |               |         |         | ±20% | GRM188B11H472MA01# |  |
|        |               |         | 6800pF  | ±10% | GRM188B11H682KA01# |  |
|        |               |         |         | ±20% | GRM188B11H682MA01# |  |
|        |               |         | 10000pF | ±10% | GRM188B11H103KA01# |  |
|        |               |         |         | ±20% | GRM188B11H103MA01# |  |
|        |               |         | 15000pF | ±10% | GRM188B11H153KA01# |  |
|        |               |         |         | ±20% | GRM188B11H153MA01# |  |
|        |               |         | 22000pF | ±10% | GRM188B11H223KA01# |  |
|        |               |         |         | ±20% | GRM188B11H223MA01# |  |
|        |               |         | 33000pF | ±10% | GRM188B11H333KA61# |  |
|        |               |         |         | ±20% | GRM188B11H333MA61# |  |
|        |               |         | 47000pF | ±10% | GRM188B11H473KA61# |  |
|        |               |         |         | ±20% | GRM188B11H473MA61# |  |
|        |               |         | 68000pF | ±10% | GRM188B31H683KA92# |  |
|        |               |         |         | ±20% | GRM188B31H683MA92# |  |
|        |               |         | 0.10μF  | ±10% | GRM188B31H104KA92# |  |
|        |               |         |         | ±20% | GRM188B31H104MA92# |  |
|        |               |         | 1.0μF   | ±10% | GRM188B31H105KAAL# |  |
|        |               |         |         | ±20% | GRM188B31H105MAAL# |  |
|        | 25Vdc         | X7R     | 33000pF | ±10% | GRM188R71E333KA01# |  |
|        |               |         | 47000pF | ±10% | GRM188R71E473KA01# |  |
|        |               |         | 68000pF | ±10% | GRM188R71E683KA01# |  |
|        |               |         | 0.15μF  | ±10% | GRM188R71E154KA01# |  |
|        |               |         | 0.22μF  | ±10% | GRM188R71E224KA88# |  |
|        |               |         | 1.0μF   | ±10% | GRM188R71E105KA12# |  |

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.9mm  | 25Vdc         | X7R     | 1.0μF   | ±20% | GRM188R71E105MA12# |  |
|        |               |         | 33000pF | ±10% | GRM188R11E333KA01# |  |
|        |               |         |         | ±10% | GRM188R11E473KA01# |  |
|        |               |         |         | ±10% | GRM188R11E683KA01# |  |
|        |               |         | 0.15μF  | ±10% | GRM188R11E154KA01# |  |
|        |               |         |         | ±10% | GRM188R11E224KA88# |  |
|        |               | X5R     | 0.22μF  | ±10% | GRM188R61E224KA88# |  |
|        |               |         |         | ±10% | GRM188R61E474KA12# |  |
|        |               |         | 0.47μF  | ±20% | GRM188R61E474MA12# |  |
|        |               |         |         | ±10% | GRM188R61E684KA75# |  |
|        |               |         | 0.68μF  | ±10% | GRM188R61E684MA75# |  |
|        |               |         |         | ±20% | GRM188R61E105KA12# |  |
|        |               |         | 1.0μF   | ±10% | GRM188R61E105MA12# |  |
|        |               |         |         | ±20% | GRM188R61E225KA12# |  |
|        |               |         | 2.2μF   | ±10% | GRM188R61E225MA12# |  |
|        |               |         |         | ±20% | GRM188B11E103KA01# |  |
|        |               | B       | 10000pF | ±10% | GRM188B11E103KA01# |  |
|        |               |         |         | ±20% | GRM188B11E103MA01# |  |
|        |               |         | 15000pF | ±10% | GRM188B11E153KA01# |  |
|        |               |         |         | ±20% | GRM188B11E153MA01# |  |
|        |               |         | 22000pF | ±10% | GRM188B11E223KA01# |  |
|        |               |         |         | ±20% | GRM188B11E223MA01# |  |
|        |               |         | 33000pF | ±10% | GRM188B11E333KA01# |  |
|        |               |         |         | ±20% | GRM188B11E333MA01# |  |
|        |               |         | 47000pF | ±10% | GRM188B11E473KA01# |  |
|        |               |         |         | ±20% | GRM188B11E473MA01# |  |
|        |               |         | 68000pF | ±10% | GRM188B11E683KA01# |  |
|        |               |         |         | ±20% | GRM188B11E683MA01# |  |
|        |               |         | 0.10μF  | ±10% | GRM188B11E104KA01# |  |
|        |               |         |         | ±20% | GRM188B11E104MA01# |  |
|        |               |         | 0.15μF  | ±10% | GRM188B11E154KA01# |  |
|        |               |         |         | ±10% | GRM188B31E224KA87# |  |
|        |               |         | 0.22μF  | ±10% | GRM188B31E474KA75# |  |
|        |               |         |         | ±20% | GRM188B31E474MA75# |  |
|        |               |         | 0.68μF  | ±10% | GRM188B31E684KA75# |  |
|        |               |         |         | ±20% | GRM188B31E684MA75# |  |
|        |               |         | 1.0μF   | ±10% | GRM188B31E105KA75# |  |
|        |               |         |         | ±20% | GRM188B31E105MA75# |  |
|        |               |         | 2.2μF   | ±10% | GRM188B31E225KA12# |  |
|        |               |         |         | ±20% | GRM188B31E225MA12# |  |
|        | 16Vdc         | X7R     | 0.15μF  | ±10% | GRM188R71C154KA01# |  |
|        |               |         |         | ±10% | GRM188R71C224KA01# |  |
|        |               |         | 0.33μF  | ±10% | GRM188R71C334KA01# |  |
|        |               |         |         | ±10% | GRM188R71C474KA88# |  |
|        |               |         | 1.0μF   | ±10% | GRM188R71C105KE15# |  |
|        |               |         |         | ±20% | GRM188R71C105ME15# |  |
|        |               | R       | 0.33μF  | ±10% | GRM188R11C334KA01# |  |
|        |               |         |         | ±10% | GRM188R11C474KA88# |  |
|        |               | X6S     | 2.2μF   | ±10% | GRM188C81C225KA12# |  |
|        |               |         |         | ±20% | GRM188C81C225MA12# |  |
|        |               | X5R     | 0.68μF  | ±10% | GRM188R61C684KA75# |  |
|        |               |         |         | ±20% | GRM188R61C684MA75# |  |
|        |               | B       | 2.2μF   | ±10% | GRM188R61C225KE15# |  |
|        |               |         |         | ±10% | GRM188B11C334KA01# |  |
|        |               |         | 0.33μF  | ±10% | GRM188B11C334MA01# |  |
|        |               |         |         | ±20% | GRM188B11C334MA01# |  |

Part number # indicates the package specification code.



# GRM Series High Dielectric Constant Type Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |           |
|--------|---------------|---------|--------|------|--------------------|-----------|
| 0.9mm  | 16Vdc         | B       | 0.68μF | ±10% | GRM188B31C684KA75# |           |
|        |               |         |        | ±20% | GRM188B31C684MA75# |           |
|        |               |         | 2.2μF  | ±10% | GRM188B31C225KE14# |           |
|        | 10Vdc         | X7R     | 0.33μF | ±10% | GRM188R71A334KA61# |           |
|        |               |         |        | ±20% | GRM188R71A334MA61# |           |
|        |               |         | 0.68μF | ±10% | GRM188R71A684KA61# |           |
|        |               |         |        | ±20% | GRM188R71A684MA61# |           |
|        |               |         | 2.2μF  | ±10% | GRM188R71A225KE15# |           |
|        |               |         |        | ±20% | GRM188R71A225ME15# |           |
|        |               | X7T     | 2.2μF  | ±10% | GRM188D71A225KE34# |           |
|        |               |         |        | ±20% | GRM188D71A225ME34# |           |
|        |               | X5R     | 0.33μF | ±10% | GRM188R61A334KA61# |           |
|        |               |         |        | ±20% | GRM188R61A334MA61# |           |
|        |               | B       | 0.33μF | ±10% | GRM188B11A334KA61# |           |
|        |               |         |        | ±20% | GRM188B11A334MA61# |           |
| 0.95mm | 6.3Vdc        | B       | 10μF   | ±20% | GRM188B30J106ME47# |           |
|        | 25Vdc         | X5R     | 4.7μF  | ±10% | GRM188R61E475KE11# |           |
|        |               |         |        | ±20% | GRM188R61E475ME11# |           |
|        | 16Vdc         | X6S     | 4.7μF  | ±10% | GRM188C81C475KE11# |           |
|        |               |         |        | ±20% | GRM188C81C475ME11# |           |
|        |               |         |        |      |                    |           |
|        |               | X5R     | 4.7μF  | ±10% | GRM188R61C475KE11# |           |
|        |               |         |        | ±20% | GRM188R61C475ME11# |           |
|        |               |         |        |      |                    |           |
|        |               | B       | 4.7μF  | ±10% | GRM188B31C475KAAJ# | Degrating |
|        |               |         |        | ±20% | GRM188B31C475MAAJ# | Degrating |
|        | 10Vdc         | X7S     | 4.7μF  | ±10% | GRM188C71A475KE11# |           |
|        |               |         |        | ±20% | GRM188C71A475ME11# |           |
|        |               | B       | 10μF   | ±20% | GRM188B31A106ME69# | Degrating |
| 1.0mm  | 50Vdc         | X5R     | 2.2μF  | ±10% | GRM188R61H225KE11# |           |
|        |               |         |        | ±20% | GRM188R61H225ME11# |           |
|        |               | X6S     | 2.2μF  | ±10% | GRM188C8YA225KE11# |           |
|        |               |         |        | ±20% | GRM188C8YA225ME11# |           |
|        | 25Vdc         | X5R     | 4.7μF  | ±10% | GRM188R6YA475KE15# |           |
|        |               |         |        | ±20% | GRM188R6YA475ME15# |           |
|        |               |         |        |      |                    |           |
|        |               |         |        |      |                    |           |
|        |               | X7S     | 2.2μF  | ±10% | GRM188C71E225KE11# |           |
|        |               |         |        | ±20% | GRM188C71E225ME11# |           |
|        |               |         |        |      |                    |           |
|        |               |         |        |      |                    |           |
|        |               | X6S     | 2.2μF  | ±10% | GRM188C81E225KE11# |           |
|        |               |         |        | ±20% | GRM188C81E225ME11# |           |
|        |               |         |        |      |                    |           |
|        |               |         |        |      |                    |           |
|        |               | X5R     | 10μF   | ±20% | GRM188R61E106MA73# |           |
|        |               |         |        |      |                    |           |
|        |               |         |        |      |                    |           |
|        |               |         |        |      |                    |           |
|        | 16Vdc         | X7S     | 2.2μF  | ±10% | GRM188C71C225KE11# |           |
|        |               |         |        | ±20% | GRM188C71C225ME11# |           |
|        |               | X6S     | 10μF   | ±20% | GRM188C81C106MA73# |           |
|        |               |         |        |      |                    |           |
|        | 10Vdc         | X7T     | 10μF   | ±20% | GRM188D71A106MA73# |           |
|        |               |         |        |      |                    |           |
|        |               | X5R     | 22μF   | ±20% | GRM188R60J226MEA0# | Degrating |
|        |               |         |        |      |                    |           |
|        | 6.3Vdc        | X7T     | 10μF   | ±20% | GRM188D70J106MA73# |           |
|        |               |         |        |      |                    |           |
|        |               | X5R     | 22μF   | ±20% | GRM188R60G226MEA0# | Degrating |
|        |               |         |        |      |                    |           |
|        | 4Vdc          | X6S     | 22μF   | ±20% | GRM188C80G226MEA0# | Degrating |
|        |               |         |        |      |                    |           |
|        |               | X5R     | 22μF   | ±20% | GRM188R60G226MEA0# | Degrating |
|        |               |         |        |      |                    |           |
|        |               | B       | 22μF   | ±20% | GRM188B30G226MEA0# |           |
|        |               |         |        |      |                    |           |

■ 2.0×1.25mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |           |
|--------|---------------|---------|---------|------|--------------------|-----------|
| 0.7mm  | 16Vdc         | X6S     | 1.0μF   | ±10% | GRM216C81C105KA12# |           |
| 0.95mm | 100Vdc        | X7R     | 10000pF | ±10% | GRM219R72A103KA01# |           |
|        |               |         |         | ±20% | GRM219R72A103MA01# |           |
|        |               |         | 10000pF | ±10% | GRM219R71H103KA01# |           |
|        |               |         |         | ±20% | GRM219R71H103MA01# |           |
|        |               |         | 15000pF | ±10% | GRM219R71H153KA01# |           |
|        |               |         |         | ±20% | GRM219R71H153MA01# |           |
|        | 50Vdc         | X7R     | 33000pF | ±10% | GRM219R71H333KA01# |           |
|        |               |         |         | ±20% | GRM219R71H333MA01# |           |
|        |               |         | 0.33μF  | ±10% | GRM219R71H334KA88# |           |
|        |               |         |         | ±20% | GRM219R71H334MA88# |           |
|        |               | R       | 33000pF | ±10% | GRM219R11H333KA01# |           |
|        |               |         |         |      |                    |           |
|        |               | X5R     | 1.0μF   | ±10% | GRM219R61H105KA73# |           |
|        |               |         |         | ±20% | GRM219R61H105MA73# |           |
|        |               |         | 2.2μF   | ±10% | GRM219R61H225KE15# |           |
|        |               |         |         | ±20% | GRM219R61H225ME15# |           |
|        |               | B       | 0.33μF  | ±10% | GRM219B31H334KA87# |           |
|        |               |         |         | ±20% | GRM219B31H334MA87# |           |
|        |               |         | 1.0μF   | ±10% | GRM219B31H105KA73# |           |
|        |               |         |         | ±20% | GRM219B31H105MA73# |           |
|        |               |         | 2.2μF   | ±10% | GRM219B31H225KE15# |           |
|        |               |         |         | ±20% | GRM219B31H225ME15# |           |
|        | 35Vdc         | X6S     | 2.2μF   | ±10% | GRM219C8YA225KE15# |           |
|        |               |         |         | ±20% | GRM219C8YA225ME15# |           |
|        |               | X5R     | 4.7μF   | ±10% | GRM219R6YA475KA73# | Degrating |
|        |               |         |         | ±20% | GRM219R6YA475MA73# | Degrating |
|        | 25Vdc         | X7R     | 0.10μF  | ±10% | GRM219R71E104KA01# |           |
|        |               |         |         | ±20% | GRM219R71E104MA01# |           |
|        |               |         | 0.68μF  | ±10% | GRM219R71E684KA88# |           |
|        |               |         |         | ±20% | GRM219R71E684MA88# |           |
|        |               |         | 1.0μF   | ±10% | GRM219R71E105KA88# |           |
|        |               |         |         | ±20% | GRM219R71E105MA88# |           |
|        |               | R       | 68000pF | ±10% | GRM219R11E683KA01# |           |
|        |               |         |         |      |                    |           |
|        |               | X6S     | 2.2μF   | ±10% | GRM219C81E225KE15# |           |
|        |               |         |         | ±20% | GRM219C81E225ME15# |           |
|        |               | X5R     | 2.2μF   | ±10% | GRM219R61E225KA12# |           |
|        |               |         |         | ±20% | GRM219R61E225MA12# |           |
|        |               |         | 4.7μF   | ±10% | GRM219R61E475KA73# |           |
|        |               |         |         | ±20% | GRM219R61E475MA73# |           |
|        |               | B       | 10μF    | ±10% | GRM219R61E106KA12# | Degrating |
|        |               |         |         | ±20% | GRM219R61E106MA12# | Degrating |
|        |               |         | 2.2μF   | ±10% | GRM219B31E225KA75# |           |
|        |               |         |         | ±20% | GRM219B31E225MA75# |           |
|        | 16Vdc         | X7R     | 0.33μF  | ±10% | GRM219R71C334KA88# |           |
|        |               |         |         | ±20% | GRM219R71C225KE15# |           |
|        |               |         | 2.2μF   | ±10% | GRM219R71C225ME15# |           |
|        |               |         |         | ±20% | GRM219R71C225ME15# |           |
|        |               | R       | 0.68μF  | ±10% | GRM219R11C684KA01# |           |
|        |               |         |         |      |                    |           |
|        |               |         | 4.7μF   | ±10% | GRM219C81C475KA73# |           |
|        |               |         |         | ±20% | GRM219C81C475MA73# |           |
|        |               | X5R     | 4.7μF   | ±10% | GRM219R61C475KE15# |           |
|        |               |         |         | ±20% | GRM219R61C106KA73# |           |
|        |               |         | 10μF    | ±10% | GRM219R61C106MA73# |           |
|        |               |         |         | ±20% | GRM219R61C106MA73# |           |
|        |               | B       | 4.7μF   | ±10% | GRM219B31C475KE15# |           |
|        |               |         |         | ±20% | GRM219B31C106KA73# |           |
|        |               |         | 10μF    | ±10% | GRM219B31C106MA73# |           |
|        |               |         |         | ±20% | GRM219B31C106MA73# |           |

Part number # indicates the package specification code.

## GRM Series High Dielectric Constant Type Part Number List

(→ ■ 2.0×1.25mm)

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |          |
|--------|---------------|---------|---------|------|--------------------|----------|
| 0.95mm | 16Vdc         | B       | 10μF    | ±20% | GRM219B31C106MA73# |          |
|        | 10Vdc         | X7R     | 2.2μF   | ±10% | GRM219R71A225KE15# |          |
|        |               |         |         | ±20% | GRM219R71A225ME15# |          |
|        |               |         |         |      |                    |          |
|        |               | X7T     | 4.7μF   | ±10% | GRM219D71A475KE15# | Derating |
|        |               |         |         | ±20% | GRM219D71A475ME15# | Derating |
|        |               | X5R     | 22μF    | ±20% | GRM219R61A226MEA0# | Derating |
|        |               | B       | 22μF    | ±20% | GRM219B31A226MEA0# | Derating |
|        | 6.3Vdc        | X6S     | 10μF    | ±10% | GRM219C80J106KE39# |          |
|        |               |         |         | ±20% | GRM219C80J106ME39# |          |
|        |               | X5R     | 22μF    | ±20% | GRM219R60J226ME47# | Derating |
|        |               | B       | 22μF    | ±20% | GRM219B30J226ME47# | Derating |
|        | 4Vdc          | X6S     | 10μF    | ±10% | GRM219C80G106KE19# |          |
|        |               |         |         | ±20% | GRM219C80G106ME19# |          |
|        |               | X5R     | 47μF    | ±20% | GRM219R60G476ME44# | Derating |
| 1.0mm  | 250Vdc        | X7R     | 1000pF  | ±10% | GRM21AR72E102KW01# |          |
|        |               |         | 1500pF  | ±10% | GRM21AR72E152KW01# |          |
|        |               |         | 2200pF  | ±10% | GRM21AR72E222KW01# |          |
|        |               |         | 3300pF  | ±10% | GRM21AR72E332KW01# |          |
|        |               |         | 4700pF  | ±10% | GRM21AR72E472KW01# |          |
|        |               |         | 6800pF  | ±10% | GRM21AR72E682KW01# |          |
|        | 200Vdc        | X7R     | 1000pF  | ±10% | GRM21AR72D102KW01# |          |
|        |               |         | 1500pF  | ±10% | GRM21AR72D152KW01# |          |
|        |               |         | 2200pF  | ±10% | GRM21AR72D222KW01# |          |
|        |               |         | 3300pF  | ±10% | GRM21AR72D332KW01# |          |
|        |               |         | 4700pF  | ±10% | GRM21AR72D472KW01# |          |
|        |               |         | 6800pF  | ±10% | GRM21AR72D682KW01# |          |
|        | 50Vdc         | X7R     | 22000pF | ±10% | GRM219R71H223KA17# |          |
|        |               |         |         | ±20% | GRM219R71H223MA17# |          |
|        | 16Vdc         | X5R     | 22μF    | ±20% | GRM219R61C226ME15# | Derating |
| 1.35mm | 100Vdc        | X7R     | 10000pF | ±10% | GRM21BR72A103KA01# |          |
|        |               |         | 15000pF | ±10% | GRM21BR72A153KA01# |          |
|        |               |         | 22000pF | ±10% | GRM21BR72A223KA01# |          |
|        |               |         | 33000pF | ±10% | GRM21BR72A333KA01# |          |
|        |               |         | 47000pF | ±10% | GRM21BR72A473KA01# |          |
|        |               |         | 68000pF | ±10% | GRM21BR72A683KAC4# |          |
|        |               |         |         | ±20% | GRM21BR72A683MAC4# |          |
|        |               |         | 0.10μF  | ±10% | GRM21BR72A104KAC4# |          |
|        |               |         |         | ±20% | GRM21BR72A104MAC4# |          |
|        | 50Vdc         | X7R     | 47000pF | ±10% | GRM21BR71H473KA01# |          |
|        |               |         | 68000pF | ±10% | GRM21BR71H683KA01# |          |
|        |               |         | 0.10μF  | ±10% | GRM21BR71H104KA01# |          |
|        |               |         |         | ±20% | GRM21BR71H104MA01# |          |
|        |               |         | 0.15μF  | ±10% | GRM21BR71H154KA01# |          |
|        |               |         | 0.22μF  | ±10% | GRM21BR71H224KA01# |          |
|        |               |         | 0.47μF  | ±10% | GRM21BR71H474KA88# |          |
|        |               | R       | 0.10μF  | ±10% | GRM21BR11H104KA01# |          |
|        |               |         |         | ±20% | GRM21BR11H104MA01# |          |
|        |               | B       | 0.15μF  | ±10% | GRM21BB31H154KA88# |          |
|        |               |         |         | ±20% | GRM21BB31H154MA88# |          |
|        |               |         | 0.22μF  | ±10% | GRM21BB31H224KA88# |          |
|        |               |         |         | ±20% | GRM21BB31H224MA88# |          |
|        |               |         | 0.47μF  | ±10% | GRM21BB31H474KA87# |          |
|        |               |         |         | ±20% | GRM21BB31H474MA87# |          |

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |          |
|--------|---------------|---------|---------|------|--------------------|----------|
| 1.35mm | 25Vdc         | R       | 0.15μF  | ±10% | GRM21BR11E154KA01# |          |
|        |               |         |         | ±20% | GRM21BR11E154MA01# |          |
|        |               |         | 4.7μF   | ±10% | GRM21BC81E475KA12# |          |
|        |               |         |         | ±20% | GRM21BC81E475MA12# |          |
|        |               | X6S     | 4.7μF   | ±10% | GRM21BC81E475KA12# |          |
|        |               |         |         | ±20% | GRM21BC81E475MA12# |          |
|        |               | X5R     | 4.7μF   | ±10% | GRM21BR61E475KA12# |          |
|        |               |         |         | ±20% | GRM21BR61E475MA12# |          |
|        |               | B       | 2.2μF   | ±10% | GRM21BB31E225KA75# |          |
|        |               |         |         | ±20% | GRM21BB31E225MA75# |          |
|        |               |         | 4.7μF   | ±10% | GRM21BB31E475KA75# |          |
|        |               |         |         | ±20% | GRM21BB31E475MA75# |          |
|        | 16Vdc         | X7R     | 2.2μF   | ±10% | GRM21BR71C225KA12# |          |
|        |               |         |         | ±20% | GRM21BR71C225MA12# |          |
|        |               | X5R     | 10μF    | ±10% | GRM21BR61C106KE15# |          |
|        |               |         |         | ±20% | GRM21BR61C106ME15# |          |
|        |               | B       | 10μF    | ±10% | GRM21BB31C106KE15# |          |
|        |               |         |         | ±20% | GRM21BB31C106ME15# |          |
| 1.4mm  | 50Vdc         | X5R     | 2.2μF   | ±10% | GRM21BR61H225KA73# |          |
|        |               |         |         | ±20% | GRM21BR61H225MA73# |          |
|        |               |         | 4.7μF   | ±10% | GRM21BR61H475KE51# |          |
|        |               |         |         | ±20% | GRM21BR61H475ME51# |          |
|        |               | B       | 2.2μF   | ±10% | GRM21BB31H225KA73# |          |
|        |               |         |         | ±20% | GRM21BB31H225MA73# |          |
|        |               |         | 4.7μF   | ±10% | GRM21BB31H475KE51# |          |
|        |               |         |         | ±20% | GRM21BB31H475ME51# |          |
|        | 25Vdc         | X7R     | 1.0μF   | ±10% | GRM21BR71E105KA99# |          |
|        |               |         |         | ±10% | GRM21BR71E475KA73# | Derating |
|        |               | 4.7μF   |         | ±10% | GRM21BR71E475MA73# | Derating |
|        |               |         |         | ±20% | GRM21BR71E475MA73# |          |
|        |               | R       | 1.0μF   | ±10% | GRM21BR11E105KA99# |          |
|        |               | X5R     | 10μF    | ±10% | GRM21BR61E106KA73# |          |
|        |               |         |         | ±20% | GRM21BR61E106MA73# |          |
|        |               | B       | 10μF    | ±10% | GRM21BB31E106KA73# |          |
|        |               |         |         | ±20% | GRM21BB31E106MA73# |          |
|        | 16Vdc         | X7R     | 4.7μF   | ±10% | GRM21BR71C475KA73# |          |
|        |               |         |         | ±20% | GRM21BR71C475MA73# |          |
|        |               | X6S     | 10μF    | ±10% | GRM21BC81C106KA73# |          |
|        |               |         |         | ±20% | GRM21BC81C106MA73# |          |
|        | 10Vdc         | X7R     | 4.7μF   | ±10% | GRM21BR71A475KA73# |          |
|        |               |         |         | ±20% | GRM21BR71A475MA73# |          |
|        |               | 10μF    |         | ±10% | GRM21BR71A106KE51# |          |
|        |               |         |         | ±20% | GRM21BR71A106ME51# |          |
|        | 6.3Vdc        | X7R     | 10μF    | ±10% | GRM21BB31A226ME51# | Derating |
|        |               |         |         | ±20% | GRM21BB31A226ME51# |          |
|        |               | X6S     | 22μF    | ±20% | GRM21BC80J226ME51# | Derating |
|        |               |         |         | ±20% | GRM21BC80J226ME51# |          |
|        | 4Vdc          | X7U     | 22μF    | ±20% | GRM21BE70G226ME51# |          |
|        |               | X6S     | 22μF    | ±20% | GRM21BC80G226ME39# |          |
| 1.45mm | 250Vdc        | X7R     | 10000pF | ±10% | GRM21BR72E103KW03# |          |
|        |               |         | 15000pF | ±10% | GRM21BR72E153KW03# |          |
|        |               |         | 22000pF | ±10% | GRM21BR72E223KW03# |          |
|        |               | X7R     | 10000pF | ±10% | GRM21BR72D103KW03# |          |
|        |               |         | 15000pF | ±10% | GRM21BR72D153KW03# |          |
|        |               |         | 22000pF | ±10% | GRM21BR72D223KW03# |          |
|        | 25Vdc         | X6S     | 10μF    | ±10% | GRM21BC81E106KE11# | Derating |
|        |               |         |         | ±20% | GRM21BC81E106ME11# | Derating |
|        |               |         |         |      |                    |          |
|        |               |         |         |      |                    |          |

Part number # indicates the package specification code.

GRM Series High Dielectric Constant Type Part Number List

(→ ■ 2.0×1.25mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number        |          |
|--------|---------------|---------|------|------|--------------------|----------|
| 1.45mm | 25Vdc         | X5R     | 22μF | ±20% | GRM21BR61E226ME44# |          |
|        |               | X7S     | 10μF | ±10% | GRM21BC71C106KE11# |          |
|        |               |         |      | ±20% | GRM21BC71C106ME11# |          |
|        |               | X6S     | 22μF | ±20% | GRM21BC81C226ME44# | Derating |
|        |               | X5R     | 22μF | ±20% | GRM21BR61C226ME44# |          |
|        | 10Vdc         | X7T     | 22μF | ±20% | GRM21BD71A226ME44# | Derating |
|        |               | X6S     | 22μF | ±20% | GRM21BC81A226ME44# |          |
|        |               | X5R     | 22μF | ±20% | GRM21BR61A226ME44# |          |
|        | 6.3Vdc        | X7T     | 22μF | ±20% | GRM21BD70J226ME44# |          |
|        |               | X5R     | 47μF | ±20% | GRM21BR60J476ME15# | Derating |
|        |               | B       | 47μF | ±20% | GRM21BB30J476ME15# | Derating |
|        | 4Vdc          | X6S     | 47μF | ±20% | GRM21BC80G476ME15# | Derating |
|        |               | X5R     | 47μF | ±20% | GRM21BR60G476ME15# |          |
|        |               | B       | 47μF | ±20% | GRM21BB30G476ME15# |          |

■ 3.2×1.6mm

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |          |
|--------|---------------|---------|--------|------|--------------------|----------|
| 0.95mm | 35Vdc         | X5R     | 10μF   | ±10% | GRM319R6YA106KA12# | Derating |
|        |               |         |        | ±20% | GRM319R6YA106MA12# | Derating |
|        | 25Vdc         | R       | 0.33μF | ±10% | GRM319R11E334KA01# |          |
|        | 16Vdc         | X5R     | 10μF   | ±10% | GRM319R61C106KE15# |          |
|        |               |         |        | ±20% | GRM319R61C106ME15# |          |
|        |               | B       | 22μF   | ±20% | GRM319R61C226ME15# | Derating |
|        |               |         | 10μF   | ±10% | GRM319B31C106KE15# |          |
|        |               |         |        | ±20% | GRM319B31C106ME15# |          |
|        |               |         |        | ±20% | GRM319B31C226ME15# | Derating |
|        |               | X5R     | 22μF   | ±20% | GRM319R61A226ME15# |          |
|        |               |         | 22μF   | ±20% | GRM319B31A226ME15# |          |
|        | 6.3Vdc        | X6S     | 22μF   | ±20% | GRM319C80J226ME15# |          |
|        |               | X5R     | 22μF   | ±20% | GRM319R60J226ME15# |          |
|        |               | B       | 22μF   | ±20% | GRM319B30J226ME15# |          |
| 1.0mm  | 630Vdc        | X7R     | 1000pF | ±10% | GRM31AR72J102KW01# |          |
|        |               |         | 1500pF | ±10% | GRM31AR72J152KW01# |          |
|        |               |         | 2200pF | ±10% | GRM31AR72J222KW01# |          |
|        |               |         | 3300pF | ±10% | GRM31AR72J332KW01# |          |
|        |               |         | 4700pF | ±10% | GRM31AR72J472KW01# |          |
|        | 500Vdc        | X7R     | 1000pF | ±10% | GRM31AR72H102KW01# |          |
|        |               |         | 1500pF | ±10% | GRM31AR72H152KW01# |          |
|        |               |         | 2200pF | ±10% | GRM31AR72H222KW01# |          |
|        |               |         | 3300pF | ±10% | GRM31AR72H332KW01# |          |
|        |               |         | 4700pF | ±10% | GRM31AR72H472KW01# |          |
| 1.25mm | 1000Vdc       | X7R     | 470pF  | ±10% | GRM31BR73A471KW01# |          |
|        |               |         | 680pF  | ±10% | GRM31BR73A681KW01# |          |
|        |               |         | 1000pF | ±10% | GRM31BR73A102KW01# |          |
|        |               |         | 1500pF | ±10% | GRM31BR73A152KW01# |          |
|        |               |         | 2200pF | ±10% | GRM31BR73A222KW01# |          |
|        |               |         | 3300pF | ±10% | GRM31BR73A332KW01# |          |
|        |               |         | 4700pF | ±10% | GRM31BR73A472KW01# |          |
|        | 630Vdc        | X7R     | 1000pF | ±10% | GRM31BR72J102KW01# |          |
|        |               |         | 1500pF | ±10% | GRM31BR72J152KW01# |          |
|        |               |         | 2200pF | ±10% | GRM31BR72J222KW01# |          |
|        |               |         | 3300pF | ±10% | GRM31BR72J332KW01# |          |
|        |               |         |        |      |                    |          |
|        |               |         |        |      |                    |          |
|        |               |         |        |      |                    |          |

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 1.25mm | 630Vdc        | X7R     | 4700pF  | ±10% | GRM31BR72J472KW01# |  |
|        |               |         | 6800pF  | ±10% | GRM31BR72J682KW01# |  |
|        |               |         | 10000pF | ±10% | GRM31BR72J103KW01# |  |
|        | 500Vdc        | X7R     | 1000pF  | ±10% | GRM31BR72H102KW01# |  |
|        |               |         | 1500pF  | ±10% | GRM31BR72H152KW01# |  |
|        |               |         | 2200pF  | ±10% | GRM31BR72H222KW01# |  |
|        |               |         | 3300pF  | ±10% | GRM31BR72H332KW01# |  |
|        |               |         | 4700pF  | ±10% | GRM31BR72H472KW01# |  |
|        |               |         | 6800pF  | ±10% | GRM31BR72H682KW01# |  |
|        |               |         | 10000pF | ±10% | GRM31BR72H103KW01# |  |
|        | 250Vdc        | X7R     | 15000pF | ±10% | GRM31BR72E153KW01# |  |
|        |               |         | 22000pF | ±10% | GRM31BR72E223KW01# |  |
|        |               |         | 68000pF | ±10% | GRM31BR72E683KW01# |  |
|        | 200Vdc        | X7R     | 15000pF | ±10% | GRM31BR72D153KW01# |  |
|        |               |         | 22000pF | ±10% | GRM31BR72D223KW01# |  |
|        |               |         | 68000pF | ±10% | GRM31BR72D683KW01# |  |
|        | 50Vdc         | X7R     | 0.47μF  | ±10% | GRM31MR71H474KA01# |  |
|        |               |         | 0.68μF  | ±10% | GRM31MR71H684KA88# |  |
|        |               |         | 1.0μF   | ±10% | GRM31MR71H105KA88# |  |
|        |               | B       | 1.0μF   | ±10% | GRM31MB31H105KA87# |  |
|        | 25Vdc         | X5R     | 10μF    | ±20% | GRM31MR61E106MA12# |  |
| 1.8mm  | 1000Vdc       | X7R     | 6800pF  | ±10% | GRM31CR73A682KW03# |  |
|        |               |         | 10000pF | ±10% | GRM31CR73A103KW03# |  |
|        | 630Vdc        | X7R     | 15000pF | ±10% | GRM31CR72J153KW03# |  |
|        |               |         | 22000pF | ±10% | GRM31CR72J223KW03# |  |
|        | 500Vdc        | X7R     | 15000pF | ±10% | GRM31CR72H153KW03# |  |
|        |               |         | 22000pF | ±10% | GRM31CR72H223KW03# |  |
|        | 250Vdc        | X7R     | 33000pF | ±10% | GRM31CR72E333KW03# |  |
|        |               |         | 47000pF | ±10% | GRM31CR72E473KW03# |  |
|        |               |         | 0.10μF  | ±10% | GRM31CR72E104KW03# |  |
|        | 200Vdc        | X7R     | 33000pF | ±10% | GRM31CR72D333KW03# |  |
|        |               |         | 47000pF | ±10% | GRM31CR72D473KW03# |  |
|        |               |         | 0.10μF  | ±10% | GRM31CR72D104KW03# |  |
|        | 50Vdc         | X7R     | 2.2μF   | ±10% | GRM31CR71H225KA88# |  |
|        |               |         | 4.7μF   | ±10% | GRM31CR71H475KA12# |  |
|        |               | X5R     | 10μF    | ±10% | GRM31CR61H106KA12# |  |
|        |               |         |         | ±20% | GRM31CR61H106MA12# |  |
|        |               | B       | 2.2μF   | ±10% | GRM31CB31H225KA87# |  |
|        |               |         |         | ±20% | GRM31CB31H225MA87# |  |
|        |               |         | 4.7μF   | ±10% | GRM31CB31H475KA12# |  |
|        |               |         |         | ±20% | GRM31CB31H475MA12# |  |
|        |               |         | 10μF    | ±10% | GRM31CB31H106KA12# |  |
|        |               |         |         | ±20% | GRM31CB31H106MA12# |  |
|        | 25Vdc         | X7R     | 4.7μF   | ±10% | GRM31CR71E475KA88# |  |
|        |               |         | 10μF    | ±10% | GRM31CR71E106KA12# |  |
|        |               | X5R     | 22μF    | ±20% | GRM31CR61E226ME15# |  |
|        |               |         |         | ±20% | GRM31CR61E226MA15# |  |
|        | 16Vdc         | X7R     | 4.7μF   | ±20% | GRM31CR71C475MA01# |  |
|        |               |         | 22μF    | ±20% | GRM31CC81C226ME15# |  |
|        |               | X5R     | 22μF    | ±20% | GRM31CR61C226ME15# |  |
|        |               |         | 22μF    | ±20% | GRM31CB31C226ME15# |  |

Part number # indicates the package specification code.

## GRM Series High Dielectric Constant Type Part Number List

(→ ■ 3.2×1.6mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol. | Part Number        |          |
|--------|---------------|---------|-------|------|--------------------|----------|
| 1.8mm  | 10Vdc         | X7R     | 22μF  | ±20% | GRM31CR71A226ME15# |          |
|        |               | X5R     | 47μF  | ±20% | GRM31CR61A476ME15# |          |
|        |               | B       | 47μF  | ±20% | GRM31CB31A476ME15# |          |
|        | 6.3Vdc        | X7R     | 22μF  | ±20% | GRM31CR70J226ME19# |          |
|        |               | X7U     | 47μF  | ±20% | GRM31CE70J476ME15# | Derating |
|        |               | X6S     | 47μF  | ±20% | GRM31CC80J476ME18# |          |
|        |               | X5R     | 47μF  | ±20% | GRM31CR60J476ME19# |          |
|        |               | B       | 47μF  | ±20% | GRM31CB30J476ME18# |          |
|        | 4Vdc          | X7U     | 47μF  | ±20% | GRM31CE70G476ME15# |          |
|        |               | X6S     | 47μF  | ±20% | GRM31CC80G476ME19# |          |
| 1.9mm  | 100Vdc        | X7R     | 2.2μF | ±10% | GRM31CR72A225KA73# |          |
|        |               |         |       | ±20% | GRM31CR72A225MA73# |          |
|        | 6.3Vdc        | X6T     | 100μF | ±20% | GRM31CD80J107ME39# | Derating |
|        |               | X5R     | 100μF | ±20% | GRM31CR60J107ME39# |          |
|        | 4Vdc          | X7U     | 100μF | ±20% | GRM31CE70G107ME39# | Derating |
|        |               | X6T     | 100μF | ±20% | GRM31CD80G107ME39# |          |
|        |               | X5R     | 100μF | ±20% | GRM31CR60G107ME39# |          |

■ 3.2×2.5mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |          |
|--------|---------------|---------|---------|------|--------------------|----------|
| 1.5mm  | 1000Vdc       | X7R     | 6800pF  | ±10% | GRM32QR73A682KW01# |          |
|        |               |         | 10000pF | ±10% | GRM32QR73A103KW01# |          |
|        | 630Vdc        | X7R     | 22000pF | ±10% | GRM32QR72J223KW01# |          |
|        | 500Vdc        | X7R     | 22000pF | ±10% | GRM32QR72H223KW01# |          |
|        | 250Vdc        | X7R     | 68000pF | ±10% | GRM32QR72E683KW01# |          |
|        |               |         | 0.15μF  | ±10% | GRM32QR72E154KW01# |          |
|        | 200Vdc        | X7R     | 68000pF | ±10% | GRM32QR72D683KW01# |          |
|        |               |         | 0.15μF  | ±10% | GRM32QR72D154KW01# |          |
| 1.8mm  | 6.3Vdc        | X5S     | 150μF   | ±20% | GRM32RC60J157ME15# | Derating |
|        | 4Vdc          | X6T     | 150μF   | ±20% | GRM32RD80G157ME15# | Derating |
|        |               | X5S     | 150μF   | ±20% | GRM32RC60G157ME15# |          |
|        | 2.5Vdc        | X6T     | 150μF   | ±20% | GRM32RD80E157ME15# |          |
| 2.0mm  | 1000Vdc       | X7R     | 15000pF | ±10% | GRM32DR73A153KW01# |          |
|        |               |         | 22000pF | ±10% | GRM32DR73A223KW01# |          |
|        | 630Vdc        | X7R     | 33000pF | ±10% | GRM32DR72J333KW01# |          |
|        |               |         | 47000pF | ±10% | GRM32DR72J473KW01# |          |
|        | 500Vdc        | X7R     | 33000pF | ±10% | GRM32DR72H333KW01# |          |
|        |               |         | 47000pF | ±10% | GRM32DR72H473KW01# |          |
|        | 250Vdc        | X7R     | 0.10μF  | ±10% | GRM32DR72E104KW01# |          |
|        |               |         | 0.22μF  | ±10% | GRM32DR72E224KW01# |          |
| 2.0mm  | 200Vdc        | X7R     | 0.10μF  | ±10% | GRM32DR72D104KW01# |          |
|        |               |         | 0.22μF  | ±10% | GRM32DR72D224KW01# |          |
| 2.2mm  | 25Vdc         | X7R     | 10μF    | ±10% | GRM32DR71E106KA12# |          |
| 2.7mm  | 80Vdc         | X7R     | 4.7μF   | ±10% | GRM32ER71K475KE14# | Derating |
|        |               |         |         | ±20% | GRM32ER71K475ME14# | Derating |
|        | 63Vdc         | X7R     | 10μF    | ±10% | GRM32ER71J106KA12# | Derating |
|        |               |         |         | ±20% | GRM32ER71J106MA12# | Derating |
|        | 50Vdc         | X7R     | 4.7μF   | ±10% | GRM32ER71H475KA88# |          |
|        |               |         | 10μF    | ±10% | GRM32ER71H106KA12# |          |
|        |               |         |         | ±20% | GRM32ER71H106MA12# |          |
|        |               | X5R     | 10μF    | ±10% | GRM32ER61H106KA12# |          |
|        |               |         |         | ±20% | GRM32ER61H106MA12# |          |

| T max. | Rated Voltage | TC Code | Cap.  | Tol. | Part Number        |          |
|--------|---------------|---------|-------|------|--------------------|----------|
| 2.7mm  | 50Vdc         | B       | 10μF  | ±10% | GRM32EB31H106KA12# |          |
|        |               |         |       | ±20% | GRM32EB31H106MA12# |          |
|        |               | X7R     | 10μF  | ±10% | GRM32ER7YA106KA12# |          |
|        |               |         |       | ±20% | GRM32ER7YA106MA12# |          |
|        | 35Vdc         | X7R     | 10μF  | ±10% | GRM32ER7YA106KA12# |          |
|        |               |         |       | ±20% | GRM32ER7YA106MA12# |          |
|        |               | X5R     | 10μF  | ±10% | GRM32ER6YA106KA12# |          |
|        |               |         |       | ±20% | GRM32ER6YA106MA12# |          |
|        | 25Vdc         | B       | 10μF  | ±10% | GRM32EB3YA106KA12# |          |
|        |               |         |       | ±20% | GRM32EB3YA106MA12# |          |
|        |               | X7R     | 22μF  | ±20% | GRM32ER71E226ME15# |          |
|        |               |         |       | ±20% | GRM32ER61E226ME15# |          |
|        | 16Vdc         | X7R     | 22μF  | ±20% | GRM32EB31E226ME15# |          |
|        |               |         |       | ±20% | GRM32EB31E226ME15# |          |
|        |               | X6S     | 47μF  | ±20% | GRM32ER71C226MEA8# |          |
|        |               |         |       | ±20% | GRM32EC81C476ME15# | Derating |
| 2.7mm  | 10Vdc         | X5R     | 47μF  | ±20% | GRM32ER61C476ME15# |          |
|        |               |         |       | ±20% | GRM32EB31C476ME15# |          |
|        |               | B       | 47μF  | ±20% | GRM32EB31A476ME15# |          |
|        |               |         |       | ±20% | GRM32EB31A476ME20# |          |
|        | 6.3Vdc        | X7R     | 47μF  | ±20% | GRM32ER61A107ME20# | Derating |
|        |               |         |       | ±20% | GRM32ER61A107ME20# |          |
|        |               | X7U     | 100μF | ±20% | GRM32ER61A107ME20# | Derating |
|        |               |         |       | ±20% | GRM32EE70J107ME15# | Derating |
|        | 4Vdc          | X5R     | 100μF | ±20% | GRM32ER61A107ME20# |          |
|        |               |         |       | ±20% | GRM32ER60J107ME20# |          |
|        |               | B       | 100μF | ±20% | GRM32EB30J107ME16# |          |
|        |               |         |       | ±20% | GRM32EE70G107ME19# |          |

■ 4.5×3.2mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 1.5mm  | 630Vdc        | X7R     | 68000pF | ±10% | GRM43QR72J683KW01# |  |
|        | 500Vdc        | X7R     | 68000pF | ±10% | GRM43QR72H683KW01# |  |
|        | 250Vdc        | X7R     | 0.15μF  | ±10% | GRM43QR72E154KW01# |  |
|        | 200Vdc        | X7R     | 0.15μF  | ±10% | GRM43QR72D154KW01# |  |
| 2.0mm  | 1000Vdc       | X7R     | 33000pF | ±10% | GRM43DR73A333KW01# |  |
|        |               |         | 47000pF | ±10% | GRM43DR73A473KW01# |  |
|        | 630Vdc        | X7R     | 0.10μF  | ±10% | GRM43DR72J104KW01# |  |
|        | 500Vdc        | X7R     | 0.10μF  | ±10% | GRM43DR72H104KW01# |  |
|        | 250Vdc        | X7R     | 0.22μF  | ±10% | GRM43DR72E224KW01# |  |
|        |               |         | 0.33μF  | ±10% | GRM43DR72E334KW01# |  |
|        |               | X7R     | 0.47μF  | ±10% | GRM43DR72E474KW01# |  |
|        |               |         | 0.47μF  | ±10% | GRM43DR72D224KW01# |  |
|        | 200Vdc        | X7R     | 0.22μF  | ±10% | GRM43DR72D224KW01# |  |
|        |               |         | 0.33μF  | ±10% | GRM43DR72D334KW01# |  |
|        |               |         | 0.47μF  | ±10% | GRM43DR72D474KW01# |  |

■ 5.7×5.0mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 2.0mm  | 1000Vdc       | X7R     | 68000pF | ±10% | GRM55DR73A683KW01# |  |
|        |               |         | 0.10μF  | ±10% | GRM55DR73A104KW01# |  |
|        | 630Vdc        | X7R     | 0.15μF  | ±10% | GRM55DR72J154KW01# |  |
|        |               |         | 0.22μF  | ±10% | GRM55DR72J224KW01# |  |
|        | 500Vdc        | X7R     | 0.15μF  | ±10% | GRM55DR72H154KW01# |  |
|        |               |         | 0.22μF  | ±10% | GRM55DR72H224KW01# |  |

Part number # indicates the package specification code.



GRM Series

GJM Series

GMA Series

GMD Series

GQM Series

GRJ Series

GR3 Series

KRM Series

KR3 Series

LLA Series

LLL Series

LLM Series

LLR Series

⚠Caution/  
Notice

# GRM Series High Dielectric Constant Type    Part Number List

(→ ■ 5.7×5.0mm)

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |  |
|--------|---------------|---------|--------|------|--------------------|--|
| 2.0mm  | 250Vdc        | X7R     | 0.33μF | ±10% | GRM55DR72E334KW01# |  |
|        |               |         | 0.47μF | ±10% | GRM55DR72E474KW01# |  |
|        |               |         | 0.68μF | ±10% | GRM55DR72E684KW01# |  |
|        |               |         | 1.0μF  | ±10% | GRM55DR72E105KW01# |  |
|        | 200Vdc        | X7R     | 0.33μF | ±10% | GRM55DR72D334KW01# |  |
|        |               |         | 0.47μF | ±10% | GRM55DR72D474KW01# |  |
|        |               |         | 0.68μF | ±10% | GRM55DR72D684KW01# |  |
|        |               |         | 1.0μF  | ±10% | GRM55DR72D105KW01# |  |

Part number # indicates the package specification code.



High Frequency High Q Type 1005(in mm)/0402(in inch) Size Max.

## GJM Series




HiQ

This product improves the high frequency characteristics and contributes to a reduction of power consumption by the High Q and low ESR.

### Features



#### ① Mainly ideal for mobile communication devices and temperature compensation of related modules.

This product is ideal for temperature compensation of high frequency circuits, such as resonant circuits, tuning circuits, and impedance matching circuits where the operating characteristics of the device are greatly affected by the capacitance fluctuation.



#### ② High Q and low ESR in VHF, UHF and microwave frequency bands.

High Q and low ESR were achieved at a high frequency by adopting ceramic material as the dielectric material which enables an extremely low loss at high frequency, and base metal electrodes as the internal electrodes.




#### ③ Can be used for tight tolerance.

In addition to standard tolerance, the allowable range of this product is also suitable for the following tight tolerance.

| Capacitance Range   | Standard Capacitance Tolerance<br>(Capacitance Tolerance Symbol) | Narrow Capacitance Tolerance<br>(Capacitance Tolerance Symbol)           |
|---------------------|------------------------------------------------------------------|--------------------------------------------------------------------------|
| $\leq 0.9\text{pF}$ | $\pm 0.1\text{pF}$ (B)                                           | $\pm 0.05\text{pF}$ (W)                                                  |
| 1.0 to 5.0pF        | $\pm 0.25\text{pF}$ (C)                                          | $\pm 0.05\text{pF}$ (W), $\pm 0.1\text{pF}$ (B)                          |
| 5.1 to 9.9pF        | $\pm 0.5\text{pF}$ (D)                                           | $\pm 0.05\text{pF}$ (W), $\pm 0.1\text{pF}$ (B), $\pm 0.25\text{pF}$ (C) |
| $\geq 10\text{pF}$  | $\pm 5\%$ (J)                                                    | $\pm 2\%$ (G)                                                            |

### Specifications

|                   |                                                                                             |
|-------------------|---------------------------------------------------------------------------------------------|
| Size              | 0.4×0.2mm to 1.0×0.5mm                                                                      |
| Rated Voltage     | DC6.3V to 50V                                                                               |
| Capacitance       | 0.1pF to 47pF                                                                               |
| Main Applications | Small communication devices, such as mobile phones and high frequency communication modules |



This catalog contains only a portion of the product lineup.  
Please refer to the capacitor search tool on the Murata Web site for details.

## GJM Series Temperature Compensating Type HiQ Part Number List

■ 0.4×0.2mm Ultra-compact

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.22mm | 25Vdc         | C0G     | 0.20pF | ±0.05pF | GJM0225C1ER20WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1ER20BB01# |  |
|        |               |         | 0.30pF | ±0.05pF | GJM0225C1ER30WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1ER30BB01# |  |
|        |               |         | 0.40pF | ±0.05pF | GJM0225C1ER40WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1ER40BB01# |  |
|        |               |         | 0.50pF | ±0.05pF | GJM0225C1ER50WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1ER50BB01# |  |
|        |               |         | 0.60pF | ±0.05pF | GJM0225C1ER60WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1ER60BB01# |  |
|        |               |         | 0.70pF | ±0.05pF | GJM0225C1ER70WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1ER70BB01# |  |
|        |               |         | 0.80pF | ±0.05pF | GJM0225C1ER80WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1ER80BB01# |  |
|        |               |         | 0.90pF | ±0.05pF | GJM0225C1ER90WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1ER90BB01# |  |
|        |               |         | 1.0pF  | ±0.05pF | GJM0225C1E1R0WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1E1R0BB01# |  |
|        |               |         |        | ±0.25pF | GJM0225C1E1R0CB01# |  |
|        |               |         | 1.1pF  | ±0.05pF | GJM0225C1E1R1WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1E1R1BB01# |  |
|        |               |         |        | ±0.25pF | GJM0225C1E1R1CB01# |  |
|        |               |         | 1.2pF  | ±0.05pF | GJM0225C1E1R2WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1E1R2BB01# |  |
|        |               |         |        | ±0.25pF | GJM0225C1E1R2CB01# |  |
|        |               |         | 1.3pF  | ±0.05pF | GJM0225C1E1R3WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1E1R3BB01# |  |
|        |               |         |        | ±0.25pF | GJM0225C1E1R3CB01# |  |
|        |               |         | 1.4pF  | ±0.05pF | GJM0225C1E1R4WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1E1R4BB01# |  |
|        |               |         |        | ±0.25pF | GJM0225C1E1R4CB01# |  |
|        |               |         | 1.5pF  | ±0.05pF | GJM0225C1E1R5WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1E1R5BB01# |  |
|        |               |         |        | ±0.25pF | GJM0225C1E1R5CB01# |  |
|        |               |         | 1.6pF  | ±0.05pF | GJM0225C1E1R6WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1E1R6BB01# |  |
|        |               |         |        | ±0.25pF | GJM0225C1E1R6CB01# |  |
|        |               |         | 1.7pF  | ±0.05pF | GJM0225C1E1R7WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1E1R7BB01# |  |
|        |               |         |        | ±0.25pF | GJM0225C1E1R7CB01# |  |
|        |               |         | 1.8pF  | ±0.05pF | GJM0225C1E1R8WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1E1R8BB01# |  |
|        |               |         |        | ±0.25pF | GJM0225C1E1R8CB01# |  |
|        |               |         | 1.9pF  | ±0.05pF | GJM0225C1E1R9WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1E1R9BB01# |  |
|        |               |         |        | ±0.25pF | GJM0225C1E1R9CB01# |  |
|        |               |         | 2.0pF  | ±0.05pF | GJM0225C1E2R0WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1E2R0BB01# |  |
|        |               |         |        | ±0.25pF | GJM0225C1E2R0CB01# |  |
|        |               |         | 2.1pF  | ±0.05pF | GJM0225C1E2R1WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1E2R1BB01# |  |
|        |               |         |        | ±0.25pF | GJM0225C1E2R1CB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 25Vdc         | C0G     | 2.2pF | ±0.05pF | GJM0225C1E2R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E2R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E2R2CB01# |  |
|        |               |         | 2.3pF | ±0.05pF | GJM0225C1E2R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E2R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E2R3CB01# |  |
|        |               |         | 2.4pF | ±0.05pF | GJM0225C1E2R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E2R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E2R4CB01# |  |
|        |               |         | 2.5pF | ±0.05pF | GJM0225C1E2R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E2R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E2R5CB01# |  |
|        |               |         | 2.6pF | ±0.05pF | GJM0225C1E2R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E2R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E2R6CB01# |  |
|        |               |         | 2.7pF | ±0.05pF | GJM0225C1E2R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E2R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E2R7CB01# |  |
|        |               |         | 2.8pF | ±0.05pF | GJM0225C1E2R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E2R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E2R8CB01# |  |
|        |               |         | 2.9pF | ±0.05pF | GJM0225C1E2R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E2R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E2R9CB01# |  |
|        |               |         | 3.0pF | ±0.05pF | GJM0225C1E3R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E3R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E3R0CB01# |  |
|        |               |         | 3.1pF | ±0.05pF | GJM0225C1E3R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E3R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E3R1CB01# |  |
|        |               |         | 3.2pF | ±0.05pF | GJM0225C1E3R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E3R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E3R2CB01# |  |
|        |               |         | 3.3pF | ±0.05pF | GJM0225C1E3R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E3R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E3R3CB01# |  |
|        |               |         | 3.4pF | ±0.05pF | GJM0225C1E3R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E3R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E3R4CB01# |  |
|        |               |         | 3.5pF | ±0.05pF | GJM0225C1E3R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E3R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E3R5CB01# |  |
|        |               |         | 3.6pF | ±0.05pF | GJM0225C1E3R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E3R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E3R6CB01# |  |
|        |               |         | 3.7pF | ±0.05pF | GJM0225C1E3R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E3R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E3R7CB01# |  |
|        |               |         | 3.8pF | ±0.05pF | GJM0225C1E3R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E3R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E3R8CB01# |  |
|        |               |         | 3.9pF | ±0.05pF | GJM0225C1E3R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E3R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E3R9CB01# |  |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type **HiQ** Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 25Vdc         | C0G     | 4.0pF | ±0.05pF | GJM0225C1E4R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E4R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E4R0CB01# |  |
|        |               |         | 4.1pF | ±0.05pF | GJM0225C1E4R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E4R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E4R1CB01# |  |
|        |               |         | 4.2pF | ±0.05pF | GJM0225C1E4R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E4R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E4R2CB01# |  |
|        |               |         | 4.3pF | ±0.05pF | GJM0225C1E4R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E4R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E4R3CB01# |  |
|        |               |         | 4.4pF | ±0.05pF | GJM0225C1E4R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E4R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E4R4CB01# |  |
|        |               |         | 4.5pF | ±0.05pF | GJM0225C1E4R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E4R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E4R5CB01# |  |
|        |               |         | 4.6pF | ±0.05pF | GJM0225C1E4R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E4R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E4R6CB01# |  |
|        |               |         | 4.7pF | ±0.05pF | GJM0225C1E4R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E4R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E4R7CB01# |  |
|        |               |         | 4.8pF | ±0.05pF | GJM0225C1E4R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E4R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E4R8CB01# |  |
|        |               |         | 4.9pF | ±0.05pF | GJM0225C1E4R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E4R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E4R9CB01# |  |
|        |               |         | 5.0pF | ±0.05pF | GJM0225C1E5R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E5R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E5R0CB01# |  |
|        |               |         | 5.1pF | ±0.05pF | GJM0225C1E5R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E5R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E5R1CB01# |  |
|        |               |         | 5.2pF | ±0.05pF | GJM0225C1E5R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E5R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E5R2CB01# |  |
|        |               |         | 5.3pF | ±0.05pF | GJM0225C1E5R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E5R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E5R3CB01# |  |
|        |               |         | 5.4pF | ±0.05pF | GJM0225C1E5R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E5R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E5R4CB01# |  |
|        |               |         | 5.5pF | ±0.05pF | GJM0225C1E5R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E5R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E5R5CB01# |  |
|        |               |         | 5.6pF | ±0.05pF | GJM0225C1E5R5DB01# |  |
|        |               |         |       | ±0.5pF  | GJM0225C1E5R5DB01# |  |
|        |               |         | 5.6pF | ±0.05pF | GJM0225C1E5R6WB01# |  |
|        |               |         |       | ±0.5pF  | GJM0225C1E5R6WB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 25Vdc         | C0G     | 5.6pF | ±0.1pF  | GJM0225C1E5R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E5R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0225C1E5R6DB01# |  |
|        |               |         | 5.7pF | ±0.05pF | GJM0225C1E5R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E5R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E5R7CB01# |  |
|        |               |         | 5.8pF | ±0.05pF | GJM0225C1E5R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E5R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E5R8CB01# |  |
|        |               |         | 5.9pF | ±0.05pF | GJM0225C1E5R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E5R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E5R9CB01# |  |
|        |               |         | 6.0pF | ±0.05pF | GJM0225C1E6R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E6R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E6R0CB01# |  |
|        |               |         | 6.1pF | ±0.05pF | GJM0225C1E6R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E6R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E6R1CB01# |  |
|        |               |         | 6.2pF | ±0.05pF | GJM0225C1E6R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E6R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E6R2CB01# |  |
|        |               |         | 6.3pF | ±0.05pF | GJM0225C1E6R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E6R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E6R3CB01# |  |
|        |               |         | 6.4pF | ±0.05pF | GJM0225C1E6R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E6R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E6R4CB01# |  |
|        |               |         | 6.5pF | ±0.05pF | GJM0225C1E6R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E6R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E6R5CB01# |  |
|        |               |         | 6.6pF | ±0.05pF | GJM0225C1E6R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E6R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E6R6CB01# |  |
|        |               |         | 6.7pF | ±0.05pF | GJM0225C1E6R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E6R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E6R7CB01# |  |
|        |               |         | 6.8pF | ±0.05pF | GJM0225C1E6R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E6R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E6R8CB01# |  |
|        |               |         | 6.9pF | ±0.05pF | GJM0225C1E6R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E6R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E6R9CB01# |  |

Part number # indicates the package specification code.

## GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 25Vdc         | C0G     | 6.9pF | ±0.5pF  | GJM0225C1E6R9DB01# |  |
|        |               |         |       | ±0.05pF | GJM0225C1E7R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E7R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E7R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0225C1E7R0DB01# |  |
|        |               |         | 7.1pF | ±0.05pF | GJM0225C1E7R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E7R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E7R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0225C1E7R1DB01# |  |
|        |               |         | 7.2pF | ±0.05pF | GJM0225C1E7R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E7R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E7R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0225C1E7R2DB01# |  |
|        |               |         | 7.3pF | ±0.05pF | GJM0225C1E7R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E7R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E7R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0225C1E7R3DB01# |  |
|        |               |         | 7.4pF | ±0.05pF | GJM0225C1E7R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E7R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E7R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0225C1E7R4DB01# |  |
|        |               |         | 7.5pF | ±0.05pF | GJM0225C1E7R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E7R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E7R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0225C1E7R5DB01# |  |
|        |               |         | 7.6pF | ±0.05pF | GJM0225C1E7R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E7R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E7R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0225C1E7R6DB01# |  |
|        |               |         | 7.7pF | ±0.05pF | GJM0225C1E7R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E7R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E7R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0225C1E7R7DB01# |  |
|        |               |         | 7.8pF | ±0.05pF | GJM0225C1E7R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E7R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E7R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0225C1E7R8DB01# |  |
|        |               |         | 7.9pF | ±0.05pF | GJM0225C1E7R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E7R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E7R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0225C1E7R9DB01# |  |
|        |               |         | 8.0pF | ±0.05pF | GJM0225C1E8R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E8R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E8R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0225C1E8R0DB01# |  |
|        |               |         | 8.1pF | ±0.05pF | GJM0225C1E8R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E8R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E8R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0225C1E8R1DB01# |  |
|        |               |         | 8.2pF | ±0.05pF | GJM0225C1E8R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E8R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E8R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0225C1E8R2DB01# |  |
|        |               |         | 8.3pF | ±0.05pF | GJM0225C1E8R3WB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 25Vdc         | C0G     | 8.3pF | ±0.1pF  | GJM0225C1E8R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E8R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0225C1E8R3DB01# |  |
|        |               |         | 8.4pF | ±0.05pF | GJM0225C1E8R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E8R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E8R4CB01# |  |
|        |               |         | 8.5pF | ±0.05pF | GJM0225C1E8R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E8R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E8R5CB01# |  |
|        |               |         | 8.6pF | ±0.05pF | GJM0225C1E8R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E8R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E8R6CB01# |  |
|        |               |         | 8.7pF | ±0.05pF | GJM0225C1E8R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E8R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E8R7CB01# |  |
|        |               |         | 8.8pF | ±0.05pF | GJM0225C1E8R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E8R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E8R8CB01# |  |
|        |               |         | 8.9pF | ±0.05pF | GJM0225C1E8R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E8R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E8R9CB01# |  |
|        |               |         | 9.0pF | ±0.05pF | GJM0225C1E9R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E9R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E9R0CB01# |  |
|        |               |         | 9.1pF | ±0.05pF | GJM0225C1E9R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E9R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E9R1CB01# |  |
|        |               |         | 9.2pF | ±0.05pF | GJM0225C1E9R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E9R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E9R2CB01# |  |
|        |               |         | 9.3pF | ±0.05pF | GJM0225C1E9R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E9R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E9R3CB01# |  |
|        |               |         | 9.4pF | ±0.05pF | GJM0225C1E9R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E9R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E9R4CB01# |  |
|        |               |         | 9.5pF | ±0.05pF | GJM0225C1E9R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E9R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E9R5CB01# |  |
|        |               |         | 9.6pF | ±0.05pF | GJM0225C1E9R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0225C1E9R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0225C1E9R6CB01# |  |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type **HiQ** Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.22mm | 25Vdc         | C0G     | 9.6pF  | ±0.5pF  | GJM0225C1E9R6DB01# |  |
|        |               |         | 9.7pF  | ±0.05pF | GJM0225C1E9R7WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1E9R7BB01# |  |
|        |               |         |        | ±0.25pF | GJM0225C1E9R7CB01# |  |
|        |               |         |        | ±0.5pF  | GJM0225C1E9R7DB01# |  |
|        |               |         | 9.8pF  | ±0.05pF | GJM0225C1E9R8WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1E9R8BB01# |  |
|        |               |         |        | ±0.25pF | GJM0225C1E9R8CB01# |  |
|        |               |         |        | ±0.5pF  | GJM0225C1E9R8DB01# |  |
|        |               |         | 9.9pF  | ±0.05pF | GJM0225C1E9R9WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0225C1E9R9BB01# |  |
|        |               |         |        | ±0.25pF | GJM0225C1E9R9CB01# |  |
|        |               |         |        | ±0.5pF  | GJM0225C1E9R9DB01# |  |
|        |               |         | 10pF   | ±2%     | GJM0225C1E100GB01# |  |
|        |               |         |        | ±5%     | GJM0225C1E100JB01# |  |
|        |               |         | 11pF   | ±2%     | GJM0225C1E110GB01# |  |
|        |               |         |        | ±5%     | GJM0225C1E110JB01# |  |
|        |               |         | 12pF   | ±2%     | GJM0225C1E120GB01# |  |
|        |               |         |        | ±5%     | GJM0225C1E120JB01# |  |
|        |               |         | 13pF   | ±2%     | GJM0225C1E130GB01# |  |
|        |               |         |        | ±5%     | GJM0225C1E130JB01# |  |
|        |               |         | 15pF   | ±2%     | GJM0225C1E150GB01# |  |
|        |               |         |        | ±5%     | GJM0225C1E150JB01# |  |
|        |               |         | 16pF   | ±2%     | GJM0225C1E160GB01# |  |
|        |               |         |        | ±5%     | GJM0225C1E160JB01# |  |
|        |               |         | 18pF   | ±2%     | GJM0225C1E180GB01# |  |
|        |               |         |        | ±5%     | GJM0225C1E180JB01# |  |
|        |               |         | 20pF   | ±2%     | GJM0225C1E200GB01# |  |
|        |               |         |        | ±5%     | GJM0225C1E200JB01# |  |
|        |               |         | 22pF   | ±2%     | GJM0225C1E220GB01# |  |
|        |               |         |        | ±5%     | GJM0225C1E220JB01# |  |
|        |               | CK      | 0.20pF | ±0.05pF | GJM0224C1ER20WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0224C1ER20BB01# |  |
|        |               |         | 0.30pF | ±0.05pF | GJM0224C1ER30WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0224C1ER30BB01# |  |
|        |               |         | 0.40pF | ±0.05pF | GJM0224C1ER40WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0224C1ER40BB01# |  |
|        |               |         | 0.50pF | ±0.05pF | GJM0224C1ER50WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0224C1ER50BB01# |  |
|        |               |         | 0.60pF | ±0.05pF | GJM0224C1ER60WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0224C1ER60BB01# |  |
|        |               |         | 0.70pF | ±0.05pF | GJM0224C1ER70WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0224C1ER70BB01# |  |
|        |               |         | 0.80pF | ±0.05pF | GJM0224C1ER80WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0224C1ER80BB01# |  |
|        |               |         | 0.90pF | ±0.05pF | GJM0224C1ER90WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0224C1ER90BB01# |  |
|        |               |         | 1.0pF  | ±0.05pF | GJM0224C1E1R0WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0224C1E1R0BB01# |  |
|        |               |         |        | ±0.25pF | GJM0224C1E1R0CB01# |  |
|        |               |         | 1.1pF  | ±0.05pF | GJM0224C1E1R1WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0224C1E1R1BB01# |  |
|        |               |         |        | ±0.25pF | GJM0224C1E1R1CB01# |  |
|        |               |         | 1.2pF  | ±0.05pF | GJM0224C1E1R2WB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 25Vdc         | CK      | 1.2pF | ±0.1pF  | GJM0224C1E1R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0224C1E1R2CB01# |  |
|        |               |         | 1.3pF | ±0.05pF | GJM0224C1E1R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0224C1E1R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0224C1E1R3CB01# |  |
|        |               |         | 1.4pF | ±0.05pF | GJM0224C1E1R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0224C1E1R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0224C1E1R4CB01# |  |
|        |               |         | 1.5pF | ±0.05pF | GJM0224C1E1R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0224C1E1R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0224C1E1R5CB01# |  |
|        |               |         | 1.6pF | ±0.05pF | GJM0224C1E1R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0224C1E1R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0224C1E1R6CB01# |  |
|        |               |         | 1.7pF | ±0.05pF | GJM0224C1E1R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0224C1E1R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0224C1E1R7CB01# |  |
|        |               |         | 1.8pF | ±0.05pF | GJM0224C1E1R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0224C1E1R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0224C1E1R8CB01# |  |
|        |               |         | 1.9pF | ±0.05pF | GJM0224C1E1R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0224C1E1R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0224C1E1R9CB01# |  |
|        |               |         | 2.0pF | ±0.05pF | GJM0224C1E2R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0224C1E2R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0224C1E2R0CB01# |  |
|        |               | CJ      | 2.1pF | ±0.05pF | GJM0223C1E2R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E2R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E2R1CB01# |  |
|        |               |         | 2.2pF | ±0.05pF | GJM0223C1E2R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E2R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E2R2CB01# |  |
|        |               |         | 2.3pF | ±0.05pF | GJM0223C1E2R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E2R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E2R3CB01# |  |
|        |               |         | 2.4pF | ±0.05pF | GJM0223C1E2R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E2R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E2R4CB01# |  |
|        |               |         | 2.5pF | ±0.05pF | GJM0223C1E2R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E2R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E2R5CB01# |  |
|        |               |         | 2.6pF | ±0.05pF | GJM0223C1E2R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E2R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E2R6CB01# |  |
|        |               |         | 2.7pF | ±0.05pF | GJM0223C1E2R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E2R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E2R7CB01# |  |
|        |               |         | 2.8pF | ±0.05pF | GJM0223C1E2R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E2R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E2R8CB01# |  |
|        |               |         | 2.9pF | ±0.05pF | GJM0223C1E2R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E2R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E2R9CB01# |  |
|        |               |         | 3.0pF | ±0.05pF | GJM0223C1E3R0WB01# |  |

Part number # indicates the package specification code.



# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 25Vdc         | CJ      | 3.0pF | ±0.1pF  | GJM0223C1E3R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E3R0CB01# |  |
|        |               |         | 3.1pF | ±0.05pF | GJM0223C1E3R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E3R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E3R1CB01# |  |
|        |               |         | 3.2pF | ±0.05pF | GJM0223C1E3R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E3R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E3R2CB01# |  |
|        |               |         | 3.3pF | ±0.05pF | GJM0223C1E3R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E3R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E3R3CB01# |  |
|        |               |         | 3.4pF | ±0.05pF | GJM0223C1E3R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E3R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E3R4CB01# |  |
|        |               |         | 3.5pF | ±0.05pF | GJM0223C1E3R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E3R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E3R5CB01# |  |
|        |               |         | 3.6pF | ±0.05pF | GJM0223C1E3R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E3R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E3R6CB01# |  |
|        |               |         | 3.7pF | ±0.05pF | GJM0223C1E3R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E3R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E3R7CB01# |  |
|        |               |         | 3.8pF | ±0.05pF | GJM0223C1E3R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E3R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E3R8CB01# |  |
|        |               |         | 3.9pF | ±0.05pF | GJM0223C1E3R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0223C1E3R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0223C1E3R9CB01# |  |
|        |               | CH      | 4.0pF | ±0.05pF | GJM0222C1E4R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E4R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E4R0CB01# |  |
|        |               |         | 4.1pF | ±0.05pF | GJM0222C1E4R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E4R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E4R1CB01# |  |
|        |               |         | 4.2pF | ±0.05pF | GJM0222C1E4R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E4R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E4R2CB01# |  |
|        |               |         | 4.3pF | ±0.05pF | GJM0222C1E4R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E4R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E4R3CB01# |  |
|        |               |         | 4.4pF | ±0.05pF | GJM0222C1E4R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E4R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E4R4CB01# |  |
|        |               |         | 4.5pF | ±0.05pF | GJM0222C1E4R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E4R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E4R5CB01# |  |
|        |               |         | 4.6pF | ±0.05pF | GJM0222C1E4R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E4R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E4R6CB01# |  |
|        |               |         | 4.7pF | ±0.05pF | GJM0222C1E4R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E4R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E4R7CB01# |  |
|        |               |         | 4.8pF | ±0.05pF | GJM0222C1E4R8WB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 25Vdc         | CH      | 4.8pF | ±0.1pF  | GJM0222C1E4R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E4R8CB01# |  |
|        |               |         | 4.9pF | ±0.05pF | GJM0222C1E4R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E4R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E4R9CB01# |  |
|        |               |         | 5.0pF | ±0.05pF | GJM0222C1E5R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E5R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E5R0CB01# |  |
|        |               |         | 5.1pF | ±0.05pF | GJM0222C1E5R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E5R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E5R1CB01# |  |
|        |               |         | 5.2pF | ±0.05pF | GJM0222C1E5R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E5R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E5R2CB01# |  |
|        |               |         | 5.3pF | ±0.05pF | GJM0222C1E5R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E5R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E5R3CB01# |  |
|        |               |         | 5.4pF | ±0.05pF | GJM0222C1E5R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E5R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E5R4CB01# |  |
|        |               |         | 5.5pF | ±0.05pF | GJM0222C1E5R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E5R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E5R5CB01# |  |
|        |               |         | 5.6pF | ±0.05pF | GJM0222C1E5R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E5R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E5R6CB01# |  |
|        |               |         | 5.7pF | ±0.05pF | GJM0222C1E5R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E5R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E5R7CB01# |  |
|        |               |         | 5.8pF | ±0.05pF | GJM0222C1E5R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E5R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E5R8CB01# |  |
|        |               |         | 5.9pF | ±0.05pF | GJM0222C1E5R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E5R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E5R9CB01# |  |
|        |               |         | 6.0pF | ±0.05pF | GJM0222C1E6R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E6R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E6R0CB01# |  |
|        |               |         | 6.1pF | ±0.05pF | GJM0222C1E6R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E6R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E6R1CB01# |  |
|        |               |         | 6.2pF | ±0.05pF | GJM0222C1E6R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E6R2BB01# |  |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type **HiQ** Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 25Vdc         | CH      | 6.2pF | ±0.25pF | GJM0222C1E6R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E6R2DB01# |  |
|        |               |         | 6.3pF | ±0.05pF | GJM0222C1E6R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E6R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E6R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E6R3DB01# |  |
|        |               |         | 6.4pF | ±0.05pF | GJM0222C1E6R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E6R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E6R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E6R4DB01# |  |
|        |               |         | 6.5pF | ±0.05pF | GJM0222C1E6R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E6R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E6R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E6R5DB01# |  |
|        |               |         | 6.6pF | ±0.05pF | GJM0222C1E6R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E6R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E6R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E6R6DB01# |  |
|        |               |         | 6.7pF | ±0.05pF | GJM0222C1E6R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E6R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E6R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E6R7DB01# |  |
|        |               |         | 6.8pF | ±0.05pF | GJM0222C1E6R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E6R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E6R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E6R8DB01# |  |
|        |               |         | 6.9pF | ±0.05pF | GJM0222C1E6R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E6R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E6R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E6R9DB01# |  |
|        |               |         | 7.0pF | ±0.05pF | GJM0222C1E7R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E7R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E7R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E7R0DB01# |  |
|        |               |         | 7.1pF | ±0.05pF | GJM0222C1E7R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E7R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E7R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E7R1DB01# |  |
|        |               |         | 7.2pF | ±0.05pF | GJM0222C1E7R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E7R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E7R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E7R2DB01# |  |
|        |               |         | 7.3pF | ±0.05pF | GJM0222C1E7R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E7R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E7R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E7R3DB01# |  |
|        |               |         | 7.4pF | ±0.05pF | GJM0222C1E7R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E7R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E7R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E7R4DB01# |  |
|        |               |         | 7.5pF | ±0.05pF | GJM0222C1E7R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E7R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E7R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E7R5DB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 25Vdc         | CH      | 7.6pF | ±0.05pF | GJM0222C1E7R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E7R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E7R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E7R6DB01# |  |
|        |               |         | 7.7pF | ±0.05pF | GJM0222C1E7R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E7R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E7R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E7R7DB01# |  |
|        |               |         | 7.8pF | ±0.05pF | GJM0222C1E7R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E7R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E7R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E7R8DB01# |  |
|        |               |         | 7.9pF | ±0.05pF | GJM0222C1E7R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E7R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E7R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E7R9DB01# |  |
|        |               |         | 8.0pF | ±0.05pF | GJM0222C1E8R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E8R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E8R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E8R0DB01# |  |
|        |               |         | 8.1pF | ±0.05pF | GJM0222C1E8R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E8R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E8R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E8R1DB01# |  |
|        |               |         | 8.2pF | ±0.05pF | GJM0222C1E8R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E8R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E8R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E8R2DB01# |  |
|        |               |         | 8.3pF | ±0.05pF | GJM0222C1E8R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E8R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E8R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E8R3DB01# |  |
|        |               |         | 8.4pF | ±0.05pF | GJM0222C1E8R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E8R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E8R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E8R4DB01# |  |
|        |               |         | 8.5pF | ±0.05pF | GJM0222C1E8R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E8R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E8R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E8R5DB01# |  |
|        |               |         | 8.6pF | ±0.05pF | GJM0222C1E8R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E8R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E8R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E8R6DB01# |  |
|        |               |         | 8.7pF | ±0.05pF | GJM0222C1E8R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E8R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E8R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E8R7DB01# |  |
|        |               |         | 8.8pF | ±0.05pF | GJM0222C1E8R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E8R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E8R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E8R8DB01# |  |
|        |               |         | 8.9pF | ±0.05pF | GJM0222C1E8R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E8R9BB01# |  |

Part number # indicates the package specification code.

## GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.4×0.2mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.22mm | 25Vdc         | CH      | 8.9pF | ±0.25pF | GJM0222C1E8R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E8R9DB01# |  |
|        |               |         | 9.0pF | ±0.05pF | GJM0222C1E9R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E9R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E9R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E9R0DB01# |  |
|        |               |         | 9.1pF | ±0.05pF | GJM0222C1E9R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E9R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E9R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E9R1DB01# |  |
|        |               |         | 9.2pF | ±0.05pF | GJM0222C1E9R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E9R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E9R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E9R2DB01# |  |
|        |               |         | 9.3pF | ±0.05pF | GJM0222C1E9R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E9R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E9R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E9R3DB01# |  |
|        |               |         | 9.4pF | ±0.05pF | GJM0222C1E9R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E9R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E9R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E9R4DB01# |  |
|        |               |         | 9.5pF | ±0.05pF | GJM0222C1E9R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E9R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E9R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E9R5DB01# |  |
|        |               |         | 9.6pF | ±0.05pF | GJM0222C1E9R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E9R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E9R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E9R6DB01# |  |
|        |               |         | 9.7pF | ±0.05pF | GJM0222C1E9R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E9R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E9R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E9R7DB01# |  |
|        |               |         | 9.8pF | ±0.05pF | GJM0222C1E9R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E9R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E9R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E9R8DB01# |  |
|        |               |         | 9.9pF | ±0.05pF | GJM0222C1E9R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0222C1E9R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0222C1E9R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0222C1E9R9DB01# |  |
|        |               |         | 10pF  | ±2%     | GJM0222C1E100GB01# |  |
|        |               |         |       | ±5%     | GJM0222C1E100JB01# |  |
|        |               |         | 11pF  | ±2%     | GJM0222C1E110GB01# |  |
|        |               |         |       | ±5%     | GJM0222C1E110JB01# |  |
|        |               |         | 12pF  | ±2%     | GJM0222C1E120GB01# |  |
|        |               |         |       | ±5%     | GJM0222C1E120JB01# |  |
|        |               |         | 13pF  | ±2%     | GJM0222C1E130GB01# |  |
|        |               |         |       | ±5%     | GJM0222C1E130JB01# |  |
|        |               |         | 15pF  | ±2%     | GJM0222C1E150GB01# |  |
|        |               |         |       | ±5%     | GJM0222C1E150JB01# |  |
|        |               |         | 16pF  | ±2%     | GJM0222C1E160GB01# |  |
|        |               |         |       | ±5%     | GJM0222C1E160JB01# |  |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number        |  |
|--------|---------------|---------|------|------|--------------------|--|
| 0.22mm | 25Vdc         | CH      | 18pF | ±2%  | GJM0222C1E180GB01# |  |
|        |               |         |      | ±5%  | GJM0222C1E180JB01# |  |
|        |               |         | 20pF | ±2%  | GJM0222C1E200GB01# |  |
|        |               |         |      | ±5%  | GJM0222C1E200JB01# |  |
|        |               |         | 22pF | ±2%  | GJM0222C1E220GB01# |  |
|        |               |         |      | ±5%  | GJM0222C1E220JB01# |  |

■ 0.6×0.3mm Ultra-compact

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.33mm | 25Vdc         | C0G     | 0.20pF | ±0.05pF | GJM0335C1ER20WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1ER20BB01# |  |
|        |               |         | 0.30pF | ±0.05pF | GJM0335C1ER30WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1ER30BB01# |  |
|        |               |         | 0.40pF | ±0.05pF | GJM0335C1ER40WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1ER40BB01# |  |
|        |               |         | 0.50pF | ±0.05pF | GJM0335C1ER50WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1ER50BB01# |  |
|        |               |         | 0.60pF | ±0.05pF | GJM0335C1ER60WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1ER60BB01# |  |
|        |               |         | 0.70pF | ±0.05pF | GJM0335C1ER70WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1ER70BB01# |  |
|        |               |         | 0.80pF | ±0.05pF | GJM0335C1ER80WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1ER80BB01# |  |
|        |               |         | 0.90pF | ±0.05pF | GJM0335C1ER90WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1ER90BB01# |  |
|        |               |         | 1.0pF  | ±0.05pF | GJM0335C1E1R0WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1E1R0BB01# |  |
|        |               |         |        | ±0.25pF | GJM0335C1E1R0CB01# |  |
|        |               |         |        |         |                    |  |
|        |               |         | 1.1pF  | ±0.05pF | GJM0335C1E1R1WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1E1R1BB01# |  |
|        |               |         |        | ±0.25pF | GJM0335C1E1R1CB01# |  |
|        |               |         | 1.2pF  | ±0.05pF | GJM0335C1E1R2WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1E1R2BB01# |  |
|        |               |         |        | ±0.25pF | GJM0335C1E1R2CB01# |  |
|        |               |         | 1.3pF  | ±0.05pF | GJM0335C1E1R3WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1E1R3BB01# |  |
|        |               |         |        | ±0.25pF | GJM0335C1E1R3CB01# |  |
|        |               |         | 1.4pF  | ±0.05pF | GJM0335C1E1R4WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1E1R4BB01# |  |
|        |               |         |        | ±0.25pF | GJM0335C1E1R4CB01# |  |
|        |               |         | 1.5pF  | ±0.05pF | GJM0335C1E1R5WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1E1R5BB01# |  |
|        |               |         |        | ±0.25pF | GJM0335C1E1R5CB01# |  |
|        |               |         | 1.6pF  | ±0.05pF | GJM0335C1E1R6WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1E1R6BB01# |  |
|        |               |         |        | ±0.25pF | GJM0335C1E1R6CB01# |  |
|        |               |         | 1.7pF  | ±0.05pF | GJM0335C1E1R7WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1E1R7BB01# |  |
|        |               |         |        | ±0.25pF | GJM0335C1E1R7CB01# |  |
|        |               |         | 1.8pF  | ±0.05pF | GJM0335C1E1R8WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1E1R8BB01# |  |
|        |               |         |        | ±0.25pF | GJM0335C1E1R8CB01# |  |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type **HiQ** Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 25Vdc         | C0G     | 1.9pF | ±0.05pF | GJM0335C1E1R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E1R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E1R9CB01# |  |
|        |               |         | 2.0pF | ±0.05pF | GJM0335C1E2R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E2R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E2R0CB01# |  |
|        |               |         | 2.1pF | ±0.05pF | GJM0335C1E2R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E2R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E2R1CB01# |  |
|        |               |         | 2.2pF | ±0.05pF | GJM0335C1E2R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E2R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E2R2CB01# |  |
|        |               |         | 2.3pF | ±0.05pF | GJM0335C1E2R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E2R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E2R3CB01# |  |
|        |               |         | 2.4pF | ±0.05pF | GJM0335C1E2R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E2R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E2R4CB01# |  |
|        |               |         | 2.5pF | ±0.05pF | GJM0335C1E2R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E2R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E2R5CB01# |  |
|        |               |         | 2.6pF | ±0.05pF | GJM0335C1E2R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E2R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E2R6CB01# |  |
|        |               |         | 2.7pF | ±0.05pF | GJM0335C1E2R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E2R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E2R7CB01# |  |
|        |               |         | 2.8pF | ±0.05pF | GJM0335C1E2R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E2R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E2R8CB01# |  |
|        |               |         | 2.9pF | ±0.05pF | GJM0335C1E2R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E2R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E2R9CB01# |  |
|        |               |         | 3.0pF | ±0.05pF | GJM0335C1E3R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E3R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E3R0CB01# |  |
|        |               |         | 3.1pF | ±0.05pF | GJM0335C1E3R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E3R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E3R1CB01# |  |
|        |               |         | 3.2pF | ±0.05pF | GJM0335C1E3R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E3R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E3R2CB01# |  |
|        |               |         | 3.3pF | ±0.05pF | GJM0335C1E3R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E3R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E3R3CB01# |  |
|        |               |         | 3.4pF | ±0.05pF | GJM0335C1E3R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E3R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E3R4CB01# |  |
|        |               |         | 3.5pF | ±0.05pF | GJM0335C1E3R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E3R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E3R5CB01# |  |
|        |               |         | 3.6pF | ±0.05pF | GJM0335C1E3R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E3R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E3R6CB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 25Vdc         | C0G     | 3.7pF | ±0.05pF | GJM0335C1E3R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E3R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E3R7CB01# |  |
|        |               |         | 3.8pF | ±0.05pF | GJM0335C1E3R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E3R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E3R8CB01# |  |
|        |               |         | 3.9pF | ±0.05pF | GJM0335C1E3R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E3R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E3R9CB01# |  |
|        |               |         | 4.0pF | ±0.05pF | GJM0335C1E4R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E4R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E4R0CB01# |  |
|        |               |         | 4.1pF | ±0.05pF | GJM0335C1E4R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E4R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E4R1CB01# |  |
|        |               |         | 4.2pF | ±0.05pF | GJM0335C1E4R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E4R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E4R2CB01# |  |
|        |               |         | 4.3pF | ±0.05pF | GJM0335C1E4R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E4R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E4R3CB01# |  |
|        |               |         | 4.4pF | ±0.05pF | GJM0335C1E4R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E4R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E4R4CB01# |  |
|        |               |         | 4.5pF | ±0.05pF | GJM0335C1E4R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E4R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E4R5CB01# |  |
|        |               |         | 4.6pF | ±0.05pF | GJM0335C1E4R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E4R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E4R6CB01# |  |
|        |               |         | 4.7pF | ±0.05pF | GJM0335C1E4R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E4R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E4R7CB01# |  |
|        |               |         | 4.8pF | ±0.05pF | GJM0335C1E4R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E4R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E4R8CB01# |  |
|        |               |         | 4.9pF | ±0.05pF | GJM0335C1E4R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E4R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E4R9CB01# |  |
|        |               |         | 5.0pF | ±0.05pF | GJM0335C1E5R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E5R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E5R0CB01# |  |
|        |               |         | 5.1pF | ±0.05pF | GJM0335C1E5R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E5R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E5R1CB01# |  |
|        |               |         | 5.2pF | ±0.05pF | GJM0335C1E5R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E5R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E5R2CB01# |  |
|        |               |         | 5.3pF | ±0.05pF | GJM0335C1E5R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E5R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E5R3CB01# |  |
|        |               |         | 5.4pF | ±0.05pF | GJM0335C1E5R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E5R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E5R4CB01# |  |

Part number # indicates the package specification code.



# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 25Vdc         | C0G     | 5.4pF | ±0.05pF | GJM0335C1E5R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E5R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E5R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E5R4DB01# |  |
|        |               |         | 5.5pF | ±0.05pF | GJM0335C1E5R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E5R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E5R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E5R5DB01# |  |
|        |               |         | 5.6pF | ±0.05pF | GJM0335C1E5R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E5R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E5R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E5R6DB01# |  |
|        |               |         | 5.7pF | ±0.05pF | GJM0335C1E5R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E5R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E5R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E5R7DB01# |  |
|        |               |         | 5.8pF | ±0.05pF | GJM0335C1E5R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E5R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E5R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E5R8DB01# |  |
|        |               |         | 5.9pF | ±0.05pF | GJM0335C1E5R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E5R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E5R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E5R9DB01# |  |
|        |               |         | 6.0pF | ±0.05pF | GJM0335C1E6R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E6R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E6R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E6R0DB01# |  |
|        |               |         | 6.1pF | ±0.05pF | GJM0335C1E6R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E6R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E6R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E6R1DB01# |  |
|        |               |         | 6.2pF | ±0.05pF | GJM0335C1E6R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E6R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E6R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E6R2DB01# |  |
|        |               |         | 6.3pF | ±0.05pF | GJM0335C1E6R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E6R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E6R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E6R3DB01# |  |
|        |               |         | 6.4pF | ±0.05pF | GJM0335C1E6R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E6R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E6R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E6R4DB01# |  |
|        |               |         | 6.5pF | ±0.05pF | GJM0335C1E6R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E6R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E6R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E6R5DB01# |  |
|        |               |         | 6.6pF | ±0.05pF | GJM0335C1E6R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E6R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E6R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E6R6DB01# |  |
|        |               |         | 6.7pF | ±0.05pF | GJM0335C1E6R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E6R7BB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 25Vdc         | C0G     | 6.7pF | ±0.25pF | GJM0335C1E6R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E6R7DB01# |  |
|        |               |         | 6.8pF | ±0.05pF | GJM0335C1E6R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E6R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E6R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E6R8DB01# |  |
|        |               |         | 6.9pF | ±0.05pF | GJM0335C1E6R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E6R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E6R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E6R9DB01# |  |
|        |               |         | 7.0pF | ±0.05pF | GJM0335C1E7R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E7R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E7R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E7R0DB01# |  |
|        |               |         | 7.1pF | ±0.05pF | GJM0335C1E7R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E7R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E7R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E7R1DB01# |  |
|        |               |         | 7.2pF | ±0.05pF | GJM0335C1E7R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E7R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E7R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E7R2DB01# |  |
|        |               |         | 7.3pF | ±0.05pF | GJM0335C1E7R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E7R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E7R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E7R3DB01# |  |
|        |               |         | 7.4pF | ±0.05pF | GJM0335C1E7R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E7R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E7R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E7R4DB01# |  |
|        |               |         | 7.5pF | ±0.05pF | GJM0335C1E7R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E7R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E7R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E7R5DB01# |  |
|        |               |         | 7.6pF | ±0.05pF | GJM0335C1E7R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E7R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E7R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E7R6DB01# |  |
|        |               |         | 7.7pF | ±0.05pF | GJM0335C1E7R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E7R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E7R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E7R7DB01# |  |
|        |               |         | 7.8pF | ±0.05pF | GJM0335C1E7R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E7R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E7R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E7R8DB01# |  |
|        |               |         | 7.9pF | ±0.05pF | GJM0335C1E7R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E7R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E7R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E7R9DB01# |  |
|        |               |         | 8.0pF | ±0.05pF | GJM0335C1E8R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E8R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E8R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E8R0DB01# |  |

Part number # indicates the package specification code.



# GJM Series Temperature Compensating Type **HiQ** Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 25Vdc         | C0G     | 8.1pF | ±0.05pF | GJM0335C1E8R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E8R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E8R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E8R1DB01# |  |
|        |               |         | 8.2pF | ±0.05pF | GJM0335C1E8R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E8R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E8R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E8R2DB01# |  |
|        |               |         | 8.3pF | ±0.05pF | GJM0335C1E8R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E8R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E8R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E8R3DB01# |  |
|        |               |         | 8.4pF | ±0.05pF | GJM0335C1E8R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E8R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E8R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E8R4DB01# |  |
|        |               |         | 8.5pF | ±0.05pF | GJM0335C1E8R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E8R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E8R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E8R5DB01# |  |
|        |               |         | 8.6pF | ±0.05pF | GJM0335C1E8R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E8R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E8R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E8R6DB01# |  |
|        |               |         | 8.7pF | ±0.05pF | GJM0335C1E8R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E8R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E8R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E8R7DB01# |  |
|        |               |         | 8.8pF | ±0.05pF | GJM0335C1E8R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E8R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E8R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E8R8DB01# |  |
|        |               |         | 8.9pF | ±0.05pF | GJM0335C1E8R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E8R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E8R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E8R9DB01# |  |
|        |               |         | 9.0pF | ±0.05pF | GJM0335C1E9R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E9R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E9R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E9R0DB01# |  |
|        |               |         | 9.1pF | ±0.05pF | GJM0335C1E9R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E9R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E9R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E9R1DB01# |  |
|        |               |         | 9.2pF | ±0.05pF | GJM0335C1E9R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E9R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E9R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E9R2DB01# |  |
|        |               |         | 9.3pF | ±0.05pF | GJM0335C1E9R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E9R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0335C1E9R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0335C1E9R3DB01# |  |
|        |               |         | 9.4pF | ±0.05pF | GJM0335C1E9R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0335C1E9R4BB01# |  |

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.33mm | 25Vdc         | C0G     | 9.4pF  | ±0.25pF | GJM0335C1E9R4CB01# |  |
|        |               |         |        | ±0.5pF  | GJM0335C1E9R4DB01# |  |
|        |               |         | 9.5pF  | ±0.05pF | GJM0335C1E9R5WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1E9R5BB01# |  |
|        |               |         |        | ±0.25pF | GJM0335C1E9R5CB01# |  |
|        |               |         |        | ±0.5pF  | GJM0335C1E9R5DB01# |  |
|        |               |         | 9.6pF  | ±0.05pF | GJM0335C1E9R6WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1E9R6BB01# |  |
|        |               |         |        | ±0.25pF | GJM0335C1E9R6CB01# |  |
|        |               |         |        | ±0.5pF  | GJM0335C1E9R6DB01# |  |
|        |               |         | 9.7pF  | ±0.05pF | GJM0335C1E9R7WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1E9R7BB01# |  |
|        |               |         |        | ±0.25pF | GJM0335C1E9R7CB01# |  |
|        |               |         |        | ±0.5pF  | GJM0335C1E9R7DB01# |  |
|        |               |         | 9.8pF  | ±0.05pF | GJM0335C1E9R8WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1E9R8BB01# |  |
|        |               |         |        | ±0.25pF | GJM0335C1E9R8CB01# |  |
|        |               |         |        | ±0.5pF  | GJM0335C1E9R8DB01# |  |
|        |               |         | 9.9pF  | ±0.05pF | GJM0335C1E9R9WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0335C1E9R9BB01# |  |
|        |               |         |        | ±0.25pF | GJM0335C1E9R9CB01# |  |
|        |               |         |        | ±0.5pF  | GJM0335C1E9R9DB01# |  |
|        |               |         | 10pF   | ±2%     | GJM0335C1E100GB01# |  |
|        |               |         |        | ±5%     | GJM0335C1E100JB01# |  |
|        |               |         | 11pF   | ±2%     | GJM0335C1E110GB01# |  |
|        |               |         |        | ±5%     | GJM0335C1E110JB01# |  |
|        |               |         | 12pF   | ±2%     | GJM0335C1E120GB01# |  |
|        |               |         |        | ±5%     | GJM0335C1E120JB01# |  |
|        |               |         | 13pF   | ±2%     | GJM0335C1E130GB01# |  |
|        |               |         |        | ±5%     | GJM0335C1E130JB01# |  |
|        |               |         | 15pF   | ±2%     | GJM0335C1E150GB01# |  |
|        |               |         |        | ±5%     | GJM0335C1E150JB01# |  |
|        |               |         | 16pF   | ±2%     | GJM0335C1E160GB01# |  |
|        |               |         |        | ±5%     | GJM0335C1E160JB01# |  |
|        |               |         | 18pF   | ±2%     | GJM0335C1E180GB01# |  |
|        |               |         |        | ±5%     | GJM0335C1E180JB01# |  |
|        |               |         | 20pF   | ±2%     | GJM0335C1E200GB01# |  |
|        |               |         |        | ±5%     | GJM0335C1E200JB01# |  |
|        |               |         | 22pF   | ±2%     | GJM0335C1E220GB01# |  |
|        |               |         |        | ±5%     | GJM0335C1E220JB01# |  |
|        |               |         | 24pF   | ±2%     | GJM0335C1E240GB01# |  |
|        |               |         |        | ±5%     | GJM0335C1E240JB01# |  |
|        |               |         | 27pF   | ±2%     | GJM0335C1E270GB01# |  |
|        |               |         |        | ±5%     | GJM0335C1E270JB01# |  |
|        |               |         | 30pF   | ±2%     | GJM0335C1E300GB01# |  |
|        |               |         |        | ±5%     | GJM0335C1E300JB01# |  |
|        |               |         | 33pF   | ±2%     | GJM0335C1E330GB01# |  |
|        |               |         |        | ±5%     | GJM0335C1E330JB01# |  |
|        |               | CK      | 0.20pF | ±0.05pF | GJM0334C1ER20WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0334C1ER20BB01# |  |
|        |               |         | 0.30pF | ±0.05pF | GJM0334C1ER30WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0334C1ER30BB01# |  |
|        |               |         | 0.40pF | ±0.05pF | GJM0334C1ER40WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0334C1ER40BB01# |  |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.33mm | 25Vdc         | CK      | 0.50pF | ±0.05pF | GJM0334C1E50WB01#  |  |
|        |               |         |        | ±0.1pF  | GJM0334C1E50BB01#  |  |
|        |               |         | 0.60pF | ±0.05pF | GJM0334C1E60WB01#  |  |
|        |               |         |        | ±0.1pF  | GJM0334C1E60BB01#  |  |
|        |               |         | 0.70pF | ±0.05pF | GJM0334C1E70WB01#  |  |
|        |               |         |        | ±0.1pF  | GJM0334C1E70BB01#  |  |
|        |               |         | 0.80pF | ±0.05pF | GJM0334C1E80WB01#  |  |
|        |               |         |        | ±0.1pF  | GJM0334C1E80BB01#  |  |
|        |               |         | 0.90pF | ±0.05pF | GJM0334C1E90WB01#  |  |
|        |               |         |        | ±0.1pF  | GJM0334C1E90BB01#  |  |
|        |               |         | 1.0pF  | ±0.05pF | GJM0334C1E1R0WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0334C1E1R0BB01# |  |
|        |               |         |        | ±0.25pF | GJM0334C1E1R0CB01# |  |
|        |               |         | 1.1pF  | ±0.05pF | GJM0334C1E1R1WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0334C1E1R1BB01# |  |
|        |               |         |        | ±0.25pF | GJM0334C1E1R1CB01# |  |
|        |               |         | 1.2pF  | ±0.05pF | GJM0334C1E1R2WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0334C1E1R2BB01# |  |
|        |               |         |        | ±0.25pF | GJM0334C1E1R2CB01# |  |
|        |               |         | 1.3pF  | ±0.05pF | GJM0334C1E1R3WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0334C1E1R3BB01# |  |
|        |               |         |        | ±0.25pF | GJM0334C1E1R3CB01# |  |
|        |               |         | 1.4pF  | ±0.05pF | GJM0334C1E1R4WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0334C1E1R4BB01# |  |
|        |               |         |        | ±0.25pF | GJM0334C1E1R4CB01# |  |
|        |               |         | 1.5pF  | ±0.05pF | GJM0334C1E1R5WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0334C1E1R5BB01# |  |
|        |               |         |        | ±0.25pF | GJM0334C1E1R5CB01# |  |
|        |               |         | 1.6pF  | ±0.05pF | GJM0334C1E1R6WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0334C1E1R6BB01# |  |
|        |               |         |        | ±0.25pF | GJM0334C1E1R6CB01# |  |
|        |               |         | 1.7pF  | ±0.05pF | GJM0334C1E1R7WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0334C1E1R7BB01# |  |
|        |               |         |        | ±0.25pF | GJM0334C1E1R7CB01# |  |
|        |               |         | 1.8pF  | ±0.05pF | GJM0334C1E1R8WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0334C1E1R8BB01# |  |
|        |               |         |        | ±0.25pF | GJM0334C1E1R8CB01# |  |
|        |               |         | 1.9pF  | ±0.05pF | GJM0334C1E1R9WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0334C1E1R9BB01# |  |
|        |               |         |        | ±0.25pF | GJM0334C1E1R9CB01# |  |
|        |               |         | 2.0pF  | ±0.05pF | GJM0334C1E2R0WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0334C1E2R0BB01# |  |
|        |               |         |        | ±0.25pF | GJM0334C1E2R0CB01# |  |
|        |               | CJ      | 2.1pF  | ±0.05pF | GJM0333C1E2R1WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0333C1E2R1BB01# |  |
|        |               |         |        | ±0.25pF | GJM0333C1E2R1CB01# |  |
|        |               |         | 2.2pF  | ±0.05pF | GJM0333C1E2R2WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0333C1E2R2BB01# |  |
|        |               |         |        | ±0.25pF | GJM0333C1E2R2CB01# |  |
|        |               |         | 2.3pF  | ±0.05pF | GJM0333C1E2R3WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0333C1E2R3BB01# |  |
|        |               |         |        | ±0.25pF | GJM0333C1E2R3CB01# |  |
|        |               |         | 2.4pF  | ±0.05pF | GJM0333C1E2R4WB01# |  |
|        |               |         |        | ±0.1pF  | GJM0333C1E2R4BB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 25Vdc         | CJ      | 2.4pF | ±0.25pF | GJM0333C1E2R4CB01# |  |
|        |               |         |       | ±0.05pF | GJM0333C1E2R5WB01# |  |
|        |               |         | 2.5pF | ±0.05pF | GJM0333C1E2R5BB01# |  |
|        |               |         |       | ±0.1pF  | GJM0333C1E2R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0333C1E2R5CB01# |  |
|        |               |         | 2.6pF | ±0.05pF | GJM0333C1E2R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0333C1E2R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0333C1E2R6CB01# |  |
|        |               |         | 2.7pF | ±0.05pF | GJM0333C1E2R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0333C1E2R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0333C1E2R7CB01# |  |
|        |               |         | 2.8pF | ±0.05pF | GJM0333C1E2R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0333C1E2R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0333C1E2R8CB01# |  |
|        |               |         | 2.9pF | ±0.05pF | GJM0333C1E2R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0333C1E2R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0333C1E2R9CB01# |  |
|        |               |         | 3.0pF | ±0.05pF | GJM0333C1E3R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0333C1E3R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0333C1E3R0CB01# |  |
|        |               |         | 3.1pF | ±0.05pF | GJM0333C1E3R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0333C1E3R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0333C1E3R1CB01# |  |
|        |               |         | 3.2pF | ±0.05pF | GJM0333C1E3R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0333C1E3R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0333C1E3R2CB01# |  |
|        |               |         | 3.3pF | ±0.05pF | GJM0333C1E3R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0333C1E3R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0333C1E3R3CB01# |  |
|        |               |         | 3.4pF | ±0.05pF | GJM0333C1E3R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0333C1E3R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0333C1E3R4CB01# |  |
|        |               |         | 3.5pF | ±0.05pF | GJM0333C1E3R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0333C1E3R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0333C1E3R5CB01# |  |
|        |               |         | 3.6pF | ±0.05pF | GJM0333C1E3R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0333C1E3R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0333C1E3R6CB01# |  |
|        |               |         | 3.7pF | ±0.05pF | GJM0333C1E3R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0333C1E3R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0333C1E3R7CB01# |  |
|        |               |         | 3.8pF | ±0.05pF | GJM0333C1E3R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0333C1E3R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0333C1E3R8CB01# |  |
|        |               |         | 3.9pF | ±0.05pF | GJM0333C1E3R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0333C1E3R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0333C1E3R9CB01# |  |
|        |               | CH      | 4.0pF | ±0.05pF | GJM0332C1E4R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E4R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E4R0CB01# |  |
|        |               |         | 4.1pF | ±0.05pF | GJM0332C1E4R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E4R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E4R1CB01# |  |
|        |               |         | 4.2pF | ±0.05pF | GJM0332C1E4R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E4R2BB01# |  |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type **HiQ** Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 25Vdc         | CH      | 4.2pF | ±0.25pF | GJM0332C1E4R2CB01# |  |
|        |               |         |       | ±0.05pF | GJM0332C1E4R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E4R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E4R3CB01# |  |
|        |               |         | 4.4pF | ±0.05pF | GJM0332C1E4R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E4R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E4R4CB01# |  |
|        |               |         | 4.5pF | ±0.05pF | GJM0332C1E4R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E4R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E4R5CB01# |  |
|        |               |         | 4.6pF | ±0.05pF | GJM0332C1E4R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E4R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E4R6CB01# |  |
|        |               |         | 4.7pF | ±0.05pF | GJM0332C1E4R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E4R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E4R7CB01# |  |
|        |               |         | 4.8pF | ±0.05pF | GJM0332C1E4R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E4R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E4R8CB01# |  |
|        |               |         | 4.9pF | ±0.05pF | GJM0332C1E4R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E4R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E4R9CB01# |  |
|        |               |         | 5.0pF | ±0.05pF | GJM0332C1E5R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E5R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E5R0CB01# |  |
|        |               |         | 5.1pF | ±0.05pF | GJM0332C1E5R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E5R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E5R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E5R1DB01# |  |
|        |               |         | 5.2pF | ±0.05pF | GJM0332C1E5R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E5R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E5R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E5R2DB01# |  |
|        |               |         | 5.3pF | ±0.05pF | GJM0332C1E5R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E5R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E5R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E5R3DB01# |  |
|        |               |         | 5.4pF | ±0.05pF | GJM0332C1E5R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E5R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E5R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E5R4DB01# |  |
|        |               |         | 5.5pF | ±0.05pF | GJM0332C1E5R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E5R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E5R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E5R5DB01# |  |
|        |               |         | 5.6pF | ±0.05pF | GJM0332C1E5R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E5R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E5R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E5R6DB01# |  |
|        |               |         | 5.7pF | ±0.05pF | GJM0332C1E5R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E5R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E5R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E5R7DB01# |  |
|        |               |         | 5.8pF | ±0.05pF | GJM0332C1E5R8WB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 25Vdc         | CH      | 5.8pF | ±0.1pF  | GJM0332C1E5R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E5R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E5R8DB01# |  |
|        |               |         | 5.9pF | ±0.05pF | GJM0332C1E5R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E5R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E5R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E5R9DB01# |  |
|        |               |         | 6.0pF | ±0.05pF | GJM0332C1E6R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E6R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E6R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E6R0DB01# |  |
|        |               |         | 6.1pF | ±0.05pF | GJM0332C1E6R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E6R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E6R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E6R1DB01# |  |
|        |               |         | 6.2pF | ±0.05pF | GJM0332C1E6R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E6R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E6R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E6R2DB01# |  |
|        |               |         | 6.3pF | ±0.05pF | GJM0332C1E6R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E6R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E6R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E6R3DB01# |  |
|        |               |         | 6.4pF | ±0.05pF | GJM0332C1E6R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E6R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E6R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E6R4DB01# |  |
|        |               |         | 6.5pF | ±0.05pF | GJM0332C1E6R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E6R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E6R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E6R5DB01# |  |
|        |               |         | 6.6pF | ±0.05pF | GJM0332C1E6R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E6R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E6R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E6R6DB01# |  |
|        |               |         | 6.7pF | ±0.05pF | GJM0332C1E6R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E6R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E6R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E6R7DB01# |  |
|        |               |         | 6.8pF | ±0.05pF | GJM0332C1E6R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E6R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E6R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E6R8DB01# |  |
|        |               |         | 6.9pF | ±0.05pF | GJM0332C1E6R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E6R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E6R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E6R9DB01# |  |
|        |               |         | 7.0pF | ±0.05pF | GJM0332C1E7R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E7R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E7R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E7R0DB01# |  |
|        |               |         | 7.1pF | ±0.05pF | GJM0332C1E7R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E7R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E7R1CB01# |  |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 25Vdc         | CH      | 7.1pF | ±0.5pF  | GJM0332C1E7R1DB01# |  |
|        |               |         |       | ±0.05pF | GJM0332C1E7R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E7R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E7R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E7R2DB01# |  |
|        |               |         | 7.3pF | ±0.05pF | GJM0332C1E7R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E7R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E7R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E7R3DB01# |  |
|        |               |         | 7.4pF | ±0.05pF | GJM0332C1E7R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E7R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E7R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E7R4DB01# |  |
|        |               |         | 7.5pF | ±0.05pF | GJM0332C1E7R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E7R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E7R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E7R5DB01# |  |
|        |               |         | 7.6pF | ±0.05pF | GJM0332C1E7R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E7R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E7R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E7R6DB01# |  |
|        |               |         | 7.7pF | ±0.05pF | GJM0332C1E7R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E7R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E7R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E7R7DB01# |  |
|        |               |         | 7.8pF | ±0.05pF | GJM0332C1E7R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E7R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E7R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E7R8DB01# |  |
|        |               |         | 7.9pF | ±0.05pF | GJM0332C1E7R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E7R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E7R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E7R9DB01# |  |
|        |               |         | 8.0pF | ±0.05pF | GJM0332C1E8R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E8R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E8R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E8R0DB01# |  |
|        |               |         | 8.1pF | ±0.05pF | GJM0332C1E8R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E8R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E8R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E8R1DB01# |  |
|        |               |         | 8.2pF | ±0.05pF | GJM0332C1E8R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E8R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E8R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E8R2DB01# |  |
|        |               |         | 8.3pF | ±0.05pF | GJM0332C1E8R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E8R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E8R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E8R3DB01# |  |
|        |               |         | 8.4pF | ±0.05pF | GJM0332C1E8R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E8R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E8R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E8R4DB01# |  |
|        |               |         | 8.5pF | ±0.05pF | GJM0332C1E8R5WB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 25Vdc         | CH      | 8.5pF | ±0.1pF  | GJM0332C1E8R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E8R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E8R5DB01# |  |
|        |               |         | 8.6pF | ±0.05pF | GJM0332C1E8R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E8R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E8R6CB01# |  |
|        |               |         | 8.7pF | ±0.05pF | GJM0332C1E8R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E8R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E8R7CB01# |  |
|        |               |         | 8.8pF | ±0.05pF | GJM0332C1E8R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E8R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E8R8CB01# |  |
|        |               |         | 8.9pF | ±0.05pF | GJM0332C1E8R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E8R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E8R9CB01# |  |
|        |               |         | 9.0pF | ±0.05pF | GJM0332C1E9R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E9R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E9R0CB01# |  |
|        |               |         | 9.1pF | ±0.05pF | GJM0332C1E9R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E9R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E9R1CB01# |  |
|        |               |         | 9.2pF | ±0.05pF | GJM0332C1E9R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E9R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E9R2CB01# |  |
|        |               |         | 9.3pF | ±0.05pF | GJM0332C1E9R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E9R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E9R3CB01# |  |
|        |               |         | 9.4pF | ±0.05pF | GJM0332C1E9R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E9R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E9R4CB01# |  |
|        |               |         | 9.5pF | ±0.05pF | GJM0332C1E9R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E9R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E9R5CB01# |  |
|        |               |         | 9.6pF | ±0.05pF | GJM0332C1E9R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E9R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E9R6CB01# |  |
|        |               |         | 9.7pF | ±0.05pF | GJM0332C1E9R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E9R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E9R7CB01# |  |
|        |               |         | 9.8pF | ±0.05pF | GJM0332C1E9R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM0332C1E9R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E9R8CB01# |  |

Part number # indicates the package specification code.



## GJM Series Temperature Compensating Type **HiQ** Part Number List

(→ ■ 0.6×0.3mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.33mm | 25Vdc         | CH      | 9.8pF | ±0.5pF  | GJM0332C1E9R8DB01# |  |
|        |               |         |       | ±0.05pF | GJM0332C1E9R9WB01# |  |
|        |               |         | 9.9pF | ±0.1pF  | GJM0332C1E9R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM0332C1E9R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM0332C1E9R9DB01# |  |
|        |               |         | 10pF  | ±2%     | GJM0332C1E100GB01# |  |
|        |               |         |       | ±5%     | GJM0332C1E100JB01# |  |
|        |               |         | 11pF  | ±2%     | GJM0332C1E110GB01# |  |
|        |               |         |       | ±5%     | GJM0332C1E110JB01# |  |
|        |               |         | 12pF  | ±2%     | GJM0332C1E120GB01# |  |
|        |               |         |       | ±5%     | GJM0332C1E120JB01# |  |
|        |               |         | 13pF  | ±2%     | GJM0332C1E130GB01# |  |
|        |               |         |       | ±5%     | GJM0332C1E130JB01# |  |
|        |               |         | 15pF  | ±2%     | GJM0332C1E150GB01# |  |
|        |               |         |       | ±5%     | GJM0332C1E150JB01# |  |
|        |               |         | 16pF  | ±2%     | GJM0332C1E160GB01# |  |
|        |               |         |       | ±5%     | GJM0332C1E160JB01# |  |
|        |               |         | 18pF  | ±2%     | GJM0332C1E180GB01# |  |
|        |               |         |       | ±5%     | GJM0332C1E180JB01# |  |
|        |               |         | 20pF  | ±2%     | GJM0332C1E200GB01# |  |
|        |               |         |       | ±5%     | GJM0332C1E200JB01# |  |
|        |               |         | 22pF  | ±2%     | GJM0332C1E220GB01# |  |
|        |               |         |       | ±5%     | GJM0332C1E220JB01# |  |
|        |               |         | 24pF  | ±2%     | GJM0332C1E240GB01# |  |
|        |               |         |       | ±5%     | GJM0332C1E240JB01# |  |
|        |               |         | 27pF  | ±2%     | GJM0332C1E270GB01# |  |
|        |               |         |       | ±5%     | GJM0332C1E270JB01# |  |
|        |               |         | 30pF  | ±2%     | GJM0332C1E300GB01# |  |
|        |               |         |       | ±5%     | GJM0332C1E300JB01# |  |
|        |               |         | 33pF  | ±2%     | GJM0332C1E330GB01# |  |
|        |               |         |       | ±5%     | GJM0332C1E330JB01# |  |

■ 1.0×0.5mm

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.55mm | 50Vdc         | C0G     | 0.10pF | ±0.05pF | GJM1555C1HR10WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1555C1HR10BB01# |  |
|        |               |         | 0.20pF | ±0.05pF | GJM1555C1HR20WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1555C1HR20BB01# |  |
|        |               |         | 0.30pF | ±0.05pF | GJM1555C1HR30WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1555C1HR30BB01# |  |
|        |               |         | 0.40pF | ±0.05pF | GJM1555C1HR40WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1555C1HR40BB01# |  |
|        |               |         | 0.50pF | ±0.05pF | GJM1555C1HR50WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1555C1HR50BB01# |  |
|        |               |         | 0.60pF | ±0.05pF | GJM1555C1HR60WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1555C1HR60BB01# |  |
|        |               |         | 0.70pF | ±0.05pF | GJM1555C1HR70WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1555C1HR70BB01# |  |
|        |               |         | 0.80pF | ±0.05pF | GJM1555C1HR80WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1555C1HR80BB01# |  |
|        |               |         | 0.90pF | ±0.05pF | GJM1555C1HR90WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1555C1HR90BB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | C0G     | 1.0pF | ±0.05pF | GJM1555C1H1R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H1R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H1R0CB01# |  |
|        |               |         | 1.1pF | ±0.05pF | GJM1555C1H1R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H1R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H1R1CB01# |  |
|        |               |         | 1.2pF | ±0.05pF | GJM1555C1H1R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H1R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H1R2CB01# |  |
|        |               |         | 1.3pF | ±0.05pF | GJM1555C1H1R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H1R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H1R3CB01# |  |
|        |               |         | 1.4pF | ±0.05pF | GJM1555C1H1R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H1R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H1R4CB01# |  |
|        |               |         | 1.5pF | ±0.05pF | GJM1555C1H1R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H1R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H1R5CB01# |  |
|        |               |         | 1.6pF | ±0.05pF | GJM1555C1H1R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H1R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H1R6CB01# |  |
|        |               |         | 1.7pF | ±0.05pF | GJM1555C1H1R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H1R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H1R7CB01# |  |
|        |               |         | 1.8pF | ±0.05pF | GJM1555C1H1R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H1R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H1R8CB01# |  |
|        |               |         | 1.9pF | ±0.05pF | GJM1555C1H1R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H1R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H1R9CB01# |  |
|        |               |         | 2.0pF | ±0.05pF | GJM1555C1H2R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H2R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H2R0CB01# |  |
|        |               |         | 2.1pF | ±0.05pF | GJM1555C1H2R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H2R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H2R1CB01# |  |
|        |               |         | 2.2pF | ±0.05pF | GJM1555C1H2R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H2R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H2R2CB01# |  |
|        |               |         | 2.3pF | ±0.05pF | GJM1555C1H2R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H2R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H2R3CB01# |  |
|        |               |         | 2.4pF | ±0.05pF | GJM1555C1H2R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H2R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H2R4CB01# |  |
|        |               |         | 2.5pF | ±0.05pF | GJM1555C1H2R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H2R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H2R5CB01# |  |
|        |               |         | 2.6pF | ±0.05pF | GJM1555C1H2R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H2R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H2R6CB01# |  |
|        |               |         | 2.7pF | ±0.05pF | GJM1555C1H2R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H2R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H2R7CB01# |  |

Part number # indicates the package specification code.



## GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | C0G     | 2.8pF | ±0.05pF | GJM1555C1H2R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H2R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H2R8CB01# |  |
|        |               |         | 2.9pF | ±0.05pF | GJM1555C1H2R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H2R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H2R9CB01# |  |
|        |               |         | 3.0pF | ±0.05pF | GJM1555C1H3R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H3R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H3R0CB01# |  |
|        |               |         | 3.1pF | ±0.05pF | GJM1555C1H3R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H3R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H3R1CB01# |  |
|        |               |         | 3.2pF | ±0.05pF | GJM1555C1H3R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H3R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H3R2CB01# |  |
|        |               |         | 3.3pF | ±0.05pF | GJM1555C1H3R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H3R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H3R3CB01# |  |
|        |               |         | 3.4pF | ±0.05pF | GJM1555C1H3R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H3R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H3R4CB01# |  |
|        |               |         | 3.5pF | ±0.05pF | GJM1555C1H3R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H3R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H3R5CB01# |  |
|        |               |         | 3.6pF | ±0.05pF | GJM1555C1H3R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H3R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H3R6CB01# |  |
|        |               |         | 3.7pF | ±0.05pF | GJM1555C1H3R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H3R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H3R7CB01# |  |
|        |               |         | 3.8pF | ±0.05pF | GJM1555C1H3R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H3R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H3R8CB01# |  |
|        |               |         | 3.9pF | ±0.05pF | GJM1555C1H3R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H3R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H3R9CB01# |  |
|        |               |         | 4.0pF | ±0.05pF | GJM1555C1H4R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H4R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H4R0CB01# |  |
|        |               |         | 4.1pF | ±0.05pF | GJM1555C1H4R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H4R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H4R1CB01# |  |
|        |               |         | 4.2pF | ±0.05pF | GJM1555C1H4R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H4R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H4R2CB01# |  |
|        |               |         | 4.3pF | ±0.05pF | GJM1555C1H4R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H4R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H4R3CB01# |  |
|        |               |         | 4.4pF | ±0.05pF | GJM1555C1H4R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H4R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H4R4CB01# |  |
|        |               |         | 4.5pF | ±0.05pF | GJM1555C1H4R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H4R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H4R5CB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | C0G     | 4.6pF | ±0.05pF | GJM1555C1H4R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H4R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H4R6CB01# |  |
|        |               |         | 4.7pF | ±0.05pF | GJM1555C1H4R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H4R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H4R7CB01# |  |
|        |               |         | 4.8pF | ±0.05pF | GJM1555C1H4R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H4R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H4R8CB01# |  |
|        |               |         | 4.9pF | ±0.05pF | GJM1555C1H4R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H4R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H4R9CB01# |  |
|        |               |         | 5.0pF | ±0.05pF | GJM1555C1H5R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H5R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H5R0CB01# |  |
|        |               |         | 5.1pF | ±0.05pF | GJM1555C1H5R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H5R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H5R1CB01# |  |
|        |               |         | 5.2pF | ±0.05pF | GJM1555C1H5R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H5R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H5R2CB01# |  |
|        |               |         | 5.3pF | ±0.05pF | GJM1555C1H5R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H5R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H5R3CB01# |  |
|        |               |         | 5.4pF | ±0.05pF | GJM1555C1H5R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H5R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H5R4CB01# |  |
|        |               |         | 5.5pF | ±0.05pF | GJM1555C1H5R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H5R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H5R5CB01# |  |
|        |               |         | 5.6pF | ±0.05pF | GJM1555C1H5R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H5R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H5R6CB01# |  |
|        |               |         | 5.7pF | ±0.05pF | GJM1555C1H5R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H5R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H5R7CB01# |  |
|        |               |         | 5.8pF | ±0.05pF | GJM1555C1H5R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H5R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H5R8CB01# |  |
|        |               |         | 5.9pF | ±0.05pF | GJM1555C1H5R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H5R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H5R9CB01# |  |
|        |               |         | 6.0pF | ±0.05pF | GJM1555C1H6R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H6R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H6R0CB01# |  |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | C0G     | 6.0pF | ±0.5pF  | GJM1555C1H6R0DB01# |  |
|        |               |         |       | ±0.05pF | GJM1555C1H6R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H6R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H6R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H6R1DB01# |  |
|        |               |         | 6.2pF | ±0.05pF | GJM1555C1H6R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H6R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H6R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H6R2DB01# |  |
|        |               |         | 6.3pF | ±0.05pF | GJM1555C1H6R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H6R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H6R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H6R3DB01# |  |
|        |               |         | 6.4pF | ±0.05pF | GJM1555C1H6R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H6R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H6R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H6R4DB01# |  |
|        |               |         | 6.5pF | ±0.05pF | GJM1555C1H6R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H6R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H6R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H6R5DB01# |  |
|        |               |         | 6.6pF | ±0.05pF | GJM1555C1H6R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H6R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H6R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H6R6DB01# |  |
|        |               |         | 6.7pF | ±0.05pF | GJM1555C1H6R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H6R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H6R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H6R7DB01# |  |
|        |               |         | 6.8pF | ±0.05pF | GJM1555C1H6R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H6R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H6R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H6R8DB01# |  |
|        |               |         | 6.9pF | ±0.05pF | GJM1555C1H6R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H6R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H6R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H6R9DB01# |  |
|        |               |         | 7.0pF | ±0.05pF | GJM1555C1H7R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H7R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H7R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H7R0DB01# |  |
|        |               |         | 7.1pF | ±0.05pF | GJM1555C1H7R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H7R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H7R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H7R1DB01# |  |
|        |               |         | 7.2pF | ±0.05pF | GJM1555C1H7R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H7R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H7R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H7R2DB01# |  |
|        |               |         | 7.3pF | ±0.05pF | GJM1555C1H7R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H7R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H7R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H7R3DB01# |  |
|        |               |         | 7.4pF | ±0.05pF | GJM1555C1H7R4WB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | C0G     | 7.4pF | ±0.1pF  | GJM1555C1H7R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H7R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H7R4DB01# |  |
|        |               |         | 7.5pF | ±0.05pF | GJM1555C1H7R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H7R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H7R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H7R5DB01# |  |
|        |               |         | 7.6pF | ±0.05pF | GJM1555C1H7R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H7R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H7R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H7R6DB01# |  |
|        |               |         | 7.7pF | ±0.05pF | GJM1555C1H7R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H7R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H7R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H7R7DB01# |  |
|        |               |         | 7.8pF | ±0.05pF | GJM1555C1H7R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H7R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H7R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H7R8DB01# |  |
|        |               |         | 7.9pF | ±0.05pF | GJM1555C1H7R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H7R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H7R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H7R9DB01# |  |
|        |               |         | 8.0pF | ±0.05pF | GJM1555C1H8R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H8R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H8R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H8R0DB01# |  |
|        |               |         | 8.1pF | ±0.05pF | GJM1555C1H8R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H8R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H8R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H8R1DB01# |  |
|        |               |         | 8.2pF | ±0.05pF | GJM1555C1H8R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H8R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H8R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H8R2DB01# |  |
|        |               |         | 8.3pF | ±0.05pF | GJM1555C1H8R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H8R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H8R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H8R3DB01# |  |
|        |               |         | 8.4pF | ±0.05pF | GJM1555C1H8R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H8R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H8R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H8R4DB01# |  |
|        |               |         | 8.5pF | ±0.05pF | GJM1555C1H8R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H8R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H8R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H8R5DB01# |  |
|        |               |         | 8.6pF | ±0.05pF | GJM1555C1H8R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H8R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H8R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H8R6DB01# |  |
|        |               |         | 8.7pF | ±0.05pF | GJM1555C1H8R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H8R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H8R7CB01# |  |

Part number # indicates the package specification code.

## GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | C0G     | 8.7pF | ±0.5pF  | GJM1555C1H8R7DB01# |  |
|        |               |         |       | ±0.05pF | GJM1555C1H8R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H8R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H8R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H8R8DB01# |  |
|        |               |         | 8.9pF | ±0.05pF | GJM1555C1H8R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H8R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H8R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H8R9DB01# |  |
|        |               |         | 9.0pF | ±0.05pF | GJM1555C1H9R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H9R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H9R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H9R0DB01# |  |
|        |               |         | 9.1pF | ±0.05pF | GJM1555C1H9R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H9R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H9R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H9R1DB01# |  |
|        |               |         | 9.2pF | ±0.05pF | GJM1555C1H9R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H9R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H9R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H9R2DB01# |  |
|        |               |         | 9.3pF | ±0.05pF | GJM1555C1H9R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H9R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H9R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H9R3DB01# |  |
|        |               |         | 9.4pF | ±0.05pF | GJM1555C1H9R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H9R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H9R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H9R4DB01# |  |
|        |               |         | 9.5pF | ±0.05pF | GJM1555C1H9R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H9R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H9R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H9R5DB01# |  |
|        |               |         | 9.6pF | ±0.05pF | GJM1555C1H9R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H9R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H9R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H9R6DB01# |  |
|        |               |         | 9.7pF | ±0.05pF | GJM1555C1H9R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H9R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H9R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H9R7DB01# |  |
|        |               |         | 9.8pF | ±0.05pF | GJM1555C1H9R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H9R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H9R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H9R8DB01# |  |
|        |               |         | 9.9pF | ±0.05pF | GJM1555C1H9R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1555C1H9R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM1555C1H9R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1555C1H9R9DB01# |  |
|        |               |         | 10pF  | ±2%     | GJM1555C1H100GB01# |  |
|        |               |         |       | ±5%     | GJM1555C1H100JB01# |  |
|        |               |         | 11pF  | ±2%     | GJM1555C1H110GB01# |  |
|        |               |         |       | ±5%     | GJM1555C1H110JB01# |  |
|        |               |         | 12pF  | ±2%     | GJM1555C1H120GB01# |  |

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.55mm | 50Vdc         | C0G     | 12pF   | ±5%     | GJM1555C1H120JB01# |  |
|        |               |         |        | ±2%     | GJM1555C1H130GB01# |  |
|        |               |         | 13pF   | ±5%     | GJM1555C1H130JB01# |  |
|        |               |         |        | ±2%     | GJM1555C1H150GB01# |  |
|        |               |         | 15pF   | ±5%     | GJM1555C1H150JB01# |  |
|        |               |         |        | ±2%     | GJM1555C1H160GB01# |  |
|        |               |         | 16pF   | ±5%     | GJM1555C1H160JB01# |  |
|        |               |         |        | ±2%     | GJM1555C1H180GB01# |  |
|        |               |         | 18pF   | ±5%     | GJM1555C1H180JB01# |  |
|        |               |         |        | ±2%     | GJM1555C1H200GB01# |  |
|        |               |         | 20pF   | ±5%     | GJM1555C1H200JB01# |  |
|        |               |         |        | ±1%     | GJM1555C1H220FB01# |  |
|        |               |         | 22pF   | ±2%     | GJM1555C1H220GB01# |  |
|        |               |         |        | ±5%     | GJM1555C1H220JB01# |  |
|        |               |         | 24pF   | ±1%     | GJM1555C1H240FB01# |  |
|        |               |         |        | ±2%     | GJM1555C1H240GB01# |  |
|        |               |         |        | ±5%     | GJM1555C1H240JB01# |  |
|        |               |         |        | ±1%     | GJM1555C1H270FB01# |  |
|        |               |         | 27pF   | ±2%     | GJM1555C1H270GB01# |  |
|        |               |         |        | ±5%     | GJM1555C1H270JB01# |  |
|        |               |         | 30pF   | ±1%     | GJM1555C1H300FB01# |  |
|        |               |         |        | ±2%     | GJM1555C1H300GB01# |  |
|        |               |         |        | ±5%     | GJM1555C1H300JB01# |  |
|        |               |         | 33pF   | ±1%     | GJM1555C1H330FB01# |  |
|        |               |         |        | ±2%     | GJM1555C1H330GB01# |  |
|        |               |         |        | ±5%     | GJM1555C1H330JB01# |  |
|        |               |         | 36pF   | ±1%     | GJM1555C1H360FB01# |  |
|        |               |         |        | ±2%     | GJM1555C1H360GB01# |  |
|        |               |         |        | ±5%     | GJM1555C1H360JB01# |  |
|        |               |         | 39pF   | ±1%     | GJM1555C1H390FB01# |  |
|        |               |         |        | ±2%     | GJM1555C1H390GB01# |  |
|        |               |         |        | ±5%     | GJM1555C1H390JB01# |  |
|        |               |         | 43pF   | ±1%     | GJM1555C1H430FB01# |  |
|        |               |         |        | ±2%     | GJM1555C1H430GB01# |  |
|        |               |         |        | ±5%     | GJM1555C1H430JB01# |  |
|        |               |         | 47pF   | ±1%     | GJM1555C1H470FB01# |  |
|        |               |         |        | ±2%     | GJM1555C1H470GB01# |  |
|        |               |         |        | ±5%     | GJM1555C1H470JB01# |  |
|        |               | CK      | 0.10pF | ±0.05pF | GJM1554C1HR10WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1HR10BB01# |  |
|        |               |         | 0.20pF | ±0.05pF | GJM1554C1HR20WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1HR20BB01# |  |
|        |               |         | 0.30pF | ±0.05pF | GJM1554C1HR30WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1HR30BB01# |  |
|        |               |         | 0.40pF | ±0.05pF | GJM1554C1HR40WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1HR40BB01# |  |
|        |               |         | 0.50pF | ±0.05pF | GJM1554C1HR50WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1HR50BB01# |  |
|        |               |         | 0.60pF | ±0.05pF | GJM1554C1HR60WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1HR60BB01# |  |
|        |               |         | 0.70pF | ±0.05pF | GJM1554C1HR70WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1HR70BB01# |  |
|        |               |         | 0.80pF | ±0.05pF | GJM1554C1HR80WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1HR80BB01# |  |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type **HiQ** Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.   | Tol.    | Part Number        |  |
|--------|---------------|---------|--------|---------|--------------------|--|
| 0.55mm | 50Vdc         | CK      | 0.90pF | ±0.05pF | GJM1554C1HR90WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1HR90BB01# |  |
|        |               |         | 1.0pF  | ±0.05pF | GJM1554C1H1R0WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1H1R0BB01# |  |
|        |               |         |        | ±0.25pF | GJM1554C1H1R0CB01# |  |
|        |               |         | 1.1pF  | ±0.05pF | GJM1554C1H1R1WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1H1R1BB01# |  |
|        |               |         |        | ±0.25pF | GJM1554C1H1R1CB01# |  |
|        |               |         | 1.2pF  | ±0.05pF | GJM1554C1H1R2WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1H1R2BB01# |  |
|        |               |         |        | ±0.25pF | GJM1554C1H1R2CB01# |  |
|        |               |         | 1.3pF  | ±0.05pF | GJM1554C1H1R3WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1H1R3BB01# |  |
|        |               |         |        | ±0.25pF | GJM1554C1H1R3CB01# |  |
|        |               |         | 1.4pF  | ±0.05pF | GJM1554C1H1R4WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1H1R4BB01# |  |
|        |               |         |        | ±0.25pF | GJM1554C1H1R4CB01# |  |
|        |               |         | 1.5pF  | ±0.05pF | GJM1554C1H1R5WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1H1R5BB01# |  |
|        |               |         |        | ±0.25pF | GJM1554C1H1R5CB01# |  |
|        |               |         | 1.6pF  | ±0.05pF | GJM1554C1H1R6WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1H1R6BB01# |  |
|        |               |         |        | ±0.25pF | GJM1554C1H1R6CB01# |  |
|        |               |         | 1.7pF  | ±0.05pF | GJM1554C1H1R7WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1H1R7BB01# |  |
|        |               |         |        | ±0.25pF | GJM1554C1H1R7CB01# |  |
|        |               |         | 1.8pF  | ±0.05pF | GJM1554C1H1R8WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1H1R8BB01# |  |
|        |               |         |        | ±0.25pF | GJM1554C1H1R8CB01# |  |
|        |               |         | 1.9pF  | ±0.05pF | GJM1554C1H1R9WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1H1R9BB01# |  |
|        |               |         |        | ±0.25pF | GJM1554C1H1R9CB01# |  |
|        |               |         | 2.0pF  | ±0.05pF | GJM1554C1H2R0WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1554C1H2R0BB01# |  |
|        |               |         |        | ±0.25pF | GJM1554C1H2R0CB01# |  |
|        |               | CJ      | 2.1pF  | ±0.05pF | GJM1553C1H2R1WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1553C1H2R1BB01# |  |
|        |               |         |        | ±0.25pF | GJM1553C1H2R1CB01# |  |
|        |               |         | 2.2pF  | ±0.05pF | GJM1553C1H2R2WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1553C1H2R2BB01# |  |
|        |               |         |        | ±0.25pF | GJM1553C1H2R2CB01# |  |
|        |               |         | 2.3pF  | ±0.05pF | GJM1553C1H2R3WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1553C1H2R3BB01# |  |
|        |               |         |        | ±0.25pF | GJM1553C1H2R3CB01# |  |
|        |               |         | 2.4pF  | ±0.05pF | GJM1553C1H2R4WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1553C1H2R4BB01# |  |
|        |               |         |        | ±0.25pF | GJM1553C1H2R4CB01# |  |
|        |               |         | 2.5pF  | ±0.05pF | GJM1553C1H2R5WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1553C1H2R5BB01# |  |
|        |               |         |        | ±0.25pF | GJM1553C1H2R5CB01# |  |
|        |               |         | 2.6pF  | ±0.05pF | GJM1553C1H2R6WB01# |  |
|        |               |         |        | ±0.1pF  | GJM1553C1H2R6BB01# |  |
|        |               |         |        | ±0.25pF | GJM1553C1H2R6CB01# |  |
|        |               |         | 2.7pF  | ±0.05pF | GJM1553C1H2R7WB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | CJ      | 2.7pF | ±0.1pF  | GJM1553C1H2R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM1553C1H2R7CB01# |  |
|        |               |         | 2.8pF | ±0.05pF | GJM1553C1H2R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1553C1H2R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM1553C1H2R8CB01# |  |
|        |               |         | 2.9pF | ±0.05pF | GJM1553C1H2R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1553C1H2R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM1553C1H2R9CB01# |  |
|        |               |         | 3.0pF | ±0.05pF | GJM1553C1H3R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1553C1H3R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM1553C1H3R0CB01# |  |
|        |               |         | 3.1pF | ±0.05pF | GJM1553C1H3R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1553C1H3R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM1553C1H3R1CB01# |  |
|        |               |         | 3.2pF | ±0.05pF | GJM1553C1H3R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1553C1H3R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM1553C1H3R2CB01# |  |
|        |               |         | 3.3pF | ±0.05pF | GJM1553C1H3R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1553C1H3R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM1553C1H3R3CB01# |  |
|        |               |         | 3.4pF | ±0.05pF | GJM1553C1H3R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1553C1H3R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM1553C1H3R4CB01# |  |
|        |               |         | 3.5pF | ±0.05pF | GJM1553C1H3R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1553C1H3R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM1553C1H3R5CB01# |  |
|        |               |         | 3.6pF | ±0.05pF | GJM1553C1H3R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1553C1H3R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM1553C1H3R6CB01# |  |
|        |               |         | 3.7pF | ±0.05pF | GJM1553C1H3R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1553C1H3R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM1553C1H3R7CB01# |  |
|        |               |         | 3.8pF | ±0.05pF | GJM1553C1H3R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1553C1H3R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM1553C1H3R8CB01# |  |
|        |               |         | 3.9pF | ±0.05pF | GJM1553C1H3R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1553C1H3R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM1553C1H3R9CB01# |  |
|        |               | CH      | 4.0pF | ±0.05pF | GJM1552C1H4R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H4R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H4R0CB01# |  |
|        |               |         | 4.1pF | ±0.05pF | GJM1552C1H4R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H4R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H4R1CB01# |  |
|        |               |         | 4.2pF | ±0.05pF | GJM1552C1H4R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H4R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H4R2CB01# |  |
|        |               |         | 4.3pF | ±0.05pF | GJM1552C1H4R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H4R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H4R3CB01# |  |
|        |               |         | 4.4pF | ±0.05pF | GJM1552C1H4R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H4R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H4R4CB01# |  |
|        |               |         | 4.5pF | ±0.05pF | GJM1552C1H4R5WB01# |  |

Part number # indicates the package specification code.



## GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | CH      | 4.5pF | ±0.1pF  | GJM1552C1H4R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H4R5CB01# |  |
|        |               |         | 4.6pF | ±0.05pF | GJM1552C1H4R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H4R6BB01# |  |
|        |               |         | 4.7pF | ±0.25pF | GJM1552C1H4R6CB01# |  |
|        |               |         |       | ±0.05pF | GJM1552C1H4R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H4R7BB01# |  |
|        |               |         | 4.8pF | ±0.25pF | GJM1552C1H4R7CB01# |  |
|        |               |         |       | ±0.05pF | GJM1552C1H4R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H4R8BB01# |  |
|        |               |         | 4.9pF | ±0.25pF | GJM1552C1H4R8CB01# |  |
|        |               |         |       | ±0.05pF | GJM1552C1H4R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H4R9BB01# |  |
|        |               |         | 5.0pF | ±0.25pF | GJM1552C1H4R9CB01# |  |
|        |               |         |       | ±0.05pF | GJM1552C1H5R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H5R0BB01# |  |
|        |               |         | 5.1pF | ±0.25pF | GJM1552C1H5R0CB01# |  |
|        |               |         |       | ±0.05pF | GJM1552C1H5R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H5R1BB01# |  |
|        |               |         | 5.2pF | ±0.25pF | GJM1552C1H5R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H5R1DB01# |  |
|        |               |         | 5.3pF | ±0.05pF | GJM1552C1H5R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H5R2BB01# |  |
|        |               |         | 5.4pF | ±0.25pF | GJM1552C1H5R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H5R2DB01# |  |
|        |               |         | 5.5pF | ±0.05pF | GJM1552C1H5R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H5R3BB01# |  |
|        |               |         | 5.6pF | ±0.25pF | GJM1552C1H5R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H5R3DB01# |  |
|        |               |         | 5.7pF | ±0.05pF | GJM1552C1H5R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H5R4BB01# |  |
|        |               |         | 5.8pF | ±0.25pF | GJM1552C1H5R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H5R4DB01# |  |
|        |               |         | 5.9pF | ±0.05pF | GJM1552C1H5R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H5R5BB01# |  |
|        |               |         | 6.0pF | ±0.25pF | GJM1552C1H5R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H5R5DB01# |  |
|        |               |         | 6.1pF | ±0.05pF | GJM1552C1H5R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H5R6BB01# |  |
|        |               |         | 6.2pF | ±0.25pF | GJM1552C1H5R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H5R6DB01# |  |
|        |               |         | 6.3pF | ±0.05pF | GJM1552C1H5R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H5R7BB01# |  |
|        |               |         | 6.4pF | ±0.25pF | GJM1552C1H5R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H5R7DB01# |  |
|        |               |         | 6.5pF | ±0.05pF | GJM1552C1H5R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H5R8BB01# |  |
|        |               |         | 6.6pF | ±0.25pF | GJM1552C1H5R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H5R8DB01# |  |
|        |               |         | 6.7pF | ±0.05pF | GJM1552C1H5R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H5R9BB01# |  |
|        |               |         | 6.8pF | ±0.25pF | GJM1552C1H5R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H5R9DB01# |  |
|        |               |         | 6.9pF | ±0.05pF | GJM1552C1H6R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H6R0BB01# |  |
|        |               |         | 7.0pF | ±0.25pF | GJM1552C1H6R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H6R0DB01# |  |
|        |               |         | 7.1pF | ±0.05pF | GJM1552C1H6R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H6R1BB01# |  |
|        |               |         | 7.2pF | ±0.25pF | GJM1552C1H6R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H6R1DB01# |  |
|        |               |         | 7.3pF | ±0.05pF | GJM1552C1H6R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H6R2BB01# |  |
|        |               |         | 7.4pF | ±0.25pF | GJM1552C1H6R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H6R2DB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | CH      | 6.0pF | ±0.1pF  | GJM1552C1H6R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H6R0CB01# |  |
|        |               |         | 6.1pF | ±0.5pF  | GJM1552C1H6R0DB01# |  |
|        |               |         |       | ±0.05pF | GJM1552C1H6R1WB01# |  |
|        |               |         | 6.2pF | ±0.1pF  | GJM1552C1H6R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H6R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H6R1DB01# |  |
|        |               |         | 6.3pF | ±0.05pF | GJM1552C1H6R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H6R2BB01# |  |
|        |               |         | 6.4pF | ±0.25pF | GJM1552C1H6R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H6R2DB01# |  |
|        |               |         | 6.5pF | ±0.05pF | GJM1552C1H6R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H6R3BB01# |  |
|        |               |         | 6.6pF | ±0.25pF | GJM1552C1H6R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H6R3DB01# |  |
|        |               |         | 6.7pF | ±0.05pF | GJM1552C1H6R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H6R4BB01# |  |
|        |               |         | 6.8pF | ±0.25pF | GJM1552C1H6R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H6R4DB01# |  |
|        |               |         | 6.9pF | ±0.05pF | GJM1552C1H6R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H6R5BB01# |  |
|        |               |         | 7.0pF | ±0.25pF | GJM1552C1H6R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H6R5DB01# |  |
|        |               |         | 7.1pF | ±0.05pF | GJM1552C1H6R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H6R6BB01# |  |
|        |               |         | 7.2pF | ±0.25pF | GJM1552C1H6R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H6R6DB01# |  |
|        |               |         | 7.3pF | ±0.05pF | GJM1552C1H6R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H6R7BB01# |  |
|        |               |         | 7.4pF | ±0.25pF | GJM1552C1H6R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H6R7DB01# |  |
|        |               |         | 7.5pF | ±0.05pF | GJM1552C1H6R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H6R8BB01# |  |
|        |               |         | 7.6pF | ±0.25pF | GJM1552C1H6R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H6R8DB01# |  |
|        |               |         | 7.7pF | ±0.05pF | GJM1552C1H6R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H6R9BB01# |  |
|        |               |         | 7.8pF | ±0.25pF | GJM1552C1H6R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H6R9DB01# |  |
|        |               |         | 7.9pF | ±0.05pF | GJM1552C1H7R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H7R0BB01# |  |
|        |               |         | 8.0pF | ±0.25pF | GJM1552C1H7R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H7R0DB01# |  |
|        |               |         | 8.1pF | ±0.05pF | GJM1552C1H7R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H7R1BB01# |  |
|        |               |         | 8.2pF | ±0.25pF | GJM1552C1H7R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H7R1DB01# |  |
|        |               |         | 8.3pF | ±0.05pF | GJM1552C1H7R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H7R2BB01# |  |
|        |               |         | 8.4pF | ±0.25pF | GJM1552C1H7R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H7R2DB01# |  |
|        |               |         | 8.5pF | ±0.05pF | GJM1552C1H7R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H7R3BB01# |  |
|        |               |         | 8.6pF | ±0.25pF | GJM1552C1H7R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H7R3DB01# |  |

Part number # indicates the package specification code.



# GJM Series Temperature Compensating Type **HiQ** Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | CH      | 7.3pF | ±0.5pF  | GJM1552C1H7R3DB01# |  |
|        |               |         |       | ±0.05pF | GJM1552C1H7R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H7R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H7R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H7R4DB01# |  |
|        |               |         | 7.4pF | ±0.05pF | GJM1552C1H7R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H7R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H7R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H7R5DB01# |  |
|        |               |         | 7.5pF | ±0.05pF | GJM1552C1H7R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H7R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H7R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H7R6DB01# |  |
|        |               |         | 7.6pF | ±0.05pF | GJM1552C1H7R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H7R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H7R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H7R7DB01# |  |
|        |               |         | 7.7pF | ±0.05pF | GJM1552C1H7R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H7R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H7R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H7R8DB01# |  |
|        |               |         | 7.8pF | ±0.05pF | GJM1552C1H7R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H7R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H7R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H7R9DB01# |  |
|        |               |         | 7.9pF | ±0.05pF | GJM1552C1H8R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H8R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H8R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H8R0DB01# |  |
|        |               |         | 8.0pF | ±0.05pF | GJM1552C1H8R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H8R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H8R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H8R1DB01# |  |
|        |               |         | 8.1pF | ±0.05pF | GJM1552C1H8R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H8R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H8R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H8R2DB01# |  |
|        |               |         | 8.2pF | ±0.05pF | GJM1552C1H8R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H8R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H8R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H8R3DB01# |  |
|        |               |         | 8.3pF | ±0.05pF | GJM1552C1H8R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H8R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H8R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H8R4DB01# |  |
|        |               |         | 8.4pF | ±0.05pF | GJM1552C1H8R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H8R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H8R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H8R5DB01# |  |
|        |               |         | 8.5pF | ±0.05pF | GJM1552C1H8R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H8R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H8R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H8R6DB01# |  |
|        |               |         | 8.6pF | ±0.05pF | GJM1552C1H8R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H8R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H8R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H8R7DB01# |  |
|        |               |         | 8.7pF | ±0.05pF | GJM1552C1H8R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H8R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H8R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H8R8DB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.55mm | 50Vdc         | CH      | 8.7pF | ±0.1pF  | GJM1552C1H8R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H8R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H8R7DB01# |  |
|        |               |         | 8.8pF | ±0.05pF | GJM1552C1H8R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H8R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H8R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H8R8DB01# |  |
|        |               |         | 8.9pF | ±0.05pF | GJM1552C1H8R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H8R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H8R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H8R9DB01# |  |
|        |               |         | 9.0pF | ±0.05pF | GJM1552C1H9R0WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H9R0BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H9R0CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H9R0DB01# |  |
|        |               |         | 9.1pF | ±0.05pF | GJM1552C1H9R1WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H9R1BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H9R1CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H9R1DB01# |  |
|        |               |         | 9.2pF | ±0.05pF | GJM1552C1H9R2WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H9R2BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H9R2CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H9R2DB01# |  |
|        |               |         | 9.3pF | ±0.05pF | GJM1552C1H9R3WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H9R3BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H9R3CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H9R3DB01# |  |
|        |               |         | 9.4pF | ±0.05pF | GJM1552C1H9R4WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H9R4BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H9R4CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H9R4DB01# |  |
|        |               |         | 9.5pF | ±0.05pF | GJM1552C1H9R5WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H9R5BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H9R5CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H9R5DB01# |  |
|        |               |         | 9.6pF | ±0.05pF | GJM1552C1H9R6WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H9R6BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H9R6CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H9R6DB01# |  |
|        |               |         | 9.7pF | ±0.05pF | GJM1552C1H9R7WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H9R7BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H9R7CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H9R7DB01# |  |
|        |               |         | 9.8pF | ±0.05pF | GJM1552C1H9R8WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H9R8BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H9R8CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H9R8DB01# |  |
|        |               |         | 9.9pF | ±0.05pF | GJM1552C1H9R9WB01# |  |
|        |               |         |       | ±0.1pF  | GJM1552C1H9R9BB01# |  |
|        |               |         |       | ±0.25pF | GJM1552C1H9R9CB01# |  |
|        |               |         |       | ±0.5pF  | GJM1552C1H9R9DB01# |  |
|        |               |         | 10pF  | ±2%     | GJM1552C1H100GB01# |  |
|        |               |         |       | ±5%     | GJM1552C1H100JB01# |  |
|        |               |         | 11pF  | ±2%     | GJM1552C1H110GB01# |  |

Part number # indicates the package specification code.

# GJM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number        |  |
|--------|---------------|---------|------|------|--------------------|--|
| 0.55mm | 50Vdc         | CH      | 11pF | ±5%  | GJM1552C1H110JB01# |  |
|        |               |         |      | ±2%  | GJM1552C1H120GB01# |  |
|        |               |         |      | ±5%  | GJM1552C1H120JB01# |  |
|        |               |         | 13pF | ±2%  | GJM1552C1H130GB01# |  |
|        |               |         |      | ±5%  | GJM1552C1H130JB01# |  |
|        |               |         | 15pF | ±2%  | GJM1552C1H150GB01# |  |
|        |               |         |      | ±5%  | GJM1552C1H150JB01# |  |
|        |               |         | 16pF | ±2%  | GJM1552C1H160GB01# |  |
|        |               |         |      | ±5%  | GJM1552C1H160JB01# |  |
|        |               |         | 18pF | ±2%  | GJM1552C1H180GB01# |  |
|        |               |         |      | ±5%  | GJM1552C1H180JB01# |  |
|        |               |         | 20pF | ±2%  | GJM1552C1H200GB01# |  |
|        |               |         |      | ±5%  | GJM1552C1H200JB01# |  |
|        |               |         | 22pF | ±1%  | GJM1552C1H220FB01# |  |
|        |               |         |      | ±2%  | GJM1552C1H220GB01# |  |
|        |               |         |      | ±5%  | GJM1552C1H220JB01# |  |
|        |               |         | 24pF | ±1%  | GJM1552C1H240FB01# |  |
|        |               |         |      | ±2%  | GJM1552C1H240GB01# |  |
|        |               |         |      | ±5%  | GJM1552C1H240JB01# |  |
|        |               |         | 27pF | ±1%  | GJM1552C1H270FB01# |  |
|        |               |         |      | ±2%  | GJM1552C1H270GB01# |  |
|        |               |         |      | ±5%  | GJM1552C1H270JB01# |  |
|        |               |         | 30pF | ±1%  | GJM1552C1H300FB01# |  |
|        |               |         |      | ±2%  | GJM1552C1H300GB01# |  |
|        |               |         |      | ±5%  | GJM1552C1H300JB01# |  |
|        |               |         | 33pF | ±1%  | GJM1552C1H330FB01# |  |
|        |               |         |      | ±2%  | GJM1552C1H330GB01# |  |
|        |               |         |      | ±5%  | GJM1552C1H330JB01# |  |
|        |               |         | 36pF | ±1%  | GJM1552C1H360FB01# |  |
|        |               |         |      | ±2%  | GJM1552C1H360GB01# |  |
|        |               |         |      | ±5%  | GJM1552C1H360JB01# |  |
|        |               |         | 39pF | ±1%  | GJM1552C1H390FB01# |  |
|        |               |         |      | ±2%  | GJM1552C1H390GB01# |  |
|        |               |         |      | ±5%  | GJM1552C1H390JB01# |  |
|        |               |         | 43pF | ±1%  | GJM1552C1H430FB01# |  |
|        |               |         |      | ±2%  | GJM1552C1H430GB01# |  |
|        |               |         |      | ±5%  | GJM1552C1H430JB01# |  |
|        |               |         | 47pF | ±1%  | GJM1552C1H470FB01# |  |
|        |               |         |      | ±2%  | GJM1552C1H470GB01# |  |
|        |               |         |      | ±5%  | GJM1552C1H470JB01# |  |

Part number # indicates the package specification code.

## Top & Bottom Electrode Type for Bonding


# GMA Series

This capacitor is suitable for wire bonding mounting by the external electrodes of Au plating.  
Mounting in IC packages is also possible with the upper/lower electrode structure!

## Features

### ① Allows for high density mounting.

Noise can be reduced by eliminating the routing of the wire, and high efficiency can be achieved with a built-in capacitor in a package, such as IC. Miniaturization of the set is also possible.




### ② Ideal for bypass applications.

Achieved small size and large capacity with a multilayer structure.


### ③ Excellent in high frequency characteristics.

Since the capacitor consists of an upper/lower electrode structure, the current path becomes shorter and lowers the ESL. Compared with the general purpose GRM series of the same capacity, the impedance of this product becomes lower at high frequencies.



## Specifications

|                   |                                                                                                                                                                                |
|-------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Size              | 0.38×0.38mm to 0.8×0.8mm                                                                                                                                                       |
| Rated Voltage     | DC6.3V to 100V                                                                                                                                                                 |
| Capacitance       | 100pF to 0.47μF                                                                                                                                                                |
| Main Applications | 1. Optical communication related equipment<br>2. Various device related, such as GaAsIC (mounted in IC packages)<br>3. Measuring instruments, other ultra compact/thin devices |



This catalog contains only a portion of the product lineup.  
Please refer to the capacitor search tool on the Murata Web site for details.

## GMA Series High Dielectric Constant Type Part Number List

### ■ 0.38×0.38mm Ultra-compact

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.35mm | 10Vdc         | X7R     | 10000pF | ±20% | GMA0D3R71A103MA01# |  |
|        |               | R       | 10000pF | ±20% | GMA0D3R11A103MA01# |  |

### ■ 0.5×0.5mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.4mm  | 100Vdc        | X7R     | 100pF   | ±20% | GMA05XR72A101MA01# |  |
|        |               |         | 150pF   | ±20% | GMA05XR72A151MA01# |  |
|        |               |         | 220pF   | ±20% | GMA05XR72A221MA01# |  |
|        |               |         | 330pF   | ±20% | GMA05XR72A331MA01# |  |
|        |               |         | 470pF   | ±20% | GMA05XR72A471MA01# |  |
|        |               |         | 680pF   | ±20% | GMA05XR72A681MA01# |  |
|        |               |         | 1000pF  | ±20% | GMA05XR72A102MA01# |  |
|        |               |         |         |      |                    |  |
|        | 25Vdc         | X7R     | 1500pF  | ±20% | GMA05XR71E152MA11# |  |
|        |               |         | 2200pF  | ±20% | GMA05XR71E222MA11# |  |
|        |               |         | 3300pF  | ±20% | GMA05XR71E332MA11# |  |
|        |               |         | 4700pF  | ±20% | GMA05XR71E472MA11# |  |
|        |               | B       | 1500pF  | ±20% | GMA05XB31E152MA11# |  |
|        |               |         | 2200pF  | ±20% | GMA05XB31E222MA11# |  |
|        |               |         | 3300pF  | ±20% | GMA05XB31E332MA11# |  |
|        |               |         | 4700pF  | ±20% | GMA05XB31E472MA11# |  |
|        | 10Vdc         | X7R     | 6800pF  | ±20% | GMA05XR71A682MA01# |  |
|        |               |         | 10000pF | ±20% | GMA05XR71A103MA01# |  |
|        |               |         | 15000pF | ±20% | GMA05XR71A153MA01# |  |
|        |               |         | 22000pF | ±20% | GMA05XR71A223MA01# |  |
|        |               | R       | 6800pF  | ±20% | GMA05XR11A682MA01# |  |
|        |               |         | 10000pF | ±20% | GMA05XR11A103MA01# |  |
|        |               |         | 15000pF | ±20% | GMA05XR11A153MA01# |  |
|        |               |         | 22000pF | ±20% | GMA05XR11A223MA01# |  |
|        | 6.3Vdc        | X5R     | 0.10μF  | ±20% | GMA05XR60J104ME12# |  |
|        |               |         | 0.10μF  | ±20% | GMA05XB30J104ME12# |  |
|        |               | B       | 0.10μF  | ±20% | GMA05XB30J104ME12# |  |
|        |               |         | 0.10μF  | ±20% | GMA05XB30J104ME12# |  |

### ■ 0.8×0.8mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.6mm  | 100Vdc        | X7R     | 1500pF  | ±20% | GMA085R72A152MA01# |  |
|        |               |         | 2200pF  | ±20% | GMA085R72A222MA01# |  |
|        |               |         | 3300pF  | ±20% | GMA085R72A332MA01# |  |
|        |               |         | 4700pF  | ±20% | GMA085R72A472MA01# |  |
|        |               |         | 6800pF  | ±20% | GMA085R72A682MA01# |  |
|        | 25Vdc         | X7R     | 10000pF | ±20% | GMA085R71E103MA11# |  |
|        |               |         | 15000pF | ±20% | GMA085R71E153MA11# |  |
|        |               |         | 22000pF | ±20% | GMA085R71E223MA11# |  |
|        |               |         | 22000pF | ±20% | GMA085R71E223MA11# |  |
|        |               | B       | 10000pF | ±20% | GMA085B31E103MA11# |  |
|        |               |         | 15000pF | ±20% | GMA085B31E153MA11# |  |
|        |               |         | 22000pF | ±20% | GMA085B31E223MA11# |  |

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.6mm  | 10Vdc         | X7R     | 33000pF | ±20% | GMA085R71A333MA01# |  |
|        |               |         | 47000pF | ±20% | GMA085R71A473MA01# |  |
|        |               |         | 68000pF | ±20% | GMA085R71A683MA01# |  |
|        |               |         | 0.10μF  | ±20% | GMA085R71A104MA01# |  |
|        |               | R       | 33000pF | ±20% | GMA085R11A333MA01# |  |
|        |               |         | 47000pF | ±20% | GMA085R11A473MA01# |  |
|        |               |         | 68000pF | ±20% | GMA085R11A683MA01# |  |
|        |               |         | 0.10μF  | ±20% | GMA085R11A104MA01# |  |
|        | 6.3Vdc        | X5R     | 0.47μF  | ±20% | GMA085R60J474ME12# |  |
|        |               |         | 0.47μF  | ±20% | GMA085R60J474ME12# |  |
|        |               | B       | 0.47μF  | ±20% | GMA085B30J474ME12# |  |
|        |               |         | 0.47μF  | ±20% | GMA085B30J474ME12# |  |

Part number # indicates the package specification code.

Compatible to Bonding / AuSn Soldering


## GMD Series

This capacitor is compatible to wire bonding mounting by the external electrodes of Au plating.

### Features

#### ① Can be mounted by wire bonding and AuSn soldering.

Since the external electrodes are based on the Au plating specification, mounting by wire/die bonding is possible.



#### ② Ideal for mounting in packages, such as optical communication related devices , IC and etc.


Noise can be reduced by eliminating the routing of the wire, and high efficiency can be achieved with a built-in capacitor in the package, such as TO-CAN, IC and etc. by wire bonding mounting.

#### ③ Contributes to the miniaturization of the set.

Murata offers a lineup of small size products, such as the 0603 (0201) and 1005 (0402) in mm (inch).

### Specifications

|                   |                                                                          |
|-------------------|--------------------------------------------------------------------------|
| Size              | 0.6×0.3mm to 1.0×0.5mm                                                   |
| Rated Voltage     | DC6.3V to 50V                                                            |
| Capacitance       | 100pF to 1.0μF                                                           |
| Main Applications | 1. Optical communication related equipment<br>2. Mounting in IC packages |



This catalog contains only a portion of the product lineup.  
Please refer to the capacitor search tool on the Murata Web site for details.



## GMD Series High Dielectric Constant Type Part Number List

■ 0.6×0.3mm **Ultra-compact**

| T max. | Rated Voltage | TC Code | Cap.   | Tol.               | Part Number        |  |
|--------|---------------|---------|--------|--------------------|--------------------|--|
| 0.33mm | 25Vdc         | X7R     | 100pF  | ±10%               | GMD033R71E101KA01# |  |
|        |               |         | 120pF  | ±10%               | GMD033R71E121KA01# |  |
|        |               |         | 150pF  | ±10%               | GMD033R71E151KA01# |  |
|        |               |         | 180pF  | ±10%               | GMD033R71E181KA01# |  |
|        |               |         | 220pF  | ±10%               | GMD033R71E221KA01# |  |
|        |               |         | 270pF  | ±10%               | GMD033R71E271KA01# |  |
|        |               |         | 330pF  | ±10%               | GMD033R71E331KA01# |  |
|        |               |         | 390pF  | ±10%               | GMD033R71E391KA01# |  |
|        |               |         | 470pF  | ±10%               | GMD033R71E471KA01# |  |
|        |               |         | 560pF  | ±10%               | GMD033R71E561KA01# |  |
|        |               |         | 680pF  | ±10%               | GMD033R71E681KA01# |  |
|        |               |         | 820pF  | ±10%               | GMD033R71E821KA01# |  |
|        |               |         | 1000pF | ±10%               | GMD033R71E102KA01# |  |
|        |               |         | 1200pF | ±10%               | GMD033R71E122KA01# |  |
|        |               |         | 1500pF | ±10%               | GMD033R71E152KA01# |  |
|        |               | R       | 100pF  | ±10%               | GMD033R11E101KA01# |  |
|        |               |         | 120pF  | ±10%               | GMD033R11E121KA01# |  |
|        |               |         | 150pF  | ±10%               | GMD033R11E151KA01# |  |
|        |               |         | 180pF  | ±10%               | GMD033R11E181KA01# |  |
|        |               |         | 220pF  | ±10%               | GMD033R11E221KA01# |  |
|        |               |         | 270pF  | ±10%               | GMD033R11E271KA01# |  |
|        |               |         | 330pF  | ±10%               | GMD033R11E331KA01# |  |
|        |               |         | 390pF  | ±10%               | GMD033R11E391KA01# |  |
|        |               |         | 470pF  | ±10%               | GMD033R11E471KA01# |  |
|        |               |         | 560pF  | ±10%               | GMD033R11E561KA01# |  |
|        |               |         | 680pF  | ±10%               | GMD033R11E681KA01# |  |
|        |               |         | 820pF  | ±10%               | GMD033R11E821KA01# |  |
|        |               |         | 1000pF | ±10%               | GMD033R11E102KA01# |  |
|        |               |         | 1200pF | ±10%               | GMD033R11E122KA01# |  |
|        |               |         | 1500pF | ±10%               | GMD033R11E152KA01# |  |
|        |               | B       | 100pF  | ±10%               | GMD033B11E101KA01# |  |
|        |               |         | 120pF  | ±10%               | GMD033B11E121KA01# |  |
|        |               |         | 150pF  | ±10%               | GMD033B11E151KA01# |  |
|        |               |         | 180pF  | ±10%               | GMD033B11E181KA01# |  |
|        |               |         | 220pF  | ±10%               | GMD033B11E221KA01# |  |
|        |               |         | 270pF  | ±10%               | GMD033B11E271KA01# |  |
|        |               |         | 330pF  | ±10%               | GMD033B11E331KA01# |  |
|        |               |         | 390pF  | ±10%               | GMD033B11E391KA01# |  |
|        |               |         | 470pF  | ±10%               | GMD033B11E471KA01# |  |
|        |               |         | 560pF  | ±10%               | GMD033B11E561KA01# |  |
|        |               |         | 680pF  | ±10%               | GMD033B11E681KA01# |  |
|        |               |         | 820pF  | ±10%               | GMD033B11E821KA01# |  |
|        |               |         | 1000pF | ±10%               | GMD033B11E102KA01# |  |
|        |               |         | 1200pF | ±10%               | GMD033B11E122KA01# |  |
|        |               |         | 1500pF | ±10%               | GMD033B11E152KA01# |  |
|        | 16Vdc         | X7R     | 1800pF | ±10%               | GMD033R71C182KA11# |  |
|        |               |         | 2200pF | ±10%               | GMD033R71C222KA11# |  |
|        |               |         | 2700pF | ±10%               | GMD033R71C272KA11# |  |
|        |               |         | 3300pF | ±10%               | GMD033R71C332KA11# |  |
|        |               | R       | 1800pF | ±10%               | GMD033R11C182KA11# |  |
|        |               |         | 2200pF | ±10%               | GMD033R11C222KA11# |  |
| 2700pF |               |         | ±10%   | GMD033R11C272KA11# |                    |  |
|        |               |         |        |                    |                    |  |
|        |               |         |        |                    |                    |  |

| T max. | Rated Voltage | TC Code | Cap.    | Tol.               | Part Number        |                    |  |
|--------|---------------|---------|---------|--------------------|--------------------|--------------------|--|
| 0.33mm | 16Vdc         | R       | 3300pF  | ±10%               | GMD033R11C332KA11# |                    |  |
|        |               | B       | 1800pF  | ±10%               | GMD033B31C182KA11# |                    |  |
|        |               |         | 2200pF  | ±10%               | GMD033B31C222KA11# |                    |  |
|        |               |         | 2700pF  | ±10%               | GMD033B31C272KA11# |                    |  |
|        |               |         | 3300pF  | ±10%               | GMD033B31C332KA11# |                    |  |
|        | 10Vdc         | X7R     | 3900pF  | ±10%               | GMD033R71A392KA01# |                    |  |
|        |               |         | 4700pF  | ±10%               | GMD033R71A472KA01# |                    |  |
|        |               |         | 5600pF  | ±10%               | GMD033R71A562KA01# |                    |  |
|        |               |         | 6800pF  | ±10%               | GMD033R71A682KA01# |                    |  |
|        |               |         | 8200pF  | ±10%               | GMD033R71A822KA01# |                    |  |
|        |               |         | 10000pF | ±10%               | GMD033R71A103KA01# |                    |  |
|        |               | R       | 3900pF  | ±10%               | GMD033R11A392KA01# |                    |  |
|        |               |         | 4700pF  | ±10%               | GMD033R11A472KA01# |                    |  |
|        |               |         | 5600pF  | ±10%               | GMD033R11A562KA01# |                    |  |
|        |               |         | 6800pF  | ±10%               | GMD033R11A682KA01# |                    |  |
|        |               |         | 8200pF  | ±10%               | GMD033R11A822KA01# |                    |  |
|        |               |         | 10000pF | ±10%               | GMD033R11A103KA01# |                    |  |
|        |               | B       | 3900pF  | ±10%               | GMD033B11A392KA01# |                    |  |
|        |               |         | 4700pF  | ±10%               | GMD033B11A472KA01# |                    |  |
|        |               |         | 5600pF  | ±10%               | GMD033B11A562KA01# |                    |  |
|        |               |         | 6800pF  | ±10%               | GMD033B11A682KA01# |                    |  |
|        |               |         | 8200pF  | ±10%               | GMD033B11A822KA01# |                    |  |
|        |               |         | 10000pF | ±10%               | GMD033B11A103KA01# |                    |  |
|        |               | 6.3Vdc  | X5R     | 56000pF            | ±10%               | GMD033R60J563KE11# |  |
|        |               |         |         | 68000pF            | ±10%               | GMD033R60J683KE11# |  |
|        |               |         |         | 82000pF            | ±10%               | GMD033R60J823KE11# |  |
| 0.10μF | ±10%          |         |         | GMD033R60J104KE11# |                    |                    |  |
| B      | 56000pF       |         | ±10%    | GMD033B30J563KE11# |                    |                    |  |
|        | 68000pF       |         | ±10%    | GMD033B30J683KE11# |                    |                    |  |
|        | 82000pF       |         | ±10%    | GMD033B30J823KE11# |                    |                    |  |
|        | 0.10μF        |         | ±10%    | GMD033B30J104KE11# |                    |                    |  |

■ 1.0×0.5mm

| T max. | Rated Voltage | TC Code | Cap.   | Tol.  | Part Number        |                    |  |
|--------|---------------|---------|--------|-------|--------------------|--------------------|--|
| 0.55mm | 50Vdc         | X7R     | 220pF  | ±10%  | GMD155R71H221KA01# |                    |  |
|        |               |         | 270pF  | ±10%  | GMD155R71H271KA01# |                    |  |
|        |               |         | 330pF  | ±10%  | GMD155R71H331KA01# |                    |  |
|        |               |         | 390pF  | ±10%  | GMD155R71H391KA01# |                    |  |
|        |               |         | 470pF  | ±10%  | GMD155R71H471KA01# |                    |  |
|        |               |         | 560pF  | ±10%  | GMD155R71H561KA01# |                    |  |
|        |               |         | 680pF  | ±10%  | GMD155R71H681KA01# |                    |  |
|        |               |         | 820pF  | ±10%  | GMD155R71H821KA01# |                    |  |
|        |               |         | 1000pF | ±10%  | GMD155R71H102KA01# |                    |  |
|        |               |         | 1200pF | ±10%  | GMD155R71H122KA01# |                    |  |
|        |               |         | 1500pF | ±10%  | GMD155R71H152KA01# |                    |  |
|        |               |         | 1800pF | ±10%  | GMD155R71H182KA01# |                    |  |
|        |               |         | 2200pF | ±10%  | GMD155R71H222KA01# |                    |  |
|        |               |         | 2700pF | ±10%  | GMD155R71H272KA01# |                    |  |
|        |               |         | 3300pF | ±10%  | GMD155R71H332KA01# |                    |  |
|        |               |         | 3900pF | ±10%  | GMD155R71H392KA01# |                    |  |
|        |               |         | 4700pF | ±10%  | GMD155R71H472KA01# |                    |  |
|        |               |         | R      | 220pF | ±10%               | GMD155R11H221KA01# |  |

Part number # indicates the package specification code.

## GMD Series High Dielectric Constant Type Part Number List

(→ ■ 1.0×0.5mm)

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.55mm | 50Vdc         | R       | 270pF   | ±10% | GMD155R11H271KA01# |  |
|        |               |         | 330pF   | ±10% | GMD155R11H331KA01# |  |
|        |               |         | 390pF   | ±10% | GMD155R11H391KA01# |  |
|        |               |         | 470pF   | ±10% | GMD155R11H471KA01# |  |
|        |               |         | 560pF   | ±10% | GMD155R11H561KA01# |  |
|        |               |         | 680pF   | ±10% | GMD155R11H681KA01# |  |
|        |               |         | 820pF   | ±10% | GMD155R11H821KA01# |  |
|        |               |         | 1000pF  | ±10% | GMD155R11H102KA01# |  |
|        |               |         | 1200pF  | ±10% | GMD155R11H122KA01# |  |
|        |               |         | 1500pF  | ±10% | GMD155R11H152KA01# |  |
|        |               |         | 1800pF  | ±10% | GMD155R11H182KA01# |  |
|        |               |         | 2200pF  | ±10% | GMD155R11H222KA01# |  |
|        |               |         | 2700pF  | ±10% | GMD155R11H272KA01# |  |
|        |               |         | 3300pF  | ±10% | GMD155R11H332KA01# |  |
|        |               |         | 3900pF  | ±10% | GMD155R11H392KA01# |  |
|        |               |         | 4700pF  | ±10% | GMD155R11H472KA01# |  |
|        |               | B       | 220pF   | ±10% | GMD155B11H221KA01# |  |
|        |               |         | 270pF   | ±10% | GMD155B11H271KA01# |  |
|        |               |         | 330pF   | ±10% | GMD155B11H331KA01# |  |
|        |               |         | 390pF   | ±10% | GMD155B11H391KA01# |  |
|        |               |         | 470pF   | ±10% | GMD155B11H471KA01# |  |
|        |               |         | 560pF   | ±10% | GMD155B11H561KA01# |  |
|        |               |         | 680pF   | ±10% | GMD155B11H681KA01# |  |
|        |               |         | 820pF   | ±10% | GMD155B11H821KA01# |  |
|        |               |         | 1000pF  | ±10% | GMD155B11H102KA01# |  |
|        |               |         | 1200pF  | ±10% | GMD155B11H122KA01# |  |
|        |               |         | 1500pF  | ±10% | GMD155B11H152KA01# |  |
|        |               |         | 1800pF  | ±10% | GMD155B11H182KA01# |  |
|        |               |         | 2200pF  | ±10% | GMD155B11H222KA01# |  |
|        |               |         | 2700pF  | ±10% | GMD155B11H272KA01# |  |
|        |               |         | 3300pF  | ±10% | GMD155B11H332KA01# |  |
|        |               |         | 3900pF  | ±10% | GMD155B11H392KA01# |  |
|        |               |         | 4700pF  | ±10% | GMD155B11H472KA01# |  |
|        | 25Vdc         | X7R     | 5600pF  | ±10% | GMD155R71E562KA01# |  |
|        |               |         | 6800pF  | ±10% | GMD155R71E682KA01# |  |
|        |               |         | 8200pF  | ±10% | GMD155R71E822KA01# |  |
|        |               |         | 10000pF | ±10% | GMD155R71E103KA01# |  |
|        |               |         | 12000pF | ±10% | GMD155R71E123KA01# |  |
|        |               |         | 15000pF | ±10% | GMD155R71E153KA01# |  |
|        |               |         | 18000pF | ±10% | GMD155R71E183KA01# |  |
|        |               |         | 22000pF | ±10% | GMD155R71E223KA01# |  |
|        |               |         | 27000pF | ±10% | GMD155R71E273KA11# |  |
|        |               |         | 33000pF | ±10% | GMD155R71E333KA11# |  |
|        |               |         | 39000pF | ±10% | GMD155R71E393KA11# |  |
|        |               |         | 47000pF | ±10% | GMD155R71E473KA11# |  |
|        |               | R       | 5600pF  | ±10% | GMD155R11E562KA01# |  |
|        |               |         | 6800pF  | ±10% | GMD155R11E682KA01# |  |
|        |               |         | 8200pF  | ±10% | GMD155R11E822KA01# |  |
|        |               |         | 10000pF | ±10% | GMD155R11E103KA01# |  |
|        |               |         | 12000pF | ±10% | GMD155R11E123KA01# |  |
|        |               |         | 15000pF | ±10% | GMD155R11E153KA01# |  |
|        |               |         | 18000pF | ±10% | GMD155R11E183KA01# |  |
|        |               |         | 22000pF | ±10% | GMD155R11E223KA01# |  |
|        |               |         | 27000pF | ±10% | GMD155R11E273KA11# |  |

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.55mm | 25Vdc         | R       | 33000pF | ±10% | GMD155R11E333KA11# |  |
|        |               |         | 39000pF | ±10% | GMD155R11E393KA11# |  |
|        |               |         | 47000pF | ±10% | GMD155R11E473KA11# |  |
|        |               | B       | 5600pF  | ±10% | GMD155B11E562KA01# |  |
|        |               |         | 6800pF  | ±10% | GMD155B11E682KA01# |  |
|        |               |         | 8200pF  | ±10% | GMD155B11E822KA01# |  |
|        |               |         | 10000pF | ±10% | GMD155B11E103KA01# |  |
|        |               |         | 12000pF | ±10% | GMD155B11E123KA01# |  |
|        |               |         | 15000pF | ±10% | GMD155B11E153KA01# |  |
|        |               |         | 18000pF | ±10% | GMD155B11E183KA01# |  |
|        |               |         | 22000pF | ±10% | GMD155B11E223KA01# |  |
|        |               |         | 27000pF | ±10% | GMD155B31E273KA11# |  |
|        |               |         | 33000pF | ±10% | GMD155B31E333KA11# |  |
|        |               |         | 39000pF | ±10% | GMD155B31E393KA11# |  |
|        |               |         | 47000pF | ±10% | GMD155B31E473KA11# |  |
|        | 16Vdc         | X7R     | 56000pF | ±10% | GMD155R71C563KA11# |  |
|        |               |         | 68000pF | ±10% | GMD155R71C683KA11# |  |
|        |               |         | 82000pF | ±10% | GMD155R71C823KA11# |  |
|        |               |         | 0.10μF  | ±10% | GMD155R71C104KA11# |  |
|        |               | R       | 56000pF | ±10% | GMD155R11C563KA11# |  |
|        |               |         | 68000pF | ±10% | GMD155R11C683KA11# |  |
|        |               |         | 82000pF | ±10% | GMD155R11C823KA11# |  |
|        |               |         | 0.10μF  | ±10% | GMD155R11C104KA11# |  |
|        |               | B       | 56000pF | ±10% | GMD155B31C563KA11# |  |
|        |               |         | 68000pF | ±10% | GMD155B31C683KA11# |  |
|        |               |         | 82000pF | ±10% | GMD155B31C823KA11# |  |
|        |               |         | 0.10μF  | ±10% | GMD155B31C104KA11# |  |
|        | 10Vdc         | X5R     | 0.12μF  | ±10% | GMD155R61A124KE12# |  |
|        |               |         | 0.15μF  | ±10% | GMD155R61A154KE12# |  |
|        |               |         | 0.18μF  | ±10% | GMD155R61A184KE12# |  |
|        |               |         | 0.22μF  | ±10% | GMD155R61A224KE12# |  |
|        |               |         | 0.27μF  | ±10% | GMD155R61A274KE11# |  |
|        |               |         | 0.33μF  | ±10% | GMD155R61A334KE11# |  |
|        |               |         | 0.39μF  | ±10% | GMD155R61A394KE11# |  |
|        |               |         | 0.47μF  | ±10% | GMD155R61A474KE11# |  |
|        |               | B       | 0.12μF  | ±10% | GMD155B31A124KE12# |  |
|        |               |         | 0.15μF  | ±10% | GMD155B31A154KE12# |  |
|        |               |         | 0.18μF  | ±10% | GMD155B31A184KE12# |  |
|        |               |         | 0.22μF  | ±10% | GMD155B31A224KE12# |  |
|        |               |         | 0.27μF  | ±10% | GMD155B31A274KE11# |  |
|        |               |         | 0.33μF  | ±10% | GMD155B31A334KE11# |  |
|        |               |         | 0.39μF  | ±10% | GMD155B31A394KE11# |  |
|        |               |         | 0.47μF  | ±10% | GMD155B31A474KE11# |  |

Part number # indicates the package specification code.

High Frequency High Q Type 1608(in mm)/0603(in inch) Size Min.


# GQM Series **HiQ**

## High Frequency Capacitor Ideal for PA Design of Base Stations

### Features



- ① **Mainly ideal for base stations of mobile communication devices and temperature compensation of related modules.**

This product is ideal for temperature compensation of high frequency circuits, such as resonant circuits, tuning circuits, and impedance matching circuits where the operating characteristics of the device are greatly affected by the capacitance fluctuation.



- ② **High Q and low ESR in VHF, UHF and microwave frequency bands.**

High Q and low ESR were achieved at a high frequency by adopting ceramic material as the dielectric material which enables an extremely low loss at high frequency, and base metal electrodes as the internal electrodes.




- ③ **Can be used for tight tolerance.**

In addition to standard tolerance, the allowable range of this product is also suitable for the following narrow tolerance.

| Capacitance Range | Standard Capacitance Tolerance<br>(Capacitance Tolerance Symbol) | Narrow Capacitance Tolerance<br>(Capacitance Tolerance Symbol) |
|-------------------|------------------------------------------------------------------|----------------------------------------------------------------|
| ≤0.9pF            | ±0.1pF (B)                                                       | ±0.05pF (W)                                                    |
| 1.0 to 5.0pF      | ±0.25pF (C)                                                      | ±0.05pF (W), ±0.1pF (B)                                        |
| 5.1 to 9.9pF      | ±0.5pF (D)                                                       | ±0.05pF (W), ±0.1pF (B), ±0.25pF (C)                           |
| ≥10pF             | ±5% (J)                                                          | ±2% (G)                                                        |

### Specifications

|                   |                            |
|-------------------|----------------------------|
| Size              | 1.6×0.8mm to 2.8×2.8mm     |
| Rated Voltage     | DC50V to 500V              |
| Capacitance       | 0.1pF to 510pF             |
| Main Applications | Mobile phone base stations |



This catalog contains only a portion of the product lineup.  
Please refer to the capacitor search tool on the Murata Web site for details.

## GQM Series Temperature Compensating Type **HiQ** Part Number List

### ■ 1.6×0.8mm

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.8mm  | 250Vdc        | C0G     | 1.0pF | ±0.1pF  | GQM1875C2E1R0BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E1R0CB12# |  |
|        |               |         | 1.1pF | ±0.1pF  | GQM1875C2E1R1BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E1R1CB12# |  |
|        |               |         | 1.2pF | ±0.1pF  | GQM1875C2E1R2BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E1R2CB12# |  |
|        |               |         | 1.3pF | ±0.1pF  | GQM1875C2E1R3BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E1R3CB12# |  |
|        |               |         | 1.5pF | ±0.1pF  | GQM1875C2E1R5BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E1R5CB12# |  |
|        |               |         | 1.6pF | ±0.1pF  | GQM1875C2E1R6BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E1R6CB12# |  |
|        |               |         | 1.8pF | ±0.1pF  | GQM1875C2E1R8BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E1R8CB12# |  |
|        |               |         | 2.0pF | ±0.1pF  | GQM1875C2E2R0BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E2R0CB12# |  |
|        |               |         | 2.2pF | ±0.1pF  | GQM1875C2E2R2BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E2R2CB12# |  |
|        |               |         | 2.4pF | ±0.1pF  | GQM1875C2E2R4BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E2R4CB12# |  |
|        |               |         | 2.7pF | ±0.1pF  | GQM1875C2E2R7BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E2R7CB12# |  |
|        |               |         | 3.0pF | ±0.1pF  | GQM1875C2E3R0BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E3R0CB12# |  |
|        |               |         | 3.3pF | ±0.1pF  | GQM1875C2E3R3BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E3R3CB12# |  |
|        |               |         | 3.6pF | ±0.1pF  | GQM1875C2E3R6BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E3R6CB12# |  |
|        |               |         | 3.9pF | ±0.1pF  | GQM1875C2E3R9BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E3R9CB12# |  |
|        |               |         | 4.0pF | ±0.1pF  | GQM1875C2E4R0BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E4R0CB12# |  |
|        |               |         | 4.3pF | ±0.1pF  | GQM1875C2E4R3BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E4R3CB12# |  |
|        |               |         | 4.7pF | ±0.1pF  | GQM1875C2E4R7BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E4R7CB12# |  |
|        |               |         | 5.0pF | ±0.1pF  | GQM1875C2E5R0BB12# |  |
|        |               |         |       | ±0.25pF | GQM1875C2E5R0CB12# |  |
|        |               |         | 5.1pF | ±0.25pF | GQM1875C2E5R1CB12# |  |
|        |               |         |       | ±0.5pF  | GQM1875C2E5R1DB12# |  |
|        |               |         | 5.6pF | ±0.25pF | GQM1875C2E5R6CB12# |  |
|        |               |         |       | ±0.5pF  | GQM1875C2E5R6DB12# |  |
|        |               |         | 6.0pF | ±0.25pF | GQM1875C2E6R0CB12# |  |
|        |               |         |       | ±0.5pF  | GQM1875C2E6R0DB12# |  |
|        |               |         | 6.2pF | ±0.25pF | GQM1875C2E6R2CB12# |  |
|        |               |         |       | ±0.5pF  | GQM1875C2E6R2DB12# |  |
|        |               |         | 6.8pF | ±0.25pF | GQM1875C2E6R8CB12# |  |
|        |               |         |       | ±0.5pF  | GQM1875C2E6R8DB12# |  |
|        |               |         | 7.0pF | ±0.25pF | GQM1875C2E7R0CB12# |  |
|        |               |         |       | ±0.5pF  | GQM1875C2E7R0DB12# |  |
|        |               |         | 7.5pF | ±0.25pF | GQM1875C2E7R5CB12# |  |
|        |               |         |       | ±0.5pF  | GQM1875C2E7R5DB12# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.8mm  | 250Vdc        | C0G     | 8.0pF | ±0.25pF | GQM1875C2E8R0CB12# |  |
|        |               |         |       | ±0.5pF  | GQM1875C2E8R0DB12# |  |
|        |               |         | 8.2pF | ±0.25pF | GQM1875C2E8R2CB12# |  |
|        |               |         |       | ±0.5pF  | GQM1875C2E8R2DB12# |  |
|        |               |         | 9.0pF | ±0.25pF | GQM1875C2E9R0CB12# |  |
|        |               |         |       | ±0.5pF  | GQM1875C2E9R0DB12# |  |
|        |               |         | 9.1pF | ±0.25pF | GQM1875C2E9R1CB12# |  |
|        |               |         |       | ±0.5pF  | GQM1875C2E9R1DB12# |  |
|        |               |         | 10pF  | ±2%     | GQM1875C2E100GB12# |  |
|        |               |         |       | ±5%     | GQM1875C2E100JB12# |  |
|        |               |         | 11pF  | ±2%     | GQM1875C2E110GB12# |  |
|        |               |         |       | ±5%     | GQM1875C2E110JB12# |  |
|        |               |         | 12pF  | ±2%     | GQM1875C2E120GB12# |  |
|        |               |         |       | ±5%     | GQM1875C2E120JB12# |  |
|        |               |         | 13pF  | ±2%     | GQM1875C2E130GB12# |  |
|        |               |         |       | ±5%     | GQM1875C2E130JB12# |  |
|        |               |         | 15pF  | ±2%     | GQM1875C2E150GB12# |  |
|        |               |         |       | ±5%     | GQM1875C2E150JB12# |  |
|        |               |         | 16pF  | ±2%     | GQM1875C2E160GB12# |  |
|        |               |         |       | ±5%     | GQM1875C2E160JB12# |  |
|        |               |         | 18pF  | ±2%     | GQM1875C2E180GB12# |  |
|        |               |         |       | ±5%     | GQM1875C2E180JB12# |  |
|        |               |         | 20pF  | ±2%     | GQM1875C2E200GB12# |  |
|        |               |         |       | ±5%     | GQM1875C2E200JB12# |  |
|        |               |         | 22pF  | ±2%     | GQM1875C2E220GB12# |  |
|        |               |         |       | ±5%     | GQM1875C2E220JB12# |  |
|        |               |         | 24pF  | ±2%     | GQM1875C2E240GB12# |  |
|        |               |         |       | ±5%     | GQM1875C2E240JB12# |  |
|        |               |         | 27pF  | ±2%     | GQM1875C2E270GB12# |  |
|        |               |         |       | ±5%     | GQM1875C2E270JB12# |  |
|        |               |         | 30pF  | ±2%     | GQM1875C2E300GB12# |  |
|        |               |         |       | ±5%     | GQM1875C2E300JB12# |  |
|        |               |         | 33pF  | ±2%     | GQM1875C2E330GB12# |  |
|        |               |         |       | ±5%     | GQM1875C2E330JB12# |  |
|        |               |         | 36pF  | ±2%     | GQM1875C2E360GB12# |  |
|        |               |         |       | ±5%     | GQM1875C2E360JB12# |  |
|        |               |         | 39pF  | ±2%     | GQM1875C2E390GB12# |  |
|        |               |         |       | ±5%     | GQM1875C2E390JB12# |  |
|        |               |         | 43pF  | ±2%     | GQM1875C2E430GB12# |  |
|        |               |         |       | ±5%     | GQM1875C2E430JB12# |  |
|        |               |         | 47pF  | ±2%     | GQM1875C2E470GB12# |  |
|        |               |         |       | ±5%     | GQM1875C2E470JB12# |  |
| 0.9mm  | 100Vdc        | C0G     | 1.0pF | ±0.1pF  | GQM1885C2A1R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A1R0CB01# |  |
|        |               |         | 1.1pF | ±0.1pF  | GQM1885C2A1R1BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A1R1CB01# |  |
|        |               |         | 1.2pF | ±0.1pF  | GQM1885C2A1R2BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A1R2CB01# |  |
|        |               |         | 1.3pF | ±0.1pF  | GQM1885C2A1R3BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A1R3CB01# |  |
|        |               |         | 1.5pF | ±0.1pF  | GQM1885C2A1R5BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A1R5CB01# |  |
|        |               |         | 1.6pF | ±0.1pF  | GQM1885C2A1R6BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A1R6CB01# |  |

Part number # indicates the package specification code.

## GQM Series Temperature Compensating Type **HiQ** Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 100Vdc        | C0G     | 1.8pF | ±0.1pF  | GQM1885C2A1R8BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A1R8CB01# |  |
|        |               |         | 2.0pF | ±0.1pF  | GQM1885C2A2R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A2R0CB01# |  |
|        |               |         | 2.2pF | ±0.1pF  | GQM1885C2A2R2BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A2R2CB01# |  |
|        |               |         | 2.4pF | ±0.1pF  | GQM1885C2A2R4BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A2R4CB01# |  |
|        |               |         | 2.7pF | ±0.1pF  | GQM1885C2A2R7BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A2R7CB01# |  |
|        |               |         | 3.0pF | ±0.1pF  | GQM1885C2A3R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A3R0CB01# |  |
|        |               |         | 3.3pF | ±0.1pF  | GQM1885C2A3R3BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A3R3CB01# |  |
|        |               |         | 3.6pF | ±0.1pF  | GQM1885C2A3R6BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A3R6CB01# |  |
|        |               |         | 3.9pF | ±0.1pF  | GQM1885C2A3R9BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A3R9CB01# |  |
|        |               |         | 4.0pF | ±0.1pF  | GQM1885C2A4R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A4R0CB01# |  |
|        |               |         | 4.3pF | ±0.1pF  | GQM1885C2A4R3BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A4R3CB01# |  |
|        |               |         | 4.7pF | ±0.1pF  | GQM1885C2A4R7BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A4R7CB01# |  |
|        |               |         | 5.0pF | ±0.1pF  | GQM1885C2A5R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM1885C2A5R0CB01# |  |
|        |               |         | 5.1pF | ±0.25pF | GQM1885C2A5R1CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1885C2A5R1DB01# |  |
|        |               |         | 5.6pF | ±0.25pF | GQM1885C2A5R6CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1885C2A5R6DB01# |  |
|        |               |         | 6.0pF | ±0.25pF | GQM1885C2A6R0CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1885C2A6R0DB01# |  |
|        |               |         | 6.2pF | ±0.25pF | GQM1885C2A6R2CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1885C2A6R2DB01# |  |
|        |               |         | 6.8pF | ±0.25pF | GQM1885C2A6R8CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1885C2A6R8DB01# |  |
|        |               | CK      | 1.0pF | ±0.1pF  | GQM1884C2A1R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM1884C2A1R0CB01# |  |
|        |               |         | 1.1pF | ±0.1pF  | GQM1884C2A1R1BB01# |  |
|        |               |         |       | ±0.25pF | GQM1884C2A1R1CB01# |  |
|        |               |         | 1.2pF | ±0.1pF  | GQM1884C2A1R2BB01# |  |
|        |               |         |       | ±0.25pF | GQM1884C2A1R2CB01# |  |
|        |               |         | 1.3pF | ±0.1pF  | GQM1884C2A1R3BB01# |  |
|        |               |         |       | ±0.25pF | GQM1884C2A1R3CB01# |  |
|        |               |         | 1.5pF | ±0.1pF  | GQM1884C2A1R5BB01# |  |
|        |               |         |       | ±0.25pF | GQM1884C2A1R5CB01# |  |
|        |               |         | 1.6pF | ±0.1pF  | GQM1884C2A1R6BB01# |  |
|        |               |         |       | ±0.25pF | GQM1884C2A1R6CB01# |  |
|        |               |         | 1.8pF | ±0.1pF  | GQM1884C2A1R8BB01# |  |
|        |               |         |       | ±0.25pF | GQM1884C2A1R8CB01# |  |
|        |               |         | 2.0pF | ±0.1pF  | GQM1884C2A2R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM1884C2A2R0CB01# |  |
|        |               | CJ      | 2.2pF | ±0.1pF  | GQM1883C2A2R2BB01# |  |
|        |               |         |       | ±0.25pF | GQM1883C2A2R2CB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 100Vdc        | CJ      | 2.4pF | ±0.1pF  | GQM1883C2A2R4BB01# |  |
|        |               |         |       | ±0.25pF | GQM1883C2A2R4CB01# |  |
|        |               |         | 2.7pF | ±0.1pF  | GQM1883C2A2R7BB01# |  |
|        |               |         |       | ±0.25pF | GQM1883C2A2R7CB01# |  |
|        |               |         | 3.0pF | ±0.1pF  | GQM1883C2A3R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM1883C2A3R0CB01# |  |
|        |               |         | 3.3pF | ±0.1pF  | GQM1883C2A3R3BB01# |  |
|        |               |         |       | ±0.25pF | GQM1883C2A3R3CB01# |  |
|        |               |         | 3.6pF | ±0.1pF  | GQM1883C2A3R6BB01# |  |
|        |               |         |       | ±0.25pF | GQM1883C2A3R6CB01# |  |
|        |               |         | 3.9pF | ±0.1pF  | GQM1883C2A3R9BB01# |  |
|        |               |         |       | ±0.25pF | GQM1883C2A3R9CB01# |  |
|        |               | CH      | 4.0pF | ±0.1pF  | GQM1882C2A4R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM1882C2A4R0CB01# |  |
|        |               |         | 4.3pF | ±0.1pF  | GQM1882C2A4R3BB01# |  |
|        |               |         |       | ±0.25pF | GQM1882C2A4R3CB01# |  |
|        |               |         | 4.7pF | ±0.1pF  | GQM1882C2A4R7BB01# |  |
|        |               |         |       | ±0.25pF | GQM1882C2A4R7CB01# |  |
|        |               |         | 5.0pF | ±0.1pF  | GQM1882C2A5R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM1882C2A5R0CB01# |  |
|        |               |         | 5.1pF | ±0.25pF | GQM1882C2A5R1CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1882C2A5R1DB01# |  |
|        |               |         | 5.6pF | ±0.25pF | GQM1882C2A5R6CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1882C2A5R6DB01# |  |
|        |               |         | 6.0pF | ±0.25pF | GQM1882C2A6R0CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1882C2A6R0DB01# |  |
|        |               |         | 6.2pF | ±0.25pF | GQM1882C2A6R2CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1882C2A6R2DB01# |  |
|        |               |         | 6.8pF | ±0.25pF | GQM1882C2A6R8CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1882C2A6R8DB01# |  |
|        | 50Vdc         | C0G     | 7.0pF | ±0.25pF | GQM1885C1H7R0CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1885C1H7R0DB01# |  |
|        |               |         | 7.5pF | ±0.25pF | GQM1885C1H7R5CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1885C1H7R5DB01# |  |
|        |               |         | 8.0pF | ±0.25pF | GQM1885C1H8R0CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1885C1H8R0DB01# |  |
|        |               |         | 8.2pF | ±0.25pF | GQM1885C1H8R2CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1885C1H8R2DB01# |  |
|        |               |         | 9.0pF | ±0.25pF | GQM1885C1H9R0CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1885C1H9R0DB01# |  |
|        |               |         | 9.1pF | ±0.25pF | GQM1885C1H9R1CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1885C1H9R1DB01# |  |
|        |               |         | 10pF  | ±2%     | GQM1885C1H100GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H100JB01# |  |
|        |               |         | 11pF  | ±2%     | GQM1885C1H110GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H110JB01# |  |
|        |               |         | 12pF  | ±2%     | GQM1885C1H120GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H120JB01# |  |
|        |               |         | 13pF  | ±2%     | GQM1885C1H130GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H130JB01# |  |
|        |               |         | 15pF  | ±2%     | GQM1885C1H150GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H150JB01# |  |
|        |               |         | 16pF  | ±2%     | GQM1885C1H160GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H160JB01# |  |

Part number # indicates the package specification code.



## GQM Series Temperature Compensating Type **HiQ** Part Number List

(→ ■ 1.6×0.8mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.9mm  | 50Vdc         | C0G     | 18pF  | ±2%     | GQM1885C1H180GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H180JB01# |  |
|        |               |         | 20pF  | ±2%     | GQM1885C1H200GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H200JB01# |  |
|        |               |         | 22pF  | ±2%     | GQM1885C1H220GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H220JB01# |  |
|        |               |         | 24pF  | ±2%     | GQM1885C1H240GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H240JB01# |  |
|        |               |         | 27pF  | ±2%     | GQM1885C1H270GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H270JB01# |  |
|        |               |         | 30pF  | ±2%     | GQM1885C1H300GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H300JB01# |  |
|        |               |         | 33pF  | ±2%     | GQM1885C1H330GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H330JB01# |  |
|        |               |         | 36pF  | ±2%     | GQM1885C1H360GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H360JB01# |  |
|        |               |         | 39pF  | ±2%     | GQM1885C1H390GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H390JB01# |  |
|        |               |         | 43pF  | ±2%     | GQM1885C1H430GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H430JB01# |  |
|        |               |         | 47pF  | ±2%     | GQM1885C1H470GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H470JB01# |  |
|        |               |         | 51pF  | ±2%     | GQM1885C1H510GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H510JB01# |  |
|        |               |         | 56pF  | ±2%     | GQM1885C1H560GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H560JB01# |  |
|        |               |         | 62pF  | ±2%     | GQM1885C1H620GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H620JB01# |  |
|        |               |         | 68pF  | ±2%     | GQM1885C1H680GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H680JB01# |  |
|        |               |         | 75pF  | ±2%     | GQM1885C1H750GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H750JB01# |  |
|        |               |         | 82pF  | ±2%     | GQM1885C1H820GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H820JB01# |  |
|        |               |         | 91pF  | ±2%     | GQM1885C1H910GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H910JB01# |  |
|        |               |         | 100pF | ±2%     | GQM1885C1H101GB01# |  |
|        |               |         |       | ±5%     | GQM1885C1H101JB01# |  |
|        |               | CH      | 7.0pF | ±0.25pF | GQM1882C1H7R0CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1882C1H7R0DB01# |  |
|        |               |         | 7.5pF | ±0.25pF | GQM1882C1H7R5CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1882C1H7R5DB01# |  |
|        |               |         | 8.0pF | ±0.25pF | GQM1882C1H8R0CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1882C1H8R0DB01# |  |
|        |               |         | 8.2pF | ±0.25pF | GQM1882C1H8R2CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1882C1H8R2DB01# |  |
|        |               |         | 9.0pF | ±0.25pF | GQM1882C1H9R0CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1882C1H9R0DB01# |  |
|        |               |         | 9.1pF | ±0.25pF | GQM1882C1H9R1CB01# |  |
|        |               |         |       | ±0.5pF  | GQM1882C1H9R1DB01# |  |
|        |               |         | 10pF  | ±2%     | GQM1882C1H100GB01# |  |
|        |               |         |       | ±5%     | GQM1882C1H100JB01# |  |
|        |               |         | 11pF  | ±2%     | GQM1882C1H110GB01# |  |
|        |               |         |       | ±5%     | GQM1882C1H110JB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol. | Part Number        |  |
|--------|---------------|---------|-------|------|--------------------|--|
| 0.9mm  | 50Vdc         | CH      | 12pF  | ±2%  | GQM1882C1H120GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H120JB01# |  |
|        |               |         | 13pF  | ±2%  | GQM1882C1H130GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H130JB01# |  |
|        |               |         | 15pF  | ±2%  | GQM1882C1H150GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H150JB01# |  |
|        |               |         | 16pF  | ±2%  | GQM1882C1H160GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H160JB01# |  |
|        |               |         | 18pF  | ±2%  | GQM1882C1H180GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H180JB01# |  |
|        |               |         | 20pF  | ±2%  | GQM1882C1H200GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H200JB01# |  |
|        |               |         | 22pF  | ±2%  | GQM1882C1H220GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H220JB01# |  |
|        |               |         | 24pF  | ±2%  | GQM1882C1H240GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H240JB01# |  |
|        |               |         | 27pF  | ±2%  | GQM1882C1H270GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H270JB01# |  |
|        |               |         | 30pF  | ±2%  | GQM1882C1H300GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H300JB01# |  |
|        |               |         | 33pF  | ±2%  | GQM1882C1H330GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H330JB01# |  |
|        |               |         | 36pF  | ±2%  | GQM1882C1H360GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H360JB01# |  |
|        |               |         | 39pF  | ±2%  | GQM1882C1H390GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H390JB01# |  |
|        |               |         | 43pF  | ±2%  | GQM1882C1H430GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H430JB01# |  |
|        |               |         | 47pF  | ±2%  | GQM1882C1H470GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H470JB01# |  |
|        |               |         | 51pF  | ±2%  | GQM1882C1H510GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H510JB01# |  |
|        |               |         | 56pF  | ±2%  | GQM1882C1H560GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H560JB01# |  |
|        |               |         | 62pF  | ±2%  | GQM1882C1H620GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H620JB01# |  |
|        |               |         | 68pF  | ±2%  | GQM1882C1H680GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H680JB01# |  |
|        |               |         | 75pF  | ±2%  | GQM1882C1H750GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H750JB01# |  |
|        |               |         | 82pF  | ±2%  | GQM1882C1H820GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H820JB01# |  |
|        |               |         | 91pF  | ±2%  | GQM1882C1H910GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H910JB01# |  |
|        |               |         | 100pF | ±2%  | GQM1882C1H101GB01# |  |
|        |               |         |       | ±5%  | GQM1882C1H101JB01# |  |

■ 2.0×1.25mm

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.95mm | 100Vdc        | C0G     | 1.0pF | ±0.1pF  | GQM2195C2A1R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A1R0CB01# |  |
|        |               |         | 1.1pF | ±0.1pF  | GQM2195C2A1R1BB01# |  |

Part number # indicates the package specification code.

## GQM Series Temperature Compensating Type **HiQ** Part Number List

(→ ■ 2.0×1.25mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.95mm | 100Vdc        | C0G     | 1.1pF | ±0.25pF | GQM2195C2A1R1CB01# |  |
|        |               |         |       | ±0.1pF  | GQM2195C2A1R2BB01# |  |
|        |               |         | 1.2pF | ±0.25pF | GQM2195C2A1R2CB01# |  |
|        |               |         |       | ±0.1pF  | GQM2195C2A1R3BB01# |  |
|        |               |         | 1.3pF | ±0.1pF  | GQM2195C2A1R3CB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A1R5BB01# |  |
|        |               |         | 1.5pF | ±0.1pF  | GQM2195C2A1R5CB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A1R6BB01# |  |
|        |               |         | 1.6pF | ±0.1pF  | GQM2195C2A1R6CB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A1R8BB01# |  |
|        |               |         | 1.8pF | ±0.1pF  | GQM2195C2A1R8CB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A2R0BB01# |  |
|        |               |         | 2.0pF | ±0.1pF  | GQM2195C2A2R0CB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A2R2BB01# |  |
|        |               |         | 2.2pF | ±0.1pF  | GQM2195C2A2R2CB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A2R4BB01# |  |
|        |               |         | 2.4pF | ±0.1pF  | GQM2195C2A2R4CB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A2R7BB01# |  |
|        |               |         | 2.7pF | ±0.1pF  | GQM2195C2A2R7CB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A3R0BB01# |  |
|        |               |         | 3.0pF | ±0.1pF  | GQM2195C2A3R0CB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A3R3BB01# |  |
|        |               |         | 3.3pF | ±0.1pF  | GQM2195C2A3R3CB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A3R6BB01# |  |
|        |               |         | 3.6pF | ±0.1pF  | GQM2195C2A3R6CB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A3R9BB01# |  |
|        |               |         | 3.9pF | ±0.1pF  | GQM2195C2A3R9CB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A4R0BB01# |  |
|        |               |         | 4.0pF | ±0.1pF  | GQM2195C2A4R0CB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A4R3BB01# |  |
|        |               |         | 4.3pF | ±0.1pF  | GQM2195C2A4R3CB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A4R7BB01# |  |
|        |               |         | 4.7pF | ±0.1pF  | GQM2195C2A4R7CB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A5R0BB01# |  |
|        |               |         | 5.0pF | ±0.1pF  | GQM2195C2A5R0CB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A5R1CB01# |  |
|        |               |         | 5.1pF | ±0.25pF | GQM2195C2A5R1DB01# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2A5R6CB01# |  |
|        |               |         | 5.6pF | ±0.25pF | GQM2195C2A5R6DB01# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2A6R0CB01# |  |
|        |               |         | 6.0pF | ±0.25pF | GQM2195C2A6R0DB01# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2A6R2CB01# |  |
|        |               |         | 6.2pF | ±0.25pF | GQM2195C2A6R2DB01# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2A6R8CB01# |  |
|        |               |         | 6.8pF | ±0.25pF | GQM2195C2A6R8DB01# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2A7R0CB01# |  |
|        |               |         | 7.0pF | ±0.25pF | GQM2195C2A7R0DB01# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2A7R5CB01# |  |
|        |               |         | 7.5pF | ±0.25pF | GQM2195C2A7R5DB01# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2A8R0CB01# |  |
|        |               |         | 8.0pF | ±0.25pF | GQM2195C2A8R0DB01# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2A8R2CB01# |  |
|        |               |         | 8.2pF | ±0.25pF | GQM2195C2A8R2DB01# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2A9R0CB01# |  |
|        |               |         | 9.0pF | ±0.25pF | GQM2195C2A9R0DB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.95mm | 100Vdc        | C0G     | 9.0pF | ±0.5pF  | GQM2195C2A9R0DB01# |  |
|        |               |         |       | ±0.25pF | GQM2195C2A9R1CB01# |  |
|        |               |         | 9.1pF | ±0.25pF | GQM2195C2A9R1DB01# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2A100GB01# |  |
|        |               |         | 10pF  | ±2%     | GQM2195C2A100GB01# |  |
|        |               |         |       | ±5%     | GQM2195C2A100JB01# |  |
|        |               |         | 11pF  | ±2%     | GQM2195C2A110GB01# |  |
|        |               |         |       | ±5%     | GQM2195C2A110JB01# |  |
|        |               |         | 12pF  | ±2%     | GQM2195C2A120GB01# |  |
|        |               |         |       | ±5%     | GQM2195C2A120JB01# |  |
|        |               |         | 13pF  | ±2%     | GQM2195C2A130GB01# |  |
|        |               |         |       | ±5%     | GQM2195C2A130JB01# |  |
|        |               |         | 15pF  | ±2%     | GQM2195C2A150GB01# |  |
|        |               |         |       | ±5%     | GQM2195C2A150JB01# |  |
|        |               |         | 16pF  | ±2%     | GQM2195C2A160GB01# |  |
|        |               |         |       | ±5%     | GQM2195C2A160JB01# |  |
|        |               |         | 18pF  | ±2%     | GQM2195C2A180GB01# |  |
|        |               |         |       | ±5%     | GQM2195C2A180JB01# |  |
|        |               | CK      | 1.0pF | ±0.1pF  | GQM2194C2A1R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM2194C2A1R0CB01# |  |
|        |               |         | 1.1pF | ±0.1pF  | GQM2194C2A1R1BB01# |  |
|        |               |         |       | ±0.25pF | GQM2194C2A1R1CB01# |  |
|        |               |         | 1.2pF | ±0.1pF  | GQM2194C2A1R2BB01# |  |
|        |               |         |       | ±0.25pF | GQM2194C2A1R2CB01# |  |
|        |               |         | 1.3pF | ±0.1pF  | GQM2194C2A1R3BB01# |  |
|        |               |         |       | ±0.25pF | GQM2194C2A1R3CB01# |  |
|        |               |         | 1.5pF | ±0.1pF  | GQM2194C2A1R5BB01# |  |
|        |               |         |       | ±0.25pF | GQM2194C2A1R5CB01# |  |
|        |               |         | 1.6pF | ±0.1pF  | GQM2194C2A1R6BB01# |  |
|        |               |         |       | ±0.25pF | GQM2194C2A1R6CB01# |  |
|        |               |         | 1.8pF | ±0.1pF  | GQM2194C2A1R8BB01# |  |
|        |               |         |       | ±0.25pF | GQM2194C2A1R8CB01# |  |
|        |               |         | 2.0pF | ±0.1pF  | GQM2194C2A2R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM2194C2A2R0CB01# |  |
|        |               | CJ      | 2.2pF | ±0.1pF  | GQM2193C2A2R2BB01# |  |
|        |               |         |       | ±0.25pF | GQM2193C2A2R2CB01# |  |
|        |               |         | 2.4pF | ±0.1pF  | GQM2193C2A2R4BB01# |  |
|        |               |         |       | ±0.25pF | GQM2193C2A2R4CB01# |  |
|        |               |         | 2.7pF | ±0.1pF  | GQM2193C2A2R7BB01# |  |
|        |               |         |       | ±0.25pF | GQM2193C2A2R7CB01# |  |
|        |               |         | 3.0pF | ±0.1pF  | GQM2193C2A3R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM2193C2A3R0CB01# |  |
|        |               |         | 3.3pF | ±0.1pF  | GQM2193C2A3R3BB01# |  |
|        |               |         |       | ±0.25pF | GQM2193C2A3R3CB01# |  |
|        |               |         | 3.6pF | ±0.1pF  | GQM2193C2A3R6BB01# |  |
|        |               |         |       | ±0.25pF | GQM2193C2A3R6CB01# |  |
|        |               |         | 3.9pF | ±0.1pF  | GQM2193C2A3R9BB01# |  |
|        |               |         |       | ±0.25pF | GQM2193C2A3R9CB01# |  |
|        |               | CH      | 4.0pF | ±0.1pF  | GQM2192C2A4R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM2192C2A4R0CB01# |  |
|        |               |         | 4.3pF | ±0.1pF  | GQM2192C2A4R3BB01# |  |
|        |               |         |       | ±0.25pF | GQM2192C2A4R3CB01# |  |
|        |               |         | 4.7pF | ±0.1pF  | GQM2192C2A4R7BB01# |  |
|        |               |         |       | ±0.25pF | GQM2192C2A4R7CB01# |  |
|        |               |         | 5.0pF | ±0.1pF  | GQM2192C2A5R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM2192C2A5R0DB01# |  |

Part number # indicates the package specification code.

# GQM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 2.0×1.25mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.95mm | 100Vdc        | CH      | 5.0pF | ±0.25pF | GQM2192C2A5R0CB01# |  |
|        |               |         |       | ±0.25pF | GQM2192C2A5R1CB01# |  |
|        |               |         |       | ±0.5pF  | GQM2192C2A5R1DB01# |  |
|        |               |         | 5.6pF | ±0.25pF | GQM2192C2A5R6CB01# |  |
|        |               |         |       | ±0.5pF  | GQM2192C2A5R6DB01# |  |
|        |               |         | 6.0pF | ±0.25pF | GQM2192C2A6R0CB01# |  |
|        |               |         |       | ±0.5pF  | GQM2192C2A6R0DB01# |  |
|        |               |         | 6.2pF | ±0.25pF | GQM2192C2A6R2CB01# |  |
|        |               |         |       | ±0.5pF  | GQM2192C2A6R2DB01# |  |
|        |               |         | 6.8pF | ±0.25pF | GQM2192C2A6R8CB01# |  |
|        |               |         |       | ±0.5pF  | GQM2192C2A6R8DB01# |  |
|        |               |         | 7.0pF | ±0.25pF | GQM2192C2A7R0CB01# |  |
|        |               |         |       | ±0.5pF  | GQM2192C2A7R0DB01# |  |
|        |               |         | 7.5pF | ±0.25pF | GQM2192C2A7R5CB01# |  |
|        |               |         |       | ±0.5pF  | GQM2192C2A7R5DB01# |  |
|        |               |         | 8.0pF | ±0.25pF | GQM2192C2A8R0CB01# |  |
|        |               |         |       | ±0.5pF  | GQM2192C2A8R0DB01# |  |
|        |               |         | 8.2pF | ±0.25pF | GQM2192C2A8R2CB01# |  |
|        |               |         |       | ±0.5pF  | GQM2192C2A8R2DB01# |  |
|        |               |         | 9.0pF | ±0.25pF | GQM2192C2A9R0CB01# |  |
|        |               |         |       | ±0.5pF  | GQM2192C2A9R0DB01# |  |
|        |               |         | 9.1pF | ±0.25pF | GQM2192C2A9R1CB01# |  |
|        |               |         |       | ±0.5pF  | GQM2192C2A9R1DB01# |  |
|        |               |         | 10pF  | ±2%     | GQM2192C2A100GB01# |  |
|        |               |         |       | ±5%     | GQM2192C2A100JB01# |  |
|        |               |         | 11pF  | ±2%     | GQM2192C2A110GB01# |  |
|        |               |         |       | ±5%     | GQM2192C2A110JB01# |  |
|        |               |         | 12pF  | ±2%     | GQM2192C2A120GB01# |  |
|        |               |         |       | ±5%     | GQM2192C2A120JB01# |  |
|        |               |         | 13pF  | ±2%     | GQM2192C2A130GB01# |  |
|        |               |         |       | ±5%     | GQM2192C2A130JB01# |  |
|        |               |         | 15pF  | ±2%     | GQM2192C2A150GB01# |  |
|        |               |         |       | ±5%     | GQM2192C2A150JB01# |  |
|        |               |         | 16pF  | ±2%     | GQM2192C2A160GB01# |  |
|        |               |         |       | ±5%     | GQM2192C2A160JB01# |  |
|        |               |         | 18pF  | ±2%     | GQM2192C2A180GB01# |  |
|        |               |         |       | ±5%     | GQM2192C2A180JB01# |  |
|        | 50Vdc         | C0G     | 20pF  | ±2%     | GQM2195C1H200GB01# |  |
|        |               |         |       | ±5%     | GQM2195C1H200JB01# |  |
|        |               |         | 22pF  | ±2%     | GQM2195C1H220GB01# |  |
|        |               |         |       | ±5%     | GQM2195C1H220JB01# |  |
|        |               |         | 24pF  | ±2%     | GQM2195C1H240GB01# |  |
|        |               |         |       | ±5%     | GQM2195C1H240JB01# |  |
|        |               |         | 27pF  | ±2%     | GQM2195C1H270GB01# |  |
|        |               |         |       | ±5%     | GQM2195C1H270JB01# |  |
|        |               |         | 30pF  | ±2%     | GQM2195C1H300GB01# |  |
|        |               |         |       | ±5%     | GQM2195C1H300JB01# |  |
|        |               |         | 33pF  | ±2%     | GQM2195C1H330GB01# |  |
|        |               |         |       | ±5%     | GQM2195C1H330JB01# |  |
|        |               |         | 36pF  | ±2%     | GQM2195C1H360GB01# |  |
|        |               |         |       | ±5%     | GQM2195C1H360JB01# |  |
|        |               |         | 39pF  | ±2%     | GQM2195C1H390GB01# |  |
|        |               |         |       | ±5%     | GQM2195C1H390JB01# |  |
|        |               |         | 43pF  | ±2%     | GQM2195C1H430GB01# |  |
|        |               |         |       | ±5%     | GQM2195C1H430JB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol. | Part Number        |  |
|--------|---------------|---------|-------|------|--------------------|--|
| 0.95mm | 50Vdc         | C0G     | 43pF  | ±5%  | GQM2195C1H430JB01# |  |
|        |               |         |       | ±2%  | GQM2195C1H470GB01# |  |
|        |               |         |       | ±5%  | GQM2195C1H470JB01# |  |
|        |               |         | 51pF  | ±2%  | GQM2195C1H510GB01# |  |
|        |               |         |       | ±5%  | GQM2195C1H510JB01# |  |
|        |               |         | 56pF  | ±2%  | GQM2195C1H560GB01# |  |
|        |               |         |       | ±5%  | GQM2195C1H560JB01# |  |
|        |               |         | 62pF  | ±2%  | GQM2195C1H620GB01# |  |
|        |               |         |       | ±5%  | GQM2195C1H620JB01# |  |
|        |               |         | 68pF  | ±2%  | GQM2195C1H680GB01# |  |
|        |               |         |       | ±5%  | GQM2195C1H680JB01# |  |
|        |               |         | 75pF  | ±2%  | GQM2195C1H750GB01# |  |
|        |               |         |       | ±5%  | GQM2195C1H750JB01# |  |
|        |               |         | 82pF  | ±2%  | GQM2195C1H820GB01# |  |
|        |               |         |       | ±5%  | GQM2195C1H820JB01# |  |
|        |               |         | 91pF  | ±2%  | GQM2195C1H910GB01# |  |
|        |               |         |       | ±5%  | GQM2195C1H910JB01# |  |
|        |               |         | 100pF | ±2%  | GQM2195C1H101GB01# |  |
|        |               |         |       | ±5%  | GQM2195C1H101JB01# |  |
|        |               | CH      | 20pF  | ±2%  | GQM2192C1H200GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H200JB01# |  |
|        |               |         | 22pF  | ±2%  | GQM2192C1H220GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H220JB01# |  |
|        |               |         | 24pF  | ±2%  | GQM2192C1H240GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H240JB01# |  |
|        |               |         | 27pF  | ±2%  | GQM2192C1H270GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H270JB01# |  |
|        |               |         | 30pF  | ±2%  | GQM2192C1H300GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H300JB01# |  |
|        |               |         | 33pF  | ±2%  | GQM2192C1H330GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H330JB01# |  |
|        |               |         | 36pF  | ±2%  | GQM2192C1H360GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H360JB01# |  |
|        |               |         | 39pF  | ±2%  | GQM2192C1H390GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H390JB01# |  |
|        |               |         | 43pF  | ±2%  | GQM2192C1H430GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H430JB01# |  |
|        |               |         | 47pF  | ±2%  | GQM2192C1H470GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H470JB01# |  |
|        |               |         | 51pF  | ±2%  | GQM2192C1H510GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H510JB01# |  |
|        |               |         | 56pF  | ±2%  | GQM2192C1H560GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H560JB01# |  |
|        |               |         | 62pF  | ±2%  | GQM2192C1H620GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H620JB01# |  |
|        |               |         | 68pF  | ±2%  | GQM2192C1H680GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H680JB01# |  |
|        |               |         | 75pF  | ±2%  | GQM2192C1H750GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H750JB01# |  |
|        |               |         | 82pF  | ±2%  | GQM2192C1H820GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H820JB01# |  |
|        |               |         | 91pF  | ±2%  | GQM2192C1H910GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H910JB01# |  |
|        |               |         | 100pF | ±2%  | GQM2192C1H101GB01# |  |
|        |               |         |       | ±5%  | GQM2192C1H101JB01# |  |

Part number # indicates the package specification code.

## GQM Series Temperature Compensating Type **HiQ** Part Number List

(→ ■ 2.0×1.25mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 0.95mm | 50Vdc         | CH      | 100pF | ±5%     | GQM2192C1H101JB01# |  |
| 1.0mm  | 250Vdc        | C0G     | 1.0pF | ±0.1pF  | GQM2195C2E1R0BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E1R0CB12# |  |
|        |               |         | 1.1pF | ±0.1pF  | GQM2195C2E1R1BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E1R1CB12# |  |
|        |               |         | 1.2pF | ±0.1pF  | GQM2195C2E1R2BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E1R2CB12# |  |
|        |               |         | 1.3pF | ±0.1pF  | GQM2195C2E1R3BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E1R3CB12# |  |
|        |               |         | 1.5pF | ±0.1pF  | GQM2195C2E1R5BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E1R5CB12# |  |
|        |               |         | 1.6pF | ±0.1pF  | GQM2195C2E1R6BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E1R6CB12# |  |
|        |               |         | 1.8pF | ±0.1pF  | GQM2195C2E1R8BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E1R8CB12# |  |
|        |               |         | 2.0pF | ±0.1pF  | GQM2195C2E2R0BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E2R0CB12# |  |
|        |               |         | 2.2pF | ±0.1pF  | GQM2195C2E2R2BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E2R2CB12# |  |
|        |               |         | 2.4pF | ±0.1pF  | GQM2195C2E2R4BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E2R4CB12# |  |
|        |               |         | 2.7pF | ±0.1pF  | GQM2195C2E2R7BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E2R7CB12# |  |
|        |               |         | 3.0pF | ±0.1pF  | GQM2195C2E3R0BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E3R0CB12# |  |
|        |               |         | 3.3pF | ±0.1pF  | GQM2195C2E3R3BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E3R3CB12# |  |
|        |               |         | 3.6pF | ±0.1pF  | GQM2195C2E3R6BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E3R6CB12# |  |
|        |               |         | 3.9pF | ±0.1pF  | GQM2195C2E3R9BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E3R9CB12# |  |
|        |               |         | 4.0pF | ±0.1pF  | GQM2195C2E4R0BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E4R0CB12# |  |
|        |               |         | 4.3pF | ±0.1pF  | GQM2195C2E4R3BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E4R3CB12# |  |
|        |               |         | 4.7pF | ±0.1pF  | GQM2195C2E4R7BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E4R7CB12# |  |
|        |               |         | 5.0pF | ±0.1pF  | GQM2195C2E5R0BB12# |  |
|        |               |         |       | ±0.25pF | GQM2195C2E5R0CB12# |  |
|        |               |         | 5.1pF | ±0.25pF | GQM2195C2E5R1CB12# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2E5R1DB12# |  |
|        |               |         | 5.6pF | ±0.25pF | GQM2195C2E5R6CB12# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2E5R6DB12# |  |
|        |               |         | 6.0pF | ±0.25pF | GQM2195C2E6R0CB12# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2E6R0DB12# |  |
|        |               |         | 6.2pF | ±0.25pF | GQM2195C2E6R2CB12# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2E6R2DB12# |  |
|        |               |         | 6.8pF | ±0.25pF | GQM2195C2E6R8CB12# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2E6R8DB12# |  |
|        |               |         | 7.0pF | ±0.25pF | GQM2195C2E7R0CB12# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2E7R0DB12# |  |
|        |               |         | 7.5pF | ±0.25pF | GQM2195C2E7R5CB12# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2E7R5DB12# |  |
|        |               |         | 8.0pF | ±0.25pF | GQM2195C2E8R0CB12# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 1.0mm  | 250Vdc        | C0G     | 8.0pF | ±0.5pF  | GQM2195C2E8R0DB12# |  |
|        |               |         | 8.2pF | ±0.25pF | GQM2195C2E8R2CB12# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2E8R2DB12# |  |
|        |               |         | 9.0pF | ±0.25pF | GQM2195C2E9R0CB12# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2E9R0DB12# |  |
|        |               |         | 9.1pF | ±0.25pF | GQM2195C2E9R1CB12# |  |
|        |               |         |       | ±0.5pF  | GQM2195C2E9R1DB12# |  |
|        |               |         | 10pF  | ±2%     | GQM2195C2E100GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E100JB12# |  |
|        |               |         | 11pF  | ±2%     | GQM2195C2E110GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E110JB12# |  |
|        |               |         | 12pF  | ±2%     | GQM2195C2E120GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E120JB12# |  |
|        |               |         | 13pF  | ±2%     | GQM2195C2E130GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E130JB12# |  |
|        |               |         | 15pF  | ±2%     | GQM2195C2E150GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E150JB12# |  |
|        |               |         | 16pF  | ±2%     | GQM2195C2E160GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E160JB12# |  |
|        |               |         | 18pF  | ±2%     | GQM2195C2E180GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E180JB12# |  |
|        |               |         | 20pF  | ±2%     | GQM2195C2E200GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E200JB12# |  |
|        |               |         | 22pF  | ±2%     | GQM2195C2E220GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E220JB12# |  |
|        |               |         | 24pF  | ±2%     | GQM2195C2E240GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E240JB12# |  |
|        |               |         | 27pF  | ±2%     | GQM2195C2E270GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E270JB12# |  |
|        |               |         | 30pF  | ±2%     | GQM2195C2E300GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E300JB12# |  |
|        |               |         | 33pF  | ±2%     | GQM2195C2E330GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E330JB12# |  |
|        |               |         | 36pF  | ±2%     | GQM2195C2E360GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E360JB12# |  |
|        |               |         | 39pF  | ±2%     | GQM2195C2E390GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E390JB12# |  |
|        |               |         | 43pF  | ±2%     | GQM2195C2E430GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E430JB12# |  |
|        |               |         | 47pF  | ±2%     | GQM2195C2E470GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E470JB12# |  |
|        |               |         | 51pF  | ±2%     | GQM2195C2E510GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E510JB12# |  |
|        |               |         | 56pF  | ±2%     | GQM2195C2E560GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E560JB12# |  |
|        |               |         | 62pF  | ±2%     | GQM2195C2E620GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E620JB12# |  |
|        |               |         | 68pF  | ±2%     | GQM2195C2E680GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E680JB12# |  |
|        |               |         | 75pF  | ±2%     | GQM2195C2E750GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E750JB12# |  |
|        |               |         | 82pF  | ±2%     | GQM2195C2E820GB12# |  |
|        |               |         |       | ±5%     | GQM2195C2E820JB12# |  |
|        |               |         | 91pF  | ±2%     | GQM2195C2E910GB12# |  |

Part number # indicates the package specification code.



## GQM Series Temperature Compensating Type **HiQ** Part Number List

(→ ■ 2.0×1.25mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol. | Part Number        |  |
|--------|---------------|---------|-------|------|--------------------|--|
| 1.0mm  | 250Vdc        | C0G     | 91pF  | ±5%  | GQM2195C2E910JB12# |  |
|        |               |         | 100pF | ±2%  | GQM2195C2E101GB12# |  |
|        |               |         |       | ±5%  | GQM2195C2E101JB12# |  |

■ 2.8×2.8mm

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 1.35mm | 500Vdc        | C0G     | 1.0pF | ±0.1pF  | GQM22M5C2H1R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H1R0CB01# |  |
|        |               |         | 1.1pF | ±0.1pF  | GQM22M5C2H1R1BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H1R1CB01# |  |
|        |               |         | 1.2pF | ±0.1pF  | GQM22M5C2H1R2BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H1R2CB01# |  |
|        |               |         | 1.3pF | ±0.1pF  | GQM22M5C2H1R3BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H1R3CB01# |  |
|        |               |         | 1.5pF | ±0.1pF  | GQM22M5C2H1R5BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H1R5CB01# |  |
|        |               |         | 1.6pF | ±0.1pF  | GQM22M5C2H1R6BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H1R6CB01# |  |
|        |               |         | 1.8pF | ±0.1pF  | GQM22M5C2H1R8BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H1R8CB01# |  |
|        |               |         | 2.0pF | ±0.1pF  | GQM22M5C2H2R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H2R0CB01# |  |
|        |               |         | 2.2pF | ±0.1pF  | GQM22M5C2H2R2BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H2R2CB01# |  |
|        |               |         | 2.4pF | ±0.1pF  | GQM22M5C2H2R4BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H2R4CB01# |  |
|        |               |         | 2.7pF | ±0.1pF  | GQM22M5C2H2R7BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H2R7CB01# |  |
|        |               |         | 3.0pF | ±0.1pF  | GQM22M5C2H3R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H3R0CB01# |  |
|        |               |         | 3.3pF | ±0.1pF  | GQM22M5C2H3R3BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H3R3CB01# |  |
|        |               |         | 3.6pF | ±0.1pF  | GQM22M5C2H3R6BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H3R6CB01# |  |
|        |               |         | 3.9pF | ±0.1pF  | GQM22M5C2H3R9BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H3R9CB01# |  |
|        |               |         | 4.0pF | ±0.1pF  | GQM22M5C2H4R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H4R0CB01# |  |
|        |               |         | 4.3pF | ±0.1pF  | GQM22M5C2H4R3BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H4R3CB01# |  |
|        |               |         | 4.7pF | ±0.1pF  | GQM22M5C2H4R7BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H4R7CB01# |  |
|        |               |         | 5.0pF | ±0.1pF  | GQM22M5C2H5R0BB01# |  |
|        |               |         |       | ±0.25pF | GQM22M5C2H5R0CB01# |  |
|        |               |         | 5.1pF | ±0.25pF | GQM22M5C2H5R1CB01# |  |
|        |               |         |       | ±0.5pF  | GQM22M5C2H5R1DB01# |  |
|        |               |         | 5.6pF | ±0.25pF | GQM22M5C2H5R6CB01# |  |
|        |               |         |       | ±0.5pF  | GQM22M5C2H5R6DB01# |  |
|        |               |         | 6.0pF | ±0.25pF | GQM22M5C2H6R0CB01# |  |
|        |               |         |       | ±0.5pF  | GQM22M5C2H6R0DB01# |  |
|        |               |         | 6.2pF | ±0.25pF | GQM22M5C2H6R2CB01# |  |
|        |               |         |       | ±0.5pF  | GQM22M5C2H6R2DB01# |  |

| T max. | Rated Voltage | TC Code | Cap.  | Tol.    | Part Number        |  |
|--------|---------------|---------|-------|---------|--------------------|--|
| 1.35mm | 500Vdc        | C0G     | 6.8pF | ±0.25pF | GQM22M5C2H6R8CB01# |  |
|        |               |         |       | ±0.5pF  | GQM22M5C2H6R8DB01# |  |
|        |               |         | 7.0pF | ±0.25pF | GQM22M5C2H7R0CB01# |  |
|        |               |         |       | ±0.5pF  | GQM22M5C2H7R0DB01# |  |
|        |               |         | 7.5pF | ±0.25pF | GQM22M5C2H7R5CB01# |  |
|        |               |         |       | ±0.5pF  | GQM22M5C2H7R5DB01# |  |
|        |               |         | 8.0pF | ±0.25pF | GQM22M5C2H8R0CB01# |  |
|        |               |         |       | ±0.5pF  | GQM22M5C2H8R0DB01# |  |
|        |               |         | 8.2pF | ±0.25pF | GQM22M5C2H8R2CB01# |  |
|        |               |         |       | ±0.5pF  | GQM22M5C2H8R2DB01# |  |
|        |               |         | 9.0pF | ±0.25pF | GQM22M5C2H9R0CB01# |  |
|        |               |         |       | ±0.5pF  | GQM22M5C2H9R0DB01# |  |
|        |               |         | 9.1pF | ±0.25pF | GQM22M5C2H9R1CB01# |  |
|        |               |         |       | ±0.5pF  | GQM22M5C2H9R1DB01# |  |
|        |               |         | 10pF  | ±2%     | GQM22M5C2H100GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H100JB01# |  |
|        |               |         | 11pF  | ±2%     | GQM22M5C2H110GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H110JB01# |  |
|        |               |         | 12pF  | ±2%     | GQM22M5C2H120GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H120JB01# |  |
|        |               |         | 13pF  | ±2%     | GQM22M5C2H130GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H130JB01# |  |
|        |               |         | 15pF  | ±2%     | GQM22M5C2H150GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H150JB01# |  |
|        |               |         | 16pF  | ±2%     | GQM22M5C2H160GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H160JB01# |  |
|        |               |         | 18pF  | ±2%     | GQM22M5C2H180GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H180JB01# |  |
|        |               |         | 20pF  | ±2%     | GQM22M5C2H200GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H200JB01# |  |
|        |               |         | 22pF  | ±2%     | GQM22M5C2H220GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H220JB01# |  |
|        |               |         | 24pF  | ±2%     | GQM22M5C2H240GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H240JB01# |  |
|        |               |         | 27pF  | ±2%     | GQM22M5C2H270GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H270JB01# |  |
|        |               |         | 30pF  | ±2%     | GQM22M5C2H300GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H300JB01# |  |
|        |               |         | 33pF  | ±2%     | GQM22M5C2H330GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H330JB01# |  |
|        |               |         | 36pF  | ±2%     | GQM22M5C2H360GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H360JB01# |  |
|        |               |         | 39pF  | ±2%     | GQM22M5C2H390GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H390JB01# |  |
|        |               |         | 43pF  | ±2%     | GQM22M5C2H430GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H430JB01# |  |
|        |               |         | 47pF  | ±2%     | GQM22M5C2H470GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H470JB01# |  |
|        |               |         | 51pF  | ±2%     | GQM22M5C2H510GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H510JB01# |  |
|        |               |         | 56pF  | ±2%     | GQM22M5C2H560GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H560JB01# |  |
|        |               |         | 62pF  | ±2%     | GQM22M5C2H620GB01# |  |
|        |               |         |       | ±5%     | GQM22M5C2H620JB01# |  |

Part number # indicates the package specification code.



GRRM Series

GJM Series

GMA Series

GMD Series

GQM Series

GRJ Series

GR3 Series

KRM Series

KR3 Series

LLA Series

LLL Series

LLM Series

LLR Series

⚠Caution/  
Notice

# GQM Series Temperature Compensating Type HiQ Part Number List

(→ ■ 2.8×2.8mm)

| T max. | Rated Voltage | TC Code | Cap.  | Tol. | Part Number        |  |
|--------|---------------|---------|-------|------|--------------------|--|
| 1.35mm | 500Vdc        | C0G     | 68pF  | ±2%  | GQM22M5C2H680GB01# |  |
|        |               |         |       | ±5%  | GQM22M5C2H680JB01# |  |
|        |               |         | 75pF  | ±2%  | GQM22M5C2H750GB01# |  |
|        |               |         |       | ±5%  | GQM22M5C2H750JB01# |  |
|        |               |         | 82pF  | ±2%  | GQM22M5C2H820GB01# |  |
|        |               |         |       | ±5%  | GQM22M5C2H820JB01# |  |
|        |               |         | 91pF  | ±2%  | GQM22M5C2H910GB01# |  |
|        |               |         |       | ±5%  | GQM22M5C2H910JB01# |  |
|        |               |         | 100pF | ±2%  | GQM22M5C2H101GB01# |  |
|        |               |         |       | ±5%  | GQM22M5C2H101JB01# |  |
|        |               |         |       |      |                    |  |
|        |               |         |       |      |                    |  |

Part number # indicates the package specification code.

## Resin External Electrode Type

# GRJ Series




Deflecting crack

The resin external electrodes prevent the occurrence of cracking caused by deflection stress after board mounting!


## Features

### ① The resin external electrodes suppress cracks by board deflection.

Cracking of the ceramic element is suppressed by the resin of the external electrodes, which releases the stress.



### ② Suppresses the occurrence of cracking caused by deflection stress at the time of board mounting, etc.




Due to the specification of the measuring instrument, measurements can be performed up to 8mm.

### ③ Ideal for consumer and industrial electronic equipment, etc. where there heat stress, vibration and impact are applied.

## Specifications

|                   |                                            |
|-------------------|--------------------------------------------|
| Size              | 2.0×1.25mm to 5.7×5.0mm                    |
| Rated Voltage     | DC250V to 1kV                              |
| Capacitance       | 470pF to 1.0μF                             |
| Main Applications | Consumer & Industrial Electronic Equipment |



This catalog contains only a portion of the product lineup.  
Please refer to the capacitor search tool on the Murata Web site for details.

## GRJ Series High Dielectric Constant Type Part Number List

### ■ 2.0×1.25mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 1.0mm  | 250Vdc        | X7R     | 1000pF  | ±10% | GRJ21AR72E102KWJ1# |  |
|        |               |         | 1500pF  | ±10% | GRJ21AR72E152KWJ1# |  |
|        |               |         | 2200pF  | ±10% | GRJ21AR72E222KWJ1# |  |
|        |               |         | 3300pF  | ±10% | GRJ21AR72E332KWJ1# |  |
|        |               |         | 4700pF  | ±10% | GRJ21AR72E472KWJ1# |  |
|        |               |         | 6800pF  | ±10% | GRJ21AR72E682KWJ1# |  |
| 1.45mm | 250Vdc        | X7R     | 10000pF | ±10% | GRJ21BR72E103KWJ3# |  |
|        |               |         | 15000pF | ±10% | GRJ21BR72E153KWJ3# |  |
|        |               |         | 22000pF | ±10% | GRJ21BR72E223KWJ3# |  |
|        |               |         |         |      |                    |  |

### ■ 3.2×1.6mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 1.25mm | 1000Vdc       | X7R     | 470pF   | ±10% | GRJ31BR73A471KWJ1# |  |
|        |               |         | 680pF   | ±10% | GRJ31BR73A681KWJ1# |  |
|        |               |         | 1000pF  | ±10% | GRJ31BR73A102KWJ1# |  |
|        |               |         | 1500pF  | ±10% | GRJ31BR73A152KWJ1# |  |
|        |               |         | 2200pF  | ±10% | GRJ31BR73A222KWJ1# |  |
|        |               |         | 3300pF  | ±10% | GRJ31BR73A332KWJ1# |  |
|        |               |         | 4700pF  | ±10% | GRJ31BR73A472KWJ1# |  |
|        |               |         |         |      |                    |  |
|        | 630Vdc        | X7R     | 1000pF  | ±10% | GRJ31BR72J102KWJ1# |  |
|        |               |         | 1500pF  | ±10% | GRJ31BR72J152KWJ1# |  |
|        |               |         | 2200pF  | ±10% | GRJ31BR72J222KWJ1# |  |
|        |               |         | 3300pF  | ±10% | GRJ31BR72J332KWJ1# |  |
|        |               |         | 4700pF  | ±10% | GRJ31BR72J472KWJ1# |  |
|        |               |         | 6800pF  | ±10% | GRJ31BR72J682KWJ1# |  |
|        |               |         | 10000pF | ±10% | GRJ31BR72J103KWJ1# |  |
|        |               |         |         |      |                    |  |
|        | 250Vdc        | X7R     | 15000pF | ±10% | GRJ31BR72E153KWJ1# |  |
|        |               |         | 22000pF | ±10% | GRJ31BR72E223KWJ1# |  |
|        |               |         | 68000pF | ±10% | GRJ31BR72E683KWJ1# |  |
|        |               |         |         |      |                    |  |
| 1.8mm  | 1000Vdc       | X7R     | 6800pF  | ±10% | GRJ31CR73A682KWJ3# |  |
|        |               |         | 10000pF | ±10% | GRJ31CR73A103KWJ3# |  |
|        |               |         |         |      |                    |  |
|        | 630Vdc        | X7R     | 15000pF | ±10% | GRJ31CR72J153KWJ3# |  |
|        |               |         | 22000pF | ±10% | GRJ31CR72J223KWJ3# |  |
|        | 250Vdc        | X7R     | 33000pF | ±10% | GRJ31CR72E333KWJ3# |  |
|        |               |         | 47000pF | ±10% | GRJ31CR72E473KWJ3# |  |
|        |               |         | 0.10μF  | ±10% | GRJ31CR72E104KWJ3# |  |

### ■ 3.2×2.5mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 1.5mm  | 1000Vdc       | X7R     | 6800pF  | ±10% | GRJ32QR73A682KWJ1# |  |
|        |               |         | 10000pF | ±10% | GRJ32QR73A103KWJ1# |  |
|        | 630Vdc        | X7R     | 22000pF | ±10% | GRJ32QR72J223KWJ1# |  |
|        | 250Vdc        | X7R     | 68000pF | ±10% | GRJ32QR72E683KWJ1# |  |
|        |               |         | 0.15μF  | ±10% | GRJ32QR72E154KWJ1# |  |
| 2.0mm  | 1000Vdc       | X7R     | 15000pF | ±10% | GRJ32DR73A153KWJ1# |  |
|        |               |         | 22000pF | ±10% | GRJ32DR73A223KWJ1# |  |
|        | 630Vdc        | X7R     | 33000pF | ±10% | GRJ32DR72J333KWJ1# |  |
|        |               |         | 47000pF | ±10% | GRJ32DR72J473KWJ1# |  |

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |  |
|--------|---------------|---------|--------|------|--------------------|--|
| 2.0mm  | 250Vdc        | X7R     | 0.10μF | ±10% | GRJ32DR72E104KWJ1# |  |
|        |               |         | 0.22μF | ±10% | GRJ32DR72E224KWJ1# |  |

### ■ 4.5×3.2mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 1.5mm  | 630Vdc        | X7R     | 68000pF | ±10% | GRJ43QR72J683KWJ1# |  |
|        | 250Vdc        | X7R     | 0.15μF  | ±10% | GRJ43QR72E154KWJ1# |  |
| 2.0mm  | 1000Vdc       | X7R     | 33000pF | ±10% | GRJ43DR73A333KWJ1# |  |
|        |               |         | 47000pF | ±10% | GRJ43DR73A473KWJ1# |  |
|        | 630Vdc        | X7R     | 0.10μF  | ±10% | GRJ43DR72J104KWJ1# |  |
|        |               |         | 0.22μF  | ±10% | GRJ43DR72E224KWJ1# |  |
|        | 250Vdc        | X7R     | 0.33μF  | ±10% | GRJ43DR72E334KWJ1# |  |
|        |               |         | 0.47μF  | ±10% | GRJ43DR72E474KWJ1# |  |

### ■ 5.7×5.0mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 2.0mm  | 1000Vdc       | X7R     | 68000pF | ±10% | GRJ55DR73A683KWJ1# |  |
|        |               |         | 0.10μF  | ±10% | GRJ55DR73A104KWJ1# |  |
|        | 630Vdc        | X7R     | 0.15μF  | ±10% | GRJ55DR72J154KWJ1# |  |
|        |               |         | 0.22μF  | ±10% | GRJ55DR72J224KWJ1# |  |
|        | 250Vdc        | X7R     | 0.33μF  | ±10% | GRJ55DR72E334KWJ1# |  |
|        |               |         | 0.47μF  | ±10% | GRJ55DR72E474KWJ1# |  |
|        |               |         | 0.68μF  | ±10% | GRJ55DR72E684KWJ1# |  |
|        |               |         | 1.0μF   | ±10% | GRJ55DR72E105KWJ1# |  |

Part number # indicates the package specification code.

## High Effective Capacitance & High Allowable Ripple Current


# GR3 Series **Anti-noise**

This is a general purpose high ripple resistance product excellent in DC bias characteristics.

### Features


- ① When a DC bias is applied, a capacitance higher than conventional products (X7R characteristics) can be acquired.

About twice the capacitance can be secured when DC200V is applied.




- ② Improved ripple resistance performance compared to conventional products (X7R characteristics).

In the case of a product with a capacitance of 1μF, when the exothermic temperature reaches 20°C at frequency f=300kHz, the amount of resistance of a product with conventional material is 2.9Ar.m.s.; however, the new material is 4.7Ar.m.s..




- ③ This product has a noise reduction effect.

Since dielectric materials which enable a reduction of noise are used, this product is more effective for reducing noise compared to the general purpose GRM series.



### Specifications

|                   |                                                                                                      |
|-------------------|------------------------------------------------------------------------------------------------------|
| Size              | 2.0×1.25mm to 5.7×5.0mm                                                                              |
| Rated Voltage     | DC250V to 630V                                                                                       |
| Capacitance       | 0.01μF to 1.0μF                                                                                      |
| Main Applications | For PFC (Power Factor Correction) Circuits of Power Supplies, EMI Suppression and Smoothing Circuits |



This catalog contains only a portion of the product lineup.  
Please refer to the capacitor search tool on the Murata Web site for details.

# GR3 Series High Dielectric Constant Type Anti-noise Part Number List

## ■ 2.0×1.25mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 1.0mm  | 250Vdc        | X7T     | 10000pF | ±10% | GR321AD72E103KW01# |  |
|        |               |         | 15000pF | ±10% | GR321AD72E153KW01# |  |
| 1.45mm | 250Vdc        | X7T     | 22000pF | ±10% | GR321BD72E223KW03# |  |

## ■ 3.2×1.6mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 1.0mm  | 450Vdc        | X7T     | 10000pF | ±10% | GR331AD72W103KW01# |  |
|        |               |         | 15000pF | ±10% | GR331AD72W153KW01# |  |
|        | 250Vdc        | X7T     | 33000pF | ±10% | GR331AD72E333KW01# |  |
| 1.25mm | 630Vdc        | X7T     | 10000pF | ±10% | GR331BD72J103KW01# |  |
|        | 450Vdc        | X7T     | 22000pF | ±10% | GR331BD72W223KW01# |  |
|        |               |         | 33000pF | ±10% | GR331BD72W333KW01# |  |
|        | 250Vdc        | X7T     | 47000pF | ±10% | GR331BD72E473KW01# |  |
| 1.8mm  | 630Vdc        | X7T     | 15000pF | ±10% | GR331CD72J153KW03# |  |
|        | 450Vdc        | X7T     | 47000pF | ±10% | GR331CD72W473KW03# |  |
|        | 250Vdc        | X7T     | 68000pF | ±10% | GR331CD72E683KW03# |  |

## ■ 3.2×2.5mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 1.5mm  | 630Vdc        | X7T     | 22000pF | ±10% | GR332QD72J223KW01# |  |
|        | 250Vdc        | X7T     | 0.10μF  | ±10% | GR332QD72E104KW01# |  |
| 2.0mm  | 630Vdc        | X7T     | 33000pF | ±10% | GR332DD72J333KW01# |  |
|        |               |         | 47000pF | ±10% | GR332DD72J473KW01# |  |
|        | 450Vdc        | X7T     | 68000pF | ±10% | GR332DD72W683KW01# |  |
|        |               |         | 0.10μF  | ±10% | GR332DD72W104KW01# |  |
|        | 250Vdc        | X7T     | 0.15μF  | ±10% | GR332DD72E154KW01# |  |

## ■ 4.5×3.2mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 1.5mm  | 250Vdc        | X7T     | 0.22μF  | ±10% | GR343QD72E224KW01# |  |
| 2.0mm  | 630Vdc        | X7T     | 68000pF | ±10% | GR343DD72J683KW01# |  |
|        | 450Vdc        | X7T     | 0.15μF  | ±10% | GR343DD72W154KW01# |  |
|        | 250Vdc        | X7T     | 0.33μF  | ±10% | GR343DD72E334KW01# |  |

## ■ 5.7×5.0mm

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |  |
|--------|---------------|---------|--------|------|--------------------|--|
| 2.0mm  | 630Vdc        | X7T     | 0.10μF | ±10% | GR355DD72J104KW01# |  |
|        |               |         | 0.15μF | ±10% | GR355DD72J154KW01# |  |
|        | 450Vdc        | X7T     | 0.22μF | ±10% | GR355DD72W224KW01# |  |
|        |               |         | 0.33μF | ±10% | GR355DD72W334KW01# |  |
|        |               |         | 0.47μF | ±10% | GR355DD72W474KW01# |  |
|        | 250Vdc        | X7T     | 0.47μF | ±10% | GR355DD72E474KW01# |  |
|        |               |         | 0.68μF | ±10% | GR355DD72E684KW01# |  |
| 2.7mm  | 630Vdc        | X7T     | 0.22μF | ±10% | GR355XD72J224KW05# |  |

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |  |
|--------|---------------|---------|--------|------|--------------------|--|
| 2.7mm  | 630Vdc        | X7T     | 0.27μF | ±10% | GR355XD72J274KW05# |  |
|        | 450Vdc        | X7T     | 0.56μF | ±10% | GR355XD72W564KW05# |  |
|        | 250Vdc        | X7T     | 1.0μF  | ±10% | GR355XD72E105KW05# |  |

Part number # indicates the package specification code.



## Metal Terminal Type For General Purpose

# KRM Series



Anti-noise

Deflecting crack


Soldering crack

**Bonding the metal terminals to external electrodes solves design issues by mounting large size MLCC!**

## Features

### ① Bond metal terminals to the external electrodes of chips.

The stress applied to the chip is relieved by the elastic action of the metal terminal.




### ② Substantially reduces noise, board deflection cracks and soldering cracks.


This product is not damaged even with a board deflection of 6 mm.

Solder cracks do not occur even with 2,000 cycles of heat stress.

#### ● Acoustic Noise is Reduced with Metal Terminals



#### ● Reduces Stress Caused by Board Deflection



No damage, even with 6 mm board deflection!!

#### ● Suppresses Solder Cracks Caused by Heat Stress

| Chip Size  | Chip Only<br>(5750 (in mm)/2220 (in inch) size) |  | Metal Terminal Type<br>(5750 (in mm)/2220 (in inch) size) |  |
|------------|-------------------------------------------------|--|-----------------------------------------------------------|--|
| 1000 Cycle |                                                 |  |                                                           |  |
| 2000 Cycle |                                                 |  |                                                           |  |

Compared with chips only, this product is excellent in solder cracking resistance.

Test Condition: -55 to +125°C, 5min., (Tank)  
Board Used: Glass Epoxy Board (FR-4)

Demonstrates replacement value of low noise capacitors Experience the effectiveness of the KRM Series.

▶ Examples of Noise Countermeasures

GRM Series

GJM Series

GMA Series

GMD Series

GQM Series

GRJ Series

GR3 Series

KRM Series

KR3 Series

LLA Series

LLL Series

LLM Series

LLR Series

⚠Caution/  
 Notice


### ③ 2 chips can be stacked.

Realize large capacity by stacking 2 capacitors.

## Specifications

|                   |                                                         |
|-------------------|---------------------------------------------------------|
| Size              | 2.2×1.25mm to 6.1×5.3mm                                 |
| Rated Voltage     | DC16V to 1kV                                            |
| Capacitance       | 0.068μF to 47μF                                         |
| Main Applications | For smoothing and noise suppression of DC-DC converters |

This catalog contains only a portion of the product lineup.  
 Please refer to the capacitor search tool on the Murata Web site for details.



<Dimensions>

# KRM Series High Dielectric Constant Type Anti-noise Deflecting crack Soldering crack Part Number List

## ■ 2.2×1.25mm

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number        |  |
|--------|---------------|---------|------|------|--------------------|--|
| 1.9mm  | 25Vdc         | X5R     | 10μF | ±10% | KRM21ER61E106KHA1# |  |
|        | 16Vdc         | X5R     | 10μF | ±10% | KRM21ER61C106KHA1# |  |

## ■ 3.5×1.7mm

| T max. | Rated Voltage | TC Code | Cap.  | Tol. | Part Number        |  |
|--------|---------------|---------|-------|------|--------------------|--|
| 2.0mm  | 25Vdc         | X5R     | 10μF  | ±10% | KRM31FR61E106KH01# |  |
| 2.9mm  | 100Vdc        | X7R     | 1.0μF | ±10% | KRM31KR72A105KH01# |  |
|        | 50Vdc         | X7R     | 4.7μF | ±10% | KRM31KR71H475KH01# |  |
|        | 35Vdc         | X6S     | 10μF  | ±10% | KRM31KC8YA106KH01# |  |
|        | 25Vdc         | X6S     | 10μF  | ±10% | KRM31KC81E106KH01# |  |

## ■ 3.6×1.7mm

| T max. | Rated Voltage | TC Code | Cap.  | Tol. | Part Number        |  |
|--------|---------------|---------|-------|------|--------------------|--|
| 2.9mm  | 50Vdc         | X7R     | 2.2μF | ±10% | KRM31KR71H225KH01# |  |

## ■ 3.7×1.85mm

| T max. | Rated Voltage | TC Code | Cap.  | Tol. | Part Number        |  |
|--------|---------------|---------|-------|------|--------------------|--|
| 2.9mm  | 100Vdc        | X7R     | 2.2μF | ±10% | KRM31KR72A225KH01# |  |

## ■ 6.1×5.3mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 3.0mm  | 1000Vdc       | X7R     | 68000pF | ±10% | KRM55LR73A683KH01# |  |
|        |               |         | 0.10μF  | ±10% | KRM55LR73A104KH01# |  |
|        | 630Vdc        | X7R     | 0.15μF  | ±10% | KRM55LR72J154KH01# |  |
|        |               |         | 0.22μF  | ±10% | KRM55LR72J224KH01# |  |
|        | 250Vdc        | X7R     | 0.68μF  | ±10% | KRM55LR72E684KH01# |  |
|        |               |         | 1.0μF   | ±10% | KRM55LR72E105KH01# |  |
|        | 100Vdc        | X7R     | 4.7μF   | ±10% | KRM55LR72A475KH01# |  |
|        | 63Vdc         | X7R     | 4.7μF   | ±10% | KRM55LR71J475KH01# |  |
|        | 50Vdc         | X7R     | 4.7μF   | ±10% | KRM55LR71H475KH01# |  |
|        | 35Vdc         | X7R     | 10μF    | ±10% | KRM55LR7YA106KH01# |  |
| 3.9mm  | 25Vdc         | X7R     | 15μF    | ±10% | KRM55LR71E156KH01# |  |
|        | 100Vdc        | X7R     | 6.8μF   | ±10% | KRM55QR72A685KH01# |  |
|        | 63Vdc         | X7R     | 10μF    | ±10% | KRM55QR71J106KH01# |  |
|        | 50Vdc         | X7R     | 10μF    | ±10% | KRM55QR71H106KH01# |  |
|        | 35Vdc         | X7R     | 17μF    | ±10% | KRM55QR7YA176KH01# |  |
| 5.0mm  | 25Vdc         | X7R     | 22μF    | ±10% | KRM55QR71E226KH01# |  |
|        | 1000Vdc       | X7R     | 0.15μF  | ±20% | KRM55TR73A154MH01# |  |
|        |               |         | 0.22μF  | ±20% | KRM55TR73A224MH01# |  |
|        | 630Vdc        | X7R     | 0.33μF  | ±20% | KRM55TR72J334MH01# |  |
|        |               |         | 0.47μF  | ±20% | KRM55TR72J474MH01# |  |
|        | 250Vdc        | X7R     | 1.5μF   | ±20% | KRM55TR72E155MH01# |  |
|        |               |         | 2.2μF   | ±20% | KRM55TR72E225MH01# |  |
|        | 100Vdc        | X7R     | 10μF    | ±20% | KRM55TR72A106MH01# |  |

| T max. | Rated Voltage | TC Code | Cap. | Tol. | Part Number        |  |
|--------|---------------|---------|------|------|--------------------|--|
| 5.0mm  | 35Vdc         | X7R     | 22μF | ±20% | KRM55TR7YA226MH01# |  |
|        | 25Vdc         | X7R     | 33μF | ±20% | KRM55TR71E336MH01# |  |
| 6.7mm  | 100Vdc        | X7R     | 15μF | ±20% | KRM55WR72A156MH01# |  |
|        | 63Vdc         | X7R     | 22μF | ±20% | KRM55WR71J226MH01# |  |
|        | 50Vdc         | X7R     | 22μF | ±20% | KRM55WR71H226MH01# |  |
|        | 35Vdc         | X7R     | 33μF | ±20% | KRM55WR7YA336MH01# |  |
|        | 25Vdc         | X7R     | 47μF | ±20% | KRM55WR71E476MH01# |  |

Part number # indicates the package specification code.

## Metal Terminal Type High Effective Capacitance & High Allowable Ripple Current

# KR3 Series



Anti-noise

Deflecting crack


Soldering crack

**Bonding the metal terminals to external electrodes solves design issues by mounting large size MLCC!**

### Features

#### ① Bond metal terminals to the external electrodes of chips.

The stress applied to the chip is relieved by the elastic action of the metal terminal.




#### ② Substantially reduces noise, board deflection cracks and soldering cracks.

This product is not damaged even with a board deflection of 6 mm.

Solder cracks do not occur even with 2,000 cycles of heat stress.


##### ● Comparison of Noise Reduction Effects



Evaluation Items: 5750 (in mm)/2220 (in inch) size/DC630V/220nF  
Test Method: DC50V, AC10Vp-p/3kHz  
Test Board: Glass Epoxy Board (T: 1.6mm)  
Test Quantity: 3pc  
Distance Between Microphone and Board: 3mm

Note: Results Using Murata's Evaluation Board

##### ● Reduces Stress Caused by Board Deflection



No damage, even with 6 mm board deflection!!

##### ● Suppresses Solder Cracks Caused by Heat Stress


| Chip Size  | Chip Only<br>(5750 (in mm)/2220 (in inch) size) |  | Metal Terminal Type<br>(5750 (in mm)/2220 (in inch) size) |  |
|------------|-------------------------------------------------|--|-----------------------------------------------------------|--|
| 1000 Cycle |                                                 |  |                                                           |  |
| 2000 Cycle |                                                 |  |                                                           |  |

Compared with chips only, this product is excellent in solder cracking resistance.

Test Condition: -55 to +125°C, 5min.,(Tank)  
Board Used: Glass Epoxy Board (FR-4)

### ③ Adopted Low Dielectric Constant Materials


Improved effective capacity and ripple resistant performance, compared to conventional products (X7R characteristics).



### Specifications

|                   |                                                      |
|-------------------|------------------------------------------------------|
| Size              | 6.1×5.3mm                                            |
| Rated Voltage     | DC250V to 630V                                       |
| Capacitance       | 0.1μF to 2.2μF                                       |
| Main Applications | For DC-DC converters of general electronic equipment |

This catalog contains only a portion of the product lineup.  
 Please refer to the capacitor search tool on the Murata Web site for details.





# KR3 Series High Dielectric Constant Type Anti-noise Deflecting crack Soldering crack Part Number List

## ■ 6.1×5.3mm

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |  |
|--------|---------------|---------|--------|------|--------------------|--|
| 3.0mm  | 630Vdc        | X7T     | 0.10μF | ±10% | KR355LD72J104KH01# |  |
|        |               |         | 0.15μF | ±10% | KR355LD72J154KH01# |  |
|        | 450Vdc        | X7T     | 0.22μF | ±10% | KR355LD72W224KH01# |  |
|        |               |         | 0.33μF | ±10% | KR355LD72W334KH01# |  |
|        |               |         | 0.47μF | ±10% | KR355LD72W474KH01# |  |
|        | 250Vdc        | X7T     | 0.47μF | ±10% | KR355LD72E474KH01# |  |
|        |               |         | 0.68μF | ±10% | KR355LD72E684KH01# |  |
| 3.9mm  | 630Vdc        | X7T     | 0.22μF | ±10% | KR355QD72J224KH01# |  |
|        |               |         | 0.27μF | ±10% | KR355QD72J274KH01# |  |
|        | 450Vdc        | X7T     | 0.56μF | ±10% | KR355QD72W564KH01# |  |
|        | 250Vdc        | X7T     | 1.0μF  | ±10% | KR355QD72E105KH01# |  |
| 5.0mm  | 450Vdc        | X7T     | 0.68μF | ±20% | KR355TD72W684MH01# |  |
|        |               |         | 1.0μF  | ±20% | KR355TD72W105MH01# |  |
|        | 250Vdc        | X7T     | 1.5μF  | ±20% | KR355TD72E155MH01# |  |
| 6.7mm  | 630Vdc        | X7T     | 0.47μF | ±20% | KR355WD72J474MH01# |  |
|        |               |         | 0.56μF | ±20% | KR355WD72J564MH01# |  |
|        | 450Vdc        | X7T     | 1.2μF  | ±20% | KR355WD72W125MH01# |  |
|        | 250Vdc        | X7T     | 2.2μF  | ±20% | KR355WD72E225MH01# |  |

Part number # indicates the package specification code.

## 8-Terminal Low ESL Type

# LLA Series





Low  
ESL

## 8-Terminal Type Low ESL Capacitor Ideal for Power Supply Decoupling of High-speed Operation IC


### Features

#### ① Ultra-low ESL

Since the equivalent series inductance (ESL) is very low with excellent high frequency characteristics due to the design structure, this capacitor is ideal for power supply decoupling of high-speed operation IC.



<Effectiveness of Cancelling Out Inductance by Mutual Inductance>



<Effectiveness of Suppressing Inductance when Mounting a Multi-terminal Capacitor>


The inductance for the boards also becomes lower, not only the capacitor.

#### ② A maximum operating temperature up to 125°C.

This product is applicable to high temperatures (X7\* characteristics); however, Murata also offers numerous thin type products, which are ideal as decoupling capacitors on IC package.

### Specifications

|                   |                               |
|-------------------|-------------------------------|
| Size              | 1.6×0.8mm to 3.2×1.6mm        |
| Rated Voltage     | DC4V to 25V                   |
| Capacitance       | 0.01μF to 4.7μF               |
| Main Applications | Application processor/CPU/GPU |



This catalog contains only a portion of the product lineup.  
Please refer to the capacitor search tool on the Murata Web site for details.

# LLA Series High Dielectric Constant Type Low ESL Part Number List

## ■ 1.6×0.8mm

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |  |
|--------|---------------|---------|--------|------|--------------------|--|
| 0.55mm | 4Vdc          | X7S     | 0.10μF | ±20% | LLA185C70G104MA01# |  |
|        |               |         | 0.22μF | ±20% | LLA185C70G224MA01# |  |
|        |               |         | 0.47μF | ±20% | LLA185C70G474MA01# |  |
|        |               |         | 2.2μF  | ±20% | LLA185C70G225ME16# |  |

## ■ 2.0×1.25mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.55mm | 25Vdc         | X7R     | 10000pF | ±20% | LLA215R71E103MA14# |  |
|        |               |         | 22000pF | ±20% | LLA215R71E223MA14# |  |
|        | 16Vdc         | X7R     | 47000pF | ±20% | LLA215R71C473MA14# |  |
|        |               |         | 0.10μF  | ±20% | LLA215R71C104MA14# |  |
|        | 10Vdc         | X7R     | 0.22μF  | ±20% | LLA215R71A224MA14# |  |
|        | 6.3Vdc        | X7R     | 0.47μF  | ±20% | LLA215R70J474MA14# |  |
|        | 4Vdc          | X7S     | 1.0μF   | ±20% | LLA215C70G105MA14# |  |
|        |               |         | 4.7μF   | ±20% | LLA215C70G475ME19# |  |
| 0.95mm | 25Vdc         | X7R     | 10000pF | ±20% | LLA219R71E103MA01# |  |
|        |               |         | 22000pF | ±20% | LLA219R71E223MA01# |  |
|        |               |         | 47000pF | ±20% | LLA219R71E473MA01# |  |
|        | 16Vdc         | X7R     | 0.10μF  | ±20% | LLA219R71C104MA01# |  |
|        |               |         | 0.22μF  | ±20% | LLA219R71C224MA01# |  |
|        | 10Vdc         | X7R     | 0.47μF  | ±20% | LLA219R71A474MA01# |  |
|        | 6.3Vdc        | X7R     | 1.0μF   | ±20% | LLA219R70J105MA01# |  |
|        | 4Vdc          | X7S     | 2.2μF   | ±20% | LLA219C70G225MA01# |  |

## ■ 3.2×1.6mm

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |  |
|--------|---------------|---------|--------|------|--------------------|--|
| 0.55mm | 16Vdc         | X7R     | 0.22μF | ±20% | LLA315R71C224MA14# |  |
|        | 10Vdc         | X7R     | 0.47μF | ±20% | LLA315R71A474MA14# |  |
|        | 6.3Vdc        | X7R     | 1.0μF  | ±20% | LLA315R70J105MA14# |  |
|        |               |         | 2.2μF  | ±20% | LLA315R70J225MA14# |  |
| 0.95mm | 16Vdc         | X7R     | 0.47μF | ±20% | LLA319R71C474MA01# |  |
|        | 10Vdc         | X7R     | 1.0μF  | ±20% | LLA319R71A105MA01# |  |
| 1.25mm | 16Vdc         | X7R     | 1.0μF  | ±20% | LLA31MR71C105MA01# |  |
|        | 10Vdc         | X7R     | 2.2μF  | ±20% | LLA31MR71A225MA01# |  |

## LW Reversed Low ESL Type

# LLL Series




Low  
ESL

This low ESL capacitor is ideal for power supply decoupling of high-speed operation electronic equipment.

## Features

### ① Low ESL

Since the equivalent series inductance (ESL) is low and excellent in high frequency characteristics, this capacitor is suitable for power supply decoupling of high-speed operation electronic equipment.




### ② Contributes to a reduction in the number of components.

The number of components can be reduced by using low ESL capacitors, while maintaining functions equivalent to general purpose capacitors (GRM Series).

Murata proposes the use of the LLL series to reduce the number of components and high costs. Simulation is also possible.

Proposal for Cost Reductions




### ③ A maximum operating temperature up to 125°C.

We also offer an abundant lineup of X7\* characteristics that can be used in high temperature locations, such as IC packages.

## Specifications

|                   |                               |
|-------------------|-------------------------------|
| Size              | 0.5×1.0mm to 1.6×3.2mm        |
| Rated Voltage     | DC2.5V to 50V                 |
| Capacitance       | 2,200pF to 10μF               |
| Main Applications | Application processor/CPU/GPU |



This catalog contains only a portion of the product lineup.  
Please refer to the capacitor search tool on the Murata Web site for details.

# GRM Series GJM Series GMA Series GMD Series GQM Series GRJ Series GR3 Series KRM Series KR3 Series LLA Series LLL Series LLM Series LLR Series ⚠Caution/ Notice Low ESL LLL Series High Dielectric Constant Type Part Number List

## 0.5×1.0mm

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |  |
|--------|---------------|---------|--------|------|--------------------|--|
| 0.35mm | 6.3Vdc        | X6S     | 0.10μF | ±20% | LLL153C80J104ME01# |  |
|        |               |         | 0.22μF | ±20% | LLL153C80J224ME14# |  |
|        | 4Vdc          | X7S     | 0.47μF | ±20% | LLL153C70G474ME17# |  |
|        |               | X6S     | 1.0μF  | ±20% | LLL153C80G105ME21# |  |

## 0.6×1.0mm

| T max. | Rated Voltage | TC Code | Cap.  | Tol. | Part Number        |  |
|--------|---------------|---------|-------|------|--------------------|--|
| 0.45mm | 4Vdc          | X5R     | 4.3μF | ±20% | LLL1U4R60G435ME22# |  |

## 0.8×1.6mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.5mm  | 25Vdc         | X7R     | 10000pF | ±20% | LLL185R71E103MA11# |  |
|        | 16Vdc         | X7R     | 22000pF | ±20% | LLL185R71C223MA11# |  |
|        |               |         | 47000pF | ±20% | LLL185R71C473MA11# |  |
|        | 10Vdc         | X7R     | 0.10μF  | ±20% | LLL185R71A104MA11# |  |
|        | 4Vdc          | X7S     | 0.22μF  | ±20% | LLL185C70G224MA11# |  |
| 0.55mm | 4Vdc          | X7S     | 2.2μF   | ±20% | LLL185C70G225ME01# |  |
| 0.6mm  | 50Vdc         | X7R     | 2200pF  | ±20% | LLL185R71H222MA01# |  |
|        |               |         | 4700pF  | ±20% | LLL185R71H472MA01# |  |
|        | 25Vdc         | X7R     | 10000pF | ±20% | LLL185R71E103MA01# |  |
|        |               |         | 22000pF | ±20% | LLL185R71E223MA01# |  |
|        | 16Vdc         | X7R     | 47000pF | ±20% | LLL185R71C473MA01# |  |
|        | 10Vdc         | X7R     | 0.10μF  | ±20% | LLL185R71A104MA01# |  |
|        |               |         | 0.22μF  | ±20% | LLL185R71A224MA01# |  |
|        | 4Vdc          | X7S     | 0.47μF  | ±20% | LLL185C70G474MA01# |  |

## 1.25×2.0mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.5mm  | 50Vdc         | X7R     | 10000pF | ±20% | LLL215R71H103MA11# |  |
|        | 25Vdc         | X7R     | 22000pF | ±20% | LLL215R71E223MA11# |  |
|        | 16Vdc         | X7R     | 47000pF | ±20% | LLL215R71C473MA11# |  |
|        |               |         | 0.10μF  | ±20% | LLL215R71C104MA11# |  |
|        | 10Vdc         | X7R     | 0.22μF  | ±20% | LLL215R71A224MA11# |  |
|        | 6.3Vdc        | X7R     | 0.47μF  | ±20% | LLL215R70J474MA11# |  |
|        | 4Vdc          | X7S     | 1.0μF   | ±20% | LLL215C70G105MA11# |  |
| 0.7mm  | 50Vdc         | X7R     | 10000pF | ±20% | LLL216R71H103MA01# |  |
|        |               |         | 22000pF | ±20% | LLL216R71H223MA01# |  |
|        | 25Vdc         | X7R     | 47000pF | ±20% | LLL216R71E473MA01# |  |
|        |               |         | 0.10μF  | ±20% | LLL216R71E104MA01# |  |
|        | 10Vdc         | X7R     | 0.22μF  | ±20% | LLL216R71A224MA01# |  |
| 0.95mm | 16Vdc         | X7R     | 0.22μF  | ±20% | LLL219R71C224MA01# |  |
|        | 10Vdc         | X7R     | 0.47μF  | ±20% | LLL219R71A474MA01# |  |
|        |               |         | 1.0μF   | ±20% | LLL219R71A105MA01# |  |
|        | 4Vdc          | X7S     | 2.2μF   | ±20% | LLL219C70G225MA01# |  |

## 1.6×3.2mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol.   | Part Number        |                    |
|--------|---------------|---------|---------|--------|--------------------|--------------------|
| 0.5mm  | 50Vdc         | X7R     | 10000pF | ±20%   | LLL315R71H103MA11# |                    |
|        |               |         | 22000pF | ±20%   | LLL315R71H223MA11# |                    |
|        | 25Vdc         | X7R     | 47000pF | ±20%   | LLL315R71E473MA11# |                    |
|        |               |         | 0.10μF  | ±20%   | LLL315R71E104MA11# |                    |
|        | 16Vdc         | X7R     | 0.22μF  | ±20%   | LLL315R71C224MA11# |                    |
|        | 10Vdc         | X7R     | 0.47μF  | ±20%   | LLL315R71A474MA11# |                    |
| 0.8mm  | 50Vdc         | X7R     | 10000pF | ±20%   | LLL317R71H103MA01# |                    |
|        |               |         | 22000pF | ±20%   | LLL317R71H223MA01# |                    |
|        |               |         | 47000pF | ±20%   | LLL317R71H473MA01# |                    |
|        | 25Vdc         | X7R     | 0.10μF  | ±20%   | LLL317R71E104MA01# |                    |
|        | 16Vdc         | X7R     | 0.22μF  | ±20%   | LLL317R71C224MA01# |                    |
|        |               |         | 0.47μF  | ±20%   | LLL317R71C474MA01# |                    |
|        | 10Vdc         | X7R     | 1.0μF   | ±20%   | LLL317R71A105MA01# |                    |
|        | 6.3Vdc        | X7R     | 2.2μF   | ±20%   | LLL317R70J225MA01# |                    |
|        | 1.25mm        | 50Vdc   | X7R     | 0.10μF | ±20%               | LLL31MR71H104MA01# |
| ±20%   |               |         |         |        | LLL31MR71E224MA01# |                    |
| ±20%   |               |         |         |        | LLL31MR71E474MA01# |                    |
| 16Vdc  |               | X7R     | 1.0μF   | ±20%   | LLL31MR71C105MA01# |                    |
| 10Vdc  |               | X7R     | 2.2μF   | ±20%   | LLL31MR71A225MA01# |                    |
| 6.3Vdc |               | X7R     | 4.7μF   | ±20%   | LLL31MR70J475MA01# |                    |
|        | X5R           |         | 10μF    | ±20%   | LLL31MR60J106ME01# |                    |



## 10-Terminal Low ESL Type

# LLM Series





Low  
ESL

## 10-Terminal Type Low ESL Capacitor Ideal for Power Supply Decoupling of High-speed Operation IC


### Features

#### ① This is the lowest ESL LW reversed type capacitor.

Since the equivalent series inductance (ESL) of this product is even lower than the LLA series (8-terminal product) with excellent high frequency characteristics, this capacitor is ideal for power supply decoupling of high-speed operation IC.



<Effectiveness of Cancelling Out Inductance by Mutual Inductance>



<Effectiveness of Suppressing Inductance when Mounting a Multi-terminal Capacitor>


**The inductance for the boards also becomes lower, not only the capacitor.**

#### ② A maximum operating temperature up to 125°C.

This product is applicable to high temperatures (X7\* characteristics); however, Murata also offers numerous thin type products, which are ideal as decoupling capacitors on IC package.

### Specifications

|                   |                               |
|-------------------|-------------------------------|
| Size              | 2.0×1.25mm to 3.2×1.6mm       |
| Rated Voltage     | DC4V to 25V                   |
| Capacitance       | 0.01μF to 2.2μF               |
| Main Applications | Application processor/CPU/GPU |



<Dimensions>

This catalog contains only a portion of the product lineup.  
Please refer to the capacitor search tool on the Murata Web site for details.

# LLM Series High Dielectric Constant Type Low ESL Part Number List

## ■ 2.0×1.25mm

| T max. | Rated Voltage | TC Code | Cap.    | Tol. | Part Number        |  |
|--------|---------------|---------|---------|------|--------------------|--|
| 0.55mm | 25Vdc         | X7R     | 10000pF | ±20% | LLM215R71E103MA11# |  |
|        |               |         | 22000pF | ±20% | LLM215R71E223MA11# |  |
|        | 16Vdc         | X7R     | 47000pF | ±20% | LLM215R71C473MA11# |  |
|        |               |         | 0.10μF  | ±20% | LLM215R71C104MA11# |  |
|        | 6.3Vdc        | X7R     | 0.22μF  | ±20% | LLM215R70J224MA11# |  |
|        |               |         | 0.47μF  | ±20% | LLM215R70J474MA11# |  |
|        | 4Vdc          | X7S     | 1.0μF   | ±20% | LLM215C70G105MA11# |  |

## ■ 3.2×1.6mm

| T max. | Rated Voltage | TC Code | Cap.   | Tol. | Part Number        |  |
|--------|---------------|---------|--------|------|--------------------|--|
| 0.55mm | 16Vdc         | X7R     | 0.10μF | ±20% | LLM315R71C104MA11# |  |
|        |               |         | 0.22μF | ±20% | LLM315R71C224MA11# |  |
|        | 10Vdc         | X7R     | 0.47μF | ±20% | LLM315R71A474MA11# |  |
|        | 6.3Vdc        | X7R     | 2.2μF  | ±20% | LLM315R70J225MA11# |  |

## ESR Controlled Low ESL Type

# LLR Series




Low  
ESL

## ESR Controlled Type Low ESL Capacitors Equipped with Anti-resonance Control Function

### Features

#### ① Reduces Anti-resonance

This capacitor is controlled so that the equivalent series resistance (ESR) becomes slightly higher, and is effective in reducing the anti-resonance that occurs when capacitor arrays are used.



#### ② Lineup of capacitors with ESR values from 100 to 1,000mΩ.


According to the conditions of the anti-resonance, the most suitable ESR value can be selected from 4 types.

#### ③ Low ESL

This ESR controlled type capacitor has excellent high frequency characteristics, with low equivalent series inductance (ESL). This is also ideal as a decoupling component.

### Specifications

|                   |                             |
|-------------------|-----------------------------|
| Size              | 0.8×1.6mm                   |
| Rated Voltage     | DC4V                        |
| Capacitance       | 1.0μF                       |
| Main Applications | Network processor/ASIC/PMIC |



This catalog contains only a portion of the product lineup.  
Please refer to the capacitor search tool on the Murata Web site for details.

GRM Series

GJM Series

GMA Series

GMD Series

GQM Series

GRJ Series

GR3 Series

KRM Series

KR3 Series

LLA Series

LLL Series

LLM Series

LLR Series

⚠Caution/  
Notice

LLR Series High Dielectric Constant Type **Low ESL** Part Number List

■ 0.8×1.6mm

| T<br>max. | Rated<br>Voltage | TC<br>Code | Cap.  | Tol. | ESR    | Part Number        |  |
|-----------|------------------|------------|-------|------|--------|--------------------|--|
| 0.55mm    | 4Vdc             | X7S        | 1.0μF | ±20% | 100mΩ  | LLR185C70G105ME01# |  |
|           |                  |            |       | ±20% | 220mΩ  | LLR185C70G105ME03# |  |
|           |                  |            |       | ±20% | 470mΩ  | LLR185C70G105ME05# |  |
|           |                  |            |       | ±20% | 1000mΩ | LLR185C70G105ME07# |  |

Part number # indicates the package specification code.



## ⚠Caution/Notice

### ⚠Caution

|                                                               |     |
|---------------------------------------------------------------|-----|
| ■ Storage and Operation Conditions .....                      | 138 |
| ■ Rating .....                                                | 138 |
| 1. Temperature Dependent Characteristics .....                | 138 |
| 2. Measurement of Capacitance .....                           | 138 |
| 3. Applied Voltage .....                                      | 139 |
| 4. Type of Applied Voltage and Self-heating Temperature ..... | 139 |
| 5. DC Voltage and AC Voltage Characteristics .....            | 142 |
| 6. Capacitance Aging .....                                    | 142 |
| 7. Vibration and Shock .....                                  | 143 |
| ■ Soldering and Mounting .....                                | 143 |
| 1. Mounting Position .....                                    | 143 |
| 2. Information before Mounting .....                          | 144 |
| 3. Maintenance of the Mounting (pick and place) Machine ..... | 144 |
| 4-1. Reflow Soldering .....                                   | 145 |
| 4-2. Flow Soldering .....                                     | 146 |
| 4-3. Correction of Soldered Portion .....                     | 147 |
| 5. Washing .....                                              | 148 |
| 6. Electrical Test on Printed Circuit Board .....             | 148 |
| 7. Printed Circuit Board Cropping .....                       | 148 |
| 8. Assembly .....                                             | 151 |
| 9. Die Bonding/Wire Bonding .....                             | 152 |
| ■ Other .....                                                 | 152 |
| 1. Under Operation of Equipment .....                         | 152 |
| 2. Other .....                                                | 152 |

### Notice

|                                                          |     |
|----------------------------------------------------------|-----|
| ■ Rating .....                                           | 153 |
| 1. Operating Temperature .....                           | 153 |
| 2. Atmosphere Surroundings .....                         | 153 |
| 3. Piezo-electric Phenomenon .....                       | 153 |
| ■ Soldering and Mounting .....                           | 153 |
| 1. PCB Design .....                                      | 153 |
| 1. Notice for Pattern Forms .....                        | 153 |
| 2. Land Dimensions .....                                 | 154 |
| 3. Board Design .....                                    | 155 |
| 2. Adhesive Application .....                            | 156 |
| 3. Adhesive Curing .....                                 | 156 |
| 4. Flux Application .....                                | 156 |
| 5. Flow Soldering .....                                  | 156 |
| 6. Washing .....                                         | 157 |
| 7. Coating .....                                         | 157 |
| ■ Other .....                                            | 157 |
| 1. Transportation .....                                  | 157 |
| 2. Characteristics Evaluation in the Actual System ..... | 157 |

GRM Series

GJM Series

GMA Series

GMD Series

GQM Series

GRJ Series

GR3 Series

KRM Series

KR3 Series

LLA Series

LLL Series

LLM Series

LLR Series

⚠Caution/  
Notice



## ⚠Caution

### ■ Storage and Operation Conditions

1. The performance of chip monolithic ceramic capacitors may be affected by the storage conditions.

1-1. Store the capacitors in the following conditions:

Room Temperature of +5°C to +40°C and  
a Relative Humidity of 20% to 70%.

(1) Sunlight, dust, rapid temperature changes,  
corrosive gas atmosphere, or high temperature  
and humidity conditions during storage may affect  
solderability and packaging performance.

Therefore, please maintain the storage  
temperature and humidity. Use the product within  
six months, as prolonged storage may cause  
oxidation of the electrodes.

(2) Please confirm solderability before using after six  
months. Store the capacitors without opening the  
original bag. Even if the storage period is short, do  
not exceed the specified atmospheric conditions.

1-2. Corrosive gas can react with the termination  
(external) electrodes or lead wires of capacitors, and  
result in poor solderability. Do not store the  
capacitors in an atmosphere consisting of corrosive  
gas (e.g., hydrogen sulfide, sulfur dioxide, chlorine,  
ammonia gas, etc.).

1-3. Due to moisture condensation caused by rapid  
humidity changes, or the photochemical change  
caused by direct sunlight on the terminal electrodes  
and/or the resin/epoxy coatings, the solderability and  
electrical performance may deteriorate. Do not store  
capacitors under direct sunlight or in high humidity  
conditions.

### ■ Rating

#### 1. Temperature Dependent Characteristics

1. The electrical characteristics of a capacitor can change  
with temperature.

1-1. For capacitors having larger temperature  
dependency, the capacitance may change with  
temperature changes.

The following actions are recommended in order to  
ensure suitable capacitance values.


(1) Select a suitable capacitance for the operating  
temperature range.

(2) The capacitance may change within the rated  
temperature.

When you use a high dielectric constant type  
capacitor in a circuit that needs a tight (narrow)  
capacitance tolerance (e.g., a time-constant  
circuit), please carefully consider the temperature  
characteristics, and carefully confirm the various  
characteristics in actual use conditions and the  
actual system.


[Typical Temperature Characteristics X7R]

Sample: 0.1μF, Rated Voltage 50VDC



[Typical Temperature Characteristics X5R]

Sample: 22μF, Rated Voltage 4VDC



#### 2. Measurement of Capacitance

1. Measure capacitance with the voltage and frequency  
specified in the product specifications.

1-1. The output voltage of the measuring equipment may  
decrease occasionally when capacitance is high.  
Please confirm whether a prescribed measured  
voltage is impressed to the capacitor.

1-2. The capacitance values of high dielectric constant  
type capacitors change depending on the AC voltage  
applied. Please consider the AC voltage  
characteristics when selecting a capacitor to be used  
in an AC circuit.





## ⚠Caution

Continued from the preceding page.

### 3. Applied Voltage

1. Do not apply a voltage to the capacitor that exceeds the rated voltage as called out in the specifications.
  - 1-1. Applied voltage between the terminals of a capacitor shall be less than or equal to the rated voltage.
    - (1) When AC voltage is superimposed on DC voltage, the zero-to-peak voltage shall not exceed the rated DC voltage.  
When AC voltage or pulse voltage is applied, the peak-to-peak voltage shall not exceed the rated DC voltage.
    - (2) Abnormal voltages (surge voltage, static electricity, pulse voltage, etc.) shall not exceed the rated DC voltage.

Typical Voltage Applied to the DC Capacitor

| DC Voltage                                                                        | DC Voltage+AC                                                                     | AC Voltage                                                                         | Pulse Voltage                                                                       |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|  |  |  |  |

(E: Maximum possible applied voltage.)


- 1-2. Influence of over voltage  
Over voltage that is applied to the capacitor may result in an electrical short circuit caused by the breakdown of the internal dielectric layers.  
The time duration until breakdown depends on the applied voltage and the ambient temperature.
2. Use a safety standard certified capacitor in a power supply input circuit (AC filter), as it is also necessary to consider the withstand voltage and impulse withstand voltage defined for each device.

### 4. Type of Applied Voltage and Self-heating Temperature

1. Confirm the operating conditions to make sure that no large current is flowing into the capacitor due to the continuous application of an AC voltage or pulse voltage.  
When a DC rated voltage product is used in an AC voltage circuit or a pulse voltage circuit, the AC current or pulse current will flow into the capacitor; therefore check the self-heating condition.  
Please confirm the surface temperature of the capacitor so that the temperature remains within the upper limits of the operating temperature, including the rise in temperature due to self-heating. When the capacitor is used with a high-frequency voltage or pulse voltage, heat may be generated by dielectric loss.  
<Applicable to Rated Voltage of less than 100VDC>
  - 1-1. The load should be contained to the level such that when measuring at atmospheric temperature of 25°C, the product's self-heating remains below 20°C and the surface temperature of the capacitor in the actual circuit remains within the maximum operating temperature.

[Example of Temperature Rise (Heat Generation) in Chip Monolithic Ceramic Capacitors in Contrast to Ripple Current]

Sample: R characteristics 10μF, Rated voltage: DC10V



Continued on the following page. ↗

## ⚠Caution

Continued from the preceding page.


<Applicable to Temperature Characteristic X7R, X7T beyond Rated Voltage of 200VDC>

1-2. The load should be contained so that the self-heating of the capacitor body remains below 20°C, when measuring at an ambient temperature of 25°C. In addition, use a K thermocouple of  $\phi 0.1\text{mm}$  with less heat capacity when measuring, and measure in a condition where there is no effect from the radiant heat of other components or air flow caused by convection. Excessive generation of heat may cause deterioration of the characteristics and reliability of the capacitor. (Absolutely do not perform measurements while the cooling fan is operating, as an accurate measurement may not be performed.)

<Applicable to Temperature Characteristic U2J, C0G beyond Rated Voltage of 200VDC>

1-3. Since the self-heating is low in the low loss series, the allowable power becomes extremely high compared to the common X7R characteristics. However, when a load with self-heating of 20°C is applied at the rated voltage, the allowable power may be exceeded. When the capacitor is used in a high-frequency voltage circuit of 1kHz or more, the frequency of the applied voltage should be less than 500kHz sine wave (less than 100kHz for a product with rated voltage of DC3.15kV), to limit the voltage load so that the load remains within the derating shown in the following figure. In the case of non-sine wave, high-frequency components exceeding the fundamental frequency may be included. In such a case, please contact Murata. The excessive generation of heat may cause deterioration of the characteristics and reliability of the capacitor. (Absolutely do not perform measurements while the cooling fan is operating, as an accurate measurement may not be performed.)

The temperature of the surface of capacitor: 125°C or less (including self-heating)




The sine-wave frequency VS allowable voltage

Continued on the following page. ➤

## ⚠Caution

Continued from the preceding page.

The temperature of the surface  
of capacitor: 125°C or less (including self-heating)



The sine-wave frequency VS allowable voltage

### <Design Tool>

#### • Simsurfing

Simsurfing is a web application to display the characteristics charts and download the characteristics data of our products. The frequency characteristics, temperature characteristics, bias characteristics etc. can be checked.

(Address: <http://www.murata.com/simsurfing/>)

#### • Medium Voltage Ceramic Capacitor Selection Tool

The selection tool "Murata Medium Voltage Capacitors Selection Tool by Voltage Form" is installed in the above SimSurfing, where the usability of the preferred medium voltage ceramic capacitors can be determined according to the application including automobiles.

By using this tool, the preferred products\* can be checked by specifications, such as the power, voltage, and fundamental frequency of the voltage waveform to be input into the capacitor.

#### \*Supported Series

Temperature characteristic U2J, C0G of GRM/DC200V or more

Continued on the following page. ↗

## ⚠Caution

Continued from the preceding page.

### 5. DC Voltage and AC Voltage Characteristics

1. The capacitance value of a high dielectric constant type capacitor changes depending on the DC voltage applied. Please consider the DC voltage characteristics when a capacitor is selected for use in a DC circuit.

1-1. The capacitance of ceramic capacitors may change sharply depending on the applied voltage (see figure).


Please confirm the following in order to secure the capacitance.

- (1) Determine whether the capacitance change caused by the applied voltage is within the allowed range.
- (2) In the DC voltage characteristics, the rate of capacitance change becomes larger as voltage increases, even if the applied voltage is below the rated voltage. When a high dielectric constant type capacitor is used in a circuit that requires a tight (narrow) capacitance tolerance (e.g., a time constant circuit), please carefully consider the voltage characteristics, and confirm the various characteristics in actual operating conditions in an actual system.

2. The capacitance values of high dielectric constant type capacitors changes depending on the AC voltage applied. Please consider the AC voltage characteristics when selecting a capacitor to be used in an AC circuit.


#### [DC Voltage Characteristics]

Sample: X7R Characteristics 0.1 $\mu$ F, Rated Voltage 50VDC



#### [AC Voltage Characteristics]

Sample: X7R Characteristics 10 $\mu$ F, Rated Voltage 6.3VDC




### 6. Capacitance Aging

1. The high dielectric constant type capacitors have the characteristic in which the capacitance value decreases with the passage of time.

When you use high dielectric constant type capacitors in a circuit that needs a tight (narrow) capacitance tolerance (e.g., a time-constant circuit), please carefully consider the characteristics of these capacitors, such as their aging, voltage, and temperature characteristics. In addition, check capacitors using your actual appliances at the intended environment and operating conditions.

#### [Example of Change Over Time (Aging Characteristics)]



Continued on the following page. ➤





## ⚠Caution

Continued from the preceding page.

### 7. Vibration and Shock

- Please confirm the kind of vibration and/or shock, its condition, and any generation of resonance.  
Please mount the capacitor so as not to generate resonance, and do not allow any impact on the terminals.
- Mechanical shock due to being dropped may cause damage or a crack in the dielectric material of the capacitor.  
Do not use a dropped capacitor because the quality and reliability may be deteriorated.
- When printed circuit boards are piled up or handled, the corner of another printed circuit board should not be allowed to hit the capacitor, in order to avoid a crack or other damage to the capacitor.




## ■ Soldering and Mounting

### 1. Mounting Position

- Confirm the best mounting position and direction that minimizes the stress imposed on the capacitor during flexing or bending the printed circuit board.
- 1-1. Choose a mounting position that minimizes the stress imposed on the chip during flexing or bending of the board.

#### [Component Direction]




#### [Chip Mounting Close to Board Separation Point]

It is effective to implement the following measures, to reduce stress in separating the board.


It is best to implement all of the following three measures; however, implement as many measures as possible to reduce stress.

| Contents of Measures                                                                       | Stress Level |
|--------------------------------------------------------------------------------------------|--------------|
| (1) Turn the mounting direction of the component parallel to the board separation surface. | $A > D$      |
| (2) Add slits in the board separation part.                                                | $A > B$      |
| (3) Keep the mounting position of the component away from the board separation surface.    | $A > C$      |



#### [Mounting Capacitors Near Screw Holes]

When a capacitor is mounted near a screw hole, it may be affected by the board deflection that occurs during the tightening of the screw. Mount the capacitor in a position as far away from the screw holes as possible.



Continued on the following page. ↗

## ⚠Caution


☐ Continued from the preceding page.

### 2. Information before Mounting

1. Do not re-use capacitors that were removed from the equipment.
2. Confirm capacitance characteristics under actual applied voltage.
3. Confirm the mechanical stress under actual process and equipment use.
4. Confirm the rated capacitance, rated voltage and other electrical characteristics before assembly.
5. Prior to use, confirm the solderability of capacitors that were in long-term storage.
6. Prior to measuring capacitance, carry out a heat treatment for capacitors that were in long-term storage.
7. The use of Sn-Zn based solder will deteriorate the reliability of the MLCC.  
Please contact our sales representative or product engineers on the use of Sn-Zn based solder in advance.
8. We have also produced a DVD which shows a summary of our opinions, regarding the precautions for mounting.  
Please contact our sales representative to request the DVD.

### 3. Maintenance of the Mounting (pick and place) Machine

1. Make sure that the following excessive forces are not applied to the capacitors.
  - 1-1. In mounting the capacitors on the printed circuit board, any bending force against them shall be kept to a minimum to prevent them from any bending damage or cracking. Please take into account the following precautions and recommendations for use in your process.
    - (1) Adjust the lowest position of the pickup nozzle so as not to bend the printed circuit board.
    - (2) Adjust the nozzle pressure within a static load of 1N to 3N during mounting.
2. Dirt particles and dust accumulated between the suction nozzle and the cylinder inner wall prevent the nozzle from moving smoothly. This imposes greater force upon the chip during mounting, causing cracked chips. Also, the locating claw, when worn out, imposes uneven forces on the chip when positioning, causing cracked chips. The suction nozzle and the locating claw must be maintained, checked, and replaced periodically.



Continued on the following page. ☐

## ⚠Caution

Continued from the preceding page.

### 4-1. Reflow Soldering

- When sudden heat is applied to the components, the mechanical strength of the components will decrease because a sudden temperature change causes deformation inside the components. In order to prevent mechanical damage to the components, preheating is required for both the components and the PCB. Preheating conditions are shown in table 1. It is required to keep the temperature differential between the solder and the components surface ( $\Delta T$ ) as small as possible.
- Solderability of tin plating termination chips might be deteriorated when a low temperature soldering profile where the peak solder temperature is below the melting point of tin is used. Please confirm the solderability of tin plated termination chips before use.
- When components are immersed in solvent after mounting, be sure to maintain the temperature difference ( $\Delta T$ ) between the component and the solvent within the range shown in table 1.

Table 1

| Part Number                                                                   | Temperature Differential          |
|-------------------------------------------------------------------------------|-----------------------------------|
| GJM/GMA/GMD/QQM/GR3/GRJ/GRM/<br>KRM/LLL/LLR Series<br>02/03/15/18/21/31 sizes | $\Delta T \leq 190^\circ\text{C}$ |
| LLL Series 1U size                                                            |                                   |
| GR3/GRJ/GRM/KR3/KRM Series<br>32/43/55 sizes                                  | $\Delta T \leq 130^\circ\text{C}$ |
| LLA/LLM Series 18/21/31 sizes                                                 |                                   |
| QQM Series 22 size                                                            |                                   |

#### Recommended Conditions

|                  | Pb-Sn Solder |                                     | Lead Free Solder      |
|------------------|--------------|-------------------------------------|-----------------------|
|                  | Reflow       | Vapor Reflow                        |                       |
| Peak Temperature | 230 to 250°C | 230 to 240°C                        | 240 to 260°C          |
| Atmosphere       | Air          | Saturated vapor of inactive solvent | Air or N <sub>2</sub> |

Pb-Sn Solder: Sn-37Pb

Lead Free Solder: Sn-3.0Ag-0.5Cu



#### 4. Optimum Solder Amount for Reflow Soldering

- Overly thick application of solder paste results in a excessive solder fillet height. This makes the chip more susceptible to mechanical and thermal stress on the board and may cause the chips to crack.
- Too little solder paste results in a lack of adhesive strength on the outer electrode, which may result in chips breaking loose from the PCB.
- Make sure the solder has been applied smoothly to the end surface to a height of 0.2mm\* min.


#### Inverting the PCB

Make sure not to impose any abnormal mechanical shocks to the PCB.


#### [Standard Conditions for Reflow Soldering]



#### [Allowable Reflow Soldering Temperature and Time]



In the case of repeated soldering, the accumulated soldering time must be within the range shown above.



Continued on the following page. ➡

## ⚠Caution

Continued from the preceding page.

### 4-2. Flow Soldering

- Do not apply flow soldering to chips not listed in table 2.

Table 2

| Part Number                                                                                                                                                             | Temperature Differential            |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------|
| <b>GR3/GRM Series 18/21/31 sizes</b><br><b>GQM Series 18/21 sizes</b><br><b>LLL Series 21/31 sizes</b><br><b>GRJ Series Rated Voltage 250VDC or more 18/21/31 sizes</b> | $\Delta T \leq 150^{\circ}\text{C}$ |

- When sudden heat is applied to the components, the mechanical strength of the components will decrease because a sudden temperature change causes deformation inside the components. In order to prevent mechanical damage to the components, preheating is required for both of the components and the PCB. Preheating conditions are shown in table 2. It is required to keep the temperature differential between the solder and the components surface ( $\Delta T$ ) as low as possible.
- Excessively long soldering time or high soldering temperature can result in leaching of the outer electrodes, causing poor adhesion or a reduction in capacitance value due to loss of contact between the electrodes and end termination.
- When components are immersed in solvent after mounting, be sure to maintain the temperature differential ( $\Delta T$ ) between the component and solvent within the range shown in the table 2.

#### Recommended Conditions

|                             | Pb-Sn Solder | Lead Free Solder |
|-----------------------------|--------------|------------------|
| Preheating Peak Temperature | 90 to 110°C  | 100 to 120°C     |
| Soldering Peak Temperature  | 240 to 250°C | 250 to 260°C     |
| Atmosphere                  | Air          | N <sub>2</sub>   |


Pb-Sn Solder: Sn-37Pb

Lead Free Solder: Sn-3.0Ag-0.5Cu


#### 5. Optimum Solder Amount for Flow Soldering

- The top of the solder fillet should be lower than the thickness of the components. If the solder amount is excessive, the risk of cracking is higher during board bending or any other stressful condition.


#### [Standard Conditions for Flow Soldering]



#### [Allowable Flow Soldering Temperature and Time]



In the case of repeated soldering, the accumulated soldering time must be within the range shown above.



Continued on the following page. ↗

## ⚠Caution

☐ Continued from the preceding page.

### 4-3. Correction of Soldered Portion

When sudden heat is applied to the capacitor, distortion caused by the large temperature difference occurs internally, and can be the cause of cracks. Capacitors also tend to be affected by mechanical and thermal stress depending on the board preheating temperature or the soldering fillet shape, and can be the cause of cracks. Please refer to "1. PCB Design" or "3. Optimum solder amount" for the solder amount and the fillet shapes.

#### 1. Correction with a Soldering Iron

- 1-1. In order to reduce damage to the capacitor, be sure to preheat the capacitor and the mounting board. Preheat to the temperature range shown in Table 3. A hot plate, hot air type preheater, etc. can be used for preheating.
- 1-2. After soldering, do not allow the component/PCB to cool down rapidly.
- 1-3. Perform the corrections with a soldering iron as quickly as possible. If the soldering iron is applied too long, there is a possibility of causing solder leaching on the terminal electrodes, which will cause deterioration of the adhesive strength and other problems.

#### 2. Correction with Spot Heater

Compared to local heating with a soldering iron, hot air heating by a spot heater heats the overall component and board, therefore, it tends to lessen the thermal shock. In the case of a high density mounted board, a spot heater can also prevent concerns of the soldering iron making direct contact with the component.

- 2-1. If the distance from the hot air outlet of the spot heater to the component is too close, cracks may occur due to thermal shock. To prevent this problem, follow the conditions shown in Table 4.

- 2-2. In order to create an appropriate solder fillet shape, it is recommended that hot air be applied at the angle shown in Figure 1.

#### 3. Optimum solder amount when re-working with a soldering iron

- 3-1. In the case of sizes smaller than 0603, (GJM/GQM/GR3/GRJ/GRM Series, 03/15/18 sizes), the top of the solder fillet should be lower than  $\frac{2}{3}$  of the thickness of the component or 0.5mm, whichever is smaller. In the case of 0805 and larger sizes, (GJM/GQM/GR3/GRJ/GRM Series, 21/22/31/32/43/55 sizes), the top of the solder fillet should be lower than  $\frac{2}{3}$  of the thickness of the component. If the solder amount is excessive, the risk of cracking is higher during board bending or under any other stressful condition.

Table 3



| Part Number                                               | Temperature of Soldering Iron Tip | Preheating Temperature | Temperature Differential ( $\Delta T$ ) | Atmosphere |
|-----------------------------------------------------------|-----------------------------------|------------------------|-----------------------------------------|------------|
| GJM/GQM/GR3/GRJ/GRM Series<br>03/15/18/21/31 sizes        | 350°C max.                        | 150°C min.             | $\Delta T \leq 190^\circ\text{C}$       | Air        |
| GRJ/GRM Series<br>32/43/55 sizes<br>GQM Series<br>22 size | 280°C max.                        | 150°C min.             | $\Delta T \leq 130^\circ\text{C}$       | Air        |

\*Applicable for both Pb-Sn and Lead Free Solder.  
Pb-Sn Solder: Sn-37Pb  
Lead Free Solder: Sn-3.0Ag-0.5Cu

Table 4

|                                   |                                                             |
|-----------------------------------|-------------------------------------------------------------|
| Distance                          | 5mm or more                                                 |
| Hot Air Application angle         | 45° *Figure 1                                               |
| Hot Air Temperature Nozzle Outlet | 400°C max.                                                  |
| Application Time                  | Less than 10 seconds<br>(1206 (3216 in mm) size or smaller) |
|                                   | Less than 30 seconds<br>(1210 (3225 in mm) size or larger)  |

[Figure 1]



Continued on the following page. ☐



## ⚠Caution

Continued from the preceding page.

3-2. A soldering iron with a tip of  $\phi 3\text{mm}$  or smaller should be used. It is also necessary to keep the soldering iron from touching the components during the re-work.

3-3. Solder wire with  $\phi 0.5\text{mm}$  or smaller is required for soldering.

<Applicable to KR3/KRM Series>

4. For the shape of the soldering iron tip, refer to the figure on the right.

Regarding the type of solder, use a wire diameter of  $\phi 0.5\text{mm}$  or less (rosin core wire solder).


### How to Apply the Soldering Iron

Apply the tip of the soldering iron against the lower end of the metal terminal.

- 1) In order to prevent cracking caused by sudden heating of the ceramic device, do not touch the ceramic base directly.
- 2) In order to prevent deviations and dislocating of the chip, do not touch the junction of the chip and the metal terminal, and the metal portion on the outside directly.

### Appropriate Amount of Solder

The amount of solder for corrections by soldering iron, should be lower than the height of the lower side of the chip.



## 5. Washing

Excessive ultrasonic oscillation during cleaning can cause the PCBs to resonate, resulting in cracked chips or broken solder joints. Take note not to vibrate PCBs.

## 6. Electrical Test on Printed Circuit Board


1. Confirm position of the backup pin or specific jig, when inspecting the electrical performance of a capacitor after mounting on the printed circuit board.

1-1. Avoid bending the printed circuit board by the pressure of a test-probe, etc.

The thrusting force of the test probe can flex the PCB, resulting in cracked chips or open solder joints.

Provide backup pins on the back side of the PCB to prevent warping or flexing. Install backup pins as close to the capacitor as possible.

1-2. Avoid vibration of the board by shock when a test-probe contacts a printed circuit board.




## 7. Printed Circuit Board Cropping

1. After mounting a capacitor on a printed circuit board, do not apply any stress to the capacitor that causes bending or twisting the board.

1-1. In cropping the board, the stress as shown at right may cause the capacitor to crack.

Cracked capacitors may cause deterioration of the insulation resistance, and result in a short.

Avoid this type of stress to a capacitor.



Continued on the following page. ➤

## ⚠Caution

Continued from the preceding page.

### 2. Check the cropping method for the printed circuit board in advance.

2-1. Printed circuit board cropping shall be carried out by using a jig or an apparatus (Disk separator, router type separator, etc.) to prevent the mechanical stress that can occur to the board.

| Board Separation Method  | Hand Separation<br>Nipper Separation                                            | (1) Board Separation Jig                                                                                                        | Board Separation Apparatus                                                                                                                                                           |                           |
|--------------------------|---------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------|
|                          |                                                                                 |                                                                                                                                 | (2) Disk Separator                                                                                                                                                                   | (3) Router Type Separator |
| Level of stress on board | High                                                                            | Medium                                                                                                                          | Medium                                                                                                                                                                               | Low                       |
| Recommended              | ×                                                                               | △*                                                                                                                              | △*                                                                                                                                                                                   | ○                         |
| Notes                    | Hand and nipper separation apply a high level of stress.<br>Use another method. | <ul style="list-style-type: none"> <li>Board handling</li> <li>Board bending direction</li> <li>Layout of capacitors</li> </ul> | <ul style="list-style-type: none"> <li>Board handling</li> <li>Layout of slits</li> <li>Design of V groove</li> <li>Arrangement of blades</li> <li>Controlling blade life</li> </ul> | Board handling            |


\* When a board separation jig or disk separator is used, if the following precautions are not observed, a large board deflection stress will occur and the capacitors may crack. Use router type separator if at all possible.

#### (1) Example of a suitable jig

[In the case of Single-side Mounting]

An outline of the board separation jig is shown as follows. Recommended example: Stress on the component mounting position can be minimized by holding the portion close to the jig, and bend in the direction towards the side where the capacitors are mounted. Not recommended example: The risk of cracks occurring in the capacitors increases due to large stress being applied to the component mounting position, if the portion away from the jig is held and bent in the direction opposite the side where the capacitors are mounted.

[Outline of Jig]



| Recommended | Not recommended |
|-------------|-----------------|
|             |                 |

[In the case of Double-sided Mounting]

Since components are mounted on both sides of the board, the risk of cracks occurring can not be avoided with the above method.

Therefore, implement the following measures to prevent stress from being applied to the components.  
(Measures)

- (1) Consider introducing a router type separator.  
If it is difficult to introduce a router type separator, implement the following measures. (Refer to item 1. Mounting Position)
- (2) Mount the components at a right angle to the board separation surface.
- (3) When mounting components near the board separation point, add slits in the separation position near the component.
- (4) Keep the mounting position of the components away from the board separation point.

Continued on the following page. ↗

## ⚠Caution

Continued from the preceding page.


### (2) Example of a Disk Separator

An outline of a disk separator is shown as follows. As shown in the Principle of Operation, the top blade and bottom blade are aligned with the V-grooves on the printed circuit board to separate the board.


In the following case, board deflection stress will be applied and cause cracks in the capacitors.

- (1) When the adjustment of the top and bottom blades are misaligned, such as deviating in the top-bottom, left-right or front-rear directions
  - (2) The angle of the V groove is too low, depth of the V groove is too shallow, or the V groove is misaligned top-bottom
- IF V groove is too deep, it is possible to brake when you handle and carry it. Carefully design depth of the V groove with consideration about strength of material of the printed circuit board.


[Outline of Machine]



[Principle of Operation]



[Cross-section Diagram]



| Recommended                          | Not Recommended                      |                                      |                                      |
|--------------------------------------|--------------------------------------|--------------------------------------|--------------------------------------|
|                                      | Top-bottom Misalignment              | Left-right Misalignment              | Front-rear Misalignment              |
| <p>Top Blade</p> <p>Bottom Blade</p> | <p>Top Blade</p> <p>Bottom Blade</p> | <p>Top Blade</p> <p>Bottom Blade</p> | <p>Top Blade</p> <p>Bottom Blade</p> |


| Example of Recommended V-groove Design | Not Recommended         |           |                   |                |
|----------------------------------------|-------------------------|-----------|-------------------|----------------|
|                                        | Left-right Misalignment | Low-Angle | Depth too Shallow | Depth too Deep |
|                                        |                         |           |                   |                |

### (3) Example of Router Type Separator

The router type separator performs cutting by a router rotating at a high speed. Since the board does not bend in the cutting process, stress on the board can be suppressed during board separation.

When attaching or removing boards to/from the router type separator, carefully handle the boards to prevent bending.

[Outline Drawing]



Continued on the following page. ➤

## ⚠Caution

Continued from the preceding page.

### 8. Assembly

#### 1. Handling

If a board mounted with capacitors is held with one hand, the board may bend. Firmly hold the edges of the board with both hands when handling.

If a board mounted with capacitors is dropped, cracks may occur in the capacitors.


Do not use dropped boards, as there is a possibility that the quality of the capacitors may be impaired.

#### 2. Attachment of Other Components

##### 2-1. Mounting of Other Components

Pay attention to the following items, when mounting other components on the back side of the board after capacitors have been mounted on the opposite side. When the bottom dead point of the suction nozzle is set too low, board deflection stress may be applied to the capacitors on the back side (bottom side), and cracks may occur in the capacitors.

- After the board is straightened, set the bottom dead point of the nozzle on the upper surface of the board.
- Periodically check and adjust the bottom dead point.




##### 2-2. Inserting Components with Leads into Boards

When inserting components (transformers, IC, etc.) into boards, bending the board may cause cracks in the capacitors or cracks in the solder.


Pay attention to the following.

- Increase the size of the holes to insert the leads, to reduce the stress on the board during insertion.
- Fix the board with backup pins or a dedicated jig before insertion.
- Support below the board so that the board does not bend. When using multiple backup pins on the board, periodically confirm that there is no difference in the height of each backup pin.



##### 2-3. Attaching/Removing Sockets

When the board itself is a connector, the board may bend when a socket is attached or removed. Plan the work so that the board does not bend when a socket is attached or removed.




##### 2-4. Tightening Screws

The board may be bent, when tightening screws, etc. during the attachment of the board to a shield or chassis.

Pay attention to the following items before performing the work.

- Plan the work to prevent the board from bending.
- Use a torque screwdriver, to prevent over-tightening of the screws.
- The board may bend after mounting by reflow soldering, etc. Please note, as stress may be applied to the chips by forcibly flattening the board when tightening the screws.



Continued on the following page. ➤

## ⚠Caution

☐ Continued from the preceding page.

<Applicable to GMA or GMD Series>

### 9. Die Bonding/Wire Bonding

#### 1. Die Bonding of Capacitors

- 1-1. Use the following materials for the Brazing alloys:  
Au-Sn (80/20) 300 to 320 °C in N<sub>2</sub> atmosphere
- 1-2. Mounting
  - (1) Control the temperature of the substrate so it matches the temperature of the brazing alloy.
  - (2) Place the brazing alloy on the substrate and place the capacitor on the alloy. Hold the capacitor and gently apply the load. Be sure to complete the operation within 1 minute.

#### 2. Wire Bonding

- 2-1. Wire  
Gold wire: 25 micro m (0.001 inch) diameter
- 2-2. Bonding
  - (1) Thermo compression, ultrasonic ball bonding.
  - (2) Required stage temperature: 150 to 200 °C
  - (3) Required wedge or capillary weight: 0.2N to 0.5N
  - (4) Bond the capacitor and base substrate or other devices with gold wire.

### ■ Other

#### 1. Under Operation of Equipment

- 1-1. Do not touch a capacitor directly with bare hands during operation in order to avoid the danger of an electric shock.
- 1-2. Do not allow the terminals of a capacitor to come in contact with any conductive objects (short-circuit). Do not expose a capacitor to a conductive liquid, including any acid or alkali solutions.
- 1-3. Confirm the environment in which the equipment will operate is under the specified conditions. Do not use the equipment under the following environments.
  - (1) Being spattered with water or oil.
  - (2) Being exposed to direct sunlight.
  - (3) Being exposed to ozone, ultraviolet rays, or radiation.
  - (4) Being exposed to toxic gas (e.g., hydrogen sulfide, sulfur dioxide, chlorine, ammonia gas, etc.)
  - (5) Any vibrations or mechanical shocks exceeding the specified limits.
  - (6) Moisture condensing environments.
- 1-4. Use damp proof countermeasures if using under any conditions that can cause condensation.

#### 2. Other

- 2-1. In an Emergency
  - (1) If the equipment should generate smoke, fire, or smell, immediately turn off or unplug the equipment. If the equipment is not turned off or unplugged, the hazards may be worsened by supplying continuous power.
  - (2) In this type of situation, do not allow face and hands to come in contact with the capacitor or burns may be caused by the capacitor's high temperature.

#### 2-2. Disposal of Waste

When capacitors are disposed of, they must be burned or buried by an industrial waste vendor with the appropriate licenses.

#### 2-3. Circuit Design

- (1) Addition of Fail Safe Function  
Capacitors that are cracked by dropping or bending of the board may cause deterioration of the insulation resistance, and result in a short. If the circuit being used may cause an electrical shock, smoke or fire when a capacitor is shorted, be sure to install fail-safe functions, such as a fuse, to prevent secondary accidents.
- (2) Capacitors used to prevent electromagnetic interference in the primary AC side circuit, or as a connection/insulation, must be a safety standard certified product, or satisfy the contents stipulated in the Electrical Appliance and Material Safety Law. Install a fuse for each line in case of a short.
- (3) The GJM, GMA, GMD, GQM, GR3, GRJ, GRM, KR3, KRM, LLA, LLL, LLM and LLR series are not safety standard certified products.

#### 2-4. Remarks

Failure to follow the cautions may result, worst case, in a short circuit and smoking when the product is used.

The above notices are for standard applications and conditions. Contact us when the products are used in special mounting conditions.

Select optimum conditions for operation as they determine the reliability of the product after assembly. The data herein are given in typical values, not guaranteed ratings.



## Notice

### ■ Rating

#### 1. Operating Temperature

1. The operating temperature limit depends on the capacitor.

- 1-1. Do not apply temperatures exceeding the upper operating temperature.

It is necessary to select a capacitor with a suitable rated temperature that will cover the operating temperature range.

It is also necessary to consider the temperature distribution in equipment and the seasonal temperature variable factor.

- 1-2. Consider the self-heating factor of the capacitor.

The surface temperature of the capacitor shall be the upper operating temperature or less when including the self-heating factors.

#### 2. Atmosphere Surroundings (gaseous and liquid)

1. Restriction on the operating environment of capacitors.

- 1-1. Capacitors, when used in the above, unsuitable,

operating environments may deteriorate due to the corrosion of the terminations and the penetration of moisture into the capacitor.

- 1-2. The same phenomenon as the above may occur when the electrodes or terminals of the capacitor are subject to moisture condensation.

- 1-3. The deterioration of characteristics and insulation resistance due to the oxidization or corrosion of terminal electrodes may result in breakdown when the capacitor is exposed to corrosive or volatile gases or solvents for long periods of time.

#### 3. Piezo-electric Phenomenon

1. When using high dielectric constant type capacitors in AC or pulse circuits, the capacitor itself vibrates at specific frequencies and noise may be generated. Moreover, when the mechanical vibration or shock is added to the capacitor, noise may occur.

### ■ Soldering and Mounting








#### 1. PCB Design

##### 1. Notice for Pattern Forms

- 1-1. Unlike leaded components, chip components are susceptible to flexing stresses since they are mounted directly on the substrate. They are also more sensitive to mechanical and thermal stresses than leaded components. Excess solder fillet height can multiply these stresses and cause chip cracking. When designing substrates, take land patterns and dimensions into consideration to eliminate the possibility of excess solder fillet height.

- 1-2. There is a possibility of chip cracking caused by PCB expansion/contraction with heat, because stress on a chip is different depending on PCB material and structure. When the thermal expansion coefficient greatly differs between the board used for mounting and the chip, it will cause cracking of the chip due to the thermal expansion and contraction. When small size capacitors of 1005 size or less are mounted on a single-layered glass epoxy board, it will also cause cracking of the chip for the same reason.

#### Pattern Forms

|                                                   | Prohibited                                                                          | Correct                                                                               |
|---------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| Placing Close to Chassis                          |  |  |
| Placing of Chip Components and Leaded Components  |  |  |
| Placing of Leaded Components after Chip Component |  |  |
| Lateral Mounting                                  |  |  |

Continued on the following page. ➤

## Notice

Continued from the preceding page.

### 2. Land Dimensions

- 2-1. Chip capacitors can be cracked due to the stress of PCB bending, etc. if the land area is larger than needed and has an excess amount of solder. Please refer to the land dimensions in table 1 for flow soldering, table 2 for reflow soldering, table 3 for reflow soldering for LLA Series, table 4 for reflow soldering for LLM Series. Please confirm the suitable land dimension by evaluating of the actual SET / PCB.




Table 1 Flow Soldering Method

| Part Number                                  | Dimensions | Chip (L×W) | a          | b          | c          |
|----------------------------------------------|------------|------------|------------|------------|------------|
| <b>GQM/GR3/GRJ/GRM</b> Series <b>18</b> size |            | 1.6×0.8    | 0.6 to 1.0 | 0.8 to 0.9 | 0.6 to 0.8 |
| <b>GQM/GR3/GRJ/GRM</b> Series <b>21</b> size |            | 2.0×1.25   | 1.0 to 1.2 | 0.9 to 1.0 | 0.8 to 1.1 |
| <b>GR3/GRJ/GRM</b> Series <b>31</b> size     |            | 3.2×1.6    | 2.2 to 2.6 | 1.0 to 1.1 | 1.0 to 1.4 |
| <b>LLL</b> Series <b>21</b> size             |            | 1.25×2.0   | 0.4 to 0.7 | 0.5 to 0.7 | 1.4 to 1.8 |
| <b>LLL</b> Series <b>31</b> size             |            | 1.6×3.2    | 0.6 to 1.0 | 0.8 to 0.9 | 2.6 to 2.8 |

Flow soldering can only be used for products with a chip size of 3.2x1.6mm or less.

(in mm)

Table 2 Reflow Soldering Method

| Part Number                                  | Dimensions | Chip (L×W)              | a            | b            | c           |
|----------------------------------------------|------------|-------------------------|--------------|--------------|-------------|
| <b>GJM/GRM</b> Series <b>02</b> size         |            | 0.4×0.2                 | 0.16 to 0.2  | 0.12 to 0.18 | 0.2 to 0.23 |
| <b>GJM/GRM</b> Series <b>03</b> size         |            | 0.6×0.3                 | 0.2 to 0.3   | 0.2 to 0.35  | 0.2 to 0.4  |
| <b>GJM/GRM</b> Series <b>15</b> size         |            | 1.0×0.5 (within ±0.10)  | 0.3 to 0.5   | 0.35 to 0.45 | 0.4 to 0.6  |
|                                              |            | 1.0×0.5 (±0.15/±0.20)   | 0.4 to 0.6   | 0.4 to 0.5   | 0.5 to 0.7  |
| <b>GQM/GR3/GRJ/GRM</b> Series <b>18</b> size |            | 1.6×0.8 (within ±0.10)  | 0.6 to 0.8   | 0.6 to 0.7   | 0.6 to 0.8  |
|                                              |            | 1.6×0.8 (±0.15/±0.20)   | 0.7 to 0.9   | 0.7 to 0.8   | 0.8 to 1.0  |
| <b>GQM</b> Series <b>21</b> size             |            | 2.0×1.25                | 1.0 to 1.2   | 0.6 to 0.7   | 0.8 to 1.1  |
| <b>GR3/GRJ/GRM</b> Series <b>21</b> size     |            | 2.0×1.25 (within ±0.10) | 1.2          | 0.6          | 1.25        |
|                                              |            | 2.0×1.25 (±0.15)        | 1.2          | 0.6 to 0.8   | 1.2 to 1.4  |
|                                              |            | 2.0×1.25 (±0.20)        | 1.0 to 1.4   | 0.6 to 0.8   | 1.2 to 1.4  |
| <b>GR3/GRJ/GRM</b> Series <b>31</b> size     |            | 3.2×1.6 (within ±0.20)  | 1.8 to 2.0   | 0.9 to 1.2   | 1.5 to 1.7  |
|                                              |            | 3.2×1.6 (±0.30)         | 1.9 to 2.1   | 1.0 to 1.3   | 1.7 to 1.9  |
| <b>GR3/GRJ/GRM</b> Series <b>32</b> size     |            | 3.2×2.5                 | 2.0 to 2.4   | 1.0 to 1.2   | 1.8 to 2.3  |
| <b>GR3/GRJ/GRM</b> Series <b>43</b> size     |            | 4.5×3.2                 | 3.0 to 3.5   | 1.2 to 1.4   | 2.3 to 3.0  |
| <b>GR3/GRJ/GRM</b> Series <b>55</b> size     |            | 5.7×5.0                 | 4.0 to 4.6   | 1.4 to 1.6   | 3.5 to 4.8  |
| <b>LLL</b> Series <b>15</b> size             |            | 0.5×1.0                 | 0.15 to 0.2  | 0.2 to 0.25  | 0.7 to 1.0  |
| <b>LLL</b> Series <b>1U</b> size             |            | 0.6×1.0                 | 0.20 to 0.25 | 0.25 to 0.35 | 0.7 to 1.0  |
| <b>LLL/LLR</b> Series <b>18</b> size         |            | 0.8×1.6                 | 0.2 to 0.3   | 0.3 to 0.4   | 1.4 to 1.6  |
| <b>LLL</b> Series <b>21</b> size             |            | 1.25×2.0                | 0.4 to 0.6   | 0.4 to 0.5   | 1.4 to 1.8  |
| <b>LLL</b> Series <b>31</b> size             |            | 1.6×3.2                 | 0.6 to 0.8   | 0.6 to 0.7   | 2.6 to 2.8  |
| <b>GQM</b> Series <b>22</b> size             |            | 2.8×2.8                 | 2.2 to 2.5   | 0.8 to 1.0   | 1.9 to 2.3  |

(in mm)

<Applicable to Part Number KR3/KRM>

| Part Number                          | Dimensions | Chip (L×W) | a          | b          | c          |
|--------------------------------------|------------|------------|------------|------------|------------|
| <b>KRM</b> Series <b>21</b> size     |            | 2.0×1.25   | 1.0 to 1.2 | 0.6 to 0.7 | 0.8 to 1.1 |
| <b>KRM</b> Series <b>31</b> size     |            | 3.2×1.6    | 2.2 to 2.4 | 0.8 to 0.9 | 1.0 to 1.4 |
| <b>KR3/KRM</b> Series <b>55</b> size |            | 5.7×5.0    | 2.6        | 2.7        | 5.6        |


(in mm)

Continued on the following page. ➤

## Notice

Continued from the preceding page.

[Land for LLA Series]



[Land for LLM Series]




Table 3 LLA Series Reflow Soldering Method

| Part Number        | Dimensions | Chip (L×W) | a          | b            | c           | p   |
|--------------------|------------|------------|------------|--------------|-------------|-----|
| LLA Series 18 size |            | 1.6×0.8    | 0.3 to 0.4 | 0.25 to 0.35 | 0.2 to 0.23 | 0.4 |
| LLA Series 21 size |            | 2.0×1.25   | 0.5 to 0.7 | 0.35 to 0.6  | 0.2 to 0.3  | 0.5 |
| LLA Series 31 size |            | 3.2×1.6    | 0.7 to 0.9 | 0.4 to 0.7   | 0.3 to 0.4  | 0.8 |

(in mm)

Table 4 LLM Series Reflow Soldering Method

| Part Number        | Dimensions | Chip (L×W) | a          | b, b'        | c, c' | d          | e          | f          | p   |
|--------------------|------------|------------|------------|--------------|-------|------------|------------|------------|-----|
| LLM Series 21 size |            | 2.0×1.25   | 0.6 to 0.8 | (0.3 to 0.5) | 0.3   | 2.0 to 2.6 | 1.3 to 1.8 | 1.4 to 1.6 | 0.5 |
| LLM Series 31 size |            | 3.2×1.6    | 1.0        | (0.3 to 0.5) | 0.4   | 3.2 to 3.6 | 1.6 to 2.0 | 2.6        | 0.8 |

$b=(c-e)/2$ ,  $b'=(d-f)/2$

(in mm)

### 3. Board Design


When designing the board, keep in mind that the amount of strain which occurs will increase depending on the size and material of the board.

[Relationship with amount of strain to the board thickness, length, width, etc.]

$$\epsilon = \frac{3PL}{2Ewh^2}$$

Relationship between load and strain

$\epsilon$ : Strain on center of board ( $\mu\text{st}$ )  
 $L$ : Distance between supporting points (mm)  
 $w$ : Board width (mm)  
 $h$ : Board thickness (mm)  
 $E$ : Elastic modulus of board ( $\text{N/m}^2=\text{Pa}$ )  
 $Y$ : Deflection (mm)  
 $P$ : Load (N)



When the load is constant, the following relationship can be established.

- As the distance between the supporting points ( $L$ ) increases, the amount of strain also increases.  
→Reduce the distance between the supporting points.
  - As the elastic modulus ( $E$ ) decreases, the amount of strain increases.  
→Increase the elastic modulus.
  - As the board width ( $w$ ) decreases, the amount of strain increases.  
→Increase the width of the board.
  - As the board thickness ( $h$ ) decreases, the amount of strain increases.  
→Increase the thickness of the board.
- Since the board thickness is squared, the effect on the amount of strain becomes even greater.

Continued on the following page. ➤

## Notice

Continued from the preceding page.

### 2. Adhesive Application

- Thin or insufficient adhesive can cause the chips to loosen or become disconnected during flow soldering. The amount of adhesive must be more than dimension c, shown in the drawing at right, to obtain the correct bonding strength.

The chip's electrode thickness and land thickness must also be taken into consideration.

- Low viscosity adhesive can cause chips to slip after mounting. The adhesive must have a viscosity of 5000Pa · s (500ps) min. (at 25°C).

### 3. Adhesive Coverage

| Size (L×W) (in mm) | Adhesive Coverage* |
|--------------------|--------------------|
| 1.6×0.8            | 0.05mg min.        |
| 2.0×1.25           | 0.1mg min.         |
| 3.2×1.6            | 0.15mg min.        |

\*Nominal Value

### 3. Adhesive Curing


- Insufficient curing of the adhesive can cause chips to disconnect during flow soldering and causes deterioration in the insulation resistance between the outer electrodes due to moisture absorption.  
Control curing temperature and time in order to prevent insufficient hardening.

### 4. Flux Application

- An excessive amount of flux generates a large quantity of flux gas, which can cause a deterioration of solder ability, so apply flux thinly and evenly throughout. (A foaming system is generally used for flow soldering.)
- Flux containing too high a percentage of halide may cause corrosion of the outer electrodes unless there is sufficient cleaning. Use flux with a halide content of 0.1% max.


### 5. Flow Soldering

- Set temperature and time to ensure that leaching of the outer electrode does not exceed 25% of the chip end area as a single chip (full length of the edge A-B-C-D shown at right) and 25% of the length A-B shown as mounted on substrate.




- Do not use strong acidic flux.
- Do not use water-soluble flux.\*  
(\*Water-soluble flux can be defined as non-rosin type flux including wash-type flux and non-wash-type flux.)

[As a Single Chip]



[As Mounted on Substrate]



Continued on the following page. ➤

## Notice

Continued from the preceding page.

### 6. Washing

1. Please evaluate the capacitor using actual cleaning equipment and conditions to confirm the quality, and select the solvent for cleaning.
2. Unsuitable cleaning solvent may leave residual flux or other foreign substances, causing deterioration of electrical characteristics and the reliability of the capacitors.

### 7. Coating

1. A crack may be caused in the capacitor due to the stress of the thermal contraction of the resin during curing process.  
The stress is affected by the amount of resin and curing contraction.  
Select a resin with low curing contraction.  
The difference in the thermal expansion coefficient between a coating resin or a molding resin and the capacitor may cause the destruction and deterioration of the capacitor such as a crack or peeling, and lead to the deterioration of insulation resistance or dielectric breakdown.

### ■ Other

#### 1. Transportation

1. The performance of a capacitor may be affected by the conditions during transportation.
  - 1-1. The capacitors shall be protected against excessive temperature, humidity, and mechanical force during transportation.
    - (1) Climatic condition
      - low air temperature: -40°C
      - change of temperature air/air: -25°C/+25°C
      - low air pressure: 30 kPa
      - change of air pressure: 6 kPa/min.
    - (2) Mechanical condition  
Transportation shall be done in such a way that the boxes are not deformed and forces are not directly passed on to the inner packaging.
  - 1-2. Do not apply excessive vibration, shock, or pressure to the capacitor.
    - (1) When excessive mechanical shock or pressure is applied to a capacitor, chipping or cracking may occur in the ceramic body of the capacitor.
    - (2) When the sharp edge of an air driver, a soldering iron, tweezers, a chassis, etc. impacts strongly on the surface of the capacitor, the capacitor may crack and short-circuit.
  - 1-3. Do not use a capacitor to which excessive shock was applied by dropping, etc.  
A capacitor dropped accidentally during processing may be damaged.

#### 3. Select the proper cleaning conditions.

- 3-1. Improper cleaning conditions (excessive or insufficient) may result in deterioration of the performance of the capacitors.

Select a resin for which the thermal expansion coefficient is as close to that of the capacitor as possible.

A silicone resin can be used as an under-coating to buffer against the stress.

#### 2. Select a resin that is less hygroscopic.

Using hygroscopic resins under high humidity conditions may cause the deterioration of the insulation resistance of a capacitor.

An epoxy resin can be used as a less hygroscopic resin.

#### 2. Characteristics Evaluation in the Actual System

1. Evaluate the capacitor in the actual system, to confirm that there is no problem with the performance and specification values in a finished product before using.
2. Since a voltage dependency and temperature dependency exists in the capacitance of high dielectric type ceramic capacitors, the capacitance may change depending on the operating conditions in the actual system. Therefore, be sure to evaluate the various characteristics, such as the leakage current and noise absorptivity, which will affect the capacitance value of the capacitor.
3. In addition, voltages exceeding the predetermined surge may be applied to the capacitor by the inductance in the actual system. Evaluate the surge resistance in the actual system as required.

GRM Series

GJM Series

GMA Series

GMD Series

GQM Series

GRJ Series

GR3 Series

KRM Series

KR3 Series

LLA Series

LLL Series

LLM Series

LLR Series

Notice



## Qualified Standards

The products listed here have been produced by ISO 9001 certified factory.

| Plant                                    |
|------------------------------------------|
| Fukui Murata Mfg. Co., Ltd.              |
| Izumo Murata Mfg. Co., Ltd.              |
| Okayama Murata Mfg. Co., Ltd.            |
| Murata Electronics Singapore (Pte.) Ltd. |
| Beijing Murata Electronics Co., Ltd.     |
| Wuxi Murata Electronics Co., Ltd.        |

[illegible]

# Design assistant tool: SimSurfing

# SimSurfing



for MLCC and various devices.

- Polymer capacitors
- RF inductors/Power inductors
- NTC thermistors/PTC thermistors

## Available function for MLCCs:

- ① Products search
- ② View frequency characteristics (S parameters, Z, R, X, Q, DF, L, C)  
DC bias can be applied to available part number.
- ③ DC voltage bias characteristics (absolute capacitance/change rate)
- ④ Temperature characteristics (absolute capacitance/change rate)
- ⑤ AC voltage bias characteristics (absolute capacitance/change rate)
- ⑥ Download SPICE netlist/ S parameter

### 1 Select the Products

- (1) By part number
- (2) By specification

### 2 View characteristics

By clicking buttons in this area with part number selected, you can view any electrical characteristics chart.

### 3 Data download

You can download SPICE netlist and S parameter files (S2P)



Added the capacitor finder tool for middle and high voltage capacitor which are capable for specified voltage waveform.

These images are captured at August/2013. Be sure that this software will be updated frequently.

<http://ds.murata.com/software/simsurfing/en-us/mlcc/>

# EMICON-FUN!

Please check Murata's newsletter!  
You can learn about electric parts with fun.  
[http://www.murata.com/products/emicon\\_fun/](http://www.murata.com/products/emicon_fun/)

EMICON-FUN! disseminated widely from basics (principles, characteristics, mounting, etc.) of capacitors, EMI suppression filters and inductors to information can practically be used.

Updated information is also distributed via the mail magazine.

**Click here to register as reader → <https://fofa.jp/murata/a.p/107/>**

You can register from Murata Manufacturing Web site page TOP.  
<http://www.murata.com/products/>



← This banner is the entrance of register form

**email Magazine: Have fun while learning about electronic components**

**EMICON-FUN!** Wide range of information about capacitors, noise suppression filters, and inductors.

Search: Enter keywords to be searched

**Capacitor Room**

- F2C series lead-type monolithic ceramic capacitors compatible to 150°C for automotive applications
- What kind of layout helps prevent chip monolithic ceramic capacitors from cracking?
- Why does the electrostatic capacitance increase as the thickness decreases?
- Next generation characteristics of capacitors and measurement methods
- What are important ESR frequency characteristics in capacitors?

**Noise suppression filter Room**

- Birth of the BLM-E series chip ferrite beads: Entering unexplored BLM territory
- How can the mounting area be reduced? - Methods of using low-ESL capacitors -
- Ascendancy of monolithic ferrite bead development: Horizontally wound-type ferrite beads that support GHz frequencies
- The secret story behind the birth of chip ferrite beads (part 2/2)
- The secret story behind the birth of chip ferrite beads (part 1/2)

**Inductor Room**

- Ascendancy of inductor development [No. 1] Trends in LQW solder mounting technology
- Ascendancy of inductor development [No. 4] Japan's first air-core horizontal wire-wound coil
- Ascendancy of inductor development [No. 3] The LQS series realized super tight tolerance by trimming
- Why second-generation film-type inductors are incredible
- Ascendancy of inductor development [No. 2] Birth of the first film-type inductor: the "LQP11A series"

**For the EARTH**

- Introducing Murata's school classes: What we can do for the children who will shape the world's future
- Special Feature on the Environment, Part 2 "Toward a Low-carbon Society - Initiatives for Global Warming Prevention."
- Special Feature on the Environment, Part 1 "Murata's Waste Management System"

**Sample Newsletter Content:**

#####  
email Magazine: Have fun while learning about electronic components  
The index of June 28 issue  
#####

- Capacitor Room
- Product News
- Proposal for Cost Reductions
- Examples of Problem Solving

Expertly written articles explain the basics of capacitors, inductors, and EMI suppression filters.

#####

- Capacitor Room -
- What kind of layout helps to prevent chip monolithic ceramic capacitors from cracking?

Capacitors may become cracked when boards bend during handling in processes after the capacitors are soldered onto the boards. Therefore to prevent this, the part mounting orientation is important. In order to prevent this, the part mounting orientation is important. Therefore in this article, we would like to introduce parts layouts that help prevent chip monolithic ceramic capacitors from cracking.  
<http://newsletter.murata.co.jp/c/p/02ceLoL4yC>

#####

- Product News -

General Purpose Monolithic Ceramic Capacitors <GRM Series>  
These are Murata's primary products, renowned for both small size and large capacitance value with the latest advanced technology.  
1. Achieves large capacity and small size in a multilayer structure.



The website and search engine of ceramic capacitors has been drastically renewed.

- ▶ **Convenient Search**
  - The type of searches has been increased to respond to various ways of searching.
  - The products you are searching for can easily be found from about 40,000 part numbers!
  - The frequency of revisions and discontinuance has been increased to provide the latest information at all times!
- ▶ **Substantial Technical Information**
  - Reference drawings (Specifications and Test Methods) can be downloaded in PDF format.
  - Graphs of the electrical characteristic data (Capacitance - Temperature characteristics / DC bias characteristics / AC voltage characteristics / Frequency characteristics) can be displayed.
  - Reliability test data can be downloaded.





⚠Note:

1. Export Control

<For customers outside Japan>

No Murata products should be used or sold, through any channels, for use in the design, development, production, utilization, maintenance or operation of, or otherwise contribution to (1) any weapons (Weapons of Mass Destruction [nuclear, chemical or biological weapons or missiles] or conventional weapons) or (2) goods or systems specially designed or intended for military end-use or utilization by military end-users.

<For customers in Japan>

For products which are controlled items subject to the "Foreign Exchange and Foreign Trade Law" of Japan, the export license specified by the law is required for export.

2. Please contact our sales representatives or product engineers before using the products in this catalog for the applications listed below, which require especially high reliability for the prevention of defects which might directly damage a third party's life, body or property, or when one of our products is intended for use in applications other than those specified in this catalog.

- |                             |                                                                                                      |
|-----------------------------|------------------------------------------------------------------------------------------------------|
| ① Aircraft equipment        | ② Aerospace equipment                                                                                |
| ③ Undersea equipment        | ④ Power plant equipment                                                                              |
| ⑤ Medical equipment         | ⑥ Transportation equipment (vehicles, trains, ships, etc.)                                           |
| ⑦ Traffic signal equipment  | ⑧ Disaster prevention / crime prevention equipment                                                   |
| ⑨ Data-processing equipment | ⑩ Application of similar complexity and/or reliability requirements to the applications listed above |

3. Product specifications in this catalog are as of August 2013. They are subject to change or our products in it may be discontinued without advance notice.

Please check with our sales representatives or product engineers before ordering. If there are any questions, please contact our sales representatives or product engineers.

4. Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.

5. This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

6. Please note that unless otherwise specified, we shall assume no responsibility whatsoever for any conflict or dispute that may occur in connection with the effect of our and/or a third party's intellectual property rights and other related rights in consideration of your use of our products and/or information described or contained in our catalogs. In this connection, no representation shall be made to the effect that any third parties are authorized to use the rights mentioned above under licenses without our consent.

7. No ozone depleting substances (ODS) under the Montreal Protocol are used in our manufacturing process.



<http://www.murata.com/>

**Head Office**  
1-10-1, Higashi Kotari, Nagaokakyo-shi, Kyoto 617-8555, Japan  
Phone: 81-75-951-9111

**International Division**  
3-29-12, Shibuya, Shibuya-ku, Tokyo 150-0002, Japan  
Phone: 81-3-5469-6123 Fax: 81-3-5469-6155 E-mail: [intl@murata.co.jp](mailto:intl@murata.co.jp)

**Cat. No. C02E-18**