

T5 Standard Luxline® Plus

F13W/T5/135

0000030



Range features



PRODUCT OVERVIEW

Light colour	835 white
Technology	Fluorescent
Ordering number	0000030
Energy class	A
Lamp shape	Tubular
Lamp finish	Coated
Cap/Base	G5
Type	T5 Standard
EAN code	5410288000305
CRI (Ra)	64
Colour temperature (K)	3500
Luminous flux (Rated) (lm)	880
Efficacy (Rated) 100h (lm/W)	69
Watt (Nominal) (W)	13
Voltage (V)	95

T5 Standard Luxline® Plus

F13W/T5/135

0000030

DATA TABLE

General data

Technology	Fluorescent
Ordering number	0000030
Average life (Nominal) (h)	10000
Energy class	A
Lamp shape	Tubular
Lamp finish	Coated
Cap/Base	G5
Type	T5 Standard
EAN code	5410288000305
E-number FI	4940239
Product name	F13W/T5/135
Lamp mercury content (mg)	2.3
Control gear required	Yes
Fixture rating	Open
IEC Reference	IEC 60081
IEC Reference 2	IEC 61195
Intended purpose	General lighting
Special purpose lamp	No
Transformer required	No
Sales pack quantity	25
Rated survival factor at 2000 h 50Hz	1
Rated survival factor at 4000 h 50Hz	0.99
Rated survival factor at 6000 h 50Hz	0.96
Rated survival factor at 8000 h 50Hz	0.83

Optical data

Light colour	835 white
CRI (Ra)	64
Colour temperature (K)	3500
Luminous flux (Rated) (lm)	880
Luminous flux (Nominal) (lm)	880
Rated lumen maint. factor at 2000 h 50Hz	0.88
Rated lumen maint. factor at 4000 h 50Hz	0.82
Rated lumen maint. factor at 6000 h 50Hz	0.78
Rated lumen maint. factor at 8000 h 50Hz	0.75

T5 Standard Luxline® Plus

F13W/T5/135

0000030

Electrical data

kWh per 1000 hours burning time	15
Efficacy (Rated) 100h (lm/W)	69
Watt (Rated) (W)	12.8
Watt (Nominal) (W)	13
Voltage (V)	95
Current (A)	0.165

Physical data


Weight (kg)	0.04
Length base to base (mm) - A	516.9
Length base to pin Min-Max - B	521.6-524.0
Max overall length (mm)	531.1
Lamp Diameter (mm) - D	16
Packaging outer length (cm)	54.80
Packaging outer height (cm)	10.50
Packaging outer width (cm)	11.00
Packaging single width (cm)	1.90
Packaging single length (cm)	53.20
Packaging single height (cm)	1.90

T5 Standard Luxline® Plus


F13W/T5/135

0000030

PHOTOMETRY



TECHNICAL DRAWINGS



ENERGY LABEL

