




- 1 MATERIAL: COPPER ALLOY
- 2 FINISH: GOLD PLATE .000030 [0.76µm] MIN THICK
OVER NICKEL PLATE .000050 [1.27µm] MIN THICK.
- 3 POINT OF PLATING THICKNESS MEASUREMENT - SHALL BE
MEASURED ON BOTH WIRE BARREL AND PIN END.
- 4 INSPECTION HOLE THRU ONE WALL ONLY
RADIAL LOCATION OPTIONAL.

TAPE MOUNTED 20-24 AWG WIRE	.043-.046 [1.09-1.17]	2	1	1218266-4
LOOSE PIECE 20-24 AWG WIRE	.043-.046 [1.09-1.17]	2	1	1218266-3
TAPE MOUNTED 18 AWG WIRE	.051-.053 [1.30-1.35]	2	1	1218266-2
LOOSE PIECE 18 AWG WIRE	.051-.053 [1.30-1.35]	2	1	1218266-1
REMARKS	DIM A	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. BRANDBERG 08 APR 98 CHK: G. GRIFFITH 04 DEC 98 APVD: G. GRIFFITH 04 DEC 98		AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES (mm)		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0 PLC ±.005 [0.13] 1 PLC ±.005 [0.13] 2 PLC ±.005 [0.13] 3 PLC ±.005 [0.13] 4 PLC ±.005 [0.13]		0 PLC ±.005 [0.13] 1 PLC ±.005 [0.13] 2 PLC ±.005 [0.13] 3 PLC ±.005 [0.13] 4 PLC ±.005 [0.13]		PRODUCT SPEC	
MATERIAL		FINISH		APPLICATION SPEC	
1		2		1	
CUSTOMER DRAWING		WEIGHT		RESTRICTED TO	
SCALE 15:1		SHEET 1 OF 1		REV A	