

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC
FT

DIST
0

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REVISED PER ECO-11-023401	01DEC11	KH	MS

DIM L±.02

DIM S±.02

.197±.010

.55±.01

.50±.01

.17±.02

.047±.004

.25±.01

.031±.004

.16±.02

.250±.006

NOTES:

PHYSICAL PROPERTIES:
HOUSING MATERIAL: POLYAMIDE
FLAMMABILITY: UL94V-0
COLOR: BLACK

TERMINAL:
TERMINALS: BRASS, TIN PLATED.
SCREWS: M3, STEEL, ZINC PLATED.

MECHANICAL:
PITCH (TERMINAL SPACING): .250"
RECOMMENDED PCB HOLE DIA.: .073"
RECOMMENDED TIGHTENING TORQUE: 10IN-LBS MAX.

ELECTRICAL PROPERTIES:
MAXIMUM CURRENT: 10A
OPERATING VOLTAGE: 300V
WIRE RANGE: 16-30 AWG

ENVIRONMENTAL PROPERTIES:
OPERATING TEMP RANGE: -40°C TO 105°C

1 PRELIMINARY PART NUMBER.

2 SCREWS ARE BOTTOMED.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

0

1

2

3

4

PLC
PLC
PLC
PLC
PLC

±-
±-
±-
±-
±-

ANGLES
FINISH

±-

MATERIAL

-

DWN
S SCHLEGEL
CHK
D.A. BIEVENOUR
APVD
D.A. BIEVENOUR

11JUN02
6/11/02
6/11/02

PRODUCT SPEC
APPLICATION SPEC
WEIGHT

-
-
-

STE

TE Connectivity

NAME

.250 TRI BARRIER STRIP

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1546328

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
2:1

SHEET
1 OF 1

REV
F

1	7.250	7.55	30	3-1546328-0
1	7.000	7.30	29	2-1546328-9
1	6.750	7.05	28	2-1546328-8
1	6.500	6.80	27	2-1546328-7
1	6.250	6.55	26	2-1546328-6
1	6.000	6.30	25	2-1546328-5
1	5.750	6.05	24	2-1546328-4
1	5.500	5.80	23	2-1546328-3
1	5.250	5.55	22	2-1546328-2
1	5.000	5.30	21	2-1546328-1
1	4.750	5.05	20	2-1546328-0
1	4.500	4.80	19	1-1546328-9
1	4.250	4.55	18	1-1546328-8
1	4.000	4.30	17	1-1546328-7
1	3.750	4.05	16	1-1546328-6
1	3.500	3.80	15	1-1546328-5
1	3.250	3.55	14	1-1546328-4
1	3.000	3.30	13	1-1546328-3
1	2.750	3.05	12	1-1546328-2
1	2.500	2.80	11	1-1546328-1
1	2.250	2.55	10	1-1546328-0
1	2.000	2.30	9	1546328-9
1	1.750	2.05	8	1546328-8
1	1.500	1.80	7	1546328-7
	1.250	1.55	6	1546328-6
1	1.000	1.30	5	1546328-5
1	.750	1.05	4	1546328-4
1	.500	.80	3	1546328-3
1	.250	.55	2	1546328-2
	DIM S	DIM L	POSN	TE PART NO.