


SIB-120-02-F-S



SIR1-15-L-S-A

(2,54 mm) .100"

SIB, SIR1 SERIES

ONE PIECE INTERFACES

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?SIB

Insulator Material:

Black Liquid Crystal Polymer

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over

50μ" (1,27 μm) Ni

Current Rating:

2.6 A per pin

(1 pin powered per row)

Operating Temp Range:

-55°C to +125°C

Normal Force:

111 grams (1,09 N) per contact

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable: Yes

SMT Lead Coplanarity:

(0,10 mm) .004" max (02-19)



(0,15 mm) .005" max (20-30)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594



Note: The SIB Series is intended for vertical mating only.

Note: Some sizes, styles and options are non-standard, non-returnable.

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?SIR1

Insulator Material:

Black LCP

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over

50μ" (1,27 μm) Ni

Current Rating:

2.8 A per pin

(1 pin powered per row)

Weld Tab:

Phosphor Bronze

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:



(0,10 mm) .004" max

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594



Note: Some sizes, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM