



PART NUMBER	MAX BUNDLE DIAMETER [mm]	LENGTH +/- .1 [2]
MSC4W50T15-L6	4" [102]	18.0" [457]
MSC6W50T15-L6	6" [152]	24.4" [620]
MSC8W50T15-L6	8" [203]	30.7" [780]
MSC10W50T15-L6	10" [254]	37.0" [940]



NOTES:

1. APPLICATION TOOLS: BT2MS75, BT2HT
2. ALL DIMENSIONS IN BRACKETS [] ARE MILLIMETERS.
3. BASE MATERIAL: 316 STAINLESS STEEL.
4. 100% COATED WITH BLACK NYLON OR POLYESTER.
5. COATING THICKNESS: .003/.005 [.076/.127] PER SIDE.
6. TOLERANCES (UNLESS OTHERWISE SPECIFIED):
 $\begin{matrix} \phi .X & \pm & .03 [.8] \\ .XX & \pm & .02 [.5] \\ .XXX & \pm & .007 [.18] \end{matrix}$

N41168BS_DC/00A

											 PANDUIT CORP. TINLEY PARK, ILLINOIS			
											COATED METAL STRAPPING .500" [12.7] WIDE CUSTOMER DRAWING			
00A	10/08	JAMB	SKB	ORIG REV WAS 00, ORIG CAD FILE SPEC WAS S41168_00 NOTE 1: APPLICATION TOOL BT1HT REPLACED BY BT2HT										
00	10/03	BRH	EJD	RELEASED				11159	CCH	JJB				
REV	DATE	BY	CHK	DESCRIPTION				ECN #	PM	CUST	DRAWN BY BRH	CHK'D EJD	SCALE FULL	DRAWING NO. N41168BS_DC