


NOTES

1. All Dimensions are in $\frac{\text{inches}}{[\text{millimeters}]}$
2. Dimensions appearing in table are as follows:
 - a - As Supplied
 - b - After Unrestricted Recovery
3. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.
4. Recovered parts may have angularity of $30^{\circ} - 45^{\circ}$.

REVISIONS		
LTR	DESCRIPTION	DATE
V	RELEASE PER ECO-16-009060	05/14/2016



ORDERING INFORMATION

Diagram illustrating the breakdown of a part number into its components:

- Base part number: 101A021
- Material dash number: -X
- Modification number: -XX
- Adhesive slash number: /XXX
- Color designator: -X

Material dash number
(See Compatability Chart)

Modification number

Adhesive slash number _____
(If necessary, see Compatability Chart)


Color designator

* Color code based on SAE-AMS-DTL-23053
* not all colors available for this molded part.

TABLE OF DIMENSIONS				
PART NUMBER	H		P	W
	Min a	Max b	Min b	±20% b
101A011	$\frac{.20}{[5,1]}$	$\frac{.08}{[2,0]}$	$\frac{.90}{[22,9]}$	$\frac{.04}{[1,02]}$
101A021	$\frac{.29}{[7,4]}$	$\frac{.13}{[3,3]}$	$\frac{1.00}{[25,4]}$	$\frac{.05}{[1,27]}$
101A031	$\frac{.40}{[10,2]}$	$\frac{.18}{[4,6]}$	$\frac{1.20}{[30,5]}$	$\frac{.06}{[1,52]}$
101A041	$\frac{.60}{[15,2]}$	$\frac{.25}{[6,4]}$	$\frac{1.60}{[40,6]}$	$\frac{.07}{[1,78]}$
101A052	$\frac{.81}{[20,6]}$	$\frac{.37}{[9,4]}$	$\frac{2.40}{[61,0]}$	$\frac{.08}{[2,03]}$
101A062	$\frac{1.00}{[25,4]}$	$\frac{.45}{[11,4]}$	$\frac{2.70}{[68,6]}$	$\frac{.09}{[2,29]}$
101A073	$\frac{1.55}{[39,4]}$	$\frac{.71}{[18,0]}$	$\frac{3.60}{[91,4]}$	$\frac{.10}{[2,54]}$
101A083	$\frac{2.00}{[50,8]}$	$\frac{.90}{[22,9]}$	$\frac{4.00}{[101,6]}$	$\frac{.11}{[2,79]}$
101A094	$\frac{3.30}{[83,8]}$	$\frac{1.50}{[38,1]}$	$\frac{4.50}{[114,3]}$	$\frac{.12}{[3,05]}$

Raychem Molded Parts
CUSTOMER DRAWING

COMPATIBILITY CHART				
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	ADHESIVE SLASH NO.	ADHESIVE S NUMBER
-3	Polyolefin, Semi-rigid	RT-301	/42; /86	S-1017; S-1048
-4	Polyolefin, Flexible	RT-1304	/42; /86	S-1017; S-1048
-12	*VITON, Flexible	RT-1312	N/A	N/A
-25	Elastomer, Fluid Resistant	RT-1325	/86; /225	S-1048; S-1206
-100	Polyolefin, Semi-flexible	RT-1323	/180	S-1030

THIS DRAWING AND THE INFORMATION SET FORTH HEREON ARE THE PROPERTY OF TYCO ELECTRONICS CORPORATION, AND ARE TO BE HELD IN TRUST AND CONFIDENCE. PUBLICATION, DUPLICATION, DISCLOSURE OR USE FOR ANY PURPOSE NOT EXPRESSLY AUTHORIZED IN WRITING BY TYCO ELECTRONICS CORPORATION IS PROHIBITED.					
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE METRIC AND INCHES IN BRACKETS. DECIMAL TOLERANCES XXX ± 0,13 (.005) XX ± 0,25 (.01) X ± 0,50 (.10) ANGLE TOLERANCE .X ± 1 DEG.	DRAWN M Mazariegos 05/14/16	APPROVED W. KERNS 05/14/16	 TE Connectivity		
	RPN		TITLE Cap, Round End		
	CAD FILE: 101A011thru094_CD				
TYCO ELECTRONICS RESERVES THE RIGHT TO AMEND THIS DRAWING AT ANY TIME. USERS SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.	THIRD ANGLE PROJECTION		SIZE B	CODE IDENT. NO. 06090	DWG. NO. 101A011thru094
© 2012 Tyco Electronics Corporation. All rights reserved.			DO NOT SCALE THIS DRAWING		SHEET 1 OF 1