


NICKEL METAL HYDRIDE BATTERIES: INDIVIDUAL DATA SHEET

HHR75AAA/B Cylindrical AAA size (HR 11/45)

Dimensions (with Tube) (mm)



Specifications

	mm	inch
Diameter	10.5+0/-0.7	0.41+0/-0.03
Height	44.5+0/-1.0	1.75+0/-0.04
Approximate Weight	Grams	Ounces
	12	0.42

Nominal Voltage		1.2V	
Discharge Capacity*	Average**	730 mAh	
	Rated (Min.)	700 mAh	
Approx. Internal impedance at 1000Hz at charged state.		35mΩ	
Charge	Standard	70mA x 16hrs.	
	Rapid	450mA x 1.7 hrs.	
Ambient Temperature	Charge	Standard	°C
		Rapid	°F
	Discharge	Standard	0°C to 45°C
		Rapid	0°C to 40°C
	Storage	Standard	0°C to 45°C
		Rapid	0°C to 40°C
		Discharge	-10°C to 65°C
Ambient Temperature	Charge	Standard	°C
		Rapid	°F
	Discharge	Standard	0°C to 45°C
		Rapid	0°C to 40°C
	Storage	Standard	-10°C to 65°C
		Rapid	-10°C to 65°C
		Discharge	-10°C to 65°C
Ambient Temperature	Charge	Standard	°C
		Rapid	°F
	Discharge	Standard	0°C to 45°C
		Rapid	0°C to 40°C
	Storage	Standard	-10°C to 65°C
		Rapid	-10°C to 65°C
		Discharge	-10°C to 65°C

* After charging at 0.1It for 16 hours, discharging at 0.2It.

** For reference only.


Battery performance and cycle life are strongly affected by how they are used. In order to maximize battery safety, please consult Panasonic when determining charge / discharge specs, warning label contents and unit design.

Note: [It] was previously expressed as [C]. [It] is an IEC standard expression for the amount of charge or discharge current and is expressed as:

$$It(A) = Cn(Ah)/1h.$$

- [It] is the reference test current in amperes
- [Cn] is the rated capacity of the cell or battery in Ampere-hours.
- n = the time base [hours] for which the rated capacity is declared

Typical Charge Characteristics



Typical Discharge Characteristics

