

6 WATT

SINGLE OUTPUT SWITCHING ADAPTOR

WCR6.6-SX-Y-2 SERIES



GENERAL SPECIFICATION

The purpose of the document is to specify the functional requirements of a 6.6W switching AC adaptor.

Features:

- Two pin wall mount input plug
- Wide range AC input
- Level B EMI filter
- Fully enclosed plastic case
- Fully regulated output
- High efficiency
- High Quality

1) INPUT

Description	Min.	Nominal	Max.	Condition
Input Voltage	90VAC	100/240VAC	264VAC	Auto Range; 50/60Hz
Input Current(rms)	1.0 Arms Max. At any input voltage and Max. DC output rated load.			
Line Frequency	47Hz	50/60Hz	63Hz	-
Inrush Current	70 Amps Max. Cold start at 230 Vac input, with rated load and 25 °C ambient			
AC Leakage Current	1 mA Max. At 240Vac input			
Efficiency	60% Min. at full load and 115 VAC			

2) OUTPUT

Model No.	Nominal Voltage	Max. Power	Output Current		Line Regulation	Load Regulation	Ripple & Noise
			MIN.	MAX.			
WCR6.6-3.3SX-Y-2	3.3	6.6W	0.0A	2.0A	±1%	±5%	33mVp-p

NOTE: The ripple and noise are as follows when measure with Max. Bandwidth of 20 MHz and parallel 10uF/0.1uF, crossed connected at testing point.

- 2.1) Hold up time:** 12ms typical at full load @ 115VAC
- 2.2) Turn On Delay:** 2S Max. At 115Vac input and output Max. Load.
- 2.3) Rise Time:** 20mS Max. At 115Vac input and output Max. Load.
- 2.4) Overshoot:** 5% Max. When power supply at turn on or turn off.

3) PROTECTION:

3.1) Short Circuit Protection:

The power supply will be auto recovery when short circuit faults remove.

3.2) Over Power Protection:

120% ~ 180% active for 10W rated of power.
Total power protection at normal AC input voltage,
The power supply will be auto recovery.

3.3) Over Voltage Protection:

Build-in

4) ENVIRONMENT

4.1) Operating Temperature:

5°C to 40°C, Full load, Normal operation.

4.2) Storage Temperature:

-20°C to 85°C Without package

4.3) Relative Humidity:

5%(0°C) ~ 90%(40°C) RH, 72Hrs, Full load, Normal operating

4.4) Vibration:

4.4.1) Operating: IEC 721-3-2 2M2

5~9Hz, A=3.5mm

9~200Hz, Acceleration 5m/s²

4.4.2) Transportation: IEC 721-3-2 2M2

5~9Hz, A=3.5mm

9~200Hz, Acceleration=5m/s²

200~500Hz, Acceleration=15m/s²

3 Axes, 10 cycles per axis.

(No permanent damage may occur during testing.

The product has to restore to its original situation after power off/on.)

4.5) Dropping (packed):

1 corner, 3 edges, and 6 surfaces

(Height: 76 cm)

5) SAFETY REQUIREMENTS

5.1) Safety Or EMC Requirement:

5.1.1) Model with US Plug

UL 1950

CUL (CSA C22.2 No. 950-95)

FCC PART 15

CB EN60950

PSE

6) MECHANICAL REQUIREMENT:


6.1) Enclosure:

The adaptor size L:67×W:45×H:27mm

6.2) Input Connector:

Two pin wall mount input plug

6.3) Outline Drawing:



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ETA-USA:](#)

[WCR6.6-3.3SX-Y-2](#)