General Purpose Relay
MJN

Relay with Plug-in Termination, available in SPDT, DPDT or 3PDT models

- Rugged power driver offers superior 3/16” through-air and 3/8 over-surface spacing
- Interlocked frame and contact block prevent contact misalignment during plug-in
- Available with dust covers, indicator lamps and push-to-operate buttons
- UL and CSA recognition as motor controllers up to 600 VAC
- Recognized for 1/2 hp motor control applications at 240/480/600 VAC (1/3 hp at 120 VAC)

Ordering Information

To Order: Select part number and add the desired coil voltage rating (e.g. MJN1C-AC24).

Item			**Model**			
Type	**Terminal**	**Contact form**	**10A Version, flange mounting**	**20 A Version, flange mounting**	**30A Version, flange mounting**	**10 A Relay only**
Standard	Plug-in	SPDT	**MJN1CF**	---	**MJN1Z-E-RP**	**MJN1C**
		DPDT	**MJN2CF**	**MJN2CE**	---	**MJN2C**
		3PDT	**MJN3CF**	---	---	**MJN3C**
LED indicator	Plug-in	SPDT	**MJN1CF-N***	---	---	**MJN1C-N**
		DPDT	**MJN2CF-N***	---	---	**MJN2C-N**
		3PDT	**MJN3CF-N***	---	---	**MJN3C-N**
Push-to-operate button	Plug-in	SPDT	**MJN1CF-I***	---	---	**MJN1C-I**
		DPDT	**MJN2CF-I***	---	---	**MJN2C-I**
		3PDT	**MJN3CF-I***	---	---	**MJN3C-I**
Push-to-operate button & LED indicator	Plug-in	SPDT	**MJN1CF-IN***	---	---	**MJN1C-IN**
		DPDT	**MJN2CF-IN***	---	---	**MJN2C-IN**
		3PDT	**MJN3CF-IN***	---	---	**MJN3C-IN**
Latching	Plug-in	DPDT	---	---	---	**MJN2CK**

Note: All part numbers marked with an “*” are non-standard parts. Contact an Omron representative for additional information.

Specifications

■ Contact Data

Configuration		SPDT, DPDT, 3PDT
Initial contact resistance		50 mΩ max.
Materials		3/16" diameter Ag-Alloy
Contact UL ratings	**10 A**	10 amp @ 28 VDC and 120/240 VAC at 80% pf, 1/3 hp @ 120 VAC, 1/2 hp @ 277/240/480/600 VAC 8.5 FLA - 36 LRA at 18 VDC, 3 amp @ 480/600 VAC at 80% pf, 10 amp @ 277 VAC resistive
	20 A	20 amp @28 VDC and 120/240/277 VAC, 10 amp @ 480/600 VAC, 3.4 hp @ 120 VAC, 1-1/2 hp @ 240 VAC, 17 FLA - 65 LRA at 300VAC
	30 A	30 amp @ 28 VDC, 15 amp @ 480 / 600 VAC, 1hp @ 120 VAC, 1-1/2 hp @ 240 VAC
UL recognized file number		E41643

■ Coil Data

Non-latching - AC

Nominal voltage	**Resistance in Ohms ± 10%**		**Nominal coil power**		**Coil voltages**	**Insulation resistance**	**Pick up voltage at 25°C (77°F)**
	1 & 2 PDT	**3PDT**	**1 & 2 PDT**	**3PDT**			
6 VAC	6.0	4.2	1.7 VA	2.0 VA	6 to 240 VAC 50/60 Hz	1,000 MΩ min. @ 500 VDC	85% of nominal
12 VAC	21	18					
24 VAC	75	72					
120 VAC	2,250	1,700					
240 VAC	9,100	7,200					

Non-latching - DC

Nominal voltage	**Resistance in Ohms ± 10%**	**Nominal coil power**	**Coil voltages**	**Insulation resistance**	**Pick up voltage at 25°C (77°F)**
5 VDC	20	1.2 W	5 to 110 VDC	1,000 MΩ min. @ 500 VDC	75% of nominal
6 VDC	32				
12 VDC	120				
24 VDC	470				
48 VDC	1,800				
110 VDC	10,000				

Latching - AC

Nominal voltage	**Latch coil resistance in Ohms ± 10%**	**Unlatch coil resistance in Ohms ± 10%**	**Nominal coil power**		**Coil voltages**	**Insulation resistance**	**Operate voltage (latch/unlatch) at 25°C (77°F) (see note)**
6 VAC	5.5	105	1.7 VA	2.0 VA	6 to 240 VAC 50/60 Hz	1,000 MΩ min. @ 500 VDC	85% of nominal
12 VAC	22	445					
24 VAC	88	1,740					
120 VAC	2,090	17,430					

Note: 120% of nominal or greater (one second duration single pulse) unlatch voltage - - above this the relay latches again.
Maximum continuous voltage: 120% of nominal (one coil only).

Latching - DC

Nominal voltage	Latch coil resistance in Ohms ± 10%	Unlatch coil resistance in Ohms ± 10%	Nominal coil power	Coil voltages	Insulation resistance	Operate voltage (latch/unlatch) at 25°C (77°F) (see note)
5 VDC	14	45	1.2 W	5 to 110 VDC	1,000 MΩ min. @ 500 VDC	75% of nominal
6 VDC	20	64				
12 VDC	80	275				
24 VDC	330	1,070				
48 VDC	1,290	2,850				
110 VDC	5,125	10,750				

Note: 120% of nominal or greater (one second duration single pulse) unlatch voltage - - above this the relay latches again.
Maximum continuous voltage: 120% of nominal (one coil only).

■ Characteristics

Operate time			15 ms nominal; 20 ms maximum
Release time			6 ms nominal; 10 ms maximum
Latch time			13 ms nominal with a one second pulse of nominal voltage (See note)
Unlatch time			13 ms nominal with a one second pulse of nominal unlatch voltage after latching with a one second pulse of nominal latching voltage (See note)
Operating ambient temperature	**AC: 1 & 2 pole**	**Operating**	-45° to 60°C (-49° to 140°F)
		Storage	-65° to 100°C (-85° to 212°F)
	AC: 3 pole	**Operating**	-45° to 45°C (-49° to 113°F)
		Storage	-65° to 100°C (-85° to 212°F)
	DC: 1, 2 & 3 pole	**Operating**	-45° to 70°C (-49° to 158°F)
		Storage	-65° to 100°C (-85° to 212°F)
Insulation material			High quality phenolic
Duty cycle			Rated for continuous duty operation at 25% overvoltage
Shock			15 g's 11±1 ms (non-operating test, no mechanical damage)
Vibration			0.1" DA or 10 g's, 10 to 55 Hz (operating test, no contact chatter)
Life expectancy		**Electrical at rated load**	100,000 operations
		Mechanical	10,000,000 operations
Dielectric strength			Greater than 750 VAC, RMS 60 Hz across open contacts Greater than 2,500 VAC, RMS 60 Hz all other mutually insulated elements
Terminals			Quick Connect
Weight			64 g (2.3 oz) open relay 54 g (3.0 oz) enclosed relay

Note: A latch pulse of 50 ms minimum at nominal voltage is recommended to insure positive latching.

Terminal Arrangement

■ Non-Latching

Reference only



1 Form C (SPDT)



2 Form C (DPDT)



3 Form C (3PDT)

■ Latching / Unlatching



1 Form C (SPDT)



2 Form C (DPDT)

* C denoted common connection. On 3-pole relays the common connection is a wire lead coming off of the coil. It is not terminated to the relay header. Consult your Omron representative for single coil or isolated double coil models.

Dimensions

Unit: mm (inch)

■ Relays

MJN□CF/MJN2CE
Dust cover with mounting flanges



Dust cover MJN



■ Terminal-10 Amp Version



Note: Mates with .187" UL standard quick-connect terminals; also suitable for solder connection.

■ Terminal-20 and 30 Amp Versions



■ Hold Down Springs



Hold Down Springs Dimensional Reference chart

Part number	Reference dimension	Actual dimension
PYMJN-PCB	A	58.67 (2.31)
	B	53.82 (2.12)
	C	37.08 (1.46)
PYMJN-S	A	58.67 (2.31)
	B	53.59 (2.11)
	C	40.26 (1.59)

■ Sockets (for use with 10 Amp, non-flange mount versions)

PTF11PC









PTF21PC









PTFPCB



PTF11QDC



All sales are subject to Omron Electronic Components LLC standard terms and conditions of sale, which can be found at http://www.components.omron.com/components/web/webfiles.nsf/sales_terms.html

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.
To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

OMRON ELECTRONIC COMPONENTS LLC
55 E. Commerce Drive, Suite B
Schaumburg, IL 60173
847-882-2288

OMRON ON-LINE
Global - http://www.omron.com
USA - http://www.components.omron.com

Cat. No. X301-E-1b 09/11 Specifications subject to change without notice Printed in USA