




Technical Specifications

Typical Connection Diagram

The SSR driver output is allocated to SP1 and wired to switch the load (heater) using an SSR.

- F1 Fuse:** Time lag type to IEC127. CSA/UL rating 1A 250Vac
- F2 Fuse:** High Rupture Capacity (HRC) suitable for maximum rated load current
- S1 Switch:** IEC/CSA/UL approved disconnecting device



Ordering information codes 3300, 9300 & 9400

		Code
Model	48 x 24 mm	33
	48 x 48 mm	93
	48 x 48 mm dual display	94
Outputs Reversible	2A Ssd / relay	00
	2A relay / 1A relay	11
	Ssd / Ssd	22
Unused		00
Comms	None fitted	0
	RS232 fitted	2
	RS485 fitted	4
Supply	100–240V AC	0
	12–24V AC/DC	3
Custom code Please refer to CAL for details	Standard code	0

Ordering example 1 Model 3300 48x24mm, SSd/relay, RS485, 12–24V	Ordering example 2 Model 9400 48x48mm dual display, relay/relay, RS232, 100–240 VAC
33 00 00 4 3 0	94 11 00 2 0 0

Codes for additional software and hardware	
CALCOMMS charting & logging software	10 01 XX 3 0 0
CALCOMMS CD Rom demo-disk	0 0 0 1 2 4
Communications board RS232	3C 00 00 2 0 0
Communications board RS485	3C 00 00 4 0 0
RS232 to RS485 converter	3C 24 00 0 0 0

Notes
Models 3311, 9311, 9400, 9411 and 9422 are not currently available in low voltage 12–24V option.

Your nearest CAL contact;



CAL Controls Ltd
Bury Mead Road, Hitchin, Herts, SG5 1RT. UK
Tel: + 44 (0)1462-436161 Fax: + 44 (0)1462-451801
email: sales@cal-controls.co.uk
http://www.cal-controls.com

CAL Controls Inc
1580 S. Milwaukee Avenue, Libertyville, IL 60048. USA
Tel: (847) 680-7080 Fax: (847) 816-6852
email: sales@cal-controls.com
http://www.cal-controls.com

The CAL
range of
Temperature
Controllers



The range of Autotuning P.I.D. Temperature Controllers with RS232/485 Communications and Charting & Logging Software

CAL the pioneer of temperature control

CAL is a dynamic modern company and was the first to develop the 48x48mm ($\frac{1}{16}$ THDIN) analogue controller in 1976, the first digital controller in 1986, and the first 24x48mm ($\frac{1}{32}$ NDDIN) digital controller in 1992. CAL prides itself on technical competence, customer support and long-term supply of its range of controllers.



Model 9400
48 x 48 mm
($\frac{1}{16}$ TH DIN)



Model 9300
48 x 48 mm
($\frac{1}{16}$ TH DIN)



Model 3300
48 x 24 mm
($\frac{1}{32}$ ND DIN)

CAL's temperature controllers

These controllers are designed for ease of use, low-cost and reliability in demanding applications. They are already widely used in many industrial applications such as plastics, packaging, drying, ovens & furnaces and laboratory & scientific equipment. CAL's auto-tune makes P.I.D. control simple, just a few button presses will start the controller's self-tune which automatically selects the optimum P.I.D. values. Also CAL's unique dAC function is designed to minimise the overshoot problem associated with conventional P.I.D. control.


Functionality

- Easy-to-use Auto-tune program
- Simple menu-driven programming
- Full P.I.D. operation
- Single ramp/soak (dwell) program
- Heat-cool operation
- IP66 protection
- CE compliant

3-YEAR WARRANTY

Inputs and Outputs

- Thermocouple, PT100 (RTD) & mV
- Two outputs, SSR driver or Relay
- 5-alarm modes, full scale, deviation & band
- RS232 or RS485 (retrofitable)
- MODBUS RTU protocol



Technical Specifications

Thermocouple 9 types: Standards: CJC rejection: External resistance:		Type B,E,J,K,L,N,R,S,T IPTS/68/DIN 43710 20:1 (0.05°C) typical 100Ω maximum	General Displays:		Main, 4 digits high brightness green LED, 10mm high Lower (9400 only), 4 digits high brightness orange LED, 9mm high LED output indicators – flashing SP1 square green, SP2 round red 3 full travel elastomeric buttons
Resistance Temperature Detector – (RTD) RTD/Pt100 Standards: Bulb current:		2 wire DIN 43760 (100Ω 0°C/138.5Ω 100°C Pt) 0.2mA maximum	Keypad:		
Linear process inputs mV range:		0 to 50mV (0 to 20mV, 4 to 20mV)	Environmental Safety:		UL 873, EN 61010, CSA 22.2 No. 1010.1-92
Applicable to all inputs (SM = sensor maximum) Calibration accuracy: Sampling frequency: Common mode rejection: Series mode rejection: Temperature coefficient: Reference conditions:		±0.25%SM ±1°C input 10Hz, CJC 2 sec Negligible effect up to 140dB, 240V, 50-60Hz 60dB, 50-60Hz 150ppm/°C SM 22°C ±2°C, rated voltage after 15 minutes settling time	Humidity: Altitude: Installation: Pollution: Protection: EMC emission: EMC immunity: Ambient: Mouldings:		Max 80% up to 2000m Categories II and III Degree II NEMA 4X, IP66 EN50081-1, FCC Rules 15 subpart J Class A EN50082-2 0-50°C Flame retardant polycarbonate
Output devices SSd:		(Maximum 2 outputs) Solid state relay driver: to switch a remote SSR 5Vdc +0/-15% 15mA non-isolated Form A/SPST contacts (AgCdO) 2A/250 VAC resistive load Miniature power relay:	Dimensions Front facia		Models 9300/9400 – 51.0 x 51.0mm (includes gasket) Model 3300 – 51.0 x 28.5 (includes gasket) All models – 106.7mm (with gasket fitted) Models 9300/9400 – 44.8 x 44.8mm Model 3300 – 44.8 x 22.0mm All models – 116.2mm
2nd relay (option)		Form A/SPST contacts (AgCdO) 1A/250 VAC resistive load	Sleeve length Instrument Body		
			Overall length		
			Weights		3300-110g; 9300-120g; 9400-130g.

CALCOMMS™ unique and easy-to-use

CALCOMMS™ charting and Logging software is incredibly easy to use. It is designed to connect up to 128 temperature controllers by RS485 (RS232 is for one controller only) into a standard or industrial PC. This allows the user to program all functions of the controller and to data-log the recorded temperature. Unlike complicated SCADA software, CALCOMMS™ is a mini-SCADA package that does not need specialist knowledge or training.



Chart-recorder and Data-logging software

- Log up to 128 controllers
- Windows compatible NT or 95
- Easy to set-up

FREE demo-disk
CD demo of CALCOMMS®
charting & logging
software

CALCOMMS™ uses

- Easy configuration tool for controllers
- Data-logger for archiving process data
- Chart-recorder for viewing trend information
- On-screen display of temperature
- Software 'on-screen' alarms
- Cloning of controller settings to save time
- Save and re-use applications for multiple controllers
- Remote set-point adjustment

Ideal for:

Recording temperature information for statistical process requirements, quality control or health and safety purposes.

Applications:

Food industry, Dairy industry, Ovens, Furnaces, Kilns, Plastics machines, Laboratory and Scientific equipment, Bottling and beverage production and many other manufacturing industries.

Please ask for the applications guide for installing communicating controllers. CAL's technical manuals are available in French, German, Spanish, Italian and English, both in printed and Acrobat .pdf formats.

Visit our website for - pdf technical manuals, application notes, CALCOMMS demo and much more

www.cal-controls.com