# 5082-761x Series, 5082-762x Series, 5082-765x Series, 5082-766x Series, HDSP-360x Series/-460x Series



7.6 mm (0.3 inch)/10.9 mm (0.43 inch) Seven Segment Displays

# **Data Sheet**



# **Description**

The 7.6 mm (0.3 inch) and 10.9 mm (0.43 inch) LED seven segment displays are designed for viewing distances up to 3 metres (10 feet) and 5 metres (16 feet). These devices use an industry standard size package and pinouts. All devices are available as either common anode or common cathode.

#### **Features**

- Industry standard size
- Industry standard pinout
  - 7.62 mm (0.300 inch) DIP leads on 2.54 mm (0.100 inch) centers
- Choice of colors
  - High Efficiency Red, Yellow, Green
- Excellent appearance
  - Evenly lighted segments
  - ±50° viewing angle
  - Optimum contrast given by gray top surface for Green devices
  - Red top surface for HER devices
  - Yellow top surface for yellow devices

#### Features, continued

- Design flexibility
  - Common anode or common cathode
  - Single digits
  - Left or right hand decimal point ±1. overflow character
- Categorized for luminous intensity
  - Yellow and Green categorized for color
  - Use of like categories yields a uniform display
- High light output
- High peak current
- Excellent for long digit string multiplexing
- Intensity and color selection available
  - See Intensity and Color Selected Displays Data Sheet


#### **Devices**

HER <sup>[1]</sup>	Yellow	Green		
5082-	5082-	HDSP-	Description	<b>Package Drawing</b>
7610	7620	3600	7.6 mm Common Anode Left Hand Decimal	А
7611	7621	3601	7.6 mm Common Anode Right Hand Decimal	В
7613	7623	3603	7.6 mm Common Cathode Right Hand Decimal	C
7650		4600	10.9 mm Common Anode Left Hand Decimal	E
7651	7661	4601	10.9 mm Common Anode Right Hand Decimal	F
7653	7663	4603	10.9 mm Common Cathode Right Hand Decimal	G
7656	7666	4606	10.9 mm Universal $\pm$ 1. Overflow Right Hand Decimal <sup>[2]</sup>	Н

#### Notes:

- 1. These displays are recommended for high ambient light operation. Refer to the HDSP-335X HER data sheet for low current operation.
- 2. Universal pinout brings the anode and cathode of each segment's LED out to separate pins. See internal diagram H.

# **Part Number**




#### Notes:


- 1. For codes not listed in the figure above, please refer to the respective datasheet or contact your nearest Avago representative for details.
- 2. Bin options refer to shippable bins for a part number. Color and Intensity Bins are typically restricted to 1 bin per tube (exceptions may apply). Please refer to respective datasheet for specific bin limit information.

These displays are ideal for most displays are ideal for portable applications. Pin for pin equiva-applications. The high light lent displays are also available in ambient displays are ideal for a low current or high light high light ambients or long string ambient design. The low current lengths. For additional information see the Low Current Seven Segment Displays, or High Light Ambient Seven Segment Displays data sheets.

# **Package Dimensions**



# **Internal Circuit Diagram**



# **Absolute Maximum Ratings**

Description	HER 5082-7610/ 7650 Series	Yellow 5082-7620/ 7660 Series	Green HDSP-3600/ 4600 Series	Units
Average Power per Segment or DP	105	80	105	mW
Peak Forward Current per Segment or DP	90 <sup>[1]</sup>	60[3]	90 <sup>[5]</sup>	mA
DC Forward Current per Segment or DP	30[2]	20[4]	30[6]	mA
Operating Temperature Range		-40 to +100		°C
Storage Temperature Range	-55 to +100°C		°C	
Reverse Voltage* per Segment or DP		3.0 V		V
Wave Soldering Temperature for 3 sec (1.59 mm [0.063 in.] below Body)		250		°C

reverse voltage is for LED testing purposes and is not recommended to be used as an application condition.

- See Figure 1 to establish pulsed conditions.
  Derate above 46°C at 0.54 mA/°C.
  See Figure 6 to establish pulsed conditions.
  Derate above 53°C at 0.45 mA/°C.

- See Figure 7 to establish pulsed conditions.
  Derate above 81°C at 0.52 mA/°C.
- 5. See Figure 8 to establish pulsed conditions.
- 6. Derate above 39°C at 0.37 mA/°C.

# Electrical/Optical Characteristics at $T_A=25\ ^{\circ}C$

# **High Efficiency Red**

Device Series	Parameter	Symbol	Min.	Тур.	Max.	Units	<b>Test Conditions</b>
5082-761x	Luminous Intensity/Segment <sup>[1,2,5]</sup>	l <sub>V</sub>	340	800		μcd	$I_F = 5 \text{ mA}$
5082-765x	(Digit Average)		340	1115		μcd	$I_F = 5 \text{ mA}$
	Forward Voltage/Segment or DP	V <sub>F</sub>		2.1	2.5	V	I <sub>F</sub> = 20 mA
All	Peak Wavelength	$\lambda_{PEAK}$		635		nm	
	Dominant Wavelength <sup>[3]</sup>	$\lambda_{d}$		626		nm	
	Reverse Voltage/Segment or DP <sup>[4]</sup>	V <sub>R</sub>	3.0	30		V	$I_R = 100 \mu\text{A}$
	Temperature Coefficient of V <sub>F</sub> / Segment or DP	ΔV <sub>F</sub> /°C		-2		mV/°C	
	Thermal Resistance LED Junction-to-Pin	Rθ <sub>J-PIN</sub>		280		°C/W	

# Yellow

Device Series	Parameter	Symbol	Min.	Тур.	Max.	Units	Test Conditions
5082-762x	Luminous Intensity/Segment <sup>[1,2]</sup>	l <sub>V</sub>	205	620		μcd	$I_F = 5 \text{ mA}$
5082-766x	(Digit Average)		290	835		μcd	$I_F = 5 \text{ mA}$
	Forward Voltage/Segment or DP	V <sub>F</sub>		2.2	2.5	V	I <sub>F</sub> = 20 mA
	Peak Wavelength	$\lambda_{PEAK}$		583		nm	
	Dominant Wavelength <sup>[3,6]</sup>	$\lambda_{d}$	581.5	586	592.5	nm	
All	Reverse Voltage/Segment or DP <sup>[4]</sup>	V <sub>R</sub>	3.0	40		V	$I_R = 100 \mu\text{A}$
	Temperature Coefficient of V <sub>F</sub> / Segment or DP	$\Delta V_F/^{\circ}C$		-2		mV/°C	
	Thermal Resistance LED Junction-to-Pin	Rθ <sub>J-PIN</sub>		280		°C/W/Seg	

# **High Performance Green**

<b>Device Series</b>	Parameter	Symbol	Min.	Тур.	Max.	Units	<b>Test Conditions</b>
HDSP-360x	Luminous Intensity/Segment <sup>[1,2]</sup>	l <sub>V</sub>	860	2700		μcd	I <sub>F</sub> = 10 mA
HDSP-460x	(Digit Average)		1030	4000		μcd	$I_F = 10 \text{ mA}$
	Forward Voltage/Segment or DP	V <sub>F</sub>		2.1	2.5	V	I <sub>F</sub> = 10 mA
	Peak Wavelength	λρεακ		566		nm	
	Dominant Wavelength <sup>[3,6]</sup>	$\lambda_{d}$		571	577	nm	
All	Reverse Voltage/Segment or DP <sup>[4]</sup>	V <sub>R</sub>	3.0	50		V	$I_R = 100  \mu A$
	Temperature Coefficient of V <sub>F</sub> / Segment or DP	ΔV <sub>F</sub> /°C		-2		mV/°C	
	Thermal Resistance LED Junction-to-Pin	Rθ <sub>J-PIN</sub>		280		°C/W/Seg	

#### Notos

- 1. Device case temperature is 25 °C prior to the intensity measurement.
- 2. The digits are categorized for luminous intensity. The intensity category is designated by a letter on the side of the package.
- 3. The dominant wavelength,  $\lambda_d$ , is derived from the CIE chromaticity diagram and is that single wavelength which defines the color of the device.
- 4. Typical specification for reference only. Do not exceed absolute maximum ratings.
- 5. For low current operation, the HER HDSP-335X series displays are recommended. They are tested at 2 mA dc/segment and are pin for pin compatible with the 5082-7650 series.
- 6. The Yellow (5082-7620/7660) and Green (HDSP-3600/4600) displays are categorized for dominant wavelength. The category is designated by a number adjacent to the luminous intensity category letter.

# HER, Yellow, Green




Figure 1. Maximum Tolerable Peak Current vs. Pulse Duration – HER Series.




Figure 2. Maximum Tolerable Peak Current vs. Pulse Duration – Yellow Series.




Figure 3. Allowable Peak Current vs. Pulse Duration – Green Series.




Figure 4. Maximum Allowable DC Current vs. Ambient Temperature.




Figure 5. Forward Current vs. Forward Voltage.




Figure 6. Relative Luminous Intensity vs. DC Forward Current.




Figure 7. Relative Luminous Efficiency (Luminous Intensity per Unit Current) vs. Peak Current.

# **Intensity Bin Limits (mcd)**

# HER

5082-761x			
IV Bin Category	Min.	Max.	
В	0.369	0.630	
С	0.516	0.946	
D	0.774	1.418	
Е	1.160	2.127	
F	1.740	3.190	
G	2.610	4.785	
Н	3.915	7.177	

#### 5082-765x

3002 703X			
IV Bin Category	Min.	Max.	
В	0.347	0.593	
С	0.485	0.890	
D	0.728	1.333	
E	1.091	2.000	
F	1.636	3.000	
G	2.454	4.500	
Н	3.682	6.751	

# Yellow

# 5082-762x

JUUZ / UZX			
IV Bin Category	Min.	Max.	
В	0.229	0.387	
С	0.317	0.582	
D	0.476	0.872	
Е	0.714	1.311	
F	1.073	1.967	
G	1.609	2.950	
Н	2.413	4.425	

#### 5082-766x

IV Bin Category	Min.	Max.	
С	0.297	0.543	
D	0.445	0.817	
E	0.669	1.225	
F	1.003	1.838	
G	1.504	2.758	
Н	2.256	4.137	

#### Green

HDSP-360x			
IV Bin Category	Min.	Max.	
Н	0.86	1.58	
1	1.29	2.37	
J	1.94	3.55	
K	2.90	5.33	
L	4.37	8.01	

HDSP-460x			
IV Bin Category	Min.	Max.	
G	1.03	1.88	
Н	1.54	2.82	
I	2.31	4.23	
J	3.46	6.34	
K	5.18	9.50	
L	7.78	14.26	

# **Color Categories**

		Dominant Wa	avelength (nm)
Color	Bin	Min.	Max.
Yellow	1	581.50	585.00
	3	584.00	587.50
	2	586.50	590.00
	4	589.00	592.50
Green	2	573.00	577.00
	3	570.00	574.00
	4	567.00	571.00
	5	564.00	568.00

#### Note:

All categories are established for classification of products. Products may not be available in all categories. Please contact your Avago representatives for further clarification/information.

#### **Contrast Enhancement**

For information on contrast enhancement, please see Application Note 1015.

# **Soldering/Cleaning**

For information on soldering LEDs, please refer to Application Note 1027.

For product information and a complete list of distributors, please go to our web site:

www.avagotech.com

