

**HEYCO**




## Heyco-Flex™ Quick Twist Fittings with Finishing Collar Included\*

\*Collar not assembled

- Finishing collars neaten rough cut tubing edges. See page 2-11.
- One-piece solution with smooth internal surfaces provides for easier wire routing, protection, and installation.
- Easy, permanent assembly: the installer twists the tubing over the connector ferrule.
- Fittings are for use with Heyco-Flex II Tubing. See page 2-3.
- Unique locking fingers on Snap-In Hubs accommodate various panel thicknesses.
- All nylon construction is resistant to salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents. (This feature is not assessed by UL certification and testing.)
- If using a tapped hole, Teflon® tape is needed on the threads of the connector, for all other applications an O-ring and Locknut are needed to attain liquid tight.
- Suitable for a wide array of electrical applications:
  - Commercial and Industrial HVAC Systems
  - Motorized Equipment
  - Enclosed Power Sources
  - Garage Door Openers
  - Major Appliances
- **New! Assembly Tool** available for assembling Quick Twist Fittings into HF1 and HF2 Conduit and Tubing. See page 2-12.

FITS HF2 TUBING TRADE SIZE	A		PART NO. Black		PART DIMENSIONS							
	Mounting Hole Diameter		Snap-In Hub	NPT Hub	B Max O.A. Length	C Body or Thread Length		D Wrenching Nut Thickness		E Wrenching Flats/Flange Dia.		
	in.	mm.			in.	mm.	in.	mm.	in.	mm.	in.	mm.
Straight-Thru Style												
3/8	.875	22,2	8485FC	8487FC	For Straight-Thru, Snap-In Hub Part Dimensions, see page 2-11 For Straight-Thru, NPT Hub Part Dimensions, see page 2-12							
1/2	.875	22,2	8490FC	8493FC								
3/4	1.093	27,8	8495FC	8497FC								
90° Sweep Style												
3/8	.875	22,2	8500FC	8502FC	For 90° Sweep, Snap-In Hub Part Dimensions, see page 2-15 For 90° Sweep, NPT Hub Part Dimensions, see page 2-16							
1/2	.875	22,2	8505FC	8507FC								
3/4	1.093	27,8	8510FC	8512FC								

Standard Color: Black Fitting with **Black Collar**.



*Quick  
Specs*

**Material**  
**Certifications**  
**Flammability Rating**  
**Material Temperature Index**

Nylon 6/6  
See and File Numbers on pages 2-11, 2-12, 2-15, & 2-16  
94V-2  
Maximum temperature on part not to exceed 221°F (105°C)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[8510](#)