




# LTD- 322 323 SERIES

## 0.3" DUAL DIGIT NUMERIC DISPLAYS

### FEATURES

- 0.3 INCH (7.62mm) DIGIT HEIGHT.
- CONTINUOUS UNIFORM SEGMENTS.
- CHOICE OF THREE BRIGHT COLORS-RED/  
BRIGHT RED/GREEN.
- LOW POWER REQUIREMENT.
- EXCELLENT CHARACTERS APPEARANCE.
- HIGH CONTRAST.
- HIGH BRIGHTNESS.
- WIDE VIEWING ANGLE.
- SOLID STATE RELIABILITY.
- COMMON ANODE OR COMMON CATHODE  
MODELS.
- TWO DIGIT PACKAGE SIMPLIFIES ALIGNMENTS  
& ASSEMBLY.
- LEADS ON .100" (2.54mm) CENTERS.
- CATEGORIZED FOR LUMINOUS INTENSITY.
- I.C. COMPATIBLE.
- EASY MOUNTING ON P.C. BOARD.



### DESCRIPTION

The LTD-322/323 series are 0.3 inch (7.62 mm) height dual digit displays.

The red series devices utilize LED chips which are made from GaAsP on a GaAs substrate. The bright red and green series devices utilize LED chips which are made from GaP on a transparent GaP substrate. Red, bright red and green displays have black face and white segment color.


SEVEN-SEGMENT  
LED DISPLAYS

### DEVICES

| PART NO. LTD- |               |       | DESCRIPTION    | INTERNAL<br>CIRCUIT<br>DIAGRAM |
|---------------|---------------|-------|----------------|--------------------------------|
| RED           | BRIGHT<br>RED | GREEN |                |                                |
| 322R          | 322P          | 322G  | Common Cathode | A                              |
| 323R          | 323P          | 323G  | Common Anode   | B                              |

6-58  
533

## PACKAGE DIMENSIONS




NOTE: All dimensions are in  $\frac{\text{millimeters}}{\text{(inches)}}$ , tolerance is  $\frac{0.25\text{mm}}{(0.010'')}$  unless otherwise noted.

## PIN CONNECTION


| PIN NO. | CONNECTION               |                        |
|---------|--------------------------|------------------------|
|         | A. LTD-322               | B. LTD-323             |
| 1       | Anode G                  | Cathode G              |
| 2       | No Pin                   | No Pin                 |
| 3       | Anode A                  | Cathode A              |
| 4       | Anode F                  | Cathode F              |
| 5       | Common Cathode (Digit 2) | Common Anode (Digit 2) |
| 6       | Anode D                  | Cathode D              |
| 7       | Anode E                  | Cathode E              |
| 8       | Anode C                  | Cathode C              |
| 9       | Anode B                  | Cathode B              |
| 10      | Common Cathode (Digit 1) | Common Anode (Digit 1) |

## INTERNAL CIRCUIT DIAGRAM

A. LTD-322



B. LTP-323

ABSOLUTE MAXIMUM RATINGS AT  $T_A = 25^\circ\text{C}$ 

| PARAMETER                                                                | RED            | BRIGHT RED | GREEN | UNIT  |
|--------------------------------------------------------------------------|----------------|------------|-------|-------|
| Power Dissipation Per Segment                                            | 55             | 40         | 75    | mW    |
| Peak Forward Current Per Segment<br>(1/10 Duty Cycle, 0.1ms Pulse Width) | 160            | 60         | 100   | mA    |
| Continuous Forward Current Per Segment                                   | 25             | 15         | 25    | mA    |
| Derating Linear From 25°C Per Segment                                    | 0.3            | 0.18       | 0.3   | mA/°C |
| Reverse Voltage Per Segment                                              | 5              | 5          | 5     | V     |
| Operating Temperature Range                                              | -25°C to +85°C |            |       |       |
| Storage Temperature Range                                                | -25°C to +85°C |            |       |       |
| Solder Temperature 1/16 inch Below Seating Plane for 3 Seconds at 260°C  |                |            |       |       |

SEVEN-SEGMENT  
LED DISPLAYS

# ELECTRICAL/OPTICAL CHARACTERISTICS AT $T_A = 25^\circ\text{C}$ LTD-322R/323R

| PARAMETER                            | SYMBOL          | MIN. | TYP. | MAX. | UNIT           | TEST CONDITION       |
|--------------------------------------|-----------------|------|------|------|----------------|----------------------|
| Average Luminous Intensity           | $I_v$           | 200  | 400  |      | $\mu\text{cd}$ | $I_F = 10\text{ mA}$ |
| Peak Emission Wavelength             | $\lambda_p$     |      | 655  |      | nm             | $I_F = 20\text{ mA}$ |
| Spectral Line Half-Width             | $\Delta\lambda$ |      | 24   |      | nm             | $I_F = 20\text{ mA}$ |
| Reverse Current, any Segment or D.P. | $V_F$           |      | 1.7  | 2.0  | V              | $I_F = 20\text{ mA}$ |
| Reverse Current, any Segment or D.P. | $I_R$           |      |      | 100  | $\mu\text{A}$  | $V_R = 5\text{ V}$   |
| Luminous Intensity Matching Ratio    | $I_v\text{-m}$  |      |      | 2:1  |                | $I_F = 20\text{ mA}$ |

Note: The BIN brightness classification see page 6-160, category A

## TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

( $25^\circ\text{C}$  Ambient Temperature Unless Otherwise Noted)




Fig. 1 FORWARD CURRENT Vs. FORWARD VOLTAGE.




Fig. 2 SPECTRAL RESPONSE.




Fig. 3 RELATIVE LUMINOUS INTENSITY Vs. FORWARD CURRENT (PER SEGMENT).




Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Vs AMBIENT TEMPERATURE.




Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE.% (REFRESH RATE -  $F = 1\text{ KHz}$ )




Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE% (AVERAGE  $I_F = 10\text{ mA PER SEG.}$ )

# ELECTRICAL/OPTICAL CHARACTERISTICS AT $T_A = 25^\circ\text{C}$ LTD - 322P/323P

| PARAMETER                            | SYMBOL          | MIN. | TYP. | MAX. | UNIT           | TEST CONDITION       |
|--------------------------------------|-----------------|------|------|------|----------------|----------------------|
| Average Luminous intensity           | $I_v$           | 250  | 650  |      | $\mu\text{cd}$ | $I_F = 10\text{ mA}$ |
| Peak Emission Wavelength             | $\lambda_p$     |      | 697  |      | nm             | $I_F = 20\text{ mA}$ |
| Spectral Line Half-Width             | $\Delta\lambda$ |      | 90   |      | nm             | $I_F = 20\text{ mA}$ |
| Forward Voltage any Segment or D.P.  | $V_F$           |      | 2.1  | 2.8  | V              | $I_F = 20\text{ mA}$ |
| Reverse Current, any Segment or D.P. | $I_R$           |      |      | 100  | $\mu\text{A}$  | $V_R = 5\text{ V}$   |
| Luminous Intensity Matching Ratio    | $I_v\text{-m}$  |      |      | 2:1  |                | $I_F = 20\text{ mA}$ |

Note: The BIN brightness classification see page 6-160, category A

## TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

( $25^\circ\text{C}$  Ambient Temperature Unless Otherwise Noted)




Fig. 1 FORWARD CURRENT Vs. FORWARD VOLTAGE.




Fig. 2 SPECTRAL RESPONSE.




Fig. 3 RELATIVE, LUMINOUS INTENSITY Vs. FORWARD CURRENT (PER SEGMENT).




Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Vs AMBIENT TEMPERATURE.




Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE. (REFRESH RATE -  $F = 1\text{ KHz}$ )

SEVEN-SEGMENT  
LED DISPLAYS

# ELECTRICAL/OPTICAL CHARACTERISTICS AT $T_A = 25^\circ\text{C}$ LTD-322G/323G

| PARAMETER                            | SYMBOL          | MIN. | TYP. | MAX. | UNIT           | TEST CONDITION       |
|--------------------------------------|-----------------|------|------|------|----------------|----------------------|
| Average Luminous intensity           | $I_v$           | 600  | 1600 |      | $\mu\text{cd}$ | $I_F = 10\text{ mA}$ |
| Peak Emission Wavelength             | $\lambda_p$     |      | 565  |      | nm             | $I_F = 20\text{ mA}$ |
| Spectral Line Half-Width             | $\Delta\lambda$ |      | 30   |      | nm             | $I_F = 20\text{ mA}$ |
| Forward Voltage any Segment or D.P.  | $V_F$           |      | 2.1  | 2.8  | V              | $I_F = 20\text{ mA}$ |
| Reverse Current, any Segment or D.P. | $I_R$           |      |      | 100  | $\mu\text{A}$  | $V_R = 5\text{V}$    |
| Luminous Intensity Matching Ratio    | $I_v\text{-m}$  |      |      | 2:1  |                | $I_F = 20\text{ mA}$ |

Note: The BIN brightness classification see page 6-160, category A

## TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

( $25^\circ\text{C}$  Ambient Temperature Unless Otherwise Noted)




Fig. 1 FORWARD CURRENT Vs. FORWARD VOLTAGE.




Fig. 2 SPECTRAL RESPONSE.




Fig. 3 RELATIVE LUMINOUS INTENSITY Vs. FORWARD CURRENT (PER SEGMENT).




Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Vs AMBIENT TEMPERATURE.




Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE.% (REFRESH RATE -  $F = 1\text{ KHz}$ )




Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE% (AVERAGE  $I_F = 10\text{mA PER SEG.}$ )