

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

70984-4009

Status:


Active

Overview:

DMS-59®

Description:

1.27mm Pitch LFH™ Matrix 50 Plug Cable Kit, Terminal Stick, 40 Circuits, without Bus Bar



Series

image - Reference only

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-71626 \(PDF\)](#)
- [Application Specification AS-70929-001 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	I/O Connectors
Series	70984
Application	Wire-to-Board
Comments	Trimmed-Length without Carrier, Trim Length 3.30mm
Component Type	Terminal Stick
Overview	DMS-59®
Product Name	DMS59®, LFH™
Type	N/A
UPC	800754986595

Physical

Circuits (Loaded)	40
Circuits (maximum)	40
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.523/g
Orientation	Vertical
PCB Retention	N/A
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	1.905µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-20°C to +80°C
Termination Interface: Style	Through Hole
Wire Size AWG	28, 30, 32, 34, 36

Electrical

Current - Maximum per Contact	1A
Shielded	No
Voltage - Maximum	40V

Solder Process Data

Duration at Max. Process Temperature (seconds)	40
Lead-free Process Capability	SMC & Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	3
Process Temperature max. C	260

Material Info

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
70984Series

Mates With
LFH™ Matrix 50 Receptacle 71626

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Stick Insertion Tool	0622001700

Reference - Drawing Numbers

Application Specification

Product Specification

AS-70929-001

PS-71626

This document was generated on 10/03/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION