

Aluminum electrolytic capacitors

Capacitors with screw terminals

Series/Type: **B43740, B43760**

Date: November 2012

© EPCOS AG 2015. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.

Long-life grade capacitors

Applications


- Frequency converters
- Wind power converters
- Solar inverters
- Uninterruptible power supplies
- Professional power supplies

Features

- Outstanding reliability
- Good thermal characteristics and high ripple current capability
- Extra long useful life
- Wide temperature range
- All-welded constructions ensures reliable electrical contact
- PAPR terminals available (Protection Against Polarity Reversal)
- Version with optimized construction for base cooling (heat sink mounting) available
- Version with low-inductance design available
- RoHS-compatible


Construction

- Charge-discharge proof, polar
- Aluminum case with insulating sleeve
- Poles with screw terminal connections
- Mounting with ring clips, clamps or threaded stud
- The bases of types with threaded stud and $d \leq 76.9$ mm are not insulated, types with $d = 91$ mm have fully insulated bases



B43740

B43760



Specifications and characteristics in brief


Rated voltage V_R	350 ... 500 V DC		
Surge voltage V_S	$1.10 \cdot V_R$ (105 °C: $V_R \leq 400$ V DC and $V_R = 500$ V DC, 85 °C: $V_R = 450$ V DC)		
Rated capacitance C_R	1000 ... 18000 μ F		
Capacitance tolerance	$\pm 20\% \triangleq$ M		
Dissipation factor $\tan \delta$ (20 °C, 120 Hz)	≤ 0.20		
Leakage current I_{leak} (20 °C, 5 min)	$I_{leak} \leq 0.018 \mu A \cdot \left(\frac{C_R}{\mu F} \cdot \frac{V_R}{V} \right)^{0.85} + 4 \mu A$		
Self-inductance ESL	d = 51.6 mm: approx. 15 nH d \geq 64.3 mm: approx. 20 nH Capacitors with low-inductance design: d \geq 64.3 mm: approx. 13 nH		
Useful life ¹⁾ 105 °C; V_R ; $I_{AC,R}$ 85 °C; V_R ; $I_{AC,R}$ 40 °C; V_R ; $2.0 \cdot I_{AC,R}$	> 6000 h	Requirements: $\Delta C/C \leq \pm 15\%$ of initial value	
	> 30000 h	$\tan \delta \leq 1.75$ times initial specified limit	
	> 250000 h	$I_{leak} \leq$ initial specified limit	
Voltage endurance test 105 °C; V_R ; $I_{AC,R}$	2000 h	Post test requirements:	
		$\Delta C/C \leq \pm 10\%$ of initial value	
		$\tan \delta \leq 1.3$ times initial specified limit	
Vibration resistance test		$I_{leak} \leq$ initial specified limit	
		To IEC 60068-2-6, test Fc: Frequency range 10 ... 55 Hz, displacement amplitude 0.75 mm, acceleration max. 10 g, duration 3 \times 2 h. Capacitor mounted by its body which is rigidly clamped to the work surface.	
Characteristics at low temperature	Max. impedance ratio at 100 Hz	$Z_{-25^\circ C} / Z_{20^\circ C}$	4
		$Z_{-40^\circ C} / Z_{20^\circ C}$	10
IEC climatic category	To IEC 60068-1: 40/105/56 (–40 °C/+105 °C/56 days damp heat test)		
Detail specification	Similar to CECC 30301-803, CECC 30301-807		
Sectional specification	IEC 60384-4		

Ripple current capability

Due to the ripple current capability of the contact elements, the following current upper limits must not be exceeded:

Capacitor diameter	51.6 mm	64.3 mm	76.9 mm	91 mm
$I_{AC,max}$	34 A	45 A	57 A	80 A

1) Refer to chapter "General technical information, 5 Useful life" on how to interpret useful life.




B43740, B43760

Extra long useful life – 105 °C

Dimensional drawings


B43740: Ring clip/clamp mounting



M5: Min. reach of screw = 9.5 mm
9 mm for low inductance design
M6: Min. reach of screw = 12 mm
9.5 mm for low inductance design

Positive pole marking: +


B43760: Threaded stud mounting



The base of types with threaded stud and $d = 91$ mm is fully insulated (the lengths l and l_1 are increased by 0.5 mm in these cases). For types with threaded stud and $d \leq 76$ mm the base is not insulated. Also refer to the mounting instructions in chapter "Capacitors with screw terminals – Accessories".

Dimensions and weights

Ter- minal	Dimensions (mm) with insulating sleeve							Approx. weight (g)
	d	$l \pm 1$	$l_1 \pm 1$	$l_2 +0/-1$	d_1	d_2 max.	$a +0.2/-0.4$	
M5	51.6 +0/-0.8	80.7	87.2	17	M12	10.2	22.2	220
M5	51.6 +0/-0.8	105.7	112.2	17	M12	10.2	22.2	280
M5	51.6 +0/-0.8	118.2	124.7	17	M12	10.2	22.2	320
M5	51.6 +0/-0.8	130.7	137.2	17	M12	10.2	22.2	350
M5	64.3 +0/-0.8	80.7	87.2	17	M12	13.2	28.5	370
M5	64.3 +0/-0.8	105.7	112.2	17	M12	13.2	28.5	440
M5	64.3 +0/-0.8	118.2	124.7	17	M12	13.2	28.5	510
M5	64.3 +0/-0.8	130.7	137.2	17	M12	13.2	28.5	600
M5	64.3 +0/-0.8	143.2	149.7	17	M12	13.2	28.5	630
M6	76.9 +0/-0.7	105.7	111.5	17	M12	17.7	31.7	620
M6	76.9 +0/-0.7	118.2	124.0	17	M12	17.7	31.7	700
M6	76.9 +0/-0.7	130.7	136.5	17	M12	17.7	31.7	800
M6	76.9 +0/-0.7	143.2	149.0	17	M12	17.7	31.7	840
M6	76.9 +0/-0.7	168.7	174.5	17	M12	17.7	31.7	1000
M6	76.9 +0/-0.7	190.7	196.5	17	M12	17.7	31.7	1150
M6	76.9 +0/-0.7	220.7	226.5	17	M12	17.7	31.7	1300



Ter- minal	Dimensions (mm) with insulating sleeve							Approx. weight (g)
	d	l ±1	l ₁ ±1	l ₂ +0/-1	d ₁	d ₂ max.	a +0.2/-0.4	
M6	91.0 +0/-2	144.5	149.8	17	M12	17.7	31.7	1200
M6	91.0 +0/-2	170.0	175.3	17	M12	17.7	31.7	1400
M6	91.0 +0/-2	191.0	196.3	17	M12	17.7	31.7	1650
M6	91.0 +0/-2	202.0	207.3	17	M12	17.7	31.7	1750
M6	91.0 +0/-2	221.0	226.3	17	M12	17.7	31.7	1900

For low-inductance design the following deviation applies:

d = 64.3 mm: l₁ -0.7 mm

d = 91.0 mm: l₁ -1.7 mm


Packing

Capacitor diameter d (mm)	length l (mm)	Packing units (pcs.)
51.6	all	36
64.3	all	25

Capacitor diameter d (mm)	length l (mm)	Packing units (pcs.)
76.9	105.7 - 168.7	16
	190.7 - 220.7	12
91.0	all	9



For ecological reasons the packing is pure cardboard.



B43740, B43760

Extra long useful life – 105 °C

Special designs

■ Low-inductance design


For $V_R \leq 450$ V DC

■ PAPR terminal style

For $V_R \leq 450$ V DC

With our PAPR terminal style (**P**rotection **A**gainst **P**olarity **R**eversal) we offer an optional mechanical feature in addition to the visual polarity marking on the cover disk and the sleeve, which prevents from mounting in reverse polarity. The non-circular shape of the terminals and their arrangement perpendicular to each other enables the user to definitely prevent wrong mounting with respect to polarity (Poka Yoke).

Dimensional drawing of PAPR terminal configuration



Dimensions for PAPR terminal style (mm)


Can diameter d	Terminal	$d_3 \pm 0.1$	$d_4 \pm 0.1$	a +0.2/-0.4	Min. reach of screw	
					Standard design #050	For heat sink mounting #057
51.6	M5	10	13	22.2	9.5	—
64.3	M5	13	15	28.5	9.5	7.3
76.9	M6	13	15	31.7	12.0	9.7
91.0	M6	13	15	31.7	12.0	9.7

All other dimensions of the capacitor such as diameter d, case length l and overall length l_1 are identical with those of standard capacitors of this series. Please refer to the tables "Dimensions and weights" (standard types) and "Dimensions and weights for heat sink mounting" (special designs).

■ For heat sink mounting


Design for optimal connection of capacitors to the heat sink when using base cooling with the following features (refer to chapter "General technical information, 5.2 Cooling"):

- Electrical insulation of the capacitors base with 2 overlapping thermal pads for optimal heat flow (minimal thermal resistance at the capacitor base)



- Minimal overall length tolerance (± 0.35 mm) for mounting between heat sink and bus bar
- Case with extra groove near the base for clamp mounting (recommended ring clamp B44030A0165B ... A0190B)

This version is available only for capacitors without threaded stud and for diameters ≥ 64.3 mm. Regarding ripple current and useful life, please refer to column $I_{AC,R}(B)$ in the table "Technical data and ordering codes" and in the useful life curves.



KAL1008-K-E


Dimensions and weights for heat sink mounting:

Ter- minal	Dimensions (mm) with insulating sleeve					Min. reach of screw mm	Approx. weight g
	d	$l \pm 1$	$l_1 \pm 0.35$	d_2 max.	$a + 0.2/-0.4$		
M5	64.3 +0/-0.8	80.7	86.3	13.2	28.5	7.3	370
M5	64.3 +0/-0.8	105.7	111.3	13.2	28.5	7.3	440
M6	76.9 +0/-0.7	105.7	110.6	17.7	31.7	9.7	620
M6	76.9 +0/-0.7	143.2	148.1	17.7	31.7	9.7	840
M6	91.0 +0/-2	97.0	101.4	17.7	31.7	9.7	1000
M6	91.0 +0/-2	144.5	148.9	17.7	31.7	9.7	1200

Dimensions for other sizes are available upon request.

Ordering codes:

Design	Identification in third block of ordering code	Remark
Low inductance (13 nH)	M003	For capacitors with diameter $d \geq 64.3$ mm and $V_R \leq 450$ V DC
For heat sink mounting	M007	For capacitors with diameter $d \geq 64.3$ mm and without threaded stud
PAPR terminal style	M050	For capacitors with $V_R \leq 450$ V DC; not for low inductance
PAPR terminal style and heat sink mounting	M057	For capacitors with diameter $d \geq 64.3$ mm, $V_R \leq 450$ V DC and without threaded stud; not for low inductance



B43740, B43760

Extra long useful life – 105 °C


Accessories

The following items are included in the delivery package, but are not fastened to the capacitors:

	Thread	Toothed washers	Screws/nuts	Maximum torque
For terminals	M5	A 5.1 DIN 6797	DIN 7985 / ISO 7045-M5 × 10-5.6-Z	2.5 Nm thread depth $t \geq 8$ mm
	M6	A 6.4 DIN 6797	DIN 7985 / ISO 7045-M6 × 12-5.6-Z	4.0 Nm thread depth $t \geq 9.5$ mm
For mounting	M12	J 12.5 DIN 6797	Hex nut BM 12 DIN 439	10 Nm

The following items must be ordered separately. For details, refer to chapter "Capacitors with screw terminals – Accessories".

Item	Type
Ring clips	B44030
Clamps for capacitors with $d \geq 64.3$ mm	B44030
Insulating parts	B44020




Overview of available types

V _R (V DC)	350	400	450	500
	Case dimensions d × l (mm)			
C _R (μF)				
1000	51.6 × 80.7	51.6 × 80.7	51.6 × 105.7	51.6 × 118.2 64.3 × 80.7
1200				64.3 × 105.7
1500	51.6 × 80.7	51.6 × 105.7	51.6 × 118.2	64.3 × 105.7
1800				64.3 × 118.2 76.9 × 105.7
2200	51.6 × 105.7	51.6 × 130.7 64.3 × 105.7	64.3 × 118.2	76.9 × 105.7
2700	64.3 × 80.7	64.3 × 105.7	64.3 × 130.7	76.9 × 130.7
3300	64.3 × 105.7	64.3 × 130.7 76.9 × 105.7	64.3 × 143.2 76.9 × 130.7	76.9 × 143.2
3900	64.3 × 118.2	76.9 × 118.2	76.9 × 143.2	91.0 × 144.5
4700	64.3 × 143.2 76.9 × 105.7	76.9 × 130.7	76.9 × 168.7	76.9 × 190.7 91.0 × 170.0
5600	76.9 × 130.7	76.9 × 143.2	76.9 × 190.7 91.0 × 144.5	76.9 × 220.7 91.0 × 170.0
6800	76.9 × 143.2	76.9 × 168.7 91.0 × 144.5	76.9 × 220.7 91.0 × 170.0	91.0 × 202.0
8200	76.9 × 168.7 91.0 × 144.5	76.9 × 190.7 91.0 × 144.5	91.0 × 191.0	
10000	76.9 × 190.7 91.0 × 144.5	76.9 × 220.7 91.0 × 191.0	91.0 × 221.0	
12000	76.9 × 220.7 91.0 × 170.0	91.0 × 221.0		
15000	91.0 × 191.0			
18000	91.0 × 221.0			

The capacitance and voltage ratings listed above are available in different cases upon request.

Other voltage and capacitance ratings are also available upon request.



B43740, B43760

Extra long useful life – 105 °C

Technical data and ordering codes

C_R	Case dimensions	ESR_{typ}	Z_{max}	$I_{AC,max}$	$I_{AC,R}$	$I_{AC,R}(B)$	Ordering code (composition see below)
100 Hz	d × l	100 Hz	10 kHz	100 Hz	100 Hz	100 Hz	
20 °C	mm	20 °C	20 °C	40 °C	105 °C	105 °C	
μF		mΩ	mΩ	A	A	A	
$V_R = 350$ V DC							
1000	51.6 × 80.7	100	120	13	4.2	7.9	B437*0A4108M0##
1500	51.6 × 80.7	70	84	16	5.2	10.6	B437*0A4158M0##
2200	51.6 × 105.7	47	56	21	7.0	12.8	B437*0A4228M0##
2700	64.3 × 80.7	39	47	24	7.9	16.2	B437*0A4278M0##
3300	64.3 × 105.7	33	40	28	9.1	16.5	B437*0A4338M0##
3900	64.3 × 118.2	29	35	31	10.1	17.7	B437*0A4398M0##
4700	64.3 × 143.2	25	30	35	11.5	18.6	B437*0A4478M0##
4700	76.9 × 105.7	25	30	35	11.5	22.6	B437*0B4478M0##
5600	76.9 × 130.7	20	24	41	13.4	23.8	B437*0A4568M0##
6800	76.9 × 143.2	17	20	47	15.2	26.3	B437*0A4688M0##
8200	76.9 × 168.7	13	16	56	18.4	30.1	B437*0A4828M0##
8200	91.0 × 144.5	12	14	60	19.5	34.5	B437*0B4828M0##
10000	76.9 × 190.7	11	13	57	21.2	33.5	B437*0A4109M0##
10000	91.0 × 144.5	11	13	65	21.0	38.4	B437*0B4109M0##
12000	76.9 × 220.7	9	11	57	24.9	36.8	B437*0A4129M0##
12000	91.0 × 170.0	8	10	79	25.8	44.9	B437*0B4129M0##
15000	91.0 × 191.0	8	10	80	27.3	44.9	B437*0A4159M0##
18000	91.0 × 221.0	7	8	80	30.8	49.3	B437*0A4189M0##


Composition of ordering code

* = Mounting style

- 4 = for capacitors with ring clip/clamp mounting
- 6 = for capacitors with threaded stud

= Design

- 00 = for capacitors with standard inductance
- 03 = for capacitors with low inductance (13 nH)
(only for capacitors with diameter $d \geq 64.3$ mm and rated voltage ≤ 450 V DC)
- 07 = for heat sink mounting (only for capacitors with diameter $d \geq 64.3$ mm and without threaded stud)
- 50 = for terminals with PAPR style (only for rated voltage ≤ 450 V DC, not for low inductance)
- 57 = for terminals with PAPR style and heat sink mounting (only $d \geq 64.3$ mm, rated voltage ≤ 450 V DC and without threaded stud, not for low inductance)



Technical data and ordering codes

C_R	Case dimensions	ESR_{typ}	Z_{max}	$I_{AC,max}$	$I_{AC,R}$	$I_{AC,R}(B)$	Ordering code (composition see below)
100 Hz	$d \times l$	100 Hz	10 kHz	100 Hz	100 Hz	100 Hz	
20 °C	mm	20 °C	20 °C	40 °C	105 °C	105 °C	
μF		m Ω	m Ω	A	A	A	
$V_R = 400 \text{ V DC}$							
1000	51.6 × 80.7	100	120	13	4.3	8.5	B437*0A9108M0##
1500	51.6 × 105.7	65	78	18	5.8	10.5	B437*0A9158M0##
2200	51.6 × 130.7	39	47	26	8.3	13.9	B437*0B9228M0##
2200	64.3 × 105.7	45	54	23	7.6	13.5	B437*0A9228M0##
2700	64.3 × 105.7	35	42	28	9.0	16.5	B437*0A9278M0##
3300	64.3 × 130.7	29	35	32	10.4	17.5	B437*0A9338M0##
3300	76.9 × 105.7	29	35	32	10.6	20.5	B437*0B9338M0##
3900	76.9 × 118.2	24	29	37	12.0	22.2	B437*0A9398M0##
4700	76.9 × 130.7	20	24	42	13.7	24.6	B437*0A9478M0##
5600	76.9 × 143.2	17	20	48	15.6	27.1	B437*0A9568M0##
6800	76.9 × 168.7	15	18	54	17.5	28.9	B437*0A9688M0##
6800	91.0 × 144.5	14	17	56	18.3	32.8	B437*0B9688M0##
8200	76.9 × 190.7	13	16	57	20.0	31.6	B437*0A9828M0##
8200	91.0 × 144.5	12	14	63	20.6	37.8	B437*0B9828M0##
10000	76.9 × 220.7	10	12	57	24.4	37.8	B437*0A9109M0##
10000	91.0 × 191.0	9	11	77	25.0	41.4	B437*0B9109M0##
12000	91.0 × 221.0	7	8	80	29.9	47.2	B437*0A9129M0##

Composition of ordering code

* = Mounting style

4 = for capacitors with ring clip/clamp mounting

6 = for capacitors with threaded stud

= Design

00 = for capacitors with standard inductance


03 = for capacitors with low inductance (13 nH)

(only for capacitors with diameter
 $d \geq 64.3 \text{ mm}$ and rated voltage $\leq 450 \text{ V DC}$)

07 = for heat sink mounting (only for capacitors
with diameter $d \geq 64.3 \text{ mm}$ and without
threaded stud)

50 = for terminals with PAPR style (only for rated
voltage $\leq 450 \text{ V DC}$, not for low inductance)

57 = for terminals with PAPR style and heat sink
mounting (only $d \geq 64.3 \text{ mm}$, rated voltage
 $\leq 450 \text{ V DC}$ and without threaded stud, not
for low inductance)



B43740, B43760

Extra long useful life – 105 °C

Technical data and ordering codes

C_R	Case dimensions	ESR_{typ}	Z_{max}	$I_{AC,max}$	$I_{AC,R}$	$I_{AC,R(B)}$	Ordering code (composition see below)
100 Hz	d × l	100 Hz	10 kHz	100 Hz	100 Hz	100 Hz	
20 °C	mm	20 °C	20 °C	40 °C	105 °C	105 °C	
μF		mΩ	mΩ	A	A	A	
$V_R = 450$ V DC							
1000	51.6 × 105.7	95	114	14	4.7	8.2	B437*0A5108M0##
1500	51.6 × 118.2	63	76	19	6.2	10.7	B437*0A5158M0##
2200	64.3 × 118.2	43	52	25	8.1	13.9	B437*0A5228M0##
2700	64.3 × 130.7	33	40	30	9.8	16.2	B437*0A5278M0##
3300	64.3 × 143.2	27	32	35	11.4	18.4	B437*0B5338M0##
3300	76.9 × 130.7	27	32	35	11.4	19.9	B437*0A5338M0##
3900	76.9 × 143.2	23	28	40	12.9	21.8	B437*0A5398M0##
4700	76.9 × 168.7	20	24	45	14.7	23.5	B437*0A5478M0##
5600	76.9 × 190.7	17	20	52	16.8	25.8	B437*0A5568M0##
5600	91.0 × 144.5	16	19	53	17.3	30.6	B437*0B5568M0##
6800	76.9 × 220.7	14	17	57	19.7	30.6	B437*0A5688M0##
6800	91.0 × 170.0	13	16	62	20.1	39.1	B437*0B5688M0##
8200	91.0 × 191.0	10	12	74	24.1	39.1	B437*0A5828M0##
10000	91.0 × 221.0	8	10	80	28.6	44.2	B437*0A5109M0##

Composition of ordering code

* = Mounting style

4 = for capacitors with ring clip/clamp mounting

6 = for capacitors with threaded stud

= Design

00 = for capacitors with standard inductance


03 = for capacitors with low inductance (13 nH)
(only for capacitors with diameter

d ≥ 64.3 mm and rated voltage ≤ 450 V DC)

07 = for heat sink mounting (only for capacitors
with diameter d ≥ 64.3 mm and without
threaded stud)

50 = for terminals with PAPR style (only for rated
voltage ≤ 450 V DC, not for low inductance)

57 = for terminals with PAPR style and heat sink
mounting (only d ≥ 64.3 mm, rated voltage
≤ 450 V DC and without threaded stud, not
for low inductance)


Technical data and ordering codes

C_R	Case dimensions	ESR_{typ}	Z_{max}	$I_{AC,max}$	$I_{AC,R}$	$I_{AC,R(B)}$	Ordering code (composition see below)
100 Hz	d × l	100 Hz	10 kHz	100 Hz	100 Hz	100 Hz	
20 °C	mm	20 °C	20 °C	40 °C	105 °C	105 °C	
μF		mΩ	mΩ	A	A	A	
$V_R = 500$ V DC							
1000	51.6 × 118.2	91	109	14	4.7	7.5	B437*0A6108M0##
1000	64.3 × 80.7	91	109	14	4.6	8.7	B437*0B6108M0##
1200	64.3 × 105.7	76	91	16	5.3	8.7	B437*0A6128M0##
1500	64.3 × 105.7	61	73	19	6.1	10.8	B437*0A6158M0##
1800	64.3 × 118.2	51	61	21	7.0	11.8	B437*0A6188M0##
1800	76.9 × 105.7	51	61	22	7.1	12.8	B437*0B6188M0##
2200	76.9 × 105.7	42	50	25	8.2	15.8	B437*0A6228M0##
2700	76.9 × 130.7	34	41	30	9.7	16.6	B437*0A6278M0##
3300	76.9 × 143.2	28	34	34	11.1	18.4	B437*0A6338M0##
3900	91.0 × 144.5	24	28	39	12.6	21.3	B437*0A6398M0##
4700	76.9 × 190.7	20	24	43	14.1	21.2	B437*0A6478M0##
4700	91.0 × 170.0	20	24	42	13.8	22.0	B437*0B6478M0##
5600	76.9 × 220.7	17	20	49	16.1	22.6	B437*0A6568M0##
5600	91.0 × 170.0	17	20	49	15.8	26.2	B437*0B6568M0##
6800	91.0 × 202.0	14	17	56	18.1	27.8	B437*0A6688M0##


Composition of ordering code

* = Mounting style

- 4 = for capacitors with ring clip/clamp mounting
6 = for capacitors with threaded stud

= Design

- 00 = for capacitors with standard inductance
03 = for capacitors with low inductance (13 nH)
(only for capacitors with diameter
d ≥ 64.3 mm and rated voltage ≤ 450 V DC)
07 = for heat sink mounting (only for capacitors
with diameter d ≥ 64.3 mm and without
threaded stud)
50 = for terminals with PAPR style (only for rated
voltage ≤ 450 V DC, not for low inductance)
57 = for terminals with PAPR style and heat sink
mounting (only d ≥ 64.3 mm, rated voltage
≤ 450 V DC and without threaded stud, not
for low inductance)




B43740, B43760


Extra long useful life – 105 °C

Useful life¹⁾


depending on ambient temperature T_A (for natural cooling) and versus temperature of case base T_B (for base cooling) under ripple current operating conditions²⁾



Frequency factor of permissible ripple current I_{AC} versus frequency f




- 1) Refer to chapter "General technical information, 5 Useful life" on how to interpret useful life.
- 2) The ripple current refers to $I_{AC,R}$ for natural cooling or $I_{AC,R}(B)$ for base cooling, respectively.




Frequency characteristics of ESR


Typical behavior



Impedance Z versus frequency f

Typical behavior at 20 °C





B43740, B43760

Extra long useful life – 105 °C

Cautions and warnings

Personal safety

The electrolytes used by EPCOS have been optimized both with a view to the intended application and with regard to health and environmental compatibility. They do not contain any solvents that are detrimental to health, e.g. dimethyl formamide (DMF) or dimethyl acetamide (DMAC).

Furthermore, some of the high-voltage electrolytes used by EPCOS are self-extinguishing.


As far as possible, EPCOS does not use any dangerous chemicals or compounds to produce operating electrolytes. However, in exceptional cases, such materials must be used in order to achieve specific physical and electrical properties because no alternative materials are currently known. However, the amount of dangerous materials used in our products is limited to an absolute minimum.

Materials and chemicals used in EPCOS aluminum electrolytic capacitors are continuously adapted in compliance with the EPCOS Corporate Environmental Policy and the latest EU regulations and guidelines such as RoHS, REACH/SVHC, GADSL, and ELV.

MDS (Material Data Sheets) are available on the EPCOS website for all types listed in the data book. MDS for customer specific capacitors are available upon request.

MSDS (Material Safety Data Sheets) are available for all of our electrolytes upon request.

Nevertheless, the following rules should be observed when handling aluminum electrolytic capacitors: No electrolyte should come into contact with eyes or skin. If electrolyte does come into contact with the skin, wash the affected areas immediately with running water. If the eyes are affected, rinse them for 10 minutes with plenty of water. If symptoms persist, seek medical treatment. Avoid inhaling electrolyte vapor or mists. Workplaces and other affected areas should be well ventilated. Clothing that has been contaminated by electrolyte must be changed and rinsed in water.



Product safety

The table below summarizes the safety instructions that must be observed without fail. A detailed description can be found in the relevant sections of chapter "General technical information".


Topic	Safety information	Reference chapter "General technical information"
Polarity	Make sure that polar capacitors are connected with the right polarity.	1 "Basic construction of aluminum electrolytic capacitors"
Reverse voltage	Voltages polarity classes should be prevented by connecting a diode.	3.1.6 "Reverse voltage"
Mounting position of screw-terminal capacitors	Do not mount the capacitor with the terminals (safety vent) upside down.	11.1. "Mounting positions of capacitors with screw terminals"
Robustness of terminals	The following maximum tightening torques must not be exceeded when connecting screw terminals: M5: 2.5 Nm M6: 4.0 Nm	11.3 "Mounting torques"
Mounting of single-ended capacitors	The internal structure of single-ended capacitors might be damaged if excessive force is applied to the lead wires. Avoid any compressive, tensile or flexural stress. Do not move the capacitor after soldering to PC board. Do not pick up the PC board by the soldered capacitor. Do not insert the capacitor on the PC board with a hole space different to the lead space specified.	11.4 "Mounting considerations for single-ended capacitors"
Soldering	Do not exceed the specified time or temperature limits during soldering.	11.5 "Soldering"
Soldering, cleaning agents	Do not allow halogenated hydrocarbons to come into contact with aluminum electrolytic capacitors.	11.6 "Cleaning agents"
Upper category temperature	Do not exceed the upper category temperature.	7.2 "Maximum permissible operating temperature"
Passive flammability	Avoid external energy, such as fire or electricity.	8.1 "Passive flammability"



B43740, B43760


Extra long useful life – 105 °C

Topic	Safety information	Reference chapter "General technical information"
Active flammability	Avoid overload of the capacitors.	8.2 "Active flammability"
Maintenance	Make periodic inspections of the capacitors. Before the inspection, make sure that the power supply is turned off and carefully discharge the electricity of the capacitors. Do not apply any mechanical stress to the capacitor terminals.	10 "Maintenance"
Storage	Do not store capacitors at high temperatures or high humidity. Capacitors should be stored at +5 to +35 °C and a relative humidity of $\leq 75\%$.	7.3 Storage conditions
		Reference chapter "Capacitors with screw terminals"
Breakdown strength of insulating sleeves	Do not damage the insulating sleeve, especially when ring clips are used for mounting.	"Screw terminals – accessories"



Symbols and terms

Symbol	English	German
C	Capacitance	Kapazität
C_R	Rated capacitance	Nennkapazität
C_S	Series capacitance	Serienkapazität
$C_{S,T}$	Series capacitance at temperature T	Serienkapazität bei Temperatur T
C_f	Capacitance at frequency f	Kapazität bei Frequenz f
d	Case diameter, nominal dimension	Gehäusedurchmesser, Nennmaß
d_{max}	Maximum case diameter	Maximaler Gehäusedurchmesser
ESL	Self-inductance	Eigeninduktivität
ESR	Equivalent series resistance	Ersatzserienwiderstand
ESR_f	Equivalent series resistance at frequency f	Ersatzserienwiderstand bei Frequenz f
ESR_T	Equivalent series resistance at temperature T	Ersatzserienwiderstand bei Temperatur T
f	Frequency	Frequenz
I	Current	Strom
I_{AC}	Alternating current (ripple current)	Wechselstrom
$I_{AC,rms}$	Root-mean-square value of alternating current	Wechselstrom, Effektivwert
$I_{AC,f}$	Ripple current at frequency f	Wechselstrom bei Frequenz f
$I_{AC,max}$	Maximum permissible ripple current	Maximal zulässiger Wechselstrom
$I_{AC,R}$	Rated ripple current	Nennwechselstrom
$I_{AC,R} (B)$	Rated ripple current for base cooling	Nennwechselstromstrom für Bodenkühlung
I_{leak}	Leakage current	Reststrom
$I_{leak,op}$	Operating leakage current	Betriebsreststrom
l	Case length, nominal dimension	Gehäuselänge, Nennmaß
l_{max}	Maximum case length (without terminals and mounting stud)	Maximale Gehäuselänge (ohne Anschlüsse und Gewindebolzen)
R	Resistance	Widerstand
R_{ins}	Insulation resistance	Isolationswiderstand
R_{symm}	Balancing resistance	Symmetrierwiderstand
T	Temperature	Temperatur
ΔT	Temperature difference	Temperaturdifferenz
T_A	Ambient temperature	Umgebungstemperatur
T_C	Case temperature	Gehäusetemperatur
T_B	Capacitor base temperature	Temperatur des Becherbodens
t	Time	Zeit
Δt	Period	Zeitraum
t_b	Service life (operating hours)	Brauchbarkeitsdauer (Betriebszeit)



B43740, B43760

Extra long useful life – 105 °C

Symbol	English	German
V	Voltage	Spannung
V_F	Forming voltage	Formierspannung
V_{op}	Operating voltage	Betriebsspannung
V_R	Rated voltage, DC voltage	Nennspannung, Gleichspannung
V_S	Surge voltage	Spitzenspannung
X_C	Capacitive reactance	Kapazitiver Blindwiderstand
X_L	Inductive reactance	Induktiver Blindwiderstand
Z	Impedance	Scheinwiderstand
Z_T	Impedance at temperature T	Scheinwiderstand bei Temperatur T
$\tan \delta$	Dissipation factor	Verlustfaktor
λ	Failure rate	Ausfallrate
ϵ_0	Absolute permittivity	Elektrische Feldkonstante
ϵ_r	Relative permittivity	Dielektrizitätszahl
ω	Angular velocity; $2 \cdot \pi \cdot f$	Kreisfrequenz; $2 \cdot \pi \cdot f$

Note

All dimensions are given in mm.

Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or lifesaving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
6. Unless otherwise agreed in individual contracts, **all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI)**.
7. The trade names EPCOS, BAOKE, Alu-X, CeraDiode, CeraLink, CSMP, CSSP, CTVS, DeltaCap, DigiSiMic, DSSP, FilterCap, FormFit, MiniBlue, MiniCell, MKD, MKK, MLSC, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SIP5D, SIP5K, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.