

Duplex Multimode 62.5/125 Fiber Patch Cable (MTRJ/SC), 11M (36-ft.)

MODEL NUMBER: N310-11M



Highlights

- Premium PVC 62.5/125µm multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards

Package Includes

- 11-meter (35ft) Duplex MMF Cable MTRJ/SC 62.5/125 Fiber

Description

Tripp Lite's 11-meter (35ft) multimode duplex fiber optic MTRJ/SC patch cable is manufactured from 62.5/125 zipcord fiber. The cable has MTRJ to SC connectors, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 11-meters (35ft) Connectors: MTRJ to 2 SC
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Color coded shrouds identify transmit and receive
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

General Info	
Product Group	NETWORK CABLES
OVERVIEW	
Fiber Type	62.5/125 - OM1
Intended Application	Computer Networking (Fiber)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Type	MULTIMODE 62.5/125 FIBER OPTIC
Model Type	MTRJ/SC
Network Speed	1Gbps
INPUT	
Cable Length (m)	11
UPC ASSIGNMENT	
Unit Carton UPC#	037332135087
PHYSICAL	
Color	Orange
Style	Fiber Optic
CONNECTIONS	
Connector A	MTRJ
Connector B	SC
Number of Connectors	3
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.