







10 9 8 7 6 5 4 3 2 1


ENG. NO.		Au. PLATE THICKNESS (μ m MIN.)
FORM: LOOSE	FORM: CHAIN	
50394-8100	50394-8051	0.38
50394-8200	50394-8052	0.76
50394-8400	50394-8054	GOLD FLASH 0.05-0.125 μ m



B-B




A-A



NOTES :

1. APPLICABLE HOUSING : 51110-***1
: 51110-**5*

WINDING DIRECTION



VIEW Z

TO ASSEMBLY

VIEW Z

ADD WINDING DIRECTION EC NO: S2014-0327 2013/09/30 DRWN:ATSEE CHKD:FANNYWONG 2013/09/30 APPR:LBLEE 2013/11/13	DESCRIPTION	QUALITY SYMBOLS F =0 F =0 F =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY S.Q	DATE 1994/04/20	TITLE SALES DRAWING 2.0MM GRID W TO B CONN. CRIMP TERMINAL		
			4 PLACES	± ---	± ---	CHECKED BY EDPOH	DATE 1994/04/27			
			3 PLACES	± ---	± ---	APPROVED BY BBYEE	DATE 2013/04/28			
			2 PLACES	± 0.20	± ---					
			1 PLACE	± ---	± ---			DOCUMENT NO. SD-50394-8XXX		SHEET NO. 1 OF 1
			0 PLACE	± ---	± ---					
			ANGULAR ± 3 °		MATERIAL NO.					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE					
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

9 8 7 6 5 4 3 2 1