

# 74AC244, 74ACT244

## Octal Buffer/Line Driver with 3-STATE Outputs

### Features

- $I_{CC}$  and  $I_{OZ}$  reduced by 50%
- 3-STATE outputs drive bus lines or buffer memory address registers
- Outputs source/sink 24mA
- ACT244 has TTL-compatible inputs

### General Description

The AC/ACT244 is an octal buffer and line driver designed to be employed as a memory address driver, clock driver and bus-oriented transmitter/receiver which provides improved PC board density.

### Ordering Information


| Order Number | Package Number | Package Description                                                         |
|--------------|----------------|-----------------------------------------------------------------------------|
| 74AC244SC    | M20B           | 20-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300" Wide  |
| 74AC244SJ    | M20D           | 20-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide               |
| 74AC244MTC   | MTC20          | 20-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide |
| 74AC244PC    | N20A           | 20-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300" Wide      |
| 74ACT244SC   | M20B           | 20-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300" Wide  |
| 74ACT244SJ   | M20D           | 20-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide               |
| 74ACT244MSA  | MSA20          | 20-Lead Shrink Small Outline Package (SSOP), JEDEC MO-150, 5.3mm Wide       |
| 74ACT244MTC  | MTC20          | 20-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide |
| 74ACT244PC   | N20A           | 20-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300" Wide      |

Device also available in Tape and Reel. Specify by appending suffix letter "X" to the ordering number.



All packages are lead free per JEDEC: J-STD-020B standard.


Connection Diagram



Pin Description

| Pin Names                          | Description                  |
|------------------------------------|------------------------------|
| $\overline{OE}_1, \overline{OE}_2$ | 3-STATE Output Enable Inputs |
| $I_0-I_7$                          | Inputs                       |
| $O_0-O_7$                          | Outputs                      |

Logic Symbol



Truth Tables

| Inputs            |       | Outputs               |
|-------------------|-------|-----------------------|
| $\overline{OE}_1$ | $I_n$ | (Pins 12, 14, 16, 18) |
| L                 | L     | L                     |
| L                 | H     | H                     |
| H                 | X     | Z                     |

| Inputs            |       | Outputs           |
|-------------------|-------|-------------------|
| $\overline{OE}_2$ | $I_n$ | (Pins 3, 5, 7, 9) |
| L                 | L     | L                 |
| L                 | H     | H                 |
| H                 | X     | Z                 |

X = Immaterial  
Z = High Impedance

## Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

| Symbol                | Parameter                                    | Rating                   |
|-----------------------|----------------------------------------------|--------------------------|
| $V_{CC}$              | Supply Voltage                               | −0.5V to +7.0V           |
| $I_{IK}$              | DC Input Diode Current<br>$V_I = -0.5V$      | −20mA                    |
|                       | $V_I = V_{CC} + 0.5$                         | +20mA                    |
| $V_I$                 | DC Input Voltage                             | −0.5V to $V_{CC} + 0.5V$ |
| $I_{OK}$              | DC Output Diode Current<br>$V_O = -0.5V$     | −20mA                    |
|                       | $V_O = V_{CC} + 0.5V$                        | +20mA                    |
| $V_O$                 | DC Output Voltage                            | −0.5V to $V_{CC} + 0.5V$ |
| $I_O$                 | DC Output Source or Sink Current             | ±50mA                    |
| $I_{CC}$ or $I_{GND}$ | DC $V_{CC}$ or Ground Current per Output Pin | ±50mA                    |
| $T_{STG}$             | Storage Temperature                          | −65°C to +150°C          |
| $T_J$                 | Junction Temperature                         | 140°C                    |

## Recommended Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to absolute maximum ratings.

| Symbol                | Parameter                                                                                                  | Rating         |
|-----------------------|------------------------------------------------------------------------------------------------------------|----------------|
| $V_{CC}$              | Supply Voltage<br>AC                                                                                       | 2.0V to 6.0V   |
|                       | ACT                                                                                                        | 4.5V to 5.5V   |
| $V_I$                 | Input Voltage                                                                                              | 0V to $V_{CC}$ |
| $V_O$                 | Output Voltage                                                                                             | 0V to $V_{CC}$ |
| $T_A$                 | Operating Temperature                                                                                      | −40°C to +85°C |
| $\Delta V / \Delta t$ | Minimum Input Edge Rate, AC Devices:<br>$V_{IN}$ from 30% to 70% of $V_{CC}$ , $V_{CC}$ @ 3.3V, 4.5V, 5.5V | 125mV/ns       |
| $\Delta V / \Delta t$ | Minimum Input Edge Rate, ACT Devices:<br>$V_{IN}$ from 0.8V to 2.0V, $V_{CC}$ @ 4.5V, 5.5V                 | 125mV/ns       |

## DC Electrical Characteristics for AC

| Symbol                         | Parameter                                     | V <sub>CC</sub> (V) | Conditions                                                                                                                                             | T <sub>A</sub> = +25°C |                   | T <sub>A</sub> = −55°C to +125°C | T <sub>A</sub> = −40°C to +85°C | Units |
|--------------------------------|-----------------------------------------------|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------|-------------------|----------------------------------|---------------------------------|-------|
|                                |                                               |                     |                                                                                                                                                        | Typ.                   | Guaranteed Limits |                                  |                                 |       |
| V <sub>IH</sub>                | Minimum HIGH Level Input Voltage              | 3.0                 | V <sub>OUT</sub> = 0.1V or V <sub>CC</sub> − 0.1V                                                                                                      | 1.5                    | 2.1               | 2.1                              | 2.1                             | V     |
|                                |                                               | 4.5                 |                                                                                                                                                        | 2.25                   | 3.15              | 3.15                             | 3.15                            |       |
|                                |                                               | 5.5                 |                                                                                                                                                        | 2.75                   | 3.85              | 3.85                             | 3.85                            |       |
| V <sub>IL</sub>                | Maximum LOW Level Input Voltage               | 3.0                 | V <sub>OUT</sub> = 0.1V or V <sub>CC</sub> − 0.1V                                                                                                      | 1.5                    | 0.9               | 0.9                              | 0.9                             | V     |
|                                |                                               | 4.5                 |                                                                                                                                                        | 2.25                   | 1.35              | 1.35                             | 1.35                            |       |
|                                |                                               | 5.5                 |                                                                                                                                                        | 2.75                   | 1.65              | 1.65                             | 1.65                            |       |
| V <sub>OH</sub>                | Minimum HIGH Level Output Voltage             | 3.0                 | I <sub>OUT</sub> = −50μA                                                                                                                               | 2.99                   | 2.9               | 2.9                              | 2.9                             | V     |
|                                |                                               | 4.5                 |                                                                                                                                                        | 4.49                   | 4.4               | 4.4                              | 4.4                             |       |
|                                |                                               | 5.5                 |                                                                                                                                                        | 5.49                   | 5.4               | 5.4                              | 5.4                             |       |
|                                |                                               | 3.0                 | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub> , I <sub>OH</sub> = 12mA                                                                          |                        | 2.56              | 2.4                              | 2.46                            |       |
|                                |                                               | 4.5                 | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub> , I <sub>OH</sub> = 24mA                                                                          |                        | 3.86              | 3.7                              | 3.76                            |       |
|                                |                                               | 5.5                 | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub> , I <sub>OH</sub> = 24mA <sup>(1)</sup>                                                           |                        | 4.86              | 4.7                              | 4.76                            |       |
| V <sub>OL</sub>                | Maximum LOW Level Output Voltage              | 3.0                 | I <sub>OUT</sub> = 50μA                                                                                                                                | 0.002                  | 0.1               | 0.1                              | 0.1                             | V     |
|                                |                                               | 4.5                 |                                                                                                                                                        | 0.001                  | 0.1               | 0.1                              | 0.1                             |       |
|                                |                                               | 5.5                 |                                                                                                                                                        | 0.001                  | 0.1               | 0.1                              | 0.1                             |       |
|                                |                                               | 3.0                 | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub> , I <sub>OL</sub> = 12mA                                                                          |                        | 0.36              | 0.50                             | 0.44                            |       |
|                                |                                               | 4.5                 | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub> , I <sub>OL</sub> = 24mA                                                                          |                        | 0.36              | 0.50                             | 0.44                            |       |
|                                |                                               | 5.5                 | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub> , I <sub>OL</sub> = 24mA <sup>(1)</sup>                                                           |                        | 0.36              | 0.50                             | 0.44                            |       |
| I <sub>IN</sub> <sup>(2)</sup> | Maximum Input Leakage Current                 | 5.5                 | V <sub>I</sub> = V <sub>CC</sub> , GND                                                                                                                 |                        | ±0.1              | ±1.0                             | ±1.0                            | μA    |
| I <sub>OZ</sub>                | Maximum 3-STATE Leakage Current               | 5.5                 | V <sub>I</sub> (OE) = V <sub>IL</sub> , V <sub>IH</sub> ; V <sub>I</sub> = V <sub>CC</sub> , V <sub>GND</sub> ; V <sub>O</sub> = V <sub>CC</sub> , GND |                        | ±0.25             | ±5.0                             | ±2.5                            | μA    |
| I <sub>OLD</sub>               | Minimum Dynamic Output Current <sup>(3)</sup> | 5.5                 | V <sub>OLD</sub> = 1.65V Max.                                                                                                                          |                        |                   | 50                               | 75                              | mA    |
| I <sub>OHD</sub>               |                                               | 5.5                 | V <sub>OHD</sub> = 3.85V Min.                                                                                                                          |                        |                   | −50                              | −75                             | mA    |
| I <sub>CC</sub> <sup>(2)</sup> | Maximum Quiescent Supply Current              | 5.5                 | V <sub>IN</sub> = V <sub>CC</sub> or GND                                                                                                               |                        | 4.0               | 80.0                             | 40.0                            | μA    |

## Notes:

1. All outputs loaded; thresholds on input associated with output under test.
2. I<sub>IN</sub> and I<sub>CC</sub> @ 3.0V are guaranteed to be less than or equal to the respective limit @ 5.5V V<sub>CC</sub>.
3. Maximum test duration 2.0ms, one output loaded at a time.

## DC Electrical Characteristics for ACT

| Symbol           | Parameter                                     | V <sub>CC</sub> (V) | Conditions                                                                                      | T <sub>A</sub> = +25°C |                   | T <sub>A</sub> = -55°C<br>to +125°C | T <sub>A</sub> = -40°C<br>to +85°C | Units |
|------------------|-----------------------------------------------|---------------------|-------------------------------------------------------------------------------------------------|------------------------|-------------------|-------------------------------------|------------------------------------|-------|
|                  |                                               |                     |                                                                                                 | Typ.                   | Guaranteed Limits |                                     |                                    |       |
| V <sub>IH</sub>  | Minimum HIGH Level Input Voltage              | 4.5                 | V <sub>OUT</sub> = 0.1V or<br>V <sub>CC</sub> - 0.1V                                            | 1.5                    | 2.0               | 2.0                                 | 2.0                                | V     |
|                  |                                               | 5.5                 |                                                                                                 | 1.5                    | 2.0               | 2.0                                 | 2.0                                |       |
| V <sub>IL</sub>  | Maximum LOW Level Input Voltage               | 4.5                 | V <sub>OUT</sub> = 0.1V or<br>V <sub>CC</sub> - 0.1V                                            | 1.5                    | 0.8               | 0.8                                 | 0.8                                | V     |
|                  |                                               | 5.5                 |                                                                                                 | 1.5                    | 0.8               | 0.8                                 | 0.8                                |       |
| V <sub>OH</sub>  | Minimum HIGH Level Output Voltage             | 4.5                 | I <sub>OUT</sub> = -50μA                                                                        | 4.49                   | 4.4               | 4.4                                 | 4.4                                | V     |
|                  |                                               | 5.5                 |                                                                                                 | 5.49                   | 5.4               | 5.4                                 | 5.4                                |       |
|                  |                                               | 4.5                 | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub> ,<br>I <sub>OH</sub> = 24mA                |                        | 3.86              | 3.70                                | 3.76                               |       |
|                  |                                               | 5.5                 | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub> ,<br>I <sub>OH</sub> = 24mA <sup>(4)</sup> |                        | 4.86              | 4.70                                | 4.76                               |       |
| V <sub>OL</sub>  | Maximum LOW Level Output Voltage              | 4.5                 | I <sub>OUT</sub> = 50μA                                                                         | 0.001                  | 0.1               | 0.1                                 | 0.1                                | V     |
|                  |                                               | 5.5                 |                                                                                                 | 0.001                  | 0.1               | 0.1                                 | 0.1                                |       |
|                  |                                               | 4.5                 | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub> ,<br>I <sub>OL</sub> = 24mA                |                        | 0.36              | 0.50                                | 0.44                               |       |
|                  |                                               | 5.5                 | V <sub>IN</sub> = V <sub>IL</sub> or V <sub>IH</sub> ,<br>I <sub>OL</sub> = 24mA <sup>(4)</sup> |                        | 0.36              | 0.50                                | 0.44                               |       |
| I <sub>IN</sub>  | Maximum Input Leakage Current                 | 5.5                 | V <sub>I</sub> = V <sub>CC</sub> , GND                                                          |                        | ±0.1              | ±1.0                                | ±1.0                               | μA    |
| I <sub>OZ</sub>  | Maximum 3-STATE Leakage Current               | 5.5                 | V <sub>I</sub> = V <sub>IL</sub> , V <sub>IH</sub> ;<br>V <sub>O</sub> = V <sub>CC</sub> , GND  |                        | ±0.25             | ±5.0                                | ±2.5                               | μA    |
| I <sub>CCT</sub> | Maximum I <sub>CC</sub> /Input                | 5.5                 | V <sub>I</sub> = V <sub>CC</sub> - 2.1V                                                         | 0.6                    |                   | 1.6                                 | 1.5                                | mA    |
| I <sub>OLD</sub> | Minimum Dynamic Output Current <sup>(5)</sup> | 5.5                 | V <sub>OLD</sub> = 1.65V Max.                                                                   |                        |                   | 50                                  | 75                                 | mA    |
| I <sub>OHD</sub> |                                               | 5.5                 | V <sub>OHD</sub> = 3.85V Min.                                                                   |                        |                   | -50                                 | -75                                | mA    |
| I <sub>CC</sub>  | Maximum Quiescent Supply Current              | 5.5                 | V <sub>IN</sub> = V <sub>CC</sub> or GND                                                        |                        | 4.0               | 80.0                                | 40.0                               | μA    |

**Notes:**

4. All outputs loaded; thresholds on input associated with output under test.
5. Maximum test duration 2.0ms, one output loaded at a time.

**AC Electrical Characteristics for AC**

| Symbol    | Parameter                            | $V_{CC}$ (V) <sup>(6)</sup> | $T_A = +25^\circ\text{C}$ ,<br>$C_L = 50\text{pF}$ |      |      | $T_A = -55^\circ\text{C}$<br>to $+125^\circ\text{C}$ ,<br>$C_L = 50\text{pF}$ |      | $T_A = -40^\circ\text{C}$<br>to $+85^\circ\text{C}$ ,<br>$C_L = 50\text{pF}$ |      | Units |
|-----------|--------------------------------------|-----------------------------|----------------------------------------------------|------|------|-------------------------------------------------------------------------------|------|------------------------------------------------------------------------------|------|-------|
|           |                                      |                             | Min.                                               | Typ. | Max. | Min.                                                                          | Max. | Min.                                                                         | Max. |       |
| $t_{PLH}$ | Propagation Delay,<br>Data to Output | 3.3                         | 2.0                                                | 6.5  | 9.0  | 1.0                                                                           | 12.5 | 1.5                                                                          | 10.0 | ns    |
|           |                                      | 5.0                         | 1.5                                                | 5.0  | 7.0  | 1.0                                                                           | 9.5  | 1.0                                                                          | 7.5  |       |
| $t_{PHL}$ | Propagation Delay,<br>Data to Output | 3.3                         | 2.0                                                | 6.5  | 9.0  | 1.0                                                                           | 12.0 | 2.0                                                                          | 10.0 | ns    |
|           |                                      | 5.0                         | 1.5                                                | 5.0  | 7.0  | 1.0                                                                           | 9.0  | 1.0                                                                          | 7.5  |       |
| $t_{PZH}$ | Output Enable Time                   | 3.3                         | 2.0                                                | 6.0  | 10.5 | 1.0                                                                           | 11.5 | 1.5                                                                          | 11.0 | ns    |
|           |                                      | 5.0                         | 1.5                                                | 5.0  | 7.0  | 1.0                                                                           | 9.0  | 1.5                                                                          | 8.0  |       |
| $t_{PZL}$ | Output Enable Time                   | 3.3                         | 2.5                                                | 7.5  | 10.0 | 1.0                                                                           | 13.0 | 2.0                                                                          | 11.0 | ns    |
|           |                                      | 5.0                         | 1.5                                                | 5.5  | 8.0  | 1.0                                                                           | 10.5 | 1.5                                                                          | 8.5  |       |
| $t_{PHZ}$ | Output Disable Time                  | 3.3                         | 3.0                                                | 7.0  | 10.0 | 1.0                                                                           | 12.5 | 1.5                                                                          | 10.5 | ns    |
|           |                                      | 5.0                         | 2.5                                                | 6.5  | 9.0  | 1.0                                                                           | 10.5 | 1.0                                                                          | 9.5  |       |
| $t_{PLZ}$ | Output Disable Time                  | 3.3                         | 2.5                                                | 7.5  | 10.5 | 1.0                                                                           | 13.0 | 2.5                                                                          | 11.5 | ns    |
|           |                                      | 5.0                         | 2.0                                                | 6.5  | 9.0  | 1.0                                                                           | 11.0 | 2.0                                                                          | 9.5  |       |

**Note:**

6. Voltage range 3.3 is  $3.3\text{V} \pm 0.3\text{V}$ . Voltage range 5.0 is  $5.0\text{V} \pm 0.5\text{V}$ .

**AC Electrical Characteristics for ACT**

| Symbol    | Parameter                            | $V_{CC}$ (V) <sup>(7)</sup> | $T_A = +25^\circ\text{C}$ ,<br>$C_L = 50\text{pF}$ |      |      | $T_A = -55^\circ\text{C}$<br>to $+125^\circ\text{C}$ ,<br>$C_L = 50\text{pF}$ |      | $T_A = -40^\circ\text{C}$<br>to $+85^\circ\text{C}$ ,<br>$C_L = 50\text{pF}$ |      | Units |
|-----------|--------------------------------------|-----------------------------|----------------------------------------------------|------|------|-------------------------------------------------------------------------------|------|------------------------------------------------------------------------------|------|-------|
|           |                                      |                             | Min.                                               | Typ. | Max. | Min.                                                                          | Max. | Min.                                                                         | Max. |       |
| $t_{PLH}$ | Propagation Delay,<br>Data to Output | 5.0                         | 2.0                                                | 6.5  | 9.0  | 1.0                                                                           | 10.0 | 1.5                                                                          | 10.0 | ns    |
| $t_{PHL}$ | Propagation Delay,<br>Data to Output | 5.0                         | 2.0                                                | 7.0  | 9.0  | 1.0                                                                           | 10.0 | 1.5                                                                          | 10.0 | ns    |
| $t_{PZH}$ | Output Enable Time                   | 5.0                         | 1.5                                                | 6.0  | 8.5  | 1.0                                                                           | 9.5  | 1.0                                                                          | 9.5  | ns    |
| $t_{PZL}$ | Output Enable Time                   | 5.0                         | 2.0                                                | 7.0  | 9.5  | 1.0                                                                           | 11.0 | 1.5                                                                          | 10.5 | ns    |
| $t_{PHZ}$ | Output Disable Time                  | 5.0                         | 2.0                                                | 7.0  | 9.5  | 1.0                                                                           | 11.0 | 1.5                                                                          | 10.5 | ns    |
| $t_{PLZ}$ | Output Disable Time                  | 5.0                         | 2.5                                                | 7.5  | 10.0 | 1.0                                                                           | 11.5 | 2.0                                                                          | 10.5 | ns    |


**Note:**

7. Voltage range 5.0 is  $5.0\text{V} \pm 0.5\text{V}$ .

**Capacitance**

| Symbol   | Parameter                     | Conditions             | Typ  | Units |
|----------|-------------------------------|------------------------|------|-------|
| $C_{IN}$ | Input Capacitance             | $V_{CC} = \text{OPEN}$ | 4.5  | pF    |
| $C_{PD}$ | Power Dissipation Capacitance | $V_{CC} = 5.0\text{V}$ | 45.0 | pF    |

## Physical Dimensions




**Figure 1. 20-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300" Wide**

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings:

<http://www.fairchildsemi.com/packaging/>

## Physical Dimensions (Continued)



M20DREVC

Figure 2. 20-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide



Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings:

<http://www.fairchildsemi.com/packaging/>




## Physical Dimensions (Continued)



DIMENSIONS ARE IN MILLIMETERS

## NOTES:

- CONFORMS TO JEDEC REGISTRATION MO-153, VARIATION AC, REF NOTE 6, DATE 7/93.
- DIMENSIONS ARE IN MILLIMETERS.
- DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLDS FLASH, AND TIE BAR EXTRUSIONS.
- DIMENSIONS AND TOLERANCES PER ANSI Y14.5M, 1982.




MTC20REV D1

Figure 3. 20-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings:

<http://www.fairchildsemi.com/packaging/>

**Physical Dimensions** (Continued)**NOTES:**

- A. CONFORMS TO JEDEC REGISTRATION MS-001, VARIATIONS AD.
- B. ALL DIMENSIONS ARE IN MILLIMETERS
- C. DOES NOT INCLUDE MOLD FLASH OR PROTRUSIONS. MOLD FLASH OR PROTRUSIONS SHALL NOT EXCEED 0.25MM.
- D. DOES NOT INCLUDE DAMBAR PROTRUSIONS. DAMBAR PROTRUSIONS SHALL NOT EXCEED 0.25MM.
- E. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
- F. DRAWING FILE NAME: N20AREV8


**Figure 4. 20-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300" Wide**

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings:

<http://www.fairchildsemi.com/packaging/>

## Physical Dimensions (Continued)



## NOTES:

- CONFORMS TO JEDEC REGISTRATION MO-150, VARIATION AE, DATE 1/94.
- DIMENSIONS ARE IN MILLIMETERS.
- DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
- DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994.

MSA20REVB

Figure 5. 20-Lead Shrink Small Outline Package (SSOP), JEDEC MO-150, 5.3mm Wide

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings:

<http://www.fairchildsemi.com/packaging/>



## TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

|                                                                                                |                                              |                                        |                                                                                                                 |
|------------------------------------------------------------------------------------------------|----------------------------------------------|----------------------------------------|-----------------------------------------------------------------------------------------------------------------|
| ACEx <sup>®</sup>                                                                              | FPS <sup>™</sup>                             | PDP-SPM <sup>™</sup>                   | SyncFET <sup>™</sup>                                                                                            |
| Build it Now <sup>™</sup>                                                                      | FRFET <sup>®</sup>                           | Power220 <sup>®</sup>                  |  SYSTEM GENERAL <sup>®</sup> |
| CorePLUS <sup>™</sup>                                                                          | Global Power Resource <sup>SM</sup>          | Power247 <sup>®</sup>                  | The Power Franchise <sup>®</sup>                                                                                |
| CROSSVOLT <sup>™</sup>                                                                         | Green FPS <sup>™</sup>                       | POWEREDGE <sup>®</sup>                 | the power <sup>™</sup>                                                                                          |
| CTL <sup>™</sup>                                                                               | Green FPS <sup>™</sup> e-Series <sup>™</sup> | Power-SPM <sup>™</sup>                 | franchise                                                                                                       |
| Current Transfer Logic <sup>™</sup>                                                            | GTO <sup>™</sup>                             | PowerTrench <sup>®</sup>               | TinyBoost <sup>™</sup>                                                                                          |
| EcoSPARK <sup>®</sup>                                                                          | i-Lo <sup>™</sup>                            | Programmable Active Droop <sup>™</sup> | TinyBuck <sup>™</sup>                                                                                           |
| EZSWITCH <sup>™</sup> *                                                                        | IntelliMAX <sup>™</sup>                      | QFET <sup>®</sup>                      | TinyLogic <sup>®</sup>                                                                                          |
|  <sup>™</sup> | ISOPLANAR <sup>™</sup>                       | QS <sup>™</sup>                        | TINYOPTO <sup>™</sup>                                                                                           |
|  <sup>®</sup> | MegaBuck <sup>™</sup>                        | QT Optoelectronics <sup>™</sup>        | TinyPower <sup>™</sup>                                                                                          |
| Fairchild <sup>®</sup>                                                                         | MICROCOUPLER <sup>™</sup>                    | Quiet Series <sup>™</sup>              | TinyPWM <sup>™</sup>                                                                                            |
| Fairchild Semiconductor <sup>®</sup>                                                           | MicroFET <sup>™</sup>                        | RapidConfigure <sup>™</sup>            | TinyWire <sup>™</sup>                                                                                           |
| FACT Quiet Series <sup>™</sup>                                                                 | MicroPak <sup>™</sup>                        | SMART START <sup>™</sup>               | μSerDes <sup>™</sup>                                                                                            |
| FACT <sup>®</sup>                                                                              | MillerDrive <sup>™</sup>                     | SPM <sup>®</sup>                       | UHC <sup>®</sup>                                                                                                |
| FAST <sup>®</sup>                                                                              | Motion-SPM <sup>™</sup>                      | STEALTH <sup>™</sup>                   | Ultra FRFET <sup>™</sup>                                                                                        |
| FastvCore <sup>™</sup>                                                                         | OPTOLOGIC <sup>®</sup>                       | SuperFET <sup>™</sup>                  | UniFET <sup>™</sup>                                                                                             |
| FlashWriter <sup>®</sup> *                                                                     | OPTOPLANAR <sup>®</sup>                      | SuperSOT <sup>™</sup> -3               | VCX <sup>™</sup>                                                                                                |
|                                                                                                |                                              | SuperSOT <sup>™</sup> -6               |                                                                                                                 |
|                                                                                                |                                              | SuperSOT <sup>™</sup> -8               |                                                                                                                 |

\* EZSWITCH<sup>™</sup> and FlashWriter<sup>®</sup> are trademarks of System General Corporation, used under license by Fairchild Semiconductor.

## DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

## PRODUCT STATUS DEFINITIONS

### Definition of Terms

| Datasheet Identification | Product Status         | Definition                                                                                                                                                                                               |
|--------------------------|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Advance Information      | Formative or In Design | This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.                                                                       |
| Preliminary              | First Production       | This datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design. |
| No Identification Needed | Full Production        | This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.                                               |
| Obsolete                 | Not In Production      | This datasheet contains specifications on a product that has been discontinued by Fairchild Semiconductor. The datasheet is printed for reference information only.                                      |

Rev. I32