



## FEATURES:

- Spade lug attaches securely to a screw terminal while the medium size alligator test clip can quickly grab onto terminal points.
- Spade lug and alligator bodies are nickel plating for tarnish resistance
- The alligator features a flex boot for insulation protection.
- Alligators clip has .187" (4.75mm) max. jaw opening.

## MATERIALS:

Alligator: Body: Steel, Nickel Plated

Spring: Stainless Steel

Flex Boot: Vinyl

Wire: 18 AWG, Stranding: 65 X 36 tinned copper, PVC Insulation, .144" (3.66 mm) O.D.

Marking: "POMONA 1960-XX"

Spade Lug: Body: Brass, Nickel Plated

Insulation: Polypropylene molded to the spade lug and wire. Color matches wire.

## RATINGS:

Operating Voltage: 150 VRMS

Current: 5 Amperes

Operating Temperature: +50°C (+122°F)

## ORDERING INFORMATION: Model 1960-XX-\*

XX = Length in inches

Standard Lengths: 4" (10.16cm), 8" (20.32cm), 12" (30.48cm), 24" (60.96cm), 36" (91.44cm), 48" (121.92cm) & 60" (152.40cm). Additional lengths can be quoted upon request.

\* = Color of Flex Boot and Wire, -0 Black, -2 Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[1960-48-2](#) [1960-48-0](#) [1960-12-2](#) [1960-12-0](#) [1960-60-2](#) [1960-60-0](#) [1960-24-0](#) [1960-24-2](#)