



SPECIFICATIONS

PARAMETERS	VALUES	UNITS
Rated Input Power	0.1	W
Maximum Input Power	0.2	W
Impedance (1 kHz / 1V)	$8 \pm 15\%$	Ohm
Output Sound Pressure Level @ 50 cm (At 0.8, 1.0, 1.2 and 1.5 kHz average, 0.2 W)	83 ± 3	dB
Resonant Frequency	$450 \pm 20\%$	Hz
Frequency Range	$450 \sim 5000$	Hz
Operating Temperature Range	$-20 \sim +60$	°C
Storage Temperature Range	$-30 \sim +70$	°C
Housing Material	Metal	
Weight	14.1	g



REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
-	RELEASED FROM ENGINEERING	05/07/02	



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE
OR WITHDRAWAL WITHOUT NOTICE.

DRAWING NAME
AT50008

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN MILLIMETERS
TOLERANCES ARE:
FRACTIONS DECIMALS ANGLES
 \pm $XX \pm 0.3$ \pm $XXX \pm$

APPROVALS DATE
DRAWN **RABL** 05/02

CHECKED

APPROVED **S.J.** 05/07/02

DO NOT SCALE DRAWING

 **projects[®]
unlimited**

Dayton, Ohio

DYNAMIC SPEAKER
AT-50008

SIZE **A** MATERIAL DRAWING NO.
AT50008.DWG

NOT TO SCALE MAX. WT. SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AT-50008](#)