


REV	ECN	APP'D
-	4503	10 10/31/01
A	5742	PN 12/28/05

SCFF SERIES PART NUMBERING SCHEME



RATINGS

CURRENT - 15 A
VOLTAGE - 300V
U.L. FILE NO. PENDING



RATINGS

CURRENT - 15 A
VOLTAGE - 300 V
CSA FILE NO. PENDING

DIN VDE 0627:1986
DIN VDE 0110-1:1989
EN 60947-1:1991
EN 60947-7-1:1992

CURRENT -15 A
VOLTAGE - 300 V
TUV FILE NO. PENDING

CONSULT PCD FOR PART NO. AND
AVAILABILITY OF FOLLOWING OPTIONS:
*CUSTOM COLORS *CUSTOM KEYING
*CUSTOM MARKING *SELECTIVE CONTACT LOADING
*NUMBER OF POSITIONS 9-24


INSTALLATION RECOMMENDATIONS:

WIRE RANGE: AWG #12-28, STRANDED OR SOLID,
WIRE STRIP LENGTH: .250" (6,35mm)




MATERIALS:

HOUSING: PPO, UL 94 V-0
CONTACT: PHOSPHOR BRONZE, TIN FINISH
SPRING CLAMP: STAINLESS STEEL

MAX OPERATING TEMP: 105°C

DIMENSIONS ANSI Y14.5M UNITS: INCHES Pro/E FILE	TOLERANCES .XX ±0.01 .XXX ±0.005 ANGLES ±2.0°	PROJECTION 	Amphenol Pcd ENGR C. LUSHUA 7/17/01 CHKD A. PATRIE 10/30/01 APPD I. QUINN 10/31/01	TITLE SCF SERIES PLUGGABLE TERMINAL BLOCK		
ORIGINAL STAMPED IN RED	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD, INC. PEABODY, MA, USA			SIZE A	DWG NO. SCFF02210	REV A
				CODE: 58982	SCALE: NONE	SHEET 1 OF 2

L=NUM OF POS X CL SPACING
A=NUM OF POS X CL SPACING+.060



SIZE	DWG NO.	REV
A	SCFF02210	A
CODE: 58982	SCALE: NONE	SHEET 2 OF 2