

200 V - 1,000 V Rectifiers

5.0 A Forward Current
2000 ns Recovery Time

1N5550 1N5551
1N5552 1N5553
1N5554

AXIAL LEADED
HERMETICALLY SEALED
MIL-PRF-19500/420

JAN JANTX JANTXV




3

ELECTRICAL CHARACTERISTICS AND MAXIMUM RATINGS

Part Number	Working Reverse Voltage (Vrwm)	Average Rectified Current (Io)		Reverse Current @ Vrwm (Ir)		Forward Voltage (Vf)		1 Cycle Surge Current tp=8.3ms (Ifsm)	Repetitive Surge Current (Ifrm)	Reverse Recovery Time (3) (Trr)	Thermal Impedance θ_{J-L}			Junction Cap. @50VDC @ 1kHz (Cj)
		55°C(1)	100°C(2)	25°C	100°C	25°C		25°C	25°C	25°C	L=.125	L=.375	L=.500	25°C
	Volts	Amps	Amps	µA	µA	Volts	Amps	Amps	Amps	ns	°C/W	°C/W	°C/W	pF
1N5550 1N5551	200 400	5.0 5.0	2.0 2.0	1.0 1.0	25 25	1.2 1.2	9.0 9.0	150 150	25 25	2000 2000	9 9	20 20	25 25	35 35
1N5552 1N5553	600 800	5.0 5.0	2.0 2.0	1.0 1.0	25 25	1.2 1.3	9.0 9.0	150 150	25 25	2000 2000	9 9	20 20	25 25	35 35
1N5554	1000	5.0	2.0	1.0	25	1.3	9.0	150	25	2000	9	20	25	35

(1)TL=55°C L=0.375" (2)TL=100°C L=0.375" (3)If=0.5A, Ir=1.0A, Irr=0.25A • Op.Temp.= -65°C to +175°C Stg.Temp.= -65°C to +200°C



Dimensions: In. (mm) • All temperatures are ambient unless otherwise noted. • Data subject to change without notice.



VOLTAGE MULTIPLIERS INC.
8711 W. Roosevelt Ave.
Visalia, CA 93291

TEL 559-651-1402
FAX 559-651-0740
www.voltagemultipliers.com

1N5550 1N5551 1N5552 1N5553 1N5554

