





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AA	22	A		REV PER EC 0S11-0201-04	10JUN2005	AF SF



- 1 MATERIAL: HOUSING- PCT POLYESTER, BLACK, IR REFLOW COMPATIBLE, UL 94V-0. TERMINALS - 0.33[.013] THICK PHOS BRONZE PLATED WITH 1.27µm[.000050] MIN THICK HARD GOLD IN LOCALIZED AREA AND 3.81µm [.000150] MIN THICK MATTE TIN IN SOLDER AREA OVER 1.27[.000050] MIN THICK NICKEL UNDERPLATE. SHIELD - 0.254[.010] THICK COPPER ALLOY PLATED WITH 2.03µm[.000080] MINIMUM THICK BRIGHT TIN OVER 1.27µm[.000050] MINIMUM THICK NICKEL.
- 2 JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
3. ALL DIMENSIONS SHOWN ARE NOMINAL UNLESS OTHERWISE SPECIFIED.
- 4 SHORTING PATH IS OPENED BY INSERTION OF MODULAR PLUG.

SUGGESTED PC BOARD LAYOUT
COMPONENT SIDE
SEE APPLICATION SPECIFICATION
SCALE 2:1

PC BOARD GROUND SHIELD		5558846-1	
DESCRIPTION		PART NO	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. FERNANDEZ-DOCKS 10JUN2005 CHK J. WESTMAN 10JUN2005 APD S. FLICKINGER 10JUN2005	
DIMENSIONS: INCHES		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.254 [.01] 3 PLC ± 0.127 [.005] 4 PLC ± - ANGLES ± - FINISH		Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
PRODUCT SPEC		MODULAR JACK ASSEMBLY, 8 PORT, 8 POSITION, RIGHT ANGLE, SHORTING, SHIELDED	
APPLICATION SPEC		SIZE CAGE CODE DRAWING NO	
MATERIAL 1		RESTRICTED TO	
WEIGHT -		A1 00779 ©=5558846	
RESTRICTED CUSTOMER		SCALE 1:1 SHEET 1 OF 1 REV A	