



Micro Commercial Components
21201 Itasca Street Chatsworth
CA 91311
Phone: (818) 701-4933
Fax: (818) 701-4939

SF500 GP thru SF504 GP

Features

- Low forward voltage, high current capability
- Hermetically sealed
- High surge capability
- Superfast recovery times-epitaxial construction

Maximum Ratings

- Operating Temperature: -55°C to +150°C
- Storage Temperature: -55°C to +150°C
- Maximum Thermal Resistance; 25.0°C/W Junction To Lead

Microsemi Catalog Number	Device Marking	Maximum Reccurent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
SF500GP	SF500GP	50V	35V	50V
SF501GP	SF501GP	100V	70V	100V
SF502GP	SF502GP	200V	140V	200V
SF503GP	SF503GP	300V	210V	300V
SF504GP	SF504GP	400V	280V	400V


Electrical Characteristics @ 25°C Unless Otherwise Specified

Average Forward Current	$I_{F(AV)}$	5.0A	$T_A = 55^\circ\text{C}$
Peak Forward Surge Current	I_{FSM}	150A	8.3ms, half sine
Maximum Instantaneous Forward Voltage SF500-SF502 SF503-SF504	V_F	.95V 1.25V	$I_{FM} = 5.0A$; $T_A = 25^\circ\text{C}^*$
Maximum DC Reverse Current At Rated DC Blocking Voltage	I_R	5.0uA 300uA	$T_A = 25^\circ\text{C}$ $T_A = 125^\circ\text{C}$
Maximum Reverse Recovery Time	T_{rr}	35nS	Test Conditions $I_F = .5A, I_R = 1A, I_{rr} = .25A$
Typical Junction Capacitance	C_J	45pF	Measured at 1.0MHz, $V_R = 4.0V$

*Pulse test: Pulse width 300 μsec , Duty cycle 2%

5 Amp Surper Fast Recovery Rectifiers 50 - 400Volts

DO-201AD



DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	---	.370	---	9.50	
B	---	.250	---	6.40	
C	.048	.052	1.20	1.30	
D	1.000	---	25.40	---	

SF500GP thru SF504GP




Fig. 1-REVERSE RECOVERY TIME CHARACTERISTIC AND TEST CIRCUIT DIAGRAM




Fig. 2-MAXIMUM AVERAGE FORWARD CURRENT RATING




Fig. 3-MAXIMUM AVERAGE FORWARD CURRENT RATING




Fig. 4-FORWARD CURRENT DERATING CURVE




Fig. 5-MAXIMUM NON-REPETITIVE SURGE CURRENT




Fig. 6-TYPICAL JUNCTION CAPACITANCE