





FED. MFG. CODE 91929

CATALOG LISTING
602EN226-6B

CATALOG LISTING



CIRCUIT DIAGRAM



- 1 - CORROSION RESISTANT STEEL ENCLOSURE
- 2 - SWITCH SEALED PER MIL-S-8805 SYMBOL 4
- 3 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
- 4 - CIRCUIT DIAGRAM, CATALOG LISTING AND DATE CODE AND FEDERAL MFG. CODE 91929 ARE SHOWN ON NAMEPLATE
- 5 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805
- 6 - NOTED ELECTRICAL RATINGS APPLY AS SPECIFIED IN MIL-S-8805/43 UP TO +185°F
- 7 - BASIC SWITCHES HAVE GOLD CONTACTS

ANSI Y14.5M-1982 APPLIES

ISSUE	M	CATALOG LISTING	602EN226-6B	PAGE 1 OF 1	RELEASE NO. PR-22349	REPLACES

REVISIONS	
A	PR- 22349
J J A 5 SEP 96	
B	CO- 84732
M A M 25 JUL 97	

[illegible]

REPLACES

PR-22349

RELEASE	
---------	--

11

CHECK

1

[illegible]

CHECK	
-------	--

P. 96

5	

	Y
X	

6	96
---	----

FES +

J A

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CHARACTERISTICS

OPERATING FORCE — — — — — 6 -12 LB
FULL OVERTRAVEL FORCE --- 30 LB MAX
RELEASE FORCE — — — — — 4 LB MIN
PRETRAVEL — — — — — .040 MAX
DIFFERENTIAL TRAVEL — — — .020 MAX
OVERTRAVEL — — — — — .125 MIN


ELECTRICAL DATA

CONTACT ARRANGEMENT

2X S P D T

LOAD	28 VDC 	
	SEA LEVEL	50,000 FT.
RES	1 AMP	1 AMP
IND	0.5 AMP	0.5 AMP

THIRD ANGLE PROJECTION



SCALE	FULL
-------	------

DO NOT SCALE PRINT

**UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE**

ONE PLACE	(.0)	$\pm .030$
TWO PLACE	(.00)	$\pm .015$
THREE PLACE	(.000)	$\pm .005$
ANGLES		$\pm$

WEIGHT	0.4 LB MAX
--------	------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[602EN226-6B](#)