


SMD Power Inductors (NR series H type)

NRH3010T4R7MN



■ Features

- Item Summary
4.7 μ H($\pm 20\%$), 850mA, 900mA
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Taping 2000pcs

■ Products characteristics table


CaseSize (EIA/JIS)	-/3010
Inductance	4.7 μ H($\pm 20\%$)
Inductance Measuring Frequency	100kHz
Rated Current -Saturation Current	850mA
Rated Current -Temperature Rise Current	900mA
DC Resistance (max)	0.204 Ω
Avg. of DC.Resistance	0.17 Ω
Temperature Range	-25°C to 120°C
Self-resonant Frequency (min)	50MHz
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Reflow

■ External Dimensions

L	3mm ± 0.1
W	3mm ± 0.1
H	1mm max

■ Recommended Land Patterns

【推奨ランドパター】
実装上の注意
・実装状態を確認の上ご使用ください。よろしくお願いいたします。
・本製品のはんだ付けはリフローはんだ工法に限ります。
【Recommended Land Patterns】
Surface Mounting
・Mounting and soldering conditions should be checked beforehand.
・Applicable soldering process to these products is reflow soldering only.



Type	A	B	C
NR 3010, NRH3010,			
NR 3012, NRH3012, NRV3012,	0.8	2.2	2.7
NR 3015, NRS3015			

unit:mm

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
Before making final selection, please check product specification.

2014.06.06