

THIS DRAWING IS UNPUBLISHED.





RELEASED FOR PUBLICATION

© COPYRIGHT — TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F2	ECR-17-001115	28JAN2018	SD	PS



RECOMMENDED HOLE LAYOUT

- 1 PART NUMBER AND DATE CODE MARKED IN APPROXIMATE LOCATION SHOWN
- 2 CONTACT: DUPLEX PLATED: .000010 GOLD ON CONTACT AREA, .000150-.000300 BRIGHT TIN-LEAD ON SOLDER LEADS, ALL OVER .000050 MINIMUM NICKEL.
3. TOLERANCE IS NON-CUMULATIVE.
- 4 POINT OF MEASUREMENT FOR PLATING THICKNESS (MEASURED INSIDE CONTACT BEAMS)
- 5 POINT OF CONTACT MEASUREMENT.
6. MATERIAL: HOUSING: GLASS FILLED POLYESTER-COLOR: BLACK
CONTACT: PHOSPHOR BRONZE
- 7 CONTACT: DUPLEX PLATED: .000010 GOLD ON CONTACT AREA, .000150-.000300 MATTE TIN ON SOLDER LEADS, ALL OVER .000050 MINIMUM NICKEL.
- 8 ROHS 2002/95/EC COMPLIANT
- 9 TYCO LOGO AND CSA LOGO ARE MOLDED INTO HOUSING, THIS LOCATION.
- 10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 14-5-81	TE Connectivity					
DIMENSIONS: INCHES		CHK 15-5-81						
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 20-5-81	NAME					
0 PLC ± -		PRODUCT SPEC	CONNECTOR ASSY., MOD II/IV DOUBLE ROW, .100 X .100 C/L, VERTICAL MOUNTED					
1 PLC ± -		APPLICATION SPEC						
2 PLC ± -		WEIGHT	SIZE CAGE CODE DRAWING NO RESTRICTED TO					
3 PLC ± -		CUSTOMER DRAWING	A2 00779 C=102766					
4 PLC ± -		SCALE 4:1	SHEET 1 OF 1					
ANGLES ± -		REV F2						
FINISH								
CONTACTS: SEE TABLE								