




THIS DRAWING AND THE SPECIFICATIONS CONTAINED HEREIN ARE CONFIDENTIAL AND PROPRIETARY. THEY ARE THE PROPERTY OF Aavid Thermal Technologies Inc. AND SHALL NOT BE REPRODUCED OR COPIED OR USED IN WHOLE OR IN PART AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION. THIS IS AN UNPUBLISHED WORK PROTECTED UNDER THE FEDERAL COPYRIGHT LAWS. 1995



**ROHS COMPLIANT**  
PER Aavid SPEC: ROHS - 9000

NOTES:

- 1. UNLESS OTHERWISE NOTED, USE MINIMUM BEND RADIUS (.020) [(1.51)].
- 2. MATERIAL: 1050 ANNEALED SPRING STEEL .016 [.41] THICK.
- 3. FINISH: ZINC/CLEAR .0001 MINIMUM THICKNESS (TRIVALENT) AND BAKE FOR 3.5 HOURS AT 350/370 DEGREES F FOR HYDROGEN EMBRITTLEMENT RELIEF.
- 4. PART IS DESIGNED FOR USE WITH METAL THICKNESS OF .05 [.27] TO .125 [3.12].

|                           |            |
|---------------------------|------------|
| FINISH                    | SEE NOTE 3 |
| U/O                       |            |
| MAT'L                     | SEE NOTE 2 |
| TOLERANCE<br>UNLESS NOTED |            |
| .XX = ±.015 [ ±.38 ]      |            |
| .XXX = ±.010 [ ±.25 ]     |            |
| ANGULAR ± 3°              |            |

|                                                                                                                                                                               |         |                         |       |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------|-------------------------|-------|
|                                                                                                                                                                               |         |                         |       |
| A                                                                                                                                                                             | 7/18/06 | RELEASE PER ECN# 018980 | MIKEL |
| REV.                                                                                                                                                                          | DATE    | DESCRIPTION             | CHK'D |
| <div>AAVID<br/>THERMALLOY</div> <div>80 COMMERCIAL ST.<br/>CONCORD, N.H.<br/>03301</div> |         |                         |       |
| DRAWING NO.                                                                                                                                                                   |         | 043660                  |       |
| STANDARD DESCRIPTION<br>THM,16743-1 REV E-G                                                                                                                                   |         |                         |       |
| DATE                                                                                                                                                                          | DRAWN   | ENGR.                   | APP'D |
| 04/25/03                                                                                                                                                                      | P.C.    |                         |       |
| REF: CLP-101G                                                                                                                                                                 |         |                         | SHEET |
| SCALE<br>4.000                                                                                                                                                                |         |                         |       |